

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331471-927

Luminaire Tested: **S122DIW-S290D710U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331471-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D710U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3280.9 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20
4	72	62	54	48	64	56	49	44	45	40	37	35	31	29	25	23	22	17
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	15
6	61	49	42	36	54	45	38	33	36	31	28	28	25	22	21	19	17	14
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	17	15	14	11
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7561	7561	7561	7561
5°	8475	7609	6744	7609
10°	9712	7547	5835	7547
15°	10745	7408	5157	7408
20°	10581	7261	4699	7261
25°	9540	7062	4411	7062
30°	7884	6747	4200	6747
35°	5746	6416	4050	6416
40°	4591	6028	3967	6028
45°	4010	5576	3854	5576
50°	3770	5139	3778	5139
55°	3474	4695	3676	4695
60°	3184	4224	3523	4224
65°	2904	3801	3370	3801
70°	2634	3389	3144	3389
75°	2339	2932	2782	2932
80°	2008	2427	2241	2427
85°	1797	1797	1334	1797



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	1.4
10°-20°	129.6	4.0
20°-30°	188.1	5.7
30°-40°	198.5	6.1
40°-50°	175.8	5.4
50°-60°	140.3	4.3
60°-70°	95.4	2.9
70°-80°	48.9	1.5
80°-90°	13.7	0.4
90°-100°	25.6	0.8
100°-110°	93.8	2.9
110°-120°	250.6	7.6
120°-130°	413.7	12.6
130°-140°	440.0	13.4
140°-150°	408.9	12.5
150°-160°	328.8	10.0
160°-170°	211.9	6.5
170°-180°	72.9	2.2
0°-30°	362.4	11.0
0°-40°	560.9	17.1
0°-60°	877.0	26.7
0°-90°	1034.9	31.5
90°-120°	369.9	11.3
90°-150°	1632.5	49.8
90°-180°	2246.0	68.5
0°-180°	3280.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	468	468	468	468	468	
5°	523	470	416	470	523	52
15°	643	443	308	443	643	177
25°	536	396	248	396	536	242
35°	292	326	206	326	292	190
45°	176	244	169	244	176	138
55°	123	167	131	167	123	111
65°	76	100	88	100	76	76
75°	38	47	45	47	38	40
85°	10	10	7	10	10	11
90°	15	1	15	1	15	7
95°	24	36	24	36	24	22
105°	42	169	42	169	42	44
115°	46	319	46	319	46	114
125°	474	451	474	451	474	410
135°	576	558	576	558	576	444
145°	657	647	657	647	657	411
155°	713	713	713	713	713	329
165°	749	751	749	751	749	212
175°	764	768	764	768	764	73
180°	766	766	766	766	766	



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	489.8	490.0	490.3	488.0	487.7	487.7	485.7	483.9	481.9	479.2	479.5
5°	522.9	524.9	525.6	523.5	520.2	519.9	516.8	511.8	507.1	503.4	500.7
7.5°	562.4	563.2	561.5	558.6	556.3	551.9	546.2	540.7	532.8	525.7	520.4
10°	592.4	593.5	590.4	586.3	582.9	577.8	569.6	561.1	550.9	541.0	533.1
12.5°	615.1	617.8	613.9	613.4	607.5	600.6	590.7	586.5	572.0	558.3	549.7
15°	642.8	642.6	643.0	639.5	635.3	634.1	623.8	612.4	592.1	583.9	569.9
17.5°	634.8	637.5	638.8	638.7	638.7	637.9	634.6	627.5	617.3	604.1	588.0
20°	615.8	619.4	620.0	624.1	626.5	629.5	630.7	628.8	622.5	611.5	597.5
22.5°	586.5	587.5	589.1	595.6	600.6	608.3	612.3	619.0	616.6	611.2	599.4
25°	535.5	533.8	540.0	543.3	555.0	567.2	576.1	585.7	594.4	599.6	596.2
27.5°	474.4	471.7	481.2	489.8	499.2	512.5	526.2	542.5	556.0	572.9	578.7
30°	422.9	424.5	433.5	442.7	457.1	475.8	491.3	509.1	528.4	547.2	560.4
32.5°	367.3	373.5	379.2	393.3	406.0	426.8	449.6	471.8	495.8	517.3	537.7
35°	291.5	298.7	306.7	316.9	334.7	355.4	377.6	407.6	440.4	469.7	493.8
37.5°	245.4	244.2	248.7	256.2	270.6	287.3	312.8	342.5	381.0	415.5	449.6
40°	217.8	217.1	220.2	227.1	238.1	250.3	272.7	298.7	334.5	376.7	417.2
42.5°	198.8	199.2	201.0	205.8	213.3	223.4	240.1	262.3	295.1	334.8	378.3
45°	175.6	176.9	178.9	181.3	185.5	193.8	203.2	219.0	244.9	278.1	320.8
47.5°	159.0	159.1	161.1	163.1	165.6	170.3	178.0	187.9	206.2	233.1	270.0
50°	150.1	148.9	150.3	151.9	154.6	157.8	162.9	172.2	184.4	206.2	237.0
52.5°	139.1	139.2	140.5	141.1	143.5	146.7	151.3	157.8	168.9	185.9	211.2
55°	123.4	124.4	125.1	126.1	128.3	130.6	134.3	138.6	147.2	159.9	178.7
57.5°	108.7	109.0	109.7	111.8	113.1	115.3	118.7	122.6	128.3	137.7	151.8
60°	98.6	98.6	100.1	100.9	102.7	104.9	107.6	111.4	116.5	124.1	135.5
62.5°	89.4	89.3	89.8	91.3	92.7	94.7	97.4	100.6	105.4	112.3	121.5
65°	76.0	75.6	76.7	77.0	78.4	80.4	82.6	86.0	89.8	94.8	103.1
67.5°	63.0	63.5	64.0	64.6	65.4	67.6	69.0	71.4	74.6	78.8	84.4
70°	55.8	55.8	55.8	56.3	57.4	58.5	59.9	61.9	65.0	68.5	73.6
72.5°	47.7	48.3	48.9	48.6	49.9	50.5	52.3	53.4	56.3	58.6	63.1
75°	37.5	37.5	37.5	38.3	38.9	39.4	40.5	41.6	43.0	45.9	48.2
77.5°	28.0	27.9	28.0	28.3	28.8	29.5	29.8	30.7	32.1	33.4	35.4
80°	21.6	21.9	22.1	22.5	22.5	22.8	23.1	24.3	25.2	26.1	27.3
82.5°	16.7	16.8	16.8	16.9	17.0	17.3	17.7	18.1	18.5	19.2	20.1
85°	9.7	9.5	9.5	9.9	9.7	9.7	10.1	10.5	10.5	10.6	11.2
87.5°	6.7	6.7	6.8	6.6	6.6	6.6	6.5	6.2	6.3	6.3	6.2
90°	15.0	14.7	14.5	14.3	14.0	13.5	12.9	12.4	11.7	11.1	10.1
92.5°	15.0	14.8	14.7	14.5	14.4	14.2	13.9	13.5	13.2	12.8	12.4
95°	23.8	24.0	24.1	24.2	24.3	24.1	23.4	22.9	22.3	21.6	20.8
97.5°	31.8	31.7	31.5	31.4	31.2	30.9	30.4	29.9	29.5	28.9	26.9
100°	37.2	36.9	36.7	36.4	36.2	35.6	34.5	33.6	32.6	31.6	29.5
102.5°	39.8	39.5	39.1	38.8	38.4	37.6	36.4	35.1	33.7	32.5	30.0
105°	42.1	41.7	41.2	40.6	40.2	39.2	37.9	36.5	35.2	33.8	31.5
107.5°	43.3	42.9	42.4	41.9	41.4	41.8	43.3	44.6	45.9	47.4	48.7
110°	43.8	43.3	42.9	42.3	41.8	47.8	60.0	72.4	84.8	97.0	132.7



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	44.3	43.9	43.5	43.1	42.7	65.0	110.0	154.9	199.9	244.8	253.6
115°	45.5	54.3	63.2	72.1	81.0	113.9	171.0	228.1	285.1	342.1	339.1
117.5°	185.7	214.8	244.0	273.1	302.3	323.8	337.5	351.4	365.2	379.0	376.8
120°	338.3	354.9	371.5	388.2	404.8	412.4	410.9	409.5	408.0	406.5	404.3
122.5°	422.2	425.4	428.6	431.8	435.1	436.3	435.3	434.4	433.6	432.7	430.2
125°	474.1	473.8	473.4	473.0	472.7	472.1	471.2	470.3	469.4	468.6	466.3
127.5°	507.0	506.9	506.8	506.8	506.7	506.0	504.8	503.5	502.2	501.0	499.2
130°	527.4	527.5	527.7	527.8	527.9	527.3	525.9	524.6	523.2	521.9	520.5
132.5°	547.4	547.5	547.6	547.7	547.9	547.3	546.2	545.0	543.8	542.7	541.4
135°	576.2	576.5	576.7	576.9	577.2	576.7	575.4	574.3	573.0	571.8	570.7
137.5°	602.5	602.9	603.3	603.7	604.2	603.8	602.5	601.3	600.2	599.0	597.7
140°	618.9	619.5	620.1	620.8	621.4	621.2	620.0	618.9	617.8	616.7	615.3
142.5°	634.9	635.5	636.1	636.8	637.3	637.2	636.1	635.1	634.1	633.1	631.5
145°	657.2	657.7	658.4	659.0	659.7	659.5	658.6	657.7	657.0	656.1	653.9
147.5°	676.8	677.3	677.9	678.3	678.9	678.8	678.2	677.6	676.9	676.2	674.1
150°	688.8	689.4	690.0	690.6	691.3	691.2	690.5	689.7	689.0	688.2	686.3
152.5°	698.9	699.8	700.6	701.4	702.3	702.3	701.6	700.8	700.1	699.3	697.4
155°	713.2	714.2	715.2	716.1	717.1	717.2	716.5	715.7	715.0	714.3	712.8
157.5°	726.1	727.1	728.1	729.0	730.0	730.1	729.2	728.4	727.5	726.7	725.6
160°	733.7	734.6	735.4	736.3	737.1	737.2	736.5	735.7	735.0	734.3	733.5
162.5°	739.9	740.9	742.0	743.1	744.2	744.3	743.4	742.6	741.7	740.9	740.3
165°	749.2	750.1	751.0	751.8	752.7	752.7	751.8	751.0	750.1	749.2	748.8
167.5°	755.1	756.2	757.3	758.4	759.5	759.6	758.8	758.0	757.1	756.2	755.9
170°	758.7	759.8	760.9	762.0	763.1	763.2	762.3	761.5	760.7	759.8	759.5
172.5°	761.3	762.4	763.5	764.6	765.7	765.9	765.0	764.1	763.3	762.4	762.2
175°	763.7	764.9	766.1	767.3	768.6	768.7	767.9	767.1	766.2	765.3	765.1
177.5°	765.1	766.0	766.8	767.8	768.7	768.7	768.0	767.4	766.7	766.0	765.9
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	480.5	479.3	478.6	476.0	473.7	471.4	470.7	471.0	467.8	464.8	463.5
5°	499.2	495.6	492.2	487.4	481.6	475.2	472.1	469.5	463.2	456.4	452.4
7.5°	515.9	510.8	504.2	495.1	486.7	476.8	470.5	464.9	455.7	446.1	440.1
10°	526.2	519.2	510.7	499.6	489.3	477.2	468.8	460.3	449.6	438.0	430.8
12.5°	535.0	525.5	517.2	502.9	490.8	475.6	465.6	453.7	442.4	428.6	421.6
15°	555.9	538.4	522.6	506.4	491.5	470.4	459.2	443.2	428.3	411.4	403.3
17.5°	572.0	552.4	527.5	506.9	489.5	466.1	449.8	430.6	413.0	393.6	382.6
20°	581.2	558.7	532.0	507.5	486.6	459.9	442.1	422.6	401.9	380.1	368.2
22.5°	586.7	563.1	536.5	505.3	480.9	455.0	432.5	411.0	390.1	366.5	354.1
25°	588.4	566.9	538.8	503.5	473.6	444.3	417.3	396.4	371.1	349.1	331.0
27.5°	579.9	564.4	537.4	500.1	465.3	431.0	400.9	377.3	350.5	326.7	308.4
30°	569.3	560.4	534.1	496.7	458.7	421.8	388.7	361.9	335.3	311.2	292.4
32.5°	553.1	551.2	528.1	491.8	451.6	410.2	375.9	348.8	319.2	295.6	277.7
35°	521.2	529.8	515.2	480.9	438.4	393.6	356.5	325.5	294.9	272.3	255.6
37.5°	478.3	499.8	496.0	464.9	420.4	375.5	334.5	302.2	273.1	250.2	233.8
40°	448.8	476.2	480.1	452.6	407.8	361.6	318.1	286.0	257.5	236.6	220.1
42.5°	417.2	449.1	459.9	437.9	394.0	346.8	303.5	270.1	241.9	221.7	207.0
45°	364.1	406.3	426.0	413.4	370.9	322.7	278.1	244.2	218.6	199.6	188.2
47.5°	314.4	360.6	387.0	382.5	345.2	297.5	253.3	220.9	196.0	180.8	170.6
50°	279.3	326.8	358.6	360.1	326.8	279.5	235.2	204.6	181.7	167.5	159.2
52.5°	248.7	294.1	328.8	336.5	306.2	260.8	219.0	188.5	168.3	155.3	147.9
55°	208.9	247.2	285.7	299.8	275.5	232.3	193.6	166.8	147.9	138.9	132.5
57.5°	173.7	205.7	241.2	256.7	241.8	204.8	168.5	145.2	129.9	122.0	117.0
60°	155.1	180.3	212.0	230.5	217.5	184.7	153.0	130.8	118.2	111.2	106.5
62.5°	137.8	160.2	187.0	203.9	196.9	165.8	137.4	117.9	107.0	100.4	97.0
65°	113.8	131.3	152.1	167.7	163.0	139.5	116.2	99.5	90.9	85.6	82.9
67.5°	93.6	106.4	120.7	134.4	130.7	114.0	95.4	82.3	75.9	71.4	69.7
70°	81.0	90.7	103.5	114.5	111.4	97.8	82.9	71.8	66.2	62.4	60.8
72.5°	68.9	76.8	86.7	95.6	93.6	82.1	69.9	61.5	57.1	53.6	52.4
75°	52.0	58.1	64.1	70.0	69.5	60.7	53.5	47.0	43.6	40.9	40.3
77.5°	38.4	41.8	45.9	49.4	48.4	43.3	37.7	34.0	31.5	29.7	29.4
80°	29.3	31.3	34.2	36.7	35.5	33.3	28.8	26.1	24.3	22.5	21.8
82.5°	21.3	23.2	25.0	26.4	25.3	23.4	20.6	18.8	17.7	16.5	16.2
85°	11.2	12.2	13.0	13.3	13.0	11.7	10.5	9.7	8.8	8.2	8.1
87.5°	6.2	5.9	5.8	5.8	5.1	4.8	4.0	3.2	3.4	3.6	3.5
90°	9.1	8.2	7.1	5.9	4.6	3.2	1.9	0.6	1.9	3.2	4.6
92.5°	11.9	11.4	10.9	10.7	10.9	10.9	11.1	11.2	11.1	10.9	10.9
95°	19.9	19.0	18.1	19.8	23.8	27.9	32.0	36.0	32.0	27.9	23.8
97.5°	25.0	23.0	21.0	25.7	37.2	48.6	60.0	71.5	60.0	48.6	37.2
100°	27.4	25.3	23.2	30.7	47.5	64.4	81.3	98.2	81.3	64.4	47.5
102.5°	67.6	85.1	102.6	113.1	116.7	120.3	123.9	127.5	123.9	120.3	116.7
105°	101.1	134.8	168.4	183.4	179.7	176.0	172.3	168.6	172.3	176.0	179.7
107.5°	128.1	168.4	208.7	227.4	224.4	221.5	218.5	215.5	218.5	221.5	224.4
110°	168.3	203.9	239.5	256.0	253.4	250.9	248.3	245.7	248.3	250.9	253.4



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	262.4	271.2	280.0	283.2	280.9	278.7	276.4	274.1	276.4	278.7	280.9
115°	336.0	333.0	329.9	327.3	325.2	323.1	321.0	318.9	321.0	323.1	325.2
117.5°	374.8	372.6	370.5	368.3	365.9	363.6	361.2	358.9	361.2	363.6	365.9
120°	402.0	399.8	397.6	395.6	393.7	391.9	390.1	388.2	390.1	391.9	393.7
122.5°	427.9	425.4	423.0	420.8	418.9	416.9	415.0	413.0	415.0	416.9	418.9
125°	463.9	461.6	459.2	457.2	455.7	454.1	452.5	450.8	452.5	454.1	455.7
127.5°	497.5	495.7	494.0	492.3	490.4	488.7	486.9	485.1	486.9	488.7	490.4
130°	519.1	517.8	516.4	514.8	512.8	510.8	508.8	506.8	508.8	510.8	512.8
132.5°	540.0	538.6	537.3	535.8	534.1	532.4	530.8	529.1	530.8	532.4	534.1
135°	569.6	568.5	567.4	565.8	563.8	561.8	559.8	557.9	559.8	561.8	563.8
137.5°	596.4	595.2	593.9	592.6	591.2	589.9	588.4	587.1	588.4	589.9	591.2
140°	613.9	612.6	611.2	610.1	609.1	608.1	607.1	606.2	607.1	608.1	609.1
142.5°	630.0	628.4	626.9	625.7	624.8	623.9	623.0	622.1	623.0	623.9	624.8
145°	651.9	649.7	647.7	646.7	646.8	647.0	647.1	647.2	647.1	647.0	646.8
147.5°	672.1	670.0	668.0	667.2	667.7	668.1	668.6	669.0	668.6	668.1	667.7
150°	684.3	682.3	680.3	679.8	680.6	681.5	682.4	683.3	682.4	681.5	680.6
152.5°	695.5	693.7	691.8	691.3	692.3	693.3	694.3	695.2	694.3	693.3	692.3
155°	711.3	709.9	708.4	708.2	709.3	710.4	711.5	712.6	711.5	710.4	709.3
157.5°	724.6	723.6	722.5	722.5	723.4	724.4	725.3	726.3	725.3	724.4	723.4
160°	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	733.5	732.8	732.1
162.5°	739.7	738.9	738.3	738.4	739.1	739.9	740.6	741.3	740.6	739.9	739.1
165°	748.5	748.1	747.7	747.9	748.7	749.4	750.1	750.9	750.1	749.4	748.7
167.5°	755.5	755.2	754.9	755.0	755.7	756.5	757.2	758.0	757.2	756.5	755.7
170°	759.3	759.0	758.8	759.0	759.8	760.5	761.2	762.0	761.2	760.5	759.8
172.5°	761.9	761.7	761.4	761.7	762.4	763.2	763.9	764.6	763.9	763.2	762.4
175°	764.9	764.5	764.3	764.6	765.5	766.4	767.2	768.1	767.2	766.4	765.5
177.5°	765.8	765.6	765.6	765.9	766.6	767.2	767.9	768.7	767.9	767.2	766.6
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	462.1	461.2	458.2	456.6	454.0	451.5	450.0	450.7	451.2	451.0	450.5
5°	448.8	445.4	440.1	435.7	432.5	426.5	424.0	422.7	421.6	420.4	419.1
7.5°	433.0	427.6	420.2	413.8	407.7	400.3	396.1	393.6	391.0	388.2	385.6
10°	421.8	414.2	406.3	397.4	390.1	383.5	377.6	373.6	369.9	366.5	364.1
12.5°	410.0	401.3	391.5	379.2	371.3	361.7	360.8	353.9	348.2	346.1	343.2
15°	391.3	379.0	366.5	352.0	345.7	337.1	331.7	326.2	321.4	318.0	317.1
17.5°	369.9	354.0	341.7	331.2	320.9	312.0	307.0	302.8	298.7	294.2	293.6
20°	353.6	339.9	326.5	317.3	306.7	297.6	291.5	287.2	283.8	281.1	278.8
22.5°	338.2	323.2	310.9	300.9	290.4	283.1	278.3	274.1	271.2	268.3	266.1
25°	313.5	301.8	288.3	276.9	268.3	263.6	259.7	256.1	254.3	252.3	249.8
27.5°	291.8	278.8	266.3	257.5	249.9	245.7	242.9	240.4	238.8	237.6	236.1
30°	276.6	263.5	253.6	244.9	238.6	234.5	232.7	231.2	229.3	228.5	227.8
32.5°	261.9	250.1	241.6	234.1	228.1	225.4	223.8	222.4	220.9	220.2	218.7
35°	241.1	231.2	223.0	218.8	214.0	211.6	210.4	208.6	207.2	206.4	206.2
37.5°	221.6	213.0	207.6	202.2	200.2	198.8	197.0	195.8	195.4	195.3	195.0
40°	208.9	201.9	197.0	192.7	191.9	189.6	188.2	187.2	187.2	187.4	187.2
42.5°	197.4	191.1	186.8	183.1	182.0	180.8	179.3	179.3	179.5	180.1	179.5
45°	180.0	175.5	172.4	170.6	168.7	167.4	167.2	167.7	167.9	168.1	168.7
47.5°	163.9	160.9	158.1	156.1	155.3	155.1	154.9	155.8	156.7	157.0	157.8
50°	154.4	151.0	148.6	147.3	146.6	146.3	146.6	147.7	148.5	149.3	149.9
52.5°	143.8	141.3	139.7	138.7	138.5	138.7	138.7	140.0	141.1	141.5	141.7
55°	129.0	127.2	126.9	125.2	126.0	125.8	126.7	127.4	128.5	129.6	129.8
57.5°	114.3	112.9	111.9	112.1	112.3	113.1	113.8	115.1	116.2	117.4	117.5
60°	104.6	103.9	103.3	103.3	103.6	104.7	105.6	106.9	107.6	108.4	108.8
62.5°	95.6	94.9	94.3	94.7	95.6	96.3	97.3	98.0	98.7	99.4	99.7
65°	81.5	81.2	81.7	82.1	82.2	83.1	84.4	84.9	85.6	86.0	87.3
67.5°	68.5	68.6	68.5	69.0	70.1	70.3	71.5	72.7	72.9	73.6	74.4
70°	59.7	60.1	60.4	60.8	61.7	62.1	63.0	63.5	64.2	64.8	65.4
72.5°	51.7	51.7	52.1	52.0	52.8	53.6	54.3	54.9	55.6	56.3	56.8
75°	39.8	39.8	40.2	40.3	41.2	42.1	41.9	42.3	43.0	43.7	44.1
77.5°	29.1	28.7	29.1	29.2	29.5	30.3	30.4	30.9	31.8	31.5	31.9
80°	22.1	21.6	22.1	22.3	22.3	23.2	23.2	23.6	24.1	23.6	24.1
82.5°	15.8	15.5	15.9	16.0	16.2	16.3	16.6	16.6	17.2	17.0	17.2
85°	7.9	7.8	7.9	7.8	7.9	8.1	8.1	7.9	7.9	8.2	7.8
87.5°	3.6	3.7	3.8	4.0	4.0	4.1	4.0	4.2	4.3	4.1	4.2
90°	5.9	7.1	8.2	9.1	10.1	11.1	11.7	12.4	12.9	13.5	14.0
92.5°	10.7	10.9	11.4	11.9	12.4	12.8	13.2	13.5	13.9	14.2	14.4
95°	19.8	18.1	19.0	19.9	20.8	21.6	22.3	22.9	23.4	24.1	24.3
97.5°	25.7	21.0	23.0	25.0	26.9	28.9	29.5	29.9	30.4	30.9	31.2
100°	30.7	23.2	25.3	27.4	29.5	31.6	32.6	33.6	34.5	35.6	36.2
102.5°	113.1	102.6	85.1	67.6	50.0	32.5	33.7	35.1	36.4	37.6	38.4
105°	183.4	168.4	134.8	101.1	67.5	33.8	35.2	36.5	37.9	39.2	40.2
107.5°	227.4	208.7	168.4	128.1	87.7	47.4	45.9	44.6	43.3	41.8	41.4
110°	256.0	239.5	203.9	168.3	132.7	97.0	84.8	72.4	60.0	47.8	41.8



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	283.2	280.0	271.2	262.4	253.6	244.8	199.9	154.9	110.0	65.0	42.7
115°	327.3	329.9	333.0	336.0	339.1	342.1	285.1	228.1	171.0	113.9	81.0
117.5°	368.3	370.5	372.6	374.8	376.8	379.0	365.2	351.4	337.5	323.8	302.3
120°	395.6	397.6	399.8	402.0	404.3	406.5	408.0	409.5	410.9	412.4	404.8
122.5°	420.8	423.0	425.4	427.9	430.2	432.7	433.6	434.4	435.3	436.3	435.1
125°	457.2	459.2	461.6	463.9	466.3	468.6	469.4	470.3	471.2	472.1	472.7
127.5°	492.3	494.0	495.7	497.5	499.2	501.0	502.2	503.5	504.8	506.0	506.7
130°	514.8	516.4	517.8	519.1	520.5	521.9	523.2	524.6	525.9	527.3	527.9
132.5°	535.8	537.3	538.6	540.0	541.4	542.7	543.8	545.0	546.2	547.3	547.9
135°	565.8	567.4	568.5	569.6	570.7	571.8	573.0	574.3	575.4	576.7	577.2
137.5°	592.6	593.9	595.2	596.4	597.7	599.0	600.2	601.3	602.5	603.8	604.2
140°	610.1	611.2	612.6	613.9	615.3	616.7	617.8	618.9	620.0	621.2	621.4
142.5°	625.7	626.9	628.4	630.0	631.5	633.1	634.1	635.1	636.1	637.2	637.3
145°	646.7	647.7	649.7	651.9	653.9	656.1	657.0	657.7	658.6	659.5	659.7
147.5°	667.2	668.0	670.0	672.1	674.1	676.2	676.9	677.6	678.2	678.8	678.9
150°	679.8	680.3	682.3	684.3	686.3	688.2	689.0	689.7	690.5	691.2	691.3
152.5°	691.3	691.8	693.7	695.5	697.4	699.3	700.1	700.8	701.6	702.3	702.3
155°	708.2	708.4	709.9	711.3	712.8	714.3	715.0	715.7	716.5	717.2	717.1
157.5°	722.5	722.5	723.6	724.6	725.6	726.7	727.5	728.4	729.2	730.1	730.0
160°	731.3	731.3	732.1	732.8	733.5	734.3	735.0	735.7	736.5	737.2	737.1
162.5°	738.4	738.3	738.9	739.7	740.3	740.9	741.7	742.6	743.4	744.3	744.2
165°	747.9	747.7	748.1	748.5	748.8	749.2	750.1	751.0	751.8	752.7	752.7
167.5°	755.0	754.9	755.2	755.5	755.9	756.2	757.1	758.0	758.8	759.6	759.5
170°	759.0	758.8	759.0	759.3	759.5	759.8	760.7	761.5	762.3	763.2	763.1
172.5°	761.7	761.4	761.7	761.9	762.2	762.4	763.3	764.1	765.0	765.9	765.7
175°	764.6	764.3	764.5	764.9	765.1	765.3	766.2	767.1	767.9	768.7	768.6
177.5°	765.9	765.6	765.6	765.8	765.9	766.0	766.7	767.4	768.0	768.7	768.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	449.1	448.8	448.8	447.5	448.8	448.8	449.1	450.5	451.0	451.2	450.7
5°	416.6	416.1	415.2	416.1	415.2	416.1	416.6	419.1	420.4	421.6	422.7
7.5°	384.4	382.3	382.0	379.9	382.0	382.3	384.4	385.6	388.2	391.0	393.6
10°	361.0	359.6	359.3	355.9	359.3	359.6	361.0	364.1	366.5	369.9	373.6
12.5°	343.2	339.7	340.4	338.4	340.4	339.7	343.2	343.2	346.1	348.2	353.9
15°	312.2	312.2	311.5	308.5	311.5	312.2	312.2	317.1	318.0	321.4	326.2
17.5°	290.0	289.6	288.0	288.8	288.0	289.6	290.0	293.6	294.2	298.7	302.8
20°	276.8	275.7	273.5	273.5	273.5	275.7	276.8	278.8	281.1	283.8	287.2
22.5°	264.3	264.2	261.9	262.6	261.9	264.2	264.3	266.1	268.3	271.2	274.1
25°	249.6	248.2	247.1	247.6	247.1	248.2	249.6	249.8	252.3	254.3	256.1
27.5°	235.7	234.9	234.8	233.4	234.8	234.9	235.7	236.1	237.6	238.8	240.4
30°	227.7	225.9	226.2	225.3	226.2	225.9	227.7	227.8	228.5	229.3	231.2
32.5°	218.4	217.8	217.5	216.7	217.5	217.8	218.4	218.7	220.2	220.9	222.4
35°	205.9	206.0	205.2	205.5	205.2	206.0	205.9	206.2	206.4	207.2	208.6
37.5°	194.9	195.4	195.0	195.1	195.0	195.4	194.9	195.0	195.3	195.4	195.8
40°	187.7	187.7	187.7	188.2	187.7	187.7	187.7	187.2	187.4	187.2	187.2
42.5°	180.8	180.5	180.2	180.1	180.2	180.5	180.8	179.5	180.1	179.5	179.3
45°	169.0	169.5	169.7	168.8	169.7	169.5	169.0	168.7	168.1	167.9	167.7
47.5°	158.3	158.4	158.3	159.1	158.3	158.4	158.3	157.8	157.0	156.7	155.8
50°	150.8	150.4	150.8	150.4	150.8	150.4	150.8	149.9	149.3	148.5	147.7
52.5°	142.9	143.0	142.8	142.7	142.8	143.0	142.9	141.7	141.5	141.1	140.0
55°	130.5	130.8	130.6	130.6	130.6	130.8	130.5	129.8	129.6	128.5	127.4
57.5°	117.6	118.0	118.2	117.4	118.2	118.0	117.6	117.5	117.4	116.2	115.1
60°	108.7	109.6	109.4	109.1	109.4	109.6	108.7	108.8	108.4	107.6	106.9
62.5°	100.4	100.8	100.8	100.7	100.8	100.8	100.4	99.7	99.4	98.7	98.0
65°	87.9	88.2	87.6	88.2	87.6	88.2	87.9	87.3	86.0	85.6	84.9
67.5°	74.1	74.3	74.7	74.9	74.7	74.3	74.1	74.4	73.6	72.9	72.7
70°	65.7	65.5	66.1	66.6	66.1	65.5	65.7	65.4	64.8	64.2	63.5
72.5°	56.7	57.1	57.0	57.4	57.0	57.1	56.7	56.8	56.3	55.6	54.9
75°	43.7	44.3	44.1	44.6	44.1	44.3	43.7	44.1	43.7	43.0	42.3
77.5°	31.6	31.7	31.6	31.9	31.6	31.7	31.6	31.9	31.5	31.8	30.9
80°	24.1	23.8	23.4	24.1	23.4	23.8	24.1	24.1	23.6	24.1	23.6
82.5°	16.8	17.0	16.6	16.6	16.6	17.0	16.8	17.2	17.0	17.2	16.6
85°	7.8	7.5	7.2	7.2	7.2	7.5	7.8	7.8	8.2	7.9	7.9
87.5°	4.3	4.2	4.3	4.1	4.3	4.2	4.3	4.2	4.1	4.3	4.2
90°	14.3	14.5	14.7	15.0	14.7	14.5	14.3	14.0	13.5	12.9	12.4
92.5°	14.5	14.7	14.8	15.0	14.8	14.7	14.5	14.4	14.2	13.9	13.5
95°	24.2	24.1	24.0	23.8	24.0	24.1	24.2	24.3	24.1	23.4	22.9
97.5°	31.4	31.5	31.7	31.8	31.7	31.5	31.4	31.2	30.9	30.4	29.9
100°	36.4	36.7	36.9	37.2	36.9	36.7	36.4	36.2	35.6	34.5	33.6
102.5°	38.8	39.1	39.5	39.8	39.5	39.1	38.8	38.4	37.6	36.4	35.1
105°	40.6	41.2	41.7	42.1	41.7	41.2	40.6	40.2	39.2	37.9	36.5
107.5°	41.9	42.4	42.9	43.3	42.9	42.4	41.9	41.4	41.8	43.3	44.6
110°	42.3	42.9	43.3	43.8	43.3	42.9	42.3	41.8	47.8	60.0	72.4



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	43.1	43.5	43.9	44.3	43.9	43.5	43.1	42.7	65.0	110.0	154.9
115°	72.1	63.2	54.3	45.5	54.3	63.2	72.1	81.0	113.9	171.0	228.1
117.5°	273.1	244.0	214.8	185.7	214.8	244.0	273.1	302.3	323.8	337.5	351.4
120°	388.2	371.5	354.9	338.3	354.9	371.5	388.2	404.8	412.4	410.9	409.5
122.5°	431.8	428.6	425.4	422.2	425.4	428.6	431.8	435.1	436.3	435.3	434.4
125°	473.0	473.4	473.8	474.1	473.8	473.4	473.0	472.7	472.1	471.2	470.3
127.5°	506.8	506.8	506.9	507.0	506.9	506.8	506.8	506.7	506.0	504.8	503.5
130°	527.8	527.7	527.5	527.4	527.5	527.7	527.8	527.9	527.3	525.9	524.6
132.5°	547.7	547.6	547.5	547.4	547.5	547.6	547.7	547.9	547.3	546.2	545.0
135°	576.9	576.7	576.5	576.2	576.5	576.7	576.9	577.2	576.7	575.4	574.3
137.5°	603.7	603.3	602.9	602.5	602.9	603.3	603.7	604.2	603.8	602.5	601.3
140°	620.8	620.1	619.5	618.9	619.5	620.1	620.8	621.4	621.2	620.0	618.9
142.5°	636.8	636.1	635.5	634.9	635.5	636.1	636.8	637.3	637.2	636.1	635.1
145°	659.0	658.4	657.7	657.2	657.7	658.4	659.0	659.7	659.5	658.6	657.7
147.5°	678.3	677.9	677.3	676.8	677.3	677.9	678.3	678.9	678.8	678.2	677.6
150°	690.6	690.0	689.4	688.8	689.4	690.0	690.6	691.3	691.2	690.5	689.7
152.5°	701.4	700.6	699.8	698.9	699.8	700.6	701.4	702.3	702.3	701.6	700.8
155°	716.1	715.2	714.2	713.2	714.2	715.2	716.1	717.1	717.2	716.5	715.7
157.5°	729.0	728.1	727.1	726.1	727.1	728.1	729.0	730.0	730.1	729.2	728.4
160°	736.3	735.4	734.6	733.7	734.6	735.4	736.3	737.1	737.2	736.5	735.7
162.5°	743.1	742.0	740.9	739.9	740.9	742.0	743.1	744.2	744.3	743.4	742.6
165°	751.8	751.0	750.1	749.2	750.1	751.0	751.8	752.7	752.7	751.8	751.0
167.5°	758.4	757.3	756.2	755.1	756.2	757.3	758.4	759.5	759.6	758.8	758.0
170°	762.0	760.9	759.8	758.7	759.8	760.9	762.0	763.1	763.2	762.3	761.5
172.5°	764.6	763.5	762.4	761.3	762.4	763.5	764.6	765.7	765.9	765.0	764.1
175°	767.3	766.1	764.9	763.7	764.9	766.1	767.3	768.6	768.7	767.9	767.1
177.5°	767.8	766.8	766.0	765.1	766.0	766.8	767.8	768.7	768.7	768.0	767.4
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	450.0	451.5	454.0	456.6	458.2	461.2	462.1	463.5	464.8	467.8	471.0
5°	424.0	426.5	432.5	435.7	440.1	445.4	448.8	452.4	456.4	463.2	469.5
7.5°	396.1	400.3	407.7	413.8	420.2	427.6	433.0	440.1	446.1	455.7	464.9
10°	377.6	383.5	390.1	397.4	406.3	414.2	421.8	430.8	438.0	449.6	460.3
12.5°	360.8	361.7	371.3	379.2	391.5	401.3	410.0	421.6	428.6	442.4	453.7
15°	331.7	337.1	345.7	352.0	366.5	379.0	391.3	403.3	411.4	428.3	443.2
17.5°	307.0	312.0	320.9	331.2	341.7	354.0	369.9	382.6	393.6	413.0	430.6
20°	291.5	297.6	306.7	317.3	326.5	339.9	353.6	368.2	380.1	401.9	422.6
22.5°	278.3	283.1	290.4	300.9	310.9	323.2	338.2	354.1	366.5	390.1	411.0
25°	259.7	263.6	268.3	276.9	288.3	301.8	313.5	331.0	349.1	371.1	396.4
27.5°	242.9	245.7	249.9	257.5	266.3	278.8	291.8	308.4	326.7	350.5	377.3
30°	232.7	234.5	238.6	244.9	253.6	263.5	276.6	292.4	311.2	335.3	361.9
32.5°	223.8	225.4	228.1	234.1	241.6	250.1	261.9	277.7	295.6	319.2	348.8
35°	210.4	211.6	214.0	218.8	223.0	231.2	241.1	255.6	272.3	294.9	325.5
37.5°	197.0	198.8	200.2	202.2	207.6	213.0	221.6	233.8	250.2	273.1	302.2
40°	188.2	189.6	191.9	192.7	197.0	201.9	208.9	220.1	236.6	257.5	286.0
42.5°	179.3	180.8	182.0	183.1	186.8	191.1	197.4	207.0	221.7	241.9	270.1
45°	167.2	167.4	168.7	170.6	172.4	175.5	180.0	188.2	199.6	218.6	244.2
47.5°	154.9	155.1	155.3	156.1	158.1	160.9	163.9	170.6	180.8	196.0	220.9
50°	146.6	146.3	146.6	147.3	148.6	151.0	154.4	159.2	167.5	181.7	204.6
52.5°	138.7	138.7	138.5	138.7	139.7	141.3	143.8	147.9	155.3	168.3	188.5
55°	126.7	125.8	126.0	125.2	126.9	127.2	129.0	132.5	138.9	147.9	166.8
57.5°	113.8	113.1	112.3	112.1	111.9	112.9	114.3	117.0	122.0	129.9	145.2
60°	105.6	104.7	103.6	103.3	103.3	103.9	104.6	106.5	111.2	118.2	130.8
62.5°	97.3	96.3	95.6	94.7	94.3	94.9	95.6	97.0	100.4	107.0	117.9
65°	84.4	83.1	82.2	82.1	81.7	81.2	81.5	82.9	85.6	90.9	99.5
67.5°	71.5	70.3	70.1	69.0	68.5	68.6	68.5	69.7	71.4	75.9	82.3
70°	63.0	62.1	61.7	60.8	60.4	60.1	59.7	60.8	62.4	66.2	71.8
72.5°	54.3	53.6	52.8	52.0	52.1	51.7	51.7	52.4	53.6	57.1	61.5
75°	41.9	42.1	41.2	40.3	40.2	39.8	39.8	40.3	40.9	43.6	47.0
77.5°	30.4	30.3	29.5	29.2	29.1	28.7	29.1	29.4	29.7	31.5	34.0
80°	23.2	23.2	22.3	22.3	22.1	21.6	22.1	21.8	22.5	24.3	26.1
82.5°	16.6	16.3	16.2	16.0	15.9	15.5	15.8	16.2	16.5	17.7	18.8
85°	8.1	8.1	7.9	7.8	7.9	7.8	7.9	8.1	8.2	8.8	9.7
87.5°	4.0	4.1	4.0	4.0	3.8	3.7	3.6	3.5	3.6	3.4	3.2
90°	11.7	11.1	10.1	9.1	8.2	7.1	5.9	4.6	3.2	1.9	0.6
92.5°	13.2	12.8	12.4	11.9	11.4	10.9	10.7	10.9	10.9	11.1	11.2
95°	22.3	21.6	20.8	19.9	19.0	18.1	19.8	23.8	27.9	32.0	36.0
97.5°	29.5	28.9	26.9	25.0	23.0	21.0	25.7	37.2	48.6	60.0	71.5
100°	32.6	31.6	29.5	27.4	25.3	23.2	30.7	47.5	64.4	81.3	98.2
102.5°	33.7	32.5	50.0	67.6	85.1	102.6	113.1	116.7	120.3	123.9	127.5
105°	35.2	33.8	67.5	101.1	134.8	168.4	183.4	179.7	176.0	172.3	168.6
107.5°	45.9	47.4	87.7	128.1	168.4	208.7	227.4	224.4	221.5	218.5	215.5
110°	84.8	97.0	132.7	168.3	203.9	239.5	256.0	253.4	250.9	248.3	245.7



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	199.9	244.8	253.6	262.4	271.2	280.0	283.2	280.9	278.7	276.4	274.1
115°	285.1	342.1	339.1	336.0	333.0	329.9	327.3	325.2	323.1	321.0	318.9
117.5°	365.2	379.0	376.8	374.8	372.6	370.5	368.3	365.9	363.6	361.2	358.9
120°	408.0	406.5	404.3	402.0	399.8	397.6	395.6	393.7	391.9	390.1	388.2
122.5°	433.6	432.7	430.2	427.9	425.4	423.0	420.8	418.9	416.9	415.0	413.0
125°	469.4	468.6	466.3	463.9	461.6	459.2	457.2	455.7	454.1	452.5	450.8
127.5°	502.2	501.0	499.2	497.5	495.7	494.0	492.3	490.4	488.7	486.9	485.1
130°	523.2	521.9	520.5	519.1	517.8	516.4	514.8	512.8	510.8	508.8	506.8
132.5°	543.8	542.7	541.4	540.0	538.6	537.3	535.8	534.1	532.4	530.8	529.1
135°	573.0	571.8	570.7	569.6	568.5	567.4	565.8	563.8	561.8	559.8	557.9
137.5°	600.2	599.0	597.7	596.4	595.2	593.9	592.6	591.2	589.9	588.4	587.1
140°	617.8	616.7	615.3	613.9	612.6	611.2	610.1	609.1	608.1	607.1	606.2
142.5°	634.1	633.1	631.5	630.0	628.4	626.9	625.7	624.8	623.9	623.0	622.1
145°	657.0	656.1	653.9	651.9	649.7	647.7	646.7	646.8	647.0	647.1	647.2
147.5°	676.9	676.2	674.1	672.1	670.0	668.0	667.2	667.7	668.1	668.6	669.0
150°	689.0	688.2	686.3	684.3	682.3	680.3	679.8	680.6	681.5	682.4	683.3
152.5°	700.1	699.3	697.4	695.5	693.7	691.8	691.3	692.3	693.3	694.3	695.2
155°	715.0	714.3	712.8	711.3	709.9	708.4	708.2	709.3	710.4	711.5	712.6
157.5°	727.5	726.7	725.6	724.6	723.6	722.5	722.5	723.4	724.4	725.3	726.3
160°	735.0	734.3	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3
162.5°	741.7	740.9	740.3	739.7	738.9	738.3	738.4	739.1	739.9	740.6	741.3
165°	750.1	749.2	748.8	748.5	748.1	747.7	747.9	748.7	749.4	750.1	750.9
167.5°	757.1	756.2	755.9	755.5	755.2	754.9	755.0	755.7	756.5	757.2	758.0
170°	760.7	759.8	759.5	759.3	759.0	758.8	759.0	759.8	760.5	761.2	762.0
172.5°	763.3	762.4	762.2	761.9	761.7	761.4	761.7	762.4	763.2	763.9	764.6
175°	766.2	765.3	765.1	764.9	764.5	764.3	764.6	765.5	766.4	767.2	768.1
177.5°	766.7	766.0	765.9	765.8	765.6	765.6	765.9	766.6	767.2	767.9	768.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	470.7	471.4	473.7	476.0	478.6	479.3	480.5	479.5	479.2	481.9	483.9
5°	472.1	475.2	481.6	487.4	492.2	495.6	499.2	500.7	503.4	507.1	511.8
7.5°	470.5	476.8	486.7	495.1	504.2	510.8	515.9	520.4	525.7	532.8	540.7
10°	468.8	477.2	489.3	499.6	510.7	519.2	526.2	533.1	541.0	550.9	561.1
12.5°	465.6	475.6	490.8	502.9	517.2	525.5	535.0	549.7	558.3	572.0	586.5
15°	459.2	470.4	491.5	506.4	522.6	538.4	555.9	569.9	583.9	592.1	612.4
17.5°	449.8	466.1	489.5	506.9	527.5	552.4	572.0	588.0	604.1	617.3	627.5
20°	442.1	459.9	486.6	507.5	532.0	558.7	581.2	597.5	611.5	622.5	628.8
22.5°	432.5	455.0	480.9	505.3	536.5	563.1	586.7	599.4	611.2	616.6	619.0
25°	417.3	444.3	473.6	503.5	538.8	566.9	588.4	596.2	599.6	594.4	585.7
27.5°	400.9	431.0	465.3	500.1	537.4	564.4	579.9	578.7	572.9	556.0	542.5
30°	388.7	421.8	458.7	496.7	534.1	560.4	569.3	560.4	547.2	528.4	509.1
32.5°	375.9	410.2	451.6	491.8	528.1	551.2	553.1	537.7	517.3	495.8	471.8
35°	356.5	393.6	438.4	480.9	515.2	529.8	521.2	493.8	469.7	440.4	407.6
37.5°	334.5	375.5	420.4	464.9	496.0	499.8	478.3	449.6	415.5	381.0	342.5
40°	318.1	361.6	407.8	452.6	480.1	476.2	448.8	417.2	376.7	334.5	298.7
42.5°	303.5	346.8	394.0	437.9	459.9	449.1	417.2	378.3	334.8	295.1	262.3
45°	278.1	322.7	370.9	413.4	426.0	406.3	364.1	320.8	278.1	244.9	219.0
47.5°	253.3	297.5	345.2	382.5	387.0	360.6	314.4	270.0	233.1	206.2	187.9
50°	235.2	279.5	326.8	360.1	358.6	326.8	279.3	237.0	206.2	184.4	172.2
52.5°	219.0	260.8	306.2	336.5	328.8	294.1	248.7	211.2	185.9	168.9	157.8
55°	193.6	232.3	275.5	299.8	285.7	247.2	208.9	178.7	159.9	147.2	138.6
57.5°	168.5	204.8	241.8	256.7	241.2	205.7	173.7	151.8	137.7	128.3	122.6
60°	153.0	184.7	217.5	230.5	212.0	180.3	155.1	135.5	124.1	116.5	111.4
62.5°	137.4	165.8	196.9	203.9	187.0	160.2	137.8	121.5	112.3	105.4	100.6
65°	116.2	139.5	163.0	167.7	152.1	131.3	113.8	103.1	94.8	89.8	86.0
67.5°	95.4	114.0	130.7	134.4	120.7	106.4	93.6	84.4	78.8	74.6	71.4
70°	82.9	97.8	111.4	114.5	103.5	90.7	81.0	73.6	68.5	65.0	61.9
72.5°	69.9	82.1	93.6	95.6	86.7	76.8	68.9	63.1	58.6	56.3	53.4
75°	53.5	60.7	69.5	70.0	64.1	58.1	52.0	48.2	45.9	43.0	41.6
77.5°	37.7	43.3	48.4	49.4	45.9	41.8	38.4	35.4	33.4	32.1	30.7
80°	28.8	33.3	35.5	36.7	34.2	31.3	29.3	27.3	26.1	25.2	24.3
82.5°	20.6	23.4	25.3	26.4	25.0	23.2	21.3	20.1	19.2	18.5	18.1
85°	10.5	11.7	13.0	13.3	13.0	12.2	11.2	11.2	10.6	10.5	10.5
87.5°	4.0	4.8	5.1	5.8	5.8	5.9	6.2	6.2	6.3	6.3	6.2
90°	1.9	3.2	4.6	5.9	7.1	8.2	9.1	10.1	11.1	11.7	12.4
92.5°	11.1	10.9	10.9	10.7	10.9	11.4	11.9	12.4	12.8	13.2	13.5
95°	32.0	27.9	23.8	19.8	18.1	19.0	19.9	20.8	21.6	22.3	22.9
97.5°	60.0	48.6	37.2	25.7	21.0	23.0	25.0	26.9	28.9	29.5	29.9
100°	81.3	64.4	47.5	30.7	23.2	25.3	27.4	29.5	31.6	32.6	33.6
102.5°	123.9	120.3	116.7	113.1	102.6	85.1	67.6	50.0	32.5	33.7	35.1
105°	172.3	176.0	179.7	183.4	168.4	134.8	101.1	67.5	33.8	35.2	36.5
107.5°	218.5	221.5	224.4	227.4	208.7	168.4	128.1	87.7	47.4	45.9	44.6
110°	248.3	250.9	253.4	256.0	239.5	203.9	168.3	132.7	97.0	84.8	72.4



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.4	278.7	280.9	283.2	280.0	271.2	262.4	253.6	244.8	199.9	154.9
115°	321.0	323.1	325.2	327.3	329.9	333.0	336.0	339.1	342.1	285.1	228.1
117.5°	361.2	363.6	365.9	368.3	370.5	372.6	374.8	376.8	379.0	365.2	351.4
120°	390.1	391.9	393.7	395.6	397.6	399.8	402.0	404.3	406.5	408.0	409.5
122.5°	415.0	416.9	418.9	420.8	423.0	425.4	427.9	430.2	432.7	433.6	434.4
125°	452.5	454.1	455.7	457.2	459.2	461.6	463.9	466.3	468.6	469.4	470.3
127.5°	486.9	488.7	490.4	492.3	494.0	495.7	497.5	499.2	501.0	502.2	503.5
130°	508.8	510.8	512.8	514.8	516.4	517.8	519.1	520.5	521.9	523.2	524.6
132.5°	530.8	532.4	534.1	535.8	537.3	538.6	540.0	541.4	542.7	543.8	545.0
135°	559.8	561.8	563.8	565.8	567.4	568.5	569.6	570.7	571.8	573.0	574.3
137.5°	588.4	589.9	591.2	592.6	593.9	595.2	596.4	597.7	599.0	600.2	601.3
140°	607.1	608.1	609.1	610.1	611.2	612.6	613.9	615.3	616.7	617.8	618.9
142.5°	623.0	623.9	624.8	625.7	626.9	628.4	630.0	631.5	633.1	634.1	635.1
145°	647.1	647.0	646.8	646.7	647.7	649.7	651.9	653.9	656.1	657.0	657.7
147.5°	668.6	668.1	667.7	667.2	668.0	670.0	672.1	674.1	676.2	676.9	677.6
150°	682.4	681.5	680.6	679.8	680.3	682.3	684.3	686.3	688.2	689.0	689.7
152.5°	694.3	693.3	692.3	691.3	691.8	693.7	695.5	697.4	699.3	700.1	700.8
155°	711.5	710.4	709.3	708.2	708.4	709.9	711.3	712.8	714.3	715.0	715.7
157.5°	725.3	724.4	723.4	722.5	722.5	723.6	724.6	725.6	726.7	727.5	728.4
160°	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	735.0	735.7
162.5°	740.6	739.9	739.1	738.4	738.3	738.9	739.7	740.3	740.9	741.7	742.6
165°	750.1	749.4	748.7	747.9	747.7	748.1	748.5	748.8	749.2	750.1	751.0
167.5°	757.2	756.5	755.7	755.0	754.9	755.2	755.5	755.9	756.2	757.1	758.0
170°	761.2	760.5	759.8	759.0	758.8	759.0	759.3	759.5	759.8	760.7	761.5
172.5°	763.9	763.2	762.4	761.7	761.4	761.7	761.9	762.2	762.4	763.3	764.1
175°	767.2	766.4	765.5	764.6	764.3	764.5	764.9	765.1	765.3	766.2	767.1
177.5°	767.9	767.2	766.6	765.9	765.6	765.6	765.8	765.9	766.0	766.7	767.4
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.3	468.3	468.3	468.3	468.3	468.3	468.3
2.5°	485.7	487.7	487.7	488.0	490.3	490.0	489.8
5°	516.8	519.9	520.2	523.5	525.6	524.9	522.9
7.5°	546.2	551.9	556.3	558.6	561.5	563.2	562.4
10°	569.6	577.8	582.9	586.3	590.4	593.5	592.4
12.5°	590.7	600.6	607.5	613.4	613.9	617.8	615.1
15°	623.8	634.1	635.3	639.5	643.0	642.6	642.8
17.5°	634.6	637.9	638.7	638.7	638.8	637.5	634.8
20°	630.7	629.5	626.5	624.1	620.0	619.4	615.8
22.5°	612.3	608.3	600.6	595.6	589.1	587.5	586.5
25°	576.1	567.2	555.0	543.3	540.0	533.8	535.5
27.5°	526.2	512.5	499.2	489.8	481.2	471.7	474.4
30°	491.3	475.8	457.1	442.7	433.5	424.5	422.9
32.5°	449.6	426.8	406.0	393.3	379.2	373.5	367.3
35°	377.6	355.4	334.7	316.9	306.7	298.7	291.5
37.5°	312.8	287.3	270.6	256.2	248.7	244.2	245.4
40°	272.7	250.3	238.1	227.1	220.2	217.1	217.8
42.5°	240.1	223.4	213.3	205.8	201.0	199.2	198.8
45°	203.2	193.8	185.5	181.3	178.9	176.9	175.6
47.5°	178.0	170.3	165.6	163.1	161.1	159.1	159.0
50°	162.9	157.8	154.6	151.9	150.3	148.9	150.1
52.5°	151.3	146.7	143.5	141.1	140.5	139.2	139.1
55°	134.3	130.6	128.3	126.1	125.1	124.4	123.4
57.5°	118.7	115.3	113.1	111.8	109.7	109.0	108.7
60°	107.6	104.9	102.7	100.9	100.1	98.6	98.6
62.5°	97.4	94.7	92.7	91.3	89.8	89.3	89.4
65°	82.6	80.4	78.4	77.0	76.7	75.6	76.0
67.5°	69.0	67.6	65.4	64.6	64.0	63.5	63.0
70°	59.9	58.5	57.4	56.3	55.8	55.8	55.8
72.5°	52.3	50.5	49.9	48.6	48.9	48.3	47.7
75°	40.5	39.4	38.9	38.3	37.5	37.5	37.5
77.5°	29.8	29.5	28.8	28.3	28.0	27.9	28.0
80°	23.1	22.8	22.5	22.5	22.1	21.9	21.6
82.5°	17.7	17.3	17.0	16.9	16.8	16.8	16.7
85°	10.1	9.7	9.7	9.9	9.5	9.5	9.7
87.5°	6.5	6.6	6.6	6.6	6.8	6.7	6.7
90°	12.9	13.5	14.0	14.3	14.5	14.7	15.0
92.5°	13.9	14.2	14.4	14.5	14.7	14.8	15.0
95°	23.4	24.1	24.3	24.2	24.1	24.0	23.8
97.5°	30.4	30.9	31.2	31.4	31.5	31.7	31.8
100°	34.5	35.6	36.2	36.4	36.7	36.9	37.2
102.5°	36.4	37.6	38.4	38.8	39.1	39.5	39.8
105°	37.9	39.2	40.2	40.6	41.2	41.7	42.1
107.5°	43.3	41.8	41.4	41.9	42.4	42.9	43.3
110°	60.0	47.8	41.8	42.3	42.9	43.3	43.8



TEST NUMBER: P331471-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	110.0	65.0	42.7	43.1	43.5	43.9	44.3
115°	171.0	113.9	81.0	72.1	63.2	54.3	45.5
117.5°	337.5	323.8	302.3	273.1	244.0	214.8	185.7
120°	410.9	412.4	404.8	388.2	371.5	354.9	338.3
122.5°	435.3	436.3	435.1	431.8	428.6	425.4	422.2
125°	471.2	472.1	472.7	473.0	473.4	473.8	474.1
127.5°	504.8	506.0	506.7	506.8	506.8	506.9	507.0
130°	525.9	527.3	527.9	527.8	527.7	527.5	527.4
132.5°	546.2	547.3	547.9	547.7	547.6	547.5	547.4
135°	575.4	576.7	577.2	576.9	576.7	576.5	576.2
137.5°	602.5	603.8	604.2	603.7	603.3	602.9	602.5
140°	620.0	621.2	621.4	620.8	620.1	619.5	618.9
142.5°	636.1	637.2	637.3	636.8	636.1	635.5	634.9
145°	658.6	659.5	659.7	659.0	658.4	657.7	657.2
147.5°	678.2	678.8	678.9	678.3	677.9	677.3	676.8
150°	690.5	691.2	691.3	690.6	690.0	689.4	688.8
152.5°	701.6	702.3	702.3	701.4	700.6	699.8	698.9
155°	716.5	717.2	717.1	716.1	715.2	714.2	713.2
157.5°	729.2	730.1	730.0	729.0	728.1	727.1	726.1
160°	736.5	737.2	737.1	736.3	735.4	734.6	733.7
162.5°	743.4	744.3	744.2	743.1	742.0	740.9	739.9
165°	751.8	752.7	752.7	751.8	751.0	750.1	749.2
167.5°	758.8	759.6	759.5	758.4	757.3	756.2	755.1
170°	762.3	763.2	763.1	762.0	760.9	759.8	758.7
172.5°	765.0	765.9	765.7	764.6	763.5	762.4	761.3
175°	767.9	768.7	768.6	767.3	766.1	764.9	763.7
177.5°	768.0	768.7	768.7	767.8	766.8	766.0	765.1
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4

(END OF REPORT)