

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906948

Luminaire Tested: DFN2DIP-SQ4F0-140D160US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906948
REPORT IS A COMBINATION OF REPORTS P900217 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D160US835-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 28021.0 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 265.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906948

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906948

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29
5	68	57	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3822	3822	3822
5°	3828	3770	3796
10°	3797	3720	3745
15°	3741	3659	3666
20°	3666	3575	3585
25°	3591	3474	3491
30°	3497	3380	3371
35°	3408	3269	3244
40°	3298	3157	3124
45°	3188	3045	3001
50°	3069	2927	2858
55°	2943	2791	2727
60°	2802	2629	2577
65°	2647	2462	2400
70°	2450	2258	2210
75°	2178	2014	2036
80°	1850	1704	1701
85°	1337	1165	1143

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3982 cd/sqm

TEST NUMBER: P906948

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.7	1.8
10°-20°	1442.6	5.1
20°-30°	2120.0	7.6
30°-40°	2462.3	8.8
40°-50°	2459.3	8.8
50°-60°	2144.4	7.7
60°-70°	1585.2	5.7
70°-80°	896.9	3.2
80°-90°	251.1	0.9
90°-100°	313.1	1.1
100°-110°	995.0	3.6
110°-120°	1702.7	6.1
120°-130°	2239.3	8.0
130°-140°	2513.5	9.0
140°-150°	2464.8	8.8
150°-160°	2067.6	7.4
160°-170°	1371.2	4.9
170°-180°	479.3	1.7
0°-30°	4075.3	14.5
0°-40°	6537.6	23.3
0°-60°	11141.3	39.8
0°-90°	13874.4	49.5
90°-120°	3010.8	10.7
90°-150°	10228.5	36.5
90°-180°	14147.0	50.5
0°-180°	28021.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5448	5448	5448	5448	5448	
5°	5448	5427	5369	5411	5401	517
15°	5186	5155	5086	5107	5081	1461
25°	4693	4652	4563	4573	4563	2160
35°	4049	3997	3913	3881	3855	2529
45°	3295	3258	3180	3122	3101	2543
55°	2494	2462	2399	2336	2310	2229
65°	1682	1650	1598	1550	1524	1663
75°	880	870	843	812	822	939
85°	214	210	204	188	183	239
90°	5	55	150	140	145	27
95°	223	266	273	273	266	248
105°	918	931	940	947	947	969
115°	1709	1733	1726	1721	1709	1690
125°	2485	2523	2511	2498	2493	2221
135°	3214	3262	3271	3266	3254	2485
145°	3903	3933	3958	3962	3945	2438
155°	4462	4475	4488	4510	4496	2054
165°	4855	4850	4850	4880	4859	1369
175°	5051	5039	5030	5061	5035	480
180°	5061	5061	5061	5061	5061	

TEST NUMBER: P906948

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US835-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5447.5	5447.5	5447.5	5447.5	5447.5
2.5°	5479.1	5453.0	5395.2	5447.5	5437.5
5°	5447.5	5426.9	5369.1	5410.8	5400.8
7.5°	5410.8	5379.7	5321.9	5364.1	5353.5
10°	5353.5	5316.9	5254.1	5295.8	5280.2
12.5°	5274.6	5243.5	5180.7	5206.8	5196.3
15°	5185.7	5154.6	5086.2	5107.4	5081.2
17.5°	5075.7	5044.6	4976.2	5002.3	4976.2
20°	4955.1	4924.0	4850.6	4866.2	4845.6
22.5°	4835.0	4787.8	4719.4	4719.4	4708.9
25°	4693.3	4651.6	4562.7	4572.7	4562.7
27.5°	4536.0	4499.4	4431.6	4416.0	4389.9
30°	4379.3	4337.1	4258.7	4243.2	4222.0
32.5°	4211.5	4180.4	4096.4	4064.8	4043.6
35°	4049.2	3997.0	3913.0	3881.4	3855.2
37.5°	3865.8	3818.6	3734.6	3698.0	3671.8
40°	3677.4	3635.2	3551.2	3504.6	3483.4
42.5°	3494.0	3451.8	3368.4	3315.6	3284.5
45°	3295.0	3258.4	3179.5	3122.2	3101.1
47.5°	3101.1	3064.4	2980.5	2922.7	2891.6
50°	2896.6	2870.5	2797.1	2723.7	2697.6
52.5°	2697.6	2660.9	2593.1	2535.3	2498.7
55°	2493.7	2462.0	2399.2	2336.4	2310.3
57.5°	2289.1	2263.0	2194.7	2131.9	2110.7
60°	2084.6	2064.1	1990.7	1932.9	1917.3
62.5°	1885.7	1849.0	1796.7	1744.5	1723.4
65°	1681.7	1650.0	1597.8	1550.5	1524.4
67.5°	1472.2	1445.5	1398.8	1362.1	1341.0
70°	1278.2	1257.1	1209.9	1173.2	1152.6
72.5°	1079.3	1058.1	1032.0	995.4	979.8
75°	879.8	869.8	843.1	812.0	822.5
77.5°	701.9	680.8	670.2	654.7	639.1
80°	524.1	518.5	508.0	492.4	481.8
82.5°	356.2	356.2	351.2	330.1	330.1
85°	214.5	209.5	204.5	188.4	183.4
87.5°	94.5	83.9	73.4	57.8	52.2
90°	4.6	54.9	149.5	140.4	144.9
92.5°	94.6	128.2	132.7	137.3	137.3
95°	222.7	265.5	273.1	273.1	265.5
97.5°	370.7	410.4	427.2	427.2	427.2
100°	541.6	576.7	588.9	588.9	584.3
102.5°	721.6	747.6	764.3	768.9	764.3
105°	918.4	930.6	939.8	947.4	947.4
107.5°	1113.7	1132.0	1132.0	1135.1	1113.7
110°	1302.9	1327.3	1327.3	1327.3	1315.1

TEST NUMBER: P906948

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1507.3	1533.3	1528.7	1516.5	1507.3
115°	1708.7	1733.1	1725.5	1720.9	1708.7
117.5°	1908.6	1942.1	1920.8	1908.6	1896.4
120°	2110.0	2143.5	2110.0	2110.0	2096.2
122.5°	2293.0	2335.8	2314.4	2302.2	2293.0
125°	2485.3	2523.4	2511.2	2497.5	2492.9
127.5°	2672.9	2720.2	2703.4	2685.1	2672.9
130°	2848.4	2903.3	2895.7	2886.5	2869.7
132.5°	3045.2	3087.9	3090.9	3069.6	3057.4
135°	3214.5	3261.8	3271.0	3266.4	3254.2
137.5°	3403.7	3441.8	3449.5	3446.4	3428.1
140°	3570.0	3608.1	3629.5	3629.5	3612.7
142.5°	3740.9	3779.0	3791.2	3795.8	3779.0
145°	3902.6	3933.1	3957.5	3962.1	3945.3
147.5°	4047.5	4085.7	4104.0	4111.6	4094.8
150°	4197.0	4223.0	4239.8	4253.5	4239.8
152.5°	4329.8	4355.7	4377.1	4393.8	4377.1
155°	4462.5	4474.7	4488.4	4509.8	4496.1
157.5°	4576.9	4586.1	4593.7	4624.2	4602.9
160°	4679.1	4688.3	4692.9	4718.8	4700.5
162.5°	4773.7	4773.7	4778.3	4807.3	4785.9
165°	4854.6	4850.0	4850.0	4880.5	4859.2
167.5°	4927.8	4914.1	4914.1	4944.6	4923.2
170°	4982.7	4970.5	4966.0	4996.5	4970.5
172.5°	5020.9	5008.7	5004.1	5034.6	5008.7
175°	5051.4	5039.2	5030.0	5060.6	5034.6
177.5°	5068.2	5056.0	5046.8	5072.8	5046.8
180°	5060.6	5060.6	5060.6	5060.6	5060.6

TEST NUMBER: P906948

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.90	12.75	12.86	13.73	15.01	11.45	12.31	12.41	13.29	14.56
	3H	13.56	14.33	14.53	15.31	16.62	13.07	13.84	14.04	14.82	16.12
	4H	14.15	14.88	15.14	15.87	17.18	13.66	14.38	14.64	15.37	16.68
	6H	14.55	15.22	15.55	16.22	17.54	14.05	14.72	15.05	15.72	17.04
	8H	14.66	15.30	15.66	16.31	17.63	14.16	14.80	15.16	15.81	17.13
	12H	14.71	15.32	15.72	16.32	17.67	14.20	14.81	15.21	15.81	17.16
4H	2H	12.36	13.09	13.35	14.07	15.38	12.00	12.73	12.99	13.72	15.03
	3H	14.23	14.84	15.23	15.85	17.18	13.82	14.43	14.82	15.45	16.77
	4H	14.95	15.50	15.95	16.51	17.86	14.52	15.08	15.53	16.09	17.43
	6H	15.46	15.94	16.48	16.98	18.32	15.03	15.51	16.05	16.54	17.89
	8H	15.62	16.06	16.64	17.09	18.45	15.18	15.63	16.20	16.65	18.01
	12H	15.69	16.10	16.73	17.14	18.50	15.24	15.65	16.28	16.69	18.05
8H	4H	15.14	15.59	16.16	16.62	17.97	14.77	15.21	15.79	16.24	17.60
	6H	15.78	16.15	16.82	17.22	18.57	15.39	15.76	16.44	16.83	18.19
	8H	16.00	16.33	17.06	17.38	18.76	15.61	15.93	16.66	16.99	18.36
	12H	16.14	16.42	17.19	17.47	18.89	15.72	16.01	16.78	17.06	18.48
12H	4H	15.13	15.53	16.17	16.57	17.94	14.76	15.16	15.80	16.21	17.57
	6H	15.81	16.13	16.86	17.19	18.56	15.44	15.76	16.49	16.82	18.19
	8H	16.05	16.34	17.11	17.39	18.81	15.67	15.96	16.73	17.01	18.43