

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331476-927

Luminaire Tested: **S122DIW-S290D710U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331476-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D710U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2902.7 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331476-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331476-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	82	84	81	78	75	65	62	60	50	48	47	36	35	34	28
2	85	78	72	67	77	71	66	61	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	35	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	39	34	31	31	27	24	22	20	18	15
6	60	48	40	35	54	44	37	32	35	30	27	28	24	21	20	18	16	13
7	55	44	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	11	9
10	45	33	26	21	40	30	24	20	25	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6042	6042	6042
5°	6065	5977	6015
10°	6030	5917	5946
15°	5954	5840	5835
20°	5849	5727	5720
25°	5744	5585	5585
30°	5610	5455	5407
35°	5483	5298	5219
40°	5324	5143	5044
45°	5167	4987	4864
50°	4999	4828	4657
55°	4822	4642	4467
60°	4624	4414	4253
65°	4413	4195	4000
70°	4145	3923	3734
75°	3768	3612	3525
80°	3347	3245	3078
85°	2723	2594	2334



TEST NUMBER: P331476-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.2	1.2
10°-20°	99.0	3.4
20°-30°	145.6	5.0
30°-40°	169.1	5.8
40°-50°	168.9	5.8
50°-60°	147.3	5.1
60°-70°	108.9	3.8
70°-80°	61.7	2.1
80°-90°	19.4	0.7
90°-100°	44.1	1.5
100°-110°	137.1	4.7
110°-120°	234.3	8.1
120°-130°	308.1	10.6
130°-140°	345.9	11.9
140°-150°	339.1	11.7
150°-160°	284.5	9.8
160°-170°	188.7	6.5
170°-180°	65.9	2.3
0°-30°	279.8	9.6
0°-40°	448.8	15.5
0°-60°	765.0	26.4
0°-90°	955.0	32.9
90°-120°	415.5	14.3
90°-150°	1408.7	48.5
90°-180°	1948.0	67.1
0°-180°	2902.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	374	374	374	374	374	
5°	374	373	369	372	371	35
15°	356	354	349	351	349	100
25°	322	319	314	314	314	148
35°	278	274	269	267	265	174
45°	226	224	218	215	213	175
55°	171	169	165	161	159	153
65°	116	113	110	107	105	114
75°	60	60	58	56	56	65
85°	15	14	14	13	13	17
90°	1	8	21	20	20	2
95°	31	36	38	38	36	35
105°	126	128	129	130	130	133
115°	235	238	238	237	235	233
125°	342	347	346	344	343	306
135°	443	449	450	450	448	342
145°	537	541	545	545	543	336
155°	614	616	618	620	619	283
165°	668	668	668	672	669	188
175°	695	694	692	696	693	66
180°	697	697	697	697	697	



TEST NUMBER: P331476-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	376.0	375.7	375.3	375.0	374.7	374.2	373.5	372.8	372.1	371.4	372.0
5°	374.2	373.9	373.6	373.3	373.0	372.4	371.5	370.7	369.7	368.8	369.5
7.5°	371.0	370.4	369.9	369.5	369.0	368.3	367.4	366.5	365.6	364.7	365.4
10°	367.8	367.3	366.7	366.1	365.5	364.8	363.8	362.9	361.9	360.9	361.6
12.5°	363.5	363.0	362.5	361.9	361.5	360.8	359.8	358.9	357.9	357.0	357.4
15°	356.2	355.8	355.3	354.8	354.3	353.6	352.5	351.5	350.5	349.4	349.7
17.5°	347.1	346.6	346.1	345.6	345.2	344.4	343.3	342.2	341.2	340.2	340.5
20°	340.4	339.9	339.5	339.0	338.5	337.7	336.6	335.5	334.4	333.3	333.5
22.5°	333.8	333.1	332.5	331.8	331.1	330.3	329.2	328.1	327.1	326.1	326.1
25°	322.4	321.8	321.2	320.5	319.9	318.9	317.5	316.2	314.8	313.5	313.6
27.5°	309.5	309.0	308.3	307.8	307.2	306.3	305.3	304.2	303.2	302.1	301.8
30°	300.9	300.2	299.6	299.0	298.3	297.4	296.2	295.0	293.7	292.6	292.3
32.5°	291.6	291.1	290.7	290.1	289.6	288.7	287.4	286.2	284.9	283.7	283.2
35°	278.2	277.3	276.6	275.8	275.0	273.9	272.7	271.4	270.1	268.8	268.3
37.5°	263.0	262.3	261.6	260.9	260.2	259.2	257.9	256.7	255.3	254.1	253.5
40°	252.6	252.0	251.4	250.7	250.1	249.1	247.8	246.5	245.3	244.0	243.3
42.5°	242.6	241.9	241.3	240.7	240.0	239.0	237.7	236.5	235.2	233.9	233.1
45°	226.3	225.8	225.2	224.7	224.1	223.2	222.0	220.9	219.7	218.4	217.5
47.5°	210.2	209.7	209.2	208.7	208.1	207.2	206.0	204.8	203.5	202.2	201.3
50°	199.0	198.6	198.2	197.8	197.4	196.6	195.5	194.4	193.3	192.2	191.1
52.5°	188.1	187.5	187.0	186.5	185.9	185.1	184.1	183.1	182.0	180.9	180.0
55°	171.3	170.8	170.3	169.8	169.4	168.7	167.7	166.8	165.8	164.9	163.8
57.5°	154.5	154.1	153.7	153.3	152.9	152.2	151.1	150.1	149.0	148.0	147.0
60°	143.2	142.9	142.6	142.3	142.0	141.2	140.1	139.0	137.8	136.7	135.9
62.5°	132.3	131.7	131.3	130.8	130.2	129.5	128.7	127.9	127.0	126.1	125.2
65°	115.5	115.0	114.5	114.1	113.6	113.0	112.2	111.4	110.6	109.8	109.0
67.5°	98.5	98.1	97.7	97.3	97.0	96.4	95.6	94.9	94.2	93.5	92.9
70°	87.8	87.5	87.1	86.8	86.5	86.0	85.3	84.6	83.8	83.1	82.5
72.5°	76.8	76.5	76.2	75.9	75.6	75.2	74.7	74.3	73.8	73.4	72.8
75°	60.4	60.3	60.1	60.0	59.8	59.6	59.2	58.7	58.3	57.9	57.4
77.5°	45.8	45.5	45.2	45.0	44.7	44.4	44.3	44.1	44.0	43.8	43.6
80°	36.0	35.9	35.8	35.7	35.6	35.6	35.4	35.3	35.1	34.9	34.7
82.5°	26.8	26.8	26.8	26.7	26.7	26.6	26.5	26.5	26.4	26.3	26.0
85°	14.7	14.7	14.6	14.5	14.4	14.3	14.3	14.2	14.1	14.0	13.8
87.5°	5.3	5.5	5.7	5.9	6.0	6.3	6.8	7.3	7.7	8.2	7.9
90°	0.6	2.1	3.7	5.3	6.9	9.1	12.0	14.8	17.7	20.6	20.3
92.5°	10.5	11.6	12.8	13.9	15.1	16.0	16.6	17.3	18.0	18.7	18.8
95°	30.6	31.8	33.2	34.5	35.8	36.6	36.8	37.1	37.4	37.6	37.6
97.5°	55.8	57.0	58.1	59.3	60.4	61.2	61.8	62.3	62.7	63.2	63.2
100°	74.6	75.7	76.8	77.8	78.8	79.5	79.9	80.3	80.7	81.1	81.1
102.5°	94.4	95.2	96.1	96.9	97.8	98.4	98.9	99.4	99.9	100.4	100.5
105°	126.4	126.7	127.1	127.5	127.9	128.3	128.6	128.8	129.0	129.4	129.6
107.5°	158.6	159.1	159.8	160.3	160.9	161.2	161.2	161.2	161.2	161.2	161.3
110°	179.3	180.1	180.9	181.6	182.4	182.8	182.8	182.8	182.8	182.8	182.8



TEST NUMBER: P331476-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	201.8	202.6	203.4	204.2	205.0	205.3	205.3	205.1	205.0	204.9	204.6
115°	235.1	235.9	236.7	237.5	238.3	238.5	238.3	238.0	237.7	237.5	237.3
117.5°	268.3	269.3	270.4	271.4	272.4	272.6	271.9	271.2	270.5	269.7	269.4
120°	290.4	291.4	292.5	293.5	294.5	294.5	293.5	292.5	291.4	290.4	290.4
122.5°	310.6	311.9	313.1	314.3	315.6	315.9	315.1	314.4	313.7	313.0	312.7
125°	342.1	343.3	344.4	345.6	346.8	347.2	346.8	346.4	346.0	345.6	345.2
127.5°	372.8	374.3	375.8	377.2	378.7	379.3	378.8	378.3	377.9	377.4	376.9
130°	392.1	393.8	395.5	397.2	398.9	399.6	399.3	399.1	398.8	398.5	398.3
132.5°	413.8	415.1	416.5	417.9	419.2	420.0	420.0	420.1	420.2	420.2	419.6
135°	442.7	444.1	445.5	446.9	448.4	449.2	449.5	449.8	450.0	450.3	450.1
137.5°	473.1	474.3	475.5	476.7	477.8	478.6	478.9	479.3	479.6	479.9	479.8
140°	491.5	492.6	493.8	495.0	496.1	497.0	497.7	498.4	499.0	499.6	499.6
142.5°	510.2	511.4	512.6	513.8	514.9	515.8	516.2	516.7	517.1	517.5	517.6
145°	537.3	538.2	539.1	540.0	541.0	541.8	542.6	543.4	544.2	544.9	545.0
147.5°	561.4	562.4	563.6	564.7	565.8	566.6	567.1	567.6	568.2	568.7	568.9
150°	577.8	578.6	579.4	580.2	581.0	581.6	582.2	582.7	583.2	583.8	584.2
152.5°	592.4	593.2	594.0	594.8	595.6	596.3	596.9	597.5	598.2	598.8	599.3
155°	614.3	614.7	615.1	615.4	615.8	616.2	616.6	617.0	617.4	617.8	618.5
157.5°	633.0	633.3	633.5	633.7	634.1	634.3	634.5	634.8	635.0	635.3	636.1
160°	644.3	644.5	644.8	645.1	645.3	645.5	645.6	645.8	645.9	646.0	646.8
162.5°	654.6	654.7	654.7	654.7	654.8	654.9	655.1	655.2	655.3	655.5	656.3
165°	668.4	668.2	668.1	668.0	667.9	667.8	667.8	667.8	667.8	667.8	668.7
167.5°	679.9	679.5	679.1	678.7	678.3	678.1	678.1	678.0	678.0	678.0	678.9
170°	686.0	685.6	685.2	684.8	684.4	684.2	684.0	683.9	683.8	683.7	684.6
172.5°	690.2	689.8	689.4	689.0	688.6	688.4	688.2	688.2	688.0	687.9	688.8
175°	695.4	695.1	694.7	694.3	693.9	693.6	693.2	693.0	692.8	692.4	693.4
177.5°	697.5	697.2	696.9	696.6	696.2	696.0	695.8	695.6	695.4	695.1	695.8
180°	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6



TEST NUMBER: P331476-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	372.6	373.3	373.9	374.2	374.1	373.9	373.8	373.7
5°	370.2	370.8	371.5	371.7	371.5	371.4	371.2	371.1
7.5°	366.0	366.6	367.3	367.5	367.3	367.1	366.9	366.8
10°	362.3	362.9	363.5	363.7	363.5	363.2	363.0	362.7
12.5°	357.8	358.2	358.7	358.9	358.7	358.5	358.3	358.1
15°	350.1	350.4	350.7	350.7	350.3	349.9	349.5	349.1
17.5°	340.9	341.3	341.6	341.6	341.2	340.9	340.5	340.1
20°	333.7	334.0	334.2	334.1	333.8	333.5	333.2	332.9
22.5°	326.1	326.2	326.2	326.1	326.0	325.7	325.6	325.4
25°	313.8	313.9	314.1	314.1	313.9	313.8	313.6	313.5
27.5°	301.6	301.3	301.1	300.8	300.4	300.0	299.7	299.3
30°	292.1	291.8	291.6	291.4	291.0	290.7	290.4	290.0
32.5°	282.8	282.3	281.9	281.5	281.2	280.9	280.6	280.3
35°	267.8	267.4	266.9	266.5	266.1	265.7	265.3	264.8
37.5°	252.9	252.3	251.7	251.2	250.8	250.4	250.1	249.7
40°	242.6	241.9	241.1	240.6	240.3	240.0	239.6	239.3
42.5°	232.3	231.6	230.8	230.1	229.7	229.3	228.9	228.4
45°	216.7	215.8	214.9	214.3	214.0	213.7	213.3	213.0
47.5°	200.4	199.5	198.5	197.8	197.4	196.9	196.5	196.0
50°	190.0	188.8	187.7	187.0	186.6	186.2	185.8	185.4
52.5°	179.1	178.2	177.2	176.5	175.9	175.5	174.9	174.4
55°	162.9	161.9	161.0	160.3	159.9	159.5	159.1	158.7
57.5°	146.1	145.1	144.2	143.5	143.3	143.0	142.7	142.4
60°	135.0	134.1	133.2	132.7	132.5	132.2	132.0	131.7
62.5°	124.5	123.7	122.9	122.3	122.0	121.7	121.4	121.0
65°	108.3	107.6	106.9	106.3	105.9	105.5	105.1	104.7
67.5°	92.4	91.8	91.3	90.8	90.5	90.2	89.8	89.5
70°	82.0	81.4	80.9	80.5	80.2	79.8	79.5	79.1
72.5°	72.2	71.7	71.1	70.7	70.4	70.2	69.9	69.6
75°	57.0	56.5	56.0	55.8	56.0	56.2	56.3	56.5
77.5°	43.3	43.1	42.9	42.6	42.4	42.2	42.0	41.7
80°	34.5	34.2	34.0	33.7	33.6	33.4	33.3	33.1
82.5°	25.7	25.3	25.0	24.9	24.9	24.8	24.8	24.8
85°	13.5	13.3	13.1	12.9	12.8	12.8	12.7	12.6
87.5°	7.7	7.4	7.1	7.1	7.0	7.0	6.9	6.9
90°	20.0	19.8	19.6	19.5	19.6	19.7	19.9	20.0
92.5°	18.8	18.9	18.9	18.9	18.9	19.0	19.0	19.0
95°	37.6	37.6	37.6	37.5	37.2	37.0	36.7	36.4
97.5°	63.2	63.2	63.2	63.2	63.2	63.2	63.1	63.1
100°	81.1	81.1	81.1	81.0	81.0	80.8	80.6	80.6
102.5°	100.6	100.7	100.8	100.8	100.7	100.5	100.4	100.3
105°	129.8	130.1	130.4	130.5	130.5	130.5	130.5	130.5
107.5°	161.4	161.5	161.6	161.4	160.7	160.2	159.5	159.0
110°	182.8	182.8	182.8	182.6	182.2	181.8	181.4	181.1



TEST NUMBER: P331476-927

CATALOG NUMBER: S122DIW-S290D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	204.3	204.0	203.7	203.4	203.1	202.8	202.5	202.2
115°	237.3	237.1	236.9	236.7	236.3	235.9	235.5	235.1
117.5°	269.1	268.8	268.5	268.1	267.7	267.3	266.9	266.5
120°	290.4	290.4	290.4	290.2	289.8	289.4	289.0	288.6
122.5°	312.4	312.0	311.7	311.4	311.1	310.9	310.5	310.3
125°	344.8	344.4	344.0	343.8	343.7	343.6	343.4	343.3
127.5°	376.4	376.0	375.5	375.1	374.6	374.2	373.8	373.4
130°	398.1	397.8	397.5	397.1	396.6	396.1	395.5	395.1
132.5°	419.1	418.4	417.9	417.4	417.0	416.5	416.1	415.7
135°	450.0	449.9	449.8	449.5	449.1	448.7	448.3	447.9
137.5°	479.7	479.6	479.5	479.2	478.6	478.2	477.6	477.1
140°	499.6	499.6	499.6	499.4	498.9	498.4	497.8	497.3
142.5°	517.8	517.8	517.9	517.8	517.2	516.7	516.2	515.6
145°	545.2	545.3	545.4	545.3	544.7	544.2	543.7	543.2
147.5°	569.3	569.5	569.8	569.7	569.3	568.7	568.2	567.8
150°	584.5	584.9	585.3	585.3	584.9	584.5	584.2	583.8
152.5°	599.8	600.2	600.8	600.8	600.2	599.8	599.3	598.8
155°	619.1	619.8	620.4	620.6	620.2	619.8	619.4	619.0
157.5°	637.0	637.9	638.7	638.9	638.3	637.6	637.0	636.4
160°	647.6	648.4	649.2	649.3	648.8	648.2	647.8	647.2
162.5°	657.2	658.1	659.0	659.1	658.5	657.9	657.3	656.6
165°	669.6	670.5	671.5	671.6	670.9	670.3	669.6	669.0
167.5°	679.9	680.7	681.7	681.8	681.1	680.4	679.8	679.1
170°	685.5	686.4	687.3	687.4	686.6	685.8	685.0	684.2
172.5°	689.8	690.6	691.6	691.6	690.9	690.1	689.3	688.5
175°	694.3	695.2	696.2	696.2	695.4	694.7	693.9	693.1
177.5°	696.4	697.0	697.7	697.7	697.0	696.4	695.8	695.1
180°	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6

(END OF REPORT)