

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331514-927

Luminaire Tested: **S122DIW-S485D1240U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331514-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1240U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5106.7 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	72	67	63	58	54	51	45	42	40	32	31	30	25
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	23	18
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12429	12429	12429	12429
5°	13935	12511	11086	12511
10°	15967	12408	9594	12408
15°	17665	12179	8476	12179
20°	17395	11936	7727	11936
25°	15684	11610	7252	11610
30°	12961	11091	6906	11091
35°	9447	10549	6660	10549
40°	7546	9908	6521	9908
45°	6594	9168	6336	9168
50°	6199	8450	6212	8450
55°	5714	7721	6046	7721
60°	5238	6946	5790	6946
65°	4768	6250	5540	6250
70°	4329	5570	5169	5570
75°	3843	4816	4579	4816
80°	3301	3989	3682	3989
85°	2964	2964	2186	2964



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	1.4
10°-20°	213.1	4.2
20°-30°	309.3	6.1
30°-40°	326.4	6.4
40°-50°	289.0	5.7
50°-60°	230.6	4.5
60°-70°	156.8	3.1
70°-80°	80.4	1.6
80°-90°	24.2	0.5
90°-100°	77.1	1.5
100°-110°	239.6	4.7
110°-120°	409.5	8.0
120°-130°	538.5	10.5
130°-140°	604.4	11.8
140°-150°	592.6	11.6
150°-160°	497.0	9.7
160°-170°	329.7	6.5
170°-180°	115.2	2.3
0°-30°	595.8	11.7
0°-40°	922.2	18.1
0°-60°	1441.8	28.2
0°-90°	1703.2	33.4
90°-120°	726.2	14.2
90°-150°	2461.6	48.2
90°-180°	3404.0	66.7
0°-180°	5106.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	860	772	684	772	860	86
15°	1057	729	507	729	1057	292
25°	880	652	407	652	880	398
35°	479	535	338	535	479	312
45°	289	402	278	402	289	227
55°	203	274	215	274	203	182
65°	125	164	145	164	125	124
75°	62	77	73	77	62	66
85°	16	16	12	16	16	18
90°	35	1	35	1	35	16
95°	64	53	64	53	64	71
105°	228	221	228	221	228	240
115°	411	411	411	411	411	406
125°	600	598	600	598	600	535
135°	783	774	783	774	783	602
145°	949	939	949	939	949	593
155°	1082	1073	1082	1073	1082	498
165°	1169	1168	1169	1168	1169	330
175°	1211	1215	1211	1215	1211	115
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	805.3	805.6	806.0	802.2	801.8	801.8	798.4	795.6	792.3	787.7	788.2
5°	859.8	863.0	864.2	860.6	855.3	854.7	849.7	841.4	833.7	827.5	823.1
7.5°	924.7	926.0	923.1	918.5	914.5	907.4	898.0	888.8	876.0	864.2	855.5
10°	973.9	975.7	970.7	963.8	958.2	950.0	936.4	922.4	905.6	889.3	876.3
12.5°	1011.3	1015.7	1009.2	1008.4	998.7	987.4	971.1	964.1	940.4	917.7	903.7
15°	1056.8	1056.5	1057.1	1051.5	1044.3	1042.6	1025.4	1006.8	973.4	960.0	936.9
17.5°	1043.6	1048.1	1050.2	1050.1	1050.0	1048.8	1043.3	1031.6	1014.8	993.2	966.6
20°	1012.4	1018.3	1019.2	1026.0	1029.8	1034.9	1037.0	1033.7	1023.3	1005.3	982.2
22.5°	964.1	965.7	968.5	979.1	987.5	1000.1	1006.6	1017.6	1013.6	1004.8	985.6
25°	880.4	877.5	887.8	893.2	912.4	932.5	947.0	963.0	977.2	985.8	980.2
27.5°	780.0	775.5	791.1	805.2	820.8	842.6	865.1	891.8	914.0	941.8	951.3
30°	695.2	697.9	712.7	727.8	751.5	782.2	807.6	836.9	868.6	899.7	921.2
32.5°	603.9	614.1	623.4	646.6	667.4	701.7	739.0	775.6	815.2	850.4	883.8
35°	479.3	491.1	504.1	521.0	550.2	584.3	620.7	670.1	724.0	772.1	811.8
37.5°	403.4	401.6	409.0	421.2	444.9	472.4	514.2	563.1	626.5	683.1	739.0
40°	358.0	356.8	362.1	373.4	391.4	411.5	448.2	491.1	550.0	619.2	685.8
42.5°	326.7	327.4	330.4	338.3	350.7	367.3	394.7	431.3	485.1	550.3	621.9
45°	288.8	290.8	294.1	297.9	305.0	318.6	334.0	360.0	402.7	457.1	527.5
47.5°	261.4	261.5	264.7	268.2	272.4	280.0	292.6	309.0	339.0	383.3	443.9
50°	246.8	244.6	247.0	249.7	254.1	259.4	267.8	283.1	303.2	339.1	389.6
52.5°	228.8	228.8	230.9	232.0	235.9	241.2	248.8	259.4	277.7	305.7	347.3
55°	203.0	204.5	205.7	207.4	211.0	214.8	220.7	227.8	242.0	263.0	293.7
57.5°	178.7	179.2	180.4	183.7	186.0	189.5	195.1	201.6	210.8	226.4	249.5
60°	162.2	162.2	164.5	166.0	168.9	172.5	176.9	183.2	191.4	204.1	222.8
62.5°	146.9	146.7	147.7	150.1	152.3	155.7	160.1	165.4	173.2	184.5	199.8
65°	124.8	124.3	126.0	126.6	129.0	132.2	135.8	141.4	147.7	155.9	169.5
67.5°	103.5	104.3	105.2	106.3	107.7	111.1	113.4	117.4	122.6	129.5	138.8
70°	91.7	91.7	91.7	92.6	94.3	96.2	98.5	101.8	106.8	112.7	121.0
72.5°	78.4	79.4	80.3	79.9	82.1	83.1	86.0	87.8	92.6	96.4	103.7
75°	61.6	61.6	61.6	63.0	63.9	64.8	66.5	68.4	70.7	75.4	79.3
77.5°	45.9	45.8	46.1	46.4	47.4	48.5	49.0	50.6	52.8	55.0	58.2
80°	35.5	36.1	36.4	37.0	37.0	37.5	37.9	39.9	41.4	42.9	45.0
82.5°	27.5	27.6	27.6	27.7	28.0	28.4	29.1	29.8	30.3	31.5	33.1
85°	16.0	15.7	15.7	16.2	16.0	16.0	16.6	17.2	17.2	17.4	18.4
87.5°	13.2	13.1	13.3	13.0	13.0	13.2	13.3	13.2	13.5	13.8	13.1
90°	34.9	34.7	34.5	34.2	34.0	34.1	34.6	35.0	35.5	36.0	30.9
92.5°	33.3	33.3	33.2	33.1	33.1	33.0	33.0	32.9	32.7	32.6	31.4
95°	63.7	64.2	64.6	65.0	65.5	65.8	65.8	65.8	65.8	65.8	65.3
97.5°	110.4	110.4	110.4	110.4	110.5	110.5	110.5	110.5	110.5	110.5	109.6
100°	140.7	140.9	141.2	141.4	141.6	141.7	141.7	141.7	141.7	141.7	141.1
102.5°	175.2	175.5	175.7	175.9	176.2	176.2	176.0	175.8	175.6	175.5	174.6
105°	228.1	228.1	228.1	228.1	228.1	227.8	227.4	226.9	226.4	226.0	225.5
107.5°	277.7	278.8	279.9	280.9	281.9	282.4	282.2	282.0	281.9	281.6	281.6
110°	316.4	317.0	317.7	318.5	319.1	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.3	353.9	354.3	354.8	355.4	355.8	356.4	357.0	357.5	358.1	358.2
115°	410.9	411.5	412.3	413.0	413.6	414.1	414.3	414.5	414.8	414.9	415.4
117.5°	465.7	466.4	467.1	467.8	468.5	469.1	469.6	470.2	470.7	471.3	472.5
120°	504.4	505.0	505.7	506.4	507.1	507.4	507.4	507.4	507.4	507.4	509.2
122.5°	542.2	542.6	543.1	543.7	544.2	544.7	545.3	545.8	546.3	546.8	548.1
125°	599.8	600.1	600.3	600.6	600.8	601.3	601.9	602.6	603.3	604.0	604.7
127.5°	652.4	653.2	653.9	654.7	655.4	656.2	657.0	657.8	658.6	659.4	660.3
130°	690.2	691.2	692.1	693.0	694.0	694.6	695.1	695.5	695.9	696.4	696.9
132.5°	726.4	727.1	727.9	728.6	729.4	730.2	731.2	732.2	733.2	734.2	734.1
135°	782.7	783.4	784.1	784.7	785.4	785.9	786.2	786.4	786.6	786.8	786.4
137.5°	833.7	834.6	835.5	836.4	837.3	837.9	838.0	838.2	838.4	838.6	838.0
140°	869.0	869.9	870.8	871.7	872.7	873.1	873.1	873.1	873.1	873.1	872.0
142.5°	901.0	902.0	902.9	903.8	904.7	905.1	904.9	904.7	904.5	904.4	903.6
145°	949.1	950.1	950.9	951.9	952.8	953.1	952.9	952.7	952.4	952.2	950.9
147.5°	992.0	992.9	993.8	994.7	995.5	995.7	995.2	994.7	994.2	993.7	992.8
150°	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0	1019.1
152.5°	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3	1045.2
155°	1081.6	1082.3	1083.0	1083.7	1084.3	1084.1	1083.0	1081.9	1080.7	1079.6	1078.9
157.5°	1112.0	1113.1	1114.2	1115.3	1116.4	1116.2	1114.6	1113.1	1111.5	1110.0	1109.5
160°	1130.9	1131.9	1132.7	1133.7	1134.6	1134.3	1133.0	1131.6	1130.2	1128.9	1128.6
162.5°	1147.4	1148.4	1149.5	1150.6	1151.8	1151.5	1149.9	1148.4	1146.8	1145.3	1145.1
165°	1168.9	1170.1	1171.2	1172.4	1173.5	1173.3	1171.6	1170.1	1168.5	1166.9	1166.9
167.5°	1186.6	1187.8	1189.0	1190.2	1191.4	1191.1	1189.5	1188.0	1186.4	1184.7	1184.8
170°	1195.6	1197.0	1198.4	1199.8	1201.1	1201.0	1199.4	1197.8	1196.2	1194.6	1194.8
172.5°	1203.0	1204.4	1205.8	1207.1	1208.5	1208.4	1206.8	1205.2	1203.6	1202.0	1202.2
175°	1211.0	1212.4	1213.8	1215.1	1216.6	1216.4	1214.8	1213.2	1211.6	1210.0	1210.5
177.5°	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7	1215.1
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	789.9	788.0	786.8	782.6	778.8	775.0	773.8	774.3	769.1	764.1	762.0
5°	820.7	814.8	809.1	801.1	791.7	781.3	776.0	771.9	761.5	750.3	743.8
7.5°	848.3	839.8	828.9	814.0	800.2	783.9	773.5	764.4	749.2	733.3	723.7
10°	865.1	853.5	839.6	821.3	804.4	784.6	770.7	756.8	739.0	720.1	708.3
12.5°	879.5	864.0	850.2	826.7	806.8	782.0	765.5	745.9	727.2	704.7	693.1
15°	913.9	885.2	859.1	832.5	807.9	773.3	755.0	728.6	704.1	676.3	663.0
17.5°	940.4	908.2	867.2	833.4	804.7	766.4	739.4	707.9	678.8	647.1	629.0
20°	955.6	918.6	874.5	834.3	799.9	756.2	726.9	694.7	660.6	624.8	605.3
22.5°	964.6	925.7	882.1	830.8	790.5	747.9	711.1	675.7	641.2	602.6	582.1
25°	967.4	931.9	885.7	827.8	778.6	730.5	686.0	651.7	610.1	573.9	544.1
27.5°	953.3	927.9	883.5	822.2	765.0	708.6	659.2	620.3	576.2	537.1	507.0
30°	936.0	921.2	878.1	816.5	754.1	693.5	639.1	594.9	551.2	511.5	480.8
32.5°	909.3	906.1	868.2	808.5	742.5	674.3	618.0	573.4	524.9	485.9	456.6
35°	856.7	871.0	847.0	790.5	720.6	647.1	586.1	535.2	484.9	447.6	420.1
37.5°	786.4	821.7	815.4	764.1	691.2	617.3	550.0	496.9	448.9	411.3	384.3
40°	737.8	782.8	789.3	744.0	670.4	594.4	523.1	470.1	423.3	389.0	361.8
42.5°	685.8	738.3	756.2	719.9	647.7	570.2	498.9	444.1	397.8	364.4	340.3
45°	598.5	668.0	700.3	679.5	609.7	530.4	457.1	401.5	359.5	328.1	309.4
47.5°	516.9	592.9	636.3	628.9	567.5	489.0	416.5	363.1	322.3	297.2	280.5
50°	459.1	537.3	589.6	592.0	537.3	459.5	386.7	336.4	298.8	275.4	261.8
52.5°	409.0	483.5	540.7	553.2	503.4	428.6	359.9	309.9	276.8	255.3	243.1
55°	343.5	406.5	469.8	492.9	453.0	381.9	318.3	274.3	243.2	228.4	217.8
57.5°	285.6	338.1	396.6	422.1	397.4	336.7	277.0	238.8	213.6	200.6	192.4
60°	255.0	296.4	348.5	379.0	357.7	303.6	251.4	215.1	194.4	182.8	175.2
62.5°	226.6	263.3	307.3	335.2	323.6	272.5	225.9	193.8	175.9	165.1	159.5
65°	187.0	215.9	250.0	275.8	268.1	229.3	191.2	163.6	149.4	140.9	136.4
67.5°	153.9	174.9	198.5	221.0	214.8	187.4	156.8	135.3	124.7	117.3	114.7
70°	133.2	149.1	170.1	188.1	183.2	160.7	136.4	118.0	108.8	102.7	100.0
72.5°	113.3	126.4	142.4	157.2	153.8	135.1	114.9	101.0	94.0	88.2	86.0
75°	85.5	95.5	105.4	115.1	114.2	99.7	87.9	77.2	71.6	67.2	66.3
77.5°	63.1	68.8	75.4	81.2	79.6	71.3	62.0	55.9	51.8	48.8	48.3
80°	48.2	51.5	56.2	60.4	58.3	54.7	47.4	42.9	39.9	37.0	35.8
82.5°	34.9	38.3	41.0	43.3	41.7	38.4	33.8	30.8	29.1	27.0	26.5
85°	18.4	20.1	21.3	21.9	21.3	19.3	17.2	16.0	14.5	13.6	13.3
87.5°	12.3	11.2	10.3	10.0	8.7	8.2	6.7	5.4	5.7	6.0	6.1
90°	25.9	20.9	15.8	12.0	9.3	6.5	3.8	1.0	3.8	6.5	9.3
92.5°	30.3	29.1	27.9	26.3	24.3	22.3	20.3	18.3	20.3	22.3	24.3
95°	64.8	64.4	63.9	62.6	60.3	58.0	55.7	53.4	55.7	58.0	60.3
97.5°	108.8	107.9	107.0	105.6	103.6	101.6	99.6	97.6	99.6	101.6	103.6
100°	140.4	139.7	139.0	137.8	135.9	134.1	132.3	130.5	132.3	134.1	135.9
102.5°	173.7	172.9	172.0	170.8	169.4	167.9	166.4	164.9	166.4	167.9	169.4
105°	225.1	224.6	224.2	223.6	222.9	222.2	221.5	220.9	221.5	222.2	222.9
107.5°	281.6	281.6	281.6	281.1	280.1	279.2	278.1	277.1	278.1	279.2	280.1
110°	319.5	319.5	319.5	318.8	317.4	316.0	314.7	313.3	314.7	316.0	317.4



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	358.5	358.6	358.8	358.2	356.9	355.5	354.1	352.8	354.1	355.5	356.9
115°	415.9	416.4	416.8	416.4	414.9	413.6	412.3	410.9	412.3	413.6	414.9
117.5°	473.8	475.1	476.4	476.1	474.3	472.5	470.6	468.8	470.6	472.5	474.3
120°	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	509.2	511.1	512.9
122.5°	549.5	550.7	552.0	551.5	549.3	547.2	544.9	542.7	544.9	547.2	549.3
125°	605.4	606.0	606.7	606.0	604.0	601.9	599.8	597.8	599.8	601.9	604.0
127.5°	661.1	661.9	662.7	661.9	659.3	656.6	654.0	651.4	654.0	656.6	659.3
130°	697.4	697.8	698.2	697.0	694.0	691.1	688.1	685.2	688.1	691.1	694.0
132.5°	734.0	734.0	733.9	732.6	730.2	727.8	725.3	722.9	725.3	727.8	730.2
135°	785.9	785.4	785.0	783.5	781.0	778.5	775.9	773.5	775.9	778.5	781.0
137.5°	837.4	836.8	836.2	834.9	832.8	830.8	828.7	826.6	828.7	830.8	832.8
140°	870.8	869.7	868.5	867.0	864.9	862.8	860.8	858.7	860.8	862.8	864.9
142.5°	902.8	902.0	901.2	899.8	897.8	895.7	893.7	891.6	893.7	895.7	897.8
145°	949.4	948.1	946.7	945.2	943.6	942.1	940.5	938.8	940.5	942.1	943.6
147.5°	991.9	990.9	990.1	988.6	986.7	984.8	982.9	981.0	982.9	984.8	986.7
150°	1018.2	1017.2	1016.4	1015.2	1013.8	1012.5	1011.1	1009.7	1011.1	1012.5	1013.8
152.5°	1044.1	1043.0	1041.9	1040.7	1039.3	1037.9	1036.6	1035.2	1036.6	1037.9	1039.3
155°	1078.2	1077.5	1076.8	1076.2	1075.5	1074.8	1074.1	1073.4	1074.1	1074.8	1075.5
157.5°	1109.1	1108.7	1108.3	1107.9	1107.5	1107.0	1106.5	1106.0	1106.5	1107.0	1107.5
160°	1128.4	1128.1	1128.0	1127.6	1127.2	1126.7	1126.2	1125.8	1126.2	1126.7	1127.2
162.5°	1144.9	1144.6	1144.4	1144.2	1144.1	1144.1	1144.0	1143.8	1144.0	1144.1	1144.1
165°	1166.9	1166.9	1166.9	1167.0	1167.2	1167.4	1167.7	1167.9	1167.7	1167.4	1167.2
167.5°	1184.9	1184.9	1184.9	1185.3	1186.0	1186.7	1187.3	1188.0	1187.3	1186.7	1186.0
170°	1195.1	1195.3	1195.6	1196.0	1196.7	1197.4	1198.0	1198.7	1198.0	1197.4	1196.7
172.5°	1202.5	1202.7	1202.9	1203.4	1204.0	1204.8	1205.5	1206.1	1205.5	1204.8	1204.0
175°	1210.9	1211.4	1211.9	1212.4	1213.1	1213.8	1214.5	1215.1	1214.5	1213.8	1213.1
177.5°	1215.4	1215.8	1216.2	1216.6	1217.2	1217.7	1218.3	1218.9	1218.3	1217.7	1217.2
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	759.6	758.2	753.2	750.6	746.4	742.4	739.7	740.9	741.9	741.4	740.7
5°	737.8	732.2	723.7	716.2	710.9	701.2	697.0	695.0	693.2	691.1	689.0
7.5°	711.9	703.1	690.8	680.2	670.3	658.1	651.3	647.1	642.8	638.1	634.0
10°	693.5	681.0	668.0	653.2	641.4	630.4	620.7	614.2	608.2	602.6	598.5
12.5°	674.1	659.7	643.6	623.4	610.4	594.7	593.3	581.8	572.5	569.0	564.2
15°	643.2	623.1	602.6	578.7	568.3	554.1	545.3	536.4	528.4	522.8	521.3
17.5°	608.1	582.0	561.7	544.5	527.6	513.0	504.9	497.7	491.2	483.6	482.7
20°	581.3	558.9	536.7	521.6	504.1	489.3	479.3	472.1	466.5	462.1	458.3
22.5°	556.0	531.4	511.1	494.6	477.4	465.4	457.5	450.7	446.0	441.1	437.4
25°	515.4	496.1	474.0	455.3	441.1	433.4	426.9	421.0	418.0	414.8	410.7
27.5°	479.8	458.4	437.7	423.3	410.7	403.9	399.3	395.3	392.5	390.6	388.2
30°	454.7	433.1	416.8	402.7	392.3	385.5	382.5	380.2	376.9	375.7	374.5
32.5°	430.6	411.1	397.2	384.9	375.0	370.6	367.9	365.8	363.2	362.0	359.7
35°	396.4	380.2	366.5	359.7	351.7	347.9	345.9	342.9	340.6	339.4	339.1
37.5°	364.3	350.1	341.2	332.5	329.1	326.7	323.9	321.9	321.2	321.0	320.7
40°	343.5	331.9	323.9	316.9	315.4	311.8	309.4	307.7	307.7	308.0	307.7
42.5°	324.6	314.2	307.1	301.0	299.3	297.1	294.8	294.7	295.2	296.1	295.2
45°	295.9	288.4	283.4	280.4	277.2	275.1	274.8	275.8	276.0	276.3	277.2
47.5°	269.4	264.5	260.0	256.7	255.3	254.9	254.6	256.1	257.5	258.1	259.4
50°	253.8	248.2	244.4	242.3	241.1	240.5	241.1	242.9	244.1	245.6	246.4
52.5°	236.3	232.3	229.7	228.1	227.6	228.0	228.1	230.1	232.0	232.5	233.0
55°	212.1	209.1	208.6	205.9	207.1	206.8	208.3	209.5	211.2	213.0	213.3
57.5°	188.0	185.6	184.0	184.3	184.6	185.9	187.1	189.3	191.2	193.0	193.2
60°	171.9	170.7	169.8	169.8	170.4	172.2	173.6	175.7	176.9	178.1	179.0
62.5°	157.2	156.1	155.1	155.6	157.2	158.2	159.9	161.1	162.2	163.4	163.8
65°	134.0	133.4	134.4	134.9	135.2	136.7	138.8	139.7	140.9	141.4	143.5
67.5°	112.6	112.8	112.6	113.5	115.2	115.6	117.5	119.6	119.9	121.0	122.3
70°	98.2	98.8	99.4	100.0	101.5	102.0	103.5	104.4	105.6	106.5	107.4
72.5°	85.0	85.1	85.7	85.6	86.8	88.1	89.4	90.2	91.4	92.5	93.4
75°	65.4	65.4	66.0	66.3	67.7	69.2	68.9	69.6	70.7	71.9	72.5
77.5°	47.8	47.1	47.8	48.0	48.5	49.7	50.0	50.9	52.2	51.8	52.4
80°	36.4	35.5	36.4	36.7	36.7	38.2	38.2	38.7	39.6	38.7	39.6
82.5°	26.0	25.6	26.2	26.3	26.8	26.8	27.3	27.4	28.3	27.9	28.3
85°	13.0	12.8	13.0	12.8	13.0	13.3	13.3	13.0	13.0	13.6	12.8
87.5°	6.4	7.0	7.8	8.7	9.5	10.3	9.9	9.8	9.7	9.2	9.2
90°	12.0	15.8	20.9	25.9	30.9	36.0	35.5	35.0	34.6	34.1	34.0
92.5°	26.3	27.9	29.1	30.3	31.4	32.6	32.7	32.9	33.0	33.0	33.1
95°	62.6	63.9	64.4	64.8	65.3	65.8	65.8	65.8	65.8	65.8	65.5
97.5°	105.6	107.0	107.9	108.8	109.6	110.5	110.5	110.5	110.5	110.5	110.5
100°	137.8	139.0	139.7	140.4	141.1	141.7	141.7	141.7	141.7	141.7	141.6
102.5°	170.8	172.0	172.9	173.7	174.6	175.5	175.6	175.8	176.0	176.2	176.2
105°	223.6	224.2	224.6	225.1	225.5	226.0	226.4	226.9	227.4	227.8	228.1
107.5°	281.1	281.6	281.6	281.6	281.6	281.6	281.9	282.0	282.2	282.4	281.9
110°	318.8	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.1



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	358.2	358.8	358.6	358.5	358.2	358.1	357.5	357.0	356.4	355.8	355.4
115°	416.4	416.8	416.4	415.9	415.4	414.9	414.8	414.5	414.3	414.1	413.6
117.5°	476.1	476.4	475.1	473.8	472.5	471.3	470.7	470.2	469.6	469.1	468.5
120°	514.8	514.8	512.9	511.1	509.2	507.4	507.4	507.4	507.4	507.4	507.1
122.5°	551.5	552.0	550.7	549.5	548.1	546.8	546.3	545.8	545.3	544.7	544.2
125°	606.0	606.7	606.0	605.4	604.7	604.0	603.3	602.6	601.9	601.3	600.8
127.5°	661.9	662.7	661.9	661.1	660.3	659.4	658.6	657.8	657.0	656.2	655.4
130°	697.0	698.2	697.8	697.4	696.9	696.4	695.9	695.5	695.1	694.6	694.0
132.5°	732.6	733.9	734.0	734.0	734.1	734.2	733.2	732.2	731.2	730.2	729.4
135°	783.5	785.0	785.4	785.9	786.4	786.8	786.6	786.4	786.2	785.9	785.4
137.5°	834.9	836.2	836.8	837.4	838.0	838.6	838.4	838.2	838.0	837.9	837.3
140°	867.0	868.5	869.7	870.8	872.0	873.1	873.1	873.1	873.1	873.1	872.7
142.5°	899.8	901.2	902.0	902.8	903.6	904.4	904.5	904.7	904.9	905.1	904.7
145°	945.2	946.7	948.1	949.4	950.9	952.2	952.4	952.7	952.9	953.1	952.8
147.5°	988.6	990.1	990.9	991.9	992.8	993.7	994.2	994.7	995.2	995.7	995.5
150°	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7
152.5°	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7
155°	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7	1081.9	1083.0	1084.1	1084.3
157.5°	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5	1113.1	1114.6	1116.2	1116.4
160°	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2	1131.6	1133.0	1134.3	1134.6
162.5°	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8	1148.4	1149.9	1151.5	1151.8
165°	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5	1170.1	1171.6	1173.3	1173.5
167.5°	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4	1188.0	1189.5	1191.1	1191.4
170°	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2	1197.8	1199.4	1201.0	1201.1
172.5°	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6	1205.2	1206.8	1208.4	1208.5
175°	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6	1213.2	1214.8	1216.4	1216.6
177.5°	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	738.3	737.8	737.8	735.7	737.8	737.8	738.3	740.7	741.4	741.9	740.9
5°	684.9	684.0	682.5	684.0	682.5	684.0	684.9	689.0	691.1	693.2	695.0
7.5°	632.1	628.5	628.0	624.5	628.0	628.5	632.1	634.0	638.1	642.8	647.1
10°	593.5	591.1	590.8	585.2	590.8	591.1	593.5	598.5	602.6	608.2	614.2
12.5°	564.1	558.4	559.6	556.3	559.6	558.4	564.1	564.2	569.0	572.5	581.8
15°	513.3	513.3	512.1	507.1	512.1	513.3	513.3	521.3	522.8	528.4	536.4
17.5°	476.8	476.2	473.3	474.8	473.3	476.2	476.8	482.7	483.6	491.2	497.7
20°	455.0	453.2	449.7	449.7	449.7	453.2	455.0	458.3	462.1	466.5	472.1
22.5°	434.4	434.3	430.6	431.7	430.6	434.3	434.4	437.4	441.1	446.0	450.7
25°	410.4	408.0	406.2	407.1	406.2	408.0	410.4	410.7	414.8	418.0	421.0
27.5°	387.5	386.2	386.1	383.7	386.1	386.2	387.5	388.2	390.6	392.5	395.3
30°	374.2	371.3	371.9	370.4	371.9	371.3	374.2	374.5	375.7	376.9	380.2
32.5°	359.1	358.1	357.4	356.2	357.4	358.1	359.1	359.7	362.0	363.2	365.8
35°	338.4	338.7	337.2	337.9	337.2	338.7	338.4	339.1	339.4	340.6	342.9
37.5°	320.4	321.4	320.7	320.8	320.7	321.4	320.4	320.7	321.0	321.2	321.9
40°	308.6	308.6	308.6	309.4	308.6	308.6	308.6	307.7	308.0	307.7	307.7
42.5°	297.2	296.8	296.3	296.2	296.3	296.8	297.2	295.2	296.1	295.2	294.7
45°	277.8	278.7	279.0	277.5	279.0	278.7	277.8	277.2	276.3	276.0	275.8
47.5°	260.2	260.3	260.2	261.5	260.2	260.3	260.2	259.4	258.1	257.5	256.1
50°	248.0	247.3	248.0	247.3	248.0	247.3	248.0	246.4	245.6	244.1	242.9
52.5°	234.9	235.0	234.6	234.6	234.6	235.0	234.9	233.0	232.5	232.0	230.1
55°	214.5	215.1	214.8	214.8	214.8	215.1	214.5	213.3	213.0	211.2	209.5
57.5°	193.4	193.9	194.3	193.0	194.3	193.9	193.4	193.2	193.0	191.2	189.3
60°	178.7	180.1	179.9	179.3	179.9	180.1	178.7	179.0	178.1	176.9	175.7
62.5°	165.2	165.7	165.6	165.6	165.6	165.7	165.2	163.8	163.4	162.2	161.1
65°	144.3	145.0	144.1	145.0	144.1	145.0	144.3	143.5	141.4	140.9	139.7
67.5°	121.9	122.2	122.8	123.2	122.8	122.2	121.9	122.3	121.0	119.9	119.6
70°	108.0	107.7	108.6	109.5	108.6	107.7	108.0	107.4	106.5	105.6	104.4
72.5°	93.3	94.0	93.6	94.3	93.6	94.0	93.3	93.4	92.5	91.4	90.2
75°	71.9	72.8	72.5	73.4	72.5	72.8	71.9	72.5	71.9	70.7	69.6
77.5°	52.0	52.0	52.0	52.4	52.0	52.0	52.0	52.4	51.8	52.2	50.9
80°	39.6	39.1	38.4	39.6	38.4	39.1	39.6	39.6	38.7	39.6	38.7
82.5°	27.6	28.0	27.3	27.3	27.3	28.0	27.6	28.3	27.9	28.3	27.4
85°	12.8	12.4	11.8	11.8	11.8	12.4	12.8	12.8	13.6	13.0	13.0
87.5°	9.2	9.0	9.0	8.9	9.0	9.0	9.2	9.2	9.2	9.7	9.8
90°	34.2	34.5	34.7	34.9	34.7	34.5	34.2	34.0	34.1	34.6	35.0
92.5°	33.1	33.2	33.3	33.3	33.3	33.2	33.1	33.1	33.0	33.0	32.9
95°	65.0	64.6	64.2	63.7	64.2	64.6	65.0	65.5	65.8	65.8	65.8
97.5°	110.4	110.4	110.4	110.4	110.4	110.4	110.4	110.5	110.5	110.5	110.5
100°	141.4	141.2	140.9	140.7	140.9	141.2	141.4	141.6	141.7	141.7	141.7
102.5°	175.9	175.7	175.5	175.2	175.5	175.7	175.9	176.2	176.2	176.0	175.8
105°	228.1	228.1	228.1	228.1	228.1	228.1	228.1	228.1	227.8	227.4	226.9
107.5°	280.9	279.9	278.8	277.7	278.8	279.9	280.9	281.9	282.4	282.2	282.0
110°	318.5	317.7	317.0	316.4	317.0	317.7	318.5	319.1	319.5	319.5	319.5



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	354.8	354.3	353.9	353.3	353.9	354.3	354.8	355.4	355.8	356.4	357.0
115°	413.0	412.3	411.5	410.9	411.5	412.3	413.0	413.6	414.1	414.3	414.5
117.5°	467.8	467.1	466.4	465.7	466.4	467.1	467.8	468.5	469.1	469.6	470.2
120°	506.4	505.7	505.0	504.4	505.0	505.7	506.4	507.1	507.4	507.4	507.4
122.5°	543.7	543.1	542.6	542.2	542.6	543.1	543.7	544.2	544.7	545.3	545.8
125°	600.6	600.3	600.1	599.8	600.1	600.3	600.6	600.8	601.3	601.9	602.6
127.5°	654.7	653.9	653.2	652.4	653.2	653.9	654.7	655.4	656.2	657.0	657.8
130°	693.0	692.1	691.2	690.2	691.2	692.1	693.0	694.0	694.6	695.1	695.5
132.5°	728.6	727.9	727.1	726.4	727.1	727.9	728.6	729.4	730.2	731.2	732.2
135°	784.7	784.1	783.4	782.7	783.4	784.1	784.7	785.4	785.9	786.2	786.4
137.5°	836.4	835.5	834.6	833.7	834.6	835.5	836.4	837.3	837.9	838.0	838.2
140°	871.7	870.8	869.9	869.0	869.9	870.8	871.7	872.7	873.1	873.1	873.1
142.5°	903.8	902.9	902.0	901.0	902.0	902.9	903.8	904.7	905.1	904.9	904.7
145°	951.9	950.9	950.1	949.1	950.1	950.9	951.9	952.8	953.1	952.9	952.7
147.5°	994.7	993.8	992.9	992.0	992.9	993.8	994.7	995.5	995.7	995.2	994.7
150°	1022.1	1021.4	1020.6	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4
152.5°	1048.8	1048.1	1047.2	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1
155°	1083.7	1083.0	1082.3	1081.6	1082.3	1083.0	1083.7	1084.3	1084.1	1083.0	1081.9
157.5°	1115.3	1114.2	1113.1	1112.0	1113.1	1114.2	1115.3	1116.4	1116.2	1114.6	1113.1
160°	1133.7	1132.7	1131.9	1130.9	1131.9	1132.7	1133.7	1134.6	1134.3	1133.0	1131.6
162.5°	1150.6	1149.5	1148.4	1147.4	1148.4	1149.5	1150.6	1151.8	1151.5	1149.9	1148.4
165°	1172.4	1171.2	1170.1	1168.9	1170.1	1171.2	1172.4	1173.5	1173.3	1171.6	1170.1
167.5°	1190.2	1189.0	1187.8	1186.6	1187.8	1189.0	1190.2	1191.4	1191.1	1189.5	1188.0
170°	1199.8	1198.4	1197.0	1195.6	1197.0	1198.4	1199.8	1201.1	1201.0	1199.4	1197.8
172.5°	1207.1	1205.8	1204.4	1203.0	1204.4	1205.8	1207.1	1208.5	1208.4	1206.8	1205.2
175°	1215.1	1213.8	1212.4	1211.0	1212.4	1213.8	1215.1	1216.6	1216.4	1214.8	1213.2
177.5°	1218.1	1217.0	1215.8	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	739.7	742.4	746.4	750.6	753.2	758.2	759.6	762.0	764.1	769.1	774.3
5°	697.0	701.2	710.9	716.2	723.7	732.2	737.8	743.8	750.3	761.5	771.9
7.5°	651.3	658.1	670.3	680.2	690.8	703.1	711.9	723.7	733.3	749.2	764.4
10°	620.7	630.4	641.4	653.2	668.0	681.0	693.5	708.3	720.1	739.0	756.8
12.5°	593.3	594.7	610.4	623.4	643.6	659.7	674.1	693.1	704.7	727.2	745.9
15°	545.3	554.1	568.3	578.7	602.6	623.1	643.2	663.0	676.3	704.1	728.6
17.5°	504.9	513.0	527.6	544.5	561.7	582.0	608.1	629.0	647.1	678.8	707.9
20°	479.3	489.3	504.1	521.6	536.7	558.9	581.3	605.3	624.8	660.6	694.7
22.5°	457.5	465.4	477.4	494.6	511.1	531.4	556.0	582.1	602.6	641.2	675.7
25°	426.9	433.4	441.1	455.3	474.0	496.1	515.4	544.1	573.9	610.1	651.7
27.5°	399.3	403.9	410.7	423.3	437.7	458.4	479.8	507.0	537.1	576.2	620.3
30°	382.5	385.5	392.3	402.7	416.8	433.1	454.7	480.8	511.5	551.2	594.9
32.5°	367.9	370.6	375.0	384.9	397.2	411.1	430.6	456.6	485.9	524.9	573.4
35°	345.9	347.9	351.7	359.7	366.5	380.2	396.4	420.1	447.6	484.9	535.2
37.5°	323.9	326.7	329.1	332.5	341.2	350.1	364.3	384.3	411.3	448.9	496.9
40°	309.4	311.8	315.4	316.9	323.9	331.9	343.5	361.8	389.0	423.3	470.1
42.5°	294.8	297.1	299.3	301.0	307.1	314.2	324.6	340.3	364.4	397.8	444.1
45°	274.8	275.1	277.2	280.4	283.4	288.4	295.9	309.4	328.1	359.5	401.5
47.5°	254.6	254.9	255.3	256.7	260.0	264.5	269.4	280.5	297.2	322.3	363.1
50°	241.1	240.5	241.1	242.3	244.4	248.2	253.8	261.8	275.4	298.8	336.4
52.5°	228.1	228.0	227.6	228.1	229.7	232.3	236.3	243.1	255.3	276.8	309.9
55°	208.3	206.8	207.1	205.9	208.6	209.1	212.1	217.8	228.4	243.2	274.3
57.5°	187.1	185.9	184.6	184.3	184.0	185.6	188.0	192.4	200.6	213.6	238.8
60°	173.6	172.2	170.4	169.8	169.8	170.7	171.9	175.2	182.8	194.4	215.1
62.5°	159.9	158.2	157.2	155.6	155.1	156.1	157.2	159.5	165.1	175.9	193.8
65°	138.8	136.7	135.2	134.9	134.4	133.4	134.0	136.4	140.9	149.4	163.6
67.5°	117.5	115.6	115.2	113.5	112.6	112.8	112.6	114.7	117.3	124.7	135.3
70°	103.5	102.0	101.5	100.0	99.4	98.8	98.2	100.0	102.7	108.8	118.0
72.5°	89.4	88.1	86.8	85.6	85.7	85.1	85.0	86.0	88.2	94.0	101.0
75°	68.9	69.2	67.7	66.3	66.0	65.4	65.4	66.3	67.2	71.6	77.2
77.5°	50.0	49.7	48.5	48.0	47.8	47.1	47.8	48.3	48.8	51.8	55.9
80°	38.2	38.2	36.7	36.7	36.4	35.5	36.4	35.8	37.0	39.9	42.9
82.5°	27.3	26.8	26.8	26.3	26.2	25.6	26.0	26.5	27.0	29.1	30.8
85°	13.3	13.3	13.0	12.8	13.0	12.8	13.0	13.3	13.6	14.5	16.0
87.5°	9.9	10.3	9.5	8.7	7.8	7.0	6.4	6.1	6.0	5.7	5.4
90°	35.5	36.0	30.9	25.9	20.9	15.8	12.0	9.3	6.5	3.8	1.0
92.5°	32.7	32.6	31.4	30.3	29.1	27.9	26.3	24.3	22.3	20.3	18.3
95°	65.8	65.8	65.3	64.8	64.4	63.9	62.6	60.3	58.0	55.7	53.4
97.5°	110.5	110.5	109.6	108.8	107.9	107.0	105.6	103.6	101.6	99.6	97.6
100°	141.7	141.7	141.1	140.4	139.7	139.0	137.8	135.9	134.1	132.3	130.5
102.5°	175.6	175.5	174.6	173.7	172.9	172.0	170.8	169.4	167.9	166.4	164.9
105°	226.4	226.0	225.5	225.1	224.6	224.2	223.6	222.9	222.2	221.5	220.9
107.5°	281.9	281.6	281.6	281.6	281.6	281.6	281.1	280.1	279.2	278.1	277.1
110°	319.5	319.5	319.5	319.5	319.5	319.5	318.8	317.4	316.0	314.7	313.3



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	357.5	358.1	358.2	358.5	358.6	358.8	358.2	356.9	355.5	354.1	352.8
115°	414.8	414.9	415.4	415.9	416.4	416.8	416.4	414.9	413.6	412.3	410.9
117.5°	470.7	471.3	472.5	473.8	475.1	476.4	476.1	474.3	472.5	470.6	468.8
120°	507.4	507.4	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4
122.5°	546.3	546.8	548.1	549.5	550.7	552.0	551.5	549.3	547.2	544.9	542.7
125°	603.3	604.0	604.7	605.4	606.0	606.7	606.0	604.0	601.9	599.8	597.8
127.5°	658.6	659.4	660.3	661.1	661.9	662.7	661.9	659.3	656.6	654.0	651.4
130°	695.9	696.4	696.9	697.4	697.8	698.2	697.0	694.0	691.1	688.1	685.2
132.5°	733.2	734.2	734.1	734.0	734.0	733.9	732.6	730.2	727.8	725.3	722.9
135°	786.6	786.8	786.4	785.9	785.4	785.0	783.5	781.0	778.5	775.9	773.5
137.5°	838.4	838.6	838.0	837.4	836.8	836.2	834.9	832.8	830.8	828.7	826.6
140°	873.1	873.1	872.0	870.8	869.7	868.5	867.0	864.9	862.8	860.8	858.7
142.5°	904.5	904.4	903.6	902.8	902.0	901.2	899.8	897.8	895.7	893.7	891.6
145°	952.4	952.2	950.9	949.4	948.1	946.7	945.2	943.6	942.1	940.5	938.8
147.5°	994.2	993.7	992.8	991.9	990.9	990.1	988.6	986.7	984.8	982.9	981.0
150°	1020.6	1020.0	1019.1	1018.2	1017.2	1016.4	1015.2	1013.8	1012.5	1011.1	1009.7
152.5°	1047.2	1046.3	1045.2	1044.1	1043.0	1041.9	1040.7	1039.3	1037.9	1036.6	1035.2
155°	1080.7	1079.6	1078.9	1078.2	1077.5	1076.8	1076.2	1075.5	1074.8	1074.1	1073.4
157.5°	1111.5	1110.0	1109.5	1109.1	1108.7	1108.3	1107.9	1107.5	1107.0	1106.5	1106.0
160°	1130.2	1128.9	1128.6	1128.4	1128.1	1128.0	1127.6	1127.2	1126.7	1126.2	1125.8
162.5°	1146.8	1145.3	1145.1	1144.9	1144.6	1144.4	1144.2	1144.1	1144.1	1144.0	1143.8
165°	1168.5	1166.9	1166.9	1166.9	1166.9	1166.9	1167.0	1167.2	1167.4	1167.7	1167.9
167.5°	1186.4	1184.7	1184.8	1184.9	1184.9	1184.9	1185.3	1186.0	1186.7	1187.3	1188.0
170°	1196.2	1194.6	1194.8	1195.1	1195.3	1195.6	1196.0	1196.7	1197.4	1198.0	1198.7
172.5°	1203.6	1202.0	1202.2	1202.5	1202.7	1202.9	1203.4	1204.0	1204.8	1205.5	1206.1
175°	1211.6	1210.0	1210.5	1210.9	1211.4	1211.9	1212.4	1213.1	1213.8	1214.5	1215.1
177.5°	1215.8	1214.7	1215.1	1215.4	1215.8	1216.2	1216.6	1217.2	1217.7	1218.3	1218.9
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	773.8	775.0	778.8	782.6	786.8	788.0	789.9	788.2	787.7	792.3	795.6
5°	776.0	781.3	791.7	801.1	809.1	814.8	820.7	823.1	827.5	833.7	841.4
7.5°	773.5	783.9	800.2	814.0	828.9	839.8	848.3	855.5	864.2	876.0	888.8
10°	770.7	784.6	804.4	821.3	839.6	853.5	865.1	876.3	889.3	905.6	922.4
12.5°	765.5	782.0	806.8	826.7	850.2	864.0	879.5	903.7	917.7	940.4	964.1
15°	755.0	773.3	807.9	832.5	859.1	885.2	913.9	936.9	960.0	973.4	1006.8
17.5°	739.4	766.4	804.7	833.4	867.2	908.2	940.4	966.6	993.2	1014.8	1031.6
20°	726.9	756.2	799.9	834.3	874.5	918.6	955.6	982.2	1005.3	1023.3	1033.7
22.5°	711.1	747.9	790.5	830.8	882.1	925.7	964.6	985.6	1004.8	1013.6	1017.6
25°	686.0	730.5	778.6	827.8	885.7	931.9	967.4	980.2	985.8	977.2	963.0
27.5°	659.2	708.6	765.0	822.2	883.5	927.9	953.3	951.3	941.8	914.0	891.8
30°	639.1	693.5	754.1	816.5	878.1	921.2	936.0	921.2	899.7	868.6	836.9
32.5°	618.0	674.3	742.5	808.5	868.2	906.1	909.3	883.8	850.4	815.2	775.6
35°	586.1	647.1	720.6	790.5	847.0	871.0	856.7	811.8	772.1	724.0	670.1
37.5°	550.0	617.3	691.2	764.1	815.4	821.7	786.4	739.0	683.1	626.5	563.1
40°	523.1	594.4	670.4	744.0	789.3	782.8	737.8	685.8	619.2	550.0	491.1
42.5°	498.9	570.2	647.7	719.9	756.2	738.3	685.8	621.9	550.3	485.1	431.3
45°	457.1	530.4	609.7	679.5	700.3	668.0	598.5	527.5	457.1	402.7	360.0
47.5°	416.5	489.0	567.5	628.9	636.3	592.9	516.9	443.9	383.3	339.0	309.0
50°	386.7	459.5	537.3	592.0	589.6	537.3	459.1	389.6	339.1	303.2	283.1
52.5°	359.9	428.6	503.4	553.2	540.7	483.5	409.0	347.3	305.7	277.7	259.4
55°	318.3	381.9	453.0	492.9	469.8	406.5	343.5	293.7	263.0	242.0	227.8
57.5°	277.0	336.7	397.4	422.1	396.6	338.1	285.6	249.5	226.4	210.8	201.6
60°	251.4	303.6	357.7	379.0	348.5	296.4	255.0	222.8	204.1	191.4	183.2
62.5°	225.9	272.5	323.6	335.2	307.3	263.3	226.6	199.8	184.5	173.2	165.4
65°	191.2	229.3	268.1	275.8	250.0	215.9	187.0	169.5	155.9	147.7	141.4
67.5°	156.8	187.4	214.8	221.0	198.5	174.9	153.9	138.8	129.5	122.6	117.4
70°	136.4	160.7	183.2	188.1	170.1	149.1	133.2	121.0	112.7	106.8	101.8
72.5°	114.9	135.1	153.8	157.2	142.4	126.4	113.3	103.7	96.4	92.6	87.8
75°	87.9	99.7	114.2	115.1	105.4	95.5	85.5	79.3	75.4	70.7	68.4
77.5°	62.0	71.3	79.6	81.2	75.4	68.8	63.1	58.2	55.0	52.8	50.6
80°	47.4	54.7	58.3	60.4	56.2	51.5	48.2	45.0	42.9	41.4	39.9
82.5°	33.8	38.4	41.7	43.3	41.0	38.3	34.9	33.1	31.5	30.3	29.8
85°	17.2	19.3	21.3	21.9	21.3	20.1	18.4	18.4	17.4	17.2	17.2
87.5°	6.7	8.2	8.7	10.0	10.3	11.2	12.3	13.1	13.8	13.5	13.2
90°	3.8	6.5	9.3	12.0	15.8	20.9	25.9	30.9	36.0	35.5	35.0
92.5°	20.3	22.3	24.3	26.3	27.9	29.1	30.3	31.4	32.6	32.7	32.9
95°	55.7	58.0	60.3	62.6	63.9	64.4	64.8	65.3	65.8	65.8	65.8
97.5°	99.6	101.6	103.6	105.6	107.0	107.9	108.8	109.6	110.5	110.5	110.5
100°	132.3	134.1	135.9	137.8	139.0	139.7	140.4	141.1	141.7	141.7	141.7
102.5°	166.4	167.9	169.4	170.8	172.0	172.9	173.7	174.6	175.5	175.6	175.8
105°	221.5	222.2	222.9	223.6	224.2	224.6	225.1	225.5	226.0	226.4	226.9
107.5°	278.1	279.2	280.1	281.1	281.6	281.6	281.6	281.6	281.6	281.9	282.0
110°	314.7	316.0	317.4	318.8	319.5	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	354.1	355.5	356.9	358.2	358.8	358.6	358.5	358.2	358.1	357.5	357.0
115°	412.3	413.6	414.9	416.4	416.8	416.4	415.9	415.4	414.9	414.8	414.5
117.5°	470.6	472.5	474.3	476.1	476.4	475.1	473.8	472.5	471.3	470.7	470.2
120°	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	507.4	507.4
122.5°	544.9	547.2	549.3	551.5	552.0	550.7	549.5	548.1	546.8	546.3	545.8
125°	599.8	601.9	604.0	606.0	606.7	606.0	605.4	604.7	604.0	603.3	602.6
127.5°	654.0	656.6	659.3	661.9	662.7	661.9	661.1	660.3	659.4	658.6	657.8
130°	688.1	691.1	694.0	697.0	698.2	697.8	697.4	696.9	696.4	695.9	695.5
132.5°	725.3	727.8	730.2	732.6	733.9	734.0	734.0	734.1	734.2	733.2	732.2
135°	775.9	778.5	781.0	783.5	785.0	785.4	785.9	786.4	786.8	786.6	786.4
137.5°	828.7	830.8	832.8	834.9	836.2	836.8	837.4	838.0	838.6	838.4	838.2
140°	860.8	862.8	864.9	867.0	868.5	869.7	870.8	872.0	873.1	873.1	873.1
142.5°	893.7	895.7	897.8	899.8	901.2	902.0	902.8	903.6	904.4	904.5	904.7
145°	940.5	942.1	943.6	945.2	946.7	948.1	949.4	950.9	952.2	952.4	952.7
147.5°	982.9	984.8	986.7	988.6	990.1	990.9	991.9	992.8	993.7	994.2	994.7
150°	1011.1	1012.5	1013.8	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6	1021.4
152.5°	1036.6	1037.9	1039.3	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2	1048.1
155°	1074.1	1074.8	1075.5	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7	1081.9
157.5°	1106.5	1107.0	1107.5	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5	1113.1
160°	1126.2	1126.7	1127.2	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2	1131.6
162.5°	1144.0	1144.1	1144.1	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8	1148.4
165°	1167.7	1167.4	1167.2	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5	1170.1
167.5°	1187.3	1186.7	1186.0	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4	1188.0
170°	1198.0	1197.4	1196.7	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2	1197.8
172.5°	1205.5	1204.8	1204.0	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6	1205.2
175°	1214.5	1213.8	1213.1	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6	1213.2
177.5°	1218.3	1217.7	1217.2	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8	1217.0
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	798.4	801.8	801.8	802.2	806.0	805.6	805.3
5°	849.7	854.7	855.3	860.6	864.2	863.0	859.8
7.5°	898.0	907.4	914.5	918.5	923.1	926.0	924.7
10°	936.4	950.0	958.2	963.8	970.7	975.7	973.9
12.5°	971.1	987.4	998.7	1008.4	1009.2	1015.7	1011.3
15°	1025.4	1042.6	1044.3	1051.5	1057.1	1056.5	1056.8
17.5°	1043.3	1048.8	1050.0	1050.1	1050.2	1048.1	1043.6
20°	1037.0	1034.9	1029.8	1026.0	1019.2	1018.3	1012.4
22.5°	1006.6	1000.1	987.5	979.1	968.5	965.7	964.1
25°	947.0	932.5	912.4	893.2	887.8	877.5	880.4
27.5°	865.1	842.6	820.8	805.2	791.1	775.5	780.0
30°	807.6	782.2	751.5	727.8	712.7	697.9	695.2
32.5°	739.0	701.7	667.4	646.6	623.4	614.1	603.9
35°	620.7	584.3	550.2	521.0	504.1	491.1	479.3
37.5°	514.2	472.4	444.9	421.2	409.0	401.6	403.4
40°	448.2	411.5	391.4	373.4	362.1	356.8	358.0
42.5°	394.7	367.3	350.7	338.3	330.4	327.4	326.7
45°	334.0	318.6	305.0	297.9	294.1	290.8	288.8
47.5°	292.6	280.0	272.4	268.2	264.7	261.5	261.4
50°	267.8	259.4	254.1	249.7	247.0	244.6	246.8
52.5°	248.8	241.2	235.9	232.0	230.9	228.8	228.8
55°	220.7	214.8	211.0	207.4	205.7	204.5	203.0
57.5°	195.1	189.5	186.0	183.7	180.4	179.2	178.7
60°	176.9	172.5	168.9	166.0	164.5	162.2	162.2
62.5°	160.1	155.7	152.3	150.1	147.7	146.7	146.9
65°	135.8	132.2	129.0	126.6	126.0	124.3	124.8
67.5°	113.4	111.1	107.7	106.3	105.2	104.3	103.5
70°	98.5	96.2	94.3	92.6	91.7	91.7	91.7
72.5°	86.0	83.1	82.1	79.9	80.3	79.4	78.4
75°	66.5	64.8	63.9	63.0	61.6	61.6	61.6
77.5°	49.0	48.5	47.4	46.4	46.1	45.8	45.9
80°	37.9	37.5	37.0	37.0	36.4	36.1	35.5
82.5°	29.1	28.4	28.0	27.7	27.6	27.6	27.5
85°	16.6	16.0	16.0	16.2	15.7	15.7	16.0
87.5°	13.3	13.2	13.0	13.0	13.3	13.1	13.2
90°	34.6	34.1	34.0	34.2	34.5	34.7	34.9
92.5°	33.0	33.0	33.1	33.1	33.2	33.3	33.3
95°	65.8	65.8	65.5	65.0	64.6	64.2	63.7
97.5°	110.5	110.5	110.5	110.4	110.4	110.4	110.4
100°	141.7	141.7	141.6	141.4	141.2	140.9	140.7
102.5°	176.0	176.2	176.2	175.9	175.7	175.5	175.2
105°	227.4	227.8	228.1	228.1	228.1	228.1	228.1
107.5°	282.2	282.4	281.9	280.9	279.9	278.8	277.7
110°	319.5	319.5	319.1	318.5	317.7	317.0	316.4



TEST NUMBER: P331514-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	356.4	355.8	355.4	354.8	354.3	353.9	353.3
115°	414.3	414.1	413.6	413.0	412.3	411.5	410.9
117.5°	469.6	469.1	468.5	467.8	467.1	466.4	465.7
120°	507.4	507.4	507.1	506.4	505.7	505.0	504.4
122.5°	545.3	544.7	544.2	543.7	543.1	542.6	542.2
125°	601.9	601.3	600.8	600.6	600.3	600.1	599.8
127.5°	657.0	656.2	655.4	654.7	653.9	653.2	652.4
130°	695.1	694.6	694.0	693.0	692.1	691.2	690.2
132.5°	731.2	730.2	729.4	728.6	727.9	727.1	726.4
135°	786.2	785.9	785.4	784.7	784.1	783.4	782.7
137.5°	838.0	837.9	837.3	836.4	835.5	834.6	833.7
140°	873.1	873.1	872.7	871.7	870.8	869.9	869.0
142.5°	904.9	905.1	904.7	903.8	902.9	902.0	901.0
145°	952.9	953.1	952.8	951.9	950.9	950.1	949.1
147.5°	995.2	995.7	995.5	994.7	993.8	992.9	992.0
150°	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0
152.5°	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3
155°	1083.0	1084.1	1084.3	1083.7	1083.0	1082.3	1081.6
157.5°	1114.6	1116.2	1116.4	1115.3	1114.2	1113.1	1112.0
160°	1133.0	1134.3	1134.6	1133.7	1132.7	1131.9	1130.9
162.5°	1149.9	1151.5	1151.8	1150.6	1149.5	1148.4	1147.4
165°	1171.6	1173.3	1173.5	1172.4	1171.2	1170.1	1168.9
167.5°	1189.5	1191.1	1191.4	1190.2	1189.0	1187.8	1186.6
170°	1199.4	1201.0	1201.1	1199.8	1198.4	1197.0	1195.6
172.5°	1206.8	1208.4	1208.5	1207.1	1205.8	1204.4	1203.0
175°	1214.8	1216.4	1216.6	1215.1	1213.8	1212.4	1211.0
177.5°	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2

(END OF REPORT)