

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331518-927

Luminaire Tested: **S122DIW-S485D1240U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331518-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S485D1240U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4973.8 lumens  
Efficiency: N/A  
Efficacy: 92.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331518-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331518-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9935	9935	9935
5°	9972	9828	9887
10°	9914	9729	9778
15°	9790	9603	9593
20°	9617	9414	9402
25°	9444	9180	9180
30°	9221	8968	8889
35°	9014	8712	8584
40°	8753	8456	8292
45°	8499	8200	7996
50°	8219	7935	7654
55°	7927	7626	7344
60°	7601	7259	6991
65°	7255	6896	6575
70°	6812	6453	6146
75°	6201	5939	5795
80°	5504	5337	5058
85°	4483	4279	3835



TEST NUMBER: P331518-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.9	1.2
10°-20°	162.8	3.3
20°-30°	239.3	4.8
30°-40°	278.0	5.6
40°-50°	277.7	5.6
50°-60°	242.1	4.9
60°-70°	179.0	3.6
70°-80°	101.4	2.0
80°-90°	32.1	0.6
90°-100°	77.1	1.6
100°-110°	239.6	4.8
110°-120°	409.5	8.2
120°-130°	538.5	10.8
130°-140°	604.4	12.2
140°-150°	592.6	11.9
150°-160°	497.0	10.0
160°-170°	329.7	6.6
170°-180°	115.2	2.3
0°-30°	459.9	9.2
0°-40°	737.9	14.8
0°-60°	1257.7	25.3
0°-90°	1570.3	31.6
90°-120°	726.2	14.6
90°-150°	2461.6	49.5
90°-180°	3404.0	68.4
0°-180°	4973.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	615	615	615	615	615	
5°	615	613	606	611	610	58
15°	586	582	574	577	574	165
25°	530	525	515	516	515	244
35°	457	451	442	438	436	285
45°	372	368	359	353	350	287
55°	282	278	271	264	261	252
65°	190	186	180	175	172	188
75°	99	98	95	92	93	106
85°	24	24	23	21	21	28
90°	1	14	36	34	35	4
95°	53	63	66	66	64	61
105°	221	224	226	228	228	233
115°	411	417	415	414	411	406
125°	598	606	604	601	600	534
135°	774	784	787	786	783	597
145°	939	946	952	953	949	586
155°	1073	1076	1080	1084	1082	494
165°	1168	1167	1167	1173	1169	329
175°	1215	1212	1210	1216	1211	115
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P331518-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	618.1	617.6	617.1	616.6	616.0	615.2	614.0	612.9	611.7	610.5	611.6
5°	615.3	614.7	614.3	613.7	613.2	612.2	610.8	609.3	607.8	606.4	607.4
7.5°	609.8	609.0	608.2	607.4	606.6	605.5	604.0	602.5	601.0	599.5	600.6
10°	604.7	603.7	602.8	601.9	600.9	599.7	598.1	596.6	595.0	593.4	594.5
12.5°	597.5	596.8	595.9	595.1	594.3	593.1	591.5	589.9	588.4	586.8	587.5
15°	585.7	584.9	584.2	583.4	582.6	581.3	579.6	577.9	576.2	574.5	575.0
17.5°	570.5	569.8	569.0	568.2	567.4	566.2	564.4	562.7	560.9	559.2	559.8
20°	559.7	558.9	558.1	557.3	556.5	555.2	553.3	551.5	549.7	547.9	548.3
22.5°	548.8	547.7	546.6	545.5	544.4	543.0	541.2	539.5	537.7	536.0	536.1
25°	530.1	529.0	528.0	527.0	525.9	524.3	522.0	519.8	517.5	515.3	515.6
27.5°	508.8	507.9	506.9	506.0	505.0	503.7	501.9	500.1	498.4	496.6	496.2
30°	494.6	493.5	492.5	491.5	490.4	488.9	486.9	485.0	483.0	481.0	480.6
32.5°	479.4	478.6	477.8	476.9	476.1	474.6	472.5	470.5	468.4	466.4	465.6
35°	457.3	456.0	454.7	453.4	452.1	450.4	448.3	446.2	444.0	442.0	441.2
37.5°	432.4	431.2	430.1	428.9	427.7	426.1	424.0	421.9	419.8	417.7	416.7
40°	415.3	414.2	413.2	412.2	411.1	409.6	407.4	405.4	403.2	401.2	400.0
42.5°	398.8	397.7	396.6	395.6	394.6	393.0	390.9	388.8	386.7	384.5	383.3
45°	372.2	371.2	370.3	369.4	368.4	367.0	365.0	363.1	361.1	359.1	357.7
47.5°	345.6	344.8	343.9	343.0	342.1	340.7	338.7	336.6	334.5	332.5	331.0
50°	327.2	326.5	325.8	325.2	324.6	323.3	321.5	319.6	317.7	315.9	314.1
52.5°	309.2	308.3	307.4	306.6	305.7	304.4	302.7	301.0	299.2	297.5	296.0
55°	281.6	280.8	280.0	279.2	278.5	277.3	275.7	274.1	272.5	270.9	269.4
57.5°	253.9	253.3	252.6	252.1	251.4	250.3	248.5	246.8	245.0	243.3	241.7
60°	235.4	235.0	234.4	233.9	233.4	232.2	230.4	228.5	226.6	224.8	223.4
62.5°	217.5	216.7	215.8	214.9	214.1	213.0	211.6	210.2	208.7	207.3	206.0
65°	189.9	189.1	188.3	187.5	186.8	185.7	184.4	183.1	181.7	180.5	179.3
67.5°	161.8	161.2	160.6	159.9	159.3	158.4	157.2	156.1	154.9	153.7	152.8
70°	144.3	143.9	143.3	142.8	142.3	141.4	140.2	139.0	137.8	136.7	135.8
72.5°	126.4	125.9	125.3	124.8	124.3	123.7	122.9	122.1	121.4	120.6	119.6
75°	99.4	99.1	98.9	98.6	98.3	97.9	97.2	96.6	95.9	95.2	94.4
77.5°	75.3	74.8	74.4	73.9	73.4	73.1	72.9	72.6	72.3	72.1	71.7
80°	59.2	59.0	58.9	58.8	58.6	58.5	58.1	57.9	57.7	57.4	57.0
82.5°	44.0	44.0	44.0	44.0	43.9	43.8	43.6	43.5	43.3	43.2	42.7
85°	24.2	24.2	24.0	23.8	23.8	23.6	23.4	23.4	23.2	23.1	22.7
87.5°	8.7	9.0	9.4	9.7	10.1	10.6	11.4	12.2	13.0	13.8	13.4
90°	1.0	3.8	6.5	9.3	12.0	15.8	20.9	25.9	30.9	36.0	35.5
92.5°	18.3	20.3	22.3	24.3	26.3	27.9	29.1	30.3	31.4	32.6	32.7
95°	53.4	55.7	58.0	60.3	62.6	63.9	64.4	64.8	65.3	65.8	65.8
97.5°	97.6	99.6	101.6	103.6	105.6	107.0	107.9	108.8	109.6	110.5	110.5
100°	130.5	132.3	134.1	135.9	137.8	139.0	139.7	140.4	141.1	141.7	141.7
102.5°	164.9	166.4	167.9	169.4	170.8	172.0	172.9	173.7	174.6	175.5	175.6
105°	220.9	221.5	222.2	222.9	223.6	224.2	224.6	225.1	225.5	226.0	226.4
107.5°	277.1	278.1	279.2	280.1	281.1	281.6	281.6	281.6	281.6	281.6	281.9
110°	313.3	314.7	316.0	317.4	318.8	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331518-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	352.8	354.1	355.5	356.9	358.2	358.8	358.6	358.5	358.2	358.1	357.5
115°	410.9	412.3	413.6	414.9	416.4	416.8	416.4	415.9	415.4	414.9	414.8
117.5°	468.8	470.6	472.5	474.3	476.1	476.4	475.1	473.8	472.5	471.3	470.7
120°	507.4	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	507.4
122.5°	542.7	544.9	547.2	549.3	551.5	552.0	550.7	549.5	548.1	546.8	546.3
125°	597.8	599.8	601.9	604.0	606.0	606.7	606.0	605.4	604.7	604.0	603.3
127.5°	651.4	654.0	656.6	659.3	661.9	662.7	661.9	661.1	660.3	659.4	658.6
130°	685.2	688.1	691.1	694.0	697.0	698.2	697.8	697.4	696.9	696.4	695.9
132.5°	722.9	725.3	727.8	730.2	732.6	733.9	734.0	734.0	734.1	734.2	733.2
135°	773.5	775.9	778.5	781.0	783.5	785.0	785.4	785.9	786.4	786.8	786.6
137.5°	826.6	828.7	830.8	832.8	834.9	836.2	836.8	837.4	838.0	838.6	838.4
140°	858.7	860.8	862.8	864.9	867.0	868.5	869.7	870.8	872.0	873.1	873.1
142.5°	891.6	893.7	895.7	897.8	899.8	901.2	902.0	902.8	903.6	904.4	904.5
145°	938.8	940.5	942.1	943.6	945.2	946.7	948.1	949.4	950.9	952.2	952.4
147.5°	981.0	982.9	984.8	986.7	988.6	990.1	990.9	991.9	992.8	993.7	994.2
150°	1009.7	1011.1	1012.5	1013.8	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6
152.5°	1035.2	1036.6	1037.9	1039.3	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2
155°	1073.4	1074.1	1074.8	1075.5	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7
157.5°	1106.0	1106.5	1107.0	1107.5	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5
160°	1125.8	1126.2	1126.7	1127.2	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2
162.5°	1143.8	1144.0	1144.1	1144.1	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8
165°	1167.9	1167.7	1167.4	1167.2	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5
167.5°	1188.0	1187.3	1186.7	1186.0	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4
170°	1198.7	1198.0	1197.4	1196.7	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2
172.5°	1206.1	1205.5	1204.8	1204.0	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6
175°	1215.1	1214.5	1213.8	1213.1	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6
177.5°	1218.9	1218.3	1217.7	1217.2	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331518-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	615.3	615.3	615.3	615.3	615.3	615.3	615.3	615.3
2.5°	612.7	613.7	614.7	615.2	615.0	614.7	614.6	614.3
5°	608.6	609.6	610.6	611.0	610.8	610.5	610.2	610.0
7.5°	601.7	602.7	603.8	604.1	603.9	603.6	603.2	603.0
10°	595.5	596.6	597.6	597.9	597.5	597.1	596.8	596.4
12.5°	588.3	589.0	589.7	589.9	589.6	589.4	589.1	588.7
15°	575.5	576.1	576.6	576.5	575.8	575.2	574.6	573.9
17.5°	560.4	561.0	561.7	561.6	560.9	560.4	559.8	559.1
20°	548.7	549.1	549.5	549.4	548.8	548.3	547.8	547.2
22.5°	536.1	536.2	536.3	536.2	535.9	535.6	535.3	535.0
25°	515.9	516.1	516.3	516.3	516.1	515.9	515.6	515.3
27.5°	495.8	495.4	495.0	494.6	493.9	493.3	492.7	492.0
30°	480.2	479.8	479.4	479.0	478.4	477.9	477.4	476.8
32.5°	464.9	464.2	463.5	462.9	462.3	461.8	461.3	460.7
35°	440.4	439.6	438.8	438.1	437.4	436.7	436.1	435.5
37.5°	415.7	414.8	413.8	413.0	412.3	411.7	411.1	410.5
40°	398.8	397.6	396.4	395.5	395.0	394.5	394.0	393.4
42.5°	382.0	380.7	379.4	378.4	377.6	376.9	376.2	375.4
45°	356.2	354.8	353.3	352.4	351.8	351.3	350.8	350.2
47.5°	329.5	327.9	326.4	325.3	324.5	323.8	323.0	322.2
50°	312.3	310.4	308.6	307.3	306.7	306.0	305.3	304.7
52.5°	294.5	292.9	291.4	290.2	289.3	288.4	287.6	286.7
55°	267.8	266.3	264.7	263.6	262.8	262.2	261.6	260.9
57.5°	240.2	238.6	237.1	236.1	235.5	235.0	234.6	234.0
60°	221.9	220.5	219.0	218.1	217.7	217.3	216.9	216.5
62.5°	204.6	203.3	201.9	201.1	200.5	200.0	199.6	199.0
65°	178.1	176.9	175.7	174.8	174.1	173.5	172.9	172.1
67.5°	151.9	150.9	150.0	149.3	148.8	148.2	147.7	147.2
70°	134.8	133.9	133.0	132.3	131.7	131.2	130.7	130.2
72.5°	118.7	117.8	116.9	116.2	115.8	115.3	114.9	114.5
75°	93.6	92.9	92.1	91.8	92.1	92.4	92.6	92.9
77.5°	71.3	70.9	70.5	70.1	69.7	69.4	69.0	68.6
80°	56.6	56.2	55.8	55.5	55.2	55.0	54.7	54.4
82.5°	42.2	41.7	41.2	40.9	40.9	40.8	40.7	40.7
85°	22.3	21.9	21.5	21.2	21.1	21.0	20.8	20.7
87.5°	13.0	12.6	12.2	12.0	11.9	11.8	11.8	11.7
90°	35.0	34.6	34.1	34.0	34.2	34.5	34.7	34.9
92.5°	32.9	33.0	33.0	33.1	33.1	33.2	33.3	33.3
95°	65.8	65.8	65.8	65.5	65.0	64.6	64.2	63.7
97.5°	110.5	110.5	110.5	110.5	110.4	110.4	110.4	110.4
100°	141.7	141.7	141.7	141.6	141.4	141.2	140.9	140.7
102.5°	175.8	176.0	176.2	176.2	175.9	175.7	175.5	175.2
105°	226.9	227.4	227.8	228.1	228.1	228.1	228.1	228.1
107.5°	282.0	282.2	282.4	281.9	280.9	279.9	278.8	277.7
110°	319.5	319.5	319.5	319.1	318.5	317.7	317.0	316.4





TEST NUMBER: P331518-927

CATALOG NUMBER: S122DIW-S485D1240U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	357.0	356.4	355.8	355.4	354.8	354.3	353.9	353.3
115°	414.5	414.3	414.1	413.6	413.0	412.3	411.5	410.9
117.5°	470.2	469.6	469.1	468.5	467.8	467.1	466.4	465.7
120°	507.4	507.4	507.4	507.1	506.4	505.7	505.0	504.4
122.5°	545.8	545.3	544.7	544.2	543.7	543.1	542.6	542.2
125°	602.6	601.9	601.3	600.8	600.6	600.3	600.1	599.8
127.5°	657.8	657.0	656.2	655.4	654.7	653.9	653.2	652.4
130°	695.5	695.1	694.6	694.0	693.0	692.1	691.2	690.2
132.5°	732.2	731.2	730.2	729.4	728.6	727.9	727.1	726.4
135°	786.4	786.2	785.9	785.4	784.7	784.1	783.4	782.7
137.5°	838.2	838.0	837.9	837.3	836.4	835.5	834.6	833.7
140°	873.1	873.1	873.1	872.7	871.7	870.8	869.9	869.0
142.5°	904.7	904.9	905.1	904.7	903.8	902.9	902.0	901.0
145°	952.7	952.9	953.1	952.8	951.9	950.9	950.1	949.1
147.5°	994.7	995.2	995.7	995.5	994.7	993.8	992.9	992.0
150°	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0
152.5°	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3
155°	1081.9	1083.0	1084.1	1084.3	1083.7	1083.0	1082.3	1081.6
157.5°	1113.1	1114.6	1116.2	1116.4	1115.3	1114.2	1113.1	1112.0
160°	1131.6	1133.0	1134.3	1134.6	1133.7	1132.7	1131.9	1130.9
162.5°	1148.4	1149.9	1151.5	1151.8	1150.6	1149.5	1148.4	1147.4
165°	1170.1	1171.6	1173.3	1173.5	1172.4	1171.2	1170.1	1168.9
167.5°	1188.0	1189.5	1191.1	1191.4	1190.2	1189.0	1187.8	1186.6
170°	1197.8	1199.4	1201.0	1201.1	1199.8	1198.4	1197.0	1195.6
172.5°	1205.2	1206.8	1208.4	1208.5	1207.1	1205.8	1204.4	1203.0
175°	1213.2	1214.8	1216.4	1216.6	1215.1	1213.8	1212.4	1211.0
177.5°	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2

(END OF REPORT)