

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907026

Luminaire Tested: DFN2DIP-TR2F0-030D060US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907026
REPORT IS A COMBINATION OF REPORTS P900264 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-030D060US835-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7860.0 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907026

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907026

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	103	103	103	103		93	93	93	93		74	74	74		56	56	56		40	40	40
1	94	90	86	83		85	81	78	75		65	63	61		50	48	47		36	35	34
2	86	79	73	68		77	71	67	62		57	54	51		44	42	40		32	31	29
3	79	70	63	57		71	63	57	52		51	46	43		39	36	34		29	27	25
4	72	62	54	49		65	56	50	45		45	41	37		35	32	29		26	24	22
5	66	55	47	42		59	50	43	38		40	36	32		32	28	26		23	21	19
6	61	49	42	36		55	45	38	33		36	32	28		29	25	23		21	19	17
7	56	45	37	32		51	41	34	29		33	28	25		26	23	20		19	17	15
8	52	40	33	28		47	37	30	26		30	25	22		24	20	18		18	16	14
9	49	37	30	25		44	34	27	23		28	23	20		22	19	16		17	14	13
10	45	34	27	22		41	31	25	21		25	21	18		20	17	15		15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2766	2766	2766
5°	2766	2716	2734
10°	2734	2656	2641
15°	2693	2562	2499
20°	2639	2436	2326
25°	2583	2295	2160
30°	2511	2151	1950
35°	2439	1997	1767
40°	2366	1838	1557
45°	2282	1663	1366
50°	2194	1486	1181
55°	2102	1298	1004
60°	1996	1103	822
65°	1873	905	734
70°	1724	721	658
75°	1536	624	589
80°	1267	506	497
85°	831	314	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2476 cd/sqm

TEST NUMBER: P907026

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.2	1.5
10°-20°	319.0	4.1
20°-30°	447.9	5.7
30°-40°	488.2	6.2
40°-50°	448.7	5.7
50°-60°	352.4	4.5
60°-70°	229.4	2.9
70°-80°	118.1	1.5
80°-90°	35.5	0.5
90°-100°	117.4	1.5
100°-110°	373.1	4.7
110°-120°	638.5	8.1
120°-130°	839.7	10.7
130°-140°	942.5	12.0
140°-150°	924.2	11.8
150°-160°	775.3	9.9
160°-170°	514.2	6.5
170°-180°	179.7	2.3
0°-30°	883.1	11.2
0°-40°	1371.3	17.4
0°-60°	2172.4	27.6
0°-90°	2555.4	32.5
90°-120°	1129.0	14.4
90°-150°	3835.4	48.8
90°-180°	5305.0	67.5
0°-180°	7860.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1240	1240	1240	1240	1240	
5°	1240	1234	1220	1230	1226	118
15°	1179	1167	1129	1108	1096	332
25°	1070	1034	960	914	898	492
35°	922	865	766	696	671	577
45°	754	679	561	481	454	582
55°	573	486	365	297	276	512
65°	387	296	195	157	154	384
75°	206	128	90	82	81	218
85°	48	25	21	21	21	55
90°	2	21	56	53	54	8
95°	84	100	102	102	100	93
105°	344	349	352	355	355	363
115°	641	650	647	645	641	634
125°	932	946	942	936	935	833
135°	1205	1223	1226	1225	1220	932
145°	1463	1475	1484	1486	1479	914
155°	1673	1678	1683	1691	1686	770
165°	1820	1819	1819	1830	1822	514
175°	1894	1890	1886	1898	1888	180
180°	1898	1898	1898	1898	1898	

TEST NUMBER: P907026

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1239.9	1239.9	1239.9	1239.9	1239.9
2.5°	1245.5	1239.9	1227.5	1238.8	1236.6
5°	1239.9	1234.3	1219.7	1229.8	1226.4
7.5°	1229.8	1223.1	1207.4	1211.8	1206.2
10°	1216.3	1208.5	1186.1	1182.6	1176.0
12.5°	1199.5	1189.4	1159.1	1152.4	1140.0
15°	1179.3	1166.9	1128.8	1107.5	1096.3
17.5°	1155.7	1137.8	1090.6	1066.0	1048.0
20°	1128.8	1106.3	1050.2	1022.3	997.5
22.5°	1099.7	1073.8	1008.7	970.6	953.8
25°	1070.5	1034.5	960.5	914.5	897.6
27.5°	1035.7	997.5	915.6	862.9	837.0
30°	998.7	956.0	866.2	809.1	778.7
32.5°	962.7	911.1	819.2	751.8	723.7
35°	922.4	865.1	766.4	695.7	671.0
37.5°	883.1	821.3	717.0	639.5	611.6
40°	841.6	774.3	665.4	585.7	556.6
42.5°	798.9	727.2	613.8	530.7	502.7
45°	754.1	678.8	561.1	481.3	454.4
47.5°	711.4	631.8	510.6	430.8	406.2
50°	664.3	584.6	461.2	383.7	360.2
52.5°	618.2	534.1	414.1	340.0	318.7
55°	573.3	485.8	364.6	297.4	276.1
57.5°	527.4	437.6	321.0	258.1	240.1
60°	480.2	390.5	274.9	217.7	199.8
62.5°	434.3	344.5	235.6	181.8	172.9
65°	387.1	296.2	195.2	157.1	153.7
67.5°	342.3	251.3	157.1	138.0	134.6
70°	295.1	207.6	130.1	118.9	114.4
72.5°	250.2	167.1	108.8	99.9	97.6
75°	206.4	127.9	89.8	81.9	80.8
77.5°	162.7	90.8	70.7	66.2	63.9
80°	122.3	65.1	53.8	49.4	49.4
82.5°	85.2	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	1.7	20.6	56.1	52.6	54.3
92.5°	35.5	48.1	49.8	51.5	51.5
95°	83.5	99.5	102.4	102.4	99.5
97.5°	139.0	153.9	160.2	160.2	160.2
100°	203.1	216.2	220.8	220.8	219.1
102.5°	270.6	280.3	286.6	288.3	286.6
105°	344.4	349.0	352.4	355.3	355.3
107.5°	417.6	424.5	424.5	425.6	417.6
110°	488.6	497.7	497.7	497.7	493.1

TEST NUMBER: P907026

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.2	574.9	573.2	568.6	565.2
115°	640.7	649.9	647.0	645.3	640.7
117.5°	715.7	728.3	720.2	715.7	711.1
120°	791.2	803.8	791.2	791.2	786.0
122.5°	859.8	875.8	867.8	863.3	859.8
125°	931.9	946.2	941.6	936.5	934.8
127.5°	1002.3	1020.0	1013.7	1006.9	1002.3
130°	1068.1	1088.7	1085.8	1082.4	1076.1
132.5°	1141.9	1157.9	1159.0	1151.0	1146.4
135°	1205.4	1223.1	1226.5	1224.8	1220.2
137.5°	1276.3	1290.6	1293.5	1292.3	1285.5
140°	1338.7	1353.0	1361.0	1361.0	1354.7
142.5°	1402.7	1417.0	1421.6	1423.3	1417.0
145°	1463.4	1474.8	1484.0	1485.7	1479.4
147.5°	1517.7	1532.0	1538.9	1541.7	1535.4
150°	1573.8	1583.5	1589.8	1594.9	1589.8
152.5°	1623.5	1633.3	1641.3	1647.6	1641.3
155°	1673.3	1677.9	1683.0	1691.1	1685.9
157.5°	1716.2	1719.7	1722.5	1734.0	1726.0
160°	1754.6	1758.0	1759.7	1769.4	1762.6
162.5°	1790.0	1790.0	1791.7	1802.6	1794.6
165°	1820.3	1818.6	1818.6	1830.1	1822.1
167.5°	1847.8	1842.7	1842.7	1854.1	1846.1
170°	1868.4	1863.8	1862.1	1873.5	1863.8
172.5°	1882.7	1878.1	1876.4	1887.8	1878.1
175°	1894.1	1889.6	1886.1	1897.6	1887.8
177.5°	1900.4	1895.9	1892.4	1902.1	1892.4
180°	1897.6	1897.6	1897.6	1897.6	1897.6

TEST NUMBER: P907026

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.65	9.36	9.75	10.45	11.95	4.63	5.34	5.73	6.43	7.93
	3H	10.30	10.93	11.40	12.03	13.55	5.80	6.43	6.90	7.53	9.05
	4H	10.88	11.48	12.00	12.58	14.11	6.23	6.83	7.35	7.93	9.46
	6H	11.28	11.83	12.40	12.93	14.47	6.53	7.08	7.66	8.19	9.72
	8H	11.39	11.91	12.52	13.03	14.56	6.61	7.13	7.74	8.25	9.78
	12H	11.44	11.93	12.57	13.05	14.60	6.64	7.14	7.78	8.25	9.81
4H	2H	8.65	9.25	9.78	10.35	11.88	5.20	5.80	6.33	6.90	8.43
	3H	10.44	10.94	11.57	12.07	13.61	6.52	7.02	7.65	8.15	9.68
	4H	11.11	11.57	12.24	12.69	14.24	7.05	7.51	8.18	8.62	10.18
	6H	11.60	11.99	12.74	13.13	14.68	7.44	7.84	8.59	8.98	10.53
	8H	11.76	12.12	12.90	13.25	14.82	7.56	7.93	8.70	9.06	10.63
	12H	11.83	12.16	12.99	13.31	14.88	7.61	7.94	8.77	9.09	10.66
8H	4H	11.06	11.43	12.20	12.56	14.13	7.31	7.67	8.45	8.80	10.37
	6H	11.60	11.90	12.76	13.08	14.64	7.80	8.10	8.96	9.27	10.84
	8H	11.80	12.06	12.97	13.22	14.80	7.98	8.24	9.14	9.39	10.98
	12H	11.92	12.15	13.09	13.30	14.92	8.08	8.31	9.25	9.46	11.08
12H	4H	11.01	11.34	12.17	12.49	14.06	7.30	7.63	8.46	8.78	10.35
	6H	11.57	11.84	12.74	12.99	14.57	7.84	8.10	9.01	9.26	10.84
	8H	11.77	12.00	12.94	13.15	14.77	8.03	8.26	9.20	9.41	11.03

END OF REPORT