

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331536-927

Luminaire Tested: **S122DIW-S675D710U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331536-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D710U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4090.3 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331536-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331536-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52					52			
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	52	50	49	44					44			
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37					37			
3	82	72	65	59	75	67	61	55	57	52	48	48	45	42	40	38	35	31					31			
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27					27			
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27	23					23			
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20					20			
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21	18					18			
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16					16			
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15					15			
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13					13			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13580	13580	13580
5°	13632	13434	13514
10°	13550	13298	13365
15°	13382	13125	13112
20°	13144	12866	12854
25°	12909	12549	12549
30°	12603	12258	12152
35°	12321	11907	11732
40°	11965	11556	11335
45°	11615	11209	10930
50°	11233	10846	10462
55°	10835	10427	10038
60°	10395	9923	9558
65°	9918	9425	8993
70°	9314	8818	8398
75°	8478	8122	7923
80°	7522	7290	6918
85°	6150	5835	5243



TEST NUMBER: P331536-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.9
10°-20°	222.5	5.4
20°-30°	327.1	8.0
30°-40°	379.9	9.3
40°-50°	379.5	9.3
50°-60°	331.0	8.1
60°-70°	244.7	6.0
70°-80°	138.6	3.4
80°-90°	40.1	1.0
90°-100°	44.1	1.1
100°-110°	137.1	3.4
110°-120°	234.3	5.7
120°-130°	308.1	7.5
130°-140°	345.9	8.5
140°-150°	339.1	8.3
150°-160°	284.5	7.0
160°-170°	188.7	4.6
170°-180°	65.9	1.6
0°-30°	628.7	15.4
0°-40°	1008.6	24.7
0°-60°	1719.1	42.0
0°-90°	2142.5	52.4
90°-120°	415.5	10.2
90°-150°	1408.7	34.4
90°-180°	1948.0	47.6
0°-180°	4090.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	841	841	841	841	841	
5°	841	838	829	835	834	80
15°	801	795	785	788	784	225
25°	725	718	704	706	704	333
35°	625	617	604	599	595	390
45°	509	503	491	482	479	392
55°	385	380	370	361	357	344
65°	260	254	247	240	235	257
75°	136	134	130	126	127	145
85°	33	32	32	29	28	38
90°	1	8	21	20	20	3
95°	31	36	38	38	36	35
105°	126	128	129	130	130	133
115°	235	238	238	237	235	233
125°	342	347	346	344	343	306
135°	443	449	450	450	448	342
145°	537	541	545	545	543	336
155°	614	616	618	620	619	283
165°	668	668	668	672	669	188
175°	695	694	692	696	693	66
180°	697	697	697	697	697	



TEST NUMBER: P331536-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	844.9	844.2	843.5	842.8	842.1	840.9	839.3	837.7	836.1	834.6	836.0
5°	841.1	840.3	839.6	838.9	838.2	836.9	834.9	832.9	830.9	828.9	830.4
7.5°	833.6	832.5	831.4	830.3	829.2	827.6	825.6	823.6	821.6	819.5	820.9
10°	826.5	825.2	823.9	822.7	821.5	819.8	817.6	815.5	813.3	811.1	812.5
12.5°	816.8	815.7	814.5	813.4	812.3	810.7	808.5	806.4	804.2	802.1	803.1
15°	800.6	799.5	798.4	797.4	796.3	794.6	792.3	789.9	787.6	785.2	786.0
17.5°	779.9	778.8	777.8	776.7	775.6	773.9	771.5	769.1	766.8	764.4	765.2
20°	765.0	764.0	762.9	761.8	760.7	758.9	756.4	753.9	751.4	748.8	749.4
22.5°	750.1	748.6	747.1	745.6	744.1	742.2	739.8	737.4	735.1	732.7	732.8
25°	724.6	723.2	721.8	720.3	718.8	716.6	713.5	710.5	707.4	704.4	704.7
27.5°	695.5	694.2	692.9	691.6	690.3	688.5	686.0	683.7	681.2	678.8	678.3
30°	676.0	674.6	673.2	671.8	670.3	668.3	665.6	662.9	660.2	657.5	657.0
32.5°	655.4	654.2	653.1	651.9	650.8	648.8	645.9	643.1	640.2	637.4	636.4
35°	625.1	623.4	621.5	619.7	617.9	615.6	612.8	609.8	607.0	604.1	603.0
37.5°	591.0	589.4	587.8	586.2	584.7	582.4	579.6	576.7	573.9	570.9	569.6
40°	567.7	566.3	564.8	563.4	562.0	559.8	556.9	554.1	551.2	548.3	546.7
42.5°	545.1	543.6	542.2	540.7	539.3	537.2	534.2	531.4	528.5	525.7	523.9
45°	508.7	507.4	506.1	504.9	503.7	501.7	499.0	496.3	493.6	490.9	488.9
47.5°	472.5	471.3	470.1	468.9	467.7	465.7	462.9	460.1	457.3	454.5	452.4
50°	447.2	446.3	445.4	444.5	443.6	441.9	439.4	436.9	434.4	431.8	429.4
52.5°	422.6	421.4	420.3	419.1	417.9	416.1	413.8	411.4	409.0	406.6	404.6
55°	384.9	383.9	382.8	381.7	380.6	379.0	376.8	374.7	372.6	370.4	368.2
57.5°	347.1	346.3	345.4	344.5	343.6	342.1	339.7	337.3	334.9	332.6	330.4
60°	321.9	321.2	320.4	319.7	319.0	317.3	314.9	312.4	309.8	307.3	305.3
62.5°	297.3	296.1	295.0	293.8	292.7	291.1	289.2	287.2	285.3	283.4	281.5
65°	259.6	258.5	257.5	256.4	255.2	253.8	252.1	250.3	248.4	246.7	245.0
67.5°	221.3	220.4	219.5	218.6	217.8	216.6	214.9	213.3	211.8	210.1	208.8
70°	197.3	196.6	195.9	195.2	194.5	193.3	191.6	190.0	188.5	186.8	185.5
72.5°	172.8	172.0	171.3	170.6	169.8	169.0	167.9	166.9	165.9	164.8	163.6
75°	135.9	135.5	135.1	134.8	134.4	133.8	132.9	132.0	131.1	130.2	129.1
77.5°	102.9	102.3	101.6	101.0	100.4	100.0	99.6	99.2	98.9	98.5	98.0
80°	80.9	80.7	80.5	80.3	80.2	79.9	79.5	79.1	78.8	78.4	77.9
82.5°	60.2	60.1	60.1	60.0	60.0	59.9	59.7	59.5	59.3	59.0	58.4
85°	33.2	33.0	32.8	32.6	32.4	32.2	32.1	31.9	31.7	31.5	31.0
87.5°	11.7	11.8	11.8	11.8	11.9	12.0	12.3	12.6	12.9	13.2	12.7
90°	0.6	2.1	3.7	5.3	6.9	9.1	12.0	14.8	17.7	20.6	20.3
92.5°	10.5	11.6	12.8	13.9	15.1	16.0	16.6	17.3	18.0	18.7	18.8
95°	30.6	31.8	33.2	34.5	35.8	36.6	36.8	37.1	37.4	37.6	37.6
97.5°	55.8	57.0	58.1	59.3	60.4	61.2	61.8	62.3	62.7	63.2	63.2
100°	74.6	75.7	76.8	77.8	78.8	79.5	79.9	80.3	80.7	81.1	81.1
102.5°	94.4	95.2	96.1	96.9	97.8	98.4	98.9	99.4	99.9	100.4	100.5
105°	126.4	126.7	127.1	127.5	127.9	128.3	128.6	128.8	129.0	129.4	129.6
107.5°	158.6	159.1	159.8	160.3	160.9	161.2	161.2	161.2	161.2	161.2	161.3
110°	179.3	180.1	180.9	181.6	182.4	182.8	182.8	182.8	182.8	182.8	182.8



TEST NUMBER: P331536-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	201.8	202.6	203.4	204.2	205.0	205.3	205.3	205.1	205.0	204.9	204.6
115°	235.1	235.9	236.7	237.5	238.3	238.5	238.3	238.0	237.7	237.5	237.3
117.5°	268.3	269.3	270.4	271.4	272.4	272.6	271.9	271.2	270.5	269.7	269.4
120°	290.4	291.4	292.5	293.5	294.5	294.5	293.5	292.5	291.4	290.4	290.4
122.5°	310.6	311.9	313.1	314.3	315.6	315.9	315.1	314.4	313.7	313.0	312.7
125°	342.1	343.3	344.4	345.6	346.8	347.2	346.8	346.4	346.0	345.6	345.2
127.5°	372.8	374.3	375.8	377.2	378.7	379.3	378.8	378.3	377.9	377.4	376.9
130°	392.1	393.8	395.5	397.2	398.9	399.6	399.3	399.1	398.8	398.5	398.3
132.5°	413.8	415.1	416.5	417.9	419.2	420.0	420.0	420.1	420.2	420.2	419.6
135°	442.7	444.1	445.5	446.9	448.4	449.2	449.5	449.8	450.0	450.3	450.1
137.5°	473.1	474.3	475.5	476.7	477.8	478.6	478.9	479.3	479.6	479.9	479.8
140°	491.5	492.6	493.8	495.0	496.1	497.0	497.7	498.4	499.0	499.6	499.6
142.5°	510.2	511.4	512.6	513.8	514.9	515.8	516.2	516.7	517.1	517.5	517.6
145°	537.3	538.2	539.1	540.0	541.0	541.8	542.6	543.4	544.2	544.9	545.0
147.5°	561.4	562.4	563.6	564.7	565.8	566.6	567.1	567.6	568.2	568.7	568.9
150°	577.8	578.6	579.4	580.2	581.0	581.6	582.2	582.7	583.2	583.8	584.2
152.5°	592.4	593.2	594.0	594.8	595.6	596.3	596.9	597.5	598.2	598.8	599.3
155°	614.3	614.7	615.1	615.4	615.8	616.2	616.6	617.0	617.4	617.8	618.5
157.5°	633.0	633.3	633.5	633.7	634.1	634.3	634.5	634.8	635.0	635.3	636.1
160°	644.3	644.5	644.8	645.1	645.3	645.5	645.6	645.8	645.9	646.0	646.8
162.5°	654.6	654.7	654.7	654.7	654.8	654.9	655.1	655.2	655.3	655.5	656.3
165°	668.4	668.2	668.1	668.0	667.9	667.8	667.8	667.8	667.8	667.8	668.7
167.5°	679.9	679.5	679.1	678.7	678.3	678.1	678.1	678.0	678.0	678.0	678.9
170°	686.0	685.6	685.2	684.8	684.4	684.2	684.0	683.9	683.8	683.7	684.6
172.5°	690.2	689.8	689.4	689.0	688.6	688.4	688.2	688.2	688.0	687.9	688.8
175°	695.4	695.1	694.7	694.3	693.9	693.6	693.2	693.0	692.8	692.4	693.4
177.5°	697.5	697.2	696.9	696.6	696.2	696.0	695.8	695.6	695.4	695.1	695.8
180°	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6



TEST NUMBER: P331536-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	837.4	838.9	840.3	840.9	840.6	840.3	840.0	839.8
5°	831.8	833.2	834.6	835.2	834.9	834.5	834.2	833.8
7.5°	822.4	823.9	825.3	825.8	825.4	825.1	824.7	824.3
10°	814.0	815.5	816.9	817.3	816.8	816.3	815.7	815.2
12.5°	804.1	805.1	806.1	806.4	806.0	805.6	805.3	804.9
15°	786.7	787.4	788.1	788.1	787.1	786.2	785.4	784.4
17.5°	766.0	766.8	767.7	767.7	766.8	766.0	765.1	764.2
20°	750.0	750.5	751.0	750.9	750.2	749.5	748.8	748.1
22.5°	732.9	733.0	733.1	732.9	732.5	732.1	731.7	731.3
25°	705.1	705.4	705.8	705.8	705.4	705.1	704.7	704.4
27.5°	677.7	677.2	676.7	676.0	675.1	674.2	673.4	672.5
30°	656.4	655.8	655.3	654.7	653.9	653.2	652.5	651.8
32.5°	635.5	634.5	633.5	632.7	632.0	631.3	630.5	629.8
35°	602.0	600.9	599.8	598.8	597.9	597.0	596.1	595.2
37.5°	568.3	567.0	565.6	564.5	563.6	562.8	562.0	561.1
40°	545.1	543.4	541.9	540.7	540.0	539.2	538.5	537.8
42.5°	522.1	520.4	518.6	517.2	516.2	515.2	514.2	513.2
45°	487.0	485.0	483.0	481.6	480.9	480.2	479.5	478.7
47.5°	450.4	448.2	446.2	444.6	443.5	442.5	441.5	440.5
50°	426.8	424.3	421.8	420.1	419.1	418.3	417.4	416.5
52.5°	402.4	400.4	398.3	396.6	395.5	394.3	393.1	391.9
55°	366.1	363.9	361.8	360.2	359.3	358.5	357.5	356.6
57.5°	328.3	326.1	324.1	322.7	321.9	321.3	320.6	319.9
60°	303.3	301.3	299.4	298.2	297.6	297.1	296.5	296.0
62.5°	279.7	277.9	276.1	274.8	274.1	273.4	272.7	272.0
65°	243.4	241.8	240.2	238.9	238.1	237.1	236.2	235.4
67.5°	207.6	206.4	205.1	204.1	203.4	202.6	201.9	201.2
70°	184.3	183.1	181.8	180.8	180.1	179.4	178.6	177.9
72.5°	162.3	161.1	159.8	158.8	158.3	157.7	157.2	156.5
75°	128.0	127.0	125.9	125.6	125.9	126.3	126.6	127.0
77.5°	97.4	96.9	96.3	95.9	95.3	94.8	94.3	93.8
80°	77.4	76.8	76.3	75.8	75.5	75.1	74.8	74.4
82.5°	57.7	57.0	56.3	55.9	55.8	55.8	55.7	55.6
85°	30.5	29.9	29.4	29.0	28.8	28.7	28.5	28.3
87.5°	12.2	11.7	11.2	10.9	10.9	10.7	10.6	10.5
90°	20.0	19.8	19.6	19.5	19.6	19.7	19.9	20.0
92.5°	18.8	18.9	18.9	18.9	18.9	19.0	19.0	19.0
95°	37.6	37.6	37.6	37.5	37.2	37.0	36.7	36.4
97.5°	63.2	63.2	63.2	63.2	63.2	63.2	63.1	63.1
100°	81.1	81.1	81.1	81.0	81.0	80.8	80.6	80.6
102.5°	100.6	100.7	100.8	100.8	100.7	100.5	100.4	100.3
105°	129.8	130.1	130.4	130.5	130.5	130.5	130.5	130.5
107.5°	161.4	161.5	161.6	161.4	160.7	160.2	159.5	159.0
110°	182.8	182.8	182.8	182.6	182.2	181.8	181.4	181.1



TEST NUMBER: P331536-927

CATALOG NUMBER: S122DIW-S675D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	204.3	204.0	203.7	203.4	203.1	202.8	202.5	202.2
115°	237.3	237.1	236.9	236.7	236.3	235.9	235.5	235.1
117.5°	269.1	268.8	268.5	268.1	267.7	267.3	266.9	266.5
120°	290.4	290.4	290.4	290.2	289.8	289.4	289.0	288.6
122.5°	312.4	312.0	311.7	311.4	311.1	310.9	310.5	310.3
125°	344.8	344.4	344.0	343.8	343.7	343.6	343.4	343.3
127.5°	376.4	376.0	375.5	375.1	374.6	374.2	373.8	373.4
130°	398.1	397.8	397.5	397.1	396.6	396.1	395.5	395.1
132.5°	419.1	418.4	417.9	417.4	417.0	416.5	416.1	415.7
135°	450.0	449.9	449.8	449.5	449.1	448.7	448.3	447.9
137.5°	479.7	479.6	479.5	479.2	478.6	478.2	477.6	477.1
140°	499.6	499.6	499.6	499.4	498.9	498.4	497.8	497.3
142.5°	517.8	517.8	517.9	517.8	517.2	516.7	516.2	515.6
145°	545.2	545.3	545.4	545.3	544.7	544.2	543.7	543.2
147.5°	569.3	569.5	569.8	569.7	569.3	568.7	568.2	567.8
150°	584.5	584.9	585.3	585.3	584.9	584.5	584.2	583.8
152.5°	599.8	600.2	600.8	600.8	600.2	599.8	599.3	598.8
155°	619.1	619.8	620.4	620.6	620.2	619.8	619.4	619.0
157.5°	637.0	637.9	638.7	638.9	638.3	637.6	637.0	636.4
160°	647.6	648.4	649.2	649.3	648.8	648.2	647.8	647.2
162.5°	657.2	658.1	659.0	659.1	658.5	657.9	657.3	656.6
165°	669.6	670.5	671.5	671.6	670.9	670.3	669.6	669.0
167.5°	679.9	680.7	681.7	681.8	681.1	680.4	679.8	679.1
170°	685.5	686.4	687.3	687.4	686.6	685.8	685.0	684.2
172.5°	689.8	690.6	691.6	691.6	690.9	690.1	689.3	688.5
175°	694.3	695.2	696.2	696.2	695.4	694.7	693.9	693.1
177.5°	696.4	697.0	697.7	697.7	697.0	696.4	695.8	695.1
180°	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6

(END OF REPORT)