

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331538-927

Luminaire Tested: **S122DIW-S675D970U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331538-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D970U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4983.9 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39	34
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	45	42	42	38	35	34	32	30	26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16990	16990	16990	16990
5°	19047	17099	15152	17099
10°	21827	16959	13114	16959
15°	24145	16649	11587	16649
20°	23778	16314	10562	16314
25°	21440	15871	9912	15871
30°	17717	15163	9439	15163
35°	12912	14420	9102	14420
40°	10313	13544	8916	13544
45°	9012	12529	8661	12529
50°	8470	11549	8493	11549
55°	7809	10553	8265	10553
60°	7156	9494	7915	9494
65°	6518	8542	7568	8542
70°	5915	7619	7062	7619
75°	5246	6581	6257	6581
80°	4519	5449	5040	5449
85°	4057	4057	3001	4057



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	2.0
10°-20°	291.3	5.8
20°-30°	422.8	8.5
30°-40°	446.2	9.0
40°-50°	395.0	7.9
50°-60°	315.3	6.3
60°-70°	214.3	4.3
70°-80°	109.9	2.2
80°-90°	30.3	0.6
90°-100°	60.2	1.2
100°-110°	187.1	3.8
110°-120°	319.9	6.4
120°-130°	420.6	8.4
130°-140°	472.1	9.5
140°-150°	462.9	9.3
150°-160°	388.3	7.8
160°-170°	257.5	5.2
170°-180°	90.0	1.8
0°-30°	814.3	16.3
0°-40°	1260.5	25.3
0°-60°	1970.8	39.5
0°-90°	2325.2	46.7
90°-120°	567.2	11.4
90°-150°	1922.8	38.6
90°-180°	2659.0	53.4
0°-180°	4983.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1052	1052	1052	1052	1052	
5°	1175	1055	935	1055	1175	117
15°	1444	996	693	996	1444	399
25°	1204	891	556	891	1204	544
35°	655	732	462	732	655	426
45°	395	549	379	549	395	310
55°	277	375	294	375	277	249
65°	171	224	198	224	171	170
75°	84	106	100	106	84	90
85°	22	22	16	22	22	25
90°	27	1	27	1	27	13
95°	50	42	50	42	50	55
105°	178	172	178	172	178	187
115°	321	321	321	321	321	317
125°	469	467	469	467	469	418
135°	611	604	611	604	611	471
145°	741	733	741	733	741	463
155°	845	838	845	838	845	389
165°	913	912	913	912	913	258
175°	946	949	946	949	946	90
180°	951	951	951	951	951	



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1100.7	1101.1	1101.8	1096.5	1095.9	1095.9	1091.4	1087.5	1083.0	1076.8	1077.4
5°	1175.2	1179.6	1181.2	1176.4	1169.1	1168.3	1161.4	1150.1	1139.6	1131.1	1125.1
7.5°	1264.0	1265.7	1261.8	1255.4	1250.0	1240.3	1227.5	1215.0	1197.4	1181.3	1169.3
10°	1331.3	1333.7	1326.8	1317.6	1309.9	1298.5	1279.9	1260.9	1237.9	1215.6	1197.8
12.5°	1382.4	1388.4	1379.6	1378.3	1365.2	1349.6	1327.5	1317.9	1285.4	1254.4	1235.3
15°	1444.5	1444.1	1444.9	1437.3	1427.5	1425.1	1401.6	1376.2	1330.5	1312.2	1280.7
17.5°	1426.6	1432.7	1435.5	1435.4	1435.2	1433.7	1426.2	1410.1	1387.2	1357.6	1321.2
20°	1383.9	1391.9	1393.1	1402.5	1407.7	1414.6	1417.4	1412.9	1398.8	1374.1	1342.6
22.5°	1317.9	1320.1	1323.9	1338.4	1349.8	1367.0	1376.0	1391.0	1385.5	1373.5	1347.1
25°	1203.5	1199.4	1213.6	1220.8	1247.1	1274.6	1294.5	1316.3	1335.7	1347.4	1339.7
27.5°	1066.1	1060.1	1081.2	1100.6	1122.0	1151.8	1182.6	1219.1	1249.4	1287.4	1300.4
30°	950.3	953.9	974.2	994.8	1027.1	1069.2	1104.0	1144.1	1187.3	1229.8	1259.3
32.5°	825.5	839.5	852.2	883.8	912.3	959.3	1010.2	1060.3	1114.2	1162.4	1208.2
35°	655.1	671.3	689.1	712.2	752.2	798.7	848.4	915.9	989.6	1055.5	1109.7
37.5°	551.4	548.8	559.0	575.7	608.2	645.6	702.9	769.7	856.3	933.7	1010.2
40°	489.3	487.7	495.0	510.3	535.0	562.5	612.7	671.3	751.8	846.4	937.4
42.5°	446.6	447.6	451.6	462.5	479.3	502.0	539.6	589.5	663.1	752.3	850.0
45°	394.7	397.5	402.0	407.3	416.9	435.5	456.5	492.2	550.4	624.8	721.0
47.5°	357.4	357.4	361.9	366.5	372.3	382.8	400.0	422.2	463.3	523.9	606.7
50°	337.2	334.5	337.7	341.3	347.4	354.7	366.0	387.0	414.5	463.4	532.6
52.5°	312.7	312.8	315.7	317.0	322.5	329.7	340.1	354.7	379.5	417.8	474.7
55°	277.4	279.4	281.1	283.4	288.4	293.6	301.7	311.4	330.8	359.5	401.6
57.5°	244.2	244.9	246.5	251.1	254.2	259.0	266.7	275.5	288.2	309.4	341.0
60°	221.6	221.6	224.8	226.9	230.9	235.8	241.9	250.3	261.7	279.0	304.5
62.5°	200.9	200.6	201.8	205.2	208.3	212.8	218.9	226.1	236.7	252.2	273.1
65°	170.6	169.8	172.3	173.1	176.3	180.8	185.6	193.3	201.8	213.1	231.7
67.5°	141.6	142.5	143.8	145.4	147.1	151.8	155.0	160.5	167.6	177.1	189.6
70°	125.3	125.3	125.3	126.6	129.0	131.4	134.7	139.1	146.0	154.1	165.4
72.5°	107.3	108.5	109.8	109.1	112.2	113.6	117.5	120.0	126.6	131.7	141.8
75°	84.1	84.1	84.1	86.1	87.4	88.6	91.0	93.4	96.6	103.1	108.4
77.5°	62.7	62.6	63.0	63.5	64.8	66.2	66.9	69.2	72.2	75.1	79.6
80°	48.6	49.4	49.7	50.5	50.5	51.3	51.7	54.6	56.6	58.6	61.5
82.5°	37.5	37.7	37.8	37.9	38.3	38.7	39.8	40.7	41.4	43.1	45.3
85°	21.9	21.5	21.5	22.3	21.9	21.9	22.7	23.4	23.4	23.8	25.0
87.5°	13.9	13.9	14.1	13.8	13.7	14.1	14.1	13.9	14.3	14.7	14.2
90°	27.3	27.1	26.9	26.8	26.5	26.6	27.0	27.3	27.7	28.0	24.2
92.5°	26.0	26.0	25.9	25.9	25.8	25.8	25.7	25.7	25.6	25.5	24.6
95°	49.7	50.1	50.5	50.8	51.2	51.3	51.3	51.3	51.3	51.3	51.0
97.5°	86.2	86.2	86.3	86.3	86.3	86.3	86.3	86.3	86.3	86.3	85.6
100°	110.0	110.1	110.3	110.4	110.7	110.7	110.7	110.7	110.7	110.7	110.2
102.5°	136.9	137.0	137.2	137.4	137.6	137.6	137.4	137.4	137.2	137.0	136.3
105°	178.2	178.2	178.2	178.2	178.2	177.9	177.6	177.2	176.9	176.5	176.2
107.5°	217.0	217.8	218.6	219.4	220.2	220.5	220.5	220.3	220.1	220.0	220.0
110°	247.2	247.6	248.2	248.7	249.3	249.5	249.5	249.5	249.5	249.5	249.5



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	276.0	276.4	276.8	277.2	277.6	278.0	278.5	278.8	279.2	279.7	279.9
115°	320.9	321.5	322.0	322.6	323.1	323.4	323.6	323.8	324.0	324.2	324.5
117.5°	363.8	364.3	364.9	365.4	365.9	366.4	366.9	367.3	367.7	368.1	369.2
120°	394.0	394.5	395.1	395.5	396.1	396.4	396.4	396.4	396.4	396.4	397.8
122.5°	423.5	423.9	424.3	424.7	425.1	425.5	425.9	426.4	426.7	427.1	428.2
125°	468.6	468.7	469.0	469.1	469.3	469.7	470.2	470.7	471.3	471.8	472.3
127.5°	509.7	510.2	510.8	511.4	511.9	512.5	513.2	513.8	514.4	515.2	515.8
130°	539.2	539.9	540.6	541.3	542.0	542.6	543.0	543.3	543.7	544.0	544.4
132.5°	567.4	568.0	568.5	569.2	569.7	570.4	571.2	572.0	572.7	573.5	573.5
135°	611.4	612.0	612.4	613.0	613.5	613.9	614.1	614.3	614.4	614.6	614.3
137.5°	651.2	651.9	652.6	653.3	654.0	654.5	654.7	654.7	654.9	655.1	654.6
140°	678.8	679.5	680.2	681.0	681.7	682.0	682.0	682.0	682.0	682.0	681.1
142.5°	703.9	704.6	705.3	706.0	706.7	706.9	706.9	706.7	706.5	706.4	705.8
145°	741.4	742.1	742.8	743.5	744.3	744.5	744.3	744.2	743.9	743.8	742.8
147.5°	774.9	775.6	776.3	777.0	777.6	777.8	777.4	777.0	776.6	776.2	775.5
150°	796.8	797.3	797.8	798.4	798.9	798.9	798.4	797.8	797.3	796.8	796.1
152.5°	817.3	817.9	818.6	819.4	820.0	820.0	819.4	818.6	817.9	817.3	816.4
155°	844.9	845.4	846.0	846.5	847.0	846.8	846.0	845.1	844.1	843.3	842.7
157.5°	868.6	869.5	870.4	871.2	872.0	871.9	870.7	869.5	868.2	867.0	866.7
160°	883.4	884.2	884.9	885.6	886.3	886.1	885.0	883.9	882.9	881.8	881.6
162.5°	896.3	897.1	897.9	898.8	899.7	899.5	898.3	897.1	895.9	894.6	894.5
165°	913.1	914.0	914.9	915.8	916.6	916.5	915.2	914.0	912.8	911.5	911.5
167.5°	926.9	927.8	928.8	929.7	930.6	930.4	929.2	928.0	926.7	925.4	925.5
170°	934.0	935.0	936.1	937.2	938.3	938.2	936.9	935.6	934.4	933.2	933.3
172.5°	939.8	940.8	941.9	942.9	944.0	943.9	942.7	941.4	940.2	938.9	939.1
175°	946.0	947.1	948.2	949.2	950.3	950.1	949.0	947.7	946.4	945.2	945.5
177.5°	948.9	949.7	950.6	951.4	952.3	952.3	951.4	950.6	949.7	948.9	949.2
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1079.7	1077.1	1075.5	1069.7	1064.5	1059.4	1057.7	1058.4	1051.3	1044.5	1041.6
5°	1121.8	1113.7	1106.0	1095.1	1082.2	1068.0	1060.7	1055.0	1040.9	1025.6	1016.7
7.5°	1159.5	1148.0	1133.1	1112.5	1093.8	1071.5	1057.3	1044.8	1024.1	1002.4	989.1
10°	1182.5	1166.6	1147.6	1122.6	1099.5	1072.5	1053.4	1034.4	1010.2	984.3	968.1
12.5°	1202.2	1180.9	1162.2	1130.0	1102.8	1068.9	1046.3	1019.5	994.0	963.3	947.5
15°	1249.2	1210.0	1174.3	1138.0	1104.4	1057.1	1032.1	996.0	962.4	924.5	906.3
17.5°	1285.5	1241.4	1185.3	1139.1	1099.9	1047.6	1010.7	967.7	928.0	884.5	859.8
20°	1306.2	1255.6	1195.4	1140.4	1093.4	1033.6	993.6	949.5	903.0	854.1	827.4
22.5°	1318.5	1265.4	1205.8	1135.5	1080.5	1022.3	971.9	923.6	876.5	823.7	795.7
25°	1322.4	1273.8	1210.8	1131.5	1064.4	998.5	937.8	890.9	833.9	784.5	743.7
27.5°	1303.1	1268.4	1207.7	1123.9	1045.7	968.6	901.0	847.9	787.7	734.1	693.1
30°	1279.5	1259.3	1200.2	1116.1	1030.8	947.9	873.5	813.3	753.4	699.2	657.1
32.5°	1242.9	1238.6	1186.7	1105.1	1014.9	921.7	844.7	783.8	717.5	664.2	624.2
35°	1171.2	1190.6	1157.8	1080.5	985.1	884.4	801.1	731.6	662.8	611.9	574.3
37.5°	1074.9	1123.1	1114.5	1044.6	944.8	843.8	751.9	679.1	613.6	562.2	525.3
40°	1008.5	1070.0	1079.0	1017.1	916.4	812.5	714.9	642.6	578.7	531.8	494.6
42.5°	937.4	1009.2	1033.6	984.0	885.3	779.4	682.0	607.0	543.8	498.1	465.2
45°	818.1	913.1	957.2	928.9	833.5	725.1	624.8	548.7	491.3	448.5	423.0
47.5°	706.5	810.4	869.7	859.7	775.8	668.4	569.3	496.4	440.5	406.2	383.4
50°	627.6	734.4	806.0	809.2	734.4	628.0	528.5	459.8	408.4	376.5	357.9
52.5°	559.0	660.9	739.0	756.1	688.1	586.0	492.0	423.6	378.3	349.0	332.3
55°	469.5	555.6	642.1	673.8	619.1	522.0	435.1	374.9	332.4	312.2	297.6
57.5°	390.3	462.2	542.1	576.9	543.3	460.2	378.7	326.4	291.9	274.2	263.0
60°	348.6	405.2	476.3	518.0	488.9	414.9	343.7	294.0	265.7	249.9	239.4
62.5°	309.7	359.9	420.1	458.2	442.4	372.6	308.8	264.9	240.4	225.6	218.1
65°	255.6	295.2	341.7	376.9	366.4	313.4	261.3	223.6	204.2	192.5	186.4
67.5°	210.5	239.1	271.3	302.1	293.7	256.1	214.3	185.0	170.5	160.4	156.8
70°	182.0	203.8	232.5	257.2	250.3	219.6	186.4	161.4	148.9	140.3	136.7
72.5°	154.8	172.8	194.6	214.8	210.2	184.7	157.0	138.1	128.4	120.6	117.6
75°	116.8	130.6	143.9	157.3	156.1	136.3	120.1	105.5	97.8	91.8	90.5
77.5°	86.3	94.0	103.1	111.0	108.8	97.4	84.8	76.4	70.7	66.7	66.1
80°	65.9	70.3	76.8	82.5	79.7	74.8	64.7	58.6	54.6	50.5	49.0
82.5°	47.8	52.3	56.2	59.2	57.0	52.5	46.3	42.1	39.7	37.0	36.3
85°	25.0	27.5	29.2	29.9	29.2	26.3	23.4	21.9	19.8	18.6	18.2
87.5°	13.8	13.0	12.2	12.2	10.9	10.4	8.7	7.3	7.4	7.5	7.3
90°	20.2	16.3	12.4	9.3	7.2	5.1	2.9	0.8	2.9	5.1	7.2
92.5°	23.7	22.7	21.8	20.6	19.0	17.4	15.8	14.3	15.8	17.4	19.0
95°	50.6	50.3	49.9	48.9	47.1	45.3	43.5	41.7	43.5	45.3	47.1
97.5°	85.0	84.3	83.7	82.5	81.0	79.4	77.8	76.2	77.8	79.4	81.0
100°	109.6	109.1	108.6	107.6	106.2	104.7	103.3	101.9	103.3	104.7	106.2
102.5°	135.7	135.0	134.4	133.4	132.3	131.1	130.0	128.9	130.0	131.1	132.3
105°	175.8	175.5	175.1	174.7	174.1	173.6	173.0	172.5	173.0	173.6	174.1
107.5°	220.0	220.0	220.0	219.6	218.8	218.0	217.3	216.5	217.3	218.0	218.8
110°	249.5	249.5	249.5	249.0	248.0	246.8	245.8	244.7	245.8	246.8	248.0



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.0	280.1	280.3	279.8	278.8	277.7	276.6	275.5	276.6	277.7	278.8
115°	324.9	325.2	325.6	325.2	324.2	323.1	322.0	320.9	322.0	323.1	324.2
117.5°	370.1	371.1	372.1	371.9	370.5	369.1	367.7	366.2	367.7	369.1	370.5
120°	399.3	400.7	402.1	402.1	400.7	399.3	397.8	396.4	397.8	399.3	400.7
122.5°	429.2	430.2	431.2	430.8	429.1	427.4	425.7	424.0	425.7	427.4	429.1
125°	472.9	473.4	474.0	473.4	471.8	470.2	468.6	467.0	468.6	470.2	471.8
127.5°	516.4	517.1	517.7	517.0	515.0	512.9	510.9	508.9	510.9	512.9	515.0
130°	544.7	545.1	545.4	544.5	542.2	539.8	537.5	535.2	537.5	539.8	542.2
132.5°	573.4	573.3	573.2	572.3	570.4	568.5	566.6	564.7	566.6	568.5	570.4
135°	613.9	613.5	613.1	612.0	610.1	608.1	606.2	604.2	606.2	608.1	610.1
137.5°	654.1	653.6	653.2	652.1	650.5	649.0	647.4	645.7	647.4	649.0	650.5
140°	680.2	679.4	678.4	677.2	675.6	674.0	672.4	670.7	672.4	674.0	675.6
142.5°	705.2	704.6	704.0	702.9	701.2	699.7	698.1	696.5	698.1	699.7	701.2
145°	741.6	740.6	739.5	738.4	737.1	735.9	734.6	733.3	734.6	735.9	737.1
147.5°	774.8	774.0	773.3	772.2	770.7	769.3	767.8	766.3	767.8	769.3	770.7
150°	795.4	794.6	793.9	793.0	791.9	790.8	789.8	788.7	789.8	790.8	791.9
152.5°	815.6	814.8	813.9	812.9	811.8	810.8	809.7	808.7	809.7	810.8	811.8
155°	842.2	841.7	841.1	840.6	840.1	839.6	839.0	838.4	839.0	839.6	840.1
157.5°	866.4	866.1	865.8	865.4	865.1	864.7	864.4	864.0	864.4	864.7	865.1
160°	881.5	881.3	881.1	880.8	880.4	880.1	879.7	879.4	879.7	880.1	880.4
162.5°	894.3	894.1	893.9	893.8	893.7	893.7	893.6	893.5	893.6	893.7	893.7
165°	911.5	911.5	911.5	911.6	911.7	912.0	912.1	912.3	912.1	912.0	911.7
167.5°	925.5	925.6	925.6	925.9	926.4	926.9	927.5	928.0	927.5	926.9	926.4
170°	933.5	933.7	933.9	934.2	934.8	935.3	935.8	936.4	935.8	935.3	934.8
172.5°	939.3	939.4	939.6	940.0	940.6	941.0	941.6	942.1	941.6	941.0	940.6
175°	945.9	946.3	946.6	947.1	947.6	948.2	948.6	949.2	948.6	948.2	947.6
177.5°	949.4	949.7	950.0	950.4	950.8	951.3	951.6	952.1	951.6	951.3	950.8
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1038.3	1036.4	1029.6	1026.0	1020.2	1014.7	1011.1	1012.8	1014.1	1013.4	1012.4
5°	1008.5	1000.8	989.1	979.1	971.8	958.4	952.8	949.9	947.5	944.7	941.8
7.5°	973.1	961.0	944.2	929.8	916.2	899.6	890.2	884.5	878.7	872.3	866.6
10°	947.9	930.9	913.1	892.9	876.7	861.7	848.4	839.6	831.5	823.8	818.1
12.5°	921.4	901.8	879.8	852.2	834.3	812.9	810.9	795.2	782.6	777.8	771.2
15°	879.2	851.7	823.8	791.0	776.8	757.4	745.3	733.2	722.2	714.5	712.6
17.5°	831.2	795.6	767.9	744.3	721.1	701.2	690.1	680.3	671.4	661.1	659.7
20°	794.6	763.9	733.6	713.0	689.1	668.8	655.1	645.4	637.7	631.7	626.4
22.5°	760.0	726.4	698.6	676.0	652.5	636.2	625.3	616.0	609.6	602.9	597.9
25°	704.5	678.2	647.8	622.3	602.9	592.5	583.5	575.4	571.4	567.0	561.3
27.5°	655.8	626.6	598.3	578.5	561.5	552.2	545.8	540.3	536.5	533.9	530.8
30°	621.5	592.0	569.8	550.4	536.2	527.0	522.9	519.7	515.2	513.6	512.0
32.5°	588.6	562.0	543.0	526.1	512.6	506.5	502.8	499.9	496.5	494.8	491.5
35°	541.9	519.7	501.1	491.7	480.9	475.5	472.8	468.7	465.5	463.8	463.4
37.5°	498.0	478.6	466.4	454.5	449.9	446.6	442.8	440.0	439.0	438.8	438.4
40°	469.5	453.8	442.8	433.1	431.1	426.2	423.0	420.6	420.6	421.0	420.6
42.5°	443.6	429.4	419.9	411.5	409.1	406.2	402.9	402.7	403.5	404.8	403.5
45°	404.4	394.3	387.4	383.3	378.9	376.0	375.7	376.9	377.3	377.7	378.9
47.5°	368.3	361.6	355.4	350.9	349.0	348.5	348.0	350.1	352.0	352.8	354.7
50°	347.0	339.3	334.1	331.2	329.5	328.8	329.5	332.0	333.6	335.6	336.8
52.5°	323.1	317.6	313.9	311.8	311.2	311.6	311.8	314.6	317.1	317.8	318.5
55°	289.9	285.9	285.1	281.5	283.0	282.7	284.7	286.3	288.8	291.1	291.6
57.5°	257.0	253.7	251.5	251.8	252.3	254.1	255.8	258.6	261.3	263.8	264.0
60°	235.0	233.3	232.1	232.1	232.9	235.4	237.4	240.2	241.9	243.4	244.6
62.5°	214.9	213.3	212.1	212.7	214.8	216.3	218.6	220.1	221.7	223.4	223.9
65°	183.2	182.4	183.6	184.4	184.8	186.8	189.6	190.8	192.5	193.3	196.1
67.5°	154.0	154.2	154.0	155.1	157.5	158.0	160.7	163.4	163.7	165.3	167.2
70°	134.3	135.1	135.9	136.7	138.7	139.5	141.6	142.8	144.3	145.6	146.8
72.5°	116.1	116.3	117.1	116.9	118.7	120.4	122.2	123.3	124.9	126.5	127.7
75°	89.4	89.4	90.2	90.5	92.6	94.7	94.2	95.1	96.6	98.2	99.1
77.5°	65.3	64.4	65.3	65.7	66.3	68.0	68.4	69.5	71.3	70.7	71.7
80°	49.7	48.6	49.7	50.1	50.1	52.2	52.2	53.0	54.2	53.0	54.2
82.5°	35.5	34.9	35.8	35.9	36.5	36.6	37.3	37.5	38.7	38.1	38.7
85°	17.8	17.4	17.8	17.4	17.8	18.2	18.2	17.8	17.8	18.6	17.4
87.5°	7.4	7.7	8.1	8.9	9.3	9.8	9.4	9.3	9.3	8.6	8.6
90°	9.3	12.4	16.3	20.2	24.2	28.0	27.7	27.3	27.0	26.6	26.5
92.5°	20.6	21.8	22.7	23.7	24.6	25.5	25.6	25.7	25.7	25.8	25.8
95°	48.9	49.9	50.3	50.6	51.0	51.3	51.3	51.3	51.3	51.3	51.2
97.5°	82.5	83.7	84.3	85.0	85.6	86.3	86.3	86.3	86.3	86.3	86.3
100°	107.6	108.6	109.1	109.6	110.2	110.7	110.7	110.7	110.7	110.7	110.7
102.5°	133.4	134.4	135.0	135.7	136.3	137.0	137.2	137.4	137.4	137.6	137.6
105°	174.7	175.1	175.5	175.8	176.2	176.5	176.9	177.2	177.6	177.9	178.2
107.5°	219.6	220.0	220.0	220.0	220.0	220.0	220.1	220.3	220.5	220.5	220.2
110°	249.0	249.5	249.5	249.5	249.5	249.5	249.5	249.5	249.5	249.5	249.3



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	279.8	280.3	280.1	280.0	279.9	279.7	279.2	278.8	278.5	278.0	277.6
115°	325.2	325.6	325.2	324.9	324.5	324.2	324.0	323.8	323.6	323.4	323.1
117.5°	371.9	372.1	371.1	370.1	369.2	368.1	367.7	367.3	366.9	366.4	365.9
120°	402.1	402.1	400.7	399.3	397.8	396.4	396.4	396.4	396.4	396.4	396.1
122.5°	430.8	431.2	430.2	429.2	428.2	427.1	426.7	426.4	425.9	425.5	425.1
125°	473.4	474.0	473.4	472.9	472.3	471.8	471.3	470.7	470.2	469.7	469.3
127.5°	517.0	517.7	517.1	516.4	515.8	515.2	514.4	513.8	513.2	512.5	511.9
130°	544.5	545.4	545.1	544.7	544.4	544.0	543.7	543.3	543.0	542.6	542.0
132.5°	572.3	573.2	573.3	573.4	573.5	573.5	572.7	572.0	571.2	570.4	569.7
135°	612.0	613.1	613.5	613.9	614.3	614.6	614.4	614.3	614.1	613.9	613.5
137.5°	652.1	653.2	653.6	654.1	654.6	655.1	654.9	654.7	654.7	654.5	654.0
140°	677.2	678.4	679.4	680.2	681.1	682.0	682.0	682.0	682.0	682.0	681.7
142.5°	702.9	704.0	704.6	705.2	705.8	706.4	706.5	706.7	706.9	706.9	706.7
145°	738.4	739.5	740.6	741.6	742.8	743.8	743.9	744.2	744.3	744.5	744.3
147.5°	772.2	773.3	774.0	774.8	775.5	776.2	776.6	777.0	777.4	777.8	777.6
150°	793.0	793.9	794.6	795.4	796.1	796.8	797.3	797.8	798.4	798.9	798.9
152.5°	812.9	813.9	814.8	815.6	816.4	817.3	817.9	818.6	819.4	820.0	820.0
155°	840.6	841.1	841.7	842.2	842.7	843.3	844.1	845.1	846.0	846.8	847.0
157.5°	865.4	865.8	866.1	866.4	866.7	867.0	868.2	869.5	870.7	871.9	872.0
160°	880.8	881.1	881.3	881.5	881.6	881.8	882.9	883.9	885.0	886.1	886.3
162.5°	893.8	893.9	894.1	894.3	894.5	894.6	895.9	897.1	898.3	899.5	899.7
165°	911.6	911.5	911.5	911.5	911.5	911.5	912.8	914.0	915.2	916.5	916.6
167.5°	925.9	925.6	925.6	925.5	925.5	925.4	926.7	928.0	929.2	930.4	930.6
170°	934.2	933.9	933.7	933.5	933.3	933.2	934.4	935.6	936.9	938.2	938.3
172.5°	940.0	939.6	939.4	939.3	939.1	938.9	940.2	941.4	942.7	943.9	944.0
175°	947.1	946.6	946.3	945.9	945.5	945.2	946.4	947.7	949.0	950.1	950.3
177.5°	950.4	950.0	949.7	949.4	949.2	948.9	949.7	950.6	951.4	952.3	952.3
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1009.2	1008.5	1008.5	1005.7	1008.5	1008.5	1009.2	1012.4	1013.4	1014.1	1012.8
5°	936.2	934.9	933.0	934.9	933.0	934.9	936.2	941.8	944.7	947.5	949.9
7.5°	864.0	859.1	858.4	853.6	858.4	859.1	864.0	866.6	872.3	878.7	884.5
10°	811.2	807.9	807.6	799.9	807.6	807.9	811.2	818.1	823.8	831.5	839.6
12.5°	771.1	763.3	764.9	760.4	764.9	763.3	771.1	771.2	777.8	782.6	795.2
15°	701.6	701.6	700.0	693.2	700.0	701.6	701.6	712.6	714.5	722.2	733.2
17.5°	651.7	650.9	647.1	649.0	647.1	650.9	651.7	659.7	661.1	671.4	680.3
20°	621.9	619.6	614.7	614.7	614.7	619.6	621.9	626.4	631.7	637.7	645.4
22.5°	593.8	593.7	588.5	590.1	588.5	593.7	593.8	597.9	602.9	609.6	616.0
25°	560.9	557.7	555.2	556.4	555.2	557.7	560.9	561.3	567.0	571.4	575.4
27.5°	529.7	527.9	527.8	524.4	527.8	527.9	529.7	530.8	533.9	536.5	540.3
30°	511.6	507.6	508.3	506.3	508.3	507.6	511.6	512.0	513.6	515.2	519.7
32.5°	490.8	489.4	488.6	486.9	488.6	489.4	490.8	491.5	494.8	496.5	499.9
35°	462.6	463.0	461.1	461.8	461.1	463.0	462.6	463.4	463.8	465.5	468.7
37.5°	438.0	439.3	438.3	438.6	438.3	439.3	438.0	438.4	438.8	439.0	440.0
40°	421.8	421.8	421.8	423.0	421.8	421.8	421.8	420.6	421.0	420.6	420.6
42.5°	406.2	405.6	405.0	404.9	405.0	405.6	406.2	403.5	404.8	403.5	402.7
45°	379.7	381.0	381.4	379.3	381.4	381.0	379.7	378.9	377.7	377.3	376.9
47.5°	355.7	355.8	355.7	357.5	355.7	355.8	355.7	354.7	352.8	352.0	350.1
50°	338.9	338.1	338.9	338.1	338.9	338.1	338.9	336.8	335.6	333.6	332.0
52.5°	321.1	321.2	320.8	320.6	320.8	321.2	321.1	318.5	317.8	317.1	314.6
55°	293.2	294.0	293.6	293.6	293.6	294.0	293.2	291.6	291.1	288.8	286.3
57.5°	264.4	265.1	265.6	263.8	265.6	265.1	264.4	264.0	263.8	261.3	258.6
60°	244.2	246.3	245.9	245.1	245.9	246.3	244.2	244.6	243.4	241.9	240.2
62.5°	225.9	226.6	226.5	226.3	226.5	226.6	225.9	223.9	223.4	221.7	220.1
65°	197.3	198.1	196.9	198.1	196.9	198.1	197.3	196.1	193.3	192.5	190.8
67.5°	166.7	166.9	167.9	168.4	167.9	166.9	166.7	167.2	165.3	163.7	163.4
70°	147.6	147.2	148.4	149.6	148.4	147.2	147.6	146.8	145.6	144.3	142.8
72.5°	127.5	128.4	128.0	128.9	128.0	128.4	127.5	127.7	126.5	124.9	123.3
75°	98.2	99.5	99.1	100.3	99.1	99.5	98.2	99.1	98.2	96.6	95.1
77.5°	71.0	71.1	71.0	71.7	71.0	71.1	71.0	71.7	70.7	71.3	69.5
80°	54.2	53.4	52.6	54.2	52.6	53.4	54.2	54.2	53.0	54.2	53.0
82.5°	37.7	38.2	37.4	37.4	37.4	38.2	37.7	38.7	38.1	38.7	37.5
85°	17.4	17.0	16.2	16.2	16.2	17.0	17.4	17.4	18.6	17.8	17.8
87.5°	8.6	8.3	8.3	8.1	8.3	8.3	8.6	8.6	8.6	9.3	9.3
90°	26.8	26.9	27.1	27.3	27.1	26.9	26.8	26.5	26.6	27.0	27.3
92.5°	25.9	25.9	26.0	26.0	26.0	25.9	25.9	25.8	25.8	25.7	25.7
95°	50.8	50.5	50.1	49.7	50.1	50.5	50.8	51.2	51.3	51.3	51.3
97.5°	86.3	86.3	86.2	86.2	86.2	86.3	86.3	86.3	86.3	86.3	86.3
100°	110.4	110.3	110.1	110.0	110.1	110.3	110.4	110.7	110.7	110.7	110.7
102.5°	137.4	137.2	137.0	136.9	137.0	137.2	137.4	137.6	137.6	137.4	137.4
105°	178.2	178.2	178.2	178.2	178.2	178.2	178.2	178.2	177.9	177.6	177.2
107.5°	219.4	218.6	217.8	217.0	217.8	218.6	219.4	220.2	220.5	220.5	220.3
110°	248.7	248.2	247.6	247.2	247.6	248.2	248.7	249.3	249.5	249.5	249.5



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	277.2	276.8	276.4	276.0	276.4	276.8	277.2	277.6	278.0	278.5	278.8
115°	322.6	322.0	321.5	320.9	321.5	322.0	322.6	323.1	323.4	323.6	323.8
117.5°	365.4	364.9	364.3	363.8	364.3	364.9	365.4	365.9	366.4	366.9	367.3
120°	395.5	395.1	394.5	394.0	394.5	395.1	395.5	396.1	396.4	396.4	396.4
122.5°	424.7	424.3	423.9	423.5	423.9	424.3	424.7	425.1	425.5	425.9	426.4
125°	469.1	469.0	468.7	468.6	468.7	469.0	469.1	469.3	469.7	470.2	470.7
127.5°	511.4	510.8	510.2	509.7	510.2	510.8	511.4	511.9	512.5	513.2	513.8
130°	541.3	540.6	539.9	539.2	539.9	540.6	541.3	542.0	542.6	543.0	543.3
132.5°	569.2	568.5	568.0	567.4	568.0	568.5	569.2	569.7	570.4	571.2	572.0
135°	613.0	612.4	612.0	611.4	612.0	612.4	613.0	613.5	613.9	614.1	614.3
137.5°	653.3	652.6	651.9	651.2	651.9	652.6	653.3	654.0	654.5	654.7	654.7
140°	681.0	680.2	679.5	678.8	679.5	680.2	681.0	681.7	682.0	682.0	682.0
142.5°	706.0	705.3	704.6	703.9	704.6	705.3	706.0	706.7	706.9	706.9	706.7
145°	743.5	742.8	742.1	741.4	742.1	742.8	743.5	744.3	744.5	744.3	744.2
147.5°	777.0	776.3	775.6	774.9	775.6	776.3	777.0	777.6	777.8	777.4	777.0
150°	798.4	797.8	797.3	796.8	797.3	797.8	798.4	798.9	798.9	798.4	797.8
152.5°	819.4	818.6	817.9	817.3	817.9	818.6	819.4	820.0	820.0	819.4	818.6
155°	846.5	846.0	845.4	844.9	845.4	846.0	846.5	847.0	846.8	846.0	845.1
157.5°	871.2	870.4	869.5	868.6	869.5	870.4	871.2	872.0	871.9	870.7	869.5
160°	885.6	884.9	884.2	883.4	884.2	884.9	885.6	886.3	886.1	885.0	883.9
162.5°	898.8	897.9	897.1	896.3	897.1	897.9	898.8	899.7	899.5	898.3	897.1
165°	915.8	914.9	914.0	913.1	914.0	914.9	915.8	916.6	916.5	915.2	914.0
167.5°	929.7	928.8	927.8	926.9	927.8	928.8	929.7	930.6	930.4	929.2	928.0
170°	937.2	936.1	935.0	934.0	935.0	936.1	937.2	938.3	938.2	936.9	935.6
172.5°	942.9	941.9	940.8	939.8	940.8	941.9	942.9	944.0	943.9	942.7	941.4
175°	949.2	948.2	947.1	946.0	947.1	948.2	949.2	950.3	950.1	949.0	947.7
177.5°	951.4	950.6	949.7	948.9	949.7	950.6	951.4	952.3	952.3	951.4	950.6
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1011.1	1014.7	1020.2	1026.0	1029.6	1036.4	1038.3	1041.6	1044.5	1051.3	1058.4
5°	952.8	958.4	971.8	979.1	989.1	1000.8	1008.5	1016.7	1025.6	1040.9	1055.0
7.5°	890.2	899.6	916.2	929.8	944.2	961.0	973.1	989.1	1002.4	1024.1	1044.8
10°	848.4	861.7	876.7	892.9	913.1	930.9	947.9	968.1	984.3	1010.2	1034.4
12.5°	810.9	812.9	834.3	852.2	879.8	901.8	921.4	947.5	963.3	994.0	1019.5
15°	745.3	757.4	776.8	791.0	823.8	851.7	879.2	906.3	924.5	962.4	996.0
17.5°	690.1	701.2	721.1	744.3	767.9	795.6	831.2	859.8	884.5	928.0	967.7
20°	655.1	668.8	689.1	713.0	733.6	763.9	794.6	827.4	854.1	903.0	949.5
22.5°	625.3	636.2	652.5	676.0	698.6	726.4	760.0	795.7	823.7	876.5	923.6
25°	583.5	592.5	602.9	622.3	647.8	678.2	704.5	743.7	784.5	833.9	890.9
27.5°	545.8	552.2	561.5	578.5	598.3	626.6	655.8	693.1	734.1	787.7	847.9
30°	522.9	527.0	536.2	550.4	569.8	592.0	621.5	657.1	699.2	753.4	813.3
32.5°	502.8	506.5	512.6	526.1	543.0	562.0	588.6	624.2	664.2	717.5	783.8
35°	472.8	475.5	480.9	491.7	501.1	519.7	541.9	574.3	611.9	662.8	731.6
37.5°	442.8	446.6	449.9	454.5	466.4	478.6	498.0	525.3	562.2	613.6	679.1
40°	423.0	426.2	431.1	433.1	442.8	453.8	469.5	494.6	531.8	578.7	642.6
42.5°	402.9	406.2	409.1	411.5	419.9	429.4	443.6	465.2	498.1	543.8	607.0
45°	375.7	376.0	378.9	383.3	387.4	394.3	404.4	423.0	448.5	491.3	548.7
47.5°	348.0	348.5	349.0	350.9	355.4	361.6	368.3	383.4	406.2	440.5	496.4
50°	329.5	328.8	329.5	331.2	334.1	339.3	347.0	357.9	376.5	408.4	459.8
52.5°	311.8	311.6	311.2	311.8	313.9	317.6	323.1	332.3	349.0	378.3	423.6
55°	284.7	282.7	283.0	281.5	285.1	285.9	289.9	297.6	312.2	332.4	374.9
57.5°	255.8	254.1	252.3	251.8	251.5	253.7	257.0	263.0	274.2	291.9	326.4
60°	237.4	235.4	232.9	232.1	232.1	233.3	235.0	239.4	249.9	265.7	294.0
62.5°	218.6	216.3	214.8	212.7	212.1	213.3	214.9	218.1	225.6	240.4	264.9
65°	189.6	186.8	184.8	184.4	183.6	182.4	183.2	186.4	192.5	204.2	223.6
67.5°	160.7	158.0	157.5	155.1	154.0	154.2	154.0	156.8	160.4	170.5	185.0
70°	141.6	139.5	138.7	136.7	135.9	135.1	134.3	136.7	140.3	148.9	161.4
72.5°	122.2	120.4	118.7	116.9	117.1	116.3	116.1	117.6	120.6	128.4	138.1
75°	94.2	94.7	92.6	90.5	90.2	89.4	89.4	90.5	91.8	97.8	105.5
77.5°	68.4	68.0	66.3	65.7	65.3	64.4	65.3	66.1	66.7	70.7	76.4
80°	52.2	52.2	50.1	50.1	49.7	48.6	49.7	49.0	50.5	54.6	58.6
82.5°	37.3	36.6	36.5	35.9	35.8	34.9	35.5	36.3	37.0	39.7	42.1
85°	18.2	18.2	17.8	17.4	17.8	17.4	17.8	18.2	18.6	19.8	21.9
87.5°	9.4	9.8	9.3	8.9	8.1	7.7	7.4	7.3	7.5	7.4	7.3
90°	27.7	28.0	24.2	20.2	16.3	12.4	9.3	7.2	5.1	2.9	0.8
92.5°	25.6	25.5	24.6	23.7	22.7	21.8	20.6	19.0	17.4	15.8	14.3
95°	51.3	51.3	51.0	50.6	50.3	49.9	48.9	47.1	45.3	43.5	41.7
97.5°	86.3	86.3	85.6	85.0	84.3	83.7	82.5	81.0	79.4	77.8	76.2
100°	110.7	110.7	110.2	109.6	109.1	108.6	107.6	106.2	104.7	103.3	101.9
102.5°	137.2	137.0	136.3	135.7	135.0	134.4	133.4	132.3	131.1	130.0	128.9
105°	176.9	176.5	176.2	175.8	175.5	175.1	174.7	174.1	173.6	173.0	172.5
107.5°	220.1	220.0	220.0	220.0	220.0	220.0	219.6	218.8	218.0	217.3	216.5
110°	249.5	249.5	249.5	249.5	249.5	249.5	249.0	248.0	246.8	245.8	244.7



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	279.2	279.7	279.9	280.0	280.1	280.3	279.8	278.8	277.7	276.6	275.5
115°	324.0	324.2	324.5	324.9	325.2	325.6	325.2	324.2	323.1	322.0	320.9
117.5°	367.7	368.1	369.2	370.1	371.1	372.1	371.9	370.5	369.1	367.7	366.2
120°	396.4	396.4	397.8	399.3	400.7	402.1	402.1	400.7	399.3	397.8	396.4
122.5°	426.7	427.1	428.2	429.2	430.2	431.2	430.8	429.1	427.4	425.7	424.0
125°	471.3	471.8	472.3	472.9	473.4	474.0	473.4	471.8	470.2	468.6	467.0
127.5°	514.4	515.2	515.8	516.4	517.1	517.7	517.0	515.0	512.9	510.9	508.9
130°	543.7	544.0	544.4	544.7	545.1	545.4	544.5	542.2	539.8	537.5	535.2
132.5°	572.7	573.5	573.5	573.4	573.3	573.2	572.3	570.4	568.5	566.6	564.7
135°	614.4	614.6	614.3	613.9	613.5	613.1	612.0	610.1	608.1	606.2	604.2
137.5°	654.9	655.1	654.6	654.1	653.6	653.2	652.1	650.5	649.0	647.4	645.7
140°	682.0	682.0	681.1	680.2	679.4	678.4	677.2	675.6	674.0	672.4	670.7
142.5°	706.5	706.4	705.8	705.2	704.6	704.0	702.9	701.2	699.7	698.1	696.5
145°	743.9	743.8	742.8	741.6	740.6	739.5	738.4	737.1	735.9	734.6	733.3
147.5°	776.6	776.2	775.5	774.8	774.0	773.3	772.2	770.7	769.3	767.8	766.3
150°	797.3	796.8	796.1	795.4	794.6	793.9	793.0	791.9	790.8	789.8	788.7
152.5°	817.9	817.3	816.4	815.6	814.8	813.9	812.9	811.8	810.8	809.7	808.7
155°	844.1	843.3	842.7	842.2	841.7	841.1	840.6	840.1	839.6	839.0	838.4
157.5°	868.2	867.0	866.7	866.4	866.1	865.8	865.4	865.1	864.7	864.4	864.0
160°	882.9	881.8	881.6	881.5	881.3	881.1	880.8	880.4	880.1	879.7	879.4
162.5°	895.9	894.6	894.5	894.3	894.1	893.9	893.8	893.7	893.7	893.6	893.5
165°	912.8	911.5	911.5	911.5	911.5	911.5	911.6	911.7	912.0	912.1	912.3
167.5°	926.7	925.4	925.5	925.5	925.6	925.6	925.9	926.4	926.9	927.5	928.0
170°	934.4	933.2	933.3	933.5	933.7	933.9	934.2	934.8	935.3	935.8	936.4
172.5°	940.2	938.9	939.1	939.3	939.4	939.6	940.0	940.6	941.0	941.6	942.1
175°	946.4	945.2	945.5	945.9	946.3	946.6	947.1	947.6	948.2	948.6	949.2
177.5°	949.7	948.9	949.2	949.4	949.7	950.0	950.4	950.8	951.3	951.6	952.1
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1057.7	1059.4	1064.5	1069.7	1075.5	1077.1	1079.7	1077.4	1076.8	1083.0	1087.5
5°	1060.7	1068.0	1082.2	1095.1	1106.0	1113.7	1121.8	1125.1	1131.1	1139.6	1150.1
7.5°	1057.3	1071.5	1093.8	1112.5	1133.1	1148.0	1159.5	1169.3	1181.3	1197.4	1215.0
10°	1053.4	1072.5	1099.5	1122.6	1147.6	1166.6	1182.5	1197.8	1215.6	1237.9	1260.9
12.5°	1046.3	1068.9	1102.8	1130.0	1162.2	1180.9	1202.2	1235.3	1254.4	1285.4	1317.9
15°	1032.1	1057.1	1104.4	1138.0	1174.3	1210.0	1249.2	1280.7	1312.2	1330.5	1376.2
17.5°	1010.7	1047.6	1099.9	1139.1	1185.3	1241.4	1285.5	1321.2	1357.6	1387.2	1410.1
20°	993.6	1033.6	1093.4	1140.4	1195.4	1255.6	1306.2	1342.6	1374.1	1398.8	1412.9
22.5°	971.9	1022.3	1080.5	1135.5	1205.8	1265.4	1318.5	1347.1	1373.5	1385.5	1391.0
25°	937.8	998.5	1064.4	1131.5	1210.8	1273.8	1322.4	1339.7	1347.4	1335.7	1316.3
27.5°	901.0	968.6	1045.7	1123.9	1207.7	1268.4	1303.1	1300.4	1287.4	1249.4	1219.1
30°	873.5	947.9	1030.8	1116.1	1200.2	1259.3	1279.5	1259.3	1229.8	1187.3	1144.1
32.5°	844.7	921.7	1014.9	1105.1	1186.7	1238.6	1242.9	1208.2	1162.4	1114.2	1060.3
35°	801.1	884.4	985.1	1080.5	1157.8	1190.6	1171.2	1109.7	1055.5	989.6	915.9
37.5°	751.9	843.8	944.8	1044.6	1114.5	1123.1	1074.9	1010.2	933.7	856.3	769.7
40°	714.9	812.5	916.4	1017.1	1079.0	1070.0	1008.5	937.4	846.4	751.8	671.3
42.5°	682.0	779.4	885.3	984.0	1033.6	1009.2	937.4	850.0	752.3	663.1	589.5
45°	624.8	725.1	833.5	928.9	957.2	913.1	818.1	721.0	624.8	550.4	492.2
47.5°	569.3	668.4	775.8	859.7	869.7	810.4	706.5	606.7	523.9	463.3	422.2
50°	528.5	628.0	734.4	809.2	806.0	734.4	627.6	532.6	463.4	414.5	387.0
52.5°	492.0	586.0	688.1	756.1	739.0	660.9	559.0	474.7	417.8	379.5	354.7
55°	435.1	522.0	619.1	673.8	642.1	555.6	469.5	401.6	359.5	330.8	311.4
57.5°	378.7	460.2	543.3	576.9	542.1	462.2	390.3	341.0	309.4	288.2	275.5
60°	343.7	414.9	488.9	518.0	476.3	405.2	348.6	304.5	279.0	261.7	250.3
62.5°	308.8	372.6	442.4	458.2	420.1	359.9	309.7	273.1	252.2	236.7	226.1
65°	261.3	313.4	366.4	376.9	341.7	295.2	255.6	231.7	213.1	201.8	193.3
67.5°	214.3	256.1	293.7	302.1	271.3	239.1	210.5	189.6	177.1	167.6	160.5
70°	186.4	219.6	250.3	257.2	232.5	203.8	182.0	165.4	154.1	146.0	139.1
72.5°	157.0	184.7	210.2	214.8	194.6	172.8	154.8	141.8	131.7	126.6	120.0
75°	120.1	136.3	156.1	157.3	143.9	130.6	116.8	108.4	103.1	96.6	93.4
77.5°	84.8	97.4	108.8	111.0	103.1	94.0	86.3	79.6	75.1	72.2	69.2
80°	64.7	74.8	79.7	82.5	76.8	70.3	65.9	61.5	58.6	56.6	54.6
82.5°	46.3	52.5	57.0	59.2	56.2	52.3	47.8	45.3	43.1	41.4	40.7
85°	23.4	26.3	29.2	29.9	29.2	27.5	25.0	25.0	23.8	23.4	23.4
87.5°	8.7	10.4	10.9	12.2	12.2	13.0	13.8	14.2	14.7	14.3	13.9
90°	2.9	5.1	7.2	9.3	12.4	16.3	20.2	24.2	28.0	27.7	27.3
92.5°	15.8	17.4	19.0	20.6	21.8	22.7	23.7	24.6	25.5	25.6	25.7
95°	43.5	45.3	47.1	48.9	49.9	50.3	50.6	51.0	51.3	51.3	51.3
97.5°	77.8	79.4	81.0	82.5	83.7	84.3	85.0	85.6	86.3	86.3	86.3
100°	103.3	104.7	106.2	107.6	108.6	109.1	109.6	110.2	110.7	110.7	110.7
102.5°	130.0	131.1	132.3	133.4	134.4	135.0	135.7	136.3	137.0	137.2	137.4
105°	173.0	173.6	174.1	174.7	175.1	175.5	175.8	176.2	176.5	176.9	177.2
107.5°	217.3	218.0	218.8	219.6	220.0	220.0	220.0	220.0	220.0	220.1	220.3
110°	245.8	246.8	248.0	249.0	249.5	249.5	249.5	249.5	249.5	249.5	249.5



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.6	277.7	278.8	279.8	280.3	280.1	280.0	279.9	279.7	279.2	278.8
115°	322.0	323.1	324.2	325.2	325.6	325.2	324.9	324.5	324.2	324.0	323.8
117.5°	367.7	369.1	370.5	371.9	372.1	371.1	370.1	369.2	368.1	367.7	367.3
120°	397.8	399.3	400.7	402.1	402.1	400.7	399.3	397.8	396.4	396.4	396.4
122.5°	425.7	427.4	429.1	430.8	431.2	430.2	429.2	428.2	427.1	426.7	426.4
125°	468.6	470.2	471.8	473.4	474.0	473.4	472.9	472.3	471.8	471.3	470.7
127.5°	510.9	512.9	515.0	517.0	517.7	517.1	516.4	515.8	515.2	514.4	513.8
130°	537.5	539.8	542.2	544.5	545.4	545.1	544.7	544.4	544.0	543.7	543.3
132.5°	566.6	568.5	570.4	572.3	573.2	573.3	573.4	573.5	573.5	572.7	572.0
135°	606.2	608.1	610.1	612.0	613.1	613.5	613.9	614.3	614.6	614.4	614.3
137.5°	647.4	649.0	650.5	652.1	653.2	653.6	654.1	654.6	655.1	654.9	654.7
140°	672.4	674.0	675.6	677.2	678.4	679.4	680.2	681.1	682.0	682.0	682.0
142.5°	698.1	699.7	701.2	702.9	704.0	704.6	705.2	705.8	706.4	706.5	706.7
145°	734.6	735.9	737.1	738.4	739.5	740.6	741.6	742.8	743.8	743.9	744.2
147.5°	767.8	769.3	770.7	772.2	773.3	774.0	774.8	775.5	776.2	776.6	777.0
150°	789.8	790.8	791.9	793.0	793.9	794.6	795.4	796.1	796.8	797.3	797.8
152.5°	809.7	810.8	811.8	812.9	813.9	814.8	815.6	816.4	817.3	817.9	818.6
155°	839.0	839.6	840.1	840.6	841.1	841.7	842.2	842.7	843.3	844.1	845.1
157.5°	864.4	864.7	865.1	865.4	865.8	866.1	866.4	866.7	867.0	868.2	869.5
160°	879.7	880.1	880.4	880.8	881.1	881.3	881.5	881.6	881.8	882.9	883.9
162.5°	893.6	893.7	893.7	893.8	893.9	894.1	894.3	894.5	894.6	895.9	897.1
165°	912.1	912.0	911.7	911.6	911.5	911.5	911.5	911.5	911.5	912.8	914.0
167.5°	927.5	926.9	926.4	925.9	925.6	925.6	925.5	925.5	925.4	926.7	928.0
170°	935.8	935.3	934.8	934.2	933.9	933.7	933.5	933.3	933.2	934.4	935.6
172.5°	941.6	941.0	940.6	940.0	939.6	939.4	939.3	939.1	938.9	940.2	941.4
175°	948.6	948.2	947.6	947.1	946.6	946.3	945.9	945.5	945.2	946.4	947.7
177.5°	951.6	951.3	950.8	950.4	950.0	949.7	949.4	949.2	948.9	949.7	950.6
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3
2.5°	1091.4	1095.9	1095.9	1096.5	1101.8	1101.1	1100.7
5°	1161.4	1168.3	1169.1	1176.4	1181.2	1179.6	1175.2
7.5°	1227.5	1240.3	1250.0	1255.4	1261.8	1265.7	1264.0
10°	1279.9	1298.5	1309.9	1317.6	1326.8	1333.7	1331.3
12.5°	1327.5	1349.6	1365.2	1378.3	1379.6	1388.4	1382.4
15°	1401.6	1425.1	1427.5	1437.3	1444.9	1444.1	1444.5
17.5°	1426.2	1433.7	1435.2	1435.4	1435.5	1432.7	1426.6
20°	1417.4	1414.6	1407.7	1402.5	1393.1	1391.9	1383.9
22.5°	1376.0	1367.0	1349.8	1338.4	1323.9	1320.1	1317.9
25°	1294.5	1274.6	1247.1	1220.8	1213.6	1199.4	1203.5
27.5°	1182.6	1151.8	1122.0	1100.6	1081.2	1060.1	1066.1
30°	1104.0	1069.2	1027.1	994.8	974.2	953.9	950.3
32.5°	1010.2	959.3	912.3	883.8	852.2	839.5	825.5
35°	848.4	798.7	752.2	712.2	689.1	671.3	655.1
37.5°	702.9	645.6	608.2	575.7	559.0	548.8	551.4
40°	612.7	562.5	535.0	510.3	495.0	487.7	489.3
42.5°	539.6	502.0	479.3	462.5	451.6	447.6	446.6
45°	456.5	435.5	416.9	407.3	402.0	397.5	394.7
47.5°	400.0	382.8	372.3	366.5	361.9	357.4	357.4
50°	366.0	354.7	347.4	341.3	337.7	334.5	337.2
52.5°	340.1	329.7	322.5	317.0	315.7	312.8	312.7
55°	301.7	293.6	288.4	283.4	281.1	279.4	277.4
57.5°	266.7	259.0	254.2	251.1	246.5	244.9	244.2
60°	241.9	235.8	230.9	226.9	224.8	221.6	221.6
62.5°	218.9	212.8	208.3	205.2	201.8	200.6	200.9
65°	185.6	180.8	176.3	173.1	172.3	169.8	170.6
67.5°	155.0	151.8	147.1	145.4	143.8	142.5	141.6
70°	134.7	131.4	129.0	126.6	125.3	125.3	125.3
72.5°	117.5	113.6	112.2	109.1	109.8	108.5	107.3
75°	91.0	88.6	87.4	86.1	84.1	84.1	84.1
77.5°	66.9	66.2	64.8	63.5	63.0	62.6	62.7
80°	51.7	51.3	50.5	50.5	49.7	49.4	48.6
82.5°	39.8	38.7	38.3	37.9	37.8	37.7	37.5
85°	22.7	21.9	21.9	22.3	21.5	21.5	21.9
87.5°	14.1	14.1	13.7	13.8	14.1	13.9	13.9
90°	27.0	26.6	26.5	26.8	26.9	27.1	27.3
92.5°	25.7	25.8	25.8	25.9	25.9	26.0	26.0
95°	51.3	51.3	51.2	50.8	50.5	50.1	49.7
97.5°	86.3	86.3	86.3	86.3	86.3	86.2	86.2
100°	110.7	110.7	110.7	110.4	110.3	110.1	110.0
102.5°	137.4	137.6	137.6	137.4	137.2	137.0	136.9
105°	177.6	177.9	178.2	178.2	178.2	178.2	178.2
107.5°	220.5	220.5	220.2	219.4	218.6	217.8	217.0
110°	249.5	249.5	249.3	248.7	248.2	247.6	247.2



TEST NUMBER: P331538-927

CATALOG NUMBER: S122DIW-S675D970U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	278.5	278.0	277.6	277.2	276.8	276.4	276.0
115°	323.6	323.4	323.1	322.6	322.0	321.5	320.9
117.5°	366.9	366.4	365.9	365.4	364.9	364.3	363.8
120°	396.4	396.4	396.1	395.5	395.1	394.5	394.0
122.5°	425.9	425.5	425.1	424.7	424.3	423.9	423.5
125°	470.2	469.7	469.3	469.1	469.0	468.7	468.6
127.5°	513.2	512.5	511.9	511.4	510.8	510.2	509.7
130°	543.0	542.6	542.0	541.3	540.6	539.9	539.2
132.5°	571.2	570.4	569.7	569.2	568.5	568.0	567.4
135°	614.1	613.9	613.5	613.0	612.4	612.0	611.4
137.5°	654.7	654.5	654.0	653.3	652.6	651.9	651.2
140°	682.0	682.0	681.7	681.0	680.2	679.5	678.8
142.5°	706.9	706.9	706.7	706.0	705.3	704.6	703.9
145°	744.3	744.5	744.3	743.5	742.8	742.1	741.4
147.5°	777.4	777.8	777.6	777.0	776.3	775.6	774.9
150°	798.4	798.9	798.9	798.4	797.8	797.3	796.8
152.5°	819.4	820.0	820.0	819.4	818.6	817.9	817.3
155°	846.0	846.8	847.0	846.5	846.0	845.4	844.9
157.5°	870.7	871.9	872.0	871.2	870.4	869.5	868.6
160°	885.0	886.1	886.3	885.6	884.9	884.2	883.4
162.5°	898.3	899.5	899.7	898.8	897.9	897.1	896.3
165°	915.2	916.5	916.6	915.8	914.9	914.0	913.1
167.5°	929.2	930.4	930.6	929.7	928.8	927.8	926.9
170°	936.9	938.2	938.3	937.2	936.1	935.0	934.0
172.5°	942.7	943.9	944.0	942.9	941.9	940.8	939.8
175°	949.0	950.1	950.3	949.2	948.2	947.1	946.0
177.5°	951.4	952.3	952.3	951.4	950.6	949.7	948.9
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8

(END OF REPORT)