

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331579-927

Luminaire Tested: **S122DIW-S865D1440U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331579-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1440U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7584.4 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																				
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40	34																				
2	88	81	75	70	80	74	69	64	61	57	54	48	46	44	37	36	34	29																				
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25																				
4	73	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22																				
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19																				
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17																				
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15																				
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14																				
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13																				
10	47	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	14	12																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22083	22083	22083	22083
5°	24759	22227	19697	22227
10°	28370	22046	17046	22046
15°	31385	21641	15059	21641
20°	30907	21206	13728	21206
25°	27868	20630	12886	20630
30°	23029	19708	12269	19708
35°	16783	18743	11832	18743
40°	13405	17606	11590	17606
45°	11714	16287	11259	16287
50°	11012	15013	11037	15013
55°	10151	13717	10742	13717
60°	9300	12339	10285	12339
65°	8474	11106	9838	11106
70°	7695	9904	9182	9904
75°	6818	8559	8135	8559
80°	5867	7085	6546	7085
85°	5261	5261	3890	5261



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.3	1.7
10°-20°	378.7	5.0
20°-30°	549.6	7.2
30°-40°	579.9	7.6
40°-50°	513.5	6.8
50°-60°	409.8	5.4
60°-70°	278.5	3.7
70°-80°	142.8	1.9
80°-90°	38.3	0.5
90°-100°	51.9	0.7
100°-110°	190.5	2.5
110°-120°	509.1	6.7
120°-130°	840.4	11.1
130°-140°	893.8	11.8
140°-150°	830.7	11.0
150°-160°	667.9	8.8
160°-170°	430.4	5.7
170°-180°	148.2	2.0
0°-30°	1058.5	14.0
0°-40°	1638.5	21.6
0°-60°	2561.8	33.8
0°-90°	3021.3	39.8
90°-120°	751.5	9.9
90°-150°	3316.5	43.7
90°-180°	4563.0	60.2
0°-180°	7584.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1368	1368	1368	1368	1368	
5°	1528	1371	1215	1371	1528	153
15°	1878	1295	901	1295	1878	518
25°	1564	1158	723	1158	1564	707
35°	852	951	600	951	852	554
45°	513	713	493	713	513	403
55°	361	487	382	487	361	323
65°	222	291	258	291	222	221
75°	109	137	130	137	109	117
85°	28	28	21	28	28	32
90°	30	1	30	1	30	15
95°	48	73	48	73	48	45
105°	86	342	86	342	86	89
115°	92	648	92	648	92	231
125°	963	916	963	916	963	834
135°	1171	1134	1171	1134	1171	902
145°	1335	1315	1335	1315	1335	835
155°	1449	1448	1449	1448	1449	669
165°	1522	1526	1522	1526	1522	430
175°	1551	1560	1551	1560	1551	148
180°	1557	1557	1557	1557	1557	



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1430.8	1431.2	1432.1	1425.4	1424.5	1424.5	1418.6	1413.6	1407.7	1399.7	1400.6
5°	1527.6	1533.3	1535.4	1529.1	1519.6	1518.6	1509.7	1494.9	1481.3	1470.2	1462.4
7.5°	1643.0	1645.3	1640.1	1631.8	1624.8	1612.2	1595.5	1579.3	1556.5	1535.6	1520.0
10°	1730.4	1733.6	1724.7	1712.5	1702.6	1687.8	1663.7	1638.9	1609.0	1580.1	1557.0
12.5°	1796.9	1804.7	1793.2	1791.6	1774.5	1754.3	1725.5	1713.0	1670.9	1630.5	1605.8
15°	1877.6	1877.1	1878.2	1868.1	1855.5	1852.4	1821.9	1788.8	1729.4	1705.7	1664.8
17.5°	1854.3	1862.3	1866.0	1865.8	1865.5	1863.5	1853.8	1832.9	1803.1	1764.7	1717.4
20°	1798.8	1809.3	1810.8	1823.0	1829.8	1838.7	1842.4	1836.6	1818.2	1786.1	1745.2
22.5°	1713.0	1715.9	1720.9	1739.7	1754.5	1776.9	1788.6	1808.0	1800.9	1785.3	1751.0
25°	1564.3	1559.1	1577.5	1586.9	1621.1	1656.8	1682.6	1711.0	1736.2	1751.4	1741.5
27.5°	1385.8	1377.9	1405.5	1430.6	1458.3	1497.1	1537.2	1584.6	1624.1	1673.3	1690.3
30°	1235.2	1240.0	1266.3	1293.1	1335.1	1389.8	1435.0	1487.1	1543.3	1598.5	1636.9
32.5°	1072.9	1091.2	1107.8	1148.8	1185.9	1246.8	1313.0	1378.2	1448.3	1511.0	1570.4
35°	851.5	872.6	895.7	925.7	977.7	1038.2	1102.8	1190.6	1286.3	1372.0	1442.4
37.5°	716.8	713.4	726.7	748.3	790.4	839.2	913.7	1000.4	1113.0	1213.7	1313.0
40°	636.0	633.9	643.4	663.4	695.5	731.2	796.4	872.6	977.2	1100.2	1218.5
42.5°	580.5	581.8	587.0	601.1	623.1	652.5	701.3	766.2	862.0	977.8	1104.9
45°	513.0	516.7	522.5	529.3	541.9	566.1	593.4	639.7	715.4	812.1	937.2
47.5°	464.5	464.5	470.5	476.4	483.9	497.6	519.8	548.9	602.3	681.0	788.6
50°	438.4	434.7	438.9	443.6	451.5	461.0	475.7	503.0	538.8	602.4	692.3
52.5°	406.5	406.5	410.4	412.1	419.1	428.6	442.0	461.0	493.4	543.1	617.0
55°	360.6	363.2	365.4	368.4	374.8	381.6	392.1	404.7	430.0	467.3	522.0
57.5°	317.5	318.3	320.4	326.5	330.4	336.8	346.7	358.1	374.5	402.2	443.3
60°	288.0	288.0	292.2	294.9	300.2	306.4	314.3	325.3	340.1	362.7	395.9
62.5°	261.2	260.7	262.4	266.7	270.7	276.6	284.5	293.8	307.7	327.8	355.1
65°	221.8	220.8	223.9	225.0	229.2	235.0	241.3	251.3	262.3	277.0	301.2
67.5°	183.9	185.2	187.0	188.9	191.2	197.3	201.5	208.6	217.9	230.1	246.5
70°	163.0	163.0	163.0	164.5	167.7	170.9	175.1	180.9	189.7	200.3	215.0
72.5°	139.4	141.1	142.8	141.8	145.8	147.7	152.7	156.0	164.5	171.3	184.3
75°	109.3	109.3	109.3	111.9	113.5	115.1	118.3	121.4	125.6	134.0	140.9
77.5°	81.6	81.4	81.9	82.5	84.2	86.1	87.1	89.9	93.8	97.7	103.5
80°	63.1	64.2	64.6	65.7	65.7	66.8	67.3	71.0	73.6	76.2	79.9
82.5°	48.8	49.0	49.1	49.3	49.7	50.4	51.7	52.9	53.8	56.0	58.9
85°	28.4	27.9	27.9	28.9	28.4	28.4	29.5	30.5	30.5	31.0	32.6
87.5°	17.0	17.0	17.3	16.7	16.6	16.9	16.6	15.9	16.1	16.3	16.3
90°	30.4	29.9	29.4	28.9	28.4	27.6	26.3	25.0	23.8	22.5	20.5
92.5°	30.4	30.1	29.8	29.5	29.2	28.8	28.1	27.4	26.8	26.1	25.1
95°	48.5	48.7	49.0	49.2	49.4	49.0	47.7	46.4	45.2	44.0	42.2
97.5°	64.6	64.4	64.1	63.8	63.5	62.8	61.8	60.8	59.8	58.8	54.7
100°	75.5	75.0	74.5	74.0	73.5	72.2	70.3	68.2	66.2	64.2	60.0
102.5°	80.9	80.2	79.5	78.8	78.1	76.4	73.8	71.2	68.6	66.0	101.6
105°	85.6	84.6	83.7	82.6	81.6	79.8	77.0	74.2	71.5	68.8	137.0
107.5°	88.1	87.1	86.1	85.1	84.1	85.0	87.8	90.6	93.4	96.3	178.2
110°	89.0	88.0	87.0	86.0	85.0	97.0	122.1	147.1	172.1	197.2	269.5



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	89.9	89.1	88.3	87.5	86.7	132.0	223.3	314.7	406.0	497.3	515.2
115°	92.4	110.4	128.4	146.5	164.5	231.5	347.4	463.3	579.2	695.1	688.9
117.5°	377.2	436.4	495.7	554.9	614.2	657.8	685.9	713.9	742.0	770.0	765.6
120°	687.3	721.0	754.9	788.7	822.4	837.9	834.9	831.9	828.9	825.9	821.3
122.5°	857.6	864.2	870.8	877.3	883.8	886.2	884.5	882.6	880.8	879.0	874.1
125°	963.3	962.6	961.8	961.1	960.3	959.0	957.3	955.5	953.8	952.0	947.3
127.5°	1030.0	1029.8	1029.7	1029.5	1029.4	1028.0	1025.5	1022.9	1020.4	1017.9	1014.3
130°	1071.4	1071.7	1072.0	1072.2	1072.5	1071.2	1068.5	1065.7	1063.0	1060.2	1057.4
132.5°	1112.0	1112.3	1112.5	1112.8	1113.0	1112.0	1109.6	1107.2	1104.9	1102.6	1099.8
135°	1170.6	1171.1	1171.6	1172.1	1172.6	1171.6	1169.1	1166.6	1164.1	1161.6	1159.4
137.5°	1224.0	1224.9	1225.7	1226.5	1227.4	1226.6	1224.2	1221.7	1219.2	1216.8	1214.3
140°	1257.4	1258.6	1259.9	1261.2	1262.3	1261.9	1259.6	1257.4	1255.1	1252.8	1250.1
142.5°	1289.8	1291.1	1292.3	1293.6	1294.8	1294.4	1292.4	1290.3	1288.2	1286.2	1283.0
145°	1335.1	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3	1334.6	1332.8	1328.6
147.5°	1375.0	1376.0	1377.1	1378.2	1379.2	1379.1	1377.8	1376.5	1375.1	1373.9	1369.7
150°	1399.3	1400.6	1401.8	1403.1	1404.3	1404.2	1402.7	1401.2	1399.7	1398.2	1394.2
152.5°	1420.1	1421.7	1423.4	1425.0	1426.6	1426.7	1425.2	1423.7	1422.2	1420.7	1416.9
155°	1448.9	1450.9	1452.9	1454.9	1456.9	1457.1	1455.6	1454.1	1452.6	1451.1	1448.2
157.5°	1475.3	1477.2	1479.2	1481.1	1483.0	1483.2	1481.5	1479.8	1478.1	1476.4	1474.3
160°	1490.6	1492.3	1494.1	1495.9	1497.6	1497.7	1496.2	1494.7	1493.2	1491.7	1490.2
162.5°	1503.2	1505.4	1507.5	1509.7	1511.8	1512.0	1510.4	1508.6	1507.0	1505.2	1504.0
165°	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1	1521.4
167.5°	1534.1	1536.4	1538.6	1540.9	1543.1	1543.3	1541.6	1539.8	1538.1	1536.4	1535.6
170°	1541.3	1543.6	1545.8	1548.1	1550.3	1550.5	1548.8	1547.1	1545.3	1543.6	1543.0
172.5°	1546.7	1549.0	1551.2	1553.5	1555.7	1555.9	1554.2	1552.4	1550.7	1549.0	1548.5
175°	1551.4	1553.9	1556.4	1558.9	1561.5	1561.8	1560.0	1558.3	1556.6	1554.8	1554.3
177.5°	1554.3	1556.2	1558.0	1559.7	1561.5	1561.8	1560.4	1558.9	1557.6	1556.2	1555.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1403.5	1400.1	1398.0	1390.4	1383.7	1377.0	1374.9	1375.7	1366.5	1357.6	1353.8
5°	1458.2	1447.6	1437.7	1423.5	1406.7	1388.2	1378.8	1371.4	1353.0	1333.1	1321.5
7.5°	1507.1	1492.1	1472.9	1446.2	1421.7	1392.7	1374.4	1358.0	1331.2	1303.0	1285.7
10°	1537.0	1516.5	1491.8	1459.2	1429.3	1394.0	1369.3	1344.7	1313.0	1279.5	1258.4
12.5°	1562.7	1535.0	1510.7	1468.9	1433.5	1389.4	1360.1	1325.2	1292.0	1252.1	1231.5
15°	1623.7	1572.7	1526.5	1479.2	1435.5	1374.0	1341.5	1294.7	1251.0	1201.7	1178.0
17.5°	1671.0	1613.7	1540.8	1480.7	1429.7	1361.7	1313.8	1257.7	1206.2	1149.7	1117.5
20°	1697.9	1632.1	1553.8	1482.3	1421.3	1343.5	1291.5	1234.2	1173.8	1110.2	1075.5
22.5°	1713.8	1644.7	1567.3	1476.0	1404.5	1328.8	1263.4	1200.6	1139.3	1070.6	1034.3
25°	1718.9	1655.8	1573.8	1470.8	1383.5	1297.8	1219.0	1158.0	1083.9	1019.8	966.7
27.5°	1693.8	1648.6	1569.8	1460.9	1359.2	1259.0	1171.2	1102.1	1023.9	954.3	900.9
30°	1663.2	1636.9	1560.1	1450.8	1339.9	1232.2	1135.4	1057.1	979.3	908.9	854.2
32.5°	1615.7	1610.0	1542.5	1436.5	1319.3	1198.1	1098.0	1018.8	932.6	863.4	811.3
35°	1522.3	1547.5	1504.9	1404.5	1280.5	1149.6	1041.3	950.9	861.6	795.3	746.4
37.5°	1397.2	1459.8	1448.7	1357.7	1228.1	1096.9	977.3	882.8	797.6	730.8	682.8
40°	1311.0	1390.8	1402.4	1322.0	1191.1	1056.1	929.4	835.3	752.2	691.3	642.9
42.5°	1218.5	1311.8	1343.5	1279.1	1150.7	1013.1	886.5	789.0	706.8	647.5	604.6
45°	1063.4	1186.9	1244.2	1207.4	1083.4	942.5	812.1	713.3	638.7	583.0	549.9
47.5°	918.4	1053.4	1130.4	1117.5	1008.4	868.9	740.0	645.2	572.5	528.1	498.4
50°	815.8	954.6	1047.6	1051.9	954.6	816.3	687.1	597.7	530.9	489.4	465.2
52.5°	726.7	859.1	960.6	982.9	894.5	761.7	639.5	550.6	491.8	453.6	432.0
55°	610.3	722.2	834.7	875.8	804.8	678.6	565.6	487.3	432.1	405.8	386.9
57.5°	507.4	600.7	704.6	749.9	706.2	598.2	492.2	424.2	379.4	356.4	341.9
60°	453.1	526.7	619.2	673.4	635.5	539.3	446.8	382.1	345.4	324.9	311.2
62.5°	402.7	467.9	546.1	595.6	575.0	484.3	401.4	344.3	312.5	293.3	283.4
65°	332.2	383.7	444.2	489.9	476.3	407.3	339.6	290.7	265.5	250.2	242.3
67.5°	273.5	310.8	352.7	392.8	381.8	333.0	278.5	240.4	221.7	208.5	203.7
70°	236.5	264.9	302.2	334.3	325.3	285.4	242.3	209.8	193.5	182.4	177.7
72.5°	201.2	224.6	253.0	279.2	273.2	240.0	204.1	179.4	166.9	156.8	152.9
75°	151.9	169.8	187.1	204.5	202.9	177.1	156.1	137.2	127.2	119.3	117.7
77.5°	112.2	122.2	134.0	144.3	141.4	126.7	110.2	99.3	92.0	86.7	85.9
80°	85.7	91.5	99.9	107.3	103.5	97.3	84.1	76.2	71.0	65.7	63.6
82.5°	62.1	67.9	73.0	76.9	74.1	68.2	60.1	54.7	51.7	48.0	47.2
85°	32.6	35.7	37.9	38.9	37.9	34.1	30.5	28.4	25.7	24.2	23.7
87.5°	16.3	15.9	15.5	15.9	14.1	13.5	11.3	9.5	9.6	9.7	9.4
90°	18.5	16.6	14.5	12.1	9.4	6.7	3.9	1.1	3.9	6.7	9.4
92.5°	24.2	23.1	22.1	21.8	22.0	22.3	22.5	22.7	22.5	22.3	22.0
95°	40.4	38.7	36.9	40.2	48.5	56.7	65.0	73.2	65.0	56.7	48.5
97.5°	50.7	46.7	42.6	52.2	75.5	98.8	122.1	145.4	122.1	98.8	75.5
100°	55.7	51.4	47.2	62.2	96.5	130.8	165.1	199.4	165.1	130.8	96.5
102.5°	137.2	172.9	208.4	229.9	237.1	244.4	251.7	258.9	251.7	244.4	237.1
105°	205.4	273.8	342.1	372.6	365.0	357.5	350.0	342.5	350.0	357.5	365.0
107.5°	260.2	342.1	424.1	462.1	456.0	450.0	443.9	437.8	443.9	450.0	456.0
110°	341.9	414.2	486.6	520.1	514.9	509.6	504.4	499.2	504.4	509.6	514.9



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	533.1	551.0	568.8	575.4	570.8	566.1	561.4	556.8	561.4	566.1	570.8
115°	682.6	676.4	670.1	664.9	660.6	656.3	652.1	647.8	652.1	656.3	660.6
117.5°	761.4	757.0	752.7	748.2	743.5	738.7	734.0	729.2	734.0	738.7	743.5
120°	816.8	812.3	807.8	803.7	799.9	796.1	792.4	788.7	792.4	796.1	799.9
122.5°	869.2	864.3	859.4	855.0	851.0	847.1	843.1	839.2	843.1	847.1	851.0
125°	942.5	937.8	933.0	929.0	925.7	922.5	919.2	916.0	919.2	922.5	925.7
127.5°	1010.7	1007.2	1003.6	1000.1	996.4	992.8	989.2	985.6	989.2	992.8	996.4
130°	1054.7	1051.9	1049.2	1045.8	1041.8	1037.8	1033.8	1029.8	1033.8	1037.8	1041.8
132.5°	1097.0	1094.3	1091.5	1088.5	1085.1	1081.6	1078.2	1074.8	1078.2	1081.6	1085.1
135°	1157.1	1154.8	1152.5	1149.5	1145.4	1141.5	1137.4	1133.5	1137.4	1141.5	1145.4
137.5°	1211.7	1209.1	1206.6	1203.9	1201.1	1198.3	1195.5	1192.7	1195.5	1198.3	1201.1
140°	1247.4	1244.6	1241.8	1239.4	1237.5	1235.5	1233.4	1231.4	1233.4	1235.5	1237.5
142.5°	1279.9	1276.8	1273.6	1271.1	1269.3	1267.5	1265.7	1263.9	1265.7	1267.5	1269.3
145°	1324.4	1320.1	1315.8	1313.8	1314.1	1314.3	1314.5	1314.9	1314.5	1314.3	1314.1
147.5°	1365.5	1361.2	1357.0	1355.4	1356.4	1357.3	1358.3	1359.2	1358.3	1357.3	1356.4
150°	1390.2	1386.2	1382.2	1381.0	1382.8	1384.6	1386.3	1388.1	1386.3	1384.6	1382.8
152.5°	1413.1	1409.3	1405.5	1404.6	1406.5	1408.5	1410.5	1412.4	1410.5	1408.5	1406.5
155°	1445.2	1442.2	1439.2	1438.8	1441.0	1443.3	1445.5	1447.8	1445.5	1443.3	1441.0
157.5°	1472.2	1470.1	1468.0	1467.9	1469.8	1471.7	1473.6	1475.5	1473.6	1471.7	1469.8
160°	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1490.2	1488.7	1487.2
162.5°	1502.6	1501.3	1500.0	1500.2	1501.7	1503.2	1504.7	1506.1	1504.7	1503.2	1501.7
165°	1520.6	1519.9	1519.2	1519.5	1521.0	1522.5	1524.0	1525.5	1524.0	1522.5	1521.0
167.5°	1534.9	1534.2	1533.5	1533.9	1535.4	1536.9	1538.4	1539.9	1538.4	1536.9	1535.4
170°	1542.5	1542.1	1541.5	1542.1	1543.6	1545.1	1546.6	1548.1	1546.6	1545.1	1543.6
172.5°	1547.9	1547.4	1547.0	1547.4	1549.0	1550.5	1552.0	1553.5	1552.0	1550.5	1549.0
175°	1553.8	1553.3	1552.8	1553.5	1555.2	1557.0	1558.7	1560.4	1558.7	1557.0	1555.2
177.5°	1555.8	1555.5	1555.4	1555.9	1557.4	1558.8	1560.2	1561.5	1560.2	1558.8	1557.4
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1349.6	1347.1	1338.3	1333.7	1326.1	1319.0	1314.3	1316.4	1318.1	1317.2	1316.1
5°	1311.0	1301.0	1285.7	1272.6	1263.1	1245.8	1238.4	1234.8	1231.6	1227.9	1224.2
7.5°	1265.0	1249.2	1227.2	1208.6	1190.9	1169.3	1157.1	1149.7	1142.2	1133.9	1126.5
10°	1232.2	1210.1	1186.9	1160.6	1139.6	1120.1	1102.8	1091.2	1080.8	1070.7	1063.4
12.5°	1197.6	1172.2	1143.6	1107.6	1084.5	1056.7	1054.0	1033.6	1017.2	1011.1	1002.4
15°	1142.8	1107.0	1070.7	1028.2	1009.8	984.5	968.8	953.0	938.8	928.8	926.2
17.5°	1080.5	1034.2	998.1	967.5	937.3	911.5	897.0	884.4	872.7	859.4	857.5
20°	1032.9	992.9	953.5	926.7	895.7	869.4	851.5	838.9	828.9	821.1	814.2
22.5°	987.9	944.2	908.1	878.8	848.2	827.0	812.9	800.7	792.3	783.6	777.2
25°	915.7	881.5	842.1	809.0	783.7	770.1	758.5	748.0	742.8	737.0	729.6
27.5°	852.5	814.5	777.7	752.0	729.8	717.7	709.6	702.3	697.4	694.0	689.8
30°	807.9	769.5	740.6	715.4	697.0	684.9	679.7	675.5	669.7	667.6	665.5
32.5°	765.0	730.5	705.8	683.9	666.3	658.5	653.6	649.8	645.3	643.2	639.0
35°	704.4	675.5	651.3	639.2	625.0	618.1	614.5	609.3	605.0	602.9	602.4
37.5°	647.3	622.2	606.3	590.7	584.7	580.5	575.5	571.9	570.6	570.3	569.8
40°	610.3	589.8	575.6	563.0	560.3	554.1	549.9	546.7	546.7	547.2	546.7
42.5°	576.6	558.3	545.7	534.8	531.7	528.0	523.8	523.6	524.4	526.2	524.4
45°	525.6	512.5	503.6	498.3	492.5	488.9	488.3	489.9	490.4	491.0	492.5
47.5°	478.8	470.0	461.9	456.1	453.6	453.0	452.3	455.1	457.6	458.6	461.0
50°	451.0	441.0	434.2	430.5	428.4	427.4	428.4	431.6	433.6	436.3	437.8
52.5°	419.9	412.8	408.1	405.3	404.4	405.0	405.3	408.8	412.3	413.1	413.9
55°	376.9	371.6	370.6	365.8	368.0	367.4	370.0	372.2	375.3	378.5	379.0
57.5°	334.0	329.8	326.9	327.4	328.0	330.3	332.6	336.2	339.6	342.9	343.3
60°	305.4	303.3	301.7	301.7	302.8	305.9	308.6	312.2	314.3	316.5	318.0
62.5°	279.3	277.3	275.7	276.5	279.2	281.1	284.2	286.1	288.3	290.3	291.1
65°	238.1	237.1	238.7	239.7	240.2	242.9	246.5	248.1	250.2	251.3	254.9
67.5°	200.2	200.3	200.2	201.6	204.7	205.3	208.8	212.5	212.9	214.9	217.3
70°	174.5	175.5	176.7	177.7	180.3	181.3	183.9	185.5	187.7	189.3	190.8
72.5°	151.0	151.1	152.3	152.0	154.2	156.5	158.8	160.3	162.4	164.5	166.0
75°	116.1	116.1	117.2	117.7	120.4	123.0	122.5	123.5	125.6	127.7	128.8
77.5°	84.8	83.7	84.8	85.4	86.2	88.4	88.8	90.3	92.7	92.0	93.2
80°	64.6	63.1	64.6	65.2	65.2	67.8	67.8	68.8	70.4	68.8	70.4
82.5°	46.2	45.4	46.6	46.7	47.5	47.6	48.5	48.6	50.2	49.5	50.2
85°	23.1	22.6	23.1	22.6	23.1	23.7	23.7	23.1	23.1	24.2	22.6
87.5°	9.6	9.7	9.6	10.0	10.0	10.0	9.8	10.1	10.3	9.7	9.9
90°	12.1	14.5	16.6	18.5	20.5	22.5	23.8	25.0	26.3	27.6	28.4
92.5°	21.8	22.1	23.1	24.2	25.1	26.1	26.8	27.4	28.1	28.8	29.2
95°	40.2	36.9	38.7	40.4	42.2	44.0	45.2	46.4	47.7	49.0	49.4
97.5°	52.2	42.6	46.7	50.7	54.7	58.8	59.8	60.8	61.8	62.8	63.5
100°	62.2	47.2	51.4	55.7	60.0	64.2	66.2	68.2	70.3	72.2	73.5
102.5°	229.9	208.4	172.9	137.2	101.6	66.0	68.6	71.2	73.8	76.4	78.1
105°	372.6	342.1	273.8	205.4	137.0	68.8	71.5	74.2	77.0	79.8	81.6
107.5°	462.1	424.1	342.1	260.2	178.2	96.3	93.4	90.6	87.8	85.0	84.1
110°	520.1	486.6	414.2	341.9	269.5	197.2	172.1	147.1	122.1	97.0	85.0



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	575.4	568.8	551.0	533.1	515.2	497.3	406.0	314.7	223.3	132.0	86.7
115°	664.9	670.1	676.4	682.6	688.9	695.1	579.2	463.3	347.4	231.5	164.5
117.5°	748.2	752.7	757.0	761.4	765.6	770.0	742.0	713.9	685.9	657.8	614.2
120°	803.7	807.8	812.3	816.8	821.3	825.9	828.9	831.9	834.9	837.9	822.4
122.5°	855.0	859.4	864.3	869.2	874.1	879.0	880.8	882.6	884.5	886.2	883.8
125°	929.0	933.0	937.8	942.5	947.3	952.0	953.8	955.5	957.3	959.0	960.3
127.5°	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4	1022.9	1025.5	1028.0	1029.4
130°	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0	1065.7	1068.5	1071.2	1072.5
132.5°	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9	1107.2	1109.6	1112.0	1113.0
135°	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1	1166.6	1169.1	1171.6	1172.6
137.5°	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2	1221.7	1224.2	1226.6	1227.4
140°	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1	1257.4	1259.6	1261.9	1262.3
142.5°	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2	1290.3	1292.4	1294.4	1294.8
145°	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6	1336.3	1338.1	1339.9	1340.1
147.5°	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1	1376.5	1377.8	1379.1	1379.2
150°	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7	1401.2	1402.7	1404.2	1404.3
152.5°	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2	1423.7	1425.2	1426.7	1426.6
155°	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6	1454.1	1455.6	1457.1	1456.9
157.5°	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1	1479.8	1481.5	1483.2	1483.0
160°	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2	1494.7	1496.2	1497.7	1497.6
162.5°	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0	1508.6	1510.4	1512.0	1511.8
165°	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1
167.5°	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1	1539.8	1541.6	1543.3	1543.1
170°	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3	1547.1	1548.8	1550.5	1550.3
172.5°	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7	1552.4	1554.2	1555.9	1555.7
175°	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6	1558.3	1560.0	1561.8	1561.5
177.5°	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6	1558.9	1560.4	1561.8	1561.5
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1311.8	1311.0	1311.0	1307.2	1311.0	1311.0	1311.8	1316.1	1317.2	1318.1	1316.4
5°	1216.9	1215.3	1212.7	1215.3	1212.7	1215.3	1216.9	1224.2	1227.9	1231.6	1234.8
7.5°	1123.0	1116.7	1115.7	1109.5	1115.7	1116.7	1123.0	1126.5	1133.9	1142.2	1149.7
10°	1054.5	1050.3	1049.7	1039.7	1049.7	1050.3	1054.5	1063.4	1070.7	1080.8	1091.2
12.5°	1002.3	992.2	994.2	988.4	994.2	992.2	1002.3	1002.4	1011.1	1017.2	1033.6
15°	912.0	912.0	909.9	900.9	909.9	912.0	912.0	926.2	928.8	938.8	953.0
17.5°	847.2	846.1	841.1	843.6	841.1	846.1	847.2	857.5	859.4	872.7	884.4
20°	808.4	805.3	799.0	799.0	799.0	805.3	808.4	814.2	821.1	828.9	838.9
22.5°	771.9	771.7	764.9	767.0	764.9	771.7	771.9	777.2	783.6	792.3	800.7
25°	729.0	724.8	721.8	723.3	721.8	724.8	729.0	729.6	737.0	742.8	748.0
27.5°	688.5	686.2	686.0	681.7	686.0	686.2	688.5	689.8	694.0	697.4	702.3
30°	665.0	659.7	660.8	658.1	660.8	659.7	665.0	665.5	667.6	669.7	675.5
32.5°	638.0	636.1	635.1	632.9	635.1	636.1	638.0	639.0	643.2	645.3	649.8
35°	601.3	601.9	599.2	600.3	599.2	601.9	601.3	602.4	602.9	605.0	609.3
37.5°	569.3	570.9	569.7	570.1	569.7	570.9	569.3	569.8	570.3	570.6	571.9
40°	548.3	548.3	548.3	549.9	548.3	548.3	548.3	546.7	547.2	546.7	546.7
42.5°	528.1	527.2	526.4	526.2	526.4	527.2	528.1	524.4	526.2	524.4	523.6
45°	493.6	495.2	495.7	493.1	495.7	495.2	493.6	492.5	491.0	490.4	489.9
47.5°	462.4	462.6	462.4	464.7	462.4	462.6	462.4	461.0	458.6	457.6	455.1
50°	440.5	439.4	440.5	439.4	440.5	439.4	440.5	437.8	436.3	433.6	431.6
52.5°	417.4	417.6	416.9	416.8	416.9	417.6	417.4	413.9	413.1	412.3	408.8
55°	381.1	382.1	381.6	381.6	381.6	382.1	381.1	379.0	378.5	375.3	372.2
57.5°	343.6	344.5	345.2	342.9	345.2	344.5	343.6	343.3	342.9	339.6	336.2
60°	317.5	320.1	319.6	318.5	319.6	320.1	317.5	318.0	316.5	314.3	312.2
62.5°	293.5	294.5	294.4	294.1	294.4	294.5	293.5	291.1	290.3	288.3	286.1
65°	256.5	257.5	256.0	257.5	256.0	257.5	256.5	254.9	251.3	250.2	248.1
67.5°	216.7	217.0	218.2	218.9	218.2	217.0	216.7	217.3	214.9	212.9	212.5
70°	191.9	191.3	192.9	194.5	192.9	191.3	191.9	190.8	189.3	187.7	185.5
72.5°	165.8	166.9	166.4	167.5	166.4	166.9	165.8	166.0	164.5	162.4	160.3
75°	127.7	129.3	128.8	130.4	128.8	129.3	127.7	128.8	127.7	125.6	123.5
77.5°	92.3	92.5	92.3	93.2	92.3	92.5	92.3	93.2	92.0	92.7	90.3
80°	70.4	69.4	68.4	70.4	68.4	69.4	70.4	70.4	68.8	70.4	68.8
82.5°	49.0	49.6	48.6	48.6	48.6	49.6	49.0	50.2	49.5	50.2	48.6
85°	22.6	22.1	21.0	21.0	21.0	22.1	22.6	22.6	24.2	23.1	23.1
87.5°	10.0	9.7	9.7	9.4	9.7	9.7	10.0	9.9	9.7	10.3	10.1
90°	28.9	29.4	29.9	30.4	29.9	29.4	28.9	28.4	27.6	26.3	25.0
92.5°	29.5	29.8	30.1	30.4	30.1	29.8	29.5	29.2	28.8	28.1	27.4
95°	49.2	49.0	48.7	48.5	48.7	49.0	49.2	49.4	49.0	47.7	46.4
97.5°	63.8	64.1	64.4	64.6	64.4	64.1	63.8	63.5	62.8	61.8	60.8
100°	74.0	74.5	75.0	75.5	75.0	74.5	74.0	73.5	72.2	70.3	68.2
102.5°	78.8	79.5	80.2	80.9	80.2	79.5	78.8	78.1	76.4	73.8	71.2
105°	82.6	83.7	84.6	85.6	84.6	83.7	82.6	81.6	79.8	77.0	74.2
107.5°	85.1	86.1	87.1	88.1	87.1	86.1	85.1	84.1	85.0	87.8	90.6
110°	86.0	87.0	88.0	89.0	88.0	87.0	86.0	85.0	97.0	122.1	147.1



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	87.5	88.3	89.1	89.9	89.1	88.3	87.5	86.7	132.0	223.3	314.7
115°	146.5	128.4	110.4	92.4	110.4	128.4	146.5	164.5	231.5	347.4	463.3
117.5°	554.9	495.7	436.4	377.2	436.4	495.7	554.9	614.2	657.8	685.9	713.9
120°	788.7	754.9	721.0	687.3	721.0	754.9	788.7	822.4	837.9	834.9	831.9
122.5°	877.3	870.8	864.2	857.6	864.2	870.8	877.3	883.8	886.2	884.5	882.6
125°	961.1	961.8	962.6	963.3	962.6	961.8	961.1	960.3	959.0	957.3	955.5
127.5°	1029.5	1029.7	1029.8	1030.0	1029.8	1029.7	1029.5	1029.4	1028.0	1025.5	1022.9
130°	1072.2	1072.0	1071.7	1071.4	1071.7	1072.0	1072.2	1072.5	1071.2	1068.5	1065.7
132.5°	1112.8	1112.5	1112.3	1112.0	1112.3	1112.5	1112.8	1113.0	1112.0	1109.6	1107.2
135°	1172.1	1171.6	1171.1	1170.6	1171.1	1171.6	1172.1	1172.6	1171.6	1169.1	1166.6
137.5°	1226.5	1225.7	1224.9	1224.0	1224.9	1225.7	1226.5	1227.4	1226.6	1224.2	1221.7
140°	1261.2	1259.9	1258.6	1257.4	1258.6	1259.9	1261.2	1262.3	1261.9	1259.6	1257.4
142.5°	1293.6	1292.3	1291.1	1289.8	1291.1	1292.3	1293.6	1294.8	1294.4	1292.4	1290.3
145°	1338.9	1337.6	1336.3	1335.1	1336.3	1337.6	1338.9	1340.1	1339.9	1338.1	1336.3
147.5°	1378.2	1377.1	1376.0	1375.0	1376.0	1377.1	1378.2	1379.2	1379.1	1377.8	1376.5
150°	1403.1	1401.8	1400.6	1399.3	1400.6	1401.8	1403.1	1404.3	1404.2	1402.7	1401.2
152.5°	1425.0	1423.4	1421.7	1420.1	1421.7	1423.4	1425.0	1426.6	1426.7	1425.2	1423.7
155°	1454.9	1452.9	1450.9	1448.9	1450.9	1452.9	1454.9	1456.9	1457.1	1455.6	1454.1
157.5°	1481.1	1479.2	1477.2	1475.3	1477.2	1479.2	1481.1	1483.0	1483.2	1481.5	1479.8
160°	1495.9	1494.1	1492.3	1490.6	1492.3	1494.1	1495.9	1497.6	1497.7	1496.2	1494.7
162.5°	1509.7	1507.5	1505.4	1503.2	1505.4	1507.5	1509.7	1511.8	1512.0	1510.4	1508.6
165°	1527.4	1525.7	1523.9	1522.1	1523.9	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7
167.5°	1540.9	1538.6	1536.4	1534.1	1536.4	1538.6	1540.9	1543.1	1543.3	1541.6	1539.8
170°	1548.1	1545.8	1543.6	1541.3	1543.6	1545.8	1548.1	1550.3	1550.5	1548.8	1547.1
172.5°	1553.5	1551.2	1549.0	1546.7	1549.0	1551.2	1553.5	1555.7	1555.9	1554.2	1552.4
175°	1558.9	1556.4	1553.9	1551.4	1553.9	1556.4	1558.9	1561.5	1561.8	1560.0	1558.3
177.5°	1559.7	1558.0	1556.2	1554.3	1556.2	1558.0	1559.7	1561.5	1561.8	1560.4	1558.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1314.3	1319.0	1326.1	1333.7	1338.3	1347.1	1349.6	1353.8	1357.6	1366.5	1375.7
5°	1238.4	1245.8	1263.1	1272.6	1285.7	1301.0	1311.0	1321.5	1333.1	1353.0	1371.4
7.5°	1157.1	1169.3	1190.9	1208.6	1227.2	1249.2	1265.0	1285.7	1303.0	1331.2	1358.0
10°	1102.8	1120.1	1139.6	1160.6	1186.9	1210.1	1232.2	1258.4	1279.5	1313.0	1344.7
12.5°	1054.0	1056.7	1084.5	1107.6	1143.6	1172.2	1197.6	1231.5	1252.1	1292.0	1325.2
15°	968.8	984.5	1009.8	1028.2	1070.7	1107.0	1142.8	1178.0	1201.7	1251.0	1294.7
17.5°	897.0	911.5	937.3	967.5	998.1	1034.2	1080.5	1117.5	1149.7	1206.2	1257.7
20°	851.5	869.4	895.7	926.7	953.5	992.9	1032.9	1075.5	1110.2	1173.8	1234.2
22.5°	812.9	827.0	848.2	878.8	908.1	944.2	987.9	1034.3	1070.6	1139.3	1200.6
25°	758.5	770.1	783.7	809.0	842.1	881.5	915.7	966.7	1019.8	1083.9	1158.0
27.5°	709.6	717.7	729.8	752.0	777.7	814.5	852.5	900.9	954.3	1023.9	1102.1
30°	679.7	684.9	697.0	715.4	740.6	769.5	807.9	854.2	908.9	979.3	1057.1
32.5°	653.6	658.5	666.3	683.9	705.8	730.5	765.0	811.3	863.4	932.6	1018.8
35°	614.5	618.1	625.0	639.2	651.3	675.5	704.4	746.4	795.3	861.6	950.9
37.5°	575.5	580.5	584.7	590.7	606.3	622.2	647.3	682.8	730.8	797.6	882.8
40°	549.9	554.1	560.3	563.0	575.6	589.8	610.3	642.9	691.3	752.2	835.3
42.5°	523.8	528.0	531.7	534.8	545.7	558.3	576.6	604.6	647.5	706.8	789.0
45°	488.3	488.9	492.5	498.3	503.6	512.5	525.6	549.9	583.0	638.7	713.3
47.5°	452.3	453.0	453.6	456.1	461.9	470.0	478.8	498.4	528.1	572.5	645.2
50°	428.4	427.4	428.4	430.5	434.2	441.0	451.0	465.2	489.4	530.9	597.7
52.5°	405.3	405.0	404.4	405.3	408.1	412.8	419.9	432.0	453.6	491.8	550.6
55°	370.0	367.4	368.0	365.8	370.6	371.6	376.9	386.9	405.8	432.1	487.3
57.5°	332.6	330.3	328.0	327.4	326.9	329.8	334.0	341.9	356.4	379.4	424.2
60°	308.6	305.9	302.8	301.7	301.7	303.3	305.4	311.2	324.9	345.4	382.1
62.5°	284.2	281.1	279.2	276.5	275.7	277.3	279.3	283.4	293.3	312.5	344.3
65°	246.5	242.9	240.2	239.7	238.7	237.1	238.1	242.3	250.2	265.5	290.7
67.5°	208.8	205.3	204.7	201.6	200.2	200.3	200.2	203.7	208.5	221.7	240.4
70°	183.9	181.3	180.3	177.7	176.7	175.5	174.5	177.7	182.4	193.5	209.8
72.5°	158.8	156.5	154.2	152.0	152.3	151.1	151.0	152.9	156.8	166.9	179.4
75°	122.5	123.0	120.4	117.7	117.2	116.1	116.1	117.7	119.3	127.2	137.2
77.5°	88.8	88.4	86.2	85.4	84.8	83.7	84.8	85.9	86.7	92.0	99.3
80°	67.8	67.8	65.2	65.2	64.6	63.1	64.6	63.6	65.7	71.0	76.2
82.5°	48.5	47.6	47.5	46.7	46.6	45.4	46.2	47.2	48.0	51.7	54.7
85°	23.7	23.7	23.1	22.6	23.1	22.6	23.1	23.7	24.2	25.7	28.4
87.5°	9.8	10.0	10.0	10.0	9.6	9.7	9.6	9.4	9.7	9.6	9.5
90°	23.8	22.5	20.5	18.5	16.6	14.5	12.1	9.4	6.7	3.9	1.1
92.5°	26.8	26.1	25.1	24.2	23.1	22.1	21.8	22.0	22.3	22.5	22.7
95°	45.2	44.0	42.2	40.4	38.7	36.9	40.2	48.5	56.7	65.0	73.2
97.5°	59.8	58.8	54.7	50.7	46.7	42.6	52.2	75.5	98.8	122.1	145.4
100°	66.2	64.2	60.0	55.7	51.4	47.2	62.2	96.5	130.8	165.1	199.4
102.5°	68.6	66.0	101.6	137.2	172.9	208.4	229.9	237.1	244.4	251.7	258.9
105°	71.5	68.8	137.0	205.4	273.8	342.1	372.6	365.0	357.5	350.0	342.5
107.5°	93.4	96.3	178.2	260.2	342.1	424.1	462.1	456.0	450.0	443.9	437.8
110°	172.1	197.2	269.5	341.9	414.2	486.6	520.1	514.9	509.6	504.4	499.2



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	406.0	497.3	515.2	533.1	551.0	568.8	575.4	570.8	566.1	561.4	556.8
115°	579.2	695.1	688.9	682.6	676.4	670.1	664.9	660.6	656.3	652.1	647.8
117.5°	742.0	770.0	765.6	761.4	757.0	752.7	748.2	743.5	738.7	734.0	729.2
120°	828.9	825.9	821.3	816.8	812.3	807.8	803.7	799.9	796.1	792.4	788.7
122.5°	880.8	879.0	874.1	869.2	864.3	859.4	855.0	851.0	847.1	843.1	839.2
125°	953.8	952.0	947.3	942.5	937.8	933.0	929.0	925.7	922.5	919.2	916.0
127.5°	1020.4	1017.9	1014.3	1010.7	1007.2	1003.6	1000.1	996.4	992.8	989.2	985.6
130°	1063.0	1060.2	1057.4	1054.7	1051.9	1049.2	1045.8	1041.8	1037.8	1033.8	1029.8
132.5°	1104.9	1102.6	1099.8	1097.0	1094.3	1091.5	1088.5	1085.1	1081.6	1078.2	1074.8
135°	1164.1	1161.6	1159.4	1157.1	1154.8	1152.5	1149.5	1145.4	1141.5	1137.4	1133.5
137.5°	1219.2	1216.8	1214.3	1211.7	1209.1	1206.6	1203.9	1201.1	1198.3	1195.5	1192.7
140°	1255.1	1252.8	1250.1	1247.4	1244.6	1241.8	1239.4	1237.5	1235.5	1233.4	1231.4
142.5°	1288.2	1286.2	1283.0	1279.9	1276.8	1273.6	1271.1	1269.3	1267.5	1265.7	1263.9
145°	1334.6	1332.8	1328.6	1324.4	1320.1	1315.8	1313.8	1314.1	1314.3	1314.5	1314.9
147.5°	1375.1	1373.9	1369.7	1365.5	1361.2	1357.0	1355.4	1356.4	1357.3	1358.3	1359.2
150°	1399.7	1398.2	1394.2	1390.2	1386.2	1382.2	1381.0	1382.8	1384.6	1386.3	1388.1
152.5°	1422.2	1420.7	1416.9	1413.1	1409.3	1405.5	1404.6	1406.5	1408.5	1410.5	1412.4
155°	1452.6	1451.1	1448.2	1445.2	1442.2	1439.2	1438.8	1441.0	1443.3	1445.5	1447.8
157.5°	1478.1	1476.4	1474.3	1472.2	1470.1	1468.0	1467.9	1469.8	1471.7	1473.6	1475.5
160°	1493.2	1491.7	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7
162.5°	1507.0	1505.2	1504.0	1502.6	1501.3	1500.0	1500.2	1501.7	1503.2	1504.7	1506.1
165°	1523.9	1522.1	1521.4	1520.6	1519.9	1519.2	1519.5	1521.0	1522.5	1524.0	1525.5
167.5°	1538.1	1536.4	1535.6	1534.9	1534.2	1533.5	1533.9	1535.4	1536.9	1538.4	1539.9
170°	1545.3	1543.6	1543.0	1542.5	1542.1	1541.5	1542.1	1543.6	1545.1	1546.6	1548.1
172.5°	1550.7	1549.0	1548.5	1547.9	1547.4	1547.0	1547.4	1549.0	1550.5	1552.0	1553.5
175°	1556.6	1554.8	1554.3	1553.8	1553.3	1552.8	1553.5	1555.2	1557.0	1558.7	1560.4
177.5°	1557.6	1556.2	1555.9	1555.8	1555.5	1555.4	1555.9	1557.4	1558.8	1560.2	1561.5
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1374.9	1377.0	1383.7	1390.4	1398.0	1400.1	1403.5	1400.6	1399.7	1407.7	1413.6
5°	1378.8	1388.2	1406.7	1423.5	1437.7	1447.6	1458.2	1462.4	1470.2	1481.3	1494.9
7.5°	1374.4	1392.7	1421.7	1446.2	1472.9	1492.1	1507.1	1520.0	1535.6	1556.5	1579.3
10°	1369.3	1394.0	1429.3	1459.2	1491.8	1516.5	1537.0	1557.0	1580.1	1609.0	1638.9
12.5°	1360.1	1389.4	1433.5	1468.9	1510.7	1535.0	1562.7	1605.8	1630.5	1670.9	1713.0
15°	1341.5	1374.0	1435.5	1479.2	1526.5	1572.7	1623.7	1664.8	1705.7	1729.4	1788.8
17.5°	1313.8	1361.7	1429.7	1480.7	1540.8	1613.7	1671.0	1717.4	1764.7	1803.1	1832.9
20°	1291.5	1343.5	1421.3	1482.3	1553.8	1632.1	1697.9	1745.2	1786.1	1818.2	1836.6
22.5°	1263.4	1328.8	1404.5	1476.0	1567.3	1644.7	1713.8	1751.0	1785.3	1800.9	1808.0
25°	1219.0	1297.8	1383.5	1470.8	1573.8	1655.8	1718.9	1741.5	1751.4	1736.2	1711.0
27.5°	1171.2	1259.0	1359.2	1460.9	1569.8	1648.6	1693.8	1690.3	1673.3	1624.1	1584.6
30°	1135.4	1232.2	1339.9	1450.8	1560.1	1636.9	1663.2	1636.9	1598.5	1543.3	1487.1
32.5°	1098.0	1198.1	1319.3	1436.5	1542.5	1610.0	1615.7	1570.4	1511.0	1448.3	1378.2
35°	1041.3	1149.6	1280.5	1404.5	1504.9	1547.5	1522.3	1442.4	1372.0	1286.3	1190.6
37.5°	977.3	1096.9	1228.1	1357.7	1448.7	1459.8	1397.2	1313.0	1213.7	1113.0	1000.4
40°	929.4	1056.1	1191.1	1322.0	1402.4	1390.8	1311.0	1218.5	1100.2	977.2	872.6
42.5°	886.5	1013.1	1150.7	1279.1	1343.5	1311.8	1218.5	1104.9	977.8	862.0	766.2
45°	812.1	942.5	1083.4	1207.4	1244.2	1186.9	1063.4	937.2	812.1	715.4	639.7
47.5°	740.0	868.9	1008.4	1117.5	1130.4	1053.4	918.4	788.6	681.0	602.3	548.9
50°	687.1	816.3	954.6	1051.9	1047.6	954.6	815.8	692.3	602.4	538.8	503.0
52.5°	639.5	761.7	894.5	982.9	960.6	859.1	726.7	617.0	543.1	493.4	461.0
55°	565.6	678.6	804.8	875.8	834.7	722.2	610.3	522.0	467.3	430.0	404.7
57.5°	492.2	598.2	706.2	749.9	704.6	600.7	507.4	443.3	402.2	374.5	358.1
60°	446.8	539.3	635.5	673.4	619.2	526.7	453.1	395.9	362.7	340.1	325.3
62.5°	401.4	484.3	575.0	595.6	546.1	467.9	402.7	355.1	327.8	307.7	293.8
65°	339.6	407.3	476.3	489.9	444.2	383.7	332.2	301.2	277.0	262.3	251.3
67.5°	278.5	333.0	381.8	392.8	352.7	310.8	273.5	246.5	230.1	217.9	208.6
70°	242.3	285.4	325.3	334.3	302.2	264.9	236.5	215.0	200.3	189.7	180.9
72.5°	204.1	240.0	273.2	279.2	253.0	224.6	201.2	184.3	171.3	164.5	156.0
75°	156.1	177.1	202.9	204.5	187.1	169.8	151.9	140.9	134.0	125.6	121.4
77.5°	110.2	126.7	141.4	144.3	134.0	122.2	112.2	103.5	97.7	93.8	89.9
80°	84.1	97.3	103.5	107.3	99.9	91.5	85.7	79.9	76.2	73.6	71.0
82.5°	60.1	68.2	74.1	76.9	73.0	67.9	62.1	58.9	56.0	53.8	52.9
85°	30.5	34.1	37.9	38.9	37.9	35.7	32.6	32.6	31.0	30.5	30.5
87.5°	11.3	13.5	14.1	15.9	15.5	15.9	16.3	16.3	16.3	16.1	15.9
90°	3.9	6.7	9.4	12.1	14.5	16.6	18.5	20.5	22.5	23.8	25.0
92.5°	22.5	22.3	22.0	21.8	22.1	23.1	24.2	25.1	26.1	26.8	27.4
95°	65.0	56.7	48.5	40.2	36.9	38.7	40.4	42.2	44.0	45.2	46.4
97.5°	122.1	98.8	75.5	52.2	42.6	46.7	50.7	54.7	58.8	59.8	60.8
100°	165.1	130.8	96.5	62.2	47.2	51.4	55.7	60.0	64.2	66.2	68.2
102.5°	251.7	244.4	237.1	229.9	208.4	172.9	137.2	101.6	66.0	68.6	71.2
105°	350.0	357.5	365.0	372.6	342.1	273.8	205.4	137.0	68.8	71.5	74.2
107.5°	443.9	450.0	456.0	462.1	424.1	342.1	260.2	178.2	96.3	93.4	90.6
110°	504.4	509.6	514.9	520.1	486.6	414.2	341.9	269.5	197.2	172.1	147.1



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	561.4	566.1	570.8	575.4	568.8	551.0	533.1	515.2	497.3	406.0	314.7
115°	652.1	656.3	660.6	664.9	670.1	676.4	682.6	688.9	695.1	579.2	463.3
117.5°	734.0	738.7	743.5	748.2	752.7	757.0	761.4	765.6	770.0	742.0	713.9
120°	792.4	796.1	799.9	803.7	807.8	812.3	816.8	821.3	825.9	828.9	831.9
122.5°	843.1	847.1	851.0	855.0	859.4	864.3	869.2	874.1	879.0	880.8	882.6
125°	919.2	922.5	925.7	929.0	933.0	937.8	942.5	947.3	952.0	953.8	955.5
127.5°	989.2	992.8	996.4	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4	1022.9
130°	1033.8	1037.8	1041.8	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0	1065.7
132.5°	1078.2	1081.6	1085.1	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9	1107.2
135°	1137.4	1141.5	1145.4	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1	1166.6
137.5°	1195.5	1198.3	1201.1	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2	1221.7
140°	1233.4	1235.5	1237.5	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1	1257.4
142.5°	1265.7	1267.5	1269.3	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2	1290.3
145°	1314.5	1314.3	1314.1	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6	1336.3
147.5°	1358.3	1357.3	1356.4	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1	1376.5
150°	1386.3	1384.6	1382.8	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7	1401.2
152.5°	1410.5	1408.5	1406.5	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2	1423.7
155°	1445.5	1443.3	1441.0	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6	1454.1
157.5°	1473.6	1471.7	1469.8	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1	1479.8
160°	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2	1494.7
162.5°	1504.7	1503.2	1501.7	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0	1508.6
165°	1524.0	1522.5	1521.0	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9	1525.7
167.5°	1538.4	1536.9	1535.4	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1	1539.8
170°	1546.6	1545.1	1543.6	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3	1547.1
172.5°	1552.0	1550.5	1549.0	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7	1552.4
175°	1558.7	1557.0	1555.2	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6	1558.3
177.5°	1560.2	1558.8	1557.4	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6	1558.9
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1418.6	1424.5	1424.5	1425.4	1432.1	1431.2	1430.8
5°	1509.7	1518.6	1519.6	1529.1	1535.4	1533.3	1527.6
7.5°	1595.5	1612.2	1624.8	1631.8	1640.1	1645.3	1643.0
10°	1663.7	1687.8	1702.6	1712.5	1724.7	1733.6	1730.4
12.5°	1725.5	1754.3	1774.5	1791.6	1793.2	1804.7	1796.9
15°	1821.9	1852.4	1855.5	1868.1	1878.2	1877.1	1877.6
17.5°	1853.8	1863.5	1865.5	1865.8	1866.0	1862.3	1854.3
20°	1842.4	1838.7	1829.8	1823.0	1810.8	1809.3	1798.8
22.5°	1788.6	1776.9	1754.5	1739.7	1720.9	1715.9	1713.0
25°	1682.6	1656.8	1621.1	1586.9	1577.5	1559.1	1564.3
27.5°	1537.2	1497.1	1458.3	1430.6	1405.5	1377.9	1385.8
30°	1435.0	1389.8	1335.1	1293.1	1266.3	1240.0	1235.2
32.5°	1313.0	1246.8	1185.9	1148.8	1107.8	1091.2	1072.9
35°	1102.8	1038.2	977.7	925.7	895.7	872.6	851.5
37.5°	913.7	839.2	790.4	748.3	726.7	713.4	716.8
40°	796.4	731.2	695.5	663.4	643.4	633.9	636.0
42.5°	701.3	652.5	623.1	601.1	587.0	581.8	580.5
45°	593.4	566.1	541.9	529.3	522.5	516.7	513.0
47.5°	519.8	497.6	483.9	476.4	470.5	464.5	464.5
50°	475.7	461.0	451.5	443.6	438.9	434.7	438.4
52.5°	442.0	428.6	419.1	412.1	410.4	406.5	406.5
55°	392.1	381.6	374.8	368.4	365.4	363.2	360.6
57.5°	346.7	336.8	330.4	326.5	320.4	318.3	317.5
60°	314.3	306.4	300.2	294.9	292.2	288.0	288.0
62.5°	284.5	276.6	270.7	266.7	262.4	260.7	261.2
65°	241.3	235.0	229.2	225.0	223.9	220.8	221.8
67.5°	201.5	197.3	191.2	188.9	187.0	185.2	183.9
70°	175.1	170.9	167.7	164.5	163.0	163.0	163.0
72.5°	152.7	147.7	145.8	141.8	142.8	141.1	139.4
75°	118.3	115.1	113.5	111.9	109.3	109.3	109.3
77.5°	87.1	86.1	84.2	82.5	81.9	81.4	81.6
80°	67.3	66.8	65.7	65.7	64.6	64.2	63.1
82.5°	51.7	50.4	49.7	49.3	49.1	49.0	48.8
85°	29.5	28.4	28.4	28.9	27.9	27.9	28.4
87.5°	16.6	16.9	16.6	16.7	17.3	17.0	17.0
90°	26.3	27.6	28.4	28.9	29.4	29.9	30.4
92.5°	28.1	28.8	29.2	29.5	29.8	30.1	30.4
95°	47.7	49.0	49.4	49.2	49.0	48.7	48.5
97.5°	61.8	62.8	63.5	63.8	64.1	64.4	64.6
100°	70.3	72.2	73.5	74.0	74.5	75.0	75.5
102.5°	73.8	76.4	78.1	78.8	79.5	80.2	80.9
105°	77.0	79.8	81.6	82.6	83.7	84.6	85.6
107.5°	87.8	85.0	84.1	85.1	86.1	87.1	88.1
110°	122.1	97.0	85.0	86.0	87.0	88.0	89.0



TEST NUMBER: P331579-927

CATALOG NUMBER: S122DIW-S865D1440U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	223.3	132.0	86.7	87.5	88.3	89.1	89.9
115°	347.4	231.5	164.5	146.5	128.4	110.4	92.4
117.5°	685.9	657.8	614.2	554.9	495.7	436.4	377.2
120°	834.9	837.9	822.4	788.7	754.9	721.0	687.3
122.5°	884.5	886.2	883.8	877.3	870.8	864.2	857.6
125°	957.3	959.0	960.3	961.1	961.8	962.6	963.3
127.5°	1025.5	1028.0	1029.4	1029.5	1029.7	1029.8	1030.0
130°	1068.5	1071.2	1072.5	1072.2	1072.0	1071.7	1071.4
132.5°	1109.6	1112.0	1113.0	1112.8	1112.5	1112.3	1112.0
135°	1169.1	1171.6	1172.6	1172.1	1171.6	1171.1	1170.6
137.5°	1224.2	1226.6	1227.4	1226.5	1225.7	1224.9	1224.0
140°	1259.6	1261.9	1262.3	1261.2	1259.9	1258.6	1257.4
142.5°	1292.4	1294.4	1294.8	1293.6	1292.3	1291.1	1289.8
145°	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1335.1
147.5°	1377.8	1379.1	1379.2	1378.2	1377.1	1376.0	1375.0
150°	1402.7	1404.2	1404.3	1403.1	1401.8	1400.6	1399.3
152.5°	1425.2	1426.7	1426.6	1425.0	1423.4	1421.7	1420.1
155°	1455.6	1457.1	1456.9	1454.9	1452.9	1450.9	1448.9
157.5°	1481.5	1483.2	1483.0	1481.1	1479.2	1477.2	1475.3
160°	1496.2	1497.7	1497.6	1495.9	1494.1	1492.3	1490.6
162.5°	1510.4	1512.0	1511.8	1509.7	1507.5	1505.4	1503.2
165°	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1
167.5°	1541.6	1543.3	1543.1	1540.9	1538.6	1536.4	1534.1
170°	1548.8	1550.5	1550.3	1548.1	1545.8	1543.6	1541.3
172.5°	1554.2	1555.9	1555.7	1553.5	1551.2	1549.0	1546.7
175°	1560.0	1561.8	1561.5	1558.9	1556.4	1553.9	1551.4
177.5°	1560.4	1561.8	1561.5	1559.7	1558.0	1556.2	1554.3
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0

(END OF REPORT)