

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331857-927

Luminaire Tested: **S122RDIW-S1005D1240U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331857-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1240U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6947.3 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	82	73	66	60	74	67	61	56	56	52	48	46	43	41	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	42	38	35	33	31	29	25
5	69	58	51	45	63	54	47	42	45	40	37	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	38	33	38	33	29	32	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	35	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28208	28208	28208	28208
5°	31504	28386	25167	28386
10°	34954	28186	21815	28186
15°	36672	27773	17188	27773
20°	31792	27161	14874	27161
25°	20851	26323	13279	26323
30°	14033	25307	12020	25307
35°	11367	24025	10841	24025
40°	10108	22634	10030	22634
45°	9149	21000	8953	21000
50°	8324	19381	8297	19381
55°	7828	17582	7724	17582
60°	6546	15936	6468	15936
65°	5521	14472	6262	14472
70°	5103	12925	5906	12925
75°	4772	11248	5452	11248
80°	4407	9261	4854	9261
85°	4057	7317	4279	7317



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.6	2.4
10°-20°	461.5	6.6
20°-30°	594.7	8.6
30°-40°	565.1	8.1
40°-50°	484.1	7.0
50°-60°	368.7	5.3
60°-70°	233.1	3.4
70°-80°	116.4	1.7
80°-90°	33.6	0.5
90°-100°	44.7	0.6
100°-110°	163.8	2.4
110°-120°	437.9	6.3
120°-130°	722.9	10.4
130°-140°	768.8	11.1
140°-150°	714.5	10.3
150°-160°	574.5	8.3
160°-170°	370.2	5.3
170°-180°	127.4	1.8
0°-30°	1221.8	17.6
0°-40°	1786.9	25.7
0°-60°	2639.7	38.0
0°-90°	3022.7	43.5
90°-120°	646.4	9.3
90°-150°	2852.5	41.1
90°-180°	3925.0	56.5
0°-180°	6947.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1747	1747	1747	1747	1747	
5°	1944	1751	1553	1751	1944	192
15°	2194	1662	1028	1662	2194	592
25°	1170	1478	745	1478	1170	555
35°	577	1219	550	1219	577	369
45°	401	920	392	920	401	310
55°	278	625	274	625	278	244
65°	144	379	164	379	144	147
75°	76	180	87	180	76	81
85°	22	40	23	40	22	24
90°	26	1	26	1	26	13
95°	42	63	42	63	42	39
105°	74	295	74	295	74	77
115°	80	557	80	557	80	199
125°	828	788	828	788	828	717
135°	1007	975	1007	975	1007	776
145°	1148	1131	1148	1131	1148	718
155°	1246	1245	1246	1245	1246	575
165°	1309	1312	1309	1312	1309	370
175°	1334	1342	1334	1342	1334	127
180°	1339	1339	1339	1339	1339	



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1818.0	1819.5	1820.9	1817.5	1817.5	1814.6	1808.3	1803.4	1789.9	1787.9	1787.9
5°	1943.8	1942.6	1945.0	1937.1	1926.2	1923.7	1912.2	1897.0	1881.3	1863.7	1860.0
7.5°	2068.9	2067.0	2062.1	2060.9	2052.5	2034.1	2015.5	1995.7	1969.5	1943.9	1931.0
10°	2132.0	2152.0	2139.8	2118.6	2122.9	2094.4	2079.2	2053.1	2031.2	1993.0	1984.5
12.5°	2194.1	2202.0	2198.1	2186.1	2180.6	2160.8	2140.3	2117.7	2077.3	2043.0	2013.1
15°	2193.9	2205.4	2208.4	2204.8	2207.9	2206.6	2195.7	2176.9	2141.7	2104.0	2071.2
17.5°	2031.9	2039.9	2059.8	2073.3	2090.3	2126.3	2144.0	2150.9	2145.7	2124.2	2101.1
20°	1850.3	1836.9	1892.8	1921.4	1945.6	2006.3	2058.5	2078.5	2110.7	2110.1	2104.0
22.5°	1592.9	1596.1	1649.0	1682.9	1753.8	1814.5	1874.0	1949.4	2011.7	2052.8	2076.9
25°	1170.4	1193.5	1246.3	1292.4	1371.3	1484.2	1586.8	1705.8	1818.1	1906.8	1991.2
27.5°	879.0	880.7	922.6	965.2	1012.1	1104.6	1233.7	1375.9	1536.0	1668.1	1820.0
30°	752.7	749.1	766.7	792.8	832.9	904.5	1001.6	1141.3	1300.9	1500.0	1677.3
32.5°	663.4	663.6	676.8	696.2	729.4	777.8	844.3	957.7	1108.6	1304.3	1512.2
35°	576.7	576.1	585.8	599.8	613.7	644.7	690.2	749.7	853.5	1036.3	1248.7
37.5°	514.5	517.2	522.0	530.7	546.1	563.3	590.7	630.6	704.6	812.6	991.2
40°	479.6	480.8	487.4	494.7	503.8	517.2	539.6	571.9	625.9	712.1	842.6
42.5°	447.5	448.8	453.4	460.3	467.5	480.8	499.4	527.2	571.0	638.3	745.9
45°	400.7	400.7	404.9	408.0	415.8	427.9	443.1	466.2	496.5	546.4	618.0
47.5°	356.7	356.8	359.7	364.9	369.8	379.3	394.2	413.0	435.1	473.6	534.8
50°	331.4	332.1	333.9	338.1	341.2	349.7	361.2	377.6	400.7	430.4	481.4
52.5°	311.1	310.7	313.0	314.8	316.9	323.0	331.6	346.0	366.6	392.5	434.7
55°	278.1	275.6	279.2	282.3	284.1	286.5	291.4	300.5	318.1	339.9	371.5
57.5°	236.8	235.8	238.4	241.1	246.8	253.4	257.5	263.3	272.4	288.1	319.4
60°	202.7	202.7	208.2	210.0	216.7	225.2	233.7	238.6	247.7	258.0	281.1
62.5°	172.6	173.2	175.7	177.5	181.3	191.7	203.6	214.3	222.9	232.7	248.0
65°	144.5	145.7	145.7	146.9	149.3	151.8	156.6	165.1	180.3	194.2	205.8
67.5°	122.6	123.0	123.3	124.5	125.2	127.9	129.8	133.6	137.0	150.3	164.6
70°	108.1	109.9	109.2	110.5	111.1	112.3	114.7	116.5	122.0	125.1	133.6
72.5°	94.4	95.8	95.7	96.4	98.0	98.2	100.1	102.0	105.5	108.1	112.6
75°	76.5	75.9	76.5	77.7	78.3	78.9	78.9	81.4	83.2	85.6	88.6
77.5°	59.0	59.7	59.5	59.7	59.7	60.8	60.7	61.8	63.6	64.8	66.3
80°	47.4	47.9	47.4	47.9	48.6	49.2	48.6	49.2	51.0	52.2	52.2
82.5°	36.7	36.8	37.2	37.3	37.4	37.5	38.3	38.5	39.8	39.6	40.1
85°	21.9	21.2	21.2	21.2	21.9	22.5	21.9	21.9	22.5	22.5	22.5
87.5°	13.0	13.4	13.3	13.2	13.2	13.0	12.8	13.1	12.4	12.6	11.8
90°	26.1	25.7	25.3	24.9	24.5	23.7	22.6	21.5	20.4	19.4	17.7
92.5°	26.1	25.9	25.7	25.3	25.1	24.7	24.2	23.6	23.1	22.5	21.6
95°	41.7	41.9	42.1	42.3	42.5	42.1	41.0	39.9	38.9	37.8	36.3
97.5°	55.6	55.4	55.1	54.8	54.6	54.0	53.2	52.3	51.4	50.6	47.1
100°	65.0	64.5	64.1	63.6	63.2	62.1	60.4	58.7	57.0	55.2	51.6
102.5°	69.6	69.0	68.4	67.7	67.2	65.8	63.5	61.2	59.0	56.8	87.4
105°	73.7	72.8	71.9	71.1	70.2	68.6	66.2	63.8	61.5	59.1	117.9
107.5°	75.8	74.9	74.1	73.2	72.3	73.1	75.5	78.0	80.3	82.8	153.3
110°	76.5	75.7	74.9	74.0	73.1	83.4	105.0	126.5	148.1	169.6	231.8



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	77.3	76.6	76.0	75.3	74.5	113.5	192.1	270.6	349.2	427.7	443.1
115°	79.5	95.0	110.5	126.0	141.5	199.1	298.8	398.5	498.2	597.9	592.6
117.5°	324.4	375.4	426.4	477.3	528.2	565.8	589.9	614.0	638.1	662.3	658.5
120°	591.1	620.2	649.3	678.3	707.4	720.6	718.0	715.5	712.9	710.3	706.5
122.5°	737.6	743.3	748.9	754.6	760.2	762.2	760.7	759.1	757.6	756.1	751.9
125°	828.5	827.9	827.3	826.6	825.9	824.9	823.4	821.9	820.4	818.9	814.8
127.5°	885.9	885.7	885.7	885.5	885.4	884.2	882.0	879.8	877.7	875.4	872.4
130°	921.5	921.8	922.0	922.2	922.4	921.3	919.0	916.6	914.3	911.9	909.5
132.5°	956.5	956.6	956.9	957.1	957.3	956.4	954.3	952.4	950.3	948.3	945.9
135°	1006.9	1007.3	1007.7	1008.1	1008.5	1007.7	1005.5	1003.4	1001.2	999.1	997.1
137.5°	1052.7	1053.5	1054.2	1054.9	1055.7	1055.0	1052.9	1050.8	1048.7	1046.6	1044.3
140°	1081.5	1082.5	1083.6	1084.7	1085.8	1085.4	1083.4	1081.5	1079.5	1077.6	1075.2
142.5°	1109.4	1110.4	1111.5	1112.6	1113.6	1113.3	1111.6	1109.8	1108.0	1106.3	1103.5
145°	1148.3	1149.4	1150.5	1151.5	1152.6	1152.4	1150.9	1149.4	1147.9	1146.4	1142.7
147.5°	1182.6	1183.5	1184.4	1185.3	1186.2	1186.1	1185.0	1183.9	1182.8	1181.6	1178.1
150°	1203.6	1204.6	1205.7	1206.8	1207.8	1207.8	1206.5	1205.1	1203.9	1202.6	1199.1
152.5°	1221.4	1222.8	1224.2	1225.7	1227.1	1227.2	1225.8	1224.6	1223.3	1221.9	1218.7
155°	1246.2	1247.9	1249.7	1251.3	1253.1	1253.3	1252.0	1250.7	1249.4	1248.2	1245.5
157.5°	1268.8	1270.6	1272.2	1273.9	1275.6	1275.7	1274.2	1272.8	1271.3	1269.9	1268.0
160°	1282.1	1283.6	1285.1	1286.6	1288.1	1288.2	1286.9	1285.6	1284.3	1283.0	1281.8
162.5°	1292.9	1294.7	1296.6	1298.5	1300.3	1300.5	1299.0	1297.6	1296.1	1294.7	1293.6
165°	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2	1308.5
167.5°	1319.5	1321.4	1323.3	1325.2	1327.2	1327.4	1325.9	1324.4	1322.9	1321.4	1320.8
170°	1325.6	1327.6	1329.5	1331.5	1333.4	1333.6	1332.1	1330.6	1329.1	1327.6	1327.1
172.5°	1330.3	1332.2	1334.2	1336.1	1338.1	1338.2	1336.7	1335.2	1333.7	1332.2	1331.8
175°	1334.4	1336.5	1338.7	1340.8	1343.0	1343.3	1341.8	1340.3	1338.8	1337.3	1336.9
177.5°	1336.9	1338.5	1340.0	1341.6	1343.1	1343.3	1342.0	1340.8	1339.7	1338.5	1338.2
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1788.9	1784.9	1781.6	1772.8	1768.5	1758.7	1757.3	1756.8	1744.2	1732.0	1728.6
5°	1850.3	1840.6	1826.1	1809.0	1791.4	1773.2	1761.1	1751.4	1727.0	1704.0	1690.7
7.5°	1912.2	1891.3	1866.2	1834.1	1807.2	1777.1	1754.8	1734.7	1700.3	1667.2	1645.0
10°	1958.4	1924.4	1890.9	1846.7	1812.0	1778.1	1746.5	1719.2	1680.3	1636.6	1605.7
12.5°	1987.0	1949.6	1903.6	1860.3	1815.4	1772.3	1730.0	1694.9	1649.2	1604.1	1567.3
15°	2025.8	1985.7	1929.8	1867.9	1810.2	1753.8	1705.3	1661.5	1602.0	1548.0	1503.1
17.5°	2057.5	2002.3	1942.4	1870.7	1804.0	1732.2	1669.7	1613.8	1547.6	1482.4	1429.5
20°	2067.6	2013.0	1943.8	1872.2	1793.3	1708.9	1641.5	1580.8	1509.7	1438.7	1378.0
22.5°	2061.3	2018.8	1941.9	1856.2	1775.3	1687.0	1610.9	1540.5	1461.7	1389.2	1318.7
25°	2018.5	2003.9	1931.0	1837.5	1745.3	1642.7	1554.7	1477.6	1387.7	1310.0	1233.5
27.5°	1918.5	1950.0	1904.8	1805.2	1702.6	1592.7	1493.7	1406.0	1312.7	1225.3	1149.1
30°	1822.4	1894.6	1875.2	1782.9	1668.2	1560.1	1449.1	1357.4	1257.8	1168.0	1092.7
32.5°	1690.8	1810.1	1829.1	1751.8	1633.2	1514.5	1398.0	1306.9	1202.9	1108.3	1034.9
35°	1481.2	1659.7	1741.6	1692.5	1573.5	1445.4	1325.2	1218.9	1114.5	1021.0	948.2
37.5°	1231.2	1474.3	1610.9	1614.4	1505.1	1372.0	1241.0	1135.6	1028.7	936.9	858.2
40°	1069.1	1332.5	1510.4	1549.8	1457.5	1313.7	1181.3	1073.9	969.5	879.6	789.2
42.5°	923.4	1185.8	1404.5	1473.1	1399.8	1256.9	1124.0	1011.7	910.2	825.2	732.8
45°	746.7	976.1	1217.1	1339.7	1299.1	1166.7	1026.5	919.7	824.3	750.9	662.3
47.5°	629.9	791.6	1024.8	1190.6	1189.9	1069.1	931.2	828.9	740.5	671.6	599.9
50°	563.3	704.2	901.5	1089.6	1105.4	1004.1	872.9	771.6	689.0	616.8	559.1
52.5°	503.6	619.6	797.1	977.5	1022.4	934.6	807.4	713.8	633.7	567.2	517.8
55°	425.6	515.4	650.1	818.9	886.9	825.0	712.1	624.6	559.7	503.8	461.4
57.5°	360.0	427.4	535.5	671.4	750.6	711.6	618.5	547.5	491.9	441.3	407.8
60°	318.7	373.9	465.6	579.2	666.5	639.2	559.7	493.5	446.2	402.5	370.9
62.5°	279.9	327.3	405.9	498.0	578.1	566.9	501.9	446.4	404.9	365.1	338.3
65°	225.2	259.8	321.2	393.4	457.7	463.2	416.5	378.8	341.7	310.2	286.5
67.5°	179.4	201.9	245.1	305.9	354.2	371.4	342.9	314.1	284.7	260.3	239.8
70°	151.1	169.4	200.9	250.1	294.5	312.6	296.3	273.8	248.3	228.2	210.6
72.5°	122.5	140.2	163.5	199.6	237.6	257.3	251.6	235.4	214.8	198.1	181.5
75°	92.3	97.8	113.5	137.8	167.5	184.6	188.8	180.3	163.9	151.1	141.4
77.5°	68.2	71.5	79.1	91.8	111.2	126.4	132.6	131.6	120.3	112.9	103.8
80°	54.7	56.5	60.1	65.6	80.2	95.3	99.6	99.6	91.7	88.6	79.5
82.5°	41.5	42.9	45.1	48.1	54.9	68.1	72.9	73.8	68.8	64.8	57.7
85°	23.7	23.1	24.3	26.1	27.3	31.0	38.3	39.5	38.3	33.4	31.5
87.5°	11.4	11.6	11.2	10.4	10.4	10.4	12.4	14.3	12.8	11.8	11.3
90°	15.9	14.2	12.5	10.5	8.1	5.7	3.3	1.0	3.3	5.7	8.1
92.5°	20.8	19.9	19.0	18.7	18.9	19.2	19.3	19.6	19.3	19.2	18.9
95°	34.8	33.3	31.8	34.5	41.7	48.8	55.8	63.0	55.8	48.8	41.7
97.5°	43.6	40.1	36.6	44.9	65.0	84.9	105.0	125.0	105.0	84.9	65.0
100°	47.9	44.3	40.6	53.6	83.0	112.5	142.0	171.5	142.0	112.5	83.0
102.5°	118.0	148.6	179.3	197.7	204.0	210.2	216.4	222.7	216.4	210.2	204.0
105°	176.7	235.5	294.3	320.4	313.9	307.5	301.0	294.6	301.0	307.5	313.9
107.5°	223.8	294.3	364.8	397.4	392.2	387.0	381.8	376.6	381.8	387.0	392.2
110°	294.1	356.3	418.5	447.3	442.8	438.3	433.8	429.3	433.8	438.3	442.8



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	458.5	473.9	489.3	495.0	490.9	486.9	482.9	478.9	482.9	486.9	490.9
115°	587.2	581.8	576.4	571.9	568.2	564.5	560.9	557.2	560.9	564.5	568.2
117.5°	654.8	651.1	647.5	643.6	639.4	635.3	631.3	627.2	631.3	635.3	639.4
120°	702.6	698.7	694.8	691.3	688.0	684.8	681.6	678.3	681.6	684.8	688.0
122.5°	747.6	743.4	739.2	735.4	732.0	728.6	725.2	721.8	725.2	728.6	732.0
125°	810.6	806.6	802.5	799.0	796.2	793.4	790.6	787.8	790.6	793.4	796.2
127.5°	869.3	866.3	863.2	860.2	857.1	853.9	850.8	847.7	850.8	853.9	857.1
130°	907.1	904.8	902.4	899.5	896.0	892.6	889.1	885.7	889.1	892.6	896.0
132.5°	943.6	941.2	938.8	936.2	933.3	930.3	927.4	924.5	927.4	930.3	933.3
135°	995.2	993.2	991.3	988.6	985.2	981.8	978.3	974.9	978.3	981.8	985.2
137.5°	1042.2	1040.0	1037.8	1035.5	1033.1	1030.6	1028.3	1025.8	1028.3	1030.6	1033.1
140°	1072.9	1070.5	1068.1	1066.0	1064.3	1062.6	1060.9	1059.1	1060.9	1062.6	1064.3
142.5°	1100.8	1098.1	1095.4	1093.3	1091.7	1090.2	1088.6	1087.1	1088.6	1090.2	1091.7
145°	1139.1	1135.4	1131.7	1130.0	1130.2	1130.4	1130.7	1130.8	1130.7	1130.4	1130.2
147.5°	1174.4	1170.8	1167.2	1165.8	1166.6	1167.4	1168.2	1169.0	1168.2	1167.4	1166.6
150°	1195.7	1192.2	1188.8	1187.8	1189.3	1190.9	1192.4	1193.9	1192.4	1190.9	1189.3
152.5°	1215.4	1212.1	1208.9	1208.1	1209.7	1211.4	1213.1	1214.8	1213.1	1211.4	1209.7
155°	1242.9	1240.4	1237.8	1237.5	1239.4	1241.3	1243.3	1245.2	1243.3	1241.3	1239.4
157.5°	1266.2	1264.4	1262.6	1262.5	1264.2	1265.7	1267.4	1269.1	1267.4	1265.7	1264.2
160°	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1281.8	1280.4	1279.1
162.5°	1292.4	1291.3	1290.1	1290.2	1291.6	1292.8	1294.1	1295.5	1294.1	1292.8	1291.6
165°	1307.9	1307.3	1306.6	1306.9	1308.2	1309.5	1310.8	1312.1	1310.8	1309.5	1308.2
167.5°	1320.2	1319.6	1319.0	1319.3	1320.6	1321.9	1323.2	1324.5	1323.2	1321.9	1320.6
170°	1326.7	1326.3	1325.9	1326.3	1327.6	1328.9	1330.2	1331.5	1330.2	1328.9	1327.6
172.5°	1331.3	1330.9	1330.5	1330.9	1332.2	1333.6	1334.8	1336.1	1334.8	1333.6	1332.2
175°	1336.4	1336.0	1335.5	1336.1	1337.6	1339.1	1340.6	1342.1	1340.6	1339.1	1337.6
177.5°	1338.1	1337.9	1337.8	1338.2	1339.5	1340.7	1341.9	1343.1	1341.9	1340.7	1339.5
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1722.4	1719.0	1712.6	1702.9	1697.1	1686.9	1680.1	1683.9	1685.0	1683.9	1683.0
5°	1676.1	1663.3	1645.8	1628.7	1613.0	1595.9	1586.3	1582.0	1573.5	1568.6	1566.2
7.5°	1620.1	1598.1	1573.3	1543.6	1518.5	1492.2	1478.7	1472.0	1454.6	1445.2	1436.9
10°	1578.3	1543.7	1518.9	1480.0	1456.3	1421.7	1398.0	1398.7	1375.0	1361.6	1351.9
12.5°	1532.2	1494.2	1452.8	1417.8	1385.0	1357.2	1328.6	1317.1	1292.0	1279.1	1252.8
15°	1455.7	1411.4	1367.7	1320.3	1287.0	1243.9	1202.6	1152.2	1111.5	1076.3	1066.6
17.5°	1372.2	1317.3	1273.5	1217.9	1160.7	1088.2	1040.4	1011.1	986.6	968.0	954.2
20°	1314.9	1259.0	1212.3	1128.5	1051.4	1002.3	967.0	944.6	919.1	899.0	888.1
22.5°	1254.7	1196.4	1132.7	1039.2	979.1	939.6	908.2	882.4	865.1	849.5	839.6
25°	1169.2	1105.4	1000.4	936.0	887.5	846.2	824.3	808.6	790.4	769.1	759.5
27.5°	1078.9	977.5	902.1	854.2	807.9	781.0	761.4	737.8	721.5	711.9	701.9
30°	1011.4	910.0	851.1	798.9	766.1	736.3	713.3	700.0	684.1	667.7	661.1
32.5°	936.0	855.1	798.7	755.2	721.9	696.6	678.3	656.7	645.3	635.3	621.2
35°	842.6	781.3	729.7	694.5	662.9	642.3	621.0	608.2	587.6	579.2	573.7
37.5°	763.4	710.3	671.8	634.6	609.6	586.8	573.8	553.5	544.5	532.7	521.3
40°	718.7	666.5	629.5	599.1	571.2	554.2	537.8	521.5	508.1	502.6	488.7
42.5°	673.1	630.6	593.6	560.3	541.6	523.6	502.9	490.8	477.1	468.2	459.5
45°	610.1	572.4	540.9	513.6	492.9	474.1	460.7	440.7	432.8	415.3	408.0
47.5°	554.8	519.8	489.6	463.7	443.5	431.3	411.7	396.0	383.4	372.6	363.3
50°	515.4	486.2	457.1	434.0	415.8	398.2	378.2	370.3	350.9	345.4	339.9
52.5°	479.4	451.8	425.1	402.5	384.3	367.2	349.5	339.2	326.1	320.7	316.6
55°	429.2	402.5	377.0	357.0	338.7	321.2	310.2	297.5	291.4	287.2	282.3
57.5°	378.7	354.7	335.1	314.8	296.5	282.5	269.9	262.2	256.0	250.3	244.5
60°	346.7	323.5	305.9	287.2	268.3	256.7	247.1	238.0	230.7	222.2	219.8
62.5°	312.6	292.5	276.3	258.0	241.6	231.1	221.8	213.2	204.5	192.1	188.7
65°	265.9	250.1	233.1	217.9	203.4	193.1	179.7	170.0	166.4	165.1	164.5
67.5°	223.6	208.7	194.2	178.6	165.3	155.7	149.0	147.5	145.0	144.3	142.5
70°	195.5	181.5	166.9	152.3	139.7	137.8	135.4	132.9	129.9	128.7	127.5
72.5°	170.2	155.7	141.2	129.5	124.1	121.8	119.4	116.9	114.9	113.7	112.9
75°	130.6	117.2	107.4	103.2	100.1	98.3	94.7	92.8	91.7	89.8	89.2
77.5°	94.0	86.4	82.0	79.3	76.1	74.1	72.1	70.3	69.0	68.6	67.7
80°	71.6	68.0	65.0	61.3	60.1	57.7	57.0	55.2	55.8	54.0	54.0
82.5°	55.6	51.0	48.5	46.7	45.6	43.6	43.0	42.1	42.2	40.9	40.9
85°	28.5	27.3	26.1	24.9	24.9	23.1	23.7	23.1	23.1	21.9	21.2
87.5°	11.3	11.2	10.6	10.9	11.3	11.2	11.4	11.1	11.3	11.6	11.2
90°	10.5	12.5	14.2	15.9	17.7	19.4	20.4	21.5	22.6	23.7	24.5
92.5°	18.7	19.0	19.9	20.8	21.6	22.5	23.1	23.6	24.2	24.7	25.1
95°	34.5	31.8	33.3	34.8	36.3	37.8	38.9	39.9	41.0	42.1	42.5
97.5°	44.9	36.6	40.1	43.6	47.1	50.6	51.4	52.3	53.2	54.0	54.6
100°	53.6	40.6	44.3	47.9	51.6	55.2	57.0	58.7	60.4	62.1	63.2
102.5°	197.7	179.3	148.6	118.0	87.4	56.8	59.0	61.2	63.5	65.8	67.2
105°	320.4	294.3	235.5	176.7	117.9	59.1	61.5	63.8	66.2	68.6	70.2
107.5°	397.4	364.8	294.3	223.8	153.3	82.8	80.3	78.0	75.5	73.1	72.3
110°	447.3	418.5	356.3	294.1	231.8	169.6	148.1	126.5	105.0	83.4	73.1



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	495.0	489.3	473.9	458.5	443.1	427.7	349.2	270.6	192.1	113.5	74.5
115°	571.9	576.4	581.8	587.2	592.6	597.9	498.2	398.5	298.8	199.1	141.5
117.5°	643.6	647.5	651.1	654.8	658.5	662.3	638.1	614.0	589.9	565.8	528.2
120°	691.3	694.8	698.7	702.6	706.5	710.3	712.9	715.5	718.0	720.6	707.4
122.5°	735.4	739.2	743.4	747.6	751.9	756.1	757.6	759.1	760.7	762.2	760.2
125°	799.0	802.5	806.6	810.6	814.8	818.9	820.4	821.9	823.4	824.9	825.9
127.5°	860.2	863.2	866.3	869.3	872.4	875.4	877.7	879.8	882.0	884.2	885.4
130°	899.5	902.4	904.8	907.1	909.5	911.9	914.3	916.6	919.0	921.3	922.4
132.5°	936.2	938.8	941.2	943.6	945.9	948.3	950.3	952.4	954.3	956.4	957.3
135°	988.6	991.3	993.2	995.2	997.1	999.1	1001.2	1003.4	1005.5	1007.7	1008.5
137.5°	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7	1050.8	1052.9	1055.0	1055.7
140°	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5	1081.5	1083.4	1085.4	1085.8
142.5°	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0	1109.8	1111.6	1113.3	1113.6
145°	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9	1149.4	1150.9	1152.4	1152.6
147.5°	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8	1183.9	1185.0	1186.1	1186.2
150°	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9	1205.1	1206.5	1207.8	1207.8
152.5°	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3	1224.6	1225.8	1227.2	1227.1
155°	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4	1250.7	1252.0	1253.3	1253.1
157.5°	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3	1272.8	1274.2	1275.7	1275.6
160°	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3	1285.6	1286.9	1288.2	1288.1
162.5°	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1	1297.6	1299.0	1300.5	1300.3
165°	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2
167.5°	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9	1324.4	1325.9	1327.4	1327.2
170°	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1	1330.6	1332.1	1333.6	1333.4
172.5°	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7	1335.2	1336.7	1338.2	1338.1
175°	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8	1340.3	1341.8	1343.3	1343.0
177.5°	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7	1340.8	1342.0	1343.3	1343.1
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1677.7	1678.6	1677.2	1678.2	1677.2	1678.6	1677.7	1683.0	1683.9	1685.0	1683.9
5°	1563.1	1555.8	1554.7	1552.8	1554.7	1555.8	1563.1	1566.2	1568.6	1573.5	1582.0
7.5°	1426.5	1425.4	1422.4	1418.1	1422.4	1425.4	1426.5	1436.9	1445.2	1454.6	1472.0
10°	1338.6	1335.5	1334.9	1330.6	1334.9	1335.5	1338.6	1351.9	1361.6	1375.0	1398.7
12.5°	1235.6	1216.1	1214.0	1203.4	1214.0	1216.1	1235.6	1252.8	1279.1	1292.0	1317.1
15°	1052.0	1048.4	1036.3	1028.3	1036.3	1048.4	1052.0	1066.6	1076.3	1111.5	1152.2
17.5°	947.1	935.3	931.4	929.8	931.4	935.3	947.1	954.2	968.0	986.6	1011.1
20°	879.6	868.7	866.9	865.7	866.9	868.7	879.6	888.1	899.0	919.1	944.6
22.5°	833.0	821.6	816.8	813.2	816.8	821.6	833.0	839.6	849.5	865.1	882.4
25°	753.4	749.1	746.7	745.4	746.7	749.1	753.4	759.5	769.1	790.4	808.6
27.5°	691.1	681.8	679.9	676.8	679.9	681.8	691.1	701.9	711.9	721.5	737.8
30°	655.6	652.6	648.3	644.7	648.3	652.6	655.6	661.1	667.7	684.1	700.0
32.5°	613.9	611.3	607.5	605.9	607.5	611.3	613.9	621.2	635.3	645.3	656.7
35°	567.6	559.1	555.5	550.0	555.5	559.1	567.6	573.7	579.2	587.6	608.2
37.5°	518.6	514.2	509.1	510.9	509.1	514.2	518.6	521.3	532.7	544.5	553.5
40°	480.8	477.8	476.6	475.9	476.6	477.8	480.8	488.7	502.6	508.1	521.5
42.5°	450.7	442.3	439.1	439.0	439.1	442.3	450.7	459.5	468.2	477.1	490.8
45°	404.9	397.0	391.6	392.1	391.6	397.0	404.9	408.0	415.3	432.8	440.7
47.5°	358.1	357.8	354.4	355.5	354.4	357.8	358.1	363.3	372.6	383.4	396.0
50°	335.7	332.1	329.6	330.3	329.6	332.1	335.7	339.9	345.4	350.9	370.3
52.5°	314.3	311.2	309.3	311.8	309.3	311.2	314.3	316.6	320.7	326.1	339.2
55°	279.2	275.6	275.0	274.4	275.0	275.6	279.2	282.3	287.2	291.4	297.5
57.5°	240.0	237.6	233.9	232.3	233.9	237.6	240.0	244.5	250.3	256.0	262.2
60°	211.8	207.0	200.9	200.3	200.9	207.0	211.8	219.8	222.2	230.7	238.0
62.5°	186.1	185.1	183.9	183.8	183.9	185.1	186.1	188.7	192.1	204.5	213.2
65°	163.3	162.7	163.3	163.9	163.3	162.7	163.3	164.5	165.1	166.4	170.0
67.5°	142.3	141.2	140.1	140.6	140.1	141.2	142.3	142.5	144.3	145.0	147.5
70°	126.3	125.6	125.1	125.1	125.1	125.6	126.3	127.5	128.7	129.9	132.9
72.5°	110.7	110.6	110.0	109.5	110.0	110.6	110.7	112.9	113.7	114.9	116.9
75°	88.6	87.4	87.4	87.4	87.4	87.4	88.6	89.2	89.8	91.7	92.8
77.5°	67.5	66.9	66.3	65.8	66.3	66.9	67.5	67.7	68.6	69.0	70.3
80°	53.4	52.8	52.2	52.2	52.2	52.8	53.4	54.0	54.0	55.8	55.2
82.5°	40.8	40.2	40.1	39.6	40.1	40.2	40.8	40.9	40.9	42.2	42.1
85°	21.9	22.5	21.9	23.1	21.9	22.5	21.9	21.2	21.9	23.1	23.1
87.5°	11.2	10.9	11.5	11.1	11.5	10.9	11.2	11.2	11.6	11.3	11.1
90°	24.9	25.3	25.7	26.1	25.7	25.3	24.9	24.5	23.7	22.6	21.5
92.5°	25.3	25.7	25.9	26.1	25.9	25.7	25.3	25.1	24.7	24.2	23.6
95°	42.3	42.1	41.9	41.7	41.9	42.1	42.3	42.5	42.1	41.0	39.9
97.5°	54.8	55.1	55.4	55.6	55.4	55.1	54.8	54.6	54.0	53.2	52.3
100°	63.6	64.1	64.5	65.0	64.5	64.1	63.6	63.2	62.1	60.4	58.7
102.5°	67.7	68.4	69.0	69.6	69.0	68.4	67.7	67.2	65.8	63.5	61.2
105°	71.1	71.9	72.8	73.7	72.8	71.9	71.1	70.2	68.6	66.2	63.8
107.5°	73.2	74.1	74.9	75.8	74.9	74.1	73.2	72.3	73.1	75.5	78.0
110°	74.0	74.9	75.7	76.5	75.7	74.9	74.0	73.1	83.4	105.0	126.5



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	75.3	76.0	76.6	77.3	76.6	76.0	75.3	74.5	113.5	192.1	270.6
115°	126.0	110.5	95.0	79.5	95.0	110.5	126.0	141.5	199.1	298.8	398.5
117.5°	477.3	426.4	375.4	324.4	375.4	426.4	477.3	528.2	565.8	589.9	614.0
120°	678.3	649.3	620.2	591.1	620.2	649.3	678.3	707.4	720.6	718.0	715.5
122.5°	754.6	748.9	743.3	737.6	743.3	748.9	754.6	760.2	762.2	760.7	759.1
125°	826.6	827.3	827.9	828.5	827.9	827.3	826.6	825.9	824.9	823.4	821.9
127.5°	885.5	885.7	885.7	885.9	885.7	885.7	885.5	885.4	884.2	882.0	879.8
130°	922.2	922.0	921.8	921.5	921.8	922.0	922.2	922.4	921.3	919.0	916.6
132.5°	957.1	956.9	956.6	956.5	956.6	956.9	957.1	957.3	956.4	954.3	952.4
135°	1008.1	1007.7	1007.3	1006.9	1007.3	1007.7	1008.1	1008.5	1007.7	1005.5	1003.4
137.5°	1054.9	1054.2	1053.5	1052.7	1053.5	1054.2	1054.9	1055.7	1055.0	1052.9	1050.8
140°	1084.7	1083.6	1082.5	1081.5	1082.5	1083.6	1084.7	1085.8	1085.4	1083.4	1081.5
142.5°	1112.6	1111.5	1110.4	1109.4	1110.4	1111.5	1112.6	1113.6	1113.3	1111.6	1109.8
145°	1151.5	1150.5	1149.4	1148.3	1149.4	1150.5	1151.5	1152.6	1152.4	1150.9	1149.4
147.5°	1185.3	1184.4	1183.5	1182.6	1183.5	1184.4	1185.3	1186.2	1186.1	1185.0	1183.9
150°	1206.8	1205.7	1204.6	1203.6	1204.6	1205.7	1206.8	1207.8	1207.8	1206.5	1205.1
152.5°	1225.7	1224.2	1222.8	1221.4	1222.8	1224.2	1225.7	1227.1	1227.2	1225.8	1224.6
155°	1251.3	1249.7	1247.9	1246.2	1247.9	1249.7	1251.3	1253.1	1253.3	1252.0	1250.7
157.5°	1273.9	1272.2	1270.6	1268.8	1270.6	1272.2	1273.9	1275.6	1275.7	1274.2	1272.8
160°	1286.6	1285.1	1283.6	1282.1	1283.6	1285.1	1286.6	1288.1	1288.2	1286.9	1285.6
162.5°	1298.5	1296.6	1294.7	1292.9	1294.7	1296.6	1298.5	1300.3	1300.5	1299.0	1297.6
165°	1313.7	1312.2	1310.7	1309.2	1310.7	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2
167.5°	1325.2	1323.3	1321.4	1319.5	1321.4	1323.3	1325.2	1327.2	1327.4	1325.9	1324.4
170°	1331.5	1329.5	1327.6	1325.6	1327.6	1329.5	1331.5	1333.4	1333.6	1332.1	1330.6
172.5°	1336.1	1334.2	1332.2	1330.3	1332.2	1334.2	1336.1	1338.1	1338.2	1336.7	1335.2
175°	1340.8	1338.7	1336.5	1334.4	1336.5	1338.7	1340.8	1343.0	1343.3	1341.8	1340.3
177.5°	1341.6	1340.0	1338.5	1336.9	1338.5	1340.0	1341.6	1343.1	1343.3	1342.0	1340.8
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1680.1	1686.9	1697.1	1702.9	1712.6	1719.0	1722.4	1728.6	1732.0	1744.2	1756.8
5°	1586.3	1595.9	1613.0	1628.7	1645.8	1663.3	1676.1	1690.7	1704.0	1727.0	1751.4
7.5°	1478.7	1492.2	1518.5	1543.6	1573.3	1598.1	1620.1	1645.0	1667.2	1700.3	1734.7
10°	1398.0	1421.7	1456.3	1480.0	1518.9	1543.7	1578.3	1605.7	1636.6	1680.3	1719.2
12.5°	1328.6	1357.2	1385.0	1417.8	1452.8	1494.2	1532.2	1567.3	1604.1	1649.2	1694.9
15°	1202.6	1243.9	1287.0	1320.3	1367.7	1411.4	1455.7	1503.1	1548.0	1602.0	1661.5
17.5°	1040.4	1088.2	1160.7	1217.9	1273.5	1317.3	1372.2	1429.5	1482.4	1547.6	1613.8
20°	967.0	1002.3	1051.4	1128.5	1212.3	1259.0	1314.9	1378.0	1438.7	1509.7	1580.8
22.5°	908.2	939.6	979.1	1039.2	1132.7	1196.4	1254.7	1318.7	1389.2	1461.7	1540.5
25°	824.3	846.2	887.5	936.0	1000.4	1105.4	1169.2	1233.5	1310.0	1387.7	1477.6
27.5°	761.4	781.0	807.9	854.2	902.1	977.5	1078.9	1149.1	1225.3	1312.7	1406.0
30°	713.3	736.3	766.1	798.9	851.1	910.0	1011.4	1092.7	1168.0	1257.8	1357.4
32.5°	678.3	696.6	721.9	755.2	798.7	855.1	936.0	1034.9	1108.3	1202.9	1306.9
35°	621.0	642.3	662.9	694.5	729.7	781.3	842.6	948.2	1021.0	1114.5	1218.9
37.5°	573.8	586.8	609.6	634.6	671.8	710.3	763.4	858.2	936.9	1028.7	1135.6
40°	537.8	554.2	571.2	599.1	629.5	666.5	718.7	789.2	879.6	969.5	1073.9
42.5°	502.9	523.6	541.6	560.3	593.6	630.6	673.1	732.8	825.2	910.2	1011.7
45°	460.7	474.1	492.9	513.6	540.9	572.4	610.1	662.3	750.9	824.3	919.7
47.5°	411.7	431.3	443.5	463.7	489.6	519.8	554.8	599.9	671.6	740.5	828.9
50°	378.2	398.2	415.8	434.0	457.1	486.2	515.4	559.1	616.8	689.0	771.6
52.5°	349.5	367.2	384.3	402.5	425.1	451.8	479.4	517.8	567.2	633.7	713.8
55°	310.2	321.2	338.7	357.0	377.0	402.5	429.2	461.4	503.8	559.7	624.6
57.5°	269.9	282.5	296.5	314.8	335.1	354.7	378.7	407.8	441.3	491.9	547.5
60°	247.1	256.7	268.3	287.2	305.9	323.5	346.7	370.9	402.5	446.2	493.5
62.5°	221.8	231.1	241.6	258.0	276.3	292.5	312.6	338.3	365.1	404.9	446.4
65°	179.7	193.1	203.4	217.9	233.1	250.1	265.9	286.5	310.2	341.7	378.8
67.5°	149.0	155.7	165.3	178.6	194.2	208.7	223.6	239.8	260.3	284.7	314.1
70°	135.4	137.8	139.7	152.3	166.9	181.5	195.5	210.6	228.2	248.3	273.8
72.5°	119.4	121.8	124.1	129.5	141.2	155.7	170.2	181.5	198.1	214.8	235.4
75°	94.7	98.3	100.1	103.2	107.4	117.2	130.6	141.4	151.1	163.9	180.3
77.5°	72.1	74.1	76.1	79.3	82.0	86.4	94.0	103.8	112.9	120.3	131.6
80°	57.0	57.7	60.1	61.3	65.0	68.0	71.6	79.5	88.6	91.7	99.6
82.5°	43.0	43.6	45.6	46.7	48.5	51.0	55.6	57.7	64.8	68.8	73.8
85°	23.7	23.1	24.9	24.9	26.1	27.3	28.5	31.5	33.4	38.3	39.5
87.5°	11.4	11.2	11.3	10.9	10.6	11.2	11.3	11.3	11.8	12.8	14.3
90°	20.4	19.4	17.7	15.9	14.2	12.5	10.5	8.1	5.7	3.3	1.0
92.5°	23.1	22.5	21.6	20.8	19.9	19.0	18.7	18.9	19.2	19.3	19.6
95°	38.9	37.8	36.3	34.8	33.3	31.8	34.5	41.7	48.8	55.8	63.0
97.5°	51.4	50.6	47.1	43.6	40.1	36.6	44.9	65.0	84.9	105.0	125.0
100°	57.0	55.2	51.6	47.9	44.3	40.6	53.6	83.0	112.5	142.0	171.5
102.5°	59.0	56.8	87.4	118.0	148.6	179.3	197.7	204.0	210.2	216.4	222.7
105°	61.5	59.1	117.9	176.7	235.5	294.3	320.4	313.9	307.5	301.0	294.6
107.5°	80.3	82.8	153.3	223.8	294.3	364.8	397.4	392.2	387.0	381.8	376.6
110°	148.1	169.6	231.8	294.1	356.3	418.5	447.3	442.8	438.3	433.8	429.3



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	349.2	427.7	443.1	458.5	473.9	489.3	495.0	490.9	486.9	482.9	478.9
115°	498.2	597.9	592.6	587.2	581.8	576.4	571.9	568.2	564.5	560.9	557.2
117.5°	638.1	662.3	658.5	654.8	651.1	647.5	643.6	639.4	635.3	631.3	627.2
120°	712.9	710.3	706.5	702.6	698.7	694.8	691.3	688.0	684.8	681.6	678.3
122.5°	757.6	756.1	751.9	747.6	743.4	739.2	735.4	732.0	728.6	725.2	721.8
125°	820.4	818.9	814.8	810.6	806.6	802.5	799.0	796.2	793.4	790.6	787.8
127.5°	877.7	875.4	872.4	869.3	866.3	863.2	860.2	857.1	853.9	850.8	847.7
130°	914.3	911.9	909.5	907.1	904.8	902.4	899.5	896.0	892.6	889.1	885.7
132.5°	950.3	948.3	945.9	943.6	941.2	938.8	936.2	933.3	930.3	927.4	924.5
135°	1001.2	999.1	997.1	995.2	993.2	991.3	988.6	985.2	981.8	978.3	974.9
137.5°	1048.7	1046.6	1044.3	1042.2	1040.0	1037.8	1035.5	1033.1	1030.6	1028.3	1025.8
140°	1079.5	1077.6	1075.2	1072.9	1070.5	1068.1	1066.0	1064.3	1062.6	1060.9	1059.1
142.5°	1108.0	1106.3	1103.5	1100.8	1098.1	1095.4	1093.3	1091.7	1090.2	1088.6	1087.1
145°	1147.9	1146.4	1142.7	1139.1	1135.4	1131.7	1130.0	1130.2	1130.4	1130.7	1130.8
147.5°	1182.8	1181.6	1178.1	1174.4	1170.8	1167.2	1165.8	1166.6	1167.4	1168.2	1169.0
150°	1203.9	1202.6	1199.1	1195.7	1192.2	1188.8	1187.8	1189.3	1190.9	1192.4	1193.9
152.5°	1223.3	1221.9	1218.7	1215.4	1212.1	1208.9	1208.1	1209.7	1211.4	1213.1	1214.8
155°	1249.4	1248.2	1245.5	1242.9	1240.4	1237.8	1237.5	1239.4	1241.3	1243.3	1245.2
157.5°	1271.3	1269.9	1268.0	1266.2	1264.4	1262.6	1262.5	1264.2	1265.7	1267.4	1269.1
160°	1284.3	1283.0	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0
162.5°	1296.1	1294.7	1293.6	1292.4	1291.3	1290.1	1290.2	1291.6	1292.8	1294.1	1295.5
165°	1310.7	1309.2	1308.5	1307.9	1307.3	1306.6	1306.9	1308.2	1309.5	1310.8	1312.1
167.5°	1322.9	1321.4	1320.8	1320.2	1319.6	1319.0	1319.3	1320.6	1321.9	1323.2	1324.5
170°	1329.1	1327.6	1327.1	1326.7	1326.3	1325.9	1326.3	1327.6	1328.9	1330.2	1331.5
172.5°	1333.7	1332.2	1331.8	1331.3	1330.9	1330.5	1330.9	1332.2	1333.6	1334.8	1336.1
175°	1338.8	1337.3	1336.9	1336.4	1336.0	1335.5	1336.1	1337.6	1339.1	1340.6	1342.1
177.5°	1339.7	1338.5	1338.2	1338.1	1337.9	1337.8	1338.2	1339.5	1340.7	1341.9	1343.1
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1757.3	1758.7	1768.5	1772.8	1781.6	1784.9	1788.9	1787.9	1787.9	1789.9	1803.4
5°	1761.1	1773.2	1791.4	1809.0	1826.1	1840.6	1850.3	1860.0	1863.7	1881.3	1897.0
7.5°	1754.8	1777.1	1807.2	1834.1	1866.2	1891.3	1912.2	1931.0	1943.9	1969.5	1995.7
10°	1746.5	1778.1	1812.0	1846.7	1890.9	1924.4	1958.4	1984.5	1993.0	2031.2	2053.1
12.5°	1730.0	1772.3	1815.4	1860.3	1903.6	1949.6	1987.0	2013.1	2043.0	2077.3	2117.7
15°	1705.3	1753.8	1810.2	1867.9	1929.8	1985.7	2025.8	2071.2	2104.0	2141.7	2176.9
17.5°	1669.7	1732.2	1804.0	1870.7	1942.4	2002.3	2057.5	2101.1	2124.2	2145.7	2150.9
20°	1641.5	1708.9	1793.3	1872.2	1943.8	2013.0	2067.6	2104.0	2110.1	2110.7	2078.5
22.5°	1610.9	1687.0	1775.3	1856.2	1941.9	2018.8	2061.3	2076.9	2052.8	2011.7	1949.4
25°	1554.7	1642.7	1745.3	1837.5	1931.0	2003.9	2018.5	1991.2	1906.8	1818.1	1705.8
27.5°	1493.7	1592.7	1702.6	1805.2	1904.8	1950.0	1918.5	1820.0	1668.1	1536.0	1375.9
30°	1449.1	1560.1	1668.2	1782.9	1875.2	1894.6	1822.4	1677.3	1500.0	1300.9	1141.3
32.5°	1398.0	1514.5	1633.2	1751.8	1829.1	1810.1	1690.8	1512.2	1304.3	1108.6	957.7
35°	1325.2	1445.4	1573.5	1692.5	1741.6	1659.7	1481.2	1248.7	1036.3	853.5	749.7
37.5°	1241.0	1372.0	1505.1	1614.4	1610.9	1474.3	1231.2	991.2	812.6	704.6	630.6
40°	1181.3	1313.7	1457.5	1549.8	1510.4	1332.5	1069.1	842.6	712.1	625.9	571.9
42.5°	1124.0	1256.9	1399.8	1473.1	1404.5	1185.8	923.4	745.9	638.3	571.0	527.2
45°	1026.5	1166.7	1299.1	1339.7	1217.1	976.1	746.7	618.0	546.4	496.5	466.2
47.5°	931.2	1069.1	1189.9	1190.6	1024.8	791.6	629.9	534.8	473.6	435.1	413.0
50°	872.9	1004.1	1105.4	1089.6	901.5	704.2	563.3	481.4	430.4	400.7	377.6
52.5°	807.4	934.6	1022.4	977.5	797.1	619.6	503.6	434.7	392.5	366.6	346.0
55°	712.1	825.0	886.9	818.9	650.1	515.4	425.6	371.5	339.9	318.1	300.5
57.5°	618.5	711.6	750.6	671.4	535.5	427.4	360.0	319.4	288.1	272.4	263.3
60°	559.7	639.2	666.5	579.2	465.6	373.9	318.7	281.1	258.0	247.7	238.6
62.5°	501.9	566.9	578.1	498.0	405.9	327.3	279.9	248.0	232.7	222.9	214.3
65°	416.5	463.2	457.7	393.4	321.2	259.8	225.2	205.8	194.2	180.3	165.1
67.5°	342.9	371.4	354.2	305.9	245.1	201.9	179.4	164.6	150.3	137.0	133.6
70°	296.3	312.6	294.5	250.1	200.9	169.4	151.1	133.6	125.1	122.0	116.5
72.5°	251.6	257.3	237.6	199.6	163.5	140.2	122.5	112.6	108.1	105.5	102.0
75°	188.8	184.6	167.5	137.8	113.5	97.8	92.3	88.6	85.6	83.2	81.4
77.5°	132.6	126.4	111.2	91.8	79.1	71.5	68.2	66.3	64.8	63.6	61.8
80°	99.6	95.3	80.2	65.6	60.1	56.5	54.7	52.2	52.2	51.0	49.2
82.5°	72.9	68.1	54.9	48.1	45.1	42.9	41.5	40.1	39.6	39.8	38.5
85°	38.3	31.0	27.3	26.1	24.3	23.1	23.7	22.5	22.5	22.5	21.9
87.5°	12.4	10.4	10.4	10.4	11.2	11.6	11.4	11.8	12.6	12.4	13.1
90°	3.3	5.7	8.1	10.5	12.5	14.2	15.9	17.7	19.4	20.4	21.5
92.5°	19.3	19.2	18.9	18.7	19.0	19.9	20.8	21.6	22.5	23.1	23.6
95°	55.8	48.8	41.7	34.5	31.8	33.3	34.8	36.3	37.8	38.9	39.9
97.5°	105.0	84.9	65.0	44.9	36.6	40.1	43.6	47.1	50.6	51.4	52.3
100°	142.0	112.5	83.0	53.6	40.6	44.3	47.9	51.6	55.2	57.0	58.7
102.5°	216.4	210.2	204.0	197.7	179.3	148.6	118.0	87.4	56.8	59.0	61.2
105°	301.0	307.5	313.9	320.4	294.3	235.5	176.7	117.9	59.1	61.5	63.8
107.5°	381.8	387.0	392.2	397.4	364.8	294.3	223.8	153.3	82.8	80.3	78.0
110°	433.8	438.3	442.8	447.3	418.5	356.3	294.1	231.8	169.6	148.1	126.5



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	482.9	486.9	490.9	495.0	489.3	473.9	458.5	443.1	427.7	349.2	270.6
115°	560.9	564.5	568.2	571.9	576.4	581.8	587.2	592.6	597.9	498.2	398.5
117.5°	631.3	635.3	639.4	643.6	647.5	651.1	654.8	658.5	662.3	638.1	614.0
120°	681.6	684.8	688.0	691.3	694.8	698.7	702.6	706.5	710.3	712.9	715.5
122.5°	725.2	728.6	732.0	735.4	739.2	743.4	747.6	751.9	756.1	757.6	759.1
125°	790.6	793.4	796.2	799.0	802.5	806.6	810.6	814.8	818.9	820.4	821.9
127.5°	850.8	853.9	857.1	860.2	863.2	866.3	869.3	872.4	875.4	877.7	879.8
130°	889.1	892.6	896.0	899.5	902.4	904.8	907.1	909.5	911.9	914.3	916.6
132.5°	927.4	930.3	933.3	936.2	938.8	941.2	943.6	945.9	948.3	950.3	952.4
135°	978.3	981.8	985.2	988.6	991.3	993.2	995.2	997.1	999.1	1001.2	1003.4
137.5°	1028.3	1030.6	1033.1	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7	1050.8
140°	1060.9	1062.6	1064.3	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5	1081.5
142.5°	1088.6	1090.2	1091.7	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0	1109.8
145°	1130.7	1130.4	1130.2	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9	1149.4
147.5°	1168.2	1167.4	1166.6	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8	1183.9
150°	1192.4	1190.9	1189.3	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9	1205.1
152.5°	1213.1	1211.4	1209.7	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3	1224.6
155°	1243.3	1241.3	1239.4	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4	1250.7
157.5°	1267.4	1265.7	1264.2	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3	1272.8
160°	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3	1285.6
162.5°	1294.1	1292.8	1291.6	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1	1297.6
165°	1310.8	1309.5	1308.2	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7	1312.2
167.5°	1323.2	1321.9	1320.6	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9	1324.4
170°	1330.2	1328.9	1327.6	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1	1330.6
172.5°	1334.8	1333.6	1332.2	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7	1335.2
175°	1340.6	1339.1	1337.6	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8	1340.3
177.5°	1341.9	1340.7	1339.5	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7	1340.8
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1808.3	1814.6	1817.5	1817.5	1820.9	1819.5	1818.0
5°	1912.2	1923.7	1926.2	1937.1	1945.0	1942.6	1943.8
7.5°	2015.5	2034.1	2052.5	2060.9	2062.1	2067.0	2068.9
10°	2079.2	2094.4	2122.9	2118.6	2139.8	2152.0	2132.0
12.5°	2140.3	2160.8	2180.6	2186.1	2198.1	2202.0	2194.1
15°	2195.7	2206.6	2207.9	2204.8	2208.4	2205.4	2193.9
17.5°	2144.0	2126.3	2090.3	2073.3	2059.8	2039.9	2031.9
20°	2058.5	2006.3	1945.6	1921.4	1892.8	1836.9	1850.3
22.5°	1874.0	1814.5	1753.8	1682.9	1649.0	1596.1	1592.9
25°	1586.8	1484.2	1371.3	1292.4	1246.3	1193.5	1170.4
27.5°	1233.7	1104.6	1012.1	965.2	922.6	880.7	879.0
30°	1001.6	904.5	832.9	792.8	766.7	749.1	752.7
32.5°	844.3	777.8	729.4	696.2	676.8	663.6	663.4
35°	690.2	644.7	613.7	599.8	585.8	576.1	576.7
37.5°	590.7	563.3	546.1	530.7	522.0	517.2	514.5
40°	539.6	517.2	503.8	494.7	487.4	480.8	479.6
42.5°	499.4	480.8	467.5	460.3	453.4	448.8	447.5
45°	443.1	427.9	415.8	408.0	404.9	400.7	400.7
47.5°	394.2	379.3	369.8	364.9	359.7	356.8	356.7
50°	361.2	349.7	341.2	338.1	333.9	332.1	331.4
52.5°	331.6	323.0	316.9	314.8	313.0	310.7	311.1
55°	291.4	286.5	284.1	282.3	279.2	275.6	278.1
57.5°	257.5	253.4	246.8	241.1	238.4	235.8	236.8
60°	233.7	225.2	216.7	210.0	208.2	202.7	202.7
62.5°	203.6	191.7	181.3	177.5	175.7	173.2	172.6
65°	156.6	151.8	149.3	146.9	145.7	145.7	144.5
67.5°	129.8	127.9	125.2	124.5	123.3	123.0	122.6
70°	114.7	112.3	111.1	110.5	109.2	109.9	108.1
72.5°	100.1	98.2	98.0	96.4	95.7	95.8	94.4
75°	78.9	78.9	78.3	77.7	76.5	75.9	76.5
77.5°	60.7	60.8	59.7	59.7	59.5	59.7	59.0
80°	48.6	49.2	48.6	47.9	47.4	47.9	47.4
82.5°	38.3	37.5	37.4	37.3	37.2	36.8	36.7
85°	21.9	22.5	21.9	21.2	21.2	21.2	21.9
87.5°	12.8	13.0	13.2	13.2	13.3	13.4	13.0
90°	22.6	23.7	24.5	24.9	25.3	25.7	26.1
92.5°	24.2	24.7	25.1	25.3	25.7	25.9	26.1
95°	41.0	42.1	42.5	42.3	42.1	41.9	41.7
97.5°	53.2	54.0	54.6	54.8	55.1	55.4	55.6
100°	60.4	62.1	63.2	63.6	64.1	64.5	65.0
102.5°	63.5	65.8	67.2	67.7	68.4	69.0	69.6
105°	66.2	68.6	70.2	71.1	71.9	72.8	73.7
107.5°	75.5	73.1	72.3	73.2	74.1	74.9	75.8
110°	105.0	83.4	73.1	74.0	74.9	75.7	76.5



TEST NUMBER: P331857-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	192.1	113.5	74.5	75.3	76.0	76.6	77.3
115°	298.8	199.1	141.5	126.0	110.5	95.0	79.5
117.5°	589.9	565.8	528.2	477.3	426.4	375.4	324.4
120°	718.0	720.6	707.4	678.3	649.3	620.2	591.1
122.5°	760.7	762.2	760.2	754.6	748.9	743.3	737.6
125°	823.4	824.9	825.9	826.6	827.3	827.9	828.5
127.5°	882.0	884.2	885.4	885.5	885.7	885.7	885.9
130°	919.0	921.3	922.4	922.2	922.0	921.8	921.5
132.5°	954.3	956.4	957.3	957.1	956.9	956.6	956.5
135°	1005.5	1007.7	1008.5	1008.1	1007.7	1007.3	1006.9
137.5°	1052.9	1055.0	1055.7	1054.9	1054.2	1053.5	1052.7
140°	1083.4	1085.4	1085.8	1084.7	1083.6	1082.5	1081.5
142.5°	1111.6	1113.3	1113.6	1112.6	1111.5	1110.4	1109.4
145°	1150.9	1152.4	1152.6	1151.5	1150.5	1149.4	1148.3
147.5°	1185.0	1186.1	1186.2	1185.3	1184.4	1183.5	1182.6
150°	1206.5	1207.8	1207.8	1206.8	1205.7	1204.6	1203.6
152.5°	1225.8	1227.2	1227.1	1225.7	1224.2	1222.8	1221.4
155°	1252.0	1253.3	1253.1	1251.3	1249.7	1247.9	1246.2
157.5°	1274.2	1275.7	1275.6	1273.9	1272.2	1270.6	1268.8
160°	1286.9	1288.2	1288.1	1286.6	1285.1	1283.6	1282.1
162.5°	1299.0	1300.5	1300.3	1298.5	1296.6	1294.7	1292.9
165°	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2
167.5°	1325.9	1327.4	1327.2	1325.2	1323.3	1321.4	1319.5
170°	1332.1	1333.6	1333.4	1331.5	1329.5	1327.6	1325.6
172.5°	1336.7	1338.2	1338.1	1336.1	1334.2	1332.2	1330.3
175°	1341.8	1343.3	1343.0	1340.8	1338.7	1336.5	1334.4
177.5°	1342.0	1343.3	1343.1	1341.6	1340.0	1338.5	1336.9
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2

(END OF REPORT)