

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331858-927

Luminaire Tested: **S122RDIW-S1005D1240U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331858-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6427.8 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	94	90	87	90	86	83	81	73	70	68	60	58	57	48	47	46	41
2	90	83	77	72	82	76	72	67	65	61	58	54	51	49	43	42	40	36
3	82	73	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	52	70	61	54	49	52	47	43	43	40	37	36	33	31	27
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	33	30	28	24
6	65	53	45	40	59	49	43	38	42	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	22	20
8	56	44	37	32	51	41	35	30	36	30	27	30	26	24	26	23	20	18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19	17
10	49	37	30	26	45	35	29	25	30	25	22	26	22	20	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28208	28208	28208	28208
5°	31504	28386	25167	28386
10°	34954	28186	21815	28186
15°	36672	27773	17188	27773
20°	31792	27161	14874	27161
25°	20851	26323	13279	26323
30°	14033	25307	12020	25307
35°	11367	24025	10841	24025
40°	10108	22634	10030	22634
45°	9149	21000	8953	21000
50°	8324	19381	8297	19381
55°	7828	17582	7724	17582
60°	6546	15936	6468	15936
65°	5521	14472	6262	14472
70°	5103	12925	5906	12925
75°	4772	11248	5452	11248
80°	4407	9261	4854	9261
85°	4057	7317	4279	7317



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.6	2.6
10°-20°	461.5	7.2
20°-30°	594.7	9.3
30°-40°	565.1	8.8
40°-50°	484.1	7.5
50°-60°	368.7	5.7
60°-70°	233.1	3.6
70°-80°	116.4	1.8
80°-90°	35.2	0.5
90°-100°	77.1	1.2
100°-110°	239.6	3.7
110°-120°	409.5	6.4
120°-130°	538.5	8.4
130°-140°	604.4	9.4
140°-150°	592.6	9.2
150°-160°	497.0	7.7
160°-170°	329.7	5.1
170°-180°	115.2	1.8
0°-30°	1221.8	19.0
0°-40°	1786.9	27.8
0°-60°	2639.7	41.1
0°-90°	3024.2	47.0
90°-120°	726.2	11.3
90°-150°	2461.6	38.3
90°-180°	3404.0	53.0
0°-180°	6427.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1747	1747	1747	1747	1747	
5°	1944	1751	1553	1751	1944	192
15°	2194	1662	1028	1662	2194	592
25°	1170	1478	745	1478	1170	555
35°	577	1219	550	1219	577	369
45°	401	920	392	920	401	310
55°	278	625	274	625	278	244
65°	144	379	164	379	144	147
75°	76	180	87	180	76	81
85°	22	40	23	40	22	24
90°	35	1	35	1	35	16
95°	64	53	64	53	64	71
105°	228	221	228	221	228	240
115°	411	411	411	411	411	406
125°	600	598	600	598	600	535
135°	783	774	783	774	783	602
145°	949	939	949	939	949	593
155°	1082	1073	1082	1073	1082	498
165°	1169	1168	1169	1168	1169	330
175°	1211	1215	1211	1215	1211	115
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1818.0	1819.5	1820.9	1817.5	1817.5	1814.6	1808.3	1803.4	1789.9	1787.9	1787.9
5°	1943.8	1942.6	1945.0	1937.1	1926.2	1923.7	1912.2	1897.0	1881.3	1863.7	1860.0
7.5°	2068.9	2067.0	2062.1	2060.9	2052.5	2034.1	2015.5	1995.7	1969.5	1943.9	1931.0
10°	2132.0	2152.0	2139.8	2118.6	2122.9	2094.4	2079.2	2053.1	2031.2	1993.0	1984.5
12.5°	2194.1	2202.0	2198.1	2186.1	2180.6	2160.8	2140.3	2117.7	2077.3	2043.0	2013.1
15°	2193.9	2205.4	2208.4	2204.8	2207.9	2206.6	2195.7	2176.9	2141.7	2104.0	2071.2
17.5°	2031.9	2039.9	2059.8	2073.3	2090.3	2126.3	2144.0	2150.9	2145.7	2124.2	2101.1
20°	1850.3	1836.9	1892.8	1921.4	1945.6	2006.3	2058.5	2078.5	2110.7	2110.1	2104.0
22.5°	1592.9	1596.1	1649.0	1682.9	1753.8	1814.5	1874.0	1949.4	2011.7	2052.8	2076.9
25°	1170.4	1193.5	1246.3	1292.4	1371.3	1484.2	1586.8	1705.8	1818.1	1906.8	1991.2
27.5°	879.0	880.7	922.6	965.2	1012.1	1104.6	1233.7	1375.9	1536.0	1668.1	1820.0
30°	752.7	749.1	766.7	792.8	832.9	904.5	1001.6	1141.3	1300.9	1500.0	1677.3
32.5°	663.4	663.6	676.8	696.2	729.4	777.8	844.3	957.7	1108.6	1304.3	1512.2
35°	576.7	576.1	585.8	599.8	613.7	644.7	690.2	749.7	853.5	1036.3	1248.7
37.5°	514.5	517.2	522.0	530.7	546.1	563.3	590.7	630.6	704.6	812.6	991.2
40°	479.6	480.8	487.4	494.7	503.8	517.2	539.6	571.9	625.9	712.1	842.6
42.5°	447.5	448.8	453.4	460.3	467.5	480.8	499.4	527.2	571.0	638.3	745.9
45°	400.7	400.7	404.9	408.0	415.8	427.9	443.1	466.2	496.5	546.4	618.0
47.5°	356.7	356.8	359.7	364.9	369.8	379.3	394.2	413.0	435.1	473.6	534.8
50°	331.4	332.1	333.9	338.1	341.2	349.7	361.2	377.6	400.7	430.4	481.4
52.5°	311.1	310.7	313.0	314.8	316.9	323.0	331.6	346.0	366.6	392.5	434.7
55°	278.1	275.6	279.2	282.3	284.1	286.5	291.4	300.5	318.1	339.9	371.5
57.5°	236.8	235.8	238.4	241.1	246.8	253.4	257.5	263.3	272.4	288.1	319.4
60°	202.7	202.7	208.2	210.0	216.7	225.2	233.7	238.6	247.7	258.0	281.1
62.5°	172.6	173.2	175.7	177.5	181.3	191.7	203.6	214.3	222.9	232.7	248.0
65°	144.5	145.7	145.7	146.9	149.3	151.8	156.6	165.1	180.3	194.2	205.8
67.5°	122.6	123.0	123.3	124.5	125.2	127.9	129.8	133.6	137.0	150.3	164.6
70°	108.1	109.9	109.2	110.5	111.1	112.3	114.7	116.5	122.0	125.1	133.6
72.5°	94.4	95.8	95.7	96.4	98.0	98.2	100.1	102.0	105.5	108.1	112.6
75°	76.5	75.9	76.5	77.7	78.3	78.9	78.9	81.4	83.2	85.6	88.6
77.5°	59.0	59.7	59.5	59.7	59.7	60.8	60.7	61.8	63.6	64.8	66.3
80°	47.4	47.9	47.4	47.9	48.6	49.2	48.6	49.2	51.0	52.2	52.2
82.5°	36.7	36.8	37.2	37.3	37.4	37.5	38.3	38.5	39.8	39.6	40.1
85°	21.9	21.2	21.2	21.2	21.9	22.5	21.9	21.9	22.5	22.5	22.5
87.5°	14.7	15.2	15.1	15.1	15.1	15.1	15.2	15.8	15.4	15.9	14.4
90°	34.9	34.7	34.5	34.2	34.0	34.1	34.6	35.0	35.5	36.0	30.9
92.5°	33.3	33.3	33.2	33.1	33.1	33.0	33.0	32.9	32.7	32.6	31.4
95°	63.7	64.2	64.6	65.0	65.5	65.8	65.8	65.8	65.8	65.8	65.3
97.5°	110.4	110.4	110.4	110.4	110.5	110.5	110.5	110.5	110.5	110.5	109.6
100°	140.7	140.9	141.2	141.4	141.6	141.7	141.7	141.7	141.7	141.7	141.1
102.5°	175.2	175.5	175.7	175.9	176.2	176.2	176.0	175.8	175.6	175.5	174.6
105°	228.1	228.1	228.1	228.1	228.1	227.8	227.4	226.9	226.4	226.0	225.5
107.5°	277.7	278.8	279.9	280.9	281.9	282.4	282.2	282.0	281.9	281.6	281.6
110°	316.4	317.0	317.7	318.5	319.1	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.3	353.9	354.3	354.8	355.4	355.8	356.4	357.0	357.5	358.1	358.2
115°	410.9	411.5	412.3	413.0	413.6	414.1	414.3	414.5	414.8	414.9	415.4
117.5°	465.7	466.4	467.1	467.8	468.5	469.1	469.6	470.2	470.7	471.3	472.5
120°	504.4	505.0	505.7	506.4	507.1	507.4	507.4	507.4	507.4	507.4	509.2
122.5°	542.2	542.6	543.1	543.7	544.2	544.7	545.3	545.8	546.3	546.8	548.1
125°	599.8	600.1	600.3	600.6	600.8	601.3	601.9	602.6	603.3	604.0	604.7
127.5°	652.4	653.2	653.9	654.7	655.4	656.2	657.0	657.8	658.6	659.4	660.3
130°	690.2	691.2	692.1	693.0	694.0	694.6	695.1	695.5	695.9	696.4	696.9
132.5°	726.4	727.1	727.9	728.6	729.4	730.2	731.2	732.2	733.2	734.2	734.1
135°	782.7	783.4	784.1	784.7	785.4	785.9	786.2	786.4	786.6	786.8	786.4
137.5°	833.7	834.6	835.5	836.4	837.3	837.9	838.0	838.2	838.4	838.6	838.0
140°	869.0	869.9	870.8	871.7	872.7	873.1	873.1	873.1	873.1	873.1	872.0
142.5°	901.0	902.0	902.9	903.8	904.7	905.1	904.9	904.7	904.5	904.4	903.6
145°	949.1	950.1	950.9	951.9	952.8	953.1	952.9	952.7	952.4	952.2	950.9
147.5°	992.0	992.9	993.8	994.7	995.5	995.7	995.2	994.7	994.2	993.7	992.8
150°	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0	1019.1
152.5°	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3	1045.2
155°	1081.6	1082.3	1083.0	1083.7	1084.3	1084.1	1083.0	1081.9	1080.7	1079.6	1078.9
157.5°	1112.0	1113.1	1114.2	1115.3	1116.4	1116.2	1114.6	1113.1	1111.5	1110.0	1109.5
160°	1130.9	1131.9	1132.7	1133.7	1134.6	1134.3	1133.0	1131.6	1130.2	1128.9	1128.6
162.5°	1147.4	1148.4	1149.5	1150.6	1151.8	1151.5	1149.9	1148.4	1146.8	1145.3	1145.1
165°	1168.9	1170.1	1171.2	1172.4	1173.5	1173.3	1171.6	1170.1	1168.5	1166.9	1166.9
167.5°	1186.6	1187.8	1189.0	1190.2	1191.4	1191.1	1189.5	1188.0	1186.4	1184.7	1184.8
170°	1195.6	1197.0	1198.4	1199.8	1201.1	1201.0	1199.4	1197.8	1196.2	1194.6	1194.8
172.5°	1203.0	1204.4	1205.8	1207.1	1208.5	1208.4	1206.8	1205.2	1203.6	1202.0	1202.2
175°	1211.0	1212.4	1213.8	1215.1	1216.6	1216.4	1214.8	1213.2	1211.6	1210.0	1210.5
177.5°	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7	1215.1
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1788.9	1784.9	1781.6	1772.8	1768.5	1758.7	1757.3	1756.8	1744.2	1732.0	1728.6
5°	1850.3	1840.6	1826.1	1809.0	1791.4	1773.2	1761.1	1751.4	1727.0	1704.0	1690.7
7.5°	1912.2	1891.3	1866.2	1834.1	1807.2	1777.1	1754.8	1734.7	1700.3	1667.2	1645.0
10°	1958.4	1924.4	1890.9	1846.7	1812.0	1778.1	1746.5	1719.2	1680.3	1636.6	1605.7
12.5°	1987.0	1949.6	1903.6	1860.3	1815.4	1772.3	1730.0	1694.9	1649.2	1604.1	1567.3
15°	2025.8	1985.7	1929.8	1867.9	1810.2	1753.8	1705.3	1661.5	1602.0	1548.0	1503.1
17.5°	2057.5	2002.3	1942.4	1870.7	1804.0	1732.2	1669.7	1613.8	1547.6	1482.4	1429.5
20°	2067.6	2013.0	1943.8	1872.2	1793.3	1708.9	1641.5	1580.8	1509.7	1438.7	1378.0
22.5°	2061.3	2018.8	1941.9	1856.2	1775.3	1687.0	1610.9	1540.5	1461.7	1389.2	1318.7
25°	2018.5	2003.9	1931.0	1837.5	1745.3	1642.7	1554.7	1477.6	1387.7	1310.0	1233.5
27.5°	1918.5	1950.0	1904.8	1805.2	1702.6	1592.7	1493.7	1406.0	1312.7	1225.3	1149.1
30°	1822.4	1894.6	1875.2	1782.9	1668.2	1560.1	1449.1	1357.4	1257.8	1168.0	1092.7
32.5°	1690.8	1810.1	1829.1	1751.8	1633.2	1514.5	1398.0	1306.9	1202.9	1108.3	1034.9
35°	1481.2	1659.7	1741.6	1692.5	1573.5	1445.4	1325.2	1218.9	1114.5	1021.0	948.2
37.5°	1231.2	1474.3	1610.9	1614.4	1505.1	1372.0	1241.0	1135.6	1028.7	936.9	858.2
40°	1069.1	1332.5	1510.4	1549.8	1457.5	1313.7	1181.3	1073.9	969.5	879.6	789.2
42.5°	923.4	1185.8	1404.5	1473.1	1399.8	1256.9	1124.0	1011.7	910.2	825.2	732.8
45°	746.7	976.1	1217.1	1339.7	1299.1	1166.7	1026.5	919.7	824.3	750.9	662.3
47.5°	629.9	791.6	1024.8	1190.6	1189.9	1069.1	931.2	828.9	740.5	671.6	599.9
50°	563.3	704.2	901.5	1089.6	1105.4	1004.1	872.9	771.6	689.0	616.8	559.1
52.5°	503.6	619.6	797.1	977.5	1022.4	934.6	807.4	713.8	633.7	567.2	517.8
55°	425.6	515.4	650.1	818.9	886.9	825.0	712.1	624.6	559.7	503.8	461.4
57.5°	360.0	427.4	535.5	671.4	750.6	711.6	618.5	547.5	491.9	441.3	407.8
60°	318.7	373.9	465.6	579.2	666.5	639.2	559.7	493.5	446.2	402.5	370.9
62.5°	279.9	327.3	405.9	498.0	578.1	566.9	501.9	446.4	404.9	365.1	338.3
65°	225.2	259.8	321.2	393.4	457.7	463.2	416.5	378.8	341.7	310.2	286.5
67.5°	179.4	201.9	245.1	305.9	354.2	371.4	342.9	314.1	284.7	260.3	239.8
70°	151.1	169.4	200.9	250.1	294.5	312.6	296.3	273.8	248.3	228.2	210.6
72.5°	122.5	140.2	163.5	199.6	237.6	257.3	251.6	235.4	214.8	198.1	181.5
75°	92.3	97.8	113.5	137.8	167.5	184.6	188.8	180.3	163.9	151.1	141.4
77.5°	68.2	71.5	79.1	91.8	111.2	126.4	132.6	131.6	120.3	112.9	103.8
80°	54.7	56.5	60.1	65.6	80.2	95.3	99.6	99.6	91.7	88.6	79.5
82.5°	41.5	42.9	45.1	48.1	54.9	68.1	72.9	73.8	68.8	64.8	57.7
85°	23.7	23.1	24.3	26.1	27.3	31.0	38.3	39.5	38.3	33.4	31.5
87.5°	13.5	12.9	11.9	10.6	10.6	10.5	12.4	14.3	12.9	12.0	11.6
90°	25.9	20.9	15.8	12.0	9.3	6.5	3.8	1.0	3.8	6.5	9.3
92.5°	30.3	29.1	27.9	26.3	24.3	22.3	20.3	18.3	20.3	22.3	24.3
95°	64.8	64.4	63.9	62.6	60.3	58.0	55.7	53.4	55.7	58.0	60.3
97.5°	108.8	107.9	107.0	105.6	103.6	101.6	99.6	97.6	99.6	101.6	103.6
100°	140.4	139.7	139.0	137.8	135.9	134.1	132.3	130.5	132.3	134.1	135.9
102.5°	173.7	172.9	172.0	170.8	169.4	167.9	166.4	164.9	166.4	167.9	169.4
105°	225.1	224.6	224.2	223.6	222.9	222.2	221.5	220.9	221.5	222.2	222.9
107.5°	281.6	281.6	281.6	281.1	280.1	279.2	278.1	277.1	278.1	279.2	280.1
110°	319.5	319.5	319.5	318.8	317.4	316.0	314.7	313.3	314.7	316.0	317.4



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	358.5	358.6	358.8	358.2	356.9	355.5	354.1	352.8	354.1	355.5	356.9
115°	415.9	416.4	416.8	416.4	414.9	413.6	412.3	410.9	412.3	413.6	414.9
117.5°	473.8	475.1	476.4	476.1	474.3	472.5	470.6	468.8	470.6	472.5	474.3
120°	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	509.2	511.1	512.9
122.5°	549.5	550.7	552.0	551.5	549.3	547.2	544.9	542.7	544.9	547.2	549.3
125°	605.4	606.0	606.7	606.0	604.0	601.9	599.8	597.8	599.8	601.9	604.0
127.5°	661.1	661.9	662.7	661.9	659.3	656.6	654.0	651.4	654.0	656.6	659.3
130°	697.4	697.8	698.2	697.0	694.0	691.1	688.1	685.2	688.1	691.1	694.0
132.5°	734.0	734.0	733.9	732.6	730.2	727.8	725.3	722.9	725.3	727.8	730.2
135°	785.9	785.4	785.0	783.5	781.0	778.5	775.9	773.5	775.9	778.5	781.0
137.5°	837.4	836.8	836.2	834.9	832.8	830.8	828.7	826.6	828.7	830.8	832.8
140°	870.8	869.7	868.5	867.0	864.9	862.8	860.8	858.7	860.8	862.8	864.9
142.5°	902.8	902.0	901.2	899.8	897.8	895.7	893.7	891.6	893.7	895.7	897.8
145°	949.4	948.1	946.7	945.2	943.6	942.1	940.5	938.8	940.5	942.1	943.6
147.5°	991.9	990.9	990.1	988.6	986.7	984.8	982.9	981.0	982.9	984.8	986.7
150°	1018.2	1017.2	1016.4	1015.2	1013.8	1012.5	1011.1	1009.7	1011.1	1012.5	1013.8
152.5°	1044.1	1043.0	1041.9	1040.7	1039.3	1037.9	1036.6	1035.2	1036.6	1037.9	1039.3
155°	1078.2	1077.5	1076.8	1076.2	1075.5	1074.8	1074.1	1073.4	1074.1	1074.8	1075.5
157.5°	1109.1	1108.7	1108.3	1107.9	1107.5	1107.0	1106.5	1106.0	1106.5	1107.0	1107.5
160°	1128.4	1128.1	1128.0	1127.6	1127.2	1126.7	1126.2	1125.8	1126.2	1126.7	1127.2
162.5°	1144.9	1144.6	1144.4	1144.2	1144.1	1144.1	1144.0	1143.8	1144.0	1144.1	1144.1
165°	1166.9	1166.9	1166.9	1167.0	1167.2	1167.4	1167.7	1167.9	1167.7	1167.4	1167.2
167.5°	1184.9	1184.9	1184.9	1185.3	1186.0	1186.7	1187.3	1188.0	1187.3	1186.7	1186.0
170°	1195.1	1195.3	1195.6	1196.0	1196.7	1197.4	1198.0	1198.7	1198.0	1197.4	1196.7
172.5°	1202.5	1202.7	1202.9	1203.4	1204.0	1204.8	1205.5	1206.1	1205.5	1204.8	1204.0
175°	1210.9	1211.4	1211.9	1212.4	1213.1	1213.8	1214.5	1215.1	1214.5	1213.8	1213.1
177.5°	1215.4	1215.8	1216.2	1216.6	1217.2	1217.7	1218.3	1218.9	1218.3	1217.7	1217.2
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1722.4	1719.0	1712.6	1702.9	1697.1	1686.9	1680.1	1683.9	1685.0	1683.9	1683.0
5°	1676.1	1663.3	1645.8	1628.7	1613.0	1595.9	1586.3	1582.0	1573.5	1568.6	1566.2
7.5°	1620.1	1598.1	1573.3	1543.6	1518.5	1492.2	1478.7	1472.0	1454.6	1445.2	1436.9
10°	1578.3	1543.7	1518.9	1480.0	1456.3	1421.7	1398.0	1398.7	1375.0	1361.6	1351.9
12.5°	1532.2	1494.2	1452.8	1417.8	1385.0	1357.2	1328.6	1317.1	1292.0	1279.1	1252.8
15°	1455.7	1411.4	1367.7	1320.3	1287.0	1243.9	1202.6	1152.2	1111.5	1076.3	1066.6
17.5°	1372.2	1317.3	1273.5	1217.9	1160.7	1088.2	1040.4	1011.1	986.6	968.0	954.2
20°	1314.9	1259.0	1212.3	1128.5	1051.4	1002.3	967.0	944.6	919.1	899.0	888.1
22.5°	1254.7	1196.4	1132.7	1039.2	979.1	939.6	908.2	882.4	865.1	849.5	839.6
25°	1169.2	1105.4	1000.4	936.0	887.5	846.2	824.3	808.6	790.4	769.1	759.5
27.5°	1078.9	977.5	902.1	854.2	807.9	781.0	761.4	737.8	721.5	711.9	701.9
30°	1011.4	910.0	851.1	798.9	766.1	736.3	713.3	700.0	684.1	667.7	661.1
32.5°	936.0	855.1	798.7	755.2	721.9	696.6	678.3	656.7	645.3	635.3	621.2
35°	842.6	781.3	729.7	694.5	662.9	642.3	621.0	608.2	587.6	579.2	573.7
37.5°	763.4	710.3	671.8	634.6	609.6	586.8	573.8	553.5	544.5	532.7	521.3
40°	718.7	666.5	629.5	599.1	571.2	554.2	537.8	521.5	508.1	502.6	488.7
42.5°	673.1	630.6	593.6	560.3	541.6	523.6	502.9	490.8	477.1	468.2	459.5
45°	610.1	572.4	540.9	513.6	492.9	474.1	460.7	440.7	432.8	415.3	408.0
47.5°	554.8	519.8	489.6	463.7	443.5	431.3	411.7	396.0	383.4	372.6	363.3
50°	515.4	486.2	457.1	434.0	415.8	398.2	378.2	370.3	350.9	345.4	339.9
52.5°	479.4	451.8	425.1	402.5	384.3	367.2	349.5	339.2	326.1	320.7	316.6
55°	429.2	402.5	377.0	357.0	338.7	321.2	310.2	297.5	291.4	287.2	282.3
57.5°	378.7	354.7	335.1	314.8	296.5	282.5	269.9	262.2	256.0	250.3	244.5
60°	346.7	323.5	305.9	287.2	268.3	256.7	247.1	238.0	230.7	222.2	219.8
62.5°	312.6	292.5	276.3	258.0	241.6	231.1	221.8	213.2	204.5	192.1	188.7
65°	265.9	250.1	233.1	217.9	203.4	193.1	179.7	170.0	166.4	165.1	164.5
67.5°	223.6	208.7	194.2	178.6	165.3	155.7	149.0	147.5	145.0	144.3	142.5
70°	195.5	181.5	166.9	152.3	139.7	137.8	135.4	132.9	129.9	128.7	127.5
72.5°	170.2	155.7	141.2	129.5	124.1	121.8	119.4	116.9	114.9	113.7	112.9
75°	130.6	117.2	107.4	103.2	100.1	98.3	94.7	92.8	91.7	89.8	89.2
77.5°	94.0	86.4	82.0	79.3	76.1	74.1	72.1	70.3	69.0	68.6	67.7
80°	71.6	68.0	65.0	61.3	60.1	57.7	57.0	55.2	55.8	54.0	54.0
82.5°	55.6	51.0	48.5	46.7	45.6	43.6	43.0	42.1	42.2	40.9	40.9
85°	28.5	27.3	26.1	24.9	24.9	23.1	23.7	23.1	23.1	21.9	21.2
87.5°	11.6	11.9	12.0	12.9	13.9	14.5	14.4	13.8	13.7	13.6	13.2
90°	12.0	15.8	20.9	25.9	30.9	36.0	35.5	35.0	34.6	34.1	34.0
92.5°	26.3	27.9	29.1	30.3	31.4	32.6	32.7	32.9	33.0	33.0	33.1
95°	62.6	63.9	64.4	64.8	65.3	65.8	65.8	65.8	65.8	65.8	65.5
97.5°	105.6	107.0	107.9	108.8	109.6	110.5	110.5	110.5	110.5	110.5	110.5
100°	137.8	139.0	139.7	140.4	141.1	141.7	141.7	141.7	141.7	141.7	141.6
102.5°	170.8	172.0	172.9	173.7	174.6	175.5	175.6	175.8	176.0	176.2	176.2
105°	223.6	224.2	224.6	225.1	225.5	226.0	226.4	226.9	227.4	227.8	228.1
107.5°	281.1	281.6	281.6	281.6	281.6	281.6	281.9	282.0	282.2	282.4	281.9
110°	318.8	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.1



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	358.2	358.8	358.6	358.5	358.2	358.1	357.5	357.0	356.4	355.8	355.4
115°	416.4	416.8	416.4	415.9	415.4	414.9	414.8	414.5	414.3	414.1	413.6
117.5°	476.1	476.4	475.1	473.8	472.5	471.3	470.7	470.2	469.6	469.1	468.5
120°	514.8	514.8	512.9	511.1	509.2	507.4	507.4	507.4	507.4	507.4	507.1
122.5°	551.5	552.0	550.7	549.5	548.1	546.8	546.3	545.8	545.3	544.7	544.2
125°	606.0	606.7	606.0	605.4	604.7	604.0	603.3	602.6	601.9	601.3	600.8
127.5°	661.9	662.7	661.9	661.1	660.3	659.4	658.6	657.8	657.0	656.2	655.4
130°	697.0	698.2	697.8	697.4	696.9	696.4	695.9	695.5	695.1	694.6	694.0
132.5°	732.6	733.9	734.0	734.0	734.1	734.2	733.2	732.2	731.2	730.2	729.4
135°	783.5	785.0	785.4	785.9	786.4	786.8	786.6	786.4	786.2	785.9	785.4
137.5°	834.9	836.2	836.8	837.4	838.0	838.6	838.4	838.2	838.0	837.9	837.3
140°	867.0	868.5	869.7	870.8	872.0	873.1	873.1	873.1	873.1	873.1	872.7
142.5°	899.8	901.2	902.0	902.8	903.6	904.4	904.5	904.7	904.9	905.1	904.7
145°	945.2	946.7	948.1	949.4	950.9	952.2	952.4	952.7	952.9	953.1	952.8
147.5°	988.6	990.1	990.9	991.9	992.8	993.7	994.2	994.7	995.2	995.7	995.5
150°	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7
152.5°	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7
155°	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7	1081.9	1083.0	1084.1	1084.3
157.5°	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5	1113.1	1114.6	1116.2	1116.4
160°	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2	1131.6	1133.0	1134.3	1134.6
162.5°	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8	1148.4	1149.9	1151.5	1151.8
165°	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5	1170.1	1171.6	1173.3	1173.5
167.5°	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4	1188.0	1189.5	1191.1	1191.4
170°	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2	1197.8	1199.4	1201.0	1201.1
172.5°	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6	1205.2	1206.8	1208.4	1208.5
175°	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6	1213.2	1214.8	1216.4	1216.6
177.5°	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1677.7	1678.6	1677.2	1678.2	1677.2	1678.6	1677.7	1683.0	1683.9	1685.0	1683.9
5°	1563.1	1555.8	1554.7	1552.8	1554.7	1555.8	1563.1	1566.2	1568.6	1573.5	1582.0
7.5°	1426.5	1425.4	1422.4	1418.1	1422.4	1425.4	1426.5	1436.9	1445.2	1454.6	1472.0
10°	1338.6	1335.5	1334.9	1330.6	1334.9	1335.5	1338.6	1351.9	1361.6	1375.0	1398.7
12.5°	1235.6	1216.1	1214.0	1203.4	1214.0	1216.1	1235.6	1252.8	1279.1	1292.0	1317.1
15°	1052.0	1048.4	1036.3	1028.3	1036.3	1048.4	1052.0	1066.6	1076.3	1111.5	1152.2
17.5°	947.1	935.3	931.4	929.8	931.4	935.3	947.1	954.2	968.0	986.6	1011.1
20°	879.6	868.7	866.9	865.7	866.9	868.7	879.6	888.1	899.0	919.1	944.6
22.5°	833.0	821.6	816.8	813.2	816.8	821.6	833.0	839.6	849.5	865.1	882.4
25°	753.4	749.1	746.7	745.4	746.7	749.1	753.4	759.5	769.1	790.4	808.6
27.5°	691.1	681.8	679.9	676.8	679.9	681.8	691.1	701.9	711.9	721.5	737.8
30°	655.6	652.6	648.3	644.7	648.3	652.6	655.6	661.1	667.7	684.1	700.0
32.5°	613.9	611.3	607.5	605.9	607.5	611.3	613.9	621.2	635.3	645.3	656.7
35°	567.6	559.1	555.5	550.0	555.5	559.1	567.6	573.7	579.2	587.6	608.2
37.5°	518.6	514.2	509.1	510.9	509.1	514.2	518.6	521.3	532.7	544.5	553.5
40°	480.8	477.8	476.6	475.9	476.6	477.8	480.8	488.7	502.6	508.1	521.5
42.5°	450.7	442.3	439.1	439.0	439.1	442.3	450.7	459.5	468.2	477.1	490.8
45°	404.9	397.0	391.6	392.1	391.6	397.0	404.9	408.0	415.3	432.8	440.7
47.5°	358.1	357.8	354.4	355.5	354.4	357.8	358.1	363.3	372.6	383.4	396.0
50°	335.7	332.1	329.6	330.3	329.6	332.1	335.7	339.9	345.4	350.9	370.3
52.5°	314.3	311.2	309.3	311.8	309.3	311.2	314.3	316.6	320.7	326.1	339.2
55°	279.2	275.6	275.0	274.4	275.0	275.6	279.2	282.3	287.2	291.4	297.5
57.5°	240.0	237.6	233.9	232.3	233.9	237.6	240.0	244.5	250.3	256.0	262.2
60°	211.8	207.0	200.9	200.3	200.9	207.0	211.8	219.8	222.2	230.7	238.0
62.5°	186.1	185.1	183.9	183.8	183.9	185.1	186.1	188.7	192.1	204.5	213.2
65°	163.3	162.7	163.3	163.9	163.3	162.7	163.3	164.5	165.1	166.4	170.0
67.5°	142.3	141.2	140.1	140.6	140.1	141.2	142.3	142.5	144.3	145.0	147.5
70°	126.3	125.6	125.1	125.1	125.1	125.6	126.3	127.5	128.7	129.9	132.9
72.5°	110.7	110.6	110.0	109.5	110.0	110.6	110.7	112.9	113.7	114.9	116.9
75°	88.6	87.4	87.4	87.4	87.4	87.4	88.6	89.2	89.8	91.7	92.8
77.5°	67.5	66.9	66.3	65.8	66.3	66.9	67.5	67.7	68.6	69.0	70.3
80°	53.4	52.8	52.2	52.2	52.2	52.8	53.4	54.0	54.0	55.8	55.2
82.5°	40.8	40.2	40.1	39.6	40.1	40.2	40.8	40.9	40.9	42.2	42.1
85°	21.9	22.5	21.9	23.1	21.9	22.5	21.9	21.2	21.9	23.1	23.1
87.5°	13.2	12.8	13.2	12.8	13.2	12.8	13.2	13.2	13.6	13.7	13.8
90°	34.2	34.5	34.7	34.9	34.7	34.5	34.2	34.0	34.1	34.6	35.0
92.5°	33.1	33.2	33.3	33.3	33.3	33.2	33.1	33.1	33.0	33.0	32.9
95°	65.0	64.6	64.2	63.7	64.2	64.6	65.0	65.5	65.8	65.8	65.8
97.5°	110.4	110.4	110.4	110.4	110.4	110.4	110.4	110.5	110.5	110.5	110.5
100°	141.4	141.2	140.9	140.7	140.9	141.2	141.4	141.6	141.7	141.7	141.7
102.5°	175.9	175.7	175.5	175.2	175.5	175.7	175.9	176.2	176.2	176.0	175.8
105°	228.1	228.1	228.1	228.1	228.1	228.1	228.1	228.1	227.8	227.4	226.9
107.5°	280.9	279.9	278.8	277.7	278.8	279.9	280.9	281.9	282.4	282.2	282.0
110°	318.5	317.7	317.0	316.4	317.0	317.7	318.5	319.1	319.5	319.5	319.5



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	354.8	354.3	353.9	353.3	353.9	354.3	354.8	355.4	355.8	356.4	357.0
115°	413.0	412.3	411.5	410.9	411.5	412.3	413.0	413.6	414.1	414.3	414.5
117.5°	467.8	467.1	466.4	465.7	466.4	467.1	467.8	468.5	469.1	469.6	470.2
120°	506.4	505.7	505.0	504.4	505.0	505.7	506.4	507.1	507.4	507.4	507.4
122.5°	543.7	543.1	542.6	542.2	542.6	543.1	543.7	544.2	544.7	545.3	545.8
125°	600.6	600.3	600.1	599.8	600.1	600.3	600.6	600.8	601.3	601.9	602.6
127.5°	654.7	653.9	653.2	652.4	653.2	653.9	654.7	655.4	656.2	657.0	657.8
130°	693.0	692.1	691.2	690.2	691.2	692.1	693.0	694.0	694.6	695.1	695.5
132.5°	728.6	727.9	727.1	726.4	727.1	727.9	728.6	729.4	730.2	731.2	732.2
135°	784.7	784.1	783.4	782.7	783.4	784.1	784.7	785.4	785.9	786.2	786.4
137.5°	836.4	835.5	834.6	833.7	834.6	835.5	836.4	837.3	837.9	838.0	838.2
140°	871.7	870.8	869.9	869.0	869.9	870.8	871.7	872.7	873.1	873.1	873.1
142.5°	903.8	902.9	902.0	901.0	902.0	902.9	903.8	904.7	905.1	904.9	904.7
145°	951.9	950.9	950.1	949.1	950.1	950.9	951.9	952.8	953.1	952.9	952.7
147.5°	994.7	993.8	992.9	992.0	992.9	993.8	994.7	995.5	995.7	995.2	994.7
150°	1022.1	1021.4	1020.6	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4
152.5°	1048.8	1048.1	1047.2	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1
155°	1083.7	1083.0	1082.3	1081.6	1082.3	1083.0	1083.7	1084.3	1084.1	1083.0	1081.9
157.5°	1115.3	1114.2	1113.1	1112.0	1113.1	1114.2	1115.3	1116.4	1116.2	1114.6	1113.1
160°	1133.7	1132.7	1131.9	1130.9	1131.9	1132.7	1133.7	1134.6	1134.3	1133.0	1131.6
162.5°	1150.6	1149.5	1148.4	1147.4	1148.4	1149.5	1150.6	1151.8	1151.5	1149.9	1148.4
165°	1172.4	1171.2	1170.1	1168.9	1170.1	1171.2	1172.4	1173.5	1173.3	1171.6	1170.1
167.5°	1190.2	1189.0	1187.8	1186.6	1187.8	1189.0	1190.2	1191.4	1191.1	1189.5	1188.0
170°	1199.8	1198.4	1197.0	1195.6	1197.0	1198.4	1199.8	1201.1	1201.0	1199.4	1197.8
172.5°	1207.1	1205.8	1204.4	1203.0	1204.4	1205.8	1207.1	1208.5	1208.4	1206.8	1205.2
175°	1215.1	1213.8	1212.4	1211.0	1212.4	1213.8	1215.1	1216.6	1216.4	1214.8	1213.2
177.5°	1218.1	1217.0	1215.8	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1680.1	1686.9	1697.1	1702.9	1712.6	1719.0	1722.4	1728.6	1732.0	1744.2	1756.8
5°	1586.3	1595.9	1613.0	1628.7	1645.8	1663.3	1676.1	1690.7	1704.0	1727.0	1751.4
7.5°	1478.7	1492.2	1518.5	1543.6	1573.3	1598.1	1620.1	1645.0	1667.2	1700.3	1734.7
10°	1398.0	1421.7	1456.3	1480.0	1518.9	1543.7	1578.3	1605.7	1636.6	1680.3	1719.2
12.5°	1328.6	1357.2	1385.0	1417.8	1452.8	1494.2	1532.2	1567.3	1604.1	1649.2	1694.9
15°	1202.6	1243.9	1287.0	1320.3	1367.7	1411.4	1455.7	1503.1	1548.0	1602.0	1661.5
17.5°	1040.4	1088.2	1160.7	1217.9	1273.5	1317.3	1372.2	1429.5	1482.4	1547.6	1613.8
20°	967.0	1002.3	1051.4	1128.5	1212.3	1259.0	1314.9	1378.0	1438.7	1509.7	1580.8
22.5°	908.2	939.6	979.1	1039.2	1132.7	1196.4	1254.7	1318.7	1389.2	1461.7	1540.5
25°	824.3	846.2	887.5	936.0	1000.4	1105.4	1169.2	1233.5	1310.0	1387.7	1477.6
27.5°	761.4	781.0	807.9	854.2	902.1	977.5	1078.9	1149.1	1225.3	1312.7	1406.0
30°	713.3	736.3	766.1	798.9	851.1	910.0	1011.4	1092.7	1168.0	1257.8	1357.4
32.5°	678.3	696.6	721.9	755.2	798.7	855.1	936.0	1034.9	1108.3	1202.9	1306.9
35°	621.0	642.3	662.9	694.5	729.7	781.3	842.6	948.2	1021.0	1114.5	1218.9
37.5°	573.8	586.8	609.6	634.6	671.8	710.3	763.4	858.2	936.9	1028.7	1135.6
40°	537.8	554.2	571.2	599.1	629.5	666.5	718.7	789.2	879.6	969.5	1073.9
42.5°	502.9	523.6	541.6	560.3	593.6	630.6	673.1	732.8	825.2	910.2	1011.7
45°	460.7	474.1	492.9	513.6	540.9	572.4	610.1	662.3	750.9	824.3	919.7
47.5°	411.7	431.3	443.5	463.7	489.6	519.8	554.8	599.9	671.6	740.5	828.9
50°	378.2	398.2	415.8	434.0	457.1	486.2	515.4	559.1	616.8	689.0	771.6
52.5°	349.5	367.2	384.3	402.5	425.1	451.8	479.4	517.8	567.2	633.7	713.8
55°	310.2	321.2	338.7	357.0	377.0	402.5	429.2	461.4	503.8	559.7	624.6
57.5°	269.9	282.5	296.5	314.8	335.1	354.7	378.7	407.8	441.3	491.9	547.5
60°	247.1	256.7	268.3	287.2	305.9	323.5	346.7	370.9	402.5	446.2	493.5
62.5°	221.8	231.1	241.6	258.0	276.3	292.5	312.6	338.3	365.1	404.9	446.4
65°	179.7	193.1	203.4	217.9	233.1	250.1	265.9	286.5	310.2	341.7	378.8
67.5°	149.0	155.7	165.3	178.6	194.2	208.7	223.6	239.8	260.3	284.7	314.1
70°	135.4	137.8	139.7	152.3	166.9	181.5	195.5	210.6	228.2	248.3	273.8
72.5°	119.4	121.8	124.1	129.5	141.2	155.7	170.2	181.5	198.1	214.8	235.4
75°	94.7	98.3	100.1	103.2	107.4	117.2	130.6	141.4	151.1	163.9	180.3
77.5°	72.1	74.1	76.1	79.3	82.0	86.4	94.0	103.8	112.9	120.3	131.6
80°	57.0	57.7	60.1	61.3	65.0	68.0	71.6	79.5	88.6	91.7	99.6
82.5°	43.0	43.6	45.6	46.7	48.5	51.0	55.6	57.7	64.8	68.8	73.8
85°	23.7	23.1	24.9	24.9	26.1	27.3	28.5	31.5	33.4	38.3	39.5
87.5°	14.4	14.5	13.9	12.9	12.0	11.9	11.6	11.6	12.0	12.9	14.3
90°	35.5	36.0	30.9	25.9	20.9	15.8	12.0	9.3	6.5	3.8	1.0
92.5°	32.7	32.6	31.4	30.3	29.1	27.9	26.3	24.3	22.3	20.3	18.3
95°	65.8	65.8	65.3	64.8	64.4	63.9	62.6	60.3	58.0	55.7	53.4
97.5°	110.5	110.5	109.6	108.8	107.9	107.0	105.6	103.6	101.6	99.6	97.6
100°	141.7	141.7	141.1	140.4	139.7	139.0	137.8	135.9	134.1	132.3	130.5
102.5°	175.6	175.5	174.6	173.7	172.9	172.0	170.8	169.4	167.9	166.4	164.9
105°	226.4	226.0	225.5	225.1	224.6	224.2	223.6	222.9	222.2	221.5	220.9
107.5°	281.9	281.6	281.6	281.6	281.6	281.6	281.1	280.1	279.2	278.1	277.1
110°	319.5	319.5	319.5	319.5	319.5	319.5	318.8	317.4	316.0	314.7	313.3



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	357.5	358.1	358.2	358.5	358.6	358.8	358.2	356.9	355.5	354.1	352.8
115°	414.8	414.9	415.4	415.9	416.4	416.8	416.4	414.9	413.6	412.3	410.9
117.5°	470.7	471.3	472.5	473.8	475.1	476.4	476.1	474.3	472.5	470.6	468.8
120°	507.4	507.4	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4
122.5°	546.3	546.8	548.1	549.5	550.7	552.0	551.5	549.3	547.2	544.9	542.7
125°	603.3	604.0	604.7	605.4	606.0	606.7	606.0	604.0	601.9	599.8	597.8
127.5°	658.6	659.4	660.3	661.1	661.9	662.7	661.9	659.3	656.6	654.0	651.4
130°	695.9	696.4	696.9	697.4	697.8	698.2	697.0	694.0	691.1	688.1	685.2
132.5°	733.2	734.2	734.1	734.0	734.0	733.9	732.6	730.2	727.8	725.3	722.9
135°	786.6	786.8	786.4	785.9	785.4	785.0	783.5	781.0	778.5	775.9	773.5
137.5°	838.4	838.6	838.0	837.4	836.8	836.2	834.9	832.8	830.8	828.7	826.6
140°	873.1	873.1	872.0	870.8	869.7	868.5	867.0	864.9	862.8	860.8	858.7
142.5°	904.5	904.4	903.6	902.8	902.0	901.2	899.8	897.8	895.7	893.7	891.6
145°	952.4	952.2	950.9	949.4	948.1	946.7	945.2	943.6	942.1	940.5	938.8
147.5°	994.2	993.7	992.8	991.9	990.9	990.1	988.6	986.7	984.8	982.9	981.0
150°	1020.6	1020.0	1019.1	1018.2	1017.2	1016.4	1015.2	1013.8	1012.5	1011.1	1009.7
152.5°	1047.2	1046.3	1045.2	1044.1	1043.0	1041.9	1040.7	1039.3	1037.9	1036.6	1035.2
155°	1080.7	1079.6	1078.9	1078.2	1077.5	1076.8	1076.2	1075.5	1074.8	1074.1	1073.4
157.5°	1111.5	1110.0	1109.5	1109.1	1108.7	1108.3	1107.9	1107.5	1107.0	1106.5	1106.0
160°	1130.2	1128.9	1128.6	1128.4	1128.1	1128.0	1127.6	1127.2	1126.7	1126.2	1125.8
162.5°	1146.8	1145.3	1145.1	1144.9	1144.6	1144.4	1144.2	1144.1	1144.1	1144.0	1143.8
165°	1168.5	1166.9	1166.9	1166.9	1166.9	1166.9	1167.0	1167.2	1167.4	1167.7	1167.9
167.5°	1186.4	1184.7	1184.8	1184.9	1184.9	1184.9	1185.3	1186.0	1186.7	1187.3	1188.0
170°	1196.2	1194.6	1194.8	1195.1	1195.3	1195.6	1196.0	1196.7	1197.4	1198.0	1198.7
172.5°	1203.6	1202.0	1202.2	1202.5	1202.7	1202.9	1203.4	1204.0	1204.8	1205.5	1206.1
175°	1211.6	1210.0	1210.5	1210.9	1211.4	1211.9	1212.4	1213.1	1213.8	1214.5	1215.1
177.5°	1215.8	1214.7	1215.1	1215.4	1215.8	1216.2	1216.6	1217.2	1217.7	1218.3	1218.9
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1757.3	1758.7	1768.5	1772.8	1781.6	1784.9	1788.9	1787.9	1787.9	1789.9	1803.4
5°	1761.1	1773.2	1791.4	1809.0	1826.1	1840.6	1850.3	1860.0	1863.7	1881.3	1897.0
7.5°	1754.8	1777.1	1807.2	1834.1	1866.2	1891.3	1912.2	1931.0	1943.9	1969.5	1995.7
10°	1746.5	1778.1	1812.0	1846.7	1890.9	1924.4	1958.4	1984.5	1993.0	2031.2	2053.1
12.5°	1730.0	1772.3	1815.4	1860.3	1903.6	1949.6	1987.0	2013.1	2043.0	2077.3	2117.7
15°	1705.3	1753.8	1810.2	1867.9	1929.8	1985.7	2025.8	2071.2	2104.0	2141.7	2176.9
17.5°	1669.7	1732.2	1804.0	1870.7	1942.4	2002.3	2057.5	2101.1	2124.2	2145.7	2150.9
20°	1641.5	1708.9	1793.3	1872.2	1943.8	2013.0	2067.6	2104.0	2110.1	2110.7	2078.5
22.5°	1610.9	1687.0	1775.3	1856.2	1941.9	2018.8	2061.3	2076.9	2052.8	2011.7	1949.4
25°	1554.7	1642.7	1745.3	1837.5	1931.0	2003.9	2018.5	1991.2	1906.8	1818.1	1705.8
27.5°	1493.7	1592.7	1702.6	1805.2	1904.8	1950.0	1918.5	1820.0	1668.1	1536.0	1375.9
30°	1449.1	1560.1	1668.2	1782.9	1875.2	1894.6	1822.4	1677.3	1500.0	1300.9	1141.3
32.5°	1398.0	1514.5	1633.2	1751.8	1829.1	1810.1	1690.8	1512.2	1304.3	1108.6	957.7
35°	1325.2	1445.4	1573.5	1692.5	1741.6	1659.7	1481.2	1248.7	1036.3	853.5	749.7
37.5°	1241.0	1372.0	1505.1	1614.4	1610.9	1474.3	1231.2	991.2	812.6	704.6	630.6
40°	1181.3	1313.7	1457.5	1549.8	1510.4	1332.5	1069.1	842.6	712.1	625.9	571.9
42.5°	1124.0	1256.9	1399.8	1473.1	1404.5	1185.8	923.4	745.9	638.3	571.0	527.2
45°	1026.5	1166.7	1299.1	1339.7	1217.1	976.1	746.7	618.0	546.4	496.5	466.2
47.5°	931.2	1069.1	1189.9	1190.6	1024.8	791.6	629.9	534.8	473.6	435.1	413.0
50°	872.9	1004.1	1105.4	1089.6	901.5	704.2	563.3	481.4	430.4	400.7	377.6
52.5°	807.4	934.6	1022.4	977.5	797.1	619.6	503.6	434.7	392.5	366.6	346.0
55°	712.1	825.0	886.9	818.9	650.1	515.4	425.6	371.5	339.9	318.1	300.5
57.5°	618.5	711.6	750.6	671.4	535.5	427.4	360.0	319.4	288.1	272.4	263.3
60°	559.7	639.2	666.5	579.2	465.6	373.9	318.7	281.1	258.0	247.7	238.6
62.5°	501.9	566.9	578.1	498.0	405.9	327.3	279.9	248.0	232.7	222.9	214.3
65°	416.5	463.2	457.7	393.4	321.2	259.8	225.2	205.8	194.2	180.3	165.1
67.5°	342.9	371.4	354.2	305.9	245.1	201.9	179.4	164.6	150.3	137.0	133.6
70°	296.3	312.6	294.5	250.1	200.9	169.4	151.1	133.6	125.1	122.0	116.5
72.5°	251.6	257.3	237.6	199.6	163.5	140.2	122.5	112.6	108.1	105.5	102.0
75°	188.8	184.6	167.5	137.8	113.5	97.8	92.3	88.6	85.6	83.2	81.4
77.5°	132.6	126.4	111.2	91.8	79.1	71.5	68.2	66.3	64.8	63.6	61.8
80°	99.6	95.3	80.2	65.6	60.1	56.5	54.7	52.2	52.2	51.0	49.2
82.5°	72.9	68.1	54.9	48.1	45.1	42.9	41.5	40.1	39.6	39.8	38.5
85°	38.3	31.0	27.3	26.1	24.3	23.1	23.7	22.5	22.5	22.5	21.9
87.5°	12.4	10.5	10.6	10.6	11.9	12.9	13.5	14.4	15.9	15.4	15.8
90°	3.8	6.5	9.3	12.0	15.8	20.9	25.9	30.9	36.0	35.5	35.0
92.5°	20.3	22.3	24.3	26.3	27.9	29.1	30.3	31.4	32.6	32.7	32.9
95°	55.7	58.0	60.3	62.6	63.9	64.4	64.8	65.3	65.8	65.8	65.8
97.5°	99.6	101.6	103.6	105.6	107.0	107.9	108.8	109.6	110.5	110.5	110.5
100°	132.3	134.1	135.9	137.8	139.0	139.7	140.4	141.1	141.7	141.7	141.7
102.5°	166.4	167.9	169.4	170.8	172.0	172.9	173.7	174.6	175.5	175.6	175.8
105°	221.5	222.2	222.9	223.6	224.2	224.6	225.1	225.5	226.0	226.4	226.9
107.5°	278.1	279.2	280.1	281.1	281.6	281.6	281.6	281.6	281.6	281.9	282.0
110°	314.7	316.0	317.4	318.8	319.5	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	354.1	355.5	356.9	358.2	358.8	358.6	358.5	358.2	358.1	357.5	357.0
115°	412.3	413.6	414.9	416.4	416.8	416.4	415.9	415.4	414.9	414.8	414.5
117.5°	470.6	472.5	474.3	476.1	476.4	475.1	473.8	472.5	471.3	470.7	470.2
120°	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	507.4	507.4
122.5°	544.9	547.2	549.3	551.5	552.0	550.7	549.5	548.1	546.8	546.3	545.8
125°	599.8	601.9	604.0	606.0	606.7	606.0	605.4	604.7	604.0	603.3	602.6
127.5°	654.0	656.6	659.3	661.9	662.7	661.9	661.1	660.3	659.4	658.6	657.8
130°	688.1	691.1	694.0	697.0	698.2	697.8	697.4	696.9	696.4	695.9	695.5
132.5°	725.3	727.8	730.2	732.6	733.9	734.0	734.0	734.1	734.2	733.2	732.2
135°	775.9	778.5	781.0	783.5	785.0	785.4	785.9	786.4	786.8	786.6	786.4
137.5°	828.7	830.8	832.8	834.9	836.2	836.8	837.4	838.0	838.6	838.4	838.2
140°	860.8	862.8	864.9	867.0	868.5	869.7	870.8	872.0	873.1	873.1	873.1
142.5°	893.7	895.7	897.8	899.8	901.2	902.0	902.8	903.6	904.4	904.5	904.7
145°	940.5	942.1	943.6	945.2	946.7	948.1	949.4	950.9	952.2	952.4	952.7
147.5°	982.9	984.8	986.7	988.6	990.1	990.9	991.9	992.8	993.7	994.2	994.7
150°	1011.1	1012.5	1013.8	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6	1021.4
152.5°	1036.6	1037.9	1039.3	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2	1048.1
155°	1074.1	1074.8	1075.5	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7	1081.9
157.5°	1106.5	1107.0	1107.5	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5	1113.1
160°	1126.2	1126.7	1127.2	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2	1131.6
162.5°	1144.0	1144.1	1144.1	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8	1148.4
165°	1167.7	1167.4	1167.2	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5	1170.1
167.5°	1187.3	1186.7	1186.0	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4	1188.0
170°	1198.0	1197.4	1196.7	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2	1197.8
172.5°	1205.5	1204.8	1204.0	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6	1205.2
175°	1214.5	1213.8	1213.1	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6	1213.2
177.5°	1218.3	1217.7	1217.2	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8	1217.0
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1808.3	1814.6	1817.5	1817.5	1820.9	1819.5	1818.0
5°	1912.2	1923.7	1926.2	1937.1	1945.0	1942.6	1943.8
7.5°	2015.5	2034.1	2052.5	2060.9	2062.1	2067.0	2068.9
10°	2079.2	2094.4	2122.9	2118.6	2139.8	2152.0	2132.0
12.5°	2140.3	2160.8	2180.6	2186.1	2198.1	2202.0	2194.1
15°	2195.7	2206.6	2207.9	2204.8	2208.4	2205.4	2193.9
17.5°	2144.0	2126.3	2090.3	2073.3	2059.8	2039.9	2031.9
20°	2058.5	2006.3	1945.6	1921.4	1892.8	1836.9	1850.3
22.5°	1874.0	1814.5	1753.8	1682.9	1649.0	1596.1	1592.9
25°	1586.8	1484.2	1371.3	1292.4	1246.3	1193.5	1170.4
27.5°	1233.7	1104.6	1012.1	965.2	922.6	880.7	879.0
30°	1001.6	904.5	832.9	792.8	766.7	749.1	752.7
32.5°	844.3	777.8	729.4	696.2	676.8	663.6	663.4
35°	690.2	644.7	613.7	599.8	585.8	576.1	576.7
37.5°	590.7	563.3	546.1	530.7	522.0	517.2	514.5
40°	539.6	517.2	503.8	494.7	487.4	480.8	479.6
42.5°	499.4	480.8	467.5	460.3	453.4	448.8	447.5
45°	443.1	427.9	415.8	408.0	404.9	400.7	400.7
47.5°	394.2	379.3	369.8	364.9	359.7	356.8	356.7
50°	361.2	349.7	341.2	338.1	333.9	332.1	331.4
52.5°	331.6	323.0	316.9	314.8	313.0	310.7	311.1
55°	291.4	286.5	284.1	282.3	279.2	275.6	278.1
57.5°	257.5	253.4	246.8	241.1	238.4	235.8	236.8
60°	233.7	225.2	216.7	210.0	208.2	202.7	202.7
62.5°	203.6	191.7	181.3	177.5	175.7	173.2	172.6
65°	156.6	151.8	149.3	146.9	145.7	145.7	144.5
67.5°	129.8	127.9	125.2	124.5	123.3	123.0	122.6
70°	114.7	112.3	111.1	110.5	109.2	109.9	108.1
72.5°	100.1	98.2	98.0	96.4	95.7	95.8	94.4
75°	78.9	78.9	78.3	77.7	76.5	75.9	76.5
77.5°	60.7	60.8	59.7	59.7	59.5	59.7	59.0
80°	48.6	49.2	48.6	47.9	47.4	47.9	47.4
82.5°	38.3	37.5	37.4	37.3	37.2	36.8	36.7
85°	21.9	22.5	21.9	21.2	21.2	21.2	21.9
87.5°	15.2	15.1	15.1	15.1	15.1	15.2	14.7
90°	34.6	34.1	34.0	34.2	34.5	34.7	34.9
92.5°	33.0	33.0	33.1	33.1	33.2	33.3	33.3
95°	65.8	65.8	65.5	65.0	64.6	64.2	63.7
97.5°	110.5	110.5	110.5	110.4	110.4	110.4	110.4
100°	141.7	141.7	141.6	141.4	141.2	140.9	140.7
102.5°	176.0	176.2	176.2	175.9	175.7	175.5	175.2
105°	227.4	227.8	228.1	228.1	228.1	228.1	228.1
107.5°	282.2	282.4	281.9	280.9	279.9	278.8	277.7
110°	319.5	319.5	319.1	318.5	317.7	317.0	316.4



TEST NUMBER: P331858-927

CATALOG NUMBER: S122RDIW-S1005D1240U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	356.4	355.8	355.4	354.8	354.3	353.9	353.3
115°	414.3	414.1	413.6	413.0	412.3	411.5	410.9
117.5°	469.6	469.1	468.5	467.8	467.1	466.4	465.7
120°	507.4	507.4	507.1	506.4	505.7	505.0	504.4
122.5°	545.3	544.7	544.2	543.7	543.1	542.6	542.2
125°	601.9	601.3	600.8	600.6	600.3	600.1	599.8
127.5°	657.0	656.2	655.4	654.7	653.9	653.2	652.4
130°	695.1	694.6	694.0	693.0	692.1	691.2	690.2
132.5°	731.2	730.2	729.4	728.6	727.9	727.1	726.4
135°	786.2	785.9	785.4	784.7	784.1	783.4	782.7
137.5°	838.0	837.9	837.3	836.4	835.5	834.6	833.7
140°	873.1	873.1	872.7	871.7	870.8	869.9	869.0
142.5°	904.9	905.1	904.7	903.8	902.9	902.0	901.0
145°	952.9	953.1	952.8	951.9	950.9	950.1	949.1
147.5°	995.2	995.7	995.5	994.7	993.8	992.9	992.0
150°	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0
152.5°	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3
155°	1083.0	1084.1	1084.3	1083.7	1083.0	1082.3	1081.6
157.5°	1114.6	1116.2	1116.4	1115.3	1114.2	1113.1	1112.0
160°	1133.0	1134.3	1134.6	1133.7	1132.7	1131.9	1130.9
162.5°	1149.9	1151.5	1151.8	1150.6	1149.5	1148.4	1147.4
165°	1171.6	1173.3	1173.5	1172.4	1171.2	1170.1	1168.9
167.5°	1189.5	1191.1	1191.4	1190.2	1189.0	1187.8	1186.6
170°	1199.4	1201.0	1201.1	1199.8	1198.4	1197.0	1195.6
172.5°	1206.8	1208.4	1208.5	1207.1	1205.8	1204.4	1203.0
175°	1214.8	1216.4	1216.6	1215.1	1213.8	1212.4	1211.0
177.5°	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2

(END OF REPORT)