

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331862-927

Luminaire Tested: **S122RDIW-S1005D1440U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331862-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6982.2 lumens  
Efficiency: N/A  
Efficacy: 84.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	89	85	82	79	71	69	67	57	56	55	45	44	43	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	41	38	35	33	31	29	25
5	69	58	50	45	63	54	47	42	45	40	36	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	37	33	38	32	29	31	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	34	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	28208	28208	28208	28208
5°	31504	28386	25167	28386
10°	34954	28186	21815	28186
15°	36672	27773	17188	27773
20°	31792	27161	14874	27161
25°	20851	26323	13279	26323
30°	14033	25307	12020	25307
35°	11367	24025	10841	24025
40°	10108	22634	10030	22634
45°	9149	21000	8953	21000
50°	8324	19381	8297	19381
55°	7828	17582	7724	17582
60°	6546	15936	6468	15936
65°	5521	14472	6262	14472
70°	5103	12925	5906	12925
75°	4772	11248	5452	11248
80°	4407	9261	4854	9261
85°	4057	7317	4279	7317



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.6	2.4
10°-20°	461.5	6.6
20°-30°	594.7	8.5
30°-40°	565.1	8.1
40°-50°	484.1	6.9
50°-60°	368.7	5.3
60°-70°	233.1	3.3
70°-80°	116.4	1.7
80°-90°	35.9	0.5
90°-100°	89.7	1.3
100°-110°	278.5	4.0
110°-120°	476.1	6.8
120°-130°	626.1	9.0
130°-140°	702.7	10.1
140°-150°	689.0	9.9
150°-160°	577.9	8.3
160°-170°	383.3	5.5
170°-180°	134.0	1.9
0°-30°	1221.8	17.5
0°-40°	1786.9	25.6
0°-60°	2639.7	37.8
0°-90°	3025.0	43.3
90°-120°	844.3	12.1
90°-150°	2862.0	41.0
90°-180°	3957.0	56.7
0°-180°	6982.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1747	1747	1747	1747	1747	
5°	1944	1751	1553	1751	1944	192
15°	2194	1662	1028	1662	2194	592
25°	1170	1478	745	1478	1170	555
35°	577	1219	550	1219	577	369
45°	401	920	392	920	401	310
55°	278	625	274	625	278	244
65°	144	379	164	379	144	147
75°	76	180	87	180	76	81
85°	22	40	23	40	22	25
90°	41	1	41	1	41	19
95°	74	62	74	62	74	83
105°	265	257	265	257	265	279
115°	478	478	478	478	478	472
125°	697	695	697	695	697	622
135°	910	899	910	899	910	700
145°	1104	1092	1104	1092	1104	689
155°	1258	1248	1258	1248	1258	579
165°	1359	1358	1359	1358	1359	383
175°	1408	1413	1408	1413	1408	134
180°	1415	1415	1415	1415	1415	



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1818.0	1819.5	1820.9	1817.5	1817.5	1814.6	1808.3	1803.4	1789.9	1787.9	1787.9
5°	1943.8	1942.6	1945.0	1937.1	1926.2	1923.7	1912.2	1897.0	1881.3	1863.7	1860.0
7.5°	2068.9	2067.0	2062.1	2060.9	2052.5	2034.1	2015.5	1995.7	1969.5	1943.9	1931.0
10°	2132.0	2152.0	2139.8	2118.6	2122.9	2094.4	2079.2	2053.1	2031.2	1993.0	1984.5
12.5°	2194.1	2202.0	2198.1	2186.1	2180.6	2160.8	2140.3	2117.7	2077.3	2043.0	2013.1
15°	2193.9	2205.4	2208.4	2204.8	2207.9	2206.6	2195.7	2176.9	2141.7	2104.0	2071.2
17.5°	2031.9	2039.9	2059.8	2073.3	2090.3	2126.3	2144.0	2150.9	2145.7	2124.2	2101.1
20°	1850.3	1836.9	1892.8	1921.4	1945.6	2006.3	2058.5	2078.5	2110.7	2110.1	2104.0
22.5°	1592.9	1596.1	1649.0	1682.9	1753.8	1814.5	1874.0	1949.4	2011.7	2052.8	2076.9
25°	1170.4	1193.5	1246.3	1292.4	1371.3	1484.2	1586.8	1705.8	1818.1	1906.8	1991.2
27.5°	879.0	880.7	922.6	965.2	1012.1	1104.6	1233.7	1375.9	1536.0	1668.1	1820.0
30°	752.7	749.1	766.7	792.8	832.9	904.5	1001.6	1141.3	1300.9	1500.0	1677.3
32.5°	663.4	663.6	676.8	696.2	729.4	777.8	844.3	957.7	1108.6	1304.3	1512.2
35°	576.7	576.1	585.8	599.8	613.7	644.7	690.2	749.7	853.5	1036.3	1248.7
37.5°	514.5	517.2	522.0	530.7	546.1	563.3	590.7	630.6	704.6	812.6	991.2
40°	479.6	480.8	487.4	494.7	503.8	517.2	539.6	571.9	625.9	712.1	842.6
42.5°	447.5	448.8	453.4	460.3	467.5	480.8	499.4	527.2	571.0	638.3	745.9
45°	400.7	400.7	404.9	408.0	415.8	427.9	443.1	466.2	496.5	546.4	618.0
47.5°	356.7	356.8	359.7	364.9	369.8	379.3	394.2	413.0	435.1	473.6	534.8
50°	331.4	332.1	333.9	338.1	341.2	349.7	361.2	377.6	400.7	430.4	481.4
52.5°	311.1	310.7	313.0	314.8	316.9	323.0	331.6	346.0	366.6	392.5	434.7
55°	278.1	275.6	279.2	282.3	284.1	286.5	291.4	300.5	318.1	339.9	371.5
57.5°	236.8	235.8	238.4	241.1	246.8	253.4	257.5	263.3	272.4	288.1	319.4
60°	202.7	202.7	208.2	210.0	216.7	225.2	233.7	238.6	247.7	258.0	281.1
62.5°	172.6	173.2	175.7	177.5	181.3	191.7	203.6	214.3	222.9	232.7	248.0
65°	144.5	145.7	145.7	146.9	149.3	151.8	156.6	165.1	180.3	194.2	205.8
67.5°	122.6	123.0	123.3	124.5	125.2	127.9	129.8	133.6	137.0	150.3	164.6
70°	108.1	109.9	109.2	110.5	111.1	112.3	114.7	116.5	122.0	125.1	133.6
72.5°	94.4	95.8	95.7	96.4	98.0	98.2	100.1	102.0	105.5	108.1	112.6
75°	76.5	75.9	76.5	77.7	78.3	78.9	78.9	81.4	83.2	85.6	88.6
77.5°	59.0	59.7	59.5	59.7	59.7	60.8	60.7	61.8	63.6	64.8	66.3
80°	47.4	47.9	47.4	47.9	48.6	49.2	48.6	49.2	51.0	52.2	52.2
82.5°	36.7	36.8	37.2	37.3	37.4	37.5	38.3	38.5	39.8	39.6	40.1
85°	21.9	21.2	21.2	21.2	21.9	22.5	21.9	21.9	22.5	22.5	22.5
87.5°	15.9	16.3	16.2	16.2	16.2	16.2	16.3	16.9	16.5	17.1	15.4
90°	40.6	40.3	40.1	39.8	39.5	39.7	40.2	40.7	41.3	41.8	36.0
92.5°	38.7	38.7	38.6	38.5	38.5	38.4	38.3	38.2	38.1	37.9	36.6
95°	74.1	74.5	75.1	75.7	76.1	76.4	76.4	76.4	76.4	76.4	75.9
97.5°	128.3	128.3	128.3	128.4	128.5	128.5	128.5	128.5	128.5	128.5	127.5
100°	163.6	163.9	164.1	164.4	164.7	164.8	164.8	164.8	164.8	164.8	164.0
102.5°	203.7	204.0	204.3	204.5	204.8	204.9	204.6	204.4	204.2	204.0	203.0
105°	265.1	265.1	265.1	265.1	265.1	264.8	264.4	263.8	263.2	262.8	262.2
107.5°	322.9	324.2	325.3	326.6	327.8	328.3	328.1	327.9	327.6	327.5	327.5
110°	367.8	368.6	369.4	370.2	371.0	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	410.8	411.4	412.0	412.6	413.1	413.8	414.4	415.0	415.7	416.3	416.5
115°	477.7	478.5	479.3	480.1	480.9	481.4	481.6	482.0	482.2	482.5	483.0
117.5°	541.5	542.2	543.0	543.8	544.6	545.4	546.1	546.7	547.3	548.0	549.4
120°	586.4	587.2	588.0	588.7	589.5	589.9	589.9	589.9	589.9	589.9	592.1
122.5°	630.3	630.9	631.5	632.1	632.6	633.3	633.9	634.5	635.2	635.8	637.3
125°	697.4	697.8	698.0	698.2	698.5	699.0	699.8	700.6	701.4	702.2	703.1
127.5°	758.6	759.5	760.3	761.1	762.0	762.9	763.8	764.8	765.7	766.8	767.7
130°	802.6	803.6	804.7	805.7	806.8	807.6	808.1	808.7	809.2	809.7	810.2
132.5°	844.5	845.4	846.3	847.2	848.0	849.0	850.2	851.4	852.5	853.7	853.6
135°	910.1	910.9	911.6	912.4	913.2	913.8	914.0	914.3	914.6	914.8	914.3
137.5°	969.2	970.3	971.4	972.5	973.5	974.1	974.4	974.5	974.8	975.0	974.3
140°	1010.3	1011.4	1012.5	1013.5	1014.6	1015.1	1015.1	1015.1	1015.1	1015.1	1013.8
142.5°	1047.6	1048.7	1049.7	1050.8	1051.9	1052.3	1052.1	1051.9	1051.6	1051.5	1050.5
145°	1103.5	1104.5	1105.6	1106.7	1107.7	1108.1	1107.9	1107.6	1107.3	1107.1	1105.5
147.5°	1153.4	1154.4	1155.4	1156.4	1157.5	1157.7	1157.1	1156.5	1156.0	1155.3	1154.3
150°	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9	1184.9
152.5°	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5	1215.2
155°	1257.6	1258.4	1259.2	1260.0	1260.8	1260.4	1259.2	1257.8	1256.5	1255.1	1254.3
157.5°	1292.9	1294.2	1295.5	1296.7	1298.0	1297.8	1295.9	1294.1	1292.3	1290.5	1290.1
160°	1314.9	1316.0	1317.0	1318.0	1319.1	1318.8	1317.2	1315.7	1314.1	1312.5	1312.2
162.5°	1334.0	1335.3	1336.6	1337.8	1339.1	1338.8	1337.0	1335.2	1333.4	1331.6	1331.3
165°	1359.1	1360.4	1361.8	1363.0	1364.4	1364.1	1362.2	1360.4	1358.5	1356.7	1356.7
167.5°	1379.6	1381.0	1382.4	1383.8	1385.1	1384.9	1383.1	1381.2	1379.3	1377.4	1377.5
170°	1390.1	1391.7	1393.3	1394.9	1396.5	1396.4	1394.5	1392.7	1390.8	1388.9	1389.2
172.5°	1398.8	1400.3	1401.9	1403.5	1405.1	1404.9	1403.1	1401.2	1399.4	1397.5	1397.8
175°	1408.0	1409.6	1411.2	1412.8	1414.4	1414.3	1412.4	1410.6	1408.7	1406.8	1407.4
177.5°	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3	1412.8
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1788.9	1784.9	1781.6	1772.8	1768.5	1758.7	1757.3	1756.8	1744.2	1732.0	1728.6
5°	1850.3	1840.6	1826.1	1809.0	1791.4	1773.2	1761.1	1751.4	1727.0	1704.0	1690.7
7.5°	1912.2	1891.3	1866.2	1834.1	1807.2	1777.1	1754.8	1734.7	1700.3	1667.2	1645.0
10°	1958.4	1924.4	1890.9	1846.7	1812.0	1778.1	1746.5	1719.2	1680.3	1636.6	1605.7
12.5°	1987.0	1949.6	1903.6	1860.3	1815.4	1772.3	1730.0	1694.9	1649.2	1604.1	1567.3
15°	2025.8	1985.7	1929.8	1867.9	1810.2	1753.8	1705.3	1661.5	1602.0	1548.0	1503.1
17.5°	2057.5	2002.3	1942.4	1870.7	1804.0	1732.2	1669.7	1613.8	1547.6	1482.4	1429.5
20°	2067.6	2013.0	1943.8	1872.2	1793.3	1708.9	1641.5	1580.8	1509.7	1438.7	1378.0
22.5°	2061.3	2018.8	1941.9	1856.2	1775.3	1687.0	1610.9	1540.5	1461.7	1389.2	1318.7
25°	2018.5	2003.9	1931.0	1837.5	1745.3	1642.7	1554.7	1477.6	1387.7	1310.0	1233.5
27.5°	1918.5	1950.0	1904.8	1805.2	1702.6	1592.7	1493.7	1406.0	1312.7	1225.3	1149.1
30°	1822.4	1894.6	1875.2	1782.9	1668.2	1560.1	1449.1	1357.4	1257.8	1168.0	1092.7
32.5°	1690.8	1810.1	1829.1	1751.8	1633.2	1514.5	1398.0	1306.9	1202.9	1108.3	1034.9
35°	1481.2	1659.7	1741.6	1692.5	1573.5	1445.4	1325.2	1218.9	1114.5	1021.0	948.2
37.5°	1231.2	1474.3	1610.9	1614.4	1505.1	1372.0	1241.0	1135.6	1028.7	936.9	858.2
40°	1069.1	1332.5	1510.4	1549.8	1457.5	1313.7	1181.3	1073.9	969.5	879.6	789.2
42.5°	923.4	1185.8	1404.5	1473.1	1399.8	1256.9	1124.0	1011.7	910.2	825.2	732.8
45°	746.7	976.1	1217.1	1339.7	1299.1	1166.7	1026.5	919.7	824.3	750.9	662.3
47.5°	629.9	791.6	1024.8	1190.6	1189.9	1069.1	931.2	828.9	740.5	671.6	599.9
50°	563.3	704.2	901.5	1089.6	1105.4	1004.1	872.9	771.6	689.0	616.8	559.1
52.5°	503.6	619.6	797.1	977.5	1022.4	934.6	807.4	713.8	633.7	567.2	517.8
55°	425.6	515.4	650.1	818.9	886.9	825.0	712.1	624.6	559.7	503.8	461.4
57.5°	360.0	427.4	535.5	671.4	750.6	711.6	618.5	547.5	491.9	441.3	407.8
60°	318.7	373.9	465.6	579.2	666.5	639.2	559.7	493.5	446.2	402.5	370.9
62.5°	279.9	327.3	405.9	498.0	578.1	566.9	501.9	446.4	404.9	365.1	338.3
65°	225.2	259.8	321.2	393.4	457.7	463.2	416.5	378.8	341.7	310.2	286.5
67.5°	179.4	201.9	245.1	305.9	354.2	371.4	342.9	314.1	284.7	260.3	239.8
70°	151.1	169.4	200.9	250.1	294.5	312.6	296.3	273.8	248.3	228.2	210.6
72.5°	122.5	140.2	163.5	199.6	237.6	257.3	251.6	235.4	214.8	198.1	181.5
75°	92.3	97.8	113.5	137.8	167.5	184.6	188.8	180.3	163.9	151.1	141.4
77.5°	68.2	71.5	79.1	91.8	111.2	126.4	132.6	131.6	120.3	112.9	103.8
80°	54.7	56.5	60.1	65.6	80.2	95.3	99.6	99.6	91.7	88.6	79.5
82.5°	41.5	42.9	45.1	48.1	54.9	68.1	72.9	73.8	68.8	64.8	57.7
85°	23.7	23.1	24.3	26.1	27.3	31.0	38.3	39.5	38.3	33.4	31.5
87.5°	14.3	13.6	12.4	11.0	10.9	10.8	12.5	14.3	13.0	12.2	11.9
90°	30.1	24.3	18.5	13.9	10.8	7.5	4.4	1.2	4.4	7.5	10.8
92.5°	35.3	33.8	32.5	30.6	28.3	25.9	23.6	21.2	23.6	25.9	28.3
95°	75.3	74.9	74.3	72.7	70.0	67.4	64.7	62.1	64.7	67.4	70.0
97.5°	126.5	125.5	124.5	122.8	120.5	118.1	115.8	113.4	115.8	118.1	120.5
100°	163.2	162.4	161.6	160.2	158.0	155.9	153.8	151.7	153.8	155.9	158.0
102.5°	201.9	201.0	199.9	198.6	196.9	195.2	193.5	191.8	193.5	195.2	196.9
105°	261.7	261.2	260.6	259.9	259.1	258.3	257.5	256.7	257.5	258.3	259.1
107.5°	327.5	327.5	327.5	326.9	325.7	324.6	323.4	322.2	323.4	324.6	325.7
110°	371.5	371.5	371.5	370.6	369.0	367.4	365.8	364.2	365.8	367.4	369.0





TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.8	416.9	417.2	416.5	414.9	413.3	411.7	410.1	411.7	413.3	414.9
115°	483.5	484.1	484.6	484.1	482.5	480.9	479.3	477.7	479.3	480.9	482.5
117.5°	550.9	552.4	553.9	553.6	551.4	549.3	547.2	545.1	547.2	549.3	551.4
120°	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	592.1	594.2	596.4
122.5°	638.8	640.3	641.7	641.3	638.7	636.1	633.6	631.1	633.6	636.1	638.7
125°	703.9	704.6	705.4	704.6	702.2	699.8	697.4	695.1	697.4	699.8	702.2
127.5°	768.7	769.6	770.6	769.5	766.5	763.4	760.4	757.4	760.4	763.4	766.5
130°	810.8	811.3	811.8	810.4	806.9	803.5	800.0	796.5	800.0	803.5	806.9
132.5°	853.4	853.3	853.3	851.8	849.0	846.1	843.4	840.5	843.4	846.1	849.0
135°	913.8	913.2	912.7	910.9	908.0	905.1	902.2	899.3	902.2	905.1	908.0
137.5°	973.6	973.0	972.2	970.7	968.3	965.9	963.5	961.2	963.5	965.9	968.3
140°	1012.5	1011.1	1009.8	1008.0	1005.6	1003.2	1000.8	998.4	1000.8	1003.2	1005.6
142.5°	1049.6	1048.7	1047.8	1046.2	1043.8	1041.4	1039.0	1036.6	1039.0	1041.4	1043.8
145°	1103.9	1102.3	1100.7	1099.0	1097.1	1095.3	1093.4	1091.5	1093.4	1095.3	1097.1
147.5°	1153.2	1152.1	1151.1	1149.5	1147.2	1144.9	1142.7	1140.5	1142.7	1144.9	1147.2
150°	1183.8	1182.7	1181.6	1180.4	1178.8	1177.2	1175.5	1173.9	1175.5	1177.2	1178.8
152.5°	1213.9	1212.7	1211.4	1210.0	1208.3	1206.7	1205.1	1203.6	1205.1	1206.7	1208.3
155°	1253.5	1252.8	1252.0	1251.2	1250.4	1249.6	1248.8	1248.0	1248.8	1249.6	1250.4
157.5°	1289.6	1289.1	1288.6	1288.1	1287.6	1287.1	1286.5	1285.9	1286.5	1287.1	1287.6
160°	1311.9	1311.7	1311.5	1311.1	1310.5	1310.0	1309.5	1308.9	1309.5	1310.0	1310.5
162.5°	1331.1	1330.8	1330.5	1330.4	1330.2	1330.2	1330.1	1329.9	1330.1	1330.2	1330.2
165°	1356.7	1356.7	1356.7	1356.8	1357.1	1357.3	1357.6	1357.9	1357.6	1357.3	1357.1
167.5°	1377.6	1377.6	1377.7	1378.1	1378.9	1379.7	1380.5	1381.2	1380.5	1379.7	1378.9
170°	1389.5	1389.7	1390.0	1390.5	1391.3	1392.1	1392.9	1393.7	1392.9	1392.1	1391.3
172.5°	1398.0	1398.4	1398.6	1399.2	1399.9	1400.7	1401.5	1402.3	1401.5	1400.7	1399.9
175°	1407.9	1408.4	1409.0	1409.6	1410.4	1411.2	1412.0	1412.8	1412.0	1411.2	1410.4
177.5°	1413.2	1413.6	1414.0	1414.6	1415.2	1415.9	1416.5	1417.1	1416.5	1415.9	1415.2
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1722.4	1719.0	1712.6	1702.9	1697.1	1686.9	1680.1	1683.9	1685.0	1683.9	1683.0
5°	1676.1	1663.3	1645.8	1628.7	1613.0	1595.9	1586.3	1582.0	1573.5	1568.6	1566.2
7.5°	1620.1	1598.1	1573.3	1543.6	1518.5	1492.2	1478.7	1472.0	1454.6	1445.2	1436.9
10°	1578.3	1543.7	1518.9	1480.0	1456.3	1421.7	1398.0	1398.7	1375.0	1361.6	1351.9
12.5°	1532.2	1494.2	1452.8	1417.8	1385.0	1357.2	1328.6	1317.1	1292.0	1279.1	1252.8
15°	1455.7	1411.4	1367.7	1320.3	1287.0	1243.9	1202.6	1152.2	1111.5	1076.3	1066.6
17.5°	1372.2	1317.3	1273.5	1217.9	1160.7	1088.2	1040.4	1011.1	986.6	968.0	954.2
20°	1314.9	1259.0	1212.3	1128.5	1051.4	1002.3	967.0	944.6	919.1	899.0	888.1
22.5°	1254.7	1196.4	1132.7	1039.2	979.1	939.6	908.2	882.4	865.1	849.5	839.6
25°	1169.2	1105.4	1000.4	936.0	887.5	846.2	824.3	808.6	790.4	769.1	759.5
27.5°	1078.9	977.5	902.1	854.2	807.9	781.0	761.4	737.8	721.5	711.9	701.9
30°	1011.4	910.0	851.1	798.9	766.1	736.3	713.3	700.0	684.1	667.7	661.1
32.5°	936.0	855.1	798.7	755.2	721.9	696.6	678.3	656.7	645.3	635.3	621.2
35°	842.6	781.3	729.7	694.5	662.9	642.3	621.0	608.2	587.6	579.2	573.7
37.5°	763.4	710.3	671.8	634.6	609.6	586.8	573.8	553.5	544.5	532.7	521.3
40°	718.7	666.5	629.5	599.1	571.2	554.2	537.8	521.5	508.1	502.6	488.7
42.5°	673.1	630.6	593.6	560.3	541.6	523.6	502.9	490.8	477.1	468.2	459.5
45°	610.1	572.4	540.9	513.6	492.9	474.1	460.7	440.7	432.8	415.3	408.0
47.5°	554.8	519.8	489.6	463.7	443.5	431.3	411.7	396.0	383.4	372.6	363.3
50°	515.4	486.2	457.1	434.0	415.8	398.2	378.2	370.3	350.9	345.4	339.9
52.5°	479.4	451.8	425.1	402.5	384.3	367.2	349.5	339.2	326.1	320.7	316.6
55°	429.2	402.5	377.0	357.0	338.7	321.2	310.2	297.5	291.4	287.2	282.3
57.5°	378.7	354.7	335.1	314.8	296.5	282.5	269.9	262.2	256.0	250.3	244.5
60°	346.7	323.5	305.9	287.2	268.3	256.7	247.1	238.0	230.7	222.2	219.8
62.5°	312.6	292.5	276.3	258.0	241.6	231.1	221.8	213.2	204.5	192.1	188.7
65°	265.9	250.1	233.1	217.9	203.4	193.1	179.7	170.0	166.4	165.1	164.5
67.5°	223.6	208.7	194.2	178.6	165.3	155.7	149.0	147.5	145.0	144.3	142.5
70°	195.5	181.5	166.9	152.3	139.7	137.8	135.4	132.9	129.9	128.7	127.5
72.5°	170.2	155.7	141.2	129.5	124.1	121.8	119.4	116.9	114.9	113.7	112.9
75°	130.6	117.2	107.4	103.2	100.1	98.3	94.7	92.8	91.7	89.8	89.2
77.5°	94.0	86.4	82.0	79.3	76.1	74.1	72.1	70.3	69.0	68.6	67.7
80°	71.6	68.0	65.0	61.3	60.1	57.7	57.0	55.2	55.8	54.0	54.0
82.5°	55.6	51.0	48.5	46.7	45.6	43.6	43.0	42.1	42.2	40.9	40.9
85°	28.5	27.3	26.1	24.9	24.9	23.1	23.7	23.1	23.1	21.9	21.2
87.5°	12.0	12.4	12.6	13.8	15.0	15.6	15.5	15.0	14.8	14.7	14.3
90°	13.9	18.5	24.3	30.1	36.0	41.8	41.3	40.7	40.2	39.7	39.5
92.5°	30.6	32.5	33.8	35.3	36.6	37.9	38.1	38.2	38.3	38.4	38.5
95°	72.7	74.3	74.9	75.3	75.9	76.4	76.4	76.4	76.4	76.4	76.1
97.5°	122.8	124.5	125.5	126.5	127.5	128.5	128.5	128.5	128.5	128.5	128.5
100°	160.2	161.6	162.4	163.2	164.0	164.8	164.8	164.8	164.8	164.8	164.7
102.5°	198.6	199.9	201.0	201.9	203.0	204.0	204.2	204.4	204.6	204.9	204.8
105°	259.9	260.6	261.2	261.7	262.2	262.8	263.2	263.8	264.4	264.8	265.1
107.5°	326.9	327.5	327.5	327.5	327.5	327.5	327.6	327.9	328.1	328.3	327.8
110°	370.6	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.0



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	416.5	417.2	416.9	416.8	416.5	416.3	415.7	415.0	414.4	413.8	413.1
115°	484.1	484.6	484.1	483.5	483.0	482.5	482.2	482.0	481.6	481.4	480.9
117.5°	553.6	553.9	552.4	550.9	549.4	548.0	547.3	546.7	546.1	545.4	544.6
120°	598.5	598.5	596.4	594.2	592.1	589.9	589.9	589.9	589.9	589.9	589.5
122.5°	641.3	641.7	640.3	638.8	637.3	635.8	635.2	634.5	633.9	633.3	632.6
125°	704.6	705.4	704.6	703.9	703.1	702.2	701.4	700.6	699.8	699.0	698.5
127.5°	769.5	770.6	769.6	768.7	767.7	766.8	765.7	764.8	763.8	762.9	762.0
130°	810.4	811.8	811.3	810.8	810.2	809.7	809.2	808.7	808.1	807.6	806.8
132.5°	851.8	853.3	853.3	853.4	853.6	853.7	852.5	851.4	850.2	849.0	848.0
135°	910.9	912.7	913.2	913.8	914.3	914.8	914.6	914.3	914.0	913.8	913.2
137.5°	970.7	972.2	973.0	973.6	974.3	975.0	974.8	974.5	974.4	974.1	973.5
140°	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1	1015.1	1015.1	1015.1	1014.6
142.5°	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6	1051.9	1052.1	1052.3	1051.9
145°	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3	1107.6	1107.9	1108.1	1107.7
147.5°	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0	1156.5	1157.1	1157.7	1157.5
150°	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1
152.5°	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5
155°	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5	1257.8	1259.2	1260.4	1260.8
157.5°	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3	1294.1	1295.9	1297.8	1298.0
160°	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1	1315.7	1317.2	1318.8	1319.1
162.5°	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4	1335.2	1337.0	1338.8	1339.1
165°	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5	1360.4	1362.2	1364.1	1364.4
167.5°	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3	1381.2	1383.1	1384.9	1385.1
170°	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8	1392.7	1394.5	1396.4	1396.5
172.5°	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4	1401.2	1403.1	1404.9	1405.1
175°	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7	1410.6	1412.4	1414.3	1414.4
177.5°	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1677.7	1678.6	1677.2	1678.2	1677.2	1678.6	1677.7	1683.0	1683.9	1685.0	1683.9
5°	1563.1	1555.8	1554.7	1552.8	1554.7	1555.8	1563.1	1566.2	1568.6	1573.5	1582.0
7.5°	1426.5	1425.4	1422.4	1418.1	1422.4	1425.4	1426.5	1436.9	1445.2	1454.6	1472.0
10°	1338.6	1335.5	1334.9	1330.6	1334.9	1335.5	1338.6	1351.9	1361.6	1375.0	1398.7
12.5°	1235.6	1216.1	1214.0	1203.4	1214.0	1216.1	1235.6	1252.8	1279.1	1292.0	1317.1
15°	1052.0	1048.4	1036.3	1028.3	1036.3	1048.4	1052.0	1066.6	1076.3	1111.5	1152.2
17.5°	947.1	935.3	931.4	929.8	931.4	935.3	947.1	954.2	968.0	986.6	1011.1
20°	879.6	868.7	866.9	865.7	866.9	868.7	879.6	888.1	899.0	919.1	944.6
22.5°	833.0	821.6	816.8	813.2	816.8	821.6	833.0	839.6	849.5	865.1	882.4
25°	753.4	749.1	746.7	745.4	746.7	749.1	753.4	759.5	769.1	790.4	808.6
27.5°	691.1	681.8	679.9	676.8	679.9	681.8	691.1	701.9	711.9	721.5	737.8
30°	655.6	652.6	648.3	644.7	648.3	652.6	655.6	661.1	667.7	684.1	700.0
32.5°	613.9	611.3	607.5	605.9	607.5	611.3	613.9	621.2	635.3	645.3	656.7
35°	567.6	559.1	555.5	550.0	555.5	559.1	567.6	573.7	579.2	587.6	608.2
37.5°	518.6	514.2	509.1	510.9	509.1	514.2	518.6	521.3	532.7	544.5	553.5
40°	480.8	477.8	476.6	475.9	476.6	477.8	480.8	488.7	502.6	508.1	521.5
42.5°	450.7	442.3	439.1	439.0	439.1	442.3	450.7	459.5	468.2	477.1	490.8
45°	404.9	397.0	391.6	392.1	391.6	397.0	404.9	408.0	415.3	432.8	440.7
47.5°	358.1	357.8	354.4	355.5	354.4	357.8	358.1	363.3	372.6	383.4	396.0
50°	335.7	332.1	329.6	330.3	329.6	332.1	335.7	339.9	345.4	350.9	370.3
52.5°	314.3	311.2	309.3	311.8	309.3	311.2	314.3	316.6	320.7	326.1	339.2
55°	279.2	275.6	275.0	274.4	275.0	275.6	279.2	282.3	287.2	291.4	297.5
57.5°	240.0	237.6	233.9	232.3	233.9	237.6	240.0	244.5	250.3	256.0	262.2
60°	211.8	207.0	200.9	200.3	200.9	207.0	211.8	219.8	222.2	230.7	238.0
62.5°	186.1	185.1	183.9	183.8	183.9	185.1	186.1	188.7	192.1	204.5	213.2
65°	163.3	162.7	163.3	163.9	163.3	162.7	163.3	164.5	165.1	166.4	170.0
67.5°	142.3	141.2	140.1	140.6	140.1	141.2	142.3	142.5	144.3	145.0	147.5
70°	126.3	125.6	125.1	125.1	125.1	125.6	126.3	127.5	128.7	129.9	132.9
72.5°	110.7	110.6	110.0	109.5	110.0	110.6	110.7	112.9	113.7	114.9	116.9
75°	88.6	87.4	87.4	87.4	87.4	87.4	88.6	89.2	89.8	91.7	92.8
77.5°	67.5	66.9	66.3	65.8	66.3	66.9	67.5	67.7	68.6	69.0	70.3
80°	53.4	52.8	52.2	52.2	52.2	52.8	53.4	54.0	54.0	55.8	55.2
82.5°	40.8	40.2	40.1	39.6	40.1	40.2	40.8	40.9	40.9	42.2	42.1
85°	21.9	22.5	21.9	23.1	21.9	22.5	21.9	21.2	21.9	23.1	23.1
87.5°	14.3	13.9	14.4	13.9	14.4	13.9	14.3	14.3	14.7	14.8	15.0
90°	39.8	40.1	40.3	40.6	40.3	40.1	39.8	39.5	39.7	40.2	40.7
92.5°	38.5	38.6	38.7	38.7	38.7	38.6	38.5	38.5	38.4	38.3	38.2
95°	75.7	75.1	74.5	74.1	74.5	75.1	75.7	76.1	76.4	76.4	76.4
97.5°	128.4	128.3	128.3	128.3	128.3	128.3	128.4	128.5	128.5	128.5	128.5
100°	164.4	164.1	163.9	163.6	163.9	164.1	164.4	164.7	164.8	164.8	164.8
102.5°	204.5	204.3	204.0	203.7	204.0	204.3	204.5	204.8	204.9	204.6	204.4
105°	265.1	265.1	265.1	265.1	265.1	265.1	265.1	265.1	264.8	264.4	263.8
107.5°	326.6	325.3	324.2	322.9	324.2	325.3	326.6	327.8	328.3	328.1	327.9
110°	370.2	369.4	368.6	367.8	368.6	369.4	370.2	371.0	371.5	371.5	371.5



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	412.6	412.0	411.4	410.8	411.4	412.0	412.6	413.1	413.8	414.4	415.0
115°	480.1	479.3	478.5	477.7	478.5	479.3	480.1	480.9	481.4	481.6	482.0
117.5°	543.8	543.0	542.2	541.5	542.2	543.0	543.8	544.6	545.4	546.1	546.7
120°	588.7	588.0	587.2	586.4	587.2	588.0	588.7	589.5	589.9	589.9	589.9
122.5°	632.1	631.5	630.9	630.3	630.9	631.5	632.1	632.6	633.3	633.9	634.5
125°	698.2	698.0	697.8	697.4	697.8	698.0	698.2	698.5	699.0	699.8	700.6
127.5°	761.1	760.3	759.5	758.6	759.5	760.3	761.1	762.0	762.9	763.8	764.8
130°	805.7	804.7	803.6	802.6	803.6	804.7	805.7	806.8	807.6	808.1	808.7
132.5°	847.2	846.3	845.4	844.5	845.4	846.3	847.2	848.0	849.0	850.2	851.4
135°	912.4	911.6	910.9	910.1	910.9	911.6	912.4	913.2	913.8	914.0	914.3
137.5°	972.5	971.4	970.3	969.2	970.3	971.4	972.5	973.5	974.1	974.4	974.5
140°	1013.5	1012.5	1011.4	1010.3	1011.4	1012.5	1013.5	1014.6	1015.1	1015.1	1015.1
142.5°	1050.8	1049.7	1048.7	1047.6	1048.7	1049.7	1050.8	1051.9	1052.3	1052.1	1051.9
145°	1106.7	1105.6	1104.5	1103.5	1104.5	1105.6	1106.7	1107.7	1108.1	1107.9	1107.6
147.5°	1156.4	1155.4	1154.4	1153.4	1154.4	1155.4	1156.4	1157.5	1157.7	1157.1	1156.5
150°	1188.3	1187.5	1186.7	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5
152.5°	1219.5	1218.5	1217.5	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5
155°	1260.0	1259.2	1258.4	1257.6	1258.4	1259.2	1260.0	1260.8	1260.4	1259.2	1257.8
157.5°	1296.7	1295.5	1294.2	1292.9	1294.2	1295.5	1296.7	1298.0	1297.8	1295.9	1294.1
160°	1318.0	1317.0	1316.0	1314.9	1316.0	1317.0	1318.0	1319.1	1318.8	1317.2	1315.7
162.5°	1337.8	1336.6	1335.3	1334.0	1335.3	1336.6	1337.8	1339.1	1338.8	1337.0	1335.2
165°	1363.0	1361.8	1360.4	1359.1	1360.4	1361.8	1363.0	1364.4	1364.1	1362.2	1360.4
167.5°	1383.8	1382.4	1381.0	1379.6	1381.0	1382.4	1383.8	1385.1	1384.9	1383.1	1381.2
170°	1394.9	1393.3	1391.7	1390.1	1391.7	1393.3	1394.9	1396.5	1396.4	1394.5	1392.7
172.5°	1403.5	1401.9	1400.3	1398.8	1400.3	1401.9	1403.5	1405.1	1404.9	1403.1	1401.2
175°	1412.8	1411.2	1409.6	1408.0	1409.6	1411.2	1412.8	1414.4	1414.3	1412.4	1410.6
177.5°	1416.2	1414.9	1413.6	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1680.1	1686.9	1697.1	1702.9	1712.6	1719.0	1722.4	1728.6	1732.0	1744.2	1756.8
5°	1586.3	1595.9	1613.0	1628.7	1645.8	1663.3	1676.1	1690.7	1704.0	1727.0	1751.4
7.5°	1478.7	1492.2	1518.5	1543.6	1573.3	1598.1	1620.1	1645.0	1667.2	1700.3	1734.7
10°	1398.0	1421.7	1456.3	1480.0	1518.9	1543.7	1578.3	1605.7	1636.6	1680.3	1719.2
12.5°	1328.6	1357.2	1385.0	1417.8	1452.8	1494.2	1532.2	1567.3	1604.1	1649.2	1694.9
15°	1202.6	1243.9	1287.0	1320.3	1367.7	1411.4	1455.7	1503.1	1548.0	1602.0	1661.5
17.5°	1040.4	1088.2	1160.7	1217.9	1273.5	1317.3	1372.2	1429.5	1482.4	1547.6	1613.8
20°	967.0	1002.3	1051.4	1128.5	1212.3	1259.0	1314.9	1378.0	1438.7	1509.7	1580.8
22.5°	908.2	939.6	979.1	1039.2	1132.7	1196.4	1254.7	1318.7	1389.2	1461.7	1540.5
25°	824.3	846.2	887.5	936.0	1000.4	1105.4	1169.2	1233.5	1310.0	1387.7	1477.6
27.5°	761.4	781.0	807.9	854.2	902.1	977.5	1078.9	1149.1	1225.3	1312.7	1406.0
30°	713.3	736.3	766.1	798.9	851.1	910.0	1011.4	1092.7	1168.0	1257.8	1357.4
32.5°	678.3	696.6	721.9	755.2	798.7	855.1	936.0	1034.9	1108.3	1202.9	1306.9
35°	621.0	642.3	662.9	694.5	729.7	781.3	842.6	948.2	1021.0	1114.5	1218.9
37.5°	573.8	586.8	609.6	634.6	671.8	710.3	763.4	858.2	936.9	1028.7	1135.6
40°	537.8	554.2	571.2	599.1	629.5	666.5	718.7	789.2	879.6	969.5	1073.9
42.5°	502.9	523.6	541.6	560.3	593.6	630.6	673.1	732.8	825.2	910.2	1011.7
45°	460.7	474.1	492.9	513.6	540.9	572.4	610.1	662.3	750.9	824.3	919.7
47.5°	411.7	431.3	443.5	463.7	489.6	519.8	554.8	599.9	671.6	740.5	828.9
50°	378.2	398.2	415.8	434.0	457.1	486.2	515.4	559.1	616.8	689.0	771.6
52.5°	349.5	367.2	384.3	402.5	425.1	451.8	479.4	517.8	567.2	633.7	713.8
55°	310.2	321.2	338.7	357.0	377.0	402.5	429.2	461.4	503.8	559.7	624.6
57.5°	269.9	282.5	296.5	314.8	335.1	354.7	378.7	407.8	441.3	491.9	547.5
60°	247.1	256.7	268.3	287.2	305.9	323.5	346.7	370.9	402.5	446.2	493.5
62.5°	221.8	231.1	241.6	258.0	276.3	292.5	312.6	338.3	365.1	404.9	446.4
65°	179.7	193.1	203.4	217.9	233.1	250.1	265.9	286.5	310.2	341.7	378.8
67.5°	149.0	155.7	165.3	178.6	194.2	208.7	223.6	239.8	260.3	284.7	314.1
70°	135.4	137.8	139.7	152.3	166.9	181.5	195.5	210.6	228.2	248.3	273.8
72.5°	119.4	121.8	124.1	129.5	141.2	155.7	170.2	181.5	198.1	214.8	235.4
75°	94.7	98.3	100.1	103.2	107.4	117.2	130.6	141.4	151.1	163.9	180.3
77.5°	72.1	74.1	76.1	79.3	82.0	86.4	94.0	103.8	112.9	120.3	131.6
80°	57.0	57.7	60.1	61.3	65.0	68.0	71.6	79.5	88.6	91.7	99.6
82.5°	43.0	43.6	45.6	46.7	48.5	51.0	55.6	57.7	64.8	68.8	73.8
85°	23.7	23.1	24.9	24.9	26.1	27.3	28.5	31.5	33.4	38.3	39.5
87.5°	15.5	15.6	15.0	13.8	12.6	12.4	12.0	11.9	12.2	13.0	14.3
90°	41.3	41.8	36.0	30.1	24.3	18.5	13.9	10.8	7.5	4.4	1.2
92.5°	38.1	37.9	36.6	35.3	33.8	32.5	30.6	28.3	25.9	23.6	21.2
95°	76.4	76.4	75.9	75.3	74.9	74.3	72.7	70.0	67.4	64.7	62.1
97.5°	128.5	128.5	127.5	126.5	125.5	124.5	122.8	120.5	118.1	115.8	113.4
100°	164.8	164.8	164.0	163.2	162.4	161.6	160.2	158.0	155.9	153.8	151.7
102.5°	204.2	204.0	203.0	201.9	201.0	199.9	198.6	196.9	195.2	193.5	191.8
105°	263.2	262.8	262.2	261.7	261.2	260.6	259.9	259.1	258.3	257.5	256.7
107.5°	327.6	327.5	327.5	327.5	327.5	327.5	326.9	325.7	324.6	323.4	322.2
110°	371.5	371.5	371.5	371.5	371.5	371.5	370.6	369.0	367.4	365.8	364.2



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	415.7	416.3	416.5	416.8	416.9	417.2	416.5	414.9	413.3	411.7	410.1
115°	482.2	482.5	483.0	483.5	484.1	484.6	484.1	482.5	480.9	479.3	477.7
117.5°	547.3	548.0	549.4	550.9	552.4	553.9	553.6	551.4	549.3	547.2	545.1
120°	589.9	589.9	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9
122.5°	635.2	635.8	637.3	638.8	640.3	641.7	641.3	638.7	636.1	633.6	631.1
125°	701.4	702.2	703.1	703.9	704.6	705.4	704.6	702.2	699.8	697.4	695.1
127.5°	765.7	766.8	767.7	768.7	769.6	770.6	769.5	766.5	763.4	760.4	757.4
130°	809.2	809.7	810.2	810.8	811.3	811.8	810.4	806.9	803.5	800.0	796.5
132.5°	852.5	853.7	853.6	853.4	853.3	853.3	851.8	849.0	846.1	843.4	840.5
135°	914.6	914.8	914.3	913.8	913.2	912.7	910.9	908.0	905.1	902.2	899.3
137.5°	974.8	975.0	974.3	973.6	973.0	972.2	970.7	968.3	965.9	963.5	961.2
140°	1015.1	1015.1	1013.8	1012.5	1011.1	1009.8	1008.0	1005.6	1003.2	1000.8	998.4
142.5°	1051.6	1051.5	1050.5	1049.6	1048.7	1047.8	1046.2	1043.8	1041.4	1039.0	1036.6
145°	1107.3	1107.1	1105.5	1103.9	1102.3	1100.7	1099.0	1097.1	1095.3	1093.4	1091.5
147.5°	1156.0	1155.3	1154.3	1153.2	1152.1	1151.1	1149.5	1147.2	1144.9	1142.7	1140.5
150°	1186.7	1185.9	1184.9	1183.8	1182.7	1181.6	1180.4	1178.8	1177.2	1175.5	1173.9
152.5°	1217.5	1216.5	1215.2	1213.9	1212.7	1211.4	1210.0	1208.3	1206.7	1205.1	1203.6
155°	1256.5	1255.1	1254.3	1253.5	1252.8	1252.0	1251.2	1250.4	1249.6	1248.8	1248.0
157.5°	1292.3	1290.5	1290.1	1289.6	1289.1	1288.6	1288.1	1287.6	1287.1	1286.5	1285.9
160°	1314.1	1312.5	1312.2	1311.9	1311.7	1311.5	1311.1	1310.5	1310.0	1309.5	1308.9
162.5°	1333.4	1331.6	1331.3	1331.1	1330.8	1330.5	1330.4	1330.2	1330.2	1330.1	1329.9
165°	1358.5	1356.7	1356.7	1356.7	1356.7	1356.7	1356.8	1357.1	1357.3	1357.6	1357.9
167.5°	1379.3	1377.4	1377.5	1377.6	1377.6	1377.7	1378.1	1378.9	1379.7	1380.5	1381.2
170°	1390.8	1388.9	1389.2	1389.5	1389.7	1390.0	1390.5	1391.3	1392.1	1392.9	1393.7
172.5°	1399.4	1397.5	1397.8	1398.0	1398.4	1398.6	1399.2	1399.9	1400.7	1401.5	1402.3
175°	1408.7	1406.8	1407.4	1407.9	1408.4	1409.0	1409.6	1410.4	1411.2	1412.0	1412.8
177.5°	1413.6	1412.3	1412.8	1413.2	1413.6	1414.0	1414.6	1415.2	1415.9	1416.5	1417.1
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1757.3	1758.7	1768.5	1772.8	1781.6	1784.9	1788.9	1787.9	1787.9	1789.9	1803.4
5°	1761.1	1773.2	1791.4	1809.0	1826.1	1840.6	1850.3	1860.0	1863.7	1881.3	1897.0
7.5°	1754.8	1777.1	1807.2	1834.1	1866.2	1891.3	1912.2	1931.0	1943.9	1969.5	1995.7
10°	1746.5	1778.1	1812.0	1846.7	1890.9	1924.4	1958.4	1984.5	1993.0	2031.2	2053.1
12.5°	1730.0	1772.3	1815.4	1860.3	1903.6	1949.6	1987.0	2013.1	2043.0	2077.3	2117.7
15°	1705.3	1753.8	1810.2	1867.9	1929.8	1985.7	2025.8	2071.2	2104.0	2141.7	2176.9
17.5°	1669.7	1732.2	1804.0	1870.7	1942.4	2002.3	2057.5	2101.1	2124.2	2145.7	2150.9
20°	1641.5	1708.9	1793.3	1872.2	1943.8	2013.0	2067.6	2104.0	2110.1	2110.7	2078.5
22.5°	1610.9	1687.0	1775.3	1856.2	1941.9	2018.8	2061.3	2076.9	2052.8	2011.7	1949.4
25°	1554.7	1642.7	1745.3	1837.5	1931.0	2003.9	2018.5	1991.2	1906.8	1818.1	1705.8
27.5°	1493.7	1592.7	1702.6	1805.2	1904.8	1950.0	1918.5	1820.0	1668.1	1536.0	1375.9
30°	1449.1	1560.1	1668.2	1782.9	1875.2	1894.6	1822.4	1677.3	1500.0	1300.9	1141.3
32.5°	1398.0	1514.5	1633.2	1751.8	1829.1	1810.1	1690.8	1512.2	1304.3	1108.6	957.7
35°	1325.2	1445.4	1573.5	1692.5	1741.6	1659.7	1481.2	1248.7	1036.3	853.5	749.7
37.5°	1241.0	1372.0	1505.1	1614.4	1610.9	1474.3	1231.2	991.2	812.6	704.6	630.6
40°	1181.3	1313.7	1457.5	1549.8	1510.4	1332.5	1069.1	842.6	712.1	625.9	571.9
42.5°	1124.0	1256.9	1399.8	1473.1	1404.5	1185.8	923.4	745.9	638.3	571.0	527.2
45°	1026.5	1166.7	1299.1	1339.7	1217.1	976.1	746.7	618.0	546.4	496.5	466.2
47.5°	931.2	1069.1	1189.9	1190.6	1024.8	791.6	629.9	534.8	473.6	435.1	413.0
50°	872.9	1004.1	1105.4	1089.6	901.5	704.2	563.3	481.4	430.4	400.7	377.6
52.5°	807.4	934.6	1022.4	977.5	797.1	619.6	503.6	434.7	392.5	366.6	346.0
55°	712.1	825.0	886.9	818.9	650.1	515.4	425.6	371.5	339.9	318.1	300.5
57.5°	618.5	711.6	750.6	671.4	535.5	427.4	360.0	319.4	288.1	272.4	263.3
60°	559.7	639.2	666.5	579.2	465.6	373.9	318.7	281.1	258.0	247.7	238.6
62.5°	501.9	566.9	578.1	498.0	405.9	327.3	279.9	248.0	232.7	222.9	214.3
65°	416.5	463.2	457.7	393.4	321.2	259.8	225.2	205.8	194.2	180.3	165.1
67.5°	342.9	371.4	354.2	305.9	245.1	201.9	179.4	164.6	150.3	137.0	133.6
70°	296.3	312.6	294.5	250.1	200.9	169.4	151.1	133.6	125.1	122.0	116.5
72.5°	251.6	257.3	237.6	199.6	163.5	140.2	122.5	112.6	108.1	105.5	102.0
75°	188.8	184.6	167.5	137.8	113.5	97.8	92.3	88.6	85.6	83.2	81.4
77.5°	132.6	126.4	111.2	91.8	79.1	71.5	68.2	66.3	64.8	63.6	61.8
80°	99.6	95.3	80.2	65.6	60.1	56.5	54.7	52.2	52.2	51.0	49.2
82.5°	72.9	68.1	54.9	48.1	45.1	42.9	41.5	40.1	39.6	39.8	38.5
85°	38.3	31.0	27.3	26.1	24.3	23.1	23.7	22.5	22.5	22.5	21.9
87.5°	12.5	10.8	10.9	11.0	12.4	13.6	14.3	15.4	17.1	16.5	16.9
90°	4.4	7.5	10.8	13.9	18.5	24.3	30.1	36.0	41.8	41.3	40.7
92.5°	23.6	25.9	28.3	30.6	32.5	33.8	35.3	36.6	37.9	38.1	38.2
95°	64.7	67.4	70.0	72.7	74.3	74.9	75.3	75.9	76.4	76.4	76.4
97.5°	115.8	118.1	120.5	122.8	124.5	125.5	126.5	127.5	128.5	128.5	128.5
100°	153.8	155.9	158.0	160.2	161.6	162.4	163.2	164.0	164.8	164.8	164.8
102.5°	193.5	195.2	196.9	198.6	199.9	201.0	201.9	203.0	204.0	204.2	204.4
105°	257.5	258.3	259.1	259.9	260.6	261.2	261.7	262.2	262.8	263.2	263.8
107.5°	323.4	324.6	325.7	326.9	327.5	327.5	327.5	327.5	327.5	327.6	327.9
110°	365.8	367.4	369.0	370.6	371.5	371.5	371.5	371.5	371.5	371.5	371.5





TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	411.7	413.3	414.9	416.5	417.2	416.9	416.8	416.5	416.3	415.7	415.0
115°	479.3	480.9	482.5	484.1	484.6	484.1	483.5	483.0	482.5	482.2	482.0
117.5°	547.2	549.3	551.4	553.6	553.9	552.4	550.9	549.4	548.0	547.3	546.7
120°	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	589.9	589.9
122.5°	633.6	636.1	638.7	641.3	641.7	640.3	638.8	637.3	635.8	635.2	634.5
125°	697.4	699.8	702.2	704.6	705.4	704.6	703.9	703.1	702.2	701.4	700.6
127.5°	760.4	763.4	766.5	769.5	770.6	769.6	768.7	767.7	766.8	765.7	764.8
130°	800.0	803.5	806.9	810.4	811.8	811.3	810.8	810.2	809.7	809.2	808.7
132.5°	843.4	846.1	849.0	851.8	853.3	853.3	853.4	853.6	853.7	852.5	851.4
135°	902.2	905.1	908.0	910.9	912.7	913.2	913.8	914.3	914.8	914.6	914.3
137.5°	963.5	965.9	968.3	970.7	972.2	973.0	973.6	974.3	975.0	974.8	974.5
140°	1000.8	1003.2	1005.6	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1	1015.1
142.5°	1039.0	1041.4	1043.8	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6	1051.9
145°	1093.4	1095.3	1097.1	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3	1107.6
147.5°	1142.7	1144.9	1147.2	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0	1156.5
150°	1175.5	1177.2	1178.8	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7	1187.5
152.5°	1205.1	1206.7	1208.3	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5	1218.5
155°	1248.8	1249.6	1250.4	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5	1257.8
157.5°	1286.5	1287.1	1287.6	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3	1294.1
160°	1309.5	1310.0	1310.5	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1	1315.7
162.5°	1330.1	1330.2	1330.2	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4	1335.2
165°	1357.6	1357.3	1357.1	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5	1360.4
167.5°	1380.5	1379.7	1378.9	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3	1381.2
170°	1392.9	1392.1	1391.3	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8	1392.7
172.5°	1401.5	1400.7	1399.9	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4	1401.2
175°	1412.0	1411.2	1410.4	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7	1410.6
177.5°	1416.5	1415.9	1415.2	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6	1414.9
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1808.3	1814.6	1817.5	1817.5	1820.9	1819.5	1818.0
5°	1912.2	1923.7	1926.2	1937.1	1945.0	1942.6	1943.8
7.5°	2015.5	2034.1	2052.5	2060.9	2062.1	2067.0	2068.9
10°	2079.2	2094.4	2122.9	2118.6	2139.8	2152.0	2132.0
12.5°	2140.3	2160.8	2180.6	2186.1	2198.1	2202.0	2194.1
15°	2195.7	2206.6	2207.9	2204.8	2208.4	2205.4	2193.9
17.5°	2144.0	2126.3	2090.3	2073.3	2059.8	2039.9	2031.9
20°	2058.5	2006.3	1945.6	1921.4	1892.8	1836.9	1850.3
22.5°	1874.0	1814.5	1753.8	1682.9	1649.0	1596.1	1592.9
25°	1586.8	1484.2	1371.3	1292.4	1246.3	1193.5	1170.4
27.5°	1233.7	1104.6	1012.1	965.2	922.6	880.7	879.0
30°	1001.6	904.5	832.9	792.8	766.7	749.1	752.7
32.5°	844.3	777.8	729.4	696.2	676.8	663.6	663.4
35°	690.2	644.7	613.7	599.8	585.8	576.1	576.7
37.5°	590.7	563.3	546.1	530.7	522.0	517.2	514.5
40°	539.6	517.2	503.8	494.7	487.4	480.8	479.6
42.5°	499.4	480.8	467.5	460.3	453.4	448.8	447.5
45°	443.1	427.9	415.8	408.0	404.9	400.7	400.7
47.5°	394.2	379.3	369.8	364.9	359.7	356.8	356.7
50°	361.2	349.7	341.2	338.1	333.9	332.1	331.4
52.5°	331.6	323.0	316.9	314.8	313.0	310.7	311.1
55°	291.4	286.5	284.1	282.3	279.2	275.6	278.1
57.5°	257.5	253.4	246.8	241.1	238.4	235.8	236.8
60°	233.7	225.2	216.7	210.0	208.2	202.7	202.7
62.5°	203.6	191.7	181.3	177.5	175.7	173.2	172.6
65°	156.6	151.8	149.3	146.9	145.7	145.7	144.5
67.5°	129.8	127.9	125.2	124.5	123.3	123.0	122.6
70°	114.7	112.3	111.1	110.5	109.2	109.9	108.1
72.5°	100.1	98.2	98.0	96.4	95.7	95.8	94.4
75°	78.9	78.9	78.3	77.7	76.5	75.9	76.5
77.5°	60.7	60.8	59.7	59.7	59.5	59.7	59.0
80°	48.6	49.2	48.6	47.9	47.4	47.9	47.4
82.5°	38.3	37.5	37.4	37.3	37.2	36.8	36.7
85°	21.9	22.5	21.9	21.2	21.2	21.2	21.9
87.5°	16.3	16.2	16.2	16.2	16.2	16.3	15.9
90°	40.2	39.7	39.5	39.8	40.1	40.3	40.6
92.5°	38.3	38.4	38.5	38.5	38.6	38.7	38.7
95°	76.4	76.4	76.1	75.7	75.1	74.5	74.1
97.5°	128.5	128.5	128.5	128.4	128.3	128.3	128.3
100°	164.8	164.8	164.7	164.4	164.1	163.9	163.6
102.5°	204.6	204.9	204.8	204.5	204.3	204.0	203.7
105°	264.4	264.8	265.1	265.1	265.1	265.1	265.1
107.5°	328.1	328.3	327.8	326.6	325.3	324.2	322.9
110°	371.5	371.5	371.0	370.2	369.4	368.6	367.8



TEST NUMBER: P331862-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	414.4	413.8	413.1	412.6	412.0	411.4	410.8
115°	481.6	481.4	480.9	480.1	479.3	478.5	477.7
117.5°	546.1	545.4	544.6	543.8	543.0	542.2	541.5
120°	589.9	589.9	589.5	588.7	588.0	587.2	586.4
122.5°	633.9	633.3	632.6	632.1	631.5	630.9	630.3
125°	699.8	699.0	698.5	698.2	698.0	697.8	697.4
127.5°	763.8	762.9	762.0	761.1	760.3	759.5	758.6
130°	808.1	807.6	806.8	805.7	804.7	803.6	802.6
132.5°	850.2	849.0	848.0	847.2	846.3	845.4	844.5
135°	914.0	913.8	913.2	912.4	911.6	910.9	910.1
137.5°	974.4	974.1	973.5	972.5	971.4	970.3	969.2
140°	1015.1	1015.1	1014.6	1013.5	1012.5	1011.4	1010.3
142.5°	1052.1	1052.3	1051.9	1050.8	1049.7	1048.7	1047.6
145°	1107.9	1108.1	1107.7	1106.7	1105.6	1104.5	1103.5
147.5°	1157.1	1157.7	1157.5	1156.4	1155.4	1154.4	1153.4
150°	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9
152.5°	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5
155°	1259.2	1260.4	1260.8	1260.0	1259.2	1258.4	1257.6
157.5°	1295.9	1297.8	1298.0	1296.7	1295.5	1294.2	1292.9
160°	1317.2	1318.8	1319.1	1318.0	1317.0	1316.0	1314.9
162.5°	1337.0	1338.8	1339.1	1337.8	1336.6	1335.3	1334.0
165°	1362.2	1364.1	1364.4	1363.0	1361.8	1360.4	1359.1
167.5°	1383.1	1384.9	1385.1	1383.8	1382.4	1381.0	1379.6
170°	1394.5	1396.4	1396.5	1394.9	1393.3	1391.7	1390.1
172.5°	1403.1	1404.9	1405.1	1403.5	1401.9	1400.3	1398.8
175°	1412.4	1414.3	1414.4	1412.8	1411.2	1409.6	1408.0
177.5°	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2

(END OF REPORT)