

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331863-927

Luminaire Tested: **S122RDIW-S1005D1440U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331863-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1440U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7326.0 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331863-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331863-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	88	84	86	83	80	77	67	65	63	53	52	51	40	39	39
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33
3	80	71	64	58	72	64	59	54	53	49	45	42	39	37	32	30	28
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21660	21660	21660
5°	21742	21389	21507
10°	21577	21040	20859
15°	21329	20415	19826
20°	20984	19524	18545
25°	20633	18513	17302
30°	20144	17473	15709
35°	19669	16344	14310
40°	19191	15173	12690
45°	18630	13860	11227
50°	18053	12534	9789
55°	17464	11108	8408
60°	16779	9607	6978
65°	16000	8073	6357
70°	15073	6652	5844
75°	13936	6057	5452
80°	12301	5421	4965
85°	9670	4279	4279



TEST NUMBER: P331863-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.6	1.7
10°-20°	344.8	4.7
20°-30°	484.2	6.6
30°-40°	528.0	7.2
40°-50°	485.4	6.6
50°-60°	381.3	5.2
60°-70°	248.6	3.4
70°-80°	128.2	1.7
80°-90°	37.1	0.5
90°-100°	51.9	0.7
100°-110°	190.5	2.6
110°-120°	509.1	6.9
120°-130°	840.4	11.5
130°-140°	893.8	12.2
140°-150°	830.7	11.3
150°-160°	667.9	9.1
160°-170°	430.4	5.9
170°-180°	148.2	2.0
0°-30°	954.5	13.0
0°-40°	1482.5	20.2
0°-60°	2349.2	32.1
0°-90°	2763.0	37.7
90°-120°	751.5	10.3
90°-150°	3316.5	45.3
90°-180°	4563.0	62.3
0°-180°	7326.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1342	1342	1342	1342	1342	
5°	1342	1335	1320	1330	1327	127
15°	1276	1261	1221	1199	1186	359
25°	1158	1117	1039	991	971	532
35°	998	934	829	755	726	624
45°	816	732	607	524	492	630
55°	620	524	395	324	299	554
65°	419	320	211	172	166	415
75°	223	141	97	89	87	236
85°	52	28	23	23	23	62
90°	1	13	22	28	30	6
95°	73	39	44	49	48	90
105°	342	357	69	81	86	366
115°	648	668	695	198	92	638
125°	916	931	952	960	963	816
135°	1134	1151	1162	1172	1171	875
145°	1315	1315	1333	1340	1335	822
155°	1448	1439	1451	1457	1449	667
165°	1526	1519	1522	1529	1522	431
175°	1560	1553	1555	1562	1551	148
180°	1557	1557	1557	1557	1557	



TEST NUMBER: P331863-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1346.4	1345.3	1344.2	1343.1	1342.0	1340.3	1337.9	1335.6	1333.2	1330.9	1333.0
5°	1341.5	1340.1	1338.8	1337.4	1336.1	1333.7	1330.2	1326.7	1323.2	1319.7	1322.1
7.5°	1327.7	1326.0	1324.4	1322.6	1321.0	1318.1	1314.0	1309.9	1305.8	1301.7	1302.4
10°	1316.1	1314.2	1312.2	1310.3	1308.4	1304.8	1299.4	1294.0	1288.6	1283.3	1282.5
12.5°	1301.5	1299.1	1296.8	1294.5	1292.2	1287.5	1280.6	1273.7	1266.9	1260.0	1258.5
15°	1276.0	1273.0	1270.0	1267.0	1264.1	1258.0	1248.9	1239.7	1230.5	1221.3	1216.2
17.5°	1244.6	1240.1	1235.6	1231.1	1226.5	1218.4	1206.6	1194.8	1183.0	1171.3	1165.2
20°	1221.3	1215.9	1210.5	1205.1	1199.8	1190.3	1176.8	1163.3	1149.9	1136.3	1129.6
22.5°	1196.0	1190.0	1184.0	1178.0	1171.9	1161.3	1146.1	1130.8	1115.6	1100.4	1091.7
25°	1158.2	1149.5	1140.9	1132.3	1123.6	1110.5	1092.7	1074.8	1057.0	1039.2	1028.2
27.5°	1112.5	1103.2	1093.8	1084.4	1075.0	1060.3	1040.2	1020.1	1000.1	980.0	967.1
30°	1080.5	1070.2	1060.0	1049.7	1039.5	1023.6	1002.0	980.4	958.9	937.2	923.4
32.5°	1049.4	1037.4	1025.5	1013.5	1001.5	984.5	962.5	940.5	918.5	896.4	880.7
35°	997.9	984.2	970.4	956.6	942.9	924.2	900.4	876.7	852.9	829.2	812.2
37.5°	946.5	931.4	916.2	901.1	886.1	865.9	840.5	815.2	789.9	764.6	745.9
40°	910.5	894.4	878.1	862.0	845.8	824.6	798.4	772.3	746.1	719.9	700.8
42.5°	873.6	856.6	839.6	822.4	805.4	783.4	756.4	729.3	702.3	675.3	655.5
45°	815.9	797.7	779.7	761.6	743.5	720.3	692.0	663.7	635.3	607.0	587.9
47.5°	759.5	740.4	721.2	702.0	682.9	658.7	629.5	600.2	570.9	541.7	522.7
50°	718.7	699.6	680.4	661.2	642.1	617.7	588.0	558.3	528.6	499.0	480.4
52.5°	678.9	658.9	638.9	618.9	598.8	574.3	545.3	516.3	487.2	458.2	440.2
55°	620.4	599.4	578.3	557.2	536.2	511.1	482.0	452.8	423.7	394.6	378.3
57.5°	560.4	538.8	517.2	495.7	474.0	449.2	421.3	393.2	365.3	337.2	322.4
60°	519.6	498.0	476.4	454.9	433.2	408.6	380.8	353.0	325.2	297.5	283.7
62.5°	479.8	458.2	436.7	415.0	393.5	369.4	342.9	316.4	289.9	263.5	250.3
65°	418.8	397.0	375.2	353.3	331.4	308.4	284.1	259.8	235.5	211.3	202.1
67.5°	360.0	338.4	316.7	295.0	273.3	251.5	229.7	207.9	186.0	164.1	159.9
70°	319.3	298.3	277.2	256.2	235.1	215.3	196.7	178.1	159.5	140.9	138.2
72.5°	280.4	260.2	240.1	219.9	199.7	182.1	167.2	152.3	137.3	122.4	120.1
75°	223.4	204.5	185.6	166.8	147.8	133.8	124.6	115.5	106.3	97.1	95.2
77.5°	167.3	150.8	134.2	117.6	101.0	90.5	86.1	81.7	77.2	72.9	71.8
80°	132.3	118.6	104.8	91.0	77.3	69.1	66.4	63.7	61.0	58.3	57.2
82.5°	100.3	89.5	78.8	68.0	57.4	51.0	49.2	47.4	45.6	43.7	43.1
85°	52.2	46.5	40.9	35.2	29.5	26.3	25.5	24.7	23.8	23.1	23.1
87.5°	15.8	14.6	13.4	12.2	11.1	10.7	11.1	11.5	11.9	12.3	12.3
90°	1.1	3.9	6.7	9.4	12.1	14.5	16.6	18.5	20.5	22.5	23.8
92.5°	22.7	22.5	22.3	22.0	21.8	22.1	23.1	24.2	25.1	26.1	26.8
95°	73.2	65.0	56.7	48.5	40.2	36.9	38.7	40.4	42.2	44.0	45.2
97.5°	145.4	122.1	98.8	75.5	52.2	42.6	46.7	50.7	54.7	58.8	59.8
100°	199.4	165.1	130.8	96.5	62.2	47.2	51.4	55.7	60.0	64.2	66.2
102.5°	258.9	251.7	244.4	237.1	229.9	208.4	172.9	137.2	101.6	66.0	68.6
105°	342.5	350.0	357.5	365.0	372.6	342.1	273.8	205.4	137.0	68.8	71.5
107.5°	437.8	443.9	450.0	456.0	462.1	424.1	342.1	260.2	178.2	96.3	93.4
110°	499.2	504.4	509.6	514.9	520.1	486.6	414.2	341.9	269.5	197.2	172.1



TEST NUMBER: P331863-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	556.8	561.4	566.1	570.8	575.4	568.8	551.0	533.1	515.2	497.3	406.0
115°	647.8	652.1	656.3	660.6	664.9	670.1	676.4	682.6	688.9	695.1	579.2
117.5°	729.2	734.0	738.7	743.5	748.2	752.7	757.0	761.4	765.6	770.0	742.0
120°	788.7	792.4	796.1	799.9	803.7	807.8	812.3	816.8	821.3	825.9	828.9
122.5°	839.2	843.1	847.1	851.0	855.0	859.4	864.3	869.2	874.1	879.0	880.8
125°	916.0	919.2	922.5	925.7	929.0	933.0	937.8	942.5	947.3	952.0	953.8
127.5°	985.6	989.2	992.8	996.4	1000.1	1003.6	1007.2	1010.7	1014.3	1017.9	1020.4
130°	1029.8	1033.8	1037.8	1041.8	1045.8	1049.2	1051.9	1054.7	1057.4	1060.2	1063.0
132.5°	1074.8	1078.2	1081.6	1085.1	1088.5	1091.5	1094.3	1097.0	1099.8	1102.6	1104.9
135°	1133.5	1137.4	1141.5	1145.4	1149.5	1152.5	1154.8	1157.1	1159.4	1161.6	1164.1
137.5°	1192.7	1195.5	1198.3	1201.1	1203.9	1206.6	1209.1	1211.7	1214.3	1216.8	1219.2
140°	1231.4	1233.4	1235.5	1237.5	1239.4	1241.8	1244.6	1247.4	1250.1	1252.8	1255.1
142.5°	1263.9	1265.7	1267.5	1269.3	1271.1	1273.6	1276.8	1279.9	1283.0	1286.2	1288.2
145°	1314.9	1314.5	1314.3	1314.1	1313.8	1315.8	1320.1	1324.4	1328.6	1332.8	1334.6
147.5°	1359.2	1358.3	1357.3	1356.4	1355.4	1357.0	1361.2	1365.5	1369.7	1373.9	1375.1
150°	1388.1	1386.3	1384.6	1382.8	1381.0	1382.2	1386.2	1390.2	1394.2	1398.2	1399.7
152.5°	1412.4	1410.5	1408.5	1406.5	1404.6	1405.5	1409.3	1413.1	1416.9	1420.7	1422.2
155°	1447.8	1445.5	1443.3	1441.0	1438.8	1439.2	1442.2	1445.2	1448.2	1451.1	1452.6
157.5°	1475.5	1473.6	1471.7	1469.8	1467.9	1468.0	1470.1	1472.2	1474.3	1476.4	1478.1
160°	1491.7	1490.2	1488.7	1487.2	1485.7	1485.7	1487.2	1488.7	1490.2	1491.7	1493.2
162.5°	1506.1	1504.7	1503.2	1501.7	1500.2	1500.0	1501.3	1502.6	1504.0	1505.2	1507.0
165°	1525.5	1524.0	1522.5	1521.0	1519.5	1519.2	1519.9	1520.6	1521.4	1522.1	1523.9
167.5°	1539.9	1538.4	1536.9	1535.4	1533.9	1533.5	1534.2	1534.9	1535.6	1536.4	1538.1
170°	1548.1	1546.6	1545.1	1543.6	1542.1	1541.5	1542.1	1542.5	1543.0	1543.6	1545.3
172.5°	1553.5	1552.0	1550.5	1549.0	1547.4	1547.0	1547.4	1547.9	1548.5	1549.0	1550.7
175°	1560.4	1558.7	1557.0	1555.2	1553.5	1552.8	1553.3	1553.8	1554.3	1554.8	1556.6
177.5°	1561.5	1560.2	1558.8	1557.4	1555.9	1555.4	1555.5	1555.8	1555.9	1556.2	1557.6
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0



TEST NUMBER: P331863-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1335.1	1337.3	1339.5	1340.3	1339.9	1339.5	1339.0	1338.6
5°	1324.5	1327.0	1329.4	1330.2	1329.4	1328.6	1327.8	1327.0
7.5°	1303.1	1303.8	1304.5	1304.2	1302.7	1301.3	1300.0	1298.5
10°	1281.6	1280.8	1280.0	1278.8	1277.2	1275.6	1273.9	1272.3
12.5°	1257.0	1255.5	1254.1	1252.0	1249.4	1246.7	1244.0	1241.3
15°	1211.1	1205.9	1200.8	1196.9	1194.2	1191.5	1188.8	1186.1
17.5°	1159.1	1153.0	1146.9	1141.5	1136.9	1132.3	1127.6	1123.0
20°	1122.8	1116.1	1109.4	1103.0	1097.1	1091.2	1085.2	1079.3
22.5°	1083.1	1074.4	1065.6	1059.1	1054.7	1050.3	1045.8	1041.4
25°	1017.1	1006.1	995.0	987.5	983.3	979.3	975.3	971.2
27.5°	954.2	941.3	928.4	918.7	912.3	905.9	899.4	893.0
30°	909.7	896.0	882.2	871.7	864.4	857.1	849.9	842.6
32.5°	865.1	849.4	833.6	822.4	815.6	808.7	801.8	795.0
35°	795.2	778.2	761.2	749.7	743.8	737.8	731.9	726.0
37.5°	727.1	708.4	689.7	676.9	670.2	663.4	656.6	649.7
40°	681.6	662.4	643.3	630.3	623.2	616.2	609.2	602.1
42.5°	635.6	615.8	596.0	582.7	575.9	569.1	562.4	555.6
45°	568.7	549.5	530.4	517.6	511.1	504.6	498.1	491.7
47.5°	503.6	484.6	465.5	453.0	447.2	441.3	435.4	429.5
50°	461.8	443.1	424.5	412.3	406.7	401.0	395.4	389.7
52.5°	422.2	404.3	386.3	374.7	369.5	364.2	359.0	353.8
55°	362.2	346.0	329.8	319.2	314.0	308.9	303.8	298.7
57.5°	307.6	292.7	277.9	268.3	264.0	259.7	255.4	251.0
60°	269.9	256.2	242.4	233.4	229.0	224.7	220.4	216.1
62.5°	237.3	224.1	211.0	203.1	200.6	198.0	195.4	192.8
65°	192.9	183.7	174.5	169.5	168.7	167.9	167.2	166.4
67.5°	155.7	151.5	147.3	144.7	143.9	143.1	142.2	141.3
70°	135.5	132.8	130.1	128.2	127.1	126.0	124.9	123.8
72.5°	117.9	115.6	113.3	111.9	111.2	110.6	109.9	109.2
75°	93.3	91.5	89.6	88.5	88.2	87.9	87.7	87.4
77.5°	70.7	69.6	68.5	67.7	67.3	66.9	66.5	66.1
80°	56.1	55.1	53.9	53.4	53.4	53.4	53.4	53.4
82.5°	42.4	41.7	41.1	40.8	40.8	40.8	40.8	40.8
85°	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1
87.5°	12.4	12.4	12.4	12.5	12.6	12.7	12.8	12.9
90°	25.0	26.3	27.6	28.4	28.9	29.4	29.9	30.4
92.5°	27.4	28.1	28.8	29.2	29.5	29.8	30.1	30.4
95°	46.4	47.7	49.0	49.4	49.2	49.0	48.7	48.5
97.5°	60.8	61.8	62.8	63.5	63.8	64.1	64.4	64.6
100°	68.2	70.3	72.2	73.5	74.0	74.5	75.0	75.5
102.5°	71.2	73.8	76.4	78.1	78.8	79.5	80.2	80.9
105°	74.2	77.0	79.8	81.6	82.6	83.7	84.6	85.6
107.5°	90.6	87.8	85.0	84.1	85.1	86.1	87.1	88.1
110°	147.1	122.1	97.0	85.0	86.0	87.0	88.0	89.0



TEST NUMBER: P331863-927

CATALOG NUMBER: S122RDIW-S1005D1440U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	314.7	223.3	132.0	86.7	87.5	88.3	89.1	89.9
115°	463.3	347.4	231.5	164.5	146.5	128.4	110.4	92.4
117.5°	713.9	685.9	657.8	614.2	554.9	495.7	436.4	377.2
120°	831.9	834.9	837.9	822.4	788.7	754.9	721.0	687.3
122.5°	882.6	884.5	886.2	883.8	877.3	870.8	864.2	857.6
125°	955.5	957.3	959.0	960.3	961.1	961.8	962.6	963.3
127.5°	1022.9	1025.5	1028.0	1029.4	1029.5	1029.7	1029.8	1030.0
130°	1065.7	1068.5	1071.2	1072.5	1072.2	1072.0	1071.7	1071.4
132.5°	1107.2	1109.6	1112.0	1113.0	1112.8	1112.5	1112.3	1112.0
135°	1166.6	1169.1	1171.6	1172.6	1172.1	1171.6	1171.1	1170.6
137.5°	1221.7	1224.2	1226.6	1227.4	1226.5	1225.7	1224.9	1224.0
140°	1257.4	1259.6	1261.9	1262.3	1261.2	1259.9	1258.6	1257.4
142.5°	1290.3	1292.4	1294.4	1294.8	1293.6	1292.3	1291.1	1289.8
145°	1336.3	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1335.1
147.5°	1376.5	1377.8	1379.1	1379.2	1378.2	1377.1	1376.0	1375.0
150°	1401.2	1402.7	1404.2	1404.3	1403.1	1401.8	1400.6	1399.3
152.5°	1423.7	1425.2	1426.7	1426.6	1425.0	1423.4	1421.7	1420.1
155°	1454.1	1455.6	1457.1	1456.9	1454.9	1452.9	1450.9	1448.9
157.5°	1479.8	1481.5	1483.2	1483.0	1481.1	1479.2	1477.2	1475.3
160°	1494.7	1496.2	1497.7	1497.6	1495.9	1494.1	1492.3	1490.6
162.5°	1508.6	1510.4	1512.0	1511.8	1509.7	1507.5	1505.4	1503.2
165°	1525.7	1527.4	1529.1	1529.1	1527.4	1525.7	1523.9	1522.1
167.5°	1539.8	1541.6	1543.3	1543.1	1540.9	1538.6	1536.4	1534.1
170°	1547.1	1548.8	1550.5	1550.3	1548.1	1545.8	1543.6	1541.3
172.5°	1552.4	1554.2	1555.9	1555.7	1553.5	1551.2	1549.0	1546.7
175°	1558.3	1560.0	1561.8	1561.5	1558.9	1556.4	1553.9	1551.4
177.5°	1558.9	1560.4	1561.8	1561.5	1559.7	1558.0	1556.2	1554.3
180°	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0	1557.0

(END OF REPORT)