

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331847-927

Luminaire Tested: **S122RDIW-S1005D435U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331847-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D435U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4131.6 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331847-927

CATALOG NUMBER: S122RDIW-S1005D435U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331847-927

CATALOG NUMBER: S122RDIW-S1005D435U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	62	58
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49
3	86	77	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46	42
4	79	68	60	54	74	65	58	52	58	53	48	52	48	44	46	43	40	37
5	73	61	53	47	68	58	51	45	52	47	42	47	42	39	42	38	35	33
6	67	55	47	41	63	53	45	40	48	42	37	43	38	34	38	35	31	29
7	62	50	42	37	59	48	41	36	43	37	33	39	34	31	35	31	28	26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	23
9	54	42	35	30	51	40	33	29	37	31	27	33	29	25	30	26	23	21
10	51	39	32	27	48	37	31	26	34	28	24	31	26	23	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21660	21660	21660
5°	21742	21389	21507
10°	21577	21040	20859
15°	21329	20415	19826
20°	20984	19524	18545
25°	20633	18513	17302
30°	20144	17473	15709
35°	19669	16344	14310
40°	19191	15173	12690
45°	18630	13860	11227
50°	18053	12534	9789
55°	17464	11108	8408
60°	16779	9607	6978
65°	16000	8073	6357
70°	15073	6652	5844
75°	13936	6057	5452
80°	12301	5421	4965
85°	9670	4279	4279



TEST NUMBER: P331847-927

CATALOG NUMBER: S122RDIW-S1005D435U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.6	3.0
10°-20°	344.8	8.3
20°-30°	484.2	11.7
30°-40°	528.0	12.8
40°-50°	485.4	11.7
50°-60°	381.3	9.2
60°-70°	248.6	6.0
70°-80°	128.2	3.1
80°-90°	34.4	0.8
90°-100°	15.6	0.4
100°-110°	57.2	1.4
110°-120°	153.0	3.7
120°-130°	252.6	6.1
130°-140°	268.6	6.5
140°-150°	249.7	6.0
150°-160°	200.7	4.9
160°-170°	129.3	3.1
170°-180°	44.5	1.1
0°-30°	954.5	23.1
0°-40°	1482.5	35.9
0°-60°	2349.2	56.9
0°-90°	2760.3	66.8
90°-120°	225.9	5.5
90°-150°	996.7	24.1
90°-180°	1371.0	33.2
0°-180°	4131.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1342	1342	1342	1342	1342	
5°	1342	1335	1320	1330	1327	127
15°	1276	1261	1221	1199	1186	359
25°	1158	1117	1039	991	971	532
35°	998	934	829	755	726	624
45°	816	732	607	524	492	630
55°	620	524	395	324	299	554
65°	419	320	211	172	166	415
75°	223	141	97	89	87	236
85°	52	28	23	23	23	62
90°	0	4	7	8	9	3
95°	22	12	13	15	15	27
105°	103	107	21	24	26	110
115°	195	201	209	60	28	192
125°	275	280	286	288	290	245
135°	341	346	349	352	352	263
145°	395	395	400	403	401	247
155°	435	432	436	438	436	200
165°	458	457	457	460	457	129
175°	469	467	467	469	466	45
180°	468	468	468	468	468	



TEST NUMBER: P331847-927

CATALOG NUMBER: S122RDIW-S1005D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1346.4	1345.3	1344.2	1343.1	1342.0	1340.3	1337.9	1335.6	1333.2	1330.9	1333.0
5°	1341.5	1340.1	1338.8	1337.4	1336.1	1333.7	1330.2	1326.7	1323.2	1319.7	1322.1
7.5°	1327.7	1326.0	1324.4	1322.6	1321.0	1318.1	1314.0	1309.9	1305.8	1301.7	1302.4
10°	1316.1	1314.2	1312.2	1310.3	1308.4	1304.8	1299.4	1294.0	1288.6	1283.3	1282.5
12.5°	1301.5	1299.1	1296.8	1294.5	1292.2	1287.5	1280.6	1273.7	1266.9	1260.0	1258.5
15°	1276.0	1273.0	1270.0	1267.0	1264.1	1258.0	1248.9	1239.7	1230.5	1221.3	1216.2
17.5°	1244.6	1240.1	1235.6	1231.1	1226.5	1218.4	1206.6	1194.8	1183.0	1171.3	1165.2
20°	1221.3	1215.9	1210.5	1205.1	1199.8	1190.3	1176.8	1163.3	1149.9	1136.3	1129.6
22.5°	1196.0	1190.0	1184.0	1178.0	1171.9	1161.3	1146.1	1130.8	1115.6	1100.4	1091.7
25°	1158.2	1149.5	1140.9	1132.3	1123.6	1110.5	1092.7	1074.8	1057.0	1039.2	1028.2
27.5°	1112.5	1103.2	1093.8	1084.4	1075.0	1060.3	1040.2	1020.1	1000.1	980.0	967.1
30°	1080.5	1070.2	1060.0	1049.7	1039.5	1023.6	1002.0	980.4	958.9	937.2	923.4
32.5°	1049.4	1037.4	1025.5	1013.5	1001.5	984.5	962.5	940.5	918.5	896.4	880.7
35°	997.9	984.2	970.4	956.6	942.9	924.2	900.4	876.7	852.9	829.2	812.2
37.5°	946.5	931.4	916.2	901.1	886.1	865.9	840.5	815.2	789.9	764.6	745.9
40°	910.5	894.4	878.1	862.0	845.8	824.6	798.4	772.3	746.1	719.9	700.8
42.5°	873.6	856.6	839.6	822.4	805.4	783.4	756.4	729.3	702.3	675.3	655.5
45°	815.9	797.7	779.7	761.6	743.5	720.3	692.0	663.7	635.3	607.0	587.9
47.5°	759.5	740.4	721.2	702.0	682.9	658.7	629.5	600.2	570.9	541.7	522.7
50°	718.7	699.6	680.4	661.2	642.1	617.7	588.0	558.3	528.6	499.0	480.4
52.5°	678.9	658.9	638.9	618.9	598.8	574.3	545.3	516.3	487.2	458.2	440.2
55°	620.4	599.4	578.3	557.2	536.2	511.1	482.0	452.8	423.7	394.6	378.3
57.5°	560.4	538.8	517.2	495.7	474.0	449.2	421.3	393.2	365.3	337.2	322.4
60°	519.6	498.0	476.4	454.9	433.2	408.6	380.8	353.0	325.2	297.5	283.7
62.5°	479.8	458.2	436.7	415.0	393.5	369.4	342.9	316.4	289.9	263.5	250.3
65°	418.8	397.0	375.2	353.3	331.4	308.4	284.1	259.8	235.5	211.3	202.1
67.5°	360.0	338.4	316.7	295.0	273.3	251.5	229.7	207.9	186.0	164.1	159.9
70°	319.3	298.3	277.2	256.2	235.1	215.3	196.7	178.1	159.5	140.9	138.2
72.5°	280.4	260.2	240.1	219.9	199.7	182.1	167.2	152.3	137.3	122.4	120.1
75°	223.4	204.5	185.6	166.8	147.8	133.8	124.6	115.5	106.3	97.1	95.2
77.5°	167.3	150.8	134.2	117.6	101.0	90.5	86.1	81.7	77.2	72.9	71.8
80°	132.3	118.6	104.8	91.0	77.3	69.1	66.4	63.7	61.0	58.3	57.2
82.5°	100.3	89.5	78.8	68.0	57.4	51.0	49.2	47.4	45.6	43.7	43.1
85°	52.2	46.5	40.9	35.2	29.5	26.3	25.5	24.7	23.8	23.1	23.1
87.5°	15.6	14.0	12.5	10.9	9.3	8.6	8.8	8.9	9.0	9.1	9.0
90°	0.3	1.2	2.0	2.9	3.6	4.4	5.0	5.5	6.2	6.7	7.1
92.5°	6.8	6.7	6.7	6.6	6.6	6.7	7.0	7.3	7.5	7.8	8.1
95°	22.0	19.5	17.0	14.6	12.0	11.1	11.6	12.1	12.7	13.2	13.5
97.5°	43.6	36.7	29.7	22.7	15.7	12.8	14.0	15.2	16.5	17.7	18.0
100°	60.0	49.6	39.3	29.0	18.7	14.2	15.4	16.7	18.0	19.3	19.9
102.5°	77.8	75.7	73.4	71.3	69.1	62.7	52.0	41.3	30.6	19.8	20.6
105°	102.9	105.2	107.4	109.7	111.9	102.8	82.3	61.7	41.2	20.7	21.5
107.5°	131.6	133.4	135.2	137.0	138.9	127.5	102.8	78.2	53.6	28.9	28.0
110°	150.0	151.5	153.1	154.7	156.3	146.2	124.5	102.7	81.0	59.3	51.7



TEST NUMBER: P331847-927

CATALOG NUMBER: S122RDIW-S1005D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.3	168.7	170.2	171.5	172.9	171.0	165.6	160.2	154.8	149.5	122.0
115°	194.7	196.0	197.3	198.5	199.8	201.4	203.3	205.2	207.0	208.9	174.0
117.5°	219.1	220.5	222.0	223.4	224.8	226.2	227.5	228.8	230.1	231.4	223.0
120°	237.0	238.1	239.2	240.4	241.5	242.8	244.2	245.5	246.8	248.2	249.1
122.5°	252.2	253.3	254.5	255.7	256.9	258.3	259.8	261.2	262.7	264.2	264.7
125°	275.3	276.2	277.3	278.2	279.2	280.4	281.9	283.3	284.7	286.1	286.6
127.5°	296.2	297.3	298.3	299.4	300.6	301.6	302.7	303.7	304.8	305.9	306.7
130°	309.5	310.7	311.9	313.1	314.3	315.3	316.2	317.0	317.8	318.6	319.4
132.5°	323.1	324.0	325.0	326.1	327.1	328.0	328.8	329.7	330.5	331.4	332.1
135°	340.6	341.8	343.0	344.2	345.5	346.3	347.1	347.8	348.4	349.1	349.8
137.5°	358.5	359.3	360.1	361.0	361.8	362.6	363.4	364.2	364.9	365.7	366.4
140°	370.1	370.7	371.3	371.9	372.5	373.2	374.1	374.9	375.7	376.5	377.2
142.5°	379.9	380.4	380.9	381.4	382.0	382.8	383.7	384.6	385.6	386.5	387.1
145°	395.1	395.1	395.0	394.9	394.8	395.5	396.7	398.0	399.3	400.5	401.1
147.5°	408.4	408.2	407.9	407.7	407.3	407.8	409.1	410.4	411.6	412.9	413.3
150°	417.2	416.6	416.1	415.6	415.0	415.3	416.6	417.8	419.0	420.2	420.6
152.5°	424.5	423.9	423.3	422.7	422.1	422.4	423.5	424.7	425.8	427.0	427.4
155°	435.1	434.4	433.7	433.1	432.4	432.5	433.4	434.3	435.2	436.1	436.6
157.5°	443.4	442.8	442.3	441.7	441.2	441.2	441.8	442.4	443.1	443.7	444.2
160°	448.3	447.8	447.4	446.9	446.5	446.5	446.9	447.4	447.8	448.3	448.8
162.5°	452.7	452.2	451.7	451.3	450.8	450.8	451.1	451.5	451.9	452.3	452.9
165°	458.4	458.0	457.6	457.1	456.6	456.5	456.8	457.0	457.2	457.4	458.0
167.5°	462.8	462.3	461.9	461.4	461.0	460.9	461.1	461.3	461.5	461.7	462.2
170°	465.2	464.8	464.3	463.9	463.4	463.3	463.4	463.6	463.7	463.9	464.4
172.5°	466.8	466.4	466.0	465.5	465.0	464.9	465.0	465.2	465.3	465.5	466.0
175°	469.0	468.4	467.9	467.4	466.8	466.7	466.8	467.0	467.1	467.2	467.8
177.5°	469.3	468.9	468.4	468.0	467.6	467.4	467.5	467.5	467.6	467.6	468.1
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9



TEST NUMBER: P331847-927

CATALOG NUMBER: S122RDIW-S1005D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1335.1	1337.3	1339.5	1340.3	1339.9	1339.5	1339.0	1338.6
5°	1324.5	1327.0	1329.4	1330.2	1329.4	1328.6	1327.8	1327.0
7.5°	1303.1	1303.8	1304.5	1304.2	1302.7	1301.3	1300.0	1298.5
10°	1281.6	1280.8	1280.0	1278.8	1277.2	1275.6	1273.9	1272.3
12.5°	1257.0	1255.5	1254.1	1252.0	1249.4	1246.7	1244.0	1241.3
15°	1211.1	1205.9	1200.8	1196.9	1194.2	1191.5	1188.8	1186.1
17.5°	1159.1	1153.0	1146.9	1141.5	1136.9	1132.3	1127.6	1123.0
20°	1122.8	1116.1	1109.4	1103.0	1097.1	1091.2	1085.2	1079.3
22.5°	1083.1	1074.4	1065.6	1059.1	1054.7	1050.3	1045.8	1041.4
25°	1017.1	1006.1	995.0	987.5	983.3	979.3	975.3	971.2
27.5°	954.2	941.3	928.4	918.7	912.3	905.9	899.4	893.0
30°	909.7	896.0	882.2	871.7	864.4	857.1	849.9	842.6
32.5°	865.1	849.4	833.6	822.4	815.6	808.7	801.8	795.0
35°	795.2	778.2	761.2	749.7	743.8	737.8	731.9	726.0
37.5°	727.1	708.4	689.7	676.9	670.2	663.4	656.6	649.7
40°	681.6	662.4	643.3	630.3	623.2	616.2	609.2	602.1
42.5°	635.6	615.8	596.0	582.7	575.9	569.1	562.4	555.6
45°	568.7	549.5	530.4	517.6	511.1	504.6	498.1	491.7
47.5°	503.6	484.6	465.5	453.0	447.2	441.3	435.4	429.5
50°	461.8	443.1	424.5	412.3	406.7	401.0	395.4	389.7
52.5°	422.2	404.3	386.3	374.7	369.5	364.2	359.0	353.8
55°	362.2	346.0	329.8	319.2	314.0	308.9	303.8	298.7
57.5°	307.6	292.7	277.9	268.3	264.0	259.7	255.4	251.0
60°	269.9	256.2	242.4	233.4	229.0	224.7	220.4	216.1
62.5°	237.3	224.1	211.0	203.1	200.6	198.0	195.4	192.8
65°	192.9	183.7	174.5	169.5	168.7	167.9	167.2	166.4
67.5°	155.7	151.5	147.3	144.7	143.9	143.1	142.2	141.3
70°	135.5	132.8	130.1	128.2	127.1	126.0	124.9	123.8
72.5°	117.9	115.6	113.3	111.9	111.2	110.6	109.9	109.2
75°	93.3	91.5	89.6	88.5	88.2	87.9	87.7	87.4
77.5°	70.7	69.6	68.5	67.7	67.3	66.9	66.5	66.1
80°	56.1	55.1	53.9	53.4	53.4	53.4	53.4	53.4
82.5°	42.4	41.7	41.1	40.8	40.8	40.8	40.8	40.8
85°	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1
87.5°	8.9	8.7	8.6	8.5	8.6	8.6	8.6	8.6
90°	7.5	7.9	8.2	8.6	8.7	8.9	9.0	9.1
92.5°	8.2	8.5	8.6	8.8	8.9	9.0	9.0	9.1
95°	13.9	14.3	14.7	14.9	14.8	14.7	14.7	14.6
97.5°	18.3	18.6	18.9	19.1	19.2	19.3	19.3	19.4
100°	20.5	21.1	21.7	22.1	22.3	22.4	22.5	22.7
102.5°	21.4	22.2	23.0	23.4	23.7	23.9	24.1	24.3
105°	22.3	23.1	24.0	24.6	24.8	25.1	25.4	25.7
107.5°	27.3	26.4	25.5	25.3	25.6	25.9	26.1	26.5
110°	44.2	36.7	29.2	25.5	25.8	26.1	26.5	26.8



TEST NUMBER: P331847-927

CATALOG NUMBER: S122RDIW-S1005D435U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	94.6	67.1	39.7	26.1	26.3	26.5	26.8	27.0
115°	139.3	104.4	69.6	49.4	44.0	38.6	33.2	27.7
117.5°	214.5	206.1	197.6	184.6	166.8	148.9	131.2	113.4
120°	250.0	250.9	251.8	247.2	237.0	226.9	216.7	206.5
122.5°	265.2	265.8	266.3	265.6	263.6	261.7	259.7	257.7
125°	287.2	287.7	288.2	288.6	288.8	289.1	289.3	289.5
127.5°	307.4	308.2	309.0	309.3	309.4	309.4	309.5	309.5
130°	320.3	321.1	321.9	322.3	322.3	322.2	322.1	322.0
132.5°	332.8	333.4	334.1	334.5	334.4	334.3	334.3	334.2
135°	350.6	351.3	352.1	352.4	352.3	352.1	352.0	351.8
137.5°	367.2	367.9	368.6	368.8	368.6	368.4	368.1	367.8
140°	377.9	378.6	379.2	379.4	379.0	378.6	378.3	377.9
142.5°	387.8	388.4	389.0	389.1	388.7	388.4	388.0	387.6
145°	401.6	402.1	402.7	402.7	402.3	402.0	401.6	401.2
147.5°	413.7	414.1	414.5	414.5	414.2	413.8	413.5	413.2
150°	421.1	421.5	422.0	422.1	421.7	421.3	420.9	420.6
152.5°	427.9	428.3	428.8	428.7	428.3	427.8	427.2	426.7
155°	437.0	437.4	437.9	437.8	437.2	436.7	436.0	435.5
157.5°	444.7	445.2	445.8	445.7	445.1	444.5	443.9	443.4
160°	449.2	449.6	450.1	450.0	449.6	449.0	448.5	448.0
162.5°	453.4	453.9	454.4	454.3	453.7	453.0	452.4	451.8
165°	458.5	459.0	459.5	459.5	459.0	458.5	458.0	457.4
167.5°	462.8	463.3	463.8	463.7	463.0	462.4	461.7	461.1
170°	464.9	465.5	466.0	465.9	465.2	464.5	463.9	463.2
172.5°	466.5	467.1	467.6	467.5	466.8	466.2	465.5	464.9
175°	468.3	468.8	469.4	469.3	468.5	467.8	467.0	466.3
177.5°	468.5	468.9	469.4	469.3	468.7	468.2	467.6	467.1
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9

(END OF REPORT)