

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331852-927

Luminaire Tested: **S122RDIW-S1005D710U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331852-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D710U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4709.7 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331852-927

CATALOG NUMBER: S122RDIW-S1005D710U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331852-927

CATALOG NUMBER: S122RDIW-S1005D710U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	87	84	78	76	74	67	66	64	57	56	55	50
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47	43
3	84	75	68	62	78	70	64	59	62	57	53	53	50	47	46	43	41	37
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	41	38	36	32
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32	29
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	31	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	25	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	23	21	19
10	50	38	30	26	46	36	29	25	32	27	23	28	24	21	25	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21660	21660	21660
5°	21742	21389	21507
10°	21577	21040	20859
15°	21329	20415	19826
20°	20984	19524	18545
25°	20633	18513	17302
30°	20144	17473	15709
35°	19669	16344	14310
40°	19191	15173	12690
45°	18630	13860	11227
50°	18053	12534	9789
55°	17464	11108	8408
60°	16779	9607	6978
65°	16000	8073	6357
70°	15073	6652	5844
75°	13936	6057	5452
80°	12301	5421	4965
85°	9670	4279	4279



TEST NUMBER: P331852-927

CATALOG NUMBER: S122RDIW-S1005D710U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.6	2.7
10°-20°	344.8	7.3
20°-30°	484.2	10.3
30°-40°	528.0	11.2
40°-50°	485.4	10.3
50°-60°	381.3	8.1
60°-70°	248.6	5.3
70°-80°	128.2	2.7
80°-90°	36.0	0.8
90°-100°	44.1	0.9
100°-110°	137.1	2.9
110°-120°	234.3	5.0
120°-130°	308.1	6.5
130°-140°	345.9	7.3
140°-150°	339.1	7.2
150°-160°	284.5	6.0
160°-170°	188.7	4.0
170°-180°	65.9	1.4
0°-30°	954.5	20.3
0°-40°	1482.5	31.5
0°-60°	2349.2	49.9
0°-90°	2762.0	58.6
90°-120°	415.5	8.8
90°-150°	1408.7	29.9
90°-180°	1948.0	41.4
0°-180°	4709.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1342	1342	1342	1342	1342	
5°	1342	1335	1320	1330	1327	127
15°	1276	1261	1221	1199	1186	359
25°	1158	1117	1039	991	971	532
35°	998	934	829	755	726	624
45°	816	732	607	524	492	630
55°	620	524	395	324	299	554
65°	419	320	211	172	166	415
75°	223	141	97	89	87	236
85°	52	28	23	23	23	62
90°	1	8	21	20	20	4
95°	31	36	38	38	36	35
105°	126	128	129	130	130	133
115°	235	238	238	237	235	233
125°	342	347	346	344	343	306
135°	443	449	450	450	448	342
145°	537	541	545	545	543	336
155°	614	616	618	620	619	283
165°	668	668	668	672	669	188
175°	695	694	692	696	693	66
180°	697	697	697	697	697	



TEST NUMBER: P331852-927

CATALOG NUMBER: S122RDIW-S1005D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1346.4	1345.3	1344.2	1343.1	1342.0	1340.3	1337.9	1335.6	1333.2	1330.9	1333.0
5°	1341.5	1340.1	1338.8	1337.4	1336.1	1333.7	1330.2	1326.7	1323.2	1319.7	1322.1
7.5°	1327.7	1326.0	1324.4	1322.6	1321.0	1318.1	1314.0	1309.9	1305.8	1301.7	1302.4
10°	1316.1	1314.2	1312.2	1310.3	1308.4	1304.8	1299.4	1294.0	1288.6	1283.3	1282.5
12.5°	1301.5	1299.1	1296.8	1294.5	1292.2	1287.5	1280.6	1273.7	1266.9	1260.0	1258.5
15°	1276.0	1273.0	1270.0	1267.0	1264.1	1258.0	1248.9	1239.7	1230.5	1221.3	1216.2
17.5°	1244.6	1240.1	1235.6	1231.1	1226.5	1218.4	1206.6	1194.8	1183.0	1171.3	1165.2
20°	1221.3	1215.9	1210.5	1205.1	1199.8	1190.3	1176.8	1163.3	1149.9	1136.3	1129.6
22.5°	1196.0	1190.0	1184.0	1178.0	1171.9	1161.3	1146.1	1130.8	1115.6	1100.4	1091.7
25°	1158.2	1149.5	1140.9	1132.3	1123.6	1110.5	1092.7	1074.8	1057.0	1039.2	1028.2
27.5°	1112.5	1103.2	1093.8	1084.4	1075.0	1060.3	1040.2	1020.1	1000.1	980.0	967.1
30°	1080.5	1070.2	1060.0	1049.7	1039.5	1023.6	1002.0	980.4	958.9	937.2	923.4
32.5°	1049.4	1037.4	1025.5	1013.5	1001.5	984.5	962.5	940.5	918.5	896.4	880.7
35°	997.9	984.2	970.4	956.6	942.9	924.2	900.4	876.7	852.9	829.2	812.2
37.5°	946.5	931.4	916.2	901.1	886.1	865.9	840.5	815.2	789.9	764.6	745.9
40°	910.5	894.4	878.1	862.0	845.8	824.6	798.4	772.3	746.1	719.9	700.8
42.5°	873.6	856.6	839.6	822.4	805.4	783.4	756.4	729.3	702.3	675.3	655.5
45°	815.9	797.7	779.7	761.6	743.5	720.3	692.0	663.7	635.3	607.0	587.9
47.5°	759.5	740.4	721.2	702.0	682.9	658.7	629.5	600.2	570.9	541.7	522.7
50°	718.7	699.6	680.4	661.2	642.1	617.7	588.0	558.3	528.6	499.0	480.4
52.5°	678.9	658.9	638.9	618.9	598.8	574.3	545.3	516.3	487.2	458.2	440.2
55°	620.4	599.4	578.3	557.2	536.2	511.1	482.0	452.8	423.7	394.6	378.3
57.5°	560.4	538.8	517.2	495.7	474.0	449.2	421.3	393.2	365.3	337.2	322.4
60°	519.6	498.0	476.4	454.9	433.2	408.6	380.8	353.0	325.2	297.5	283.7
62.5°	479.8	458.2	436.7	415.0	393.5	369.4	342.9	316.4	289.9	263.5	250.3
65°	418.8	397.0	375.2	353.3	331.4	308.4	284.1	259.8	235.5	211.3	202.1
67.5°	360.0	338.4	316.7	295.0	273.3	251.5	229.7	207.9	186.0	164.1	159.9
70°	319.3	298.3	277.2	256.2	235.1	215.3	196.7	178.1	159.5	140.9	138.2
72.5°	280.4	260.2	240.1	219.9	199.7	182.1	167.2	152.3	137.3	122.4	120.1
75°	223.4	204.5	185.6	166.8	147.8	133.8	124.6	115.5	106.3	97.1	95.2
77.5°	167.3	150.8	134.2	117.6	101.0	90.5	86.1	81.7	77.2	72.9	71.8
80°	132.3	118.6	104.8	91.0	77.3	69.1	66.4	63.7	61.0	58.3	57.2
82.5°	100.3	89.5	78.8	68.0	57.4	51.0	49.2	47.4	45.6	43.7	43.1
85°	52.2	46.5	40.9	35.2	29.5	26.3	25.5	24.7	23.8	23.1	23.1
87.5°	15.7	14.3	12.8	11.4	10.0	9.6	10.1	10.8	11.3	11.9	11.6
90°	0.6	2.1	3.7	5.3	6.9	9.1	12.0	14.8	17.7	20.6	20.3
92.5°	10.5	11.6	12.8	13.9	15.1	16.0	16.6	17.3	18.0	18.7	18.8
95°	30.6	31.8	33.2	34.5	35.8	36.6	36.8	37.1	37.4	37.6	37.6
97.5°	55.8	57.0	58.1	59.3	60.4	61.2	61.8	62.3	62.7	63.2	63.2
100°	74.6	75.7	76.8	77.8	78.8	79.5	79.9	80.3	80.7	81.1	81.1
102.5°	94.4	95.2	96.1	96.9	97.8	98.4	98.9	99.4	99.9	100.4	100.5
105°	126.4	126.7	127.1	127.5	127.9	128.3	128.6	128.8	129.0	129.4	129.6
107.5°	158.6	159.1	159.8	160.3	160.9	161.2	161.2	161.2	161.2	161.2	161.3
110°	179.3	180.1	180.9	181.6	182.4	182.8	182.8	182.8	182.8	182.8	182.8



TEST NUMBER: P331852-927

CATALOG NUMBER: S122RDIW-S1005D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	201.8	202.6	203.4	204.2	205.0	205.3	205.3	205.1	205.0	204.9	204.6
115°	235.1	235.9	236.7	237.5	238.3	238.5	238.3	238.0	237.7	237.5	237.3
117.5°	268.3	269.3	270.4	271.4	272.4	272.6	271.9	271.2	270.5	269.7	269.4
120°	290.4	291.4	292.5	293.5	294.5	294.5	293.5	292.5	291.4	290.4	290.4
122.5°	310.6	311.9	313.1	314.3	315.6	315.9	315.1	314.4	313.7	313.0	312.7
125°	342.1	343.3	344.4	345.6	346.8	347.2	346.8	346.4	346.0	345.6	345.2
127.5°	372.8	374.3	375.8	377.2	378.7	379.3	378.8	378.3	377.9	377.4	376.9
130°	392.1	393.8	395.5	397.2	398.9	399.6	399.3	399.1	398.8	398.5	398.3
132.5°	413.8	415.1	416.5	417.9	419.2	420.0	420.0	420.1	420.2	420.2	419.6
135°	442.7	444.1	445.5	446.9	448.4	449.2	449.5	449.8	450.0	450.3	450.1
137.5°	473.1	474.3	475.5	476.7	477.8	478.6	478.9	479.3	479.6	479.9	479.8
140°	491.5	492.6	493.8	495.0	496.1	497.0	497.7	498.4	499.0	499.6	499.6
142.5°	510.2	511.4	512.6	513.8	514.9	515.8	516.2	516.7	517.1	517.5	517.6
145°	537.3	538.2	539.1	540.0	541.0	541.8	542.6	543.4	544.2	544.9	545.0
147.5°	561.4	562.4	563.6	564.7	565.8	566.6	567.1	567.6	568.2	568.7	568.9
150°	577.8	578.6	579.4	580.2	581.0	581.6	582.2	582.7	583.2	583.8	584.2
152.5°	592.4	593.2	594.0	594.8	595.6	596.3	596.9	597.5	598.2	598.8	599.3
155°	614.3	614.7	615.1	615.4	615.8	616.2	616.6	617.0	617.4	617.8	618.5
157.5°	633.0	633.3	633.5	633.7	634.1	634.3	634.5	634.8	635.0	635.3	636.1
160°	644.3	644.5	644.8	645.1	645.3	645.5	645.6	645.8	645.9	646.0	646.8
162.5°	654.6	654.7	654.7	654.7	654.8	654.9	655.1	655.2	655.3	655.5	656.3
165°	668.4	668.2	668.1	668.0	667.9	667.8	667.8	667.8	667.8	667.8	668.7
167.5°	679.9	679.5	679.1	678.7	678.3	678.1	678.1	678.0	678.0	678.0	678.9
170°	686.0	685.6	685.2	684.8	684.4	684.2	684.0	683.9	683.8	683.7	684.6
172.5°	690.2	689.8	689.4	689.0	688.6	688.4	688.2	688.2	688.0	687.9	688.8
175°	695.4	695.1	694.7	694.3	693.9	693.6	693.2	693.0	692.8	692.4	693.4
177.5°	697.5	697.2	696.9	696.6	696.2	696.0	695.8	695.6	695.4	695.1	695.8
180°	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6



TEST NUMBER: P331852-927

CATALOG NUMBER: S122RDIW-S1005D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1335.1	1337.3	1339.5	1340.3	1339.9	1339.5	1339.0	1338.6
5°	1324.5	1327.0	1329.4	1330.2	1329.4	1328.6	1327.8	1327.0
7.5°	1303.1	1303.8	1304.5	1304.2	1302.7	1301.3	1300.0	1298.5
10°	1281.6	1280.8	1280.0	1278.8	1277.2	1275.6	1273.9	1272.3
12.5°	1257.0	1255.5	1254.1	1252.0	1249.4	1246.7	1244.0	1241.3
15°	1211.1	1205.9	1200.8	1196.9	1194.2	1191.5	1188.8	1186.1
17.5°	1159.1	1153.0	1146.9	1141.5	1136.9	1132.3	1127.6	1123.0
20°	1122.8	1116.1	1109.4	1103.0	1097.1	1091.2	1085.2	1079.3
22.5°	1083.1	1074.4	1065.6	1059.1	1054.7	1050.3	1045.8	1041.4
25°	1017.1	1006.1	995.0	987.5	983.3	979.3	975.3	971.2
27.5°	954.2	941.3	928.4	918.7	912.3	905.9	899.4	893.0
30°	909.7	896.0	882.2	871.7	864.4	857.1	849.9	842.6
32.5°	865.1	849.4	833.6	822.4	815.6	808.7	801.8	795.0
35°	795.2	778.2	761.2	749.7	743.8	737.8	731.9	726.0
37.5°	727.1	708.4	689.7	676.9	670.2	663.4	656.6	649.7
40°	681.6	662.4	643.3	630.3	623.2	616.2	609.2	602.1
42.5°	635.6	615.8	596.0	582.7	575.9	569.1	562.4	555.6
45°	568.7	549.5	530.4	517.6	511.1	504.6	498.1	491.7
47.5°	503.6	484.6	465.5	453.0	447.2	441.3	435.4	429.5
50°	461.8	443.1	424.5	412.3	406.7	401.0	395.4	389.7
52.5°	422.2	404.3	386.3	374.7	369.5	364.2	359.0	353.8
55°	362.2	346.0	329.8	319.2	314.0	308.9	303.8	298.7
57.5°	307.6	292.7	277.9	268.3	264.0	259.7	255.4	251.0
60°	269.9	256.2	242.4	233.4	229.0	224.7	220.4	216.1
62.5°	237.3	224.1	211.0	203.1	200.6	198.0	195.4	192.8
65°	192.9	183.7	174.5	169.5	168.7	167.9	167.2	166.4
67.5°	155.7	151.5	147.3	144.7	143.9	143.1	142.2	141.3
70°	135.5	132.8	130.1	128.2	127.1	126.0	124.9	123.8
72.5°	117.9	115.6	113.3	111.9	111.2	110.6	109.9	109.2
75°	93.3	91.5	89.6	88.5	88.2	87.9	87.7	87.4
77.5°	70.7	69.6	68.5	67.7	67.3	66.9	66.5	66.1
80°	56.1	55.1	53.9	53.4	53.4	53.4	53.4	53.4
82.5°	42.4	41.7	41.1	40.8	40.8	40.8	40.8	40.8
85°	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1
87.5°	11.3	11.1	10.8	10.7	10.7	10.8	10.8	10.8
90°	20.0	19.8	19.6	19.5	19.6	19.7	19.9	20.0
92.5°	18.8	18.9	18.9	18.9	18.9	19.0	19.0	19.0
95°	37.6	37.6	37.6	37.5	37.2	37.0	36.7	36.4
97.5°	63.2	63.2	63.2	63.2	63.2	63.2	63.1	63.1
100°	81.1	81.1	81.1	81.0	81.0	80.8	80.6	80.6
102.5°	100.6	100.7	100.8	100.8	100.7	100.5	100.4	100.3
105°	129.8	130.1	130.4	130.5	130.5	130.5	130.5	130.5
107.5°	161.4	161.5	161.6	161.4	160.7	160.2	159.5	159.0
110°	182.8	182.8	182.8	182.6	182.2	181.8	181.4	181.1



TEST NUMBER: P331852-927

CATALOG NUMBER: S122RDIW-S1005D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	204.3	204.0	203.7	203.4	203.1	202.8	202.5	202.2
115°	237.3	237.1	236.9	236.7	236.3	235.9	235.5	235.1
117.5°	269.1	268.8	268.5	268.1	267.7	267.3	266.9	266.5
120°	290.4	290.4	290.4	290.2	289.8	289.4	289.0	288.6
122.5°	312.4	312.0	311.7	311.4	311.1	310.9	310.5	310.3
125°	344.8	344.4	344.0	343.8	343.7	343.6	343.4	343.3
127.5°	376.4	376.0	375.5	375.1	374.6	374.2	373.8	373.4
130°	398.1	397.8	397.5	397.1	396.6	396.1	395.5	395.1
132.5°	419.1	418.4	417.9	417.4	417.0	416.5	416.1	415.7
135°	450.0	449.9	449.8	449.5	449.1	448.7	448.3	447.9
137.5°	479.7	479.6	479.5	479.2	478.6	478.2	477.6	477.1
140°	499.6	499.6	499.6	499.4	498.9	498.4	497.8	497.3
142.5°	517.8	517.8	517.9	517.8	517.2	516.7	516.2	515.6
145°	545.2	545.3	545.4	545.3	544.7	544.2	543.7	543.2
147.5°	569.3	569.5	569.8	569.7	569.3	568.7	568.2	567.8
150°	584.5	584.9	585.3	585.3	584.9	584.5	584.2	583.8
152.5°	599.8	600.2	600.8	600.8	600.2	599.8	599.3	598.8
155°	619.1	619.8	620.4	620.6	620.2	619.8	619.4	619.0
157.5°	637.0	637.9	638.7	638.9	638.3	637.6	637.0	636.4
160°	647.6	648.4	649.2	649.3	648.8	648.2	647.8	647.2
162.5°	657.2	658.1	659.0	659.1	658.5	657.9	657.3	656.6
165°	669.6	670.5	671.5	671.6	670.9	670.3	669.6	669.0
167.5°	679.9	680.7	681.7	681.8	681.1	680.4	679.8	679.1
170°	685.5	686.4	687.3	687.4	686.6	685.8	685.0	684.2
172.5°	689.8	690.6	691.6	691.6	690.9	690.1	689.3	688.5
175°	694.3	695.2	696.2	696.2	695.4	694.7	693.9	693.1
177.5°	696.4	697.0	697.7	697.7	697.0	696.4	695.8	695.1
180°	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6

(END OF REPORT)