

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331854-927

Luminaire Tested: **S122RDIW-S1005D970U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331854-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D970U927-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5681.8 lumens  
Efficiency: N/A  
Efficacy: 84.3 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	92	88	92	88	85	83	76	74	72	64	63	61	53	52	51	46
2	91	84	78	74	84	78	73	69	67	64	61	57	55	52	48	46	45	40
3	84	75	68	62	77	70	64	59	60	56	52	52	48	45	43	41	39	35
4	77	67	59	54	71	63	56	51	54	49	45	47	43	40	39	37	35	31
5	71	60	52	47	66	56	49	44	49	44	40	42	38	35	36	33	31	28
6	66	54	47	41	61	51	44	39	45	39	35	39	35	31	33	30	28	25
7	61	49	42	37	57	47	40	35	41	35	32	36	31	28	31	27	25	22
8	57	45	38	33	53	43	36	31	38	32	28	33	29	26	28	25	23	20
9	53	42	34	30	50	39	33	28	35	29	26	30	26	23	26	23	21	19
10	50	38	31	27	47	36	30	26	32	27	23	28	24	21	25	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	28208	28208	28208	28208
5°	31504	28386	25167	28386
10°	34954	28186	21815	28186
15°	36672	27773	17188	27773
20°	31792	27161	14874	27161
25°	20851	26323	13279	26323
30°	14033	25307	12020	25307
35°	11367	24025	10841	24025
40°	10108	22634	10030	22634
45°	9149	21000	8953	21000
50°	8324	19381	8297	19381
55°	7828	17582	7724	17582
60°	6546	15936	6468	15936
65°	5521	14472	6262	14472
70°	5103	12925	5906	12925
75°	4772	11248	5452	11248
80°	4407	9261	4854	9261
85°	4057	7317	4279	7317



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.6	2.9
10°-20°	461.5	8.1
20°-30°	594.7	10.5
30°-40°	565.1	9.9
40°-50°	484.1	8.5
50°-60°	368.7	6.5
60°-70°	233.1	4.1
70°-80°	116.4	2.0
80°-90°	34.1	0.6
90°-100°	60.2	1.1
100°-110°	187.1	3.3
110°-120°	319.9	5.6
120°-130°	420.6	7.4
130°-140°	472.1	8.3
140°-150°	462.9	8.1
150°-160°	388.3	6.8
160°-170°	257.5	4.5
170°-180°	90.0	1.6
0°-30°	1221.8	21.5
0°-40°	1786.9	31.4
0°-60°	2639.7	46.5
0°-90°	3023.2	53.2
90°-120°	567.2	10.0
90°-150°	1922.8	33.8
90°-180°	2659.0	46.8
0°-180°	5681.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1747	1747	1747	1747	1747	
5°	1944	1751	1553	1751	1944	192
15°	2194	1662	1028	1662	2194	592
25°	1170	1478	745	1478	1170	555
35°	577	1219	550	1219	577	369
45°	401	920	392	920	401	310
55°	278	625	274	625	278	244
65°	144	379	164	379	144	147
75°	76	180	87	180	76	81
85°	22	40	23	40	22	24
90°	27	1	27	1	27	13
95°	50	42	50	42	50	55
105°	178	172	178	172	178	187
115°	321	321	321	321	321	317
125°	469	467	469	467	469	418
135°	611	604	611	604	611	471
145°	741	733	741	733	741	463
155°	845	838	845	838	845	389
165°	913	912	913	912	913	258
175°	946	949	946	949	946	90
180°	951	951	951	951	951	



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1818.0	1819.5	1820.9	1817.5	1817.5	1814.6	1808.3	1803.4	1789.9	1787.9	1787.9
5°	1943.8	1942.6	1945.0	1937.1	1926.2	1923.7	1912.2	1897.0	1881.3	1863.7	1860.0
7.5°	2068.9	2067.0	2062.1	2060.9	2052.5	2034.1	2015.5	1995.7	1969.5	1943.9	1931.0
10°	2132.0	2152.0	2139.8	2118.6	2122.9	2094.4	2079.2	2053.1	2031.2	1993.0	1984.5
12.5°	2194.1	2202.0	2198.1	2186.1	2180.6	2160.8	2140.3	2117.7	2077.3	2043.0	2013.1
15°	2193.9	2205.4	2208.4	2204.8	2207.9	2206.6	2195.7	2176.9	2141.7	2104.0	2071.2
17.5°	2031.9	2039.9	2059.8	2073.3	2090.3	2126.3	2144.0	2150.9	2145.7	2124.2	2101.1
20°	1850.3	1836.9	1892.8	1921.4	1945.6	2006.3	2058.5	2078.5	2110.7	2110.1	2104.0
22.5°	1592.9	1596.1	1649.0	1682.9	1753.8	1814.5	1874.0	1949.4	2011.7	2052.8	2076.9
25°	1170.4	1193.5	1246.3	1292.4	1371.3	1484.2	1586.8	1705.8	1818.1	1906.8	1991.2
27.5°	879.0	880.7	922.6	965.2	1012.1	1104.6	1233.7	1375.9	1536.0	1668.1	1820.0
30°	752.7	749.1	766.7	792.8	832.9	904.5	1001.6	1141.3	1300.9	1500.0	1677.3
32.5°	663.4	663.6	676.8	696.2	729.4	777.8	844.3	957.7	1108.6	1304.3	1512.2
35°	576.7	576.1	585.8	599.8	613.7	644.7	690.2	749.7	853.5	1036.3	1248.7
37.5°	514.5	517.2	522.0	530.7	546.1	563.3	590.7	630.6	704.6	812.6	991.2
40°	479.6	480.8	487.4	494.7	503.8	517.2	539.6	571.9	625.9	712.1	842.6
42.5°	447.5	448.8	453.4	460.3	467.5	480.8	499.4	527.2	571.0	638.3	745.9
45°	400.7	400.7	404.9	408.0	415.8	427.9	443.1	466.2	496.5	546.4	618.0
47.5°	356.7	356.8	359.7	364.9	369.8	379.3	394.2	413.0	435.1	473.6	534.8
50°	331.4	332.1	333.9	338.1	341.2	349.7	361.2	377.6	400.7	430.4	481.4
52.5°	311.1	310.7	313.0	314.8	316.9	323.0	331.6	346.0	366.6	392.5	434.7
55°	278.1	275.6	279.2	282.3	284.1	286.5	291.4	300.5	318.1	339.9	371.5
57.5°	236.8	235.8	238.4	241.1	246.8	253.4	257.5	263.3	272.4	288.1	319.4
60°	202.7	202.7	208.2	210.0	216.7	225.2	233.7	238.6	247.7	258.0	281.1
62.5°	172.6	173.2	175.7	177.5	181.3	191.7	203.6	214.3	222.9	232.7	248.0
65°	144.5	145.7	145.7	146.9	149.3	151.8	156.6	165.1	180.3	194.2	205.8
67.5°	122.6	123.0	123.3	124.5	125.2	127.9	129.8	133.6	137.0	150.3	164.6
70°	108.1	109.9	109.2	110.5	111.1	112.3	114.7	116.5	122.0	125.1	133.6
72.5°	94.4	95.8	95.7	96.4	98.0	98.2	100.1	102.0	105.5	108.1	112.6
75°	76.5	75.9	76.5	77.7	78.3	78.9	78.9	81.4	83.2	85.6	88.6
77.5°	59.0	59.7	59.5	59.7	59.7	60.8	60.7	61.8	63.6	64.8	66.3
80°	47.4	47.9	47.4	47.9	48.6	49.2	48.6	49.2	51.0	52.2	52.2
82.5°	36.7	36.8	37.2	37.3	37.4	37.5	38.3	38.5	39.8	39.6	40.1
85°	21.9	21.2	21.2	21.2	21.9	22.5	21.9	21.9	22.5	22.5	22.5
87.5°	13.2	13.7	13.6	13.6	13.5	13.6	13.6	14.2	13.8	14.3	13.1
90°	27.3	27.1	26.9	26.8	26.5	26.6	27.0	27.3	27.7	28.0	24.2
92.5°	26.0	26.0	25.9	25.9	25.8	25.8	25.7	25.7	25.6	25.5	24.6
95°	49.7	50.1	50.5	50.8	51.2	51.3	51.3	51.3	51.3	51.3	51.0
97.5°	86.2	86.2	86.3	86.3	86.3	86.3	86.3	86.3	86.3	86.3	85.6
100°	110.0	110.1	110.3	110.4	110.7	110.7	110.7	110.7	110.7	110.7	110.2
102.5°	136.9	137.0	137.2	137.4	137.6	137.6	137.4	137.4	137.2	137.0	136.3
105°	178.2	178.2	178.2	178.2	178.2	177.9	177.6	177.2	176.9	176.5	176.2
107.5°	217.0	217.8	218.6	219.4	220.2	220.5	220.5	220.3	220.1	220.0	220.0
110°	247.2	247.6	248.2	248.7	249.3	249.5	249.5	249.5	249.5	249.5	249.5



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	276.0	276.4	276.8	277.2	277.6	278.0	278.5	278.8	279.2	279.7	279.9
115°	320.9	321.5	322.0	322.6	323.1	323.4	323.6	323.8	324.0	324.2	324.5
117.5°	363.8	364.3	364.9	365.4	365.9	366.4	366.9	367.3	367.7	368.1	369.2
120°	394.0	394.5	395.1	395.5	396.1	396.4	396.4	396.4	396.4	396.4	397.8
122.5°	423.5	423.9	424.3	424.7	425.1	425.5	425.9	426.4	426.7	427.1	428.2
125°	468.6	468.7	469.0	469.1	469.3	469.7	470.2	470.7	471.3	471.8	472.3
127.5°	509.7	510.2	510.8	511.4	511.9	512.5	513.2	513.8	514.4	515.2	515.8
130°	539.2	539.9	540.6	541.3	542.0	542.6	543.0	543.3	543.7	544.0	544.4
132.5°	567.4	568.0	568.5	569.2	569.7	570.4	571.2	572.0	572.7	573.5	573.5
135°	611.4	612.0	612.4	613.0	613.5	613.9	614.1	614.3	614.4	614.6	614.3
137.5°	651.2	651.9	652.6	653.3	654.0	654.5	654.7	654.7	654.9	655.1	654.6
140°	678.8	679.5	680.2	681.0	681.7	682.0	682.0	682.0	682.0	682.0	681.1
142.5°	703.9	704.6	705.3	706.0	706.7	706.9	706.9	706.7	706.5	706.4	705.8
145°	741.4	742.1	742.8	743.5	744.3	744.5	744.3	744.2	743.9	743.8	742.8
147.5°	774.9	775.6	776.3	777.0	777.6	777.8	777.4	777.0	776.6	776.2	775.5
150°	796.8	797.3	797.8	798.4	798.9	798.9	798.4	797.8	797.3	796.8	796.1
152.5°	817.3	817.9	818.6	819.4	820.0	820.0	819.4	818.6	817.9	817.3	816.4
155°	844.9	845.4	846.0	846.5	847.0	846.8	846.0	845.1	844.1	843.3	842.7
157.5°	868.6	869.5	870.4	871.2	872.0	871.9	870.7	869.5	868.2	867.0	866.7
160°	883.4	884.2	884.9	885.6	886.3	886.1	885.0	883.9	882.9	881.8	881.6
162.5°	896.3	897.1	897.9	898.8	899.7	899.5	898.3	897.1	895.9	894.6	894.5
165°	913.1	914.0	914.9	915.8	916.6	916.5	915.2	914.0	912.8	911.5	911.5
167.5°	926.9	927.8	928.8	929.7	930.6	930.4	929.2	928.0	926.7	925.4	925.5
170°	934.0	935.0	936.1	937.2	938.3	938.2	936.9	935.6	934.4	933.2	933.3
172.5°	939.8	940.8	941.9	942.9	944.0	943.9	942.7	941.4	940.2	938.9	939.1
175°	946.0	947.1	948.2	949.2	950.3	950.1	949.0	947.7	946.4	945.2	945.5
177.5°	948.9	949.7	950.6	951.4	952.3	952.3	951.4	950.6	949.7	948.9	949.2
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1788.9	1784.9	1781.6	1772.8	1768.5	1758.7	1757.3	1756.8	1744.2	1732.0	1728.6
5°	1850.3	1840.6	1826.1	1809.0	1791.4	1773.2	1761.1	1751.4	1727.0	1704.0	1690.7
7.5°	1912.2	1891.3	1866.2	1834.1	1807.2	1777.1	1754.8	1734.7	1700.3	1667.2	1645.0
10°	1958.4	1924.4	1890.9	1846.7	1812.0	1778.1	1746.5	1719.2	1680.3	1636.6	1605.7
12.5°	1987.0	1949.6	1903.6	1860.3	1815.4	1772.3	1730.0	1694.9	1649.2	1604.1	1567.3
15°	2025.8	1985.7	1929.8	1867.9	1810.2	1753.8	1705.3	1661.5	1602.0	1548.0	1503.1
17.5°	2057.5	2002.3	1942.4	1870.7	1804.0	1732.2	1669.7	1613.8	1547.6	1482.4	1429.5
20°	2067.6	2013.0	1943.8	1872.2	1793.3	1708.9	1641.5	1580.8	1509.7	1438.7	1378.0
22.5°	2061.3	2018.8	1941.9	1856.2	1775.3	1687.0	1610.9	1540.5	1461.7	1389.2	1318.7
25°	2018.5	2003.9	1931.0	1837.5	1745.3	1642.7	1554.7	1477.6	1387.7	1310.0	1233.5
27.5°	1918.5	1950.0	1904.8	1805.2	1702.6	1592.7	1493.7	1406.0	1312.7	1225.3	1149.1
30°	1822.4	1894.6	1875.2	1782.9	1668.2	1560.1	1449.1	1357.4	1257.8	1168.0	1092.7
32.5°	1690.8	1810.1	1829.1	1751.8	1633.2	1514.5	1398.0	1306.9	1202.9	1108.3	1034.9
35°	1481.2	1659.7	1741.6	1692.5	1573.5	1445.4	1325.2	1218.9	1114.5	1021.0	948.2
37.5°	1231.2	1474.3	1610.9	1614.4	1505.1	1372.0	1241.0	1135.6	1028.7	936.9	858.2
40°	1069.1	1332.5	1510.4	1549.8	1457.5	1313.7	1181.3	1073.9	969.5	879.6	789.2
42.5°	923.4	1185.8	1404.5	1473.1	1399.8	1256.9	1124.0	1011.7	910.2	825.2	732.8
45°	746.7	976.1	1217.1	1339.7	1299.1	1166.7	1026.5	919.7	824.3	750.9	662.3
47.5°	629.9	791.6	1024.8	1190.6	1189.9	1069.1	931.2	828.9	740.5	671.6	599.9
50°	563.3	704.2	901.5	1089.6	1105.4	1004.1	872.9	771.6	689.0	616.8	559.1
52.5°	503.6	619.6	797.1	977.5	1022.4	934.6	807.4	713.8	633.7	567.2	517.8
55°	425.6	515.4	650.1	818.9	886.9	825.0	712.1	624.6	559.7	503.8	461.4
57.5°	360.0	427.4	535.5	671.4	750.6	711.6	618.5	547.5	491.9	441.3	407.8
60°	318.7	373.9	465.6	579.2	666.5	639.2	559.7	493.5	446.2	402.5	370.9
62.5°	279.9	327.3	405.9	498.0	578.1	566.9	501.9	446.4	404.9	365.1	338.3
65°	225.2	259.8	321.2	393.4	457.7	463.2	416.5	378.8	341.7	310.2	286.5
67.5°	179.4	201.9	245.1	305.9	354.2	371.4	342.9	314.1	284.7	260.3	239.8
70°	151.1	169.4	200.9	250.1	294.5	312.6	296.3	273.8	248.3	228.2	210.6
72.5°	122.5	140.2	163.5	199.6	237.6	257.3	251.6	235.4	214.8	198.1	181.5
75°	92.3	97.8	113.5	137.8	167.5	184.6	188.8	180.3	163.9	151.1	141.4
77.5°	68.2	71.5	79.1	91.8	111.2	126.4	132.6	131.6	120.3	112.9	103.8
80°	54.7	56.5	60.1	65.6	80.2	95.3	99.6	99.6	91.7	88.6	79.5
82.5°	41.5	42.9	45.1	48.1	54.9	68.1	72.9	73.8	68.8	64.8	57.7
85°	23.7	23.1	24.3	26.1	27.3	31.0	38.3	39.5	38.3	33.4	31.5
87.5°	12.3	12.0	11.2	10.1	10.2	10.2	12.3	14.3	12.8	11.7	11.2
90°	20.2	16.3	12.4	9.3	7.2	5.1	2.9	0.8	2.9	5.1	7.2
92.5°	23.7	22.7	21.8	20.6	19.0	17.4	15.8	14.3	15.8	17.4	19.0
95°	50.6	50.3	49.9	48.9	47.1	45.3	43.5	41.7	43.5	45.3	47.1
97.5°	85.0	84.3	83.7	82.5	81.0	79.4	77.8	76.2	77.8	79.4	81.0
100°	109.6	109.1	108.6	107.6	106.2	104.7	103.3	101.9	103.3	104.7	106.2
102.5°	135.7	135.0	134.4	133.4	132.3	131.1	130.0	128.9	130.0	131.1	132.3
105°	175.8	175.5	175.1	174.7	174.1	173.6	173.0	172.5	173.0	173.6	174.1
107.5°	220.0	220.0	220.0	219.6	218.8	218.0	217.3	216.5	217.3	218.0	218.8
110°	249.5	249.5	249.5	249.0	248.0	246.8	245.8	244.7	245.8	246.8	248.0





TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.0	280.1	280.3	279.8	278.8	277.7	276.6	275.5	276.6	277.7	278.8
115°	324.9	325.2	325.6	325.2	324.2	323.1	322.0	320.9	322.0	323.1	324.2
117.5°	370.1	371.1	372.1	371.9	370.5	369.1	367.7	366.2	367.7	369.1	370.5
120°	399.3	400.7	402.1	402.1	400.7	399.3	397.8	396.4	397.8	399.3	400.7
122.5°	429.2	430.2	431.2	430.8	429.1	427.4	425.7	424.0	425.7	427.4	429.1
125°	472.9	473.4	474.0	473.4	471.8	470.2	468.6	467.0	468.6	470.2	471.8
127.5°	516.4	517.1	517.7	517.0	515.0	512.9	510.9	508.9	510.9	512.9	515.0
130°	544.7	545.1	545.4	544.5	542.2	539.8	537.5	535.2	537.5	539.8	542.2
132.5°	573.4	573.3	573.2	572.3	570.4	568.5	566.6	564.7	566.6	568.5	570.4
135°	613.9	613.5	613.1	612.0	610.1	608.1	606.2	604.2	606.2	608.1	610.1
137.5°	654.1	653.6	653.2	652.1	650.5	649.0	647.4	645.7	647.4	649.0	650.5
140°	680.2	679.4	678.4	677.2	675.6	674.0	672.4	670.7	672.4	674.0	675.6
142.5°	705.2	704.6	704.0	702.9	701.2	699.7	698.1	696.5	698.1	699.7	701.2
145°	741.6	740.6	739.5	738.4	737.1	735.9	734.6	733.3	734.6	735.9	737.1
147.5°	774.8	774.0	773.3	772.2	770.7	769.3	767.8	766.3	767.8	769.3	770.7
150°	795.4	794.6	793.9	793.0	791.9	790.8	789.8	788.7	789.8	790.8	791.9
152.5°	815.6	814.8	813.9	812.9	811.8	810.8	809.7	808.7	809.7	810.8	811.8
155°	842.2	841.7	841.1	840.6	840.1	839.6	839.0	838.4	839.0	839.6	840.1
157.5°	866.4	866.1	865.8	865.4	865.1	864.7	864.4	864.0	864.4	864.7	865.1
160°	881.5	881.3	881.1	880.8	880.4	880.1	879.7	879.4	879.7	880.1	880.4
162.5°	894.3	894.1	893.9	893.8	893.7	893.7	893.6	893.5	893.6	893.7	893.7
165°	911.5	911.5	911.5	911.6	911.7	912.0	912.1	912.3	912.1	912.0	911.7
167.5°	925.5	925.6	925.6	925.9	926.4	926.9	927.5	928.0	927.5	926.9	926.4
170°	933.5	933.7	933.9	934.2	934.8	935.3	935.8	936.4	935.8	935.3	934.8
172.5°	939.3	939.4	939.6	940.0	940.6	941.0	941.6	942.1	941.6	941.0	940.6
175°	945.9	946.3	946.6	947.1	947.6	948.2	948.6	949.2	948.6	948.2	947.6
177.5°	949.4	949.7	950.0	950.4	950.8	951.3	951.6	952.1	951.6	951.3	950.8
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1722.4	1719.0	1712.6	1702.9	1697.1	1686.9	1680.1	1683.9	1685.0	1683.9	1683.0
5°	1676.1	1663.3	1645.8	1628.7	1613.0	1595.9	1586.3	1582.0	1573.5	1568.6	1566.2
7.5°	1620.1	1598.1	1573.3	1543.6	1518.5	1492.2	1478.7	1472.0	1454.6	1445.2	1436.9
10°	1578.3	1543.7	1518.9	1480.0	1456.3	1421.7	1398.0	1398.7	1375.0	1361.6	1351.9
12.5°	1532.2	1494.2	1452.8	1417.8	1385.0	1357.2	1328.6	1317.1	1292.0	1279.1	1252.8
15°	1455.7	1411.4	1367.7	1320.3	1287.0	1243.9	1202.6	1152.2	1111.5	1076.3	1066.6
17.5°	1372.2	1317.3	1273.5	1217.9	1160.7	1088.2	1040.4	1011.1	986.6	968.0	954.2
20°	1314.9	1259.0	1212.3	1128.5	1051.4	1002.3	967.0	944.6	919.1	899.0	888.1
22.5°	1254.7	1196.4	1132.7	1039.2	979.1	939.6	908.2	882.4	865.1	849.5	839.6
25°	1169.2	1105.4	1000.4	936.0	887.5	846.2	824.3	808.6	790.4	769.1	759.5
27.5°	1078.9	977.5	902.1	854.2	807.9	781.0	761.4	737.8	721.5	711.9	701.9
30°	1011.4	910.0	851.1	798.9	766.1	736.3	713.3	700.0	684.1	667.7	661.1
32.5°	936.0	855.1	798.7	755.2	721.9	696.6	678.3	656.7	645.3	635.3	621.2
35°	842.6	781.3	729.7	694.5	662.9	642.3	621.0	608.2	587.6	579.2	573.7
37.5°	763.4	710.3	671.8	634.6	609.6	586.8	573.8	553.5	544.5	532.7	521.3
40°	718.7	666.5	629.5	599.1	571.2	554.2	537.8	521.5	508.1	502.6	488.7
42.5°	673.1	630.6	593.6	560.3	541.6	523.6	502.9	490.8	477.1	468.2	459.5
45°	610.1	572.4	540.9	513.6	492.9	474.1	460.7	440.7	432.8	415.3	408.0
47.5°	554.8	519.8	489.6	463.7	443.5	431.3	411.7	396.0	383.4	372.6	363.3
50°	515.4	486.2	457.1	434.0	415.8	398.2	378.2	370.3	350.9	345.4	339.9
52.5°	479.4	451.8	425.1	402.5	384.3	367.2	349.5	339.2	326.1	320.7	316.6
55°	429.2	402.5	377.0	357.0	338.7	321.2	310.2	297.5	291.4	287.2	282.3
57.5°	378.7	354.7	335.1	314.8	296.5	282.5	269.9	262.2	256.0	250.3	244.5
60°	346.7	323.5	305.9	287.2	268.3	256.7	247.1	238.0	230.7	222.2	219.8
62.5°	312.6	292.5	276.3	258.0	241.6	231.1	221.8	213.2	204.5	192.1	188.7
65°	265.9	250.1	233.1	217.9	203.4	193.1	179.7	170.0	166.4	165.1	164.5
67.5°	223.6	208.7	194.2	178.6	165.3	155.7	149.0	147.5	145.0	144.3	142.5
70°	195.5	181.5	166.9	152.3	139.7	137.8	135.4	132.9	129.9	128.7	127.5
72.5°	170.2	155.7	141.2	129.5	124.1	121.8	119.4	116.9	114.9	113.7	112.9
75°	130.6	117.2	107.4	103.2	100.1	98.3	94.7	92.8	91.7	89.8	89.2
77.5°	94.0	86.4	82.0	79.3	76.1	74.1	72.1	70.3	69.0	68.6	67.7
80°	71.6	68.0	65.0	61.3	60.1	57.7	57.0	55.2	55.8	54.0	54.0
82.5°	55.6	51.0	48.5	46.7	45.6	43.6	43.0	42.1	42.2	40.9	40.9
85°	28.5	27.3	26.1	24.9	24.9	23.1	23.7	23.1	23.1	21.9	21.2
87.5°	11.1	11.2	11.0	11.8	12.6	12.9	12.8	12.3	12.2	12.1	11.6
90°	9.3	12.4	16.3	20.2	24.2	28.0	27.7	27.3	27.0	26.6	26.5
92.5°	20.6	21.8	22.7	23.7	24.6	25.5	25.6	25.7	25.7	25.8	25.8
95°	48.9	49.9	50.3	50.6	51.0	51.3	51.3	51.3	51.3	51.3	51.2
97.5°	82.5	83.7	84.3	85.0	85.6	86.3	86.3	86.3	86.3	86.3	86.3
100°	107.6	108.6	109.1	109.6	110.2	110.7	110.7	110.7	110.7	110.7	110.7
102.5°	133.4	134.4	135.0	135.7	136.3	137.0	137.2	137.4	137.4	137.6	137.6
105°	174.7	175.1	175.5	175.8	176.2	176.5	176.9	177.2	177.6	177.9	178.2
107.5°	219.6	220.0	220.0	220.0	220.0	220.0	220.1	220.3	220.5	220.5	220.2
110°	249.0	249.5	249.5	249.5	249.5	249.5	249.5	249.5	249.5	249.5	249.3



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	279.8	280.3	280.1	280.0	279.9	279.7	279.2	278.8	278.5	278.0	277.6
115°	325.2	325.6	325.2	324.9	324.5	324.2	324.0	323.8	323.6	323.4	323.1
117.5°	371.9	372.1	371.1	370.1	369.2	368.1	367.7	367.3	366.9	366.4	365.9
120°	402.1	402.1	400.7	399.3	397.8	396.4	396.4	396.4	396.4	396.4	396.1
122.5°	430.8	431.2	430.2	429.2	428.2	427.1	426.7	426.4	425.9	425.5	425.1
125°	473.4	474.0	473.4	472.9	472.3	471.8	471.3	470.7	470.2	469.7	469.3
127.5°	517.0	517.7	517.1	516.4	515.8	515.2	514.4	513.8	513.2	512.5	511.9
130°	544.5	545.4	545.1	544.7	544.4	544.0	543.7	543.3	543.0	542.6	542.0
132.5°	572.3	573.2	573.3	573.4	573.5	573.5	572.7	572.0	571.2	570.4	569.7
135°	612.0	613.1	613.5	613.9	614.3	614.6	614.4	614.3	614.1	613.9	613.5
137.5°	652.1	653.2	653.6	654.1	654.6	655.1	654.9	654.7	654.7	654.5	654.0
140°	677.2	678.4	679.4	680.2	681.1	682.0	682.0	682.0	682.0	682.0	681.7
142.5°	702.9	704.0	704.6	705.2	705.8	706.4	706.5	706.7	706.9	706.9	706.7
145°	738.4	739.5	740.6	741.6	742.8	743.8	743.9	744.2	744.3	744.5	744.3
147.5°	772.2	773.3	774.0	774.8	775.5	776.2	776.6	777.0	777.4	777.8	777.6
150°	793.0	793.9	794.6	795.4	796.1	796.8	797.3	797.8	798.4	798.9	798.9
152.5°	812.9	813.9	814.8	815.6	816.4	817.3	817.9	818.6	819.4	820.0	820.0
155°	840.6	841.1	841.7	842.2	842.7	843.3	844.1	845.1	846.0	846.8	847.0
157.5°	865.4	865.8	866.1	866.4	866.7	867.0	868.2	869.5	870.7	871.9	872.0
160°	880.8	881.1	881.3	881.5	881.6	881.8	882.9	883.9	885.0	886.1	886.3
162.5°	893.8	893.9	894.1	894.3	894.5	894.6	895.9	897.1	898.3	899.5	899.7
165°	911.6	911.5	911.5	911.5	911.5	911.5	912.8	914.0	915.2	916.5	916.6
167.5°	925.9	925.6	925.6	925.5	925.5	925.4	926.7	928.0	929.2	930.4	930.6
170°	934.2	933.9	933.7	933.5	933.3	933.2	934.4	935.6	936.9	938.2	938.3
172.5°	940.0	939.6	939.4	939.3	939.1	938.9	940.2	941.4	942.7	943.9	944.0
175°	947.1	946.6	946.3	945.9	945.5	945.2	946.4	947.7	949.0	950.1	950.3
177.5°	950.4	950.0	949.7	949.4	949.2	948.9	949.7	950.6	951.4	952.3	952.3
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1677.7	1678.6	1677.2	1678.2	1677.2	1678.6	1677.7	1683.0	1683.9	1685.0	1683.9
5°	1563.1	1555.8	1554.7	1552.8	1554.7	1555.8	1563.1	1566.2	1568.6	1573.5	1582.0
7.5°	1426.5	1425.4	1422.4	1418.1	1422.4	1425.4	1426.5	1436.9	1445.2	1454.6	1472.0
10°	1338.6	1335.5	1334.9	1330.6	1334.9	1335.5	1338.6	1351.9	1361.6	1375.0	1398.7
12.5°	1235.6	1216.1	1214.0	1203.4	1214.0	1216.1	1235.6	1252.8	1279.1	1292.0	1317.1
15°	1052.0	1048.4	1036.3	1028.3	1036.3	1048.4	1052.0	1066.6	1076.3	1111.5	1152.2
17.5°	947.1	935.3	931.4	929.8	931.4	935.3	947.1	954.2	968.0	986.6	1011.1
20°	879.6	868.7	866.9	865.7	866.9	868.7	879.6	888.1	899.0	919.1	944.6
22.5°	833.0	821.6	816.8	813.2	816.8	821.6	833.0	839.6	849.5	865.1	882.4
25°	753.4	749.1	746.7	745.4	746.7	749.1	753.4	759.5	769.1	790.4	808.6
27.5°	691.1	681.8	679.9	676.8	679.9	681.8	691.1	701.9	711.9	721.5	737.8
30°	655.6	652.6	648.3	644.7	648.3	652.6	655.6	661.1	667.7	684.1	700.0
32.5°	613.9	611.3	607.5	605.9	607.5	611.3	613.9	621.2	635.3	645.3	656.7
35°	567.6	559.1	555.5	550.0	555.5	559.1	567.6	573.7	579.2	587.6	608.2
37.5°	518.6	514.2	509.1	510.9	509.1	514.2	518.6	521.3	532.7	544.5	553.5
40°	480.8	477.8	476.6	475.9	476.6	477.8	480.8	488.7	502.6	508.1	521.5
42.5°	450.7	442.3	439.1	439.0	439.1	442.3	450.7	459.5	468.2	477.1	490.8
45°	404.9	397.0	391.6	392.1	391.6	397.0	404.9	408.0	415.3	432.8	440.7
47.5°	358.1	357.8	354.4	355.5	354.4	357.8	358.1	363.3	372.6	383.4	396.0
50°	335.7	332.1	329.6	330.3	329.6	332.1	335.7	339.9	345.4	350.9	370.3
52.5°	314.3	311.2	309.3	311.8	309.3	311.2	314.3	316.6	320.7	326.1	339.2
55°	279.2	275.6	275.0	274.4	275.0	275.6	279.2	282.3	287.2	291.4	297.5
57.5°	240.0	237.6	233.9	232.3	233.9	237.6	240.0	244.5	250.3	256.0	262.2
60°	211.8	207.0	200.9	200.3	200.9	207.0	211.8	219.8	222.2	230.7	238.0
62.5°	186.1	185.1	183.9	183.8	183.9	185.1	186.1	188.7	192.1	204.5	213.2
65°	163.3	162.7	163.3	163.9	163.3	162.7	163.3	164.5	165.1	166.4	170.0
67.5°	142.3	141.2	140.1	140.6	140.1	141.2	142.3	142.5	144.3	145.0	147.5
70°	126.3	125.6	125.1	125.1	125.1	125.6	126.3	127.5	128.7	129.9	132.9
72.5°	110.7	110.6	110.0	109.5	110.0	110.6	110.7	112.9	113.7	114.9	116.9
75°	88.6	87.4	87.4	87.4	87.4	87.4	88.6	89.2	89.8	91.7	92.8
77.5°	67.5	66.9	66.3	65.8	66.3	66.9	67.5	67.7	68.6	69.0	70.3
80°	53.4	52.8	52.2	52.2	52.2	52.8	53.4	54.0	54.0	55.8	55.2
82.5°	40.8	40.2	40.1	39.6	40.1	40.2	40.8	40.9	40.9	42.2	42.1
85°	21.9	22.5	21.9	23.1	21.9	22.5	21.9	21.2	21.9	23.1	23.1
87.5°	11.6	11.2	11.7	11.2	11.7	11.2	11.6	11.6	12.1	12.2	12.3
90°	26.8	26.9	27.1	27.3	27.1	26.9	26.8	26.5	26.6	27.0	27.3
92.5°	25.9	25.9	26.0	26.0	26.0	25.9	25.9	25.8	25.8	25.7	25.7
95°	50.8	50.5	50.1	49.7	50.1	50.5	50.8	51.2	51.3	51.3	51.3
97.5°	86.3	86.3	86.2	86.2	86.2	86.3	86.3	86.3	86.3	86.3	86.3
100°	110.4	110.3	110.1	110.0	110.1	110.3	110.4	110.7	110.7	110.7	110.7
102.5°	137.4	137.2	137.0	136.9	137.0	137.2	137.4	137.6	137.6	137.4	137.4
105°	178.2	178.2	178.2	178.2	178.2	178.2	178.2	178.2	177.9	177.6	177.2
107.5°	219.4	218.6	217.8	217.0	217.8	218.6	219.4	220.2	220.5	220.5	220.3
110°	248.7	248.2	247.6	247.2	247.6	248.2	248.7	249.3	249.5	249.5	249.5



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	277.2	276.8	276.4	276.0	276.4	276.8	277.2	277.6	278.0	278.5	278.8
115°	322.6	322.0	321.5	320.9	321.5	322.0	322.6	323.1	323.4	323.6	323.8
117.5°	365.4	364.9	364.3	363.8	364.3	364.9	365.4	365.9	366.4	366.9	367.3
120°	395.5	395.1	394.5	394.0	394.5	395.1	395.5	396.1	396.4	396.4	396.4
122.5°	424.7	424.3	423.9	423.5	423.9	424.3	424.7	425.1	425.5	425.9	426.4
125°	469.1	469.0	468.7	468.6	468.7	469.0	469.1	469.3	469.7	470.2	470.7
127.5°	511.4	510.8	510.2	509.7	510.2	510.8	511.4	511.9	512.5	513.2	513.8
130°	541.3	540.6	539.9	539.2	539.9	540.6	541.3	542.0	542.6	543.0	543.3
132.5°	569.2	568.5	568.0	567.4	568.0	568.5	569.2	569.7	570.4	571.2	572.0
135°	613.0	612.4	612.0	611.4	612.0	612.4	613.0	613.5	613.9	614.1	614.3
137.5°	653.3	652.6	651.9	651.2	651.9	652.6	653.3	654.0	654.5	654.7	654.7
140°	681.0	680.2	679.5	678.8	679.5	680.2	681.0	681.7	682.0	682.0	682.0
142.5°	706.0	705.3	704.6	703.9	704.6	705.3	706.0	706.7	706.9	706.9	706.7
145°	743.5	742.8	742.1	741.4	742.1	742.8	743.5	744.3	744.5	744.3	744.2
147.5°	777.0	776.3	775.6	774.9	775.6	776.3	777.0	777.6	777.8	777.4	777.0
150°	798.4	797.8	797.3	796.8	797.3	797.8	798.4	798.9	798.9	798.4	797.8
152.5°	819.4	818.6	817.9	817.3	817.9	818.6	819.4	820.0	820.0	819.4	818.6
155°	846.5	846.0	845.4	844.9	845.4	846.0	846.5	847.0	846.8	846.0	845.1
157.5°	871.2	870.4	869.5	868.6	869.5	870.4	871.2	872.0	871.9	870.7	869.5
160°	885.6	884.9	884.2	883.4	884.2	884.9	885.6	886.3	886.1	885.0	883.9
162.5°	898.8	897.9	897.1	896.3	897.1	897.9	898.8	899.7	899.5	898.3	897.1
165°	915.8	914.9	914.0	913.1	914.0	914.9	915.8	916.6	916.5	915.2	914.0
167.5°	929.7	928.8	927.8	926.9	927.8	928.8	929.7	930.6	930.4	929.2	928.0
170°	937.2	936.1	935.0	934.0	935.0	936.1	937.2	938.3	938.2	936.9	935.6
172.5°	942.9	941.9	940.8	939.8	940.8	941.9	942.9	944.0	943.9	942.7	941.4
175°	949.2	948.2	947.1	946.0	947.1	948.2	949.2	950.3	950.1	949.0	947.7
177.5°	951.4	950.6	949.7	948.9	949.7	950.6	951.4	952.3	952.3	951.4	950.6
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1680.1	1686.9	1697.1	1702.9	1712.6	1719.0	1722.4	1728.6	1732.0	1744.2	1756.8
5°	1586.3	1595.9	1613.0	1628.7	1645.8	1663.3	1676.1	1690.7	1704.0	1727.0	1751.4
7.5°	1478.7	1492.2	1518.5	1543.6	1573.3	1598.1	1620.1	1645.0	1667.2	1700.3	1734.7
10°	1398.0	1421.7	1456.3	1480.0	1518.9	1543.7	1578.3	1605.7	1636.6	1680.3	1719.2
12.5°	1328.6	1357.2	1385.0	1417.8	1452.8	1494.2	1532.2	1567.3	1604.1	1649.2	1694.9
15°	1202.6	1243.9	1287.0	1320.3	1367.7	1411.4	1455.7	1503.1	1548.0	1602.0	1661.5
17.5°	1040.4	1088.2	1160.7	1217.9	1273.5	1317.3	1372.2	1429.5	1482.4	1547.6	1613.8
20°	967.0	1002.3	1051.4	1128.5	1212.3	1259.0	1314.9	1378.0	1438.7	1509.7	1580.8
22.5°	908.2	939.6	979.1	1039.2	1132.7	1196.4	1254.7	1318.7	1389.2	1461.7	1540.5
25°	824.3	846.2	887.5	936.0	1000.4	1105.4	1169.2	1233.5	1310.0	1387.7	1477.6
27.5°	761.4	781.0	807.9	854.2	902.1	977.5	1078.9	1149.1	1225.3	1312.7	1406.0
30°	713.3	736.3	766.1	798.9	851.1	910.0	1011.4	1092.7	1168.0	1257.8	1357.4
32.5°	678.3	696.6	721.9	755.2	798.7	855.1	936.0	1034.9	1108.3	1202.9	1306.9
35°	621.0	642.3	662.9	694.5	729.7	781.3	842.6	948.2	1021.0	1114.5	1218.9
37.5°	573.8	586.8	609.6	634.6	671.8	710.3	763.4	858.2	936.9	1028.7	1135.6
40°	537.8	554.2	571.2	599.1	629.5	666.5	718.7	789.2	879.6	969.5	1073.9
42.5°	502.9	523.6	541.6	560.3	593.6	630.6	673.1	732.8	825.2	910.2	1011.7
45°	460.7	474.1	492.9	513.6	540.9	572.4	610.1	662.3	750.9	824.3	919.7
47.5°	411.7	431.3	443.5	463.7	489.6	519.8	554.8	599.9	671.6	740.5	828.9
50°	378.2	398.2	415.8	434.0	457.1	486.2	515.4	559.1	616.8	689.0	771.6
52.5°	349.5	367.2	384.3	402.5	425.1	451.8	479.4	517.8	567.2	633.7	713.8
55°	310.2	321.2	338.7	357.0	377.0	402.5	429.2	461.4	503.8	559.7	624.6
57.5°	269.9	282.5	296.5	314.8	335.1	354.7	378.7	407.8	441.3	491.9	547.5
60°	247.1	256.7	268.3	287.2	305.9	323.5	346.7	370.9	402.5	446.2	493.5
62.5°	221.8	231.1	241.6	258.0	276.3	292.5	312.6	338.3	365.1	404.9	446.4
65°	179.7	193.1	203.4	217.9	233.1	250.1	265.9	286.5	310.2	341.7	378.8
67.5°	149.0	155.7	165.3	178.6	194.2	208.7	223.6	239.8	260.3	284.7	314.1
70°	135.4	137.8	139.7	152.3	166.9	181.5	195.5	210.6	228.2	248.3	273.8
72.5°	119.4	121.8	124.1	129.5	141.2	155.7	170.2	181.5	198.1	214.8	235.4
75°	94.7	98.3	100.1	103.2	107.4	117.2	130.6	141.4	151.1	163.9	180.3
77.5°	72.1	74.1	76.1	79.3	82.0	86.4	94.0	103.8	112.9	120.3	131.6
80°	57.0	57.7	60.1	61.3	65.0	68.0	71.6	79.5	88.6	91.7	99.6
82.5°	43.0	43.6	45.6	46.7	48.5	51.0	55.6	57.7	64.8	68.8	73.8
85°	23.7	23.1	24.9	24.9	26.1	27.3	28.5	31.5	33.4	38.3	39.5
87.5°	12.8	12.9	12.6	11.8	11.0	11.2	11.1	11.2	11.7	12.8	14.3
90°	27.7	28.0	24.2	20.2	16.3	12.4	9.3	7.2	5.1	2.9	0.8
92.5°	25.6	25.5	24.6	23.7	22.7	21.8	20.6	19.0	17.4	15.8	14.3
95°	51.3	51.3	51.0	50.6	50.3	49.9	48.9	47.1	45.3	43.5	41.7
97.5°	86.3	86.3	85.6	85.0	84.3	83.7	82.5	81.0	79.4	77.8	76.2
100°	110.7	110.7	110.2	109.6	109.1	108.6	107.6	106.2	104.7	103.3	101.9
102.5°	137.2	137.0	136.3	135.7	135.0	134.4	133.4	132.3	131.1	130.0	128.9
105°	176.9	176.5	176.2	175.8	175.5	175.1	174.7	174.1	173.6	173.0	172.5
107.5°	220.1	220.0	220.0	220.0	220.0	220.0	219.6	218.8	218.0	217.3	216.5
110°	249.5	249.5	249.5	249.5	249.5	249.5	249.0	248.0	246.8	245.8	244.7



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	279.2	279.7	279.9	280.0	280.1	280.3	279.8	278.8	277.7	276.6	275.5
115°	324.0	324.2	324.5	324.9	325.2	325.6	325.2	324.2	323.1	322.0	320.9
117.5°	367.7	368.1	369.2	370.1	371.1	372.1	371.9	370.5	369.1	367.7	366.2
120°	396.4	396.4	397.8	399.3	400.7	402.1	402.1	400.7	399.3	397.8	396.4
122.5°	426.7	427.1	428.2	429.2	430.2	431.2	430.8	429.1	427.4	425.7	424.0
125°	471.3	471.8	472.3	472.9	473.4	474.0	473.4	471.8	470.2	468.6	467.0
127.5°	514.4	515.2	515.8	516.4	517.1	517.7	517.0	515.0	512.9	510.9	508.9
130°	543.7	544.0	544.4	544.7	545.1	545.4	544.5	542.2	539.8	537.5	535.2
132.5°	572.7	573.5	573.5	573.4	573.3	573.2	572.3	570.4	568.5	566.6	564.7
135°	614.4	614.6	614.3	613.9	613.5	613.1	612.0	610.1	608.1	606.2	604.2
137.5°	654.9	655.1	654.6	654.1	653.6	653.2	652.1	650.5	649.0	647.4	645.7
140°	682.0	682.0	681.1	680.2	679.4	678.4	677.2	675.6	674.0	672.4	670.7
142.5°	706.5	706.4	705.8	705.2	704.6	704.0	702.9	701.2	699.7	698.1	696.5
145°	743.9	743.8	742.8	741.6	740.6	739.5	738.4	737.1	735.9	734.6	733.3
147.5°	776.6	776.2	775.5	774.8	774.0	773.3	772.2	770.7	769.3	767.8	766.3
150°	797.3	796.8	796.1	795.4	794.6	793.9	793.0	791.9	790.8	789.8	788.7
152.5°	817.9	817.3	816.4	815.6	814.8	813.9	812.9	811.8	810.8	809.7	808.7
155°	844.1	843.3	842.7	842.2	841.7	841.1	840.6	840.1	839.6	839.0	838.4
157.5°	868.2	867.0	866.7	866.4	866.1	865.8	865.4	865.1	864.7	864.4	864.0
160°	882.9	881.8	881.6	881.5	881.3	881.1	880.8	880.4	880.1	879.7	879.4
162.5°	895.9	894.6	894.5	894.3	894.1	893.9	893.8	893.7	893.7	893.6	893.5
165°	912.8	911.5	911.5	911.5	911.5	911.5	911.6	911.7	912.0	912.1	912.3
167.5°	926.7	925.4	925.5	925.5	925.6	925.6	925.9	926.4	926.9	927.5	928.0
170°	934.4	933.2	933.3	933.5	933.7	933.9	934.2	934.8	935.3	935.8	936.4
172.5°	940.2	938.9	939.1	939.3	939.4	939.6	940.0	940.6	941.0	941.6	942.1
175°	946.4	945.2	945.5	945.9	946.3	946.6	947.1	947.6	948.2	948.6	949.2
177.5°	949.7	948.9	949.2	949.4	949.7	950.0	950.4	950.8	951.3	951.6	952.1
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1757.3	1758.7	1768.5	1772.8	1781.6	1784.9	1788.9	1787.9	1787.9	1789.9	1803.4
5°	1761.1	1773.2	1791.4	1809.0	1826.1	1840.6	1850.3	1860.0	1863.7	1881.3	1897.0
7.5°	1754.8	1777.1	1807.2	1834.1	1866.2	1891.3	1912.2	1931.0	1943.9	1969.5	1995.7
10°	1746.5	1778.1	1812.0	1846.7	1890.9	1924.4	1958.4	1984.5	1993.0	2031.2	2053.1
12.5°	1730.0	1772.3	1815.4	1860.3	1903.6	1949.6	1987.0	2013.1	2043.0	2077.3	2117.7
15°	1705.3	1753.8	1810.2	1867.9	1929.8	1985.7	2025.8	2071.2	2104.0	2141.7	2176.9
17.5°	1669.7	1732.2	1804.0	1870.7	1942.4	2002.3	2057.5	2101.1	2124.2	2145.7	2150.9
20°	1641.5	1708.9	1793.3	1872.2	1943.8	2013.0	2067.6	2104.0	2110.1	2110.7	2078.5
22.5°	1610.9	1687.0	1775.3	1856.2	1941.9	2018.8	2061.3	2076.9	2052.8	2011.7	1949.4
25°	1554.7	1642.7	1745.3	1837.5	1931.0	2003.9	2018.5	1991.2	1906.8	1818.1	1705.8
27.5°	1493.7	1592.7	1702.6	1805.2	1904.8	1950.0	1918.5	1820.0	1668.1	1536.0	1375.9
30°	1449.1	1560.1	1668.2	1782.9	1875.2	1894.6	1822.4	1677.3	1500.0	1300.9	1141.3
32.5°	1398.0	1514.5	1633.2	1751.8	1829.1	1810.1	1690.8	1512.2	1304.3	1108.6	957.7
35°	1325.2	1445.4	1573.5	1692.5	1741.6	1659.7	1481.2	1248.7	1036.3	853.5	749.7
37.5°	1241.0	1372.0	1505.1	1614.4	1610.9	1474.3	1231.2	991.2	812.6	704.6	630.6
40°	1181.3	1313.7	1457.5	1549.8	1510.4	1332.5	1069.1	842.6	712.1	625.9	571.9
42.5°	1124.0	1256.9	1399.8	1473.1	1404.5	1185.8	923.4	745.9	638.3	571.0	527.2
45°	1026.5	1166.7	1299.1	1339.7	1217.1	976.1	746.7	618.0	546.4	496.5	466.2
47.5°	931.2	1069.1	1189.9	1190.6	1024.8	791.6	629.9	534.8	473.6	435.1	413.0
50°	872.9	1004.1	1105.4	1089.6	901.5	704.2	563.3	481.4	430.4	400.7	377.6
52.5°	807.4	934.6	1022.4	977.5	797.1	619.6	503.6	434.7	392.5	366.6	346.0
55°	712.1	825.0	886.9	818.9	650.1	515.4	425.6	371.5	339.9	318.1	300.5
57.5°	618.5	711.6	750.6	671.4	535.5	427.4	360.0	319.4	288.1	272.4	263.3
60°	559.7	639.2	666.5	579.2	465.6	373.9	318.7	281.1	258.0	247.7	238.6
62.5°	501.9	566.9	578.1	498.0	405.9	327.3	279.9	248.0	232.7	222.9	214.3
65°	416.5	463.2	457.7	393.4	321.2	259.8	225.2	205.8	194.2	180.3	165.1
67.5°	342.9	371.4	354.2	305.9	245.1	201.9	179.4	164.6	150.3	137.0	133.6
70°	296.3	312.6	294.5	250.1	200.9	169.4	151.1	133.6	125.1	122.0	116.5
72.5°	251.6	257.3	237.6	199.6	163.5	140.2	122.5	112.6	108.1	105.5	102.0
75°	188.8	184.6	167.5	137.8	113.5	97.8	92.3	88.6	85.6	83.2	81.4
77.5°	132.6	126.4	111.2	91.8	79.1	71.5	68.2	66.3	64.8	63.6	61.8
80°	99.6	95.3	80.2	65.6	60.1	56.5	54.7	52.2	52.2	51.0	49.2
82.5°	72.9	68.1	54.9	48.1	45.1	42.9	41.5	40.1	39.6	39.8	38.5
85°	38.3	31.0	27.3	26.1	24.3	23.1	23.7	22.5	22.5	22.5	21.9
87.5°	12.3	10.2	10.2	10.1	11.2	12.0	12.3	13.1	14.3	13.8	14.2
90°	2.9	5.1	7.2	9.3	12.4	16.3	20.2	24.2	28.0	27.7	27.3
92.5°	15.8	17.4	19.0	20.6	21.8	22.7	23.7	24.6	25.5	25.6	25.7
95°	43.5	45.3	47.1	48.9	49.9	50.3	50.6	51.0	51.3	51.3	51.3
97.5°	77.8	79.4	81.0	82.5	83.7	84.3	85.0	85.6	86.3	86.3	86.3
100°	103.3	104.7	106.2	107.6	108.6	109.1	109.6	110.2	110.7	110.7	110.7
102.5°	130.0	131.1	132.3	133.4	134.4	135.0	135.7	136.3	137.0	137.2	137.4
105°	173.0	173.6	174.1	174.7	175.1	175.5	175.8	176.2	176.5	176.9	177.2
107.5°	217.3	218.0	218.8	219.6	220.0	220.0	220.0	220.0	220.0	220.1	220.3
110°	245.8	246.8	248.0	249.0	249.5	249.5	249.5	249.5	249.5	249.5	249.5





TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.6	277.7	278.8	279.8	280.3	280.1	280.0	279.9	279.7	279.2	278.8
115°	322.0	323.1	324.2	325.2	325.6	325.2	324.9	324.5	324.2	324.0	323.8
117.5°	367.7	369.1	370.5	371.9	372.1	371.1	370.1	369.2	368.1	367.7	367.3
120°	397.8	399.3	400.7	402.1	402.1	400.7	399.3	397.8	396.4	396.4	396.4
122.5°	425.7	427.4	429.1	430.8	431.2	430.2	429.2	428.2	427.1	426.7	426.4
125°	468.6	470.2	471.8	473.4	474.0	473.4	472.9	472.3	471.8	471.3	470.7
127.5°	510.9	512.9	515.0	517.0	517.7	517.1	516.4	515.8	515.2	514.4	513.8
130°	537.5	539.8	542.2	544.5	545.4	545.1	544.7	544.4	544.0	543.7	543.3
132.5°	566.6	568.5	570.4	572.3	573.2	573.3	573.4	573.5	573.5	572.7	572.0
135°	606.2	608.1	610.1	612.0	613.1	613.5	613.9	614.3	614.6	614.4	614.3
137.5°	647.4	649.0	650.5	652.1	653.2	653.6	654.1	654.6	655.1	654.9	654.7
140°	672.4	674.0	675.6	677.2	678.4	679.4	680.2	681.1	682.0	682.0	682.0
142.5°	698.1	699.7	701.2	702.9	704.0	704.6	705.2	705.8	706.4	706.5	706.7
145°	734.6	735.9	737.1	738.4	739.5	740.6	741.6	742.8	743.8	743.9	744.2
147.5°	767.8	769.3	770.7	772.2	773.3	774.0	774.8	775.5	776.2	776.6	777.0
150°	789.8	790.8	791.9	793.0	793.9	794.6	795.4	796.1	796.8	797.3	797.8
152.5°	809.7	810.8	811.8	812.9	813.9	814.8	815.6	816.4	817.3	817.9	818.6
155°	839.0	839.6	840.1	840.6	841.1	841.7	842.2	842.7	843.3	844.1	845.1
157.5°	864.4	864.7	865.1	865.4	865.8	866.1	866.4	866.7	867.0	868.2	869.5
160°	879.7	880.1	880.4	880.8	881.1	881.3	881.5	881.6	881.8	882.9	883.9
162.5°	893.6	893.7	893.7	893.8	893.9	894.1	894.3	894.5	894.6	895.9	897.1
165°	912.1	912.0	911.7	911.6	911.5	911.5	911.5	911.5	911.5	912.8	914.0
167.5°	927.5	926.9	926.4	925.9	925.6	925.6	925.5	925.5	925.4	926.7	928.0
170°	935.8	935.3	934.8	934.2	933.9	933.7	933.5	933.3	933.2	934.4	935.6
172.5°	941.6	941.0	940.6	940.0	939.6	939.4	939.3	939.1	938.9	940.2	941.4
175°	948.6	948.2	947.6	947.1	946.6	946.3	945.9	945.5	945.2	946.4	947.7
177.5°	951.6	951.3	950.8	950.4	950.0	949.7	949.4	949.2	948.9	949.7	950.6
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1808.3	1814.6	1817.5	1817.5	1820.9	1819.5	1818.0
5°	1912.2	1923.7	1926.2	1937.1	1945.0	1942.6	1943.8
7.5°	2015.5	2034.1	2052.5	2060.9	2062.1	2067.0	2068.9
10°	2079.2	2094.4	2122.9	2118.6	2139.8	2152.0	2132.0
12.5°	2140.3	2160.8	2180.6	2186.1	2198.1	2202.0	2194.1
15°	2195.7	2206.6	2207.9	2204.8	2208.4	2205.4	2193.9
17.5°	2144.0	2126.3	2090.3	2073.3	2059.8	2039.9	2031.9
20°	2058.5	2006.3	1945.6	1921.4	1892.8	1836.9	1850.3
22.5°	1874.0	1814.5	1753.8	1682.9	1649.0	1596.1	1592.9
25°	1586.8	1484.2	1371.3	1292.4	1246.3	1193.5	1170.4
27.5°	1233.7	1104.6	1012.1	965.2	922.6	880.7	879.0
30°	1001.6	904.5	832.9	792.8	766.7	749.1	752.7
32.5°	844.3	777.8	729.4	696.2	676.8	663.6	663.4
35°	690.2	644.7	613.7	599.8	585.8	576.1	576.7
37.5°	590.7	563.3	546.1	530.7	522.0	517.2	514.5
40°	539.6	517.2	503.8	494.7	487.4	480.8	479.6
42.5°	499.4	480.8	467.5	460.3	453.4	448.8	447.5
45°	443.1	427.9	415.8	408.0	404.9	400.7	400.7
47.5°	394.2	379.3	369.8	364.9	359.7	356.8	356.7
50°	361.2	349.7	341.2	338.1	333.9	332.1	331.4
52.5°	331.6	323.0	316.9	314.8	313.0	310.7	311.1
55°	291.4	286.5	284.1	282.3	279.2	275.6	278.1
57.5°	257.5	253.4	246.8	241.1	238.4	235.8	236.8
60°	233.7	225.2	216.7	210.0	208.2	202.7	202.7
62.5°	203.6	191.7	181.3	177.5	175.7	173.2	172.6
65°	156.6	151.8	149.3	146.9	145.7	145.7	144.5
67.5°	129.8	127.9	125.2	124.5	123.3	123.0	122.6
70°	114.7	112.3	111.1	110.5	109.2	109.9	108.1
72.5°	100.1	98.2	98.0	96.4	95.7	95.8	94.4
75°	78.9	78.9	78.3	77.7	76.5	75.9	76.5
77.5°	60.7	60.8	59.7	59.7	59.5	59.7	59.0
80°	48.6	49.2	48.6	47.9	47.4	47.9	47.4
82.5°	38.3	37.5	37.4	37.3	37.2	36.8	36.7
85°	21.9	22.5	21.9	21.2	21.2	21.2	21.9
87.5°	13.6	13.6	13.5	13.6	13.6	13.7	13.2
90°	27.0	26.6	26.5	26.8	26.9	27.1	27.3
92.5°	25.7	25.8	25.8	25.9	25.9	26.0	26.0
95°	51.3	51.3	51.2	50.8	50.5	50.1	49.7
97.5°	86.3	86.3	86.3	86.3	86.3	86.2	86.2
100°	110.7	110.7	110.7	110.4	110.3	110.1	110.0
102.5°	137.4	137.6	137.6	137.4	137.2	137.0	136.9
105°	177.6	177.9	178.2	178.2	178.2	178.2	178.2
107.5°	220.5	220.5	220.2	219.4	218.6	217.8	217.0
110°	249.5	249.5	249.3	248.7	248.2	247.6	247.2



TEST NUMBER: P331854-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	278.5	278.0	277.6	277.2	276.8	276.4	276.0
115°	323.6	323.4	323.1	322.6	322.0	321.5	320.9
117.5°	366.9	366.4	365.9	365.4	364.9	364.3	363.8
120°	396.4	396.4	396.1	395.5	395.1	394.5	394.0
122.5°	425.9	425.5	425.1	424.7	424.3	423.9	423.5
125°	470.2	469.7	469.3	469.1	469.0	468.7	468.6
127.5°	513.2	512.5	511.9	511.4	510.8	510.2	509.7
130°	543.0	542.6	542.0	541.3	540.6	539.9	539.2
132.5°	571.2	570.4	569.7	569.2	568.5	568.0	567.4
135°	614.1	613.9	613.5	613.0	612.4	612.0	611.4
137.5°	654.7	654.5	654.0	653.3	652.6	651.9	651.2
140°	682.0	682.0	681.7	681.0	680.2	679.5	678.8
142.5°	706.9	706.9	706.7	706.0	705.3	704.6	703.9
145°	744.3	744.5	744.3	743.5	742.8	742.1	741.4
147.5°	777.4	777.8	777.6	777.0	776.3	775.6	774.9
150°	798.4	798.9	798.9	798.4	797.8	797.3	796.8
152.5°	819.4	820.0	820.0	819.4	818.6	817.9	817.3
155°	846.0	846.8	847.0	846.5	846.0	845.4	844.9
157.5°	870.7	871.9	872.0	871.2	870.4	869.5	868.6
160°	885.0	886.1	886.3	885.6	884.9	884.2	883.4
162.5°	898.3	899.5	899.7	898.8	897.9	897.1	896.3
165°	915.2	916.5	916.6	915.8	914.9	914.0	913.1
167.5°	929.2	930.4	930.6	929.7	928.8	927.8	926.9
170°	936.9	938.2	938.3	937.2	936.1	935.0	934.0
172.5°	942.7	943.9	944.0	942.9	941.9	940.8	939.8
175°	949.0	950.1	950.3	949.2	948.2	947.1	946.0
177.5°	951.4	952.3	952.3	951.4	950.6	949.7	948.9
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8

(END OF REPORT)