

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331856-927

Luminaire Tested: **S122RDIW-S1005D970U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331856-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D970U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5421.6 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331856-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331856-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	53	50	46	44	42	38
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21660	21660	21660
5°	21742	21389	21507
10°	21577	21040	20859
15°	21329	20415	19826
20°	20984	19524	18545
25°	20633	18513	17302
30°	20144	17473	15709
35°	19669	16344	14310
40°	19191	15173	12690
45°	18630	13860	11227
50°	18053	12534	9789
55°	17464	11108	8408
60°	16779	9607	6978
65°	16000	8073	6357
70°	15073	6652	5844
75°	13936	6057	5452
80°	12301	5421	4965
85°	9670	4279	4279



TEST NUMBER: P331856-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.6	2.3
10°-20°	344.8	6.4
20°-30°	484.2	8.9
30°-40°	528.0	9.7
40°-50°	485.4	9.0
50°-60°	381.3	7.0
60°-70°	248.6	4.6
70°-80°	128.2	2.4
80°-90°	37.0	0.7
90°-100°	60.2	1.1
100°-110°	187.1	3.5
110°-120°	319.9	5.9
120°-130°	420.6	7.8
130°-140°	472.1	8.7
140°-150°	462.9	8.5
150°-160°	388.3	7.2
160°-170°	257.5	4.7
170°-180°	90.0	1.7
0°-30°	954.5	17.6
0°-40°	1482.5	27.3
0°-60°	2349.2	43.3
0°-90°	2763.0	51.0
90°-120°	567.2	10.5
90°-150°	1922.8	35.5
90°-180°	2659.0	49.0
0°-180°	5421.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1342	1342	1342	1342	1342	
5°	1342	1335	1320	1330	1327	127
15°	1276	1261	1221	1199	1186	359
25°	1158	1117	1039	991	971	532
35°	998	934	829	755	726	624
45°	816	732	607	524	492	630
55°	620	524	395	324	299	554
65°	419	320	211	172	166	415
75°	223	141	97	89	87	236
85°	52	28	23	23	23	62
90°	1	11	28	27	27	4
95°	42	49	51	51	50	48
105°	172	175	176	178	178	182
115°	321	325	324	323	321	317
125°	467	474	472	470	469	417
135°	604	613	615	614	611	467
145°	733	739	744	744	741	458
155°	838	841	843	847	845	386
165°	912	912	912	917	913	257
175°	949	947	945	950	946	90
180°	951	951	951	951	951	



TEST NUMBER: P331856-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1346.4	1345.3	1344.2	1343.1	1342.0	1340.3	1337.9	1335.6	1333.2	1330.9	1333.0
5°	1341.5	1340.1	1338.8	1337.4	1336.1	1333.7	1330.2	1326.7	1323.2	1319.7	1322.1
7.5°	1327.7	1326.0	1324.4	1322.6	1321.0	1318.1	1314.0	1309.9	1305.8	1301.7	1302.4
10°	1316.1	1314.2	1312.2	1310.3	1308.4	1304.8	1299.4	1294.0	1288.6	1283.3	1282.5
12.5°	1301.5	1299.1	1296.8	1294.5	1292.2	1287.5	1280.6	1273.7	1266.9	1260.0	1258.5
15°	1276.0	1273.0	1270.0	1267.0	1264.1	1258.0	1248.9	1239.7	1230.5	1221.3	1216.2
17.5°	1244.6	1240.1	1235.6	1231.1	1226.5	1218.4	1206.6	1194.8	1183.0	1171.3	1165.2
20°	1221.3	1215.9	1210.5	1205.1	1199.8	1190.3	1176.8	1163.3	1149.9	1136.3	1129.6
22.5°	1196.0	1190.0	1184.0	1178.0	1171.9	1161.3	1146.1	1130.8	1115.6	1100.4	1091.7
25°	1158.2	1149.5	1140.9	1132.3	1123.6	1110.5	1092.7	1074.8	1057.0	1039.2	1028.2
27.5°	1112.5	1103.2	1093.8	1084.4	1075.0	1060.3	1040.2	1020.1	1000.1	980.0	967.1
30°	1080.5	1070.2	1060.0	1049.7	1039.5	1023.6	1002.0	980.4	958.9	937.2	923.4
32.5°	1049.4	1037.4	1025.5	1013.5	1001.5	984.5	962.5	940.5	918.5	896.4	880.7
35°	997.9	984.2	970.4	956.6	942.9	924.2	900.4	876.7	852.9	829.2	812.2
37.5°	946.5	931.4	916.2	901.1	886.1	865.9	840.5	815.2	789.9	764.6	745.9
40°	910.5	894.4	878.1	862.0	845.8	824.6	798.4	772.3	746.1	719.9	700.8
42.5°	873.6	856.6	839.6	822.4	805.4	783.4	756.4	729.3	702.3	675.3	655.5
45°	815.9	797.7	779.7	761.6	743.5	720.3	692.0	663.7	635.3	607.0	587.9
47.5°	759.5	740.4	721.2	702.0	682.9	658.7	629.5	600.2	570.9	541.7	522.7
50°	718.7	699.6	680.4	661.2	642.1	617.7	588.0	558.3	528.6	499.0	480.4
52.5°	678.9	658.9	638.9	618.9	598.8	574.3	545.3	516.3	487.2	458.2	440.2
55°	620.4	599.4	578.3	557.2	536.2	511.1	482.0	452.8	423.7	394.6	378.3
57.5°	560.4	538.8	517.2	495.7	474.0	449.2	421.3	393.2	365.3	337.2	322.4
60°	519.6	498.0	476.4	454.9	433.2	408.6	380.8	353.0	325.2	297.5	283.7
62.5°	479.8	458.2	436.7	415.0	393.5	369.4	342.9	316.4	289.9	263.5	250.3
65°	418.8	397.0	375.2	353.3	331.4	308.4	284.1	259.8	235.5	211.3	202.1
67.5°	360.0	338.4	316.7	295.0	273.3	251.5	229.7	207.9	186.0	164.1	159.9
70°	319.3	298.3	277.2	256.2	235.1	215.3	196.7	178.1	159.5	140.9	138.2
72.5°	280.4	260.2	240.1	219.9	199.7	182.1	167.2	152.3	137.3	122.4	120.1
75°	223.4	204.5	185.6	166.8	147.8	133.8	124.6	115.5	106.3	97.1	95.2
77.5°	167.3	150.8	134.2	117.6	101.0	90.5	86.1	81.7	77.2	72.9	71.8
80°	132.3	118.6	104.8	91.0	77.3	69.1	66.4	63.7	61.0	58.3	57.2
82.5°	100.3	89.5	78.8	68.0	57.4	51.0	49.2	47.4	45.6	43.7	43.1
85°	52.2	46.5	40.9	35.2	29.5	26.3	25.5	24.7	23.8	23.1	23.1
87.5°	15.7	14.4	13.1	11.8	10.5	10.2	11.0	11.8	12.6	13.4	13.1
90°	0.8	2.9	5.1	7.2	9.3	12.4	16.3	20.2	24.2	28.0	27.7
92.5°	14.3	15.8	17.4	19.0	20.6	21.8	22.7	23.7	24.6	25.5	25.6
95°	41.7	43.5	45.3	47.1	48.9	49.9	50.3	50.6	51.0	51.3	51.3
97.5°	76.2	77.8	79.4	81.0	82.5	83.7	84.3	85.0	85.6	86.3	86.3
100°	101.9	103.3	104.7	106.2	107.6	108.6	109.1	109.6	110.2	110.7	110.7
102.5°	128.9	130.0	131.1	132.3	133.4	134.4	135.0	135.7	136.3	137.0	137.2
105°	172.5	173.0	173.6	174.1	174.7	175.1	175.5	175.8	176.2	176.5	176.9
107.5°	216.5	217.3	218.0	218.8	219.6	220.0	220.0	220.0	220.0	220.0	220.1
110°	244.7	245.8	246.8	248.0	249.0	249.5	249.5	249.5	249.5	249.5	249.5



TEST NUMBER: P331856-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.5	276.6	277.7	278.8	279.8	280.3	280.1	280.0	279.9	279.7	279.2
115°	320.9	322.0	323.1	324.2	325.2	325.6	325.2	324.9	324.5	324.2	324.0
117.5°	366.2	367.7	369.1	370.5	371.9	372.1	371.1	370.1	369.2	368.1	367.7
120°	396.4	397.8	399.3	400.7	402.1	402.1	400.7	399.3	397.8	396.4	396.4
122.5°	424.0	425.7	427.4	429.1	430.8	431.2	430.2	429.2	428.2	427.1	426.7
125°	467.0	468.6	470.2	471.8	473.4	474.0	473.4	472.9	472.3	471.8	471.3
127.5°	508.9	510.9	512.9	515.0	517.0	517.7	517.1	516.4	515.8	515.2	514.4
130°	535.2	537.5	539.8	542.2	544.5	545.4	545.1	544.7	544.4	544.0	543.7
132.5°	564.7	566.6	568.5	570.4	572.3	573.2	573.3	573.4	573.5	573.5	572.7
135°	604.2	606.2	608.1	610.1	612.0	613.1	613.5	613.9	614.3	614.6	614.4
137.5°	645.7	647.4	649.0	650.5	652.1	653.2	653.6	654.1	654.6	655.1	654.9
140°	670.7	672.4	674.0	675.6	677.2	678.4	679.4	680.2	681.1	682.0	682.0
142.5°	696.5	698.1	699.7	701.2	702.9	704.0	704.6	705.2	705.8	706.4	706.5
145°	733.3	734.6	735.9	737.1	738.4	739.5	740.6	741.6	742.8	743.8	743.9
147.5°	766.3	767.8	769.3	770.7	772.2	773.3	774.0	774.8	775.5	776.2	776.6
150°	788.7	789.8	790.8	791.9	793.0	793.9	794.6	795.4	796.1	796.8	797.3
152.5°	808.7	809.7	810.8	811.8	812.9	813.9	814.8	815.6	816.4	817.3	817.9
155°	838.4	839.0	839.6	840.1	840.6	841.1	841.7	842.2	842.7	843.3	844.1
157.5°	864.0	864.4	864.7	865.1	865.4	865.8	866.1	866.4	866.7	867.0	868.2
160°	879.4	879.7	880.1	880.4	880.8	881.1	881.3	881.5	881.6	881.8	882.9
162.5°	893.5	893.6	893.7	893.7	893.8	893.9	894.1	894.3	894.5	894.6	895.9
165°	912.3	912.1	912.0	911.7	911.6	911.5	911.5	911.5	911.5	911.5	912.8
167.5°	928.0	927.5	926.9	926.4	925.9	925.6	925.6	925.5	925.5	925.4	926.7
170°	936.4	935.8	935.3	934.8	934.2	933.9	933.7	933.5	933.3	933.2	934.4
172.5°	942.1	941.6	941.0	940.6	940.0	939.6	939.4	939.3	939.1	938.9	940.2
175°	949.2	948.6	948.2	947.6	947.1	946.6	946.3	945.9	945.5	945.2	946.4
177.5°	952.1	951.6	951.3	950.8	950.4	950.0	949.7	949.4	949.2	948.9	949.7
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331856-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1335.1	1337.3	1339.5	1340.3	1339.9	1339.5	1339.0	1338.6
5°	1324.5	1327.0	1329.4	1330.2	1329.4	1328.6	1327.8	1327.0
7.5°	1303.1	1303.8	1304.5	1304.2	1302.7	1301.3	1300.0	1298.5
10°	1281.6	1280.8	1280.0	1278.8	1277.2	1275.6	1273.9	1272.3
12.5°	1257.0	1255.5	1254.1	1252.0	1249.4	1246.7	1244.0	1241.3
15°	1211.1	1205.9	1200.8	1196.9	1194.2	1191.5	1188.8	1186.1
17.5°	1159.1	1153.0	1146.9	1141.5	1136.9	1132.3	1127.6	1123.0
20°	1122.8	1116.1	1109.4	1103.0	1097.1	1091.2	1085.2	1079.3
22.5°	1083.1	1074.4	1065.6	1059.1	1054.7	1050.3	1045.8	1041.4
25°	1017.1	1006.1	995.0	987.5	983.3	979.3	975.3	971.2
27.5°	954.2	941.3	928.4	918.7	912.3	905.9	899.4	893.0
30°	909.7	896.0	882.2	871.7	864.4	857.1	849.9	842.6
32.5°	865.1	849.4	833.6	822.4	815.6	808.7	801.8	795.0
35°	795.2	778.2	761.2	749.7	743.8	737.8	731.9	726.0
37.5°	727.1	708.4	689.7	676.9	670.2	663.4	656.6	649.7
40°	681.6	662.4	643.3	630.3	623.2	616.2	609.2	602.1
42.5°	635.6	615.8	596.0	582.7	575.9	569.1	562.4	555.6
45°	568.7	549.5	530.4	517.6	511.1	504.6	498.1	491.7
47.5°	503.6	484.6	465.5	453.0	447.2	441.3	435.4	429.5
50°	461.8	443.1	424.5	412.3	406.7	401.0	395.4	389.7
52.5°	422.2	404.3	386.3	374.7	369.5	364.2	359.0	353.8
55°	362.2	346.0	329.8	319.2	314.0	308.9	303.8	298.7
57.5°	307.6	292.7	277.9	268.3	264.0	259.7	255.4	251.0
60°	269.9	256.2	242.4	233.4	229.0	224.7	220.4	216.1
62.5°	237.3	224.1	211.0	203.1	200.6	198.0	195.4	192.8
65°	192.9	183.7	174.5	169.5	168.7	167.9	167.2	166.4
67.5°	155.7	151.5	147.3	144.7	143.9	143.1	142.2	141.3
70°	135.5	132.8	130.1	128.2	127.1	126.0	124.9	123.8
72.5°	117.9	115.6	113.3	111.9	111.2	110.6	109.9	109.2
75°	93.3	91.5	89.6	88.5	88.2	87.9	87.7	87.4
77.5°	70.7	69.6	68.5	67.7	67.3	66.9	66.5	66.1
80°	56.1	55.1	53.9	53.4	53.4	53.4	53.4	53.4
82.5°	42.4	41.7	41.1	40.8	40.8	40.8	40.8	40.8
85°	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1
87.5°	12.8	12.5	12.2	12.1	12.1	12.2	12.2	12.3
90°	27.3	27.0	26.6	26.5	26.8	26.9	27.1	27.3
92.5°	25.7	25.7	25.8	25.8	25.9	25.9	26.0	26.0
95°	51.3	51.3	51.3	51.2	50.8	50.5	50.1	49.7
97.5°	86.3	86.3	86.3	86.3	86.3	86.3	86.2	86.2
100°	110.7	110.7	110.7	110.7	110.4	110.3	110.1	110.0
102.5°	137.4	137.4	137.6	137.6	137.4	137.2	137.0	136.9
105°	177.2	177.6	177.9	178.2	178.2	178.2	178.2	178.2
107.5°	220.3	220.5	220.5	220.2	219.4	218.6	217.8	217.0
110°	249.5	249.5	249.5	249.3	248.7	248.2	247.6	247.2



TEST NUMBER: P331856-927

CATALOG NUMBER: S122RDIW-S1005D970U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	278.8	278.5	278.0	277.6	277.2	276.8	276.4	276.0
115°	323.8	323.6	323.4	323.1	322.6	322.0	321.5	320.9
117.5°	367.3	366.9	366.4	365.9	365.4	364.9	364.3	363.8
120°	396.4	396.4	396.4	396.1	395.5	395.1	394.5	394.0
122.5°	426.4	425.9	425.5	425.1	424.7	424.3	423.9	423.5
125°	470.7	470.2	469.7	469.3	469.1	469.0	468.7	468.6
127.5°	513.8	513.2	512.5	511.9	511.4	510.8	510.2	509.7
130°	543.3	543.0	542.6	542.0	541.3	540.6	539.9	539.2
132.5°	572.0	571.2	570.4	569.7	569.2	568.5	568.0	567.4
135°	614.3	614.1	613.9	613.5	613.0	612.4	612.0	611.4
137.5°	654.7	654.7	654.5	654.0	653.3	652.6	651.9	651.2
140°	682.0	682.0	682.0	681.7	681.0	680.2	679.5	678.8
142.5°	706.7	706.9	706.9	706.7	706.0	705.3	704.6	703.9
145°	744.2	744.3	744.5	744.3	743.5	742.8	742.1	741.4
147.5°	777.0	777.4	777.8	777.6	777.0	776.3	775.6	774.9
150°	797.8	798.4	798.9	798.9	798.4	797.8	797.3	796.8
152.5°	818.6	819.4	820.0	820.0	819.4	818.6	817.9	817.3
155°	845.1	846.0	846.8	847.0	846.5	846.0	845.4	844.9
157.5°	869.5	870.7	871.9	872.0	871.2	870.4	869.5	868.6
160°	883.9	885.0	886.1	886.3	885.6	884.9	884.2	883.4
162.5°	897.1	898.3	899.5	899.7	898.8	897.9	897.1	896.3
165°	914.0	915.2	916.5	916.6	915.8	914.9	914.0	913.1
167.5°	928.0	929.2	930.4	930.6	929.7	928.8	927.8	926.9
170°	935.6	936.9	938.2	938.3	937.2	936.1	935.0	934.0
172.5°	941.4	942.7	943.9	944.0	942.9	941.9	940.8	939.8
175°	947.7	949.0	950.1	950.3	949.2	948.2	947.1	946.0
177.5°	950.6	951.4	952.3	952.3	951.4	950.6	949.7	948.9
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8

(END OF REPORT)