

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331772-927

Luminaire Tested: **S122RDIW-S290D710U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331772-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D710U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2768.4 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331772-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331772-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	30
1	93	89	86	82	84	80	77	75	63	61	59	48	47	45	33	33	32	25
2	85	78	73	68	76	71	66	62	56	52	50	42	40	38	30	29	27	22
3	78	69	62	57	70	62	56	52	49	45	42	38	35	33	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	16
5	66	55	47	41	59	49	43	38	39	35	31	30	27	24	22	20	18	14
6	60	49	41	36	54	44	38	33	36	31	27	27	24	22	20	18	16	13
7	56	44	37	31	50	40	33	29	32	27	24	25	22	19	18	16	14	11
8	52	40	33	28	46	36	30	25	29	25	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	15	13	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6421	6421	6421
5°	6446	6340	6374
10°	6396	6237	6184
15°	6322	6051	5877
20°	6220	5787	5498
25°	6116	5489	5129
30°	5972	5179	4657
35°	5830	4845	4242
40°	5689	4498	3762
45°	5523	4108	3329
50°	5350	3715	2901
55°	5177	3291	2494
60°	4973	2848	2070
65°	4741	2392	1883
70°	4471	1969	1733
75°	4130	1797	1616
80°	3645	1609	1469
85°	2853	1260	1260



TEST NUMBER: P331772-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.2	1.3
10°-20°	102.2	3.7
20°-30°	143.5	5.2
30°-40°	156.5	5.7
40°-50°	143.9	5.2
50°-60°	113.0	4.1
60°-70°	73.7	2.7
70°-80°	38.0	1.4
80°-90°	12.6	0.5
90°-100°	44.1	1.6
100°-110°	137.1	5.0
110°-120°	234.3	8.5
120°-130°	308.1	11.1
130°-140°	345.9	12.5
140°-150°	339.1	12.3
150°-160°	284.5	10.3
160°-170°	188.7	6.8
170°-180°	65.9	2.4
0°-30°	282.9	10.2
0°-40°	439.4	15.9
0°-60°	696.4	25.2
0°-90°	820.7	29.6
90°-120°	415.5	15.0
90°-150°	1408.7	50.9
90°-180°	1948.0	70.4
0°-180°	2768.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	398	396	391	394	393	38
15°	378	374	362	355	352	106
25°	343	331	308	294	288	158
35°	296	277	246	224	215	185
45°	242	217	180	155	146	187
55°	184	155	117	96	89	164
65°	124	95	63	51	49	123
75°	66	42	29	26	26	70
85°	15	8	7	7	7	18
90°	1	8	21	20	20	2
95°	31	36	38	38	36	35
105°	126	128	129	130	130	133
115°	235	238	238	237	235	233
125°	342	347	346	344	343	306
135°	443	449	450	450	448	342
145°	537	541	545	545	543	336
155°	614	616	618	620	619	283
165°	668	668	668	672	669	188
175°	695	694	692	696	693	66
180°	697	697	697	697	697	



TEST NUMBER: P331772-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	399.1	398.8	398.5	398.2	397.8	397.3	396.6	395.9	395.2	394.5	395.1
5°	397.7	397.3	396.9	396.5	396.1	395.3	394.3	393.2	392.2	391.2	391.9
7.5°	393.6	393.1	392.5	392.1	391.6	390.7	389.5	388.2	387.1	385.9	386.0
10°	390.1	389.5	389.0	388.4	387.9	386.7	385.2	383.6	382.0	380.4	380.2
12.5°	385.8	385.1	384.4	383.7	383.0	381.7	379.6	377.6	375.5	373.4	373.0
15°	378.2	377.3	376.4	375.6	374.7	372.9	370.2	367.5	364.7	362.0	360.5
17.5°	368.9	367.6	366.2	364.9	363.5	361.2	357.7	354.2	350.7	347.2	345.4
20°	362.0	360.4	358.9	357.2	355.6	352.8	348.8	344.8	340.9	336.8	334.9
22.5°	354.6	352.8	350.9	349.2	347.4	344.2	339.7	335.2	330.7	326.2	323.6
25°	343.3	340.7	338.2	335.6	333.1	329.2	323.8	318.6	313.3	308.1	304.8
27.5°	329.8	327.0	324.2	321.5	318.6	314.3	308.3	302.4	296.4	290.5	286.7
30°	320.3	317.3	314.2	311.2	308.2	303.4	297.0	290.7	284.2	277.8	273.8
32.5°	311.1	307.5	304.0	300.4	296.8	291.8	285.3	278.8	272.3	265.7	261.1
35°	295.8	291.8	287.6	283.6	279.5	273.9	266.9	259.8	252.9	245.8	240.7
37.5°	280.6	276.1	271.6	267.1	262.6	256.7	249.1	241.6	234.2	226.6	221.1
40°	269.9	265.1	260.3	255.5	250.7	244.5	236.7	228.9	221.2	213.4	207.7
42.5°	259.0	253.9	248.8	243.8	238.8	232.2	224.2	216.2	208.2	200.2	194.3
45°	241.9	236.5	231.1	225.8	220.4	213.5	205.1	196.7	188.3	179.9	174.3
47.5°	225.1	219.4	213.8	208.1	202.4	195.3	186.6	177.9	169.2	160.6	155.0
50°	213.0	207.4	201.7	196.0	190.4	183.1	174.3	165.5	156.7	147.9	142.4
52.5°	201.2	195.3	189.4	183.5	177.5	170.2	161.6	153.0	144.4	135.8	130.5
55°	183.9	177.7	171.4	165.2	158.9	151.5	142.8	134.2	125.6	116.9	112.2
57.5°	166.1	159.7	153.3	146.9	140.5	133.2	124.8	116.6	108.3	100.0	95.5
60°	154.0	147.7	141.2	134.8	128.4	121.1	112.9	104.6	96.4	88.2	84.1
62.5°	142.2	135.9	129.4	123.0	116.6	109.5	101.6	93.8	86.0	78.1	74.2
65°	124.1	117.6	111.2	104.7	98.2	91.4	84.2	77.0	69.8	62.6	59.9
67.5°	106.7	100.3	93.9	87.5	81.0	74.5	68.0	61.6	55.1	48.6	47.4
70°	94.7	88.4	82.1	76.0	69.7	63.8	58.3	52.8	47.3	41.7	41.0
72.5°	83.1	77.2	71.1	65.2	59.2	54.0	49.6	45.2	40.7	36.3	35.6
75°	66.2	60.6	55.1	49.4	43.8	39.7	36.9	34.2	31.5	28.8	28.2
77.5°	49.6	44.7	39.8	34.9	29.9	26.9	25.5	24.2	22.9	21.6	21.3
80°	39.2	35.2	31.1	27.0	22.9	20.4	19.6	18.9	18.1	17.3	17.0
82.5°	29.7	26.5	23.4	20.2	17.0	15.1	14.6	14.0	13.5	13.0	12.8
85°	15.4	13.8	12.1	10.5	8.8	7.8	7.5	7.3	7.1	6.8	6.8
87.5°	4.8	4.5	4.4	4.1	4.0	4.1	4.7	5.3	5.9	6.4	6.3
90°	0.6	2.1	3.7	5.3	6.9	9.1	12.0	14.8	17.7	20.6	20.3
92.5°	10.5	11.6	12.8	13.9	15.1	16.0	16.6	17.3	18.0	18.7	18.8
95°	30.6	31.8	33.2	34.5	35.8	36.6	36.8	37.1	37.4	37.6	37.6
97.5°	55.8	57.0	58.1	59.3	60.4	61.2	61.8	62.3	62.7	63.2	63.2
100°	74.6	75.7	76.8	77.8	78.8	79.5	79.9	80.3	80.7	81.1	81.1
102.5°	94.4	95.2	96.1	96.9	97.8	98.4	98.9	99.4	99.9	100.4	100.5
105°	126.4	126.7	127.1	127.5	127.9	128.3	128.6	128.8	129.0	129.4	129.6
107.5°	158.6	159.1	159.8	160.3	160.9	161.2	161.2	161.2	161.2	161.2	161.3
110°	179.3	180.1	180.9	181.6	182.4	182.8	182.8	182.8	182.8	182.8	182.8



TEST NUMBER: P331772-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	201.8	202.6	203.4	204.2	205.0	205.3	205.3	205.1	205.0	204.9	204.6
115°	235.1	235.9	236.7	237.5	238.3	238.5	238.3	238.0	237.7	237.5	237.3
117.5°	268.3	269.3	270.4	271.4	272.4	272.6	271.9	271.2	270.5	269.7	269.4
120°	290.4	291.4	292.5	293.5	294.5	294.5	293.5	292.5	291.4	290.4	290.4
122.5°	310.6	311.9	313.1	314.3	315.6	315.9	315.1	314.4	313.7	313.0	312.7
125°	342.1	343.3	344.4	345.6	346.8	347.2	346.8	346.4	346.0	345.6	345.2
127.5°	372.8	374.3	375.8	377.2	378.7	379.3	378.8	378.3	377.9	377.4	376.9
130°	392.1	393.8	395.5	397.2	398.9	399.6	399.3	399.1	398.8	398.5	398.3
132.5°	413.8	415.1	416.5	417.9	419.2	420.0	420.0	420.1	420.2	420.2	419.6
135°	442.7	444.1	445.5	446.9	448.4	449.2	449.5	449.8	450.0	450.3	450.1
137.5°	473.1	474.3	475.5	476.7	477.8	478.6	478.9	479.3	479.6	479.9	479.8
140°	491.5	492.6	493.8	495.0	496.1	497.0	497.7	498.4	499.0	499.6	499.6
142.5°	510.2	511.4	512.6	513.8	514.9	515.8	516.2	516.7	517.1	517.5	517.6
145°	537.3	538.2	539.1	540.0	541.0	541.8	542.6	543.4	544.2	544.9	545.0
147.5°	561.4	562.4	563.6	564.7	565.8	566.6	567.1	567.6	568.2	568.7	568.9
150°	577.8	578.6	579.4	580.2	581.0	581.6	582.2	582.7	583.2	583.8	584.2
152.5°	592.4	593.2	594.0	594.8	595.6	596.3	596.9	597.5	598.2	598.8	599.3
155°	614.3	614.7	615.1	615.4	615.8	616.2	616.6	617.0	617.4	617.8	618.5
157.5°	633.0	633.3	633.5	633.7	634.1	634.3	634.5	634.8	635.0	635.3	636.1
160°	644.3	644.5	644.8	645.1	645.3	645.5	645.6	645.8	645.9	646.0	646.8
162.5°	654.6	654.7	654.7	654.7	654.8	654.9	655.1	655.2	655.3	655.5	656.3
165°	668.4	668.2	668.1	668.0	667.9	667.8	667.8	667.8	667.8	667.8	668.7
167.5°	679.9	679.5	679.1	678.7	678.3	678.1	678.1	678.0	678.0	678.0	678.9
170°	686.0	685.6	685.2	684.8	684.4	684.2	684.0	683.9	683.8	683.7	684.6
172.5°	690.2	689.8	689.4	689.0	688.6	688.4	688.2	688.2	688.0	687.9	688.8
175°	695.4	695.1	694.7	694.3	693.9	693.6	693.2	693.0	692.8	692.4	693.4
177.5°	697.5	697.2	696.9	696.6	696.2	696.0	695.8	695.6	695.4	695.1	695.8
180°	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6



TEST NUMBER: P331772-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	397.7	397.7	397.7	397.7	397.7	397.7	397.7	397.7
2.5°	395.8	396.4	397.0	397.3	397.2	397.0	396.9	396.8
5°	392.6	393.3	394.0	394.3	394.0	393.8	393.6	393.3
7.5°	386.3	386.5	386.7	386.6	386.2	385.7	385.3	384.9
10°	379.9	379.7	379.5	379.1	378.6	378.1	377.6	377.2
12.5°	372.6	372.2	371.8	371.1	370.3	369.6	368.8	368.0
15°	359.0	357.4	355.9	354.8	354.0	353.2	352.4	351.6
17.5°	343.6	341.7	340.0	338.4	337.0	335.6	334.2	332.9
20°	332.9	330.8	328.8	326.9	325.2	323.4	321.7	320.0
22.5°	321.1	318.5	315.9	313.9	312.6	311.3	310.0	308.7
25°	301.5	298.2	294.9	292.7	291.5	290.3	289.1	287.9
27.5°	282.8	279.0	275.2	272.4	270.5	268.5	266.6	264.7
30°	269.7	265.6	261.5	258.4	256.2	254.1	251.9	249.8
32.5°	256.4	251.8	247.1	243.8	241.8	239.7	237.7	235.7
35°	235.8	230.7	225.6	222.2	220.5	218.7	217.0	215.2
37.5°	215.6	210.0	204.5	200.7	198.7	196.6	194.6	192.6
40°	202.1	196.4	190.7	186.8	184.7	182.7	180.5	178.5
42.5°	188.4	182.5	176.7	172.8	170.7	168.7	166.7	164.7
45°	168.6	162.9	157.2	153.4	151.5	149.6	147.7	145.8
47.5°	149.2	143.6	138.0	134.3	132.5	130.8	129.0	127.3
50°	136.9	131.3	125.8	122.2	120.6	118.9	117.2	115.5
52.5°	125.2	119.9	114.5	111.1	109.6	108.0	106.4	104.9
55°	107.3	102.6	97.8	94.6	93.1	91.6	90.1	88.6
57.5°	91.2	86.7	82.4	79.5	78.3	77.0	75.7	74.4
60°	80.0	76.0	71.9	69.2	67.9	66.6	65.4	64.1
62.5°	70.3	66.5	62.6	60.2	59.4	58.7	57.9	57.1
65°	57.2	54.4	51.7	50.2	50.0	49.7	49.5	49.3
67.5°	46.2	44.9	43.6	42.9	42.6	42.4	42.1	41.9
70°	40.2	39.4	38.6	38.0	37.6	37.3	37.0	36.7
72.5°	34.9	34.2	33.6	33.2	33.0	32.8	32.6	32.4
75°	27.6	27.1	26.5	26.2	26.1	26.1	26.0	25.9
77.5°	20.9	20.6	20.3	20.1	20.0	19.8	19.7	19.6
80°	16.6	16.3	16.0	15.8	15.8	15.8	15.8	15.8
82.5°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
87.5°	6.2	6.1	5.9	5.9	5.9	5.9	6.0	6.0
90°	20.0	19.8	19.6	19.5	19.6	19.7	19.9	20.0
92.5°	18.8	18.9	18.9	18.9	18.9	19.0	19.0	19.0
95°	37.6	37.6	37.6	37.5	37.2	37.0	36.7	36.4
97.5°	63.2	63.2	63.2	63.2	63.2	63.2	63.1	63.1
100°	81.1	81.1	81.1	81.0	81.0	80.8	80.6	80.6
102.5°	100.6	100.7	100.8	100.8	100.7	100.5	100.4	100.3
105°	129.8	130.1	130.4	130.5	130.5	130.5	130.5	130.5
107.5°	161.4	161.5	161.6	161.4	160.7	160.2	159.5	159.0
110°	182.8	182.8	182.8	182.6	182.2	181.8	181.4	181.1



TEST NUMBER: P331772-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	204.3	204.0	203.7	203.4	203.1	202.8	202.5	202.2
115°	237.3	237.1	236.9	236.7	236.3	235.9	235.5	235.1
117.5°	269.1	268.8	268.5	268.1	267.7	267.3	266.9	266.5
120°	290.4	290.4	290.4	290.2	289.8	289.4	289.0	288.6
122.5°	312.4	312.0	311.7	311.4	311.1	310.9	310.5	310.3
125°	344.8	344.4	344.0	343.8	343.7	343.6	343.4	343.3
127.5°	376.4	376.0	375.5	375.1	374.6	374.2	373.8	373.4
130°	398.1	397.8	397.5	397.1	396.6	396.1	395.5	395.1
132.5°	419.1	418.4	417.9	417.4	417.0	416.5	416.1	415.7
135°	450.0	449.9	449.8	449.5	449.1	448.7	448.3	447.9
137.5°	479.7	479.6	479.5	479.2	478.6	478.2	477.6	477.1
140°	499.6	499.6	499.6	499.4	498.9	498.4	497.8	497.3
142.5°	517.8	517.8	517.9	517.8	517.2	516.7	516.2	515.6
145°	545.2	545.3	545.4	545.3	544.7	544.2	543.7	543.2
147.5°	569.3	569.5	569.8	569.7	569.3	568.7	568.2	567.8
150°	584.5	584.9	585.3	585.3	584.9	584.5	584.2	583.8
152.5°	599.8	600.2	600.8	600.8	600.2	599.8	599.3	598.8
155°	619.1	619.8	620.4	620.6	620.2	619.8	619.4	619.0
157.5°	637.0	637.9	638.7	638.9	638.3	637.6	637.0	636.4
160°	647.6	648.4	649.2	649.3	648.8	648.2	647.8	647.2
162.5°	657.2	658.1	659.0	659.1	658.5	657.9	657.3	656.6
165°	669.6	670.5	671.5	671.6	670.9	670.3	669.6	669.0
167.5°	679.9	680.7	681.7	681.8	681.1	680.4	679.8	679.1
170°	685.5	686.4	687.3	687.4	686.6	685.8	685.0	684.2
172.5°	689.8	690.6	691.6	691.6	690.9	690.1	689.3	688.5
175°	694.3	695.2	696.2	696.2	695.4	694.7	693.9	693.1
177.5°	696.4	697.0	697.7	697.7	697.0	696.4	695.8	695.1
180°	696.6	696.6	696.6	696.6	696.6	696.6	696.6	696.6

(END OF REPORT)