

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331798-927

Luminaire Tested: **S122RDIW-S485D1240U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331798-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D1240U927-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4879.8 lumens  
Efficiency: N/A  
Efficacy: 90.7 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30				
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	34	33	26				
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	29	28	23				
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25	20				
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22	18				
5	66	55	48	42	59	50	44	39	40	36	32	31	28	26	23	21	19	16				
6	61	50	42	37	55	45	39	34	37	32	28	28	25	23	21	19	17	14				
7	57	45	38	32	51	41	34	30	33	29	25	26	23	20	19	17	16	13				
8	53	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14	12				
9	49	37	30	26	44	34	28	24	28	23	20	22	19	16	17	14	13	11				
10	46	34	27	23	41	31	25	21	26	21	18	20	17	15	15	13	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13747	13747	13747	13747
5°	15352	13833	12266	13833
10°	17033	13736	10632	13736
15°	17870	13534	8376	13534
20°	15493	13235	7247	13235
25°	10162	12827	6472	12827
30°	6840	12333	5858	12333
35°	5541	11710	5282	11710
40°	4926	11030	4890	11030
45°	4459	10234	4364	10234
50°	4057	9445	4042	9445
55°	3814	8569	3764	8569
60°	3190	7766	3152	7766
65°	2690	7053	3053	7053
70°	2488	6297	2875	6297
75°	2327	5483	2658	5483
80°	2148	4510	2362	4510
85°	1964	3575	2075	3575



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.7	1.7
10°-20°	224.9	4.6
20°-30°	289.8	5.9
30°-40°	275.4	5.6
40°-50°	235.9	4.8
50°-60°	179.7	3.7
60°-70°	113.6	2.3
70°-80°	56.7	1.2
80°-90°	19.6	0.4
90°-100°	77.1	1.6
100°-110°	239.6	4.9
110°-120°	409.5	8.4
120°-130°	538.5	11.0
130°-140°	604.4	12.4
140°-150°	592.6	12.1
150°-160°	497.0	10.2
160°-170°	329.7	6.8
170°-180°	115.2	2.4
0°-30°	595.4	12.2
0°-40°	870.8	17.8
0°-60°	1286.4	26.4
0°-90°	1476.3	30.3
90°-120°	726.2	14.9
90°-150°	2461.6	50.4
90°-180°	3404.0	69.8
0°-180°	4879.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	851	851	851	851	851	
5°	947	854	757	854	947	93
15°	1069	810	501	810	1069	288
25°	570	720	363	720	570	271
35°	281	594	268	594	281	180
45°	195	448	191	448	195	151
55°	136	304	134	304	136	119
65°	70	185	80	185	70	72
75°	37	88	43	88	37	40
85°	11	19	11	19	11	12
90°	35	1	35	1	35	16
95°	64	53	64	53	64	71
105°	228	221	228	221	228	240
115°	411	411	411	411	411	406
125°	600	598	600	598	600	535
135°	783	774	783	774	783	602
145°	949	939	949	939	949	593
155°	1082	1073	1082	1073	1082	498
165°	1169	1168	1169	1168	1169	330
175°	1211	1215	1211	1215	1211	115
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	886.0	886.7	887.4	885.7	885.7	884.3	881.2	878.8	872.2	871.2	871.2
5°	947.2	946.7	947.8	944.0	938.7	937.5	931.8	924.5	916.8	908.2	906.4
7.5°	1008.2	1007.3	1005.0	1004.2	1000.2	991.3	982.2	972.6	959.8	947.3	941.0
10°	1038.9	1048.7	1042.8	1032.5	1034.5	1020.6	1013.2	1000.5	989.8	971.2	967.1
12.5°	1069.2	1073.1	1071.2	1065.3	1062.7	1053.0	1043.1	1032.0	1012.3	995.6	981.0
15°	1069.1	1074.8	1076.3	1074.4	1075.9	1075.3	1070.0	1060.8	1043.7	1025.3	1009.4
17.5°	990.2	994.1	1003.8	1010.3	1018.7	1036.2	1044.8	1048.2	1045.6	1035.1	1023.9
20°	901.7	895.2	922.4	936.3	948.2	977.7	1003.1	1012.9	1028.6	1028.3	1025.3
22.5°	776.3	777.8	803.6	820.1	854.7	884.2	913.2	950.0	980.3	1000.4	1012.1
25°	570.4	581.6	607.4	629.8	668.3	723.3	773.3	831.3	886.0	929.2	970.3
27.5°	428.3	429.2	449.6	470.4	493.2	538.3	601.3	670.5	748.5	812.9	886.9
30°	366.9	365.0	373.7	386.3	405.9	440.8	488.1	556.2	634.0	731.0	817.4
32.5°	323.3	323.4	329.9	339.3	355.5	379.0	411.5	466.7	540.3	635.6	736.9
35°	281.1	280.7	285.5	292.3	299.0	314.2	336.4	365.4	416.0	505.0	608.6
37.5°	250.7	252.1	254.4	258.6	266.1	274.5	287.9	307.3	343.3	396.0	483.0
40°	233.7	234.3	237.6	241.1	245.6	252.1	263.0	278.7	305.0	347.0	410.6
42.5°	218.1	218.6	221.0	224.3	227.8	234.3	243.4	256.9	278.3	311.0	363.5
45°	195.3	195.3	197.3	198.8	202.6	208.6	215.9	227.2	242.0	266.3	301.2
47.5°	173.8	173.9	175.2	177.8	180.2	184.8	192.1	201.3	212.1	230.8	260.6
50°	161.5	161.8	162.7	164.8	166.3	170.4	176.0	184.0	195.3	209.8	234.6
52.5°	151.5	151.4	152.5	153.4	154.4	157.4	161.6	168.7	178.7	191.3	211.9
55°	135.5	134.3	136.1	137.5	138.5	139.7	142.0	146.5	155.0	165.6	181.0
57.5°	115.3	114.9	116.1	117.5	120.3	123.5	125.5	128.3	132.8	140.4	155.7
60°	98.8	98.8	101.5	102.3	105.6	109.7	113.9	116.3	120.7	125.7	137.0
62.5°	84.1	84.4	85.6	86.5	88.3	93.4	99.3	104.4	108.6	113.4	120.9
65°	70.4	71.0	71.0	71.6	72.8	74.0	76.3	80.5	87.9	94.7	100.3
67.5°	59.7	60.0	60.1	60.7	61.0	62.3	63.2	65.1	66.8	73.3	80.2
70°	52.7	53.6	53.2	53.9	54.1	54.7	55.9	56.8	59.5	60.9	65.1
72.5°	46.0	46.7	46.7	47.0	47.8	47.8	48.8	49.7	51.4	52.7	54.9
75°	37.3	37.0	37.3	37.9	38.2	38.4	38.4	39.6	40.6	41.7	43.2
77.5°	28.8	29.1	29.0	29.1	29.1	29.6	29.5	30.1	31.0	31.6	32.3
80°	23.1	23.4	23.1	23.4	23.7	23.9	23.7	23.9	24.9	25.4	25.4
82.5°	17.9	17.9	18.1	18.1	18.2	18.3	18.7	18.8	19.4	19.3	19.5
85°	10.6	10.4	10.4	10.4	10.6	10.9	10.6	10.6	10.9	10.9	10.9
87.5°	10.8	10.9	10.9	10.9	10.9	10.9	10.9	11.2	11.1	11.5	10.2
90°	34.9	34.7	34.5	34.2	34.0	34.1	34.6	35.0	35.5	36.0	30.9
92.5°	33.3	33.3	33.2	33.1	33.1	33.0	33.0	32.9	32.7	32.6	31.4
95°	63.7	64.2	64.6	65.0	65.5	65.8	65.8	65.8	65.8	65.8	65.3
97.5°	110.4	110.4	110.4	110.4	110.5	110.5	110.5	110.5	110.5	110.5	109.6
100°	140.7	140.9	141.2	141.4	141.6	141.7	141.7	141.7	141.7	141.7	141.1
102.5°	175.2	175.5	175.7	175.9	176.2	176.2	176.0	175.8	175.6	175.5	174.6
105°	228.1	228.1	228.1	228.1	228.1	227.8	227.4	226.9	226.4	226.0	225.5
107.5°	277.7	278.8	279.9	280.9	281.9	282.4	282.2	282.0	281.9	281.6	281.6
110°	316.4	317.0	317.7	318.5	319.1	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.3	353.9	354.3	354.8	355.4	355.8	356.4	357.0	357.5	358.1	358.2
115°	410.9	411.5	412.3	413.0	413.6	414.1	414.3	414.5	414.8	414.9	415.4
117.5°	465.7	466.4	467.1	467.8	468.5	469.1	469.6	470.2	470.7	471.3	472.5
120°	504.4	505.0	505.7	506.4	507.1	507.4	507.4	507.4	507.4	507.4	509.2
122.5°	542.2	542.6	543.1	543.7	544.2	544.7	545.3	545.8	546.3	546.8	548.1
125°	599.8	600.1	600.3	600.6	600.8	601.3	601.9	602.6	603.3	604.0	604.7
127.5°	652.4	653.2	653.9	654.7	655.4	656.2	657.0	657.8	658.6	659.4	660.3
130°	690.2	691.2	692.1	693.0	694.0	694.6	695.1	695.5	695.9	696.4	696.9
132.5°	726.4	727.1	727.9	728.6	729.4	730.2	731.2	732.2	733.2	734.2	734.1
135°	782.7	783.4	784.1	784.7	785.4	785.9	786.2	786.4	786.6	786.8	786.4
137.5°	833.7	834.6	835.5	836.4	837.3	837.9	838.0	838.2	838.4	838.6	838.0
140°	869.0	869.9	870.8	871.7	872.7	873.1	873.1	873.1	873.1	873.1	872.0
142.5°	901.0	902.0	902.9	903.8	904.7	905.1	904.9	904.7	904.5	904.4	903.6
145°	949.1	950.1	950.9	951.9	952.8	953.1	952.9	952.7	952.4	952.2	950.9
147.5°	992.0	992.9	993.8	994.7	995.5	995.7	995.2	994.7	994.2	993.7	992.8
150°	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0	1019.1
152.5°	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3	1045.2
155°	1081.6	1082.3	1083.0	1083.7	1084.3	1084.1	1083.0	1081.9	1080.7	1079.6	1078.9
157.5°	1112.0	1113.1	1114.2	1115.3	1116.4	1116.2	1114.6	1113.1	1111.5	1110.0	1109.5
160°	1130.9	1131.9	1132.7	1133.7	1134.6	1134.3	1133.0	1131.6	1130.2	1128.9	1128.6
162.5°	1147.4	1148.4	1149.5	1150.6	1151.8	1151.5	1149.9	1148.4	1146.8	1145.3	1145.1
165°	1168.9	1170.1	1171.2	1172.4	1173.5	1173.3	1171.6	1170.1	1168.5	1166.9	1166.9
167.5°	1186.6	1187.8	1189.0	1190.2	1191.4	1191.1	1189.5	1188.0	1186.4	1184.7	1184.8
170°	1195.6	1197.0	1198.4	1199.8	1201.1	1201.0	1199.4	1197.8	1196.2	1194.6	1194.8
172.5°	1203.0	1204.4	1205.8	1207.1	1208.5	1208.4	1206.8	1205.2	1203.6	1202.0	1202.2
175°	1211.0	1212.4	1213.8	1215.1	1216.6	1216.4	1214.8	1213.2	1211.6	1210.0	1210.5
177.5°	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7	1215.1
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	871.7	869.9	868.2	864.0	861.8	857.1	856.3	856.1	850.0	844.1	842.4
5°	901.7	897.0	889.9	881.5	873.0	864.1	858.2	853.5	841.6	830.4	823.9
7.5°	931.8	921.7	909.4	893.7	880.7	866.0	855.2	845.3	828.5	812.5	801.6
10°	954.3	937.8	921.5	899.9	883.0	866.5	851.1	837.8	818.9	797.6	782.4
12.5°	968.3	950.1	927.6	906.6	884.7	863.6	843.0	825.9	803.7	781.7	763.7
15°	987.2	967.7	940.5	910.3	882.2	854.7	831.0	809.7	780.7	754.4	732.5
17.5°	1002.7	975.7	946.5	911.6	879.1	844.1	813.7	786.4	754.2	722.4	696.6
20°	1007.6	981.0	947.2	912.4	873.9	832.7	799.9	770.3	735.7	701.1	671.5
22.5°	1004.5	983.8	946.3	904.5	865.1	822.1	785.1	750.7	712.3	677.0	642.7
25°	983.7	976.5	941.0	895.5	850.5	800.5	757.6	720.0	676.3	638.4	601.1
27.5°	934.9	950.3	928.3	879.7	829.7	776.1	727.9	685.2	639.7	597.1	559.9
30°	888.1	923.3	913.8	868.9	812.9	760.3	706.2	661.5	613.0	569.2	532.5
32.5°	823.9	882.1	891.4	853.7	795.9	738.0	681.3	636.8	586.2	540.0	504.3
35°	721.8	808.8	848.7	824.7	766.8	704.4	645.8	594.1	543.1	497.6	462.1
37.5°	600.0	718.4	785.1	786.7	733.5	668.6	604.8	553.4	501.3	456.6	418.2
40°	520.9	649.4	736.0	755.3	710.3	640.2	575.7	523.3	472.5	428.6	384.6
42.5°	450.0	577.9	684.4	717.9	682.1	612.5	547.8	493.1	443.5	402.1	357.1
45°	363.8	475.7	593.1	652.9	633.1	568.5	500.3	448.2	401.7	365.9	322.7
47.5°	307.0	385.8	499.4	580.3	579.9	521.0	453.8	403.9	360.8	327.3	292.3
50°	274.5	343.2	439.3	531.0	538.7	489.3	425.4	376.0	335.8	300.6	272.4
52.5°	245.4	302.0	388.4	476.3	498.2	455.4	393.5	347.8	308.8	276.4	252.3
55°	207.4	251.1	316.9	399.1	432.2	402.0	347.0	304.4	272.7	245.6	224.8
57.5°	175.4	208.3	260.9	327.2	365.8	346.7	301.4	266.8	239.7	215.1	198.8
60°	155.3	182.2	226.9	282.3	324.8	311.5	272.7	240.5	217.5	196.1	180.8
62.5°	136.4	159.5	197.8	242.7	281.8	276.2	244.6	217.5	197.3	177.9	164.9
65°	109.7	126.6	156.5	191.7	223.1	225.7	203.0	184.6	166.5	151.1	139.7
67.5°	87.4	98.4	119.5	149.1	172.6	181.0	167.1	153.0	138.7	126.8	116.8
70°	73.7	82.5	97.9	121.9	143.5	152.3	144.3	133.4	121.0	111.2	102.7
72.5°	59.7	68.4	79.7	97.3	115.8	125.4	122.6	114.7	104.6	96.6	88.5
75°	45.0	47.6	55.3	67.2	81.7	89.9	92.0	87.9	79.9	73.7	68.9
77.5°	33.3	34.9	38.5	44.8	54.2	61.6	64.6	64.2	58.6	55.1	50.6
80°	26.6	27.5	29.3	31.9	39.1	46.4	48.5	48.5	44.7	43.2	38.7
82.5°	20.2	20.9	21.9	23.4	26.8	33.2	35.5	36.0	33.5	31.6	28.1
85°	11.6	11.2	11.8	12.8	13.3	15.1	18.6	19.3	18.6	16.2	15.4
87.5°	9.2	8.5	7.4	6.4	6.1	5.8	6.4	7.1	6.7	6.5	6.6
90°	25.9	20.9	15.8	12.0	9.3	6.5	3.8	1.0	3.8	6.5	9.3
92.5°	30.3	29.1	27.9	26.3	24.3	22.3	20.3	18.3	20.3	22.3	24.3
95°	64.8	64.4	63.9	62.6	60.3	58.0	55.7	53.4	55.7	58.0	60.3
97.5°	108.8	107.9	107.0	105.6	103.6	101.6	99.6	97.6	99.6	101.6	103.6
100°	140.4	139.7	139.0	137.8	135.9	134.1	132.3	130.5	132.3	134.1	135.9
102.5°	173.7	172.9	172.0	170.8	169.4	167.9	166.4	164.9	166.4	167.9	169.4
105°	225.1	224.6	224.2	223.6	222.9	222.2	221.5	220.9	221.5	222.2	222.9
107.5°	281.6	281.6	281.6	281.1	280.1	279.2	278.1	277.1	278.1	279.2	280.1
110°	319.5	319.5	319.5	318.8	317.4	316.0	314.7	313.3	314.7	316.0	317.4





TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	358.5	358.6	358.8	358.2	356.9	355.5	354.1	352.8	354.1	355.5	356.9
115°	415.9	416.4	416.8	416.4	414.9	413.6	412.3	410.9	412.3	413.6	414.9
117.5°	473.8	475.1	476.4	476.1	474.3	472.5	470.6	468.8	470.6	472.5	474.3
120°	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	509.2	511.1	512.9
122.5°	549.5	550.7	552.0	551.5	549.3	547.2	544.9	542.7	544.9	547.2	549.3
125°	605.4	606.0	606.7	606.0	604.0	601.9	599.8	597.8	599.8	601.9	604.0
127.5°	661.1	661.9	662.7	661.9	659.3	656.6	654.0	651.4	654.0	656.6	659.3
130°	697.4	697.8	698.2	697.0	694.0	691.1	688.1	685.2	688.1	691.1	694.0
132.5°	734.0	734.0	733.9	732.6	730.2	727.8	725.3	722.9	725.3	727.8	730.2
135°	785.9	785.4	785.0	783.5	781.0	778.5	775.9	773.5	775.9	778.5	781.0
137.5°	837.4	836.8	836.2	834.9	832.8	830.8	828.7	826.6	828.7	830.8	832.8
140°	870.8	869.7	868.5	867.0	864.9	862.8	860.8	858.7	860.8	862.8	864.9
142.5°	902.8	902.0	901.2	899.8	897.8	895.7	893.7	891.6	893.7	895.7	897.8
145°	949.4	948.1	946.7	945.2	943.6	942.1	940.5	938.8	940.5	942.1	943.6
147.5°	991.9	990.9	990.1	988.6	986.7	984.8	982.9	981.0	982.9	984.8	986.7
150°	1018.2	1017.2	1016.4	1015.2	1013.8	1012.5	1011.1	1009.7	1011.1	1012.5	1013.8
152.5°	1044.1	1043.0	1041.9	1040.7	1039.3	1037.9	1036.6	1035.2	1036.6	1037.9	1039.3
155°	1078.2	1077.5	1076.8	1076.2	1075.5	1074.8	1074.1	1073.4	1074.1	1074.8	1075.5
157.5°	1109.1	1108.7	1108.3	1107.9	1107.5	1107.0	1106.5	1106.0	1106.5	1107.0	1107.5
160°	1128.4	1128.1	1128.0	1127.6	1127.2	1126.7	1126.2	1125.8	1126.2	1126.7	1127.2
162.5°	1144.9	1144.6	1144.4	1144.2	1144.1	1144.1	1144.0	1143.8	1144.0	1144.1	1144.1
165°	1166.9	1166.9	1166.9	1167.0	1167.2	1167.4	1167.7	1167.9	1167.7	1167.4	1167.2
167.5°	1184.9	1184.9	1184.9	1185.3	1186.0	1186.7	1187.3	1188.0	1187.3	1186.7	1186.0
170°	1195.1	1195.3	1195.6	1196.0	1196.7	1197.4	1198.0	1198.7	1198.0	1197.4	1196.7
172.5°	1202.5	1202.7	1202.9	1203.4	1204.0	1204.8	1205.5	1206.1	1205.5	1204.8	1204.0
175°	1210.9	1211.4	1211.9	1212.4	1213.1	1213.8	1214.5	1215.1	1214.5	1213.8	1213.1
177.5°	1215.4	1215.8	1216.2	1216.6	1217.2	1217.7	1218.3	1218.9	1218.3	1217.7	1217.2
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	839.3	837.7	834.6	829.9	827.0	822.0	818.7	820.6	821.1	820.6	820.1
5°	816.8	810.6	802.0	793.7	786.0	777.8	773.0	771.0	766.8	764.5	763.3
7.5°	789.5	778.8	766.7	752.3	740.0	727.1	720.6	717.3	708.8	704.3	700.2
10°	769.1	752.3	740.1	721.2	709.7	692.8	681.3	681.6	670.0	663.5	658.8
12.5°	746.7	728.2	708.0	690.9	674.9	661.4	647.5	641.8	629.5	623.3	610.5
15°	709.4	687.8	666.5	643.4	627.2	606.2	586.1	561.5	541.7	524.5	519.8
17.5°	668.7	642.0	620.6	593.5	565.6	530.3	507.0	492.7	480.8	471.7	465.0
20°	640.8	613.5	590.8	549.9	512.4	488.4	471.3	460.3	447.9	438.2	432.8
22.5°	611.4	583.0	552.0	506.4	477.1	457.9	442.6	430.0	421.6	414.0	409.2
25°	569.7	538.7	487.5	456.1	432.5	412.4	401.7	394.0	385.2	374.8	370.1
27.5°	525.8	476.3	439.6	416.3	393.7	380.6	371.1	359.6	351.6	347.0	342.1
30°	492.8	443.5	414.8	389.3	373.4	358.9	347.6	341.1	333.4	325.4	322.2
32.5°	456.1	416.7	389.2	368.0	351.8	339.5	330.6	320.0	314.5	309.6	302.8
35°	410.6	380.7	355.6	338.4	323.1	313.0	302.6	296.4	286.4	282.3	279.6
37.5°	372.0	346.1	327.3	309.3	297.1	286.0	279.6	269.7	265.4	259.6	254.0
40°	350.2	324.8	306.8	292.0	278.4	270.1	262.1	254.1	247.6	244.9	238.1
42.5°	328.0	307.3	289.2	273.1	264.0	255.2	245.1	239.2	232.4	228.1	223.9
45°	297.3	279.0	263.6	250.3	240.2	231.1	224.5	214.8	211.0	202.3	198.8
47.5°	270.3	253.3	238.6	225.9	216.1	210.2	200.7	193.0	186.9	181.6	177.1
50°	251.1	236.9	222.8	211.5	202.6	194.1	184.3	180.5	171.0	168.3	165.6
52.5°	233.6	220.1	207.2	196.1	187.3	179.0	170.3	165.3	158.9	156.2	154.3
55°	209.1	196.1	183.7	174.0	165.1	156.5	151.1	145.0	142.0	139.9	137.5
57.5°	184.5	172.9	163.3	153.4	144.5	137.7	131.5	127.8	124.7	122.0	119.1
60°	168.9	157.6	149.1	139.9	130.8	125.2	120.4	116.0	112.4	108.3	107.1
62.5°	152.3	142.5	134.7	125.7	117.7	112.6	108.1	103.9	99.7	93.6	92.0
65°	129.6	121.9	113.6	106.2	99.1	94.1	87.5	82.9	81.0	80.5	80.2
67.5°	109.0	101.7	94.6	87.1	80.6	75.9	72.6	71.9	70.7	70.3	69.5
70°	95.2	88.5	81.4	74.2	68.0	67.2	66.0	64.8	63.3	62.7	62.1
72.5°	82.9	75.9	68.8	63.1	60.4	59.3	58.1	57.0	56.0	55.4	55.1
75°	63.6	57.1	52.4	50.3	48.8	47.9	46.2	45.2	44.7	43.8	43.5
77.5°	45.8	42.1	39.9	38.7	37.1	36.1	35.2	34.2	33.6	33.4	33.0
80°	34.9	33.1	31.7	29.9	29.3	28.1	27.8	26.9	27.3	26.3	26.3
82.5°	27.1	24.9	23.6	22.8	22.2	21.2	20.9	20.5	20.6	20.0	20.0
85°	13.9	13.3	12.8	12.1	12.1	11.2	11.6	11.2	11.2	10.6	10.4
87.5°	6.9	7.4	8.0	9.0	10.0	10.8	10.6	10.3	10.2	10.1	9.9
90°	12.0	15.8	20.9	25.9	30.9	36.0	35.5	35.0	34.6	34.1	34.0
92.5°	26.3	27.9	29.1	30.3	31.4	32.6	32.7	32.9	33.0	33.0	33.1
95°	62.6	63.9	64.4	64.8	65.3	65.8	65.8	65.8	65.8	65.8	65.5
97.5°	105.6	107.0	107.9	108.8	109.6	110.5	110.5	110.5	110.5	110.5	110.5
100°	137.8	139.0	139.7	140.4	141.1	141.7	141.7	141.7	141.7	141.7	141.6
102.5°	170.8	172.0	172.9	173.7	174.6	175.5	175.6	175.8	176.0	176.2	176.2
105°	223.6	224.2	224.6	225.1	225.5	226.0	226.4	226.9	227.4	227.8	228.1
107.5°	281.1	281.6	281.6	281.6	281.6	281.6	281.9	282.0	282.2	282.4	281.9
110°	318.8	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.1



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	358.2	358.8	358.6	358.5	358.2	358.1	357.5	357.0	356.4	355.8	355.4
115°	416.4	416.8	416.4	415.9	415.4	414.9	414.8	414.5	414.3	414.1	413.6
117.5°	476.1	476.4	475.1	473.8	472.5	471.3	470.7	470.2	469.6	469.1	468.5
120°	514.8	514.8	512.9	511.1	509.2	507.4	507.4	507.4	507.4	507.4	507.1
122.5°	551.5	552.0	550.7	549.5	548.1	546.8	546.3	545.8	545.3	544.7	544.2
125°	606.0	606.7	606.0	605.4	604.7	604.0	603.3	602.6	601.9	601.3	600.8
127.5°	661.9	662.7	661.9	661.1	660.3	659.4	658.6	657.8	657.0	656.2	655.4
130°	697.0	698.2	697.8	697.4	696.9	696.4	695.9	695.5	695.1	694.6	694.0
132.5°	732.6	733.9	734.0	734.0	734.1	734.2	733.2	732.2	731.2	730.2	729.4
135°	783.5	785.0	785.4	785.9	786.4	786.8	786.6	786.4	786.2	785.9	785.4
137.5°	834.9	836.2	836.8	837.4	838.0	838.6	838.4	838.2	838.0	837.9	837.3
140°	867.0	868.5	869.7	870.8	872.0	873.1	873.1	873.1	873.1	873.1	872.7
142.5°	899.8	901.2	902.0	902.8	903.6	904.4	904.5	904.7	904.9	905.1	904.7
145°	945.2	946.7	948.1	949.4	950.9	952.2	952.4	952.7	952.9	953.1	952.8
147.5°	988.6	990.1	990.9	991.9	992.8	993.7	994.2	994.7	995.2	995.7	995.5
150°	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7
152.5°	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7
155°	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7	1081.9	1083.0	1084.1	1084.3
157.5°	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5	1113.1	1114.6	1116.2	1116.4
160°	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2	1131.6	1133.0	1134.3	1134.6
162.5°	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8	1148.4	1149.9	1151.5	1151.8
165°	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5	1170.1	1171.6	1173.3	1173.5
167.5°	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4	1188.0	1189.5	1191.1	1191.4
170°	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2	1197.8	1199.4	1201.0	1201.1
172.5°	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6	1205.2	1206.8	1208.4	1208.5
175°	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6	1213.2	1214.8	1216.4	1216.6
177.5°	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	817.5	818.0	817.3	817.8	817.3	818.0	817.5	820.1	820.6	821.1	820.6
5°	761.8	758.2	757.6	756.8	757.6	758.2	761.8	763.3	764.5	766.8	771.0
7.5°	695.1	694.6	693.2	691.0	693.2	694.6	695.1	700.2	704.3	708.8	717.3
10°	652.3	650.9	650.5	648.5	650.5	650.9	652.3	658.8	663.5	670.0	681.6
12.5°	602.1	592.6	591.6	586.5	591.6	592.6	602.1	610.5	623.3	629.5	641.8
15°	512.7	510.9	505.0	501.1	505.0	510.9	512.7	519.8	524.5	541.7	561.5
17.5°	461.5	455.7	453.9	453.1	453.9	455.7	461.5	465.0	471.7	480.8	492.7
20°	428.6	423.3	422.5	421.8	422.5	423.3	428.6	432.8	438.2	447.9	460.3
22.5°	405.9	400.4	398.1	396.3	398.1	400.4	405.9	409.2	414.0	421.6	430.0
25°	367.1	365.0	363.8	363.3	363.8	365.0	367.1	370.1	374.8	385.2	394.0
27.5°	336.8	332.2	331.3	329.8	331.3	332.2	336.8	342.1	347.0	351.6	359.6
30°	319.5	318.0	315.9	314.2	315.9	318.0	319.5	322.2	325.4	333.4	341.1
32.5°	299.1	297.9	296.0	295.2	296.0	297.9	299.1	302.8	309.6	314.5	320.0
35°	276.6	272.4	270.7	268.0	270.7	272.4	276.6	279.6	282.3	286.4	296.4
37.5°	252.8	250.6	248.1	249.0	248.1	250.6	252.8	254.0	259.6	265.4	269.7
40°	234.3	232.8	232.2	232.0	232.2	232.8	234.3	238.1	244.9	247.6	254.1
42.5°	219.6	215.6	214.0	214.0	214.0	215.6	219.6	223.9	228.1	232.4	239.2
45°	197.3	193.5	190.8	191.1	190.8	193.5	197.3	198.8	202.3	211.0	214.8
47.5°	174.5	174.4	172.7	173.3	172.7	174.4	174.5	177.1	181.6	186.9	193.0
50°	163.6	161.8	160.7	160.9	160.7	161.8	163.6	165.6	168.3	171.0	180.5
52.5°	153.2	151.6	150.7	151.9	150.7	151.6	153.2	154.3	156.2	158.9	165.3
55°	136.1	134.3	134.0	133.7	134.0	134.3	136.1	137.5	139.9	142.0	145.0
57.5°	117.0	115.8	114.0	113.3	114.0	115.8	117.0	119.1	122.0	124.7	127.8
60°	103.2	100.8	97.9	97.6	97.9	100.8	103.2	107.1	108.3	112.4	116.0
62.5°	90.7	90.2	89.7	89.6	89.7	90.2	90.7	92.0	93.6	99.7	103.9
65°	79.6	79.3	79.6	79.9	79.6	79.3	79.6	80.2	80.5	81.0	82.9
67.5°	69.3	68.8	68.3	68.5	68.3	68.8	69.3	69.5	70.3	70.7	71.9
70°	61.6	61.2	60.9	60.9	60.9	61.2	61.6	62.1	62.7	63.3	64.8
72.5°	53.9	53.9	53.6	53.4	53.6	53.9	53.9	55.1	55.4	56.0	57.0
75°	43.2	42.6	42.6	42.6	42.6	42.6	43.2	43.5	43.8	44.7	45.2
77.5°	32.9	32.6	32.3	32.1	32.3	32.6	32.9	33.0	33.4	33.6	34.2
80°	26.1	25.7	25.4	25.4	25.4	25.7	26.1	26.3	26.3	27.3	26.9
82.5°	19.9	19.6	19.5	19.3	19.5	19.6	19.9	20.0	20.0	20.6	20.5
85°	10.6	10.9	10.6	11.2	10.6	10.9	10.6	10.4	10.6	11.2	11.2
87.5°	9.9	9.7	10.0	9.8	10.0	9.7	9.9	9.9	10.1	10.2	10.3
90°	34.2	34.5	34.7	34.9	34.7	34.5	34.2	34.0	34.1	34.6	35.0
92.5°	33.1	33.2	33.3	33.3	33.3	33.2	33.1	33.1	33.0	33.0	32.9
95°	65.0	64.6	64.2	63.7	64.2	64.6	65.0	65.5	65.8	65.8	65.8
97.5°	110.4	110.4	110.4	110.4	110.4	110.4	110.4	110.5	110.5	110.5	110.5
100°	141.4	141.2	140.9	140.7	140.9	141.2	141.4	141.6	141.7	141.7	141.7
102.5°	175.9	175.7	175.5	175.2	175.5	175.7	175.9	176.2	176.2	176.0	175.8
105°	228.1	228.1	228.1	228.1	228.1	228.1	228.1	228.1	227.8	227.4	226.9
107.5°	280.9	279.9	278.8	277.7	278.8	279.9	280.9	281.9	282.4	282.2	282.0
110°	318.5	317.7	317.0	316.4	317.0	317.7	318.5	319.1	319.5	319.5	319.5



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	354.8	354.3	353.9	353.3	353.9	354.3	354.8	355.4	355.8	356.4	357.0
115°	413.0	412.3	411.5	410.9	411.5	412.3	413.0	413.6	414.1	414.3	414.5
117.5°	467.8	467.1	466.4	465.7	466.4	467.1	467.8	468.5	469.1	469.6	470.2
120°	506.4	505.7	505.0	504.4	505.0	505.7	506.4	507.1	507.4	507.4	507.4
122.5°	543.7	543.1	542.6	542.2	542.6	543.1	543.7	544.2	544.7	545.3	545.8
125°	600.6	600.3	600.1	599.8	600.1	600.3	600.6	600.8	601.3	601.9	602.6
127.5°	654.7	653.9	653.2	652.4	653.2	653.9	654.7	655.4	656.2	657.0	657.8
130°	693.0	692.1	691.2	690.2	691.2	692.1	693.0	694.0	694.6	695.1	695.5
132.5°	728.6	727.9	727.1	726.4	727.1	727.9	728.6	729.4	730.2	731.2	732.2
135°	784.7	784.1	783.4	782.7	783.4	784.1	784.7	785.4	785.9	786.2	786.4
137.5°	836.4	835.5	834.6	833.7	834.6	835.5	836.4	837.3	837.9	838.0	838.2
140°	871.7	870.8	869.9	869.0	869.9	870.8	871.7	872.7	873.1	873.1	873.1
142.5°	903.8	902.9	902.0	901.0	902.0	902.9	903.8	904.7	905.1	904.9	904.7
145°	951.9	950.9	950.1	949.1	950.1	950.9	951.9	952.8	953.1	952.9	952.7
147.5°	994.7	993.8	992.9	992.0	992.9	993.8	994.7	995.5	995.7	995.2	994.7
150°	1022.1	1021.4	1020.6	1020.0	1020.6	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4
152.5°	1048.8	1048.1	1047.2	1046.3	1047.2	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1
155°	1083.7	1083.0	1082.3	1081.6	1082.3	1083.0	1083.7	1084.3	1084.1	1083.0	1081.9
157.5°	1115.3	1114.2	1113.1	1112.0	1113.1	1114.2	1115.3	1116.4	1116.2	1114.6	1113.1
160°	1133.7	1132.7	1131.9	1130.9	1131.9	1132.7	1133.7	1134.6	1134.3	1133.0	1131.6
162.5°	1150.6	1149.5	1148.4	1147.4	1148.4	1149.5	1150.6	1151.8	1151.5	1149.9	1148.4
165°	1172.4	1171.2	1170.1	1168.9	1170.1	1171.2	1172.4	1173.5	1173.3	1171.6	1170.1
167.5°	1190.2	1189.0	1187.8	1186.6	1187.8	1189.0	1190.2	1191.4	1191.1	1189.5	1188.0
170°	1199.8	1198.4	1197.0	1195.6	1197.0	1198.4	1199.8	1201.1	1201.0	1199.4	1197.8
172.5°	1207.1	1205.8	1204.4	1203.0	1204.4	1205.8	1207.1	1208.5	1208.4	1206.8	1205.2
175°	1215.1	1213.8	1212.4	1211.0	1212.4	1213.8	1215.1	1216.6	1216.4	1214.8	1213.2
177.5°	1218.1	1217.0	1215.8	1214.7	1215.8	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	818.7	822.0	827.0	829.9	834.6	837.7	839.3	842.4	844.1	850.0	856.1
5°	773.0	777.8	786.0	793.7	802.0	810.6	816.8	823.9	830.4	841.6	853.5
7.5°	720.6	727.1	740.0	752.3	766.7	778.8	789.5	801.6	812.5	828.5	845.3
10°	681.3	692.8	709.7	721.2	740.1	752.3	769.1	782.4	797.6	818.9	837.8
12.5°	647.5	661.4	674.9	690.9	708.0	728.2	746.7	763.7	781.7	803.7	825.9
15°	586.1	606.2	627.2	643.4	666.5	687.8	709.4	732.5	754.4	780.7	809.7
17.5°	507.0	530.3	565.6	593.5	620.6	642.0	668.7	696.6	722.4	754.2	786.4
20°	471.3	488.4	512.4	549.9	590.8	613.5	640.8	671.5	701.1	735.7	770.3
22.5°	442.6	457.9	477.1	506.4	552.0	583.0	611.4	642.7	677.0	712.3	750.7
25°	401.7	412.4	432.5	456.1	487.5	538.7	569.7	601.1	638.4	676.3	720.0
27.5°	371.1	380.6	393.7	416.3	439.6	476.3	525.8	559.9	597.1	639.7	685.2
30°	347.6	358.9	373.4	389.3	414.8	443.5	492.8	532.5	569.2	613.0	661.5
32.5°	330.6	339.5	351.8	368.0	389.2	416.7	456.1	504.3	540.0	586.2	636.8
35°	302.6	313.0	323.1	338.4	355.6	380.7	410.6	462.1	497.6	543.1	594.1
37.5°	279.6	286.0	297.1	309.3	327.3	346.1	372.0	418.2	456.6	501.3	553.4
40°	262.1	270.1	278.4	292.0	306.8	324.8	350.2	384.6	428.6	472.5	523.3
42.5°	245.1	255.2	264.0	273.1	289.2	307.3	328.0	357.1	402.1	443.5	493.1
45°	224.5	231.1	240.2	250.3	263.6	279.0	297.3	322.7	365.9	401.7	448.2
47.5°	200.7	210.2	216.1	225.9	238.6	253.3	270.3	292.3	327.3	360.8	403.9
50°	184.3	194.1	202.6	211.5	222.8	236.9	251.1	272.4	300.6	335.8	376.0
52.5°	170.3	179.0	187.3	196.1	207.2	220.1	233.6	252.3	276.4	308.8	347.8
55°	151.1	156.5	165.1	174.0	183.7	196.1	209.1	224.8	245.6	272.7	304.4
57.5°	131.5	137.7	144.5	153.4	163.3	172.9	184.5	198.8	215.1	239.7	266.8
60°	120.4	125.2	130.8	139.9	149.1	157.6	168.9	180.8	196.1	217.5	240.5
62.5°	108.1	112.6	117.7	125.7	134.7	142.5	152.3	164.9	177.9	197.3	217.5
65°	87.5	94.1	99.1	106.2	113.6	121.9	129.6	139.7	151.1	166.5	184.6
67.5°	72.6	75.9	80.6	87.1	94.6	101.7	109.0	116.8	126.8	138.7	153.0
70°	66.0	67.2	68.0	74.2	81.4	88.5	95.2	102.7	111.2	121.0	133.4
72.5°	58.1	59.3	60.4	63.1	68.8	75.9	82.9	88.5	96.6	104.6	114.7
75°	46.2	47.9	48.8	50.3	52.4	57.1	63.6	68.9	73.7	79.9	87.9
77.5°	35.2	36.1	37.1	38.7	39.9	42.1	45.8	50.6	55.1	58.6	64.2
80°	27.8	28.1	29.3	29.9	31.7	33.1	34.9	38.7	43.2	44.7	48.5
82.5°	20.9	21.2	22.2	22.8	23.6	24.9	27.1	28.1	31.6	33.5	36.0
85°	11.6	11.2	12.1	12.1	12.8	13.3	13.9	15.4	16.2	18.6	19.3
87.5°	10.6	10.8	10.0	9.0	8.0	7.4	6.9	6.6	6.5	6.7	7.1
90°	35.5	36.0	30.9	25.9	20.9	15.8	12.0	9.3	6.5	3.8	1.0
92.5°	32.7	32.6	31.4	30.3	29.1	27.9	26.3	24.3	22.3	20.3	18.3
95°	65.8	65.8	65.3	64.8	64.4	63.9	62.6	60.3	58.0	55.7	53.4
97.5°	110.5	110.5	109.6	108.8	107.9	107.0	105.6	103.6	101.6	99.6	97.6
100°	141.7	141.7	141.1	140.4	139.7	139.0	137.8	135.9	134.1	132.3	130.5
102.5°	175.6	175.5	174.6	173.7	172.9	172.0	170.8	169.4	167.9	166.4	164.9
105°	226.4	226.0	225.5	225.1	224.6	224.2	223.6	222.9	222.2	221.5	220.9
107.5°	281.9	281.6	281.6	281.6	281.6	281.6	281.1	280.1	279.2	278.1	277.1
110°	319.5	319.5	319.5	319.5	319.5	319.5	318.8	317.4	316.0	314.7	313.3



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	357.5	358.1	358.2	358.5	358.6	358.8	358.2	356.9	355.5	354.1	352.8
115°	414.8	414.9	415.4	415.9	416.4	416.8	416.4	414.9	413.6	412.3	410.9
117.5°	470.7	471.3	472.5	473.8	475.1	476.4	476.1	474.3	472.5	470.6	468.8
120°	507.4	507.4	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4
122.5°	546.3	546.8	548.1	549.5	550.7	552.0	551.5	549.3	547.2	544.9	542.7
125°	603.3	604.0	604.7	605.4	606.0	606.7	606.0	604.0	601.9	599.8	597.8
127.5°	658.6	659.4	660.3	661.1	661.9	662.7	661.9	659.3	656.6	654.0	651.4
130°	695.9	696.4	696.9	697.4	697.8	698.2	697.0	694.0	691.1	688.1	685.2
132.5°	733.2	734.2	734.1	734.0	734.0	733.9	732.6	730.2	727.8	725.3	722.9
135°	786.6	786.8	786.4	785.9	785.4	785.0	783.5	781.0	778.5	775.9	773.5
137.5°	838.4	838.6	838.0	837.4	836.8	836.2	834.9	832.8	830.8	828.7	826.6
140°	873.1	873.1	872.0	870.8	869.7	868.5	867.0	864.9	862.8	860.8	858.7
142.5°	904.5	904.4	903.6	902.8	902.0	901.2	899.8	897.8	895.7	893.7	891.6
145°	952.4	952.2	950.9	949.4	948.1	946.7	945.2	943.6	942.1	940.5	938.8
147.5°	994.2	993.7	992.8	991.9	990.9	990.1	988.6	986.7	984.8	982.9	981.0
150°	1020.6	1020.0	1019.1	1018.2	1017.2	1016.4	1015.2	1013.8	1012.5	1011.1	1009.7
152.5°	1047.2	1046.3	1045.2	1044.1	1043.0	1041.9	1040.7	1039.3	1037.9	1036.6	1035.2
155°	1080.7	1079.6	1078.9	1078.2	1077.5	1076.8	1076.2	1075.5	1074.8	1074.1	1073.4
157.5°	1111.5	1110.0	1109.5	1109.1	1108.7	1108.3	1107.9	1107.5	1107.0	1106.5	1106.0
160°	1130.2	1128.9	1128.6	1128.4	1128.1	1128.0	1127.6	1127.2	1126.7	1126.2	1125.8
162.5°	1146.8	1145.3	1145.1	1144.9	1144.6	1144.4	1144.2	1144.1	1144.1	1144.0	1143.8
165°	1168.5	1166.9	1166.9	1166.9	1166.9	1166.9	1167.0	1167.2	1167.4	1167.7	1167.9
167.5°	1186.4	1184.7	1184.8	1184.9	1184.9	1184.9	1185.3	1186.0	1186.7	1187.3	1188.0
170°	1196.2	1194.6	1194.8	1195.1	1195.3	1195.6	1196.0	1196.7	1197.4	1198.0	1198.7
172.5°	1203.6	1202.0	1202.2	1202.5	1202.7	1202.9	1203.4	1204.0	1204.8	1205.5	1206.1
175°	1211.6	1210.0	1210.5	1210.9	1211.4	1211.9	1212.4	1213.1	1213.8	1214.5	1215.1
177.5°	1215.8	1214.7	1215.1	1215.4	1215.8	1216.2	1216.6	1217.2	1217.7	1218.3	1218.9
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	856.3	857.1	861.8	864.0	868.2	869.9	871.7	871.2	871.2	872.2	878.8
5°	858.2	864.1	873.0	881.5	889.9	897.0	901.7	906.4	908.2	916.8	924.5
7.5°	855.2	866.0	880.7	893.7	909.4	921.7	931.8	941.0	947.3	959.8	972.6
10°	851.1	866.5	883.0	899.9	921.5	937.8	954.3	967.1	971.2	989.8	1000.5
12.5°	843.0	863.6	884.7	906.6	927.6	950.1	968.3	981.0	995.6	1012.3	1032.0
15°	831.0	854.7	882.2	910.3	940.5	967.7	987.2	1009.4	1025.3	1043.7	1060.8
17.5°	813.7	844.1	879.1	911.6	946.5	975.7	1002.7	1023.9	1035.1	1045.6	1048.2
20°	799.9	832.7	873.9	912.4	947.2	981.0	1007.6	1025.3	1028.3	1028.6	1012.9
22.5°	785.1	822.1	865.1	904.5	946.3	983.8	1004.5	1012.1	1000.4	980.3	950.0
25°	757.6	800.5	850.5	895.5	941.0	976.5	983.7	970.3	929.2	886.0	831.3
27.5°	727.9	776.1	829.7	879.7	928.3	950.3	934.9	886.9	812.9	748.5	670.5
30°	706.2	760.3	812.9	868.9	913.8	923.3	888.1	817.4	731.0	634.0	556.2
32.5°	681.3	738.0	795.9	853.7	891.4	882.1	823.9	736.9	635.6	540.3	466.7
35°	645.8	704.4	766.8	824.7	848.7	808.8	721.8	608.6	505.0	416.0	365.4
37.5°	604.8	668.6	733.5	786.7	785.1	718.4	600.0	483.0	396.0	343.3	307.3
40°	575.7	640.2	710.3	755.3	736.0	649.4	520.9	410.6	347.0	305.0	278.7
42.5°	547.8	612.5	682.1	717.9	684.4	577.9	450.0	363.5	311.0	278.3	256.9
45°	500.3	568.5	633.1	652.9	593.1	475.7	363.8	301.2	266.3	242.0	227.2
47.5°	453.8	521.0	579.9	580.3	499.4	385.8	307.0	260.6	230.8	212.1	201.3
50°	425.4	489.3	538.7	531.0	439.3	343.2	274.5	234.6	209.8	195.3	184.0
52.5°	393.5	455.4	498.2	476.3	388.4	302.0	245.4	211.9	191.3	178.7	168.7
55°	347.0	402.0	432.2	399.1	316.9	251.1	207.4	181.0	165.6	155.0	146.5
57.5°	301.4	346.7	365.8	327.2	260.9	208.3	175.4	155.7	140.4	132.8	128.3
60°	272.7	311.5	324.8	282.3	226.9	182.2	155.3	137.0	125.7	120.7	116.3
62.5°	244.6	276.2	281.8	242.7	197.8	159.5	136.4	120.9	113.4	108.6	104.4
65°	203.0	225.7	223.1	191.7	156.5	126.6	109.7	100.3	94.7	87.9	80.5
67.5°	167.1	181.0	172.6	149.1	119.5	98.4	87.4	80.2	73.3	66.8	65.1
70°	144.3	152.3	143.5	121.9	97.9	82.5	73.7	65.1	60.9	59.5	56.8
72.5°	122.6	125.4	115.8	97.3	79.7	68.4	59.7	54.9	52.7	51.4	49.7
75°	92.0	89.9	81.7	67.2	55.3	47.6	45.0	43.2	41.7	40.6	39.6
77.5°	64.6	61.6	54.2	44.8	38.5	34.9	33.3	32.3	31.6	31.0	30.1
80°	48.5	46.4	39.1	31.9	29.3	27.5	26.6	25.4	25.4	24.9	23.9
82.5°	35.5	33.2	26.8	23.4	21.9	20.9	20.2	19.5	19.3	19.4	18.8
85°	18.6	15.1	13.3	12.8	11.8	11.2	11.6	10.9	10.9	10.9	10.6
87.5°	6.4	5.8	6.1	6.4	7.4	8.5	9.2	10.2	11.5	11.1	11.2
90°	3.8	6.5	9.3	12.0	15.8	20.9	25.9	30.9	36.0	35.5	35.0
92.5°	20.3	22.3	24.3	26.3	27.9	29.1	30.3	31.4	32.6	32.7	32.9
95°	55.7	58.0	60.3	62.6	63.9	64.4	64.8	65.3	65.8	65.8	65.8
97.5°	99.6	101.6	103.6	105.6	107.0	107.9	108.8	109.6	110.5	110.5	110.5
100°	132.3	134.1	135.9	137.8	139.0	139.7	140.4	141.1	141.7	141.7	141.7
102.5°	166.4	167.9	169.4	170.8	172.0	172.9	173.7	174.6	175.5	175.6	175.8
105°	221.5	222.2	222.9	223.6	224.2	224.6	225.1	225.5	226.0	226.4	226.9
107.5°	278.1	279.2	280.1	281.1	281.6	281.6	281.6	281.6	281.6	281.9	282.0
110°	314.7	316.0	317.4	318.8	319.5	319.5	319.5	319.5	319.5	319.5	319.5





TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	354.1	355.5	356.9	358.2	358.8	358.6	358.5	358.2	358.1	357.5	357.0
115°	412.3	413.6	414.9	416.4	416.8	416.4	415.9	415.4	414.9	414.8	414.5
117.5°	470.6	472.5	474.3	476.1	476.4	475.1	473.8	472.5	471.3	470.7	470.2
120°	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	507.4	507.4
122.5°	544.9	547.2	549.3	551.5	552.0	550.7	549.5	548.1	546.8	546.3	545.8
125°	599.8	601.9	604.0	606.0	606.7	606.0	605.4	604.7	604.0	603.3	602.6
127.5°	654.0	656.6	659.3	661.9	662.7	661.9	661.1	660.3	659.4	658.6	657.8
130°	688.1	691.1	694.0	697.0	698.2	697.8	697.4	696.9	696.4	695.9	695.5
132.5°	725.3	727.8	730.2	732.6	733.9	734.0	734.0	734.1	734.2	733.2	732.2
135°	775.9	778.5	781.0	783.5	785.0	785.4	785.9	786.4	786.8	786.6	786.4
137.5°	828.7	830.8	832.8	834.9	836.2	836.8	837.4	838.0	838.6	838.4	838.2
140°	860.8	862.8	864.9	867.0	868.5	869.7	870.8	872.0	873.1	873.1	873.1
142.5°	893.7	895.7	897.8	899.8	901.2	902.0	902.8	903.6	904.4	904.5	904.7
145°	940.5	942.1	943.6	945.2	946.7	948.1	949.4	950.9	952.2	952.4	952.7
147.5°	982.9	984.8	986.7	988.6	990.1	990.9	991.9	992.8	993.7	994.2	994.7
150°	1011.1	1012.5	1013.8	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6	1021.4
152.5°	1036.6	1037.9	1039.3	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2	1048.1
155°	1074.1	1074.8	1075.5	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7	1081.9
157.5°	1106.5	1107.0	1107.5	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5	1113.1
160°	1126.2	1126.7	1127.2	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2	1131.6
162.5°	1144.0	1144.1	1144.1	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8	1148.4
165°	1167.7	1167.4	1167.2	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5	1170.1
167.5°	1187.3	1186.7	1186.0	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4	1188.0
170°	1198.0	1197.4	1196.7	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2	1197.8
172.5°	1205.5	1204.8	1204.0	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6	1205.2
175°	1214.5	1213.8	1213.1	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6	1213.2
177.5°	1218.3	1217.7	1217.2	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8	1217.0
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	881.2	884.3	885.7	885.7	887.4	886.7	886.0
5°	931.8	937.5	938.7	944.0	947.8	946.7	947.2
7.5°	982.2	991.3	1000.2	1004.2	1005.0	1007.3	1008.2
10°	1013.2	1020.6	1034.5	1032.5	1042.8	1048.7	1038.9
12.5°	1043.1	1053.0	1062.7	1065.3	1071.2	1073.1	1069.2
15°	1070.0	1075.3	1075.9	1074.4	1076.3	1074.8	1069.1
17.5°	1044.8	1036.2	1018.7	1010.3	1003.8	994.1	990.2
20°	1003.1	977.7	948.2	936.3	922.4	895.2	901.7
22.5°	913.2	884.2	854.7	820.1	803.6	777.8	776.3
25°	773.3	723.3	668.3	629.8	607.4	581.6	570.4
27.5°	601.3	538.3	493.2	470.4	449.6	429.2	428.3
30°	488.1	440.8	405.9	386.3	373.7	365.0	366.9
32.5°	411.5	379.0	355.5	339.3	329.9	323.4	323.3
35°	336.4	314.2	299.0	292.3	285.5	280.7	281.1
37.5°	287.9	274.5	266.1	258.6	254.4	252.1	250.7
40°	263.0	252.1	245.6	241.1	237.6	234.3	233.7
42.5°	243.4	234.3	227.8	224.3	221.0	218.6	218.1
45°	215.9	208.6	202.6	198.8	197.3	195.3	195.3
47.5°	192.1	184.8	180.2	177.8	175.2	173.9	173.8
50°	176.0	170.4	166.3	164.8	162.7	161.8	161.5
52.5°	161.6	157.4	154.4	153.4	152.5	151.4	151.5
55°	142.0	139.7	138.5	137.5	136.1	134.3	135.5
57.5°	125.5	123.5	120.3	117.5	116.1	114.9	115.3
60°	113.9	109.7	105.6	102.3	101.5	98.8	98.8
62.5°	99.3	93.4	88.3	86.5	85.6	84.4	84.1
65°	76.3	74.0	72.8	71.6	71.0	71.0	70.4
67.5°	63.2	62.3	61.0	60.7	60.1	60.0	59.7
70°	55.9	54.7	54.1	53.9	53.2	53.6	52.7
72.5°	48.8	47.8	47.8	47.0	46.7	46.7	46.0
75°	38.4	38.4	38.2	37.9	37.3	37.0	37.3
77.5°	29.5	29.6	29.1	29.1	29.0	29.1	28.8
80°	23.7	23.9	23.7	23.4	23.1	23.4	23.1
82.5°	18.7	18.3	18.2	18.1	18.1	17.9	17.9
85°	10.6	10.9	10.6	10.4	10.4	10.4	10.6
87.5°	10.9	10.9	10.9	10.9	10.9	10.9	10.8
90°	34.6	34.1	34.0	34.2	34.5	34.7	34.9
92.5°	33.0	33.0	33.1	33.1	33.2	33.3	33.3
95°	65.8	65.8	65.5	65.0	64.6	64.2	63.7
97.5°	110.5	110.5	110.5	110.4	110.4	110.4	110.4
100°	141.7	141.7	141.6	141.4	141.2	140.9	140.7
102.5°	176.0	176.2	176.2	175.9	175.7	175.5	175.2
105°	227.4	227.8	228.1	228.1	228.1	228.1	228.1
107.5°	282.2	282.4	281.9	280.9	279.9	278.8	277.7
110°	319.5	319.5	319.1	318.5	317.7	317.0	316.4



TEST NUMBER: P331798-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	356.4	355.8	355.4	354.8	354.3	353.9	353.3
115°	414.3	414.1	413.6	413.0	412.3	411.5	410.9
117.5°	469.6	469.1	468.5	467.8	467.1	466.4	465.7
120°	507.4	507.4	507.1	506.4	505.7	505.0	504.4
122.5°	545.3	544.7	544.2	543.7	543.1	542.6	542.2
125°	601.9	601.3	600.8	600.6	600.3	600.1	599.8
127.5°	657.0	656.2	655.4	654.7	653.9	653.2	652.4
130°	695.1	694.6	694.0	693.0	692.1	691.2	690.2
132.5°	731.2	730.2	729.4	728.6	727.9	727.1	726.4
135°	786.2	785.9	785.4	784.7	784.1	783.4	782.7
137.5°	838.0	837.9	837.3	836.4	835.5	834.6	833.7
140°	873.1	873.1	872.7	871.7	870.8	869.9	869.0
142.5°	904.9	905.1	904.7	903.8	902.9	902.0	901.0
145°	952.9	953.1	952.8	951.9	950.9	950.1	949.1
147.5°	995.2	995.7	995.5	994.7	993.8	992.9	992.0
150°	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0
152.5°	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3
155°	1083.0	1084.1	1084.3	1083.7	1083.0	1082.3	1081.6
157.5°	1114.6	1116.2	1116.4	1115.3	1114.2	1113.1	1112.0
160°	1133.0	1134.3	1134.6	1133.7	1132.7	1131.9	1130.9
162.5°	1149.9	1151.5	1151.8	1150.6	1149.5	1148.4	1147.4
165°	1171.6	1173.3	1173.5	1172.4	1171.2	1170.1	1168.9
167.5°	1189.5	1191.1	1191.4	1190.2	1189.0	1187.8	1186.6
170°	1199.4	1201.0	1201.1	1199.8	1198.4	1197.0	1195.6
172.5°	1206.8	1208.4	1208.5	1207.1	1205.8	1204.4	1203.0
175°	1214.8	1216.4	1216.6	1215.1	1213.8	1212.4	1211.0
177.5°	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2

(END OF REPORT)