

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331800-927

Luminaire Tested: **S122RDIW-S485D1240U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331800-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1240U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4753.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331800-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331800-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	32	32	31	24
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18
4	71	61	53	48	63	55	49	44	44	39	36	33	30	28	23	21	20	16
5	65	54	47	41	58	49	42	37	39	34	31	30	27	24	21	19	17	14
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	16	12
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	18	15	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10555	10555	10555
5°	10595	10423	10481
10°	10516	10252	10165
15°	10394	9949	9663
20°	10227	9514	9036
25°	10055	9021	8432
30°	9818	8516	7655
35°	9585	7965	6974
40°	9352	7396	6184
45°	9079	6754	5471
50°	8796	6106	4770
55°	8510	5413	4096
60°	8176	4682	3400
65°	7798	3931	3095
70°	7345	3238	2851
75°	6787	2951	2658
80°	5997	2641	2427
85°	4705	2075	2075



TEST NUMBER: P331800-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.2	1.3
10°-20°	168.0	3.5
20°-30°	235.9	5.0
30°-40°	257.3	5.4
40°-50°	236.6	5.0
50°-60°	185.8	3.9
60°-70°	121.1	2.5
70°-80°	62.5	1.3
80°-90°	21.1	0.4
90°-100°	77.1	1.6
100°-110°	239.6	5.0
110°-120°	409.5	8.6
120°-130°	538.5	11.3
130°-140°	604.4	12.7
140°-150°	592.6	12.5
150°-160°	497.0	10.5
160°-170°	329.7	6.9
170°-180°	115.2	2.4
0°-30°	465.2	9.8
0°-40°	722.4	15.2
0°-60°	1144.8	24.1
0°-90°	1349.5	28.4
90°-120°	726.2	15.3
90°-150°	2461.6	51.8
90°-180°	3404.0	71.6
0°-180°	4753.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	654	654	654	654	654	
5°	654	650	643	648	647	62
15°	622	615	595	584	578	175
25°	564	544	506	483	473	259
35°	486	455	404	368	354	304
45°	398	357	296	255	240	307
55°	302	255	192	158	146	270
65°	204	156	103	84	81	202
75°	109	69	47	43	43	115
85°	25	14	11	11	11	30
90°	1	14	36	34	35	4
95°	53	63	66	66	64	61
105°	221	224	226	228	228	233
115°	411	417	415	414	411	406
125°	598	606	604	601	600	534
135°	774	784	787	786	783	597
145°	939	946	952	953	949	586
155°	1073	1076	1080	1084	1082	494
165°	1168	1167	1167	1173	1169	329
175°	1215	1212	1210	1216	1211	115
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P331800-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	656.1	655.6	655.1	654.5	654.0	653.2	652.0	650.9	649.7	648.6	649.6
5°	653.7	653.1	652.4	651.8	651.1	649.9	648.2	646.5	644.8	643.1	644.3
7.5°	647.0	646.2	645.4	644.5	643.7	642.3	640.3	638.3	636.4	634.4	634.7
10°	641.4	640.4	639.4	638.6	637.6	635.9	633.3	630.6	628.0	625.3	625.0
12.5°	634.2	633.1	631.9	630.8	629.7	627.5	624.1	620.8	617.3	614.0	613.3
15°	621.8	620.4	618.9	617.4	616.0	613.1	608.6	604.1	599.7	595.2	592.7
17.5°	606.6	604.4	602.1	599.9	597.7	593.7	588.0	582.3	576.6	570.8	567.8
20°	595.2	592.6	589.9	587.3	584.6	580.0	573.5	566.9	560.3	553.7	550.5
22.5°	582.9	580.0	576.9	574.0	571.1	565.9	558.5	551.0	543.7	536.2	532.0
25°	564.4	560.2	556.0	551.8	547.6	541.1	532.4	523.8	515.1	506.4	501.1
27.5°	542.2	537.6	533.0	528.5	523.9	516.7	506.9	497.1	487.4	477.5	471.3
30°	526.6	521.6	516.6	511.6	506.6	498.8	488.3	477.8	467.2	456.8	450.0
32.5°	511.4	505.6	499.7	493.9	488.1	479.7	469.1	458.3	447.6	436.9	429.2
35°	486.3	479.6	472.9	466.2	459.5	450.4	438.8	427.2	415.7	404.1	395.8
37.5°	461.2	453.8	446.5	439.1	431.8	421.9	409.6	397.3	384.9	372.6	363.5
40°	443.7	435.9	427.9	420.1	412.2	401.9	389.1	376.4	363.6	350.9	341.5
42.5°	425.7	417.4	409.1	400.8	392.5	381.8	368.6	355.4	342.2	329.1	319.4
45°	397.6	388.8	379.9	371.1	362.3	351.0	337.2	323.4	309.6	295.8	286.5
47.5°	370.1	360.8	351.5	342.1	332.8	321.0	306.7	292.5	278.2	264.0	254.7
50°	350.2	340.9	331.6	322.3	312.9	301.0	286.5	272.1	257.6	243.1	234.1
52.5°	330.8	321.1	311.3	301.6	291.8	279.9	265.7	251.6	237.4	223.3	214.5
55°	302.3	292.1	281.8	271.6	261.3	249.1	234.9	220.7	206.4	192.3	184.4
57.5°	273.1	262.6	252.1	241.5	231.0	219.0	205.3	191.6	178.0	164.4	157.1
60°	253.2	242.7	232.2	221.7	211.1	199.2	185.6	172.1	158.5	145.0	138.2
62.5°	233.8	223.3	212.8	202.2	191.7	180.1	167.2	154.2	141.3	128.4	122.0
65°	204.1	193.5	182.8	172.1	161.5	150.3	138.5	126.6	114.8	102.9	98.5
67.5°	175.5	164.9	154.3	143.8	133.2	122.6	111.9	101.3	90.6	80.0	78.0
70°	155.6	145.4	135.1	124.8	114.5	104.9	95.9	86.7	77.7	68.6	67.3
72.5°	136.7	126.8	117.0	107.2	97.4	88.8	81.5	74.2	66.9	59.7	58.5
75°	108.8	99.7	90.5	81.3	72.0	65.2	60.8	56.2	51.8	47.3	46.4
77.5°	81.5	73.4	65.4	57.3	49.3	44.1	42.0	39.8	37.6	35.5	34.9
80°	64.5	57.8	51.1	44.4	37.6	33.7	32.3	31.1	29.7	28.4	27.9
82.5°	48.9	43.6	38.4	33.2	28.0	24.9	24.0	23.1	22.2	21.3	21.0
85°	25.4	22.7	19.9	17.2	14.4	12.8	12.4	12.0	11.6	11.2	11.2
87.5°	7.8	7.4	7.2	6.9	6.6	7.0	8.0	9.0	10.0	11.0	10.8
90°	1.0	3.8	6.5	9.3	12.0	15.8	20.9	25.9	30.9	36.0	35.5
92.5°	18.3	20.3	22.3	24.3	26.3	27.9	29.1	30.3	31.4	32.6	32.7
95°	53.4	55.7	58.0	60.3	62.6	63.9	64.4	64.8	65.3	65.8	65.8
97.5°	97.6	99.6	101.6	103.6	105.6	107.0	107.9	108.8	109.6	110.5	110.5
100°	130.5	132.3	134.1	135.9	137.8	139.0	139.7	140.4	141.1	141.7	141.7
102.5°	164.9	166.4	167.9	169.4	170.8	172.0	172.9	173.7	174.6	175.5	175.6
105°	220.9	221.5	222.2	222.9	223.6	224.2	224.6	225.1	225.5	226.0	226.4
107.5°	277.1	278.1	279.2	280.1	281.1	281.6	281.6	281.6	281.6	281.6	281.9
110°	313.3	314.7	316.0	317.4	318.8	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331800-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	352.8	354.1	355.5	356.9	358.2	358.8	358.6	358.5	358.2	358.1	357.5
115°	410.9	412.3	413.6	414.9	416.4	416.8	416.4	415.9	415.4	414.9	414.8
117.5°	468.8	470.6	472.5	474.3	476.1	476.4	475.1	473.8	472.5	471.3	470.7
120°	507.4	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	507.4
122.5°	542.7	544.9	547.2	549.3	551.5	552.0	550.7	549.5	548.1	546.8	546.3
125°	597.8	599.8	601.9	604.0	606.0	606.7	606.0	605.4	604.7	604.0	603.3
127.5°	651.4	654.0	656.6	659.3	661.9	662.7	661.9	661.1	660.3	659.4	658.6
130°	685.2	688.1	691.1	694.0	697.0	698.2	697.8	697.4	696.9	696.4	695.9
132.5°	722.9	725.3	727.8	730.2	732.6	733.9	734.0	734.0	734.1	734.2	733.2
135°	773.5	775.9	778.5	781.0	783.5	785.0	785.4	785.9	786.4	786.8	786.6
137.5°	826.6	828.7	830.8	832.8	834.9	836.2	836.8	837.4	838.0	838.6	838.4
140°	858.7	860.8	862.8	864.9	867.0	868.5	869.7	870.8	872.0	873.1	873.1
142.5°	891.6	893.7	895.7	897.8	899.8	901.2	902.0	902.8	903.6	904.4	904.5
145°	938.8	940.5	942.1	943.6	945.2	946.7	948.1	949.4	950.9	952.2	952.4
147.5°	981.0	982.9	984.8	986.7	988.6	990.1	990.9	991.9	992.8	993.7	994.2
150°	1009.7	1011.1	1012.5	1013.8	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6
152.5°	1035.2	1036.6	1037.9	1039.3	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2
155°	1073.4	1074.1	1074.8	1075.5	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7
157.5°	1106.0	1106.5	1107.0	1107.5	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5
160°	1125.8	1126.2	1126.7	1127.2	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2
162.5°	1143.8	1144.0	1144.1	1144.1	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8
165°	1167.9	1167.7	1167.4	1167.2	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5
167.5°	1188.0	1187.3	1186.7	1186.0	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4
170°	1198.7	1198.0	1197.4	1196.7	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2
172.5°	1206.1	1205.5	1204.8	1204.0	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6
175°	1215.1	1214.5	1213.8	1213.1	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6
177.5°	1218.9	1218.3	1217.7	1217.2	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331800-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	650.6	651.7	652.8	653.2	653.0	652.8	652.5	652.4
5°	645.5	646.7	647.8	648.2	647.8	647.5	647.1	646.7
7.5°	635.0	635.3	635.7	635.6	634.9	634.1	633.5	632.8
10°	624.6	624.2	623.8	623.2	622.4	621.6	620.8	620.0
12.5°	612.6	611.9	611.2	610.1	608.8	607.5	606.2	604.9
15°	590.2	587.7	585.2	583.3	581.9	580.7	579.3	578.1
17.5°	564.8	561.9	558.9	556.3	554.1	551.8	549.5	547.2
20°	547.2	543.9	540.6	537.5	534.6	531.7	528.9	525.9
22.5°	527.8	523.6	519.4	516.1	514.0	511.8	509.7	507.5
25°	495.7	490.3	484.9	481.2	479.2	477.2	475.3	473.3
27.5°	465.0	458.7	452.4	447.7	444.6	441.5	438.3	435.2
30°	443.3	436.7	429.9	424.8	421.2	417.7	414.2	410.6
32.5°	421.5	413.9	406.2	400.8	397.4	394.1	390.7	387.4
35°	387.5	379.2	371.0	365.4	362.5	359.6	356.7	353.8
37.5°	354.3	345.2	336.1	329.9	326.6	323.3	320.0	316.6
40°	332.2	322.8	313.5	307.1	303.7	300.3	296.8	293.4
42.5°	309.7	300.1	290.5	284.0	280.7	277.3	274.0	270.7
45°	277.1	267.8	258.5	252.2	249.1	245.9	242.7	239.6
47.5°	245.4	236.1	226.9	220.8	217.9	215.1	212.1	209.3
50°	225.0	215.9	206.8	201.0	198.2	195.4	192.7	189.9
52.5°	205.7	197.0	188.2	182.6	180.1	177.5	174.9	172.4
55°	176.5	168.6	160.7	155.5	153.0	150.5	148.1	145.5
57.5°	149.9	142.7	135.5	130.8	128.7	126.6	124.5	122.3
60°	131.5	124.8	118.1	113.8	111.6	109.5	107.4	105.3
62.5°	115.6	109.2	102.8	99.0	97.8	96.5	95.2	94.0
65°	94.0	89.5	85.1	82.6	82.2	81.8	81.4	81.0
67.5°	75.9	73.8	71.8	70.6	70.1	69.7	69.3	68.8
70°	66.0	64.7	63.4	62.4	61.9	61.4	60.8	60.4
72.5°	57.4	56.3	55.2	54.5	54.2	53.9	53.6	53.2
75°	45.5	44.6	43.6	43.1	43.0	42.9	42.7	42.6
77.5°	34.5	33.9	33.4	33.0	32.8	32.6	32.4	32.2
80°	27.3	26.9	26.3	26.1	26.1	26.1	26.1	26.1
82.5°	20.7	20.4	20.0	19.9	19.9	19.9	19.9	19.9
85°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2
87.5°	10.6	10.4	10.2	10.1	10.1	10.2	10.2	10.3
90°	35.0	34.6	34.1	34.0	34.2	34.5	34.7	34.9
92.5°	32.9	33.0	33.0	33.1	33.1	33.2	33.3	33.3
95°	65.8	65.8	65.8	65.5	65.0	64.6	64.2	63.7
97.5°	110.5	110.5	110.5	110.5	110.4	110.4	110.4	110.4
100°	141.7	141.7	141.7	141.6	141.4	141.2	140.9	140.7
102.5°	175.8	176.0	176.2	176.2	175.9	175.7	175.5	175.2
105°	226.9	227.4	227.8	228.1	228.1	228.1	228.1	228.1
107.5°	282.0	282.2	282.4	281.9	280.9	279.9	278.8	277.7
110°	319.5	319.5	319.5	319.1	318.5	317.7	317.0	316.4



TEST NUMBER: P331800-927

CATALOG NUMBER: S122RDIW-S485D1240U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	357.0	356.4	355.8	355.4	354.8	354.3	353.9	353.3
115°	414.5	414.3	414.1	413.6	413.0	412.3	411.5	410.9
117.5°	470.2	469.6	469.1	468.5	467.8	467.1	466.4	465.7
120°	507.4	507.4	507.4	507.1	506.4	505.7	505.0	504.4
122.5°	545.8	545.3	544.7	544.2	543.7	543.1	542.6	542.2
125°	602.6	601.9	601.3	600.8	600.6	600.3	600.1	599.8
127.5°	657.8	657.0	656.2	655.4	654.7	653.9	653.2	652.4
130°	695.5	695.1	694.6	694.0	693.0	692.1	691.2	690.2
132.5°	732.2	731.2	730.2	729.4	728.6	727.9	727.1	726.4
135°	786.4	786.2	785.9	785.4	784.7	784.1	783.4	782.7
137.5°	838.2	838.0	837.9	837.3	836.4	835.5	834.6	833.7
140°	873.1	873.1	873.1	872.7	871.7	870.8	869.9	869.0
142.5°	904.7	904.9	905.1	904.7	903.8	902.9	902.0	901.0
145°	952.7	952.9	953.1	952.8	951.9	950.9	950.1	949.1
147.5°	994.7	995.2	995.7	995.5	994.7	993.8	992.9	992.0
150°	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0
152.5°	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3
155°	1081.9	1083.0	1084.1	1084.3	1083.7	1083.0	1082.3	1081.6
157.5°	1113.1	1114.6	1116.2	1116.4	1115.3	1114.2	1113.1	1112.0
160°	1131.6	1133.0	1134.3	1134.6	1133.7	1132.7	1131.9	1130.9
162.5°	1148.4	1149.9	1151.5	1151.8	1150.6	1149.5	1148.4	1147.4
165°	1170.1	1171.6	1173.3	1173.5	1172.4	1171.2	1170.1	1168.9
167.5°	1188.0	1189.5	1191.1	1191.4	1190.2	1189.0	1187.8	1186.6
170°	1197.8	1199.4	1201.0	1201.1	1199.8	1198.4	1197.0	1195.6
172.5°	1205.2	1206.8	1208.4	1208.5	1207.1	1205.8	1204.4	1203.0
175°	1213.2	1214.8	1216.4	1216.6	1215.1	1213.8	1212.4	1211.0
177.5°	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2

(END OF REPORT)