

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331802-927

Luminaire Tested: **S122RDIW-S485D1440U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331802-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1440U927-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5434.2 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27				
1	93	89	85	82	83	80	77	74	62	60	59	46	45	44	32	31	30	24				
2	85	78	73	68	76	70	65	61	55	52	49	41	39	37	28	27	26	21				
3	78	69	62	57	69	62	56	52	49	45	42	37	34	32	26	24	23	18				
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	21	20	16				
5	66	55	47	42	59	49	43	38	39	35	31	30	27	24	21	19	18	14				
6	60	49	42	36	54	44	38	33	35	31	27	27	24	22	19	17	16	13				
7	56	44	37	32	50	40	34	29	32	28	24	25	22	19	18	16	14	11				
8	52	40	33	28	46	37	30	26	29	25	22	23	20	17	16	14	13	10				
9	48	37	30	25	43	33	27	23	27	22	19	21	18	16	15	13	12	10				
10	45	34	27	22	40	31	25	21	25	20	17	19	16	14	14	12	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13747	13747	13747	13747
5°	15352	13833	12266	13833
10°	17033	13736	10632	13736
15°	17870	13534	8376	13534
20°	15493	13235	7247	13235
25°	10162	12827	6472	12827
30°	6840	12333	5858	12333
35°	5541	11710	5282	11710
40°	4926	11030	4890	11030
45°	4459	10234	4364	10234
50°	4057	9445	4042	9445
55°	3814	8569	3764	8569
60°	3190	7766	3152	7766
65°	2690	7053	3053	7053
70°	2488	6297	2875	6297
75°	2327	5483	2658	5483
80°	2148	4510	2362	4510
85°	1964	3575	2075	3575



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	1.5
10°-20°	224.9	4.1
20°-30°	289.8	5.3
30°-40°	275.4	5.1
40°-50°	235.9	4.3
50°-60°	179.7	3.3
60°-70°	113.6	2.1
70°-80°	56.7	1.0
80°-90°	20.4	0.4
90°-100°	89.7	1.6
100°-110°	278.5	5.1
110°-120°	476.1	8.8
120°-130°	626.1	11.5
130°-140°	702.7	12.9
140°-150°	689.0	12.7
150°-160°	577.9	10.6
160°-170°	383.3	7.1
170°-180°	134.0	2.5
0°-30°	595.4	11.0
0°-40°	870.8	16.0
0°-60°	1286.4	23.7
0°-90°	1477.1	27.2
90°-120°	844.3	15.5
90°-150°	2862.0	52.7
90°-180°	3957.0	72.8
0°-180°	5434.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	851	851	851	851	851	
5°	947	854	757	854	947	93
15°	1069	810	501	810	1069	288
25°	570	720	363	720	570	271
35°	281	594	268	594	281	180
45°	195	448	191	448	195	151
55°	136	304	134	304	136	119
65°	70	185	80	185	70	72
75°	37	88	43	88	37	40
85°	11	19	11	19	11	13
90°	41	1	41	1	41	18
95°	74	62	74	62	74	83
105°	265	257	265	257	265	279
115°	478	478	478	478	478	472
125°	697	695	697	695	697	622
135°	910	899	910	899	910	700
145°	1104	1092	1104	1092	1104	689
155°	1258	1248	1258	1248	1258	579
165°	1359	1358	1359	1358	1359	383
175°	1408	1413	1408	1413	1408	134
180°	1415	1415	1415	1415	1415	



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	886.0	886.7	887.4	885.7	885.7	884.3	881.2	878.8	872.2	871.2	871.2
5°	947.2	946.7	947.8	944.0	938.7	937.5	931.8	924.5	916.8	908.2	906.4
7.5°	1008.2	1007.3	1005.0	1004.2	1000.2	991.3	982.2	972.6	959.8	947.3	941.0
10°	1038.9	1048.7	1042.8	1032.5	1034.5	1020.6	1013.2	1000.5	989.8	971.2	967.1
12.5°	1069.2	1073.1	1071.2	1065.3	1062.7	1053.0	1043.1	1032.0	1012.3	995.6	981.0
15°	1069.1	1074.8	1076.3	1074.4	1075.9	1075.3	1070.0	1060.8	1043.7	1025.3	1009.4
17.5°	990.2	994.1	1003.8	1010.3	1018.7	1036.2	1044.8	1048.2	1045.6	1035.1	1023.9
20°	901.7	895.2	922.4	936.3	948.2	977.7	1003.1	1012.9	1028.6	1028.3	1025.3
22.5°	776.3	777.8	803.6	820.1	854.7	884.2	913.2	950.0	980.3	1000.4	1012.1
25°	570.4	581.6	607.4	629.8	668.3	723.3	773.3	831.3	886.0	929.2	970.3
27.5°	428.3	429.2	449.6	470.4	493.2	538.3	601.3	670.5	748.5	812.9	886.9
30°	366.9	365.0	373.7	386.3	405.9	440.8	488.1	556.2	634.0	731.0	817.4
32.5°	323.3	323.4	329.9	339.3	355.5	379.0	411.5	466.7	540.3	635.6	736.9
35°	281.1	280.7	285.5	292.3	299.0	314.2	336.4	365.4	416.0	505.0	608.6
37.5°	250.7	252.1	254.4	258.6	266.1	274.5	287.9	307.3	343.3	396.0	483.0
40°	233.7	234.3	237.6	241.1	245.6	252.1	263.0	278.7	305.0	347.0	410.6
42.5°	218.1	218.6	221.0	224.3	227.8	234.3	243.4	256.9	278.3	311.0	363.5
45°	195.3	195.3	197.3	198.8	202.6	208.6	215.9	227.2	242.0	266.3	301.2
47.5°	173.8	173.9	175.2	177.8	180.2	184.8	192.1	201.3	212.1	230.8	260.6
50°	161.5	161.8	162.7	164.8	166.3	170.4	176.0	184.0	195.3	209.8	234.6
52.5°	151.5	151.4	152.5	153.4	154.4	157.4	161.6	168.7	178.7	191.3	211.9
55°	135.5	134.3	136.1	137.5	138.5	139.7	142.0	146.5	155.0	165.6	181.0
57.5°	115.3	114.9	116.1	117.5	120.3	123.5	125.5	128.3	132.8	140.4	155.7
60°	98.8	98.8	101.5	102.3	105.6	109.7	113.9	116.3	120.7	125.7	137.0
62.5°	84.1	84.4	85.6	86.5	88.3	93.4	99.3	104.4	108.6	113.4	120.9
65°	70.4	71.0	71.0	71.6	72.8	74.0	76.3	80.5	87.9	94.7	100.3
67.5°	59.7	60.0	60.1	60.7	61.0	62.3	63.2	65.1	66.8	73.3	80.2
70°	52.7	53.6	53.2	53.9	54.1	54.7	55.9	56.8	59.5	60.9	65.1
72.5°	46.0	46.7	46.7	47.0	47.8	47.8	48.8	49.7	51.4	52.7	54.9
75°	37.3	37.0	37.3	37.9	38.2	38.4	38.4	39.6	40.6	41.7	43.2
77.5°	28.8	29.1	29.0	29.1	29.1	29.6	29.5	30.1	31.0	31.6	32.3
80°	23.1	23.4	23.1	23.4	23.7	23.9	23.7	23.9	24.9	25.4	25.4
82.5°	17.9	17.9	18.1	18.1	18.2	18.3	18.7	18.8	19.4	19.3	19.5
85°	10.6	10.4	10.4	10.4	10.6	10.9	10.6	10.6	10.9	10.9	10.9
87.5°	11.9	12.1	12.0	12.0	12.0	12.0	12.0	12.4	12.3	12.6	11.2
90°	40.6	40.3	40.1	39.8	39.5	39.7	40.2	40.7	41.3	41.8	36.0
92.5°	38.7	38.7	38.6	38.5	38.5	38.4	38.3	38.2	38.1	37.9	36.6
95°	74.1	74.5	75.1	75.7	76.1	76.4	76.4	76.4	76.4	76.4	75.9
97.5°	128.3	128.3	128.3	128.4	128.5	128.5	128.5	128.5	128.5	128.5	127.5
100°	163.6	163.9	164.1	164.4	164.7	164.8	164.8	164.8	164.8	164.8	164.0
102.5°	203.7	204.0	204.3	204.5	204.8	204.9	204.6	204.4	204.2	204.0	203.0
105°	265.1	265.1	265.1	265.1	265.1	264.8	264.4	263.8	263.2	262.8	262.2
107.5°	322.9	324.2	325.3	326.6	327.8	328.3	328.1	327.9	327.6	327.5	327.5
110°	367.8	368.6	369.4	370.2	371.0	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	410.8	411.4	412.0	412.6	413.1	413.8	414.4	415.0	415.7	416.3	416.5
115°	477.7	478.5	479.3	480.1	480.9	481.4	481.6	482.0	482.2	482.5	483.0
117.5°	541.5	542.2	543.0	543.8	544.6	545.4	546.1	546.7	547.3	548.0	549.4
120°	586.4	587.2	588.0	588.7	589.5	589.9	589.9	589.9	589.9	589.9	592.1
122.5°	630.3	630.9	631.5	632.1	632.6	633.3	633.9	634.5	635.2	635.8	637.3
125°	697.4	697.8	698.0	698.2	698.5	699.0	699.8	700.6	701.4	702.2	703.1
127.5°	758.6	759.5	760.3	761.1	762.0	762.9	763.8	764.8	765.7	766.8	767.7
130°	802.6	803.6	804.7	805.7	806.8	807.6	808.1	808.7	809.2	809.7	810.2
132.5°	844.5	845.4	846.3	847.2	848.0	849.0	850.2	851.4	852.5	853.7	853.6
135°	910.1	910.9	911.6	912.4	913.2	913.8	914.0	914.3	914.6	914.8	914.3
137.5°	969.2	970.3	971.4	972.5	973.5	974.1	974.4	974.5	974.8	975.0	974.3
140°	1010.3	1011.4	1012.5	1013.5	1014.6	1015.1	1015.1	1015.1	1015.1	1015.1	1013.8
142.5°	1047.6	1048.7	1049.7	1050.8	1051.9	1052.3	1052.1	1051.9	1051.6	1051.5	1050.5
145°	1103.5	1104.5	1105.6	1106.7	1107.7	1108.1	1107.9	1107.6	1107.3	1107.1	1105.5
147.5°	1153.4	1154.4	1155.4	1156.4	1157.5	1157.7	1157.1	1156.5	1156.0	1155.3	1154.3
150°	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9	1184.9
152.5°	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5	1215.2
155°	1257.6	1258.4	1259.2	1260.0	1260.8	1260.4	1259.2	1257.8	1256.5	1255.1	1254.3
157.5°	1292.9	1294.2	1295.5	1296.7	1298.0	1297.8	1295.9	1294.1	1292.3	1290.5	1290.1
160°	1314.9	1316.0	1317.0	1318.0	1319.1	1318.8	1317.2	1315.7	1314.1	1312.5	1312.2
162.5°	1334.0	1335.3	1336.6	1337.8	1339.1	1338.8	1337.0	1335.2	1333.4	1331.6	1331.3
165°	1359.1	1360.4	1361.8	1363.0	1364.4	1364.1	1362.2	1360.4	1358.5	1356.7	1356.7
167.5°	1379.6	1381.0	1382.4	1383.8	1385.1	1384.9	1383.1	1381.2	1379.3	1377.4	1377.5
170°	1390.1	1391.7	1393.3	1394.9	1396.5	1396.4	1394.5	1392.7	1390.8	1388.9	1389.2
172.5°	1398.8	1400.3	1401.9	1403.5	1405.1	1404.9	1403.1	1401.2	1399.4	1397.5	1397.8
175°	1408.0	1409.6	1411.2	1412.8	1414.4	1414.3	1412.4	1410.6	1408.7	1406.8	1407.4
177.5°	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3	1412.8
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	871.7	869.9	868.2	864.0	861.8	857.1	856.3	856.1	850.0	844.1	842.4
5°	901.7	897.0	889.9	881.5	873.0	864.1	858.2	853.5	841.6	830.4	823.9
7.5°	931.8	921.7	909.4	893.7	880.7	866.0	855.2	845.3	828.5	812.5	801.6
10°	954.3	937.8	921.5	899.9	883.0	866.5	851.1	837.8	818.9	797.6	782.4
12.5°	968.3	950.1	927.6	906.6	884.7	863.6	843.0	825.9	803.7	781.7	763.7
15°	987.2	967.7	940.5	910.3	882.2	854.7	831.0	809.7	780.7	754.4	732.5
17.5°	1002.7	975.7	946.5	911.6	879.1	844.1	813.7	786.4	754.2	722.4	696.6
20°	1007.6	981.0	947.2	912.4	873.9	832.7	799.9	770.3	735.7	701.1	671.5
22.5°	1004.5	983.8	946.3	904.5	865.1	822.1	785.1	750.7	712.3	677.0	642.7
25°	983.7	976.5	941.0	895.5	850.5	800.5	757.6	720.0	676.3	638.4	601.1
27.5°	934.9	950.3	928.3	879.7	829.7	776.1	727.9	685.2	639.7	597.1	559.9
30°	888.1	923.3	913.8	868.9	812.9	760.3	706.2	661.5	613.0	569.2	532.5
32.5°	823.9	882.1	891.4	853.7	795.9	738.0	681.3	636.8	586.2	540.0	504.3
35°	721.8	808.8	848.7	824.7	766.8	704.4	645.8	594.1	543.1	497.6	462.1
37.5°	600.0	718.4	785.1	786.7	733.5	668.6	604.8	553.4	501.3	456.6	418.2
40°	520.9	649.4	736.0	755.3	710.3	640.2	575.7	523.3	472.5	428.6	384.6
42.5°	450.0	577.9	684.4	717.9	682.1	612.5	547.8	493.1	443.5	402.1	357.1
45°	363.8	475.7	593.1	652.9	633.1	568.5	500.3	448.2	401.7	365.9	322.7
47.5°	307.0	385.8	499.4	580.3	579.9	521.0	453.8	403.9	360.8	327.3	292.3
50°	274.5	343.2	439.3	531.0	538.7	489.3	425.4	376.0	335.8	300.6	272.4
52.5°	245.4	302.0	388.4	476.3	498.2	455.4	393.5	347.8	308.8	276.4	252.3
55°	207.4	251.1	316.9	399.1	432.2	402.0	347.0	304.4	272.7	245.6	224.8
57.5°	175.4	208.3	260.9	327.2	365.8	346.7	301.4	266.8	239.7	215.1	198.8
60°	155.3	182.2	226.9	282.3	324.8	311.5	272.7	240.5	217.5	196.1	180.8
62.5°	136.4	159.5	197.8	242.7	281.8	276.2	244.6	217.5	197.3	177.9	164.9
65°	109.7	126.6	156.5	191.7	223.1	225.7	203.0	184.6	166.5	151.1	139.7
67.5°	87.4	98.4	119.5	149.1	172.6	181.0	167.1	153.0	138.7	126.8	116.8
70°	73.7	82.5	97.9	121.9	143.5	152.3	144.3	133.4	121.0	111.2	102.7
72.5°	59.7	68.4	79.7	97.3	115.8	125.4	122.6	114.7	104.6	96.6	88.5
75°	45.0	47.6	55.3	67.2	81.7	89.9	92.0	87.9	79.9	73.7	68.9
77.5°	33.3	34.9	38.5	44.8	54.2	61.6	64.6	64.2	58.6	55.1	50.6
80°	26.6	27.5	29.3	31.9	39.1	46.4	48.5	48.5	44.7	43.2	38.7
82.5°	20.2	20.9	21.9	23.4	26.8	33.2	35.5	36.0	33.5	31.6	28.1
85°	11.6	11.2	11.8	12.8	13.3	15.1	18.6	19.3	18.6	16.2	15.4
87.5°	10.1	9.1	7.9	6.8	6.4	6.0	6.6	7.1	6.8	6.7	6.9
90°	30.1	24.3	18.5	13.9	10.8	7.5	4.4	1.2	4.4	7.5	10.8
92.5°	35.3	33.8	32.5	30.6	28.3	25.9	23.6	21.2	23.6	25.9	28.3
95°	75.3	74.9	74.3	72.7	70.0	67.4	64.7	62.1	64.7	67.4	70.0
97.5°	126.5	125.5	124.5	122.8	120.5	118.1	115.8	113.4	115.8	118.1	120.5
100°	163.2	162.4	161.6	160.2	158.0	155.9	153.8	151.7	153.8	155.9	158.0
102.5°	201.9	201.0	199.9	198.6	196.9	195.2	193.5	191.8	193.5	195.2	196.9
105°	261.7	261.2	260.6	259.9	259.1	258.3	257.5	256.7	257.5	258.3	259.1
107.5°	327.5	327.5	327.5	326.9	325.7	324.6	323.4	322.2	323.4	324.6	325.7
110°	371.5	371.5	371.5	370.6	369.0	367.4	365.8	364.2	365.8	367.4	369.0



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.8	416.9	417.2	416.5	414.9	413.3	411.7	410.1	411.7	413.3	414.9
115°	483.5	484.1	484.6	484.1	482.5	480.9	479.3	477.7	479.3	480.9	482.5
117.5°	550.9	552.4	553.9	553.6	551.4	549.3	547.2	545.1	547.2	549.3	551.4
120°	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	592.1	594.2	596.4
122.5°	638.8	640.3	641.7	641.3	638.7	636.1	633.6	631.1	633.6	636.1	638.7
125°	703.9	704.6	705.4	704.6	702.2	699.8	697.4	695.1	697.4	699.8	702.2
127.5°	768.7	769.6	770.6	769.5	766.5	763.4	760.4	757.4	760.4	763.4	766.5
130°	810.8	811.3	811.8	810.4	806.9	803.5	800.0	796.5	800.0	803.5	806.9
132.5°	853.4	853.3	853.3	851.8	849.0	846.1	843.4	840.5	843.4	846.1	849.0
135°	913.8	913.2	912.7	910.9	908.0	905.1	902.2	899.3	902.2	905.1	908.0
137.5°	973.6	973.0	972.2	970.7	968.3	965.9	963.5	961.2	963.5	965.9	968.3
140°	1012.5	1011.1	1009.8	1008.0	1005.6	1003.2	1000.8	998.4	1000.8	1003.2	1005.6
142.5°	1049.6	1048.7	1047.8	1046.2	1043.8	1041.4	1039.0	1036.6	1039.0	1041.4	1043.8
145°	1103.9	1102.3	1100.7	1099.0	1097.1	1095.3	1093.4	1091.5	1093.4	1095.3	1097.1
147.5°	1153.2	1152.1	1151.1	1149.5	1147.2	1144.9	1142.7	1140.5	1142.7	1144.9	1147.2
150°	1183.8	1182.7	1181.6	1180.4	1178.8	1177.2	1175.5	1173.9	1175.5	1177.2	1178.8
152.5°	1213.9	1212.7	1211.4	1210.0	1208.3	1206.7	1205.1	1203.6	1205.1	1206.7	1208.3
155°	1253.5	1252.8	1252.0	1251.2	1250.4	1249.6	1248.8	1248.0	1248.8	1249.6	1250.4
157.5°	1289.6	1289.1	1288.6	1288.1	1287.6	1287.1	1286.5	1285.9	1286.5	1287.1	1287.6
160°	1311.9	1311.7	1311.5	1311.1	1310.5	1310.0	1309.5	1308.9	1309.5	1310.0	1310.5
162.5°	1331.1	1330.8	1330.5	1330.4	1330.2	1330.2	1330.1	1329.9	1330.1	1330.2	1330.2
165°	1356.7	1356.7	1356.7	1356.8	1357.1	1357.3	1357.6	1357.9	1357.6	1357.3	1357.1
167.5°	1377.6	1377.6	1377.7	1378.1	1378.9	1379.7	1380.5	1381.2	1380.5	1379.7	1378.9
170°	1389.5	1389.7	1390.0	1390.5	1391.3	1392.1	1392.9	1393.7	1392.9	1392.1	1391.3
172.5°	1398.0	1398.4	1398.6	1399.2	1399.9	1400.7	1401.5	1402.3	1401.5	1400.7	1399.9
175°	1407.9	1408.4	1409.0	1409.6	1410.4	1411.2	1412.0	1412.8	1412.0	1411.2	1410.4
177.5°	1413.2	1413.6	1414.0	1414.6	1415.2	1415.9	1416.5	1417.1	1416.5	1415.9	1415.2
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	839.3	837.7	834.6	829.9	827.0	822.0	818.7	820.6	821.1	820.6	820.1
5°	816.8	810.6	802.0	793.7	786.0	777.8	773.0	771.0	766.8	764.5	763.3
7.5°	789.5	778.8	766.7	752.3	740.0	727.1	720.6	717.3	708.8	704.3	700.2
10°	769.1	752.3	740.1	721.2	709.7	692.8	681.3	681.6	670.0	663.5	658.8
12.5°	746.7	728.2	708.0	690.9	674.9	661.4	647.5	641.8	629.5	623.3	610.5
15°	709.4	687.8	666.5	643.4	627.2	606.2	586.1	561.5	541.7	524.5	519.8
17.5°	668.7	642.0	620.6	593.5	565.6	530.3	507.0	492.7	480.8	471.7	465.0
20°	640.8	613.5	590.8	549.9	512.4	488.4	471.3	460.3	447.9	438.2	432.8
22.5°	611.4	583.0	552.0	506.4	477.1	457.9	442.6	430.0	421.6	414.0	409.2
25°	569.7	538.7	487.5	456.1	432.5	412.4	401.7	394.0	385.2	374.8	370.1
27.5°	525.8	476.3	439.6	416.3	393.7	380.6	371.1	359.6	351.6	347.0	342.1
30°	492.8	443.5	414.8	389.3	373.4	358.9	347.6	341.1	333.4	325.4	322.2
32.5°	456.1	416.7	389.2	368.0	351.8	339.5	330.6	320.0	314.5	309.6	302.8
35°	410.6	380.7	355.6	338.4	323.1	313.0	302.6	296.4	286.4	282.3	279.6
37.5°	372.0	346.1	327.3	309.3	297.1	286.0	279.6	269.7	265.4	259.6	254.0
40°	350.2	324.8	306.8	292.0	278.4	270.1	262.1	254.1	247.6	244.9	238.1
42.5°	328.0	307.3	289.2	273.1	264.0	255.2	245.1	239.2	232.4	228.1	223.9
45°	297.3	279.0	263.6	250.3	240.2	231.1	224.5	214.8	211.0	202.3	198.8
47.5°	270.3	253.3	238.6	225.9	216.1	210.2	200.7	193.0	186.9	181.6	177.1
50°	251.1	236.9	222.8	211.5	202.6	194.1	184.3	180.5	171.0	168.3	165.6
52.5°	233.6	220.1	207.2	196.1	187.3	179.0	170.3	165.3	158.9	156.2	154.3
55°	209.1	196.1	183.7	174.0	165.1	156.5	151.1	145.0	142.0	139.9	137.5
57.5°	184.5	172.9	163.3	153.4	144.5	137.7	131.5	127.8	124.7	122.0	119.1
60°	168.9	157.6	149.1	139.9	130.8	125.2	120.4	116.0	112.4	108.3	107.1
62.5°	152.3	142.5	134.7	125.7	117.7	112.6	108.1	103.9	99.7	93.6	92.0
65°	129.6	121.9	113.6	106.2	99.1	94.1	87.5	82.9	81.0	80.5	80.2
67.5°	109.0	101.7	94.6	87.1	80.6	75.9	72.6	71.9	70.7	70.3	69.5
70°	95.2	88.5	81.4	74.2	68.0	67.2	66.0	64.8	63.3	62.7	62.1
72.5°	82.9	75.9	68.8	63.1	60.4	59.3	58.1	57.0	56.0	55.4	55.1
75°	63.6	57.1	52.4	50.3	48.8	47.9	46.2	45.2	44.7	43.8	43.5
77.5°	45.8	42.1	39.9	38.7	37.1	36.1	35.2	34.2	33.6	33.4	33.0
80°	34.9	33.1	31.7	29.9	29.3	28.1	27.8	26.9	27.3	26.3	26.3
82.5°	27.1	24.9	23.6	22.8	22.2	21.2	20.9	20.5	20.6	20.0	20.0
85°	13.9	13.3	12.8	12.1	12.1	11.2	11.6	11.2	11.2	10.6	10.4
87.5°	7.3	7.9	8.6	9.8	11.0	11.9	11.8	11.5	11.3	11.2	11.0
90°	13.9	18.5	24.3	30.1	36.0	41.8	41.3	40.7	40.2	39.7	39.5
92.5°	30.6	32.5	33.8	35.3	36.6	37.9	38.1	38.2	38.3	38.4	38.5
95°	72.7	74.3	74.9	75.3	75.9	76.4	76.4	76.4	76.4	76.4	76.1
97.5°	122.8	124.5	125.5	126.5	127.5	128.5	128.5	128.5	128.5	128.5	128.5
100°	160.2	161.6	162.4	163.2	164.0	164.8	164.8	164.8	164.8	164.8	164.7
102.5°	198.6	199.9	201.0	201.9	203.0	204.0	204.2	204.4	204.6	204.9	204.8
105°	259.9	260.6	261.2	261.7	262.2	262.8	263.2	263.8	264.4	264.8	265.1
107.5°	326.9	327.5	327.5	327.5	327.5	327.5	327.6	327.9	328.1	328.3	327.8
110°	370.6	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.5	371.0



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	416.5	417.2	416.9	416.8	416.5	416.3	415.7	415.0	414.4	413.8	413.1
115°	484.1	484.6	484.1	483.5	483.0	482.5	482.2	482.0	481.6	481.4	480.9
117.5°	553.6	553.9	552.4	550.9	549.4	548.0	547.3	546.7	546.1	545.4	544.6
120°	598.5	598.5	596.4	594.2	592.1	589.9	589.9	589.9	589.9	589.9	589.5
122.5°	641.3	641.7	640.3	638.8	637.3	635.8	635.2	634.5	633.9	633.3	632.6
125°	704.6	705.4	704.6	703.9	703.1	702.2	701.4	700.6	699.8	699.0	698.5
127.5°	769.5	770.6	769.6	768.7	767.7	766.8	765.7	764.8	763.8	762.9	762.0
130°	810.4	811.8	811.3	810.8	810.2	809.7	809.2	808.7	808.1	807.6	806.8
132.5°	851.8	853.3	853.3	853.4	853.6	853.7	852.5	851.4	850.2	849.0	848.0
135°	910.9	912.7	913.2	913.8	914.3	914.8	914.6	914.3	914.0	913.8	913.2
137.5°	970.7	972.2	973.0	973.6	974.3	975.0	974.8	974.5	974.4	974.1	973.5
140°	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1	1015.1	1015.1	1015.1	1014.6
142.5°	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6	1051.9	1052.1	1052.3	1051.9
145°	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3	1107.6	1107.9	1108.1	1107.7
147.5°	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0	1156.5	1157.1	1157.7	1157.5
150°	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1
152.5°	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5
155°	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5	1257.8	1259.2	1260.4	1260.8
157.5°	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3	1294.1	1295.9	1297.8	1298.0
160°	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1	1315.7	1317.2	1318.8	1319.1
162.5°	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4	1335.2	1337.0	1338.8	1339.1
165°	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5	1360.4	1362.2	1364.1	1364.4
167.5°	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3	1381.2	1383.1	1384.9	1385.1
170°	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8	1392.7	1394.5	1396.4	1396.5
172.5°	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4	1401.2	1403.1	1404.9	1405.1
175°	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7	1410.6	1412.4	1414.3	1414.4
177.5°	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	817.5	818.0	817.3	817.8	817.3	818.0	817.5	820.1	820.6	821.1	820.6
5°	761.8	758.2	757.6	756.8	757.6	758.2	761.8	763.3	764.5	766.8	771.0
7.5°	695.1	694.6	693.2	691.0	693.2	694.6	695.1	700.2	704.3	708.8	717.3
10°	652.3	650.9	650.5	648.5	650.5	650.9	652.3	658.8	663.5	670.0	681.6
12.5°	602.1	592.6	591.6	586.5	591.6	592.6	602.1	610.5	623.3	629.5	641.8
15°	512.7	510.9	505.0	501.1	505.0	510.9	512.7	519.8	524.5	541.7	561.5
17.5°	461.5	455.7	453.9	453.1	453.9	455.7	461.5	465.0	471.7	480.8	492.7
20°	428.6	423.3	422.5	421.8	422.5	423.3	428.6	432.8	438.2	447.9	460.3
22.5°	405.9	400.4	398.1	396.3	398.1	400.4	405.9	409.2	414.0	421.6	430.0
25°	367.1	365.0	363.8	363.3	363.8	365.0	367.1	370.1	374.8	385.2	394.0
27.5°	336.8	332.2	331.3	329.8	331.3	332.2	336.8	342.1	347.0	351.6	359.6
30°	319.5	318.0	315.9	314.2	315.9	318.0	319.5	322.2	325.4	333.4	341.1
32.5°	299.1	297.9	296.0	295.2	296.0	297.9	299.1	302.8	309.6	314.5	320.0
35°	276.6	272.4	270.7	268.0	270.7	272.4	276.6	279.6	282.3	286.4	296.4
37.5°	252.8	250.6	248.1	249.0	248.1	250.6	252.8	254.0	259.6	265.4	269.7
40°	234.3	232.8	232.2	232.0	232.2	232.8	234.3	238.1	244.9	247.6	254.1
42.5°	219.6	215.6	214.0	214.0	214.0	215.6	219.6	223.9	228.1	232.4	239.2
45°	197.3	193.5	190.8	191.1	190.8	193.5	197.3	198.8	202.3	211.0	214.8
47.5°	174.5	174.4	172.7	173.3	172.7	174.4	174.5	177.1	181.6	186.9	193.0
50°	163.6	161.8	160.7	160.9	160.7	161.8	163.6	165.6	168.3	171.0	180.5
52.5°	153.2	151.6	150.7	151.9	150.7	151.6	153.2	154.3	156.2	158.9	165.3
55°	136.1	134.3	134.0	133.7	134.0	134.3	136.1	137.5	139.9	142.0	145.0
57.5°	117.0	115.8	114.0	113.3	114.0	115.8	117.0	119.1	122.0	124.7	127.8
60°	103.2	100.8	97.9	97.6	97.9	100.8	103.2	107.1	108.3	112.4	116.0
62.5°	90.7	90.2	89.7	89.6	89.7	90.2	90.7	92.0	93.6	99.7	103.9
65°	79.6	79.3	79.6	79.9	79.6	79.3	79.6	80.2	80.5	81.0	82.9
67.5°	69.3	68.8	68.3	68.5	68.3	68.8	69.3	69.5	70.3	70.7	71.9
70°	61.6	61.2	60.9	60.9	60.9	61.2	61.6	62.1	62.7	63.3	64.8
72.5°	53.9	53.9	53.6	53.4	53.6	53.9	53.9	55.1	55.4	56.0	57.0
75°	43.2	42.6	42.6	42.6	42.6	42.6	43.2	43.5	43.8	44.7	45.2
77.5°	32.9	32.6	32.3	32.1	32.3	32.6	32.9	33.0	33.4	33.6	34.2
80°	26.1	25.7	25.4	25.4	25.4	25.7	26.1	26.3	26.3	27.3	26.9
82.5°	19.9	19.6	19.5	19.3	19.5	19.6	19.9	20.0	20.0	20.6	20.5
85°	10.6	10.9	10.6	11.2	10.6	10.9	10.6	10.4	10.6	11.2	11.2
87.5°	11.0	10.9	11.2	10.9	11.2	10.9	11.0	11.0	11.2	11.3	11.5
90°	39.8	40.1	40.3	40.6	40.3	40.1	39.8	39.5	39.7	40.2	40.7
92.5°	38.5	38.6	38.7	38.7	38.7	38.6	38.5	38.5	38.4	38.3	38.2
95°	75.7	75.1	74.5	74.1	74.5	75.1	75.7	76.1	76.4	76.4	76.4
97.5°	128.4	128.3	128.3	128.3	128.3	128.3	128.4	128.5	128.5	128.5	128.5
100°	164.4	164.1	163.9	163.6	163.9	164.1	164.4	164.7	164.8	164.8	164.8
102.5°	204.5	204.3	204.0	203.7	204.0	204.3	204.5	204.8	204.9	204.6	204.4
105°	265.1	265.1	265.1	265.1	265.1	265.1	265.1	265.1	264.8	264.4	263.8
107.5°	326.6	325.3	324.2	322.9	324.2	325.3	326.6	327.8	328.3	328.1	327.9
110°	370.2	369.4	368.6	367.8	368.6	369.4	370.2	371.0	371.5	371.5	371.5



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	412.6	412.0	411.4	410.8	411.4	412.0	412.6	413.1	413.8	414.4	415.0
115°	480.1	479.3	478.5	477.7	478.5	479.3	480.1	480.9	481.4	481.6	482.0
117.5°	543.8	543.0	542.2	541.5	542.2	543.0	543.8	544.6	545.4	546.1	546.7
120°	588.7	588.0	587.2	586.4	587.2	588.0	588.7	589.5	589.9	589.9	589.9
122.5°	632.1	631.5	630.9	630.3	630.9	631.5	632.1	632.6	633.3	633.9	634.5
125°	698.2	698.0	697.8	697.4	697.8	698.0	698.2	698.5	699.0	699.8	700.6
127.5°	761.1	760.3	759.5	758.6	759.5	760.3	761.1	762.0	762.9	763.8	764.8
130°	805.7	804.7	803.6	802.6	803.6	804.7	805.7	806.8	807.6	808.1	808.7
132.5°	847.2	846.3	845.4	844.5	845.4	846.3	847.2	848.0	849.0	850.2	851.4
135°	912.4	911.6	910.9	910.1	910.9	911.6	912.4	913.2	913.8	914.0	914.3
137.5°	972.5	971.4	970.3	969.2	970.3	971.4	972.5	973.5	974.1	974.4	974.5
140°	1013.5	1012.5	1011.4	1010.3	1011.4	1012.5	1013.5	1014.6	1015.1	1015.1	1015.1
142.5°	1050.8	1049.7	1048.7	1047.6	1048.7	1049.7	1050.8	1051.9	1052.3	1052.1	1051.9
145°	1106.7	1105.6	1104.5	1103.5	1104.5	1105.6	1106.7	1107.7	1108.1	1107.9	1107.6
147.5°	1156.4	1155.4	1154.4	1153.4	1154.4	1155.4	1156.4	1157.5	1157.7	1157.1	1156.5
150°	1188.3	1187.5	1186.7	1185.9	1186.7	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5
152.5°	1219.5	1218.5	1217.5	1216.5	1217.5	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5
155°	1260.0	1259.2	1258.4	1257.6	1258.4	1259.2	1260.0	1260.8	1260.4	1259.2	1257.8
157.5°	1296.7	1295.5	1294.2	1292.9	1294.2	1295.5	1296.7	1298.0	1297.8	1295.9	1294.1
160°	1318.0	1317.0	1316.0	1314.9	1316.0	1317.0	1318.0	1319.1	1318.8	1317.2	1315.7
162.5°	1337.8	1336.6	1335.3	1334.0	1335.3	1336.6	1337.8	1339.1	1338.8	1337.0	1335.2
165°	1363.0	1361.8	1360.4	1359.1	1360.4	1361.8	1363.0	1364.4	1364.1	1362.2	1360.4
167.5°	1383.8	1382.4	1381.0	1379.6	1381.0	1382.4	1383.8	1385.1	1384.9	1383.1	1381.2
170°	1394.9	1393.3	1391.7	1390.1	1391.7	1393.3	1394.9	1396.5	1396.4	1394.5	1392.7
172.5°	1403.5	1401.9	1400.3	1398.8	1400.3	1401.9	1403.5	1405.1	1404.9	1403.1	1401.2
175°	1412.8	1411.2	1409.6	1408.0	1409.6	1411.2	1412.8	1414.4	1414.3	1412.4	1410.6
177.5°	1416.2	1414.9	1413.6	1412.3	1413.6	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	818.7	822.0	827.0	829.9	834.6	837.7	839.3	842.4	844.1	850.0	856.1
5°	773.0	777.8	786.0	793.7	802.0	810.6	816.8	823.9	830.4	841.6	853.5
7.5°	720.6	727.1	740.0	752.3	766.7	778.8	789.5	801.6	812.5	828.5	845.3
10°	681.3	692.8	709.7	721.2	740.1	752.3	769.1	782.4	797.6	818.9	837.8
12.5°	647.5	661.4	674.9	690.9	708.0	728.2	746.7	763.7	781.7	803.7	825.9
15°	586.1	606.2	627.2	643.4	666.5	687.8	709.4	732.5	754.4	780.7	809.7
17.5°	507.0	530.3	565.6	593.5	620.6	642.0	668.7	696.6	722.4	754.2	786.4
20°	471.3	488.4	512.4	549.9	590.8	613.5	640.8	671.5	701.1	735.7	770.3
22.5°	442.6	457.9	477.1	506.4	552.0	583.0	611.4	642.7	677.0	712.3	750.7
25°	401.7	412.4	432.5	456.1	487.5	538.7	569.7	601.1	638.4	676.3	720.0
27.5°	371.1	380.6	393.7	416.3	439.6	476.3	525.8	559.9	597.1	639.7	685.2
30°	347.6	358.9	373.4	389.3	414.8	443.5	492.8	532.5	569.2	613.0	661.5
32.5°	330.6	339.5	351.8	368.0	389.2	416.7	456.1	504.3	540.0	586.2	636.8
35°	302.6	313.0	323.1	338.4	355.6	380.7	410.6	462.1	497.6	543.1	594.1
37.5°	279.6	286.0	297.1	309.3	327.3	346.1	372.0	418.2	456.6	501.3	553.4
40°	262.1	270.1	278.4	292.0	306.8	324.8	350.2	384.6	428.6	472.5	523.3
42.5°	245.1	255.2	264.0	273.1	289.2	307.3	328.0	357.1	402.1	443.5	493.1
45°	224.5	231.1	240.2	250.3	263.6	279.0	297.3	322.7	365.9	401.7	448.2
47.5°	200.7	210.2	216.1	225.9	238.6	253.3	270.3	292.3	327.3	360.8	403.9
50°	184.3	194.1	202.6	211.5	222.8	236.9	251.1	272.4	300.6	335.8	376.0
52.5°	170.3	179.0	187.3	196.1	207.2	220.1	233.6	252.3	276.4	308.8	347.8
55°	151.1	156.5	165.1	174.0	183.7	196.1	209.1	224.8	245.6	272.7	304.4
57.5°	131.5	137.7	144.5	153.4	163.3	172.9	184.5	198.8	215.1	239.7	266.8
60°	120.4	125.2	130.8	139.9	149.1	157.6	168.9	180.8	196.1	217.5	240.5
62.5°	108.1	112.6	117.7	125.7	134.7	142.5	152.3	164.9	177.9	197.3	217.5
65°	87.5	94.1	99.1	106.2	113.6	121.9	129.6	139.7	151.1	166.5	184.6
67.5°	72.6	75.9	80.6	87.1	94.6	101.7	109.0	116.8	126.8	138.7	153.0
70°	66.0	67.2	68.0	74.2	81.4	88.5	95.2	102.7	111.2	121.0	133.4
72.5°	58.1	59.3	60.4	63.1	68.8	75.9	82.9	88.5	96.6	104.6	114.7
75°	46.2	47.9	48.8	50.3	52.4	57.1	63.6	68.9	73.7	79.9	87.9
77.5°	35.2	36.1	37.1	38.7	39.9	42.1	45.8	50.6	55.1	58.6	64.2
80°	27.8	28.1	29.3	29.9	31.7	33.1	34.9	38.7	43.2	44.7	48.5
82.5°	20.9	21.2	22.2	22.8	23.6	24.9	27.1	28.1	31.6	33.5	36.0
85°	11.6	11.2	12.1	12.1	12.8	13.3	13.9	15.4	16.2	18.6	19.3
87.5°	11.8	11.9	11.0	9.8	8.6	7.9	7.3	6.9	6.7	6.8	7.1
90°	41.3	41.8	36.0	30.1	24.3	18.5	13.9	10.8	7.5	4.4	1.2
92.5°	38.1	37.9	36.6	35.3	33.8	32.5	30.6	28.3	25.9	23.6	21.2
95°	76.4	76.4	75.9	75.3	74.9	74.3	72.7	70.0	67.4	64.7	62.1
97.5°	128.5	128.5	127.5	126.5	125.5	124.5	122.8	120.5	118.1	115.8	113.4
100°	164.8	164.8	164.0	163.2	162.4	161.6	160.2	158.0	155.9	153.8	151.7
102.5°	204.2	204.0	203.0	201.9	201.0	199.9	198.6	196.9	195.2	193.5	191.8
105°	263.2	262.8	262.2	261.7	261.2	260.6	259.9	259.1	258.3	257.5	256.7
107.5°	327.6	327.5	327.5	327.5	327.5	327.5	326.9	325.7	324.6	323.4	322.2
110°	371.5	371.5	371.5	371.5	371.5	371.5	370.6	369.0	367.4	365.8	364.2



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	415.7	416.3	416.5	416.8	416.9	417.2	416.5	414.9	413.3	411.7	410.1
115°	482.2	482.5	483.0	483.5	484.1	484.6	484.1	482.5	480.9	479.3	477.7
117.5°	547.3	548.0	549.4	550.9	552.4	553.9	553.6	551.4	549.3	547.2	545.1
120°	589.9	589.9	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9
122.5°	635.2	635.8	637.3	638.8	640.3	641.7	641.3	638.7	636.1	633.6	631.1
125°	701.4	702.2	703.1	703.9	704.6	705.4	704.6	702.2	699.8	697.4	695.1
127.5°	765.7	766.8	767.7	768.7	769.6	770.6	769.5	766.5	763.4	760.4	757.4
130°	809.2	809.7	810.2	810.8	811.3	811.8	810.4	806.9	803.5	800.0	796.5
132.5°	852.5	853.7	853.6	853.4	853.3	853.3	851.8	849.0	846.1	843.4	840.5
135°	914.6	914.8	914.3	913.8	913.2	912.7	910.9	908.0	905.1	902.2	899.3
137.5°	974.8	975.0	974.3	973.6	973.0	972.2	970.7	968.3	965.9	963.5	961.2
140°	1015.1	1015.1	1013.8	1012.5	1011.1	1009.8	1008.0	1005.6	1003.2	1000.8	998.4
142.5°	1051.6	1051.5	1050.5	1049.6	1048.7	1047.8	1046.2	1043.8	1041.4	1039.0	1036.6
145°	1107.3	1107.1	1105.5	1103.9	1102.3	1100.7	1099.0	1097.1	1095.3	1093.4	1091.5
147.5°	1156.0	1155.3	1154.3	1153.2	1152.1	1151.1	1149.5	1147.2	1144.9	1142.7	1140.5
150°	1186.7	1185.9	1184.9	1183.8	1182.7	1181.6	1180.4	1178.8	1177.2	1175.5	1173.9
152.5°	1217.5	1216.5	1215.2	1213.9	1212.7	1211.4	1210.0	1208.3	1206.7	1205.1	1203.6
155°	1256.5	1255.1	1254.3	1253.5	1252.8	1252.0	1251.2	1250.4	1249.6	1248.8	1248.0
157.5°	1292.3	1290.5	1290.1	1289.6	1289.1	1288.6	1288.1	1287.6	1287.1	1286.5	1285.9
160°	1314.1	1312.5	1312.2	1311.9	1311.7	1311.5	1311.1	1310.5	1310.0	1309.5	1308.9
162.5°	1333.4	1331.6	1331.3	1331.1	1330.8	1330.5	1330.4	1330.2	1330.2	1330.1	1329.9
165°	1358.5	1356.7	1356.7	1356.7	1356.7	1356.7	1356.8	1357.1	1357.3	1357.6	1357.9
167.5°	1379.3	1377.4	1377.5	1377.6	1377.6	1377.7	1378.1	1378.9	1379.7	1380.5	1381.2
170°	1390.8	1388.9	1389.2	1389.5	1389.7	1390.0	1390.5	1391.3	1392.1	1392.9	1393.7
172.5°	1399.4	1397.5	1397.8	1398.0	1398.4	1398.6	1399.2	1399.9	1400.7	1401.5	1402.3
175°	1408.7	1406.8	1407.4	1407.9	1408.4	1409.0	1409.6	1410.4	1411.2	1412.0	1412.8
177.5°	1413.6	1412.3	1412.8	1413.2	1413.6	1414.0	1414.6	1415.2	1415.9	1416.5	1417.1
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	856.3	857.1	861.8	864.0	868.2	869.9	871.7	871.2	871.2	872.2	878.8
5°	858.2	864.1	873.0	881.5	889.9	897.0	901.7	906.4	908.2	916.8	924.5
7.5°	855.2	866.0	880.7	893.7	909.4	921.7	931.8	941.0	947.3	959.8	972.6
10°	851.1	866.5	883.0	899.9	921.5	937.8	954.3	967.1	971.2	989.8	1000.5
12.5°	843.0	863.6	884.7	906.6	927.6	950.1	968.3	981.0	995.6	1012.3	1032.0
15°	831.0	854.7	882.2	910.3	940.5	967.7	987.2	1009.4	1025.3	1043.7	1060.8
17.5°	813.7	844.1	879.1	911.6	946.5	975.7	1002.7	1023.9	1035.1	1045.6	1048.2
20°	799.9	832.7	873.9	912.4	947.2	981.0	1007.6	1025.3	1028.3	1028.6	1012.9
22.5°	785.1	822.1	865.1	904.5	946.3	983.8	1004.5	1012.1	1000.4	980.3	950.0
25°	757.6	800.5	850.5	895.5	941.0	976.5	983.7	970.3	929.2	886.0	831.3
27.5°	727.9	776.1	829.7	879.7	928.3	950.3	934.9	886.9	812.9	748.5	670.5
30°	706.2	760.3	812.9	868.9	913.8	923.3	888.1	817.4	731.0	634.0	556.2
32.5°	681.3	738.0	795.9	853.7	891.4	882.1	823.9	736.9	635.6	540.3	466.7
35°	645.8	704.4	766.8	824.7	848.7	808.8	721.8	608.6	505.0	416.0	365.4
37.5°	604.8	668.6	733.5	786.7	785.1	718.4	600.0	483.0	396.0	343.3	307.3
40°	575.7	640.2	710.3	755.3	736.0	649.4	520.9	410.6	347.0	305.0	278.7
42.5°	547.8	612.5	682.1	717.9	684.4	577.9	450.0	363.5	311.0	278.3	256.9
45°	500.3	568.5	633.1	652.9	593.1	475.7	363.8	301.2	266.3	242.0	227.2
47.5°	453.8	521.0	579.9	580.3	499.4	385.8	307.0	260.6	230.8	212.1	201.3
50°	425.4	489.3	538.7	531.0	439.3	343.2	274.5	234.6	209.8	195.3	184.0
52.5°	393.5	455.4	498.2	476.3	388.4	302.0	245.4	211.9	191.3	178.7	168.7
55°	347.0	402.0	432.2	399.1	316.9	251.1	207.4	181.0	165.6	155.0	146.5
57.5°	301.4	346.7	365.8	327.2	260.9	208.3	175.4	155.7	140.4	132.8	128.3
60°	272.7	311.5	324.8	282.3	226.9	182.2	155.3	137.0	125.7	120.7	116.3
62.5°	244.6	276.2	281.8	242.7	197.8	159.5	136.4	120.9	113.4	108.6	104.4
65°	203.0	225.7	223.1	191.7	156.5	126.6	109.7	100.3	94.7	87.9	80.5
67.5°	167.1	181.0	172.6	149.1	119.5	98.4	87.4	80.2	73.3	66.8	65.1
70°	144.3	152.3	143.5	121.9	97.9	82.5	73.7	65.1	60.9	59.5	56.8
72.5°	122.6	125.4	115.8	97.3	79.7	68.4	59.7	54.9	52.7	51.4	49.7
75°	92.0	89.9	81.7	67.2	55.3	47.6	45.0	43.2	41.7	40.6	39.6
77.5°	64.6	61.6	54.2	44.8	38.5	34.9	33.3	32.3	31.6	31.0	30.1
80°	48.5	46.4	39.1	31.9	29.3	27.5	26.6	25.4	25.4	24.9	23.9
82.5°	35.5	33.2	26.8	23.4	21.9	20.9	20.2	19.5	19.3	19.4	18.8
85°	18.6	15.1	13.3	12.8	11.8	11.2	11.6	10.9	10.9	10.9	10.6
87.5°	6.6	6.0	6.4	6.8	7.9	9.1	10.1	11.2	12.6	12.3	12.4
90°	4.4	7.5	10.8	13.9	18.5	24.3	30.1	36.0	41.8	41.3	40.7
92.5°	23.6	25.9	28.3	30.6	32.5	33.8	35.3	36.6	37.9	38.1	38.2
95°	64.7	67.4	70.0	72.7	74.3	74.9	75.3	75.9	76.4	76.4	76.4
97.5°	115.8	118.1	120.5	122.8	124.5	125.5	126.5	127.5	128.5	128.5	128.5
100°	153.8	155.9	158.0	160.2	161.6	162.4	163.2	164.0	164.8	164.8	164.8
102.5°	193.5	195.2	196.9	198.6	199.9	201.0	201.9	203.0	204.0	204.2	204.4
105°	257.5	258.3	259.1	259.9	260.6	261.2	261.7	262.2	262.8	263.2	263.8
107.5°	323.4	324.6	325.7	326.9	327.5	327.5	327.5	327.5	327.5	327.6	327.9
110°	365.8	367.4	369.0	370.6	371.5	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	411.7	413.3	414.9	416.5	417.2	416.9	416.8	416.5	416.3	415.7	415.0
115°	479.3	480.9	482.5	484.1	484.6	484.1	483.5	483.0	482.5	482.2	482.0
117.5°	547.2	549.3	551.4	553.6	553.9	552.4	550.9	549.4	548.0	547.3	546.7
120°	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	589.9	589.9
122.5°	633.6	636.1	638.7	641.3	641.7	640.3	638.8	637.3	635.8	635.2	634.5
125°	697.4	699.8	702.2	704.6	705.4	704.6	703.9	703.1	702.2	701.4	700.6
127.5°	760.4	763.4	766.5	769.5	770.6	769.6	768.7	767.7	766.8	765.7	764.8
130°	800.0	803.5	806.9	810.4	811.8	811.3	810.8	810.2	809.7	809.2	808.7
132.5°	843.4	846.1	849.0	851.8	853.3	853.3	853.4	853.6	853.7	852.5	851.4
135°	902.2	905.1	908.0	910.9	912.7	913.2	913.8	914.3	914.8	914.6	914.3
137.5°	963.5	965.9	968.3	970.7	972.2	973.0	973.6	974.3	975.0	974.8	974.5
140°	1000.8	1003.2	1005.6	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1	1015.1
142.5°	1039.0	1041.4	1043.8	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6	1051.9
145°	1093.4	1095.3	1097.1	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3	1107.6
147.5°	1142.7	1144.9	1147.2	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0	1156.5
150°	1175.5	1177.2	1178.8	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7	1187.5
152.5°	1205.1	1206.7	1208.3	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5	1218.5
155°	1248.8	1249.6	1250.4	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5	1257.8
157.5°	1286.5	1287.1	1287.6	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3	1294.1
160°	1309.5	1310.0	1310.5	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1	1315.7
162.5°	1330.1	1330.2	1330.2	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4	1335.2
165°	1357.6	1357.3	1357.1	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5	1360.4
167.5°	1380.5	1379.7	1378.9	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3	1381.2
170°	1392.9	1392.1	1391.3	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8	1392.7
172.5°	1401.5	1400.7	1399.9	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4	1401.2
175°	1412.0	1411.2	1410.4	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7	1410.6
177.5°	1416.5	1415.9	1415.2	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6	1414.9
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	881.2	884.3	885.7	885.7	887.4	886.7	886.0
5°	931.8	937.5	938.7	944.0	947.8	946.7	947.2
7.5°	982.2	991.3	1000.2	1004.2	1005.0	1007.3	1008.2
10°	1013.2	1020.6	1034.5	1032.5	1042.8	1048.7	1038.9
12.5°	1043.1	1053.0	1062.7	1065.3	1071.2	1073.1	1069.2
15°	1070.0	1075.3	1075.9	1074.4	1076.3	1074.8	1069.1
17.5°	1044.8	1036.2	1018.7	1010.3	1003.8	994.1	990.2
20°	1003.1	977.7	948.2	936.3	922.4	895.2	901.7
22.5°	913.2	884.2	854.7	820.1	803.6	777.8	776.3
25°	773.3	723.3	668.3	629.8	607.4	581.6	570.4
27.5°	601.3	538.3	493.2	470.4	449.6	429.2	428.3
30°	488.1	440.8	405.9	386.3	373.7	365.0	366.9
32.5°	411.5	379.0	355.5	339.3	329.9	323.4	323.3
35°	336.4	314.2	299.0	292.3	285.5	280.7	281.1
37.5°	287.9	274.5	266.1	258.6	254.4	252.1	250.7
40°	263.0	252.1	245.6	241.1	237.6	234.3	233.7
42.5°	243.4	234.3	227.8	224.3	221.0	218.6	218.1
45°	215.9	208.6	202.6	198.8	197.3	195.3	195.3
47.5°	192.1	184.8	180.2	177.8	175.2	173.9	173.8
50°	176.0	170.4	166.3	164.8	162.7	161.8	161.5
52.5°	161.6	157.4	154.4	153.4	152.5	151.4	151.5
55°	142.0	139.7	138.5	137.5	136.1	134.3	135.5
57.5°	125.5	123.5	120.3	117.5	116.1	114.9	115.3
60°	113.9	109.7	105.6	102.3	101.5	98.8	98.8
62.5°	99.3	93.4	88.3	86.5	85.6	84.4	84.1
65°	76.3	74.0	72.8	71.6	71.0	71.0	70.4
67.5°	63.2	62.3	61.0	60.7	60.1	60.0	59.7
70°	55.9	54.7	54.1	53.9	53.2	53.6	52.7
72.5°	48.8	47.8	47.8	47.0	46.7	46.7	46.0
75°	38.4	38.4	38.2	37.9	37.3	37.0	37.3
77.5°	29.5	29.6	29.1	29.1	29.0	29.1	28.8
80°	23.7	23.9	23.7	23.4	23.1	23.4	23.1
82.5°	18.7	18.3	18.2	18.1	18.1	17.9	17.9
85°	10.6	10.9	10.6	10.4	10.4	10.4	10.6
87.5°	12.0	12.0	12.0	12.0	12.0	12.1	11.9
90°	40.2	39.7	39.5	39.8	40.1	40.3	40.6
92.5°	38.3	38.4	38.5	38.5	38.6	38.7	38.7
95°	76.4	76.4	76.1	75.7	75.1	74.5	74.1
97.5°	128.5	128.5	128.5	128.4	128.3	128.3	128.3
100°	164.8	164.8	164.7	164.4	164.1	163.9	163.6
102.5°	204.6	204.9	204.8	204.5	204.3	204.0	203.7
105°	264.4	264.8	265.1	265.1	265.1	265.1	265.1
107.5°	328.1	328.3	327.8	326.6	325.3	324.2	322.9
110°	371.5	371.5	371.0	370.2	369.4	368.6	367.8



TEST NUMBER: P331802-927

CATALOG NUMBER: S122RDIW-S485D1440U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	414.4	413.8	413.1	412.6	412.0	411.4	410.8
115°	481.6	481.4	480.9	480.1	479.3	478.5	477.7
117.5°	546.1	545.4	544.6	543.8	543.0	542.2	541.5
120°	589.9	589.9	589.5	588.7	588.0	587.2	586.4
122.5°	633.9	633.3	632.6	632.1	631.5	630.9	630.3
125°	699.8	699.0	698.5	698.2	698.0	697.8	697.4
127.5°	763.8	762.9	762.0	761.1	760.3	759.5	758.6
130°	808.1	807.6	806.8	805.7	804.7	803.6	802.6
132.5°	850.2	849.0	848.0	847.2	846.3	845.4	844.5
135°	914.0	913.8	913.2	912.4	911.6	910.9	910.1
137.5°	974.4	974.1	973.5	972.5	971.4	970.3	969.2
140°	1015.1	1015.1	1014.6	1013.5	1012.5	1011.4	1010.3
142.5°	1052.1	1052.3	1051.9	1050.8	1049.7	1048.7	1047.6
145°	1107.9	1108.1	1107.7	1106.7	1105.6	1104.5	1103.5
147.5°	1157.1	1157.7	1157.5	1156.4	1155.4	1154.4	1153.4
150°	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9
152.5°	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5
155°	1259.2	1260.4	1260.8	1260.0	1259.2	1258.4	1257.6
157.5°	1295.9	1297.8	1298.0	1296.7	1295.5	1294.2	1292.9
160°	1317.2	1318.8	1319.1	1318.0	1317.0	1316.0	1314.9
162.5°	1337.0	1338.8	1339.1	1337.8	1336.6	1335.3	1334.0
165°	1362.2	1364.1	1364.4	1363.0	1361.8	1360.4	1359.1
167.5°	1383.1	1384.9	1385.1	1383.8	1382.4	1381.0	1379.6
170°	1394.5	1396.4	1396.5	1394.9	1393.3	1391.7	1390.1
172.5°	1403.1	1404.9	1405.1	1403.5	1401.9	1400.3	1398.8
175°	1412.4	1414.3	1414.4	1412.8	1411.2	1409.6	1408.0
177.5°	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2

(END OF REPORT)