

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331791-927

Luminaire Tested: **S122RDIW-S485D710U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331791-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D710U927-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3592.5 lumens  
Efficiency: N/A  
Efficacy: 95.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331791-927

CATALOG NUMBER: S122RDIW-S485D710U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331791-927

CATALOG NUMBER: S122RDIW-S485D710U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		60	60	60		45	45	45	37
1	95	91	88	84	86	83	80	77	67	65	63		53	52	50		40	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53		47	45	43		36	34	33	28
3	80	71	64	58	72	64	58	54	53	48	45		42	39	36		32	30	28	24
4	73	63	55	49	66	57	51	46	47	42	39		38	34	32		29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33		34	30	27		26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29		31	27	24		24	21	19	16
7	57	45	38	32	52	42	35	30	35	30	26		28	24	22		22	19	17	15
8	53	41	34	29	48	38	31	27	32	27	23		26	22	19		20	17	16	13
9	49	38	30	26	45	35	28	24	29	24	21		24	20	17		19	16	14	12
10	46	35	28	23	42	32	26	21	27	22	19		22	18	16		17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10555	10555	10555
5°	10595	10423	10481
10°	10516	10252	10165
15°	10394	9949	9663
20°	10227	9514	9036
25°	10055	9021	8432
30°	9818	8516	7655
35°	9585	7965	6974
40°	9352	7396	6184
45°	9079	6754	5471
50°	8796	6106	4770
55°	8510	5413	4096
60°	8176	4682	3400
65°	7798	3931	3095
70°	7345	3238	2851
75°	6787	2951	2658
80°	5997	2641	2427
85°	4705	2075	2075



TEST NUMBER: P331791-927

CATALOG NUMBER: S122RDIW-S485D710U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.2	1.7
10°-20°	168.0	4.7
20°-30°	235.9	6.6
30°-40°	257.3	7.2
40°-50°	236.6	6.6
50°-60°	185.8	5.2
60°-70°	121.1	3.4
70°-80°	62.5	1.7
80°-90°	18.1	0.5
90°-100°	25.6	0.7
100°-110°	93.8	2.6
110°-120°	250.6	7.0
120°-130°	413.7	11.5
130°-140°	440.0	12.2
140°-150°	408.9	11.4
150°-160°	328.8	9.2
160°-170°	211.9	5.9
170°-180°	72.9	2.0
0°-30°	465.2	12.9
0°-40°	722.4	20.1
0°-60°	1144.8	31.9
0°-90°	1346.5	37.5
90°-120°	369.9	10.3
90°-150°	1632.5	45.4
90°-180°	2246.0	62.5
0°-180°	3592.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	654	654	654	654	654	
5°	654	650	643	648	647	62
15°	622	615	595	584	578	175
25°	564	544	506	483	473	259
35°	486	455	404	368	354	304
45°	398	357	296	255	240	307
55°	302	255	192	158	146	270
65°	204	156	103	84	81	202
75°	109	69	47	43	43	115
85°	25	14	11	11	11	30
90°	1	6	11	14	15	3
95°	36	19	22	24	24	44
105°	169	176	34	40	42	180
115°	319	329	342	97	46	314
125°	451	458	469	472	474	402
135°	558	567	572	577	576	431
145°	647	647	656	660	657	405
155°	713	708	714	717	713	328
165°	751	748	749	753	749	212
175°	768	764	765	769	764	73
180°	766	766	766	766	766	



TEST NUMBER: P331791-927

CATALOG NUMBER: S122RDIW-S485D710U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	656.1	655.6	655.1	654.5	654.0	653.2	652.0	650.9	649.7	648.6	649.6
5°	653.7	653.1	652.4	651.8	651.1	649.9	648.2	646.5	644.8	643.1	644.3
7.5°	647.0	646.2	645.4	644.5	643.7	642.3	640.3	638.3	636.4	634.4	634.7
10°	641.4	640.4	639.4	638.6	637.6	635.9	633.3	630.6	628.0	625.3	625.0
12.5°	634.2	633.1	631.9	630.8	629.7	627.5	624.1	620.8	617.3	614.0	613.3
15°	621.8	620.4	618.9	617.4	616.0	613.1	608.6	604.1	599.7	595.2	592.7
17.5°	606.6	604.4	602.1	599.9	597.7	593.7	588.0	582.3	576.6	570.8	567.8
20°	595.2	592.6	589.9	587.3	584.6	580.0	573.5	566.9	560.3	553.7	550.5
22.5°	582.9	580.0	576.9	574.0	571.1	565.9	558.5	551.0	543.7	536.2	532.0
25°	564.4	560.2	556.0	551.8	547.6	541.1	532.4	523.8	515.1	506.4	501.1
27.5°	542.2	537.6	533.0	528.5	523.9	516.7	506.9	497.1	487.4	477.5	471.3
30°	526.6	521.6	516.6	511.6	506.6	498.8	488.3	477.8	467.2	456.8	450.0
32.5°	511.4	505.6	499.7	493.9	488.1	479.7	469.1	458.3	447.6	436.9	429.2
35°	486.3	479.6	472.9	466.2	459.5	450.4	438.8	427.2	415.7	404.1	395.8
37.5°	461.2	453.8	446.5	439.1	431.8	421.9	409.6	397.3	384.9	372.6	363.5
40°	443.7	435.9	427.9	420.1	412.2	401.9	389.1	376.4	363.6	350.9	341.5
42.5°	425.7	417.4	409.1	400.8	392.5	381.8	368.6	355.4	342.2	329.1	319.4
45°	397.6	388.8	379.9	371.1	362.3	351.0	337.2	323.4	309.6	295.8	286.5
47.5°	370.1	360.8	351.5	342.1	332.8	321.0	306.7	292.5	278.2	264.0	254.7
50°	350.2	340.9	331.6	322.3	312.9	301.0	286.5	272.1	257.6	243.1	234.1
52.5°	330.8	321.1	311.3	301.6	291.8	279.9	265.7	251.6	237.4	223.3	214.5
55°	302.3	292.1	281.8	271.6	261.3	249.1	234.9	220.7	206.4	192.3	184.4
57.5°	273.1	262.6	252.1	241.5	231.0	219.0	205.3	191.6	178.0	164.4	157.1
60°	253.2	242.7	232.2	221.7	211.1	199.2	185.6	172.1	158.5	145.0	138.2
62.5°	233.8	223.3	212.8	202.2	191.7	180.1	167.2	154.2	141.3	128.4	122.0
65°	204.1	193.5	182.8	172.1	161.5	150.3	138.5	126.6	114.8	102.9	98.5
67.5°	175.5	164.9	154.3	143.8	133.2	122.6	111.9	101.3	90.6	80.0	78.0
70°	155.6	145.4	135.1	124.8	114.5	104.9	95.9	86.7	77.7	68.6	67.3
72.5°	136.7	126.8	117.0	107.2	97.4	88.8	81.5	74.2	66.9	59.7	58.5
75°	108.8	99.7	90.5	81.3	72.0	65.2	60.8	56.2	51.8	47.3	46.4
77.5°	81.5	73.4	65.4	57.3	49.3	44.1	42.0	39.8	37.6	35.5	34.9
80°	64.5	57.8	51.1	44.4	37.6	33.7	32.3	31.1	29.7	28.4	27.9
82.5°	48.9	43.6	38.4	33.2	28.0	24.9	24.0	23.1	22.2	21.3	21.0
85°	25.4	22.7	19.9	17.2	14.4	12.8	12.4	12.0	11.6	11.2	11.2
87.5°	7.7	7.1	6.6	5.9	5.4	5.2	5.4	5.6	5.8	6.0	6.0
90°	0.6	1.9	3.2	4.6	5.9	7.1	8.2	9.1	10.1	11.1	11.7
92.5°	11.2	11.1	10.9	10.9	10.7	10.9	11.4	11.9	12.4	12.8	13.2
95°	36.0	32.0	27.9	23.8	19.8	18.1	19.0	19.9	20.8	21.6	22.3
97.5°	71.5	60.0	48.6	37.2	25.7	21.0	23.0	25.0	26.9	28.9	29.5
100°	98.2	81.3	64.4	47.5	30.7	23.2	25.3	27.4	29.5	31.6	32.6
102.5°	127.5	123.9	120.3	116.7	113.1	102.6	85.1	67.6	50.0	32.5	33.7
105°	168.6	172.3	176.0	179.7	183.4	168.4	134.8	101.1	67.5	33.8	35.2
107.5°	215.5	218.5	221.5	224.4	227.4	208.7	168.4	128.1	87.7	47.4	45.9
110°	245.7	248.3	250.9	253.4	256.0	239.5	203.9	168.3	132.7	97.0	84.8



TEST NUMBER: P331791-927

CATALOG NUMBER: S122RDIW-S485D710U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	274.1	276.4	278.7	280.9	283.2	280.0	271.2	262.4	253.6	244.8	199.9
115°	318.9	321.0	323.1	325.2	327.3	329.9	333.0	336.0	339.1	342.1	285.1
117.5°	358.9	361.2	363.6	365.9	368.3	370.5	372.6	374.8	376.8	379.0	365.2
120°	388.2	390.1	391.9	393.7	395.6	397.6	399.8	402.0	404.3	406.5	408.0
122.5°	413.0	415.0	416.9	418.9	420.8	423.0	425.4	427.9	430.2	432.7	433.6
125°	450.8	452.5	454.1	455.7	457.2	459.2	461.6	463.9	466.3	468.6	469.4
127.5°	485.1	486.9	488.7	490.4	492.3	494.0	495.7	497.5	499.2	501.0	502.2
130°	506.8	508.8	510.8	512.8	514.8	516.4	517.8	519.1	520.5	521.9	523.2
132.5°	529.1	530.8	532.4	534.1	535.8	537.3	538.6	540.0	541.4	542.7	543.8
135°	557.9	559.8	561.8	563.8	565.8	567.4	568.5	569.6	570.7	571.8	573.0
137.5°	587.1	588.4	589.9	591.2	592.6	593.9	595.2	596.4	597.7	599.0	600.2
140°	606.2	607.1	608.1	609.1	610.1	611.2	612.6	613.9	615.3	616.7	617.8
142.5°	622.1	623.0	623.9	624.8	625.7	626.9	628.4	630.0	631.5	633.1	634.1
145°	647.2	647.1	647.0	646.8	646.7	647.7	649.7	651.9	653.9	656.1	657.0
147.5°	669.0	668.6	668.1	667.7	667.2	668.0	670.0	672.1	674.1	676.2	676.9
150°	683.3	682.4	681.5	680.6	679.8	680.3	682.3	684.3	686.3	688.2	689.0
152.5°	695.2	694.3	693.3	692.3	691.3	691.8	693.7	695.5	697.4	699.3	700.1
155°	712.6	711.5	710.4	709.3	708.2	708.4	709.9	711.3	712.8	714.3	715.0
157.5°	726.3	725.3	724.4	723.4	722.5	722.5	723.6	724.6	725.6	726.7	727.5
160°	734.3	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	735.0
162.5°	741.3	740.6	739.9	739.1	738.4	738.3	738.9	739.7	740.3	740.9	741.7
165°	750.9	750.1	749.4	748.7	747.9	747.7	748.1	748.5	748.8	749.2	750.1
167.5°	758.0	757.2	756.5	755.7	755.0	754.9	755.2	755.5	755.9	756.2	757.1
170°	762.0	761.2	760.5	759.8	759.0	758.8	759.0	759.3	759.5	759.8	760.7
172.5°	764.6	763.9	763.2	762.4	761.7	761.4	761.7	761.9	762.2	762.4	763.3
175°	768.1	767.2	766.4	765.5	764.6	764.3	764.5	764.9	765.1	765.3	766.2
177.5°	768.7	767.9	767.2	766.6	765.9	765.6	765.6	765.8	765.9	766.0	766.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331791-927

CATALOG NUMBER: S122RDIW-S485D710U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	650.6	651.7	652.8	653.2	653.0	652.8	652.5	652.4
5°	645.5	646.7	647.8	648.2	647.8	647.5	647.1	646.7
7.5°	635.0	635.3	635.7	635.6	634.9	634.1	633.5	632.8
10°	624.6	624.2	623.8	623.2	622.4	621.6	620.8	620.0
12.5°	612.6	611.9	611.2	610.1	608.8	607.5	606.2	604.9
15°	590.2	587.7	585.2	583.3	581.9	580.7	579.3	578.1
17.5°	564.8	561.9	558.9	556.3	554.1	551.8	549.5	547.2
20°	547.2	543.9	540.6	537.5	534.6	531.7	528.9	525.9
22.5°	527.8	523.6	519.4	516.1	514.0	511.8	509.7	507.5
25°	495.7	490.3	484.9	481.2	479.2	477.2	475.3	473.3
27.5°	465.0	458.7	452.4	447.7	444.6	441.5	438.3	435.2
30°	443.3	436.7	429.9	424.8	421.2	417.7	414.2	410.6
32.5°	421.5	413.9	406.2	400.8	397.4	394.1	390.7	387.4
35°	387.5	379.2	371.0	365.4	362.5	359.6	356.7	353.8
37.5°	354.3	345.2	336.1	329.9	326.6	323.3	320.0	316.6
40°	332.2	322.8	313.5	307.1	303.7	300.3	296.8	293.4
42.5°	309.7	300.1	290.5	284.0	280.7	277.3	274.0	270.7
45°	277.1	267.8	258.5	252.2	249.1	245.9	242.7	239.6
47.5°	245.4	236.1	226.9	220.8	217.9	215.1	212.1	209.3
50°	225.0	215.9	206.8	201.0	198.2	195.4	192.7	189.9
52.5°	205.7	197.0	188.2	182.6	180.1	177.5	174.9	172.4
55°	176.5	168.6	160.7	155.5	153.0	150.5	148.1	145.5
57.5°	149.9	142.7	135.5	130.8	128.7	126.6	124.5	122.3
60°	131.5	124.8	118.1	113.8	111.6	109.5	107.4	105.3
62.5°	115.6	109.2	102.8	99.0	97.8	96.5	95.2	94.0
65°	94.0	89.5	85.1	82.6	82.2	81.8	81.4	81.0
67.5°	75.9	73.8	71.8	70.6	70.1	69.7	69.3	68.8
70°	66.0	64.7	63.4	62.4	61.9	61.4	60.8	60.4
72.5°	57.4	56.3	55.2	54.5	54.2	53.9	53.6	53.2
75°	45.5	44.6	43.6	43.1	43.0	42.9	42.7	42.6
77.5°	34.5	33.9	33.4	33.0	32.8	32.6	32.4	32.2
80°	27.3	26.9	26.3	26.1	26.1	26.1	26.1	26.1
82.5°	20.7	20.4	20.0	19.9	19.9	19.9	19.9	19.9
85°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2
87.5°	6.0	6.0	6.1	6.1	6.2	6.2	6.3	6.3
90°	12.4	12.9	13.5	14.0	14.3	14.5	14.7	15.0
92.5°	13.5	13.9	14.2	14.4	14.5	14.7	14.8	15.0
95°	22.9	23.4	24.1	24.3	24.2	24.1	24.0	23.8
97.5°	29.9	30.4	30.9	31.2	31.4	31.5	31.7	31.8
100°	33.6	34.5	35.6	36.2	36.4	36.7	36.9	37.2
102.5°	35.1	36.4	37.6	38.4	38.8	39.1	39.5	39.8
105°	36.5	37.9	39.2	40.2	40.6	41.2	41.7	42.1
107.5°	44.6	43.3	41.8	41.4	41.9	42.4	42.9	43.3
110°	72.4	60.0	47.8	41.8	42.3	42.9	43.3	43.8





TEST NUMBER: P331791-927

CATALOG NUMBER: S122RDIW-S485D710U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	154.9	110.0	65.0	42.7	43.1	43.5	43.9	44.3
115°	228.1	171.0	113.9	81.0	72.1	63.2	54.3	45.5
117.5°	351.4	337.5	323.8	302.3	273.1	244.0	214.8	185.7
120°	409.5	410.9	412.4	404.8	388.2	371.5	354.9	338.3
122.5°	434.4	435.3	436.3	435.1	431.8	428.6	425.4	422.2
125°	470.3	471.2	472.1	472.7	473.0	473.4	473.8	474.1
127.5°	503.5	504.8	506.0	506.7	506.8	506.8	506.9	507.0
130°	524.6	525.9	527.3	527.9	527.8	527.7	527.5	527.4
132.5°	545.0	546.2	547.3	547.9	547.7	547.6	547.5	547.4
135°	574.3	575.4	576.7	577.2	576.9	576.7	576.5	576.2
137.5°	601.3	602.5	603.8	604.2	603.7	603.3	602.9	602.5
140°	618.9	620.0	621.2	621.4	620.8	620.1	619.5	618.9
142.5°	635.1	636.1	637.2	637.3	636.8	636.1	635.5	634.9
145°	657.7	658.6	659.5	659.7	659.0	658.4	657.7	657.2
147.5°	677.6	678.2	678.8	678.9	678.3	677.9	677.3	676.8
150°	689.7	690.5	691.2	691.3	690.6	690.0	689.4	688.8
152.5°	700.8	701.6	702.3	702.3	701.4	700.6	699.8	698.9
155°	715.7	716.5	717.2	717.1	716.1	715.2	714.2	713.2
157.5°	728.4	729.2	730.1	730.0	729.0	728.1	727.1	726.1
160°	735.7	736.5	737.2	737.1	736.3	735.4	734.6	733.7
162.5°	742.6	743.4	744.3	744.2	743.1	742.0	740.9	739.9
165°	751.0	751.8	752.7	752.7	751.8	751.0	750.1	749.2
167.5°	758.0	758.8	759.6	759.5	758.4	757.3	756.2	755.1
170°	761.5	762.3	763.2	763.1	762.0	760.9	759.8	758.7
172.5°	764.1	765.0	765.9	765.7	764.6	763.5	762.4	761.3
175°	767.1	767.9	768.7	768.6	767.3	766.1	764.9	763.7
177.5°	767.4	768.0	768.7	768.7	767.8	766.8	766.0	765.1
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4

(END OF REPORT)