

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331793-927

Luminaire Tested: **S122RDIW-S485D970U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331793-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S485D970U927-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4539.7 lumens  
Efficiency: N/A  
Efficacy: 100.4 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32					32			
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	36	35	35	28					28			
2	86	79	74	69	78	72	67	63	58	54	51	45	42	41	32	31	30	25					25			
3	79	70	63	58	71	64	58	53	51	47	44	40	37	35	29	28	26	21					21			
4	73	62	55	50	65	57	50	46	46	41	38	36	33	30	26	25	23	19					19			
5	67	56	48	43	60	51	44	39	41	37	33	32	29	27	24	22	20	17					17			
6	62	50	43	37	55	46	39	34	37	33	29	29	26	24	22	20	18	15					15			
7	57	45	38	33	51	42	35	30	34	29	26	27	24	21	20	18	16	14					14			
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	12					12			
9	49	38	31	26	45	35	28	24	29	24	21	23	20	17	18	15	14	11					11			
10	46	35	28	23	42	32	26	22	26	22	19	21	18	16	16	14	13	11					11			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13747	13747	13747	13747
5°	15352	13833	12266	13833
10°	17033	13736	10632	13736
15°	17870	13534	8376	13534
20°	15493	13235	7247	13235
25°	10162	12827	6472	12827
30°	6840	12333	5858	12333
35°	5541	11710	5282	11710
40°	4926	11030	4890	11030
45°	4459	10234	4364	10234
50°	4057	9445	4042	9445
55°	3814	8569	3764	8569
60°	3190	7766	3152	7766
65°	2690	7053	3053	7053
70°	2488	6297	2875	6297
75°	2327	5483	2658	5483
80°	2148	4510	2362	4510
85°	1964	3575	2075	3575



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.7	1.8
10°-20°	224.9	5.0
20°-30°	289.8	6.4
30°-40°	275.4	6.1
40°-50°	235.9	5.2
50°-60°	179.7	4.0
60°-70°	113.6	2.5
70°-80°	56.7	1.2
80°-90°	17.3	0.4
90°-100°	34.9	0.8
100°-110°	128.0	2.8
110°-120°	342.1	7.5
120°-130°	564.7	12.4
130°-140°	600.5	13.2
140°-150°	558.1	12.3
150°-160°	448.7	9.9
160°-170°	289.2	6.4
170°-180°	99.5	2.2
0°-30°	595.4	13.1
0°-40°	870.8	19.2
0°-60°	1286.4	28.3
0°-90°	1474.0	32.5
90°-120°	504.9	11.1
90°-150°	2228.2	49.1
90°-180°	3066.0	67.5
0°-180°	4539.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	851	851	851	851	851	
5°	947	854	757	854	947	93
15°	1069	810	501	810	1069	288
25°	570	720	363	720	570	271
35°	281	594	268	594	281	180
45°	195	448	191	448	195	151
55°	136	304	134	304	136	119
65°	70	185	80	185	70	72
75°	37	88	43	88	37	40
85°	11	19	11	19	11	12
90°	20	1	20	1	20	9
95°	33	49	33	49	33	30
105°	58	230	58	230	58	60
115°	62	435	62	435	62	155
125°	647	615	647	615	647	560
135°	786	762	786	762	786	606
145°	897	883	897	883	897	561
155°	973	973	973	973	973	449
165°	1023	1025	1023	1025	1023	289
175°	1042	1048	1042	1048	1042	99
180°	1046	1046	1046	1046	1046	



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	886.0	886.7	887.4	885.7	885.7	884.3	881.2	878.8	872.2	871.2	871.2
5°	947.2	946.7	947.8	944.0	938.7	937.5	931.8	924.5	916.8	908.2	906.4
7.5°	1008.2	1007.3	1005.0	1004.2	1000.2	991.3	982.2	972.6	959.8	947.3	941.0
10°	1038.9	1048.7	1042.8	1032.5	1034.5	1020.6	1013.2	1000.5	989.8	971.2	967.1
12.5°	1069.2	1073.1	1071.2	1065.3	1062.7	1053.0	1043.1	1032.0	1012.3	995.6	981.0
15°	1069.1	1074.8	1076.3	1074.4	1075.9	1075.3	1070.0	1060.8	1043.7	1025.3	1009.4
17.5°	990.2	994.1	1003.8	1010.3	1018.7	1036.2	1044.8	1048.2	1045.6	1035.1	1023.9
20°	901.7	895.2	922.4	936.3	948.2	977.7	1003.1	1012.9	1028.6	1028.3	1025.3
22.5°	776.3	777.8	803.6	820.1	854.7	884.2	913.2	950.0	980.3	1000.4	1012.1
25°	570.4	581.6	607.4	629.8	668.3	723.3	773.3	831.3	886.0	929.2	970.3
27.5°	428.3	429.2	449.6	470.4	493.2	538.3	601.3	670.5	748.5	812.9	886.9
30°	366.9	365.0	373.7	386.3	405.9	440.8	488.1	556.2	634.0	731.0	817.4
32.5°	323.3	323.4	329.9	339.3	355.5	379.0	411.5	466.7	540.3	635.6	736.9
35°	281.1	280.7	285.5	292.3	299.0	314.2	336.4	365.4	416.0	505.0	608.6
37.5°	250.7	252.1	254.4	258.6	266.1	274.5	287.9	307.3	343.3	396.0	483.0
40°	233.7	234.3	237.6	241.1	245.6	252.1	263.0	278.7	305.0	347.0	410.6
42.5°	218.1	218.6	221.0	224.3	227.8	234.3	243.4	256.9	278.3	311.0	363.5
45°	195.3	195.3	197.3	198.8	202.6	208.6	215.9	227.2	242.0	266.3	301.2
47.5°	173.8	173.9	175.2	177.8	180.2	184.8	192.1	201.3	212.1	230.8	260.6
50°	161.5	161.8	162.7	164.8	166.3	170.4	176.0	184.0	195.3	209.8	234.6
52.5°	151.5	151.4	152.5	153.4	154.4	157.4	161.6	168.7	178.7	191.3	211.9
55°	135.5	134.3	136.1	137.5	138.5	139.7	142.0	146.5	155.0	165.6	181.0
57.5°	115.3	114.9	116.1	117.5	120.3	123.5	125.5	128.3	132.8	140.4	155.7
60°	98.8	98.8	101.5	102.3	105.6	109.7	113.9	116.3	120.7	125.7	137.0
62.5°	84.1	84.4	85.6	86.5	88.3	93.4	99.3	104.4	108.6	113.4	120.9
65°	70.4	71.0	71.0	71.6	72.8	74.0	76.3	80.5	87.9	94.7	100.3
67.5°	59.7	60.0	60.1	60.7	61.0	62.3	63.2	65.1	66.8	73.3	80.2
70°	52.7	53.6	53.2	53.9	54.1	54.7	55.9	56.8	59.5	60.9	65.1
72.5°	46.0	46.7	46.7	47.0	47.8	47.8	48.8	49.7	51.4	52.7	54.9
75°	37.3	37.0	37.3	37.9	38.2	38.4	38.4	39.6	40.6	41.7	43.2
77.5°	28.8	29.1	29.0	29.1	29.1	29.6	29.5	30.1	31.0	31.6	32.3
80°	23.1	23.4	23.1	23.4	23.7	23.9	23.7	23.9	24.9	25.4	25.4
82.5°	17.9	17.9	18.1	18.1	18.2	18.3	18.7	18.8	19.4	19.3	19.5
85°	10.6	10.4	10.4	10.4	10.6	10.9	10.6	10.6	10.9	10.9	10.9
87.5°	7.8	8.1	8.0	7.9	7.8	7.8	7.5	7.6	7.2	7.3	6.8
90°	20.4	20.1	19.7	19.4	19.1	18.5	17.7	16.8	16.0	15.1	13.8
92.5°	20.4	20.2	20.0	19.8	19.6	19.3	18.9	18.5	18.0	17.6	16.9
95°	32.6	32.7	32.9	33.0	33.2	32.9	32.1	31.2	30.3	29.5	28.4
97.5°	43.4	43.3	43.0	42.9	42.6	42.2	41.5	40.9	40.2	39.5	36.8
100°	50.7	50.4	50.1	49.7	49.4	48.6	47.2	45.9	44.5	43.2	40.3
102.5°	54.3	53.9	53.4	52.9	52.4	51.3	49.6	47.8	46.1	44.4	68.3
105°	57.5	56.9	56.2	55.5	54.8	53.6	51.7	49.9	48.0	46.2	92.1
107.5°	59.2	58.5	57.8	57.2	56.5	57.1	59.0	60.8	62.7	64.6	119.7
110°	59.8	59.1	58.5	57.8	57.1	65.2	82.0	98.8	115.7	132.5	181.1



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	60.4	59.9	59.3	58.8	58.2	88.6	150.0	211.4	272.7	334.1	346.1
115°	62.1	74.1	86.3	98.4	110.5	155.5	233.4	311.2	389.1	467.1	462.9
117.5°	253.4	293.3	333.0	372.8	412.6	442.0	460.8	479.6	498.4	517.3	514.4
120°	461.8	484.4	507.2	529.9	552.5	562.9	560.9	558.9	556.9	554.8	551.8
122.5°	576.2	580.6	585.0	589.4	593.8	595.4	594.2	593.0	591.8	590.6	587.2
125°	647.2	646.7	646.2	645.7	645.2	644.4	643.2	642.0	640.8	639.6	636.4
127.5°	692.0	691.9	691.8	691.7	691.6	690.7	689.0	687.3	685.6	683.8	681.4
130°	719.9	720.0	720.2	720.3	720.6	719.7	717.9	716.0	714.2	712.3	710.4
132.5°	747.1	747.3	747.4	747.6	747.8	747.1	745.5	743.9	742.4	740.8	738.9
135°	786.5	786.8	787.1	787.5	787.8	787.1	785.4	783.8	782.1	780.5	778.9
137.5°	822.4	822.9	823.5	824.1	824.7	824.1	822.4	820.8	819.2	817.5	815.8
140°	844.8	845.6	846.4	847.3	848.1	847.8	846.3	844.8	843.3	841.8	839.9
142.5°	866.6	867.4	868.2	869.1	869.9	869.7	868.3	866.9	865.5	864.1	862.1
145°	897.0	897.9	898.7	899.5	900.4	900.2	899.0	897.9	896.7	895.5	892.6
147.5°	923.8	924.5	925.2	925.9	926.6	926.5	925.7	924.8	923.9	923.1	920.2
150°	940.2	941.0	941.8	942.7	943.5	943.4	942.4	941.4	940.4	939.4	936.7
152.5°	954.1	955.2	956.3	957.4	958.5	958.5	957.5	956.6	955.5	954.5	952.0
155°	973.4	974.8	976.1	977.5	978.8	979.0	977.9	977.0	976.0	974.9	973.0
157.5°	991.2	992.4	993.8	995.1	996.4	996.5	995.4	994.2	993.1	991.9	990.5
160°	1001.5	1002.7	1003.8	1005.0	1006.2	1006.2	1005.2	1004.2	1003.2	1002.2	1001.2
162.5°	1010.0	1011.4	1012.8	1014.2	1015.7	1015.9	1014.7	1013.6	1012.4	1011.3	1010.4
165°	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4	1026.2	1025.0	1023.8	1022.6	1022.2
167.5°	1030.7	1032.2	1033.7	1035.2	1036.7	1036.9	1035.7	1034.5	1033.3	1032.2	1031.7
170°	1035.5	1037.0	1038.6	1040.1	1041.6	1041.7	1040.5	1039.4	1038.2	1037.0	1036.7
172.5°	1039.2	1040.7	1042.2	1043.7	1045.2	1045.4	1044.2	1043.0	1041.9	1040.7	1040.3
175°	1042.4	1044.0	1045.7	1047.3	1049.1	1049.3	1048.1	1046.9	1045.8	1044.6	1044.3
177.5°	1044.3	1045.5	1046.7	1047.9	1049.2	1049.2	1048.3	1047.4	1046.5	1045.5	1045.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	871.7	869.9	868.2	864.0	861.8	857.1	856.3	856.1	850.0	844.1	842.4
5°	901.7	897.0	889.9	881.5	873.0	864.1	858.2	853.5	841.6	830.4	823.9
7.5°	931.8	921.7	909.4	893.7	880.7	866.0	855.2	845.3	828.5	812.5	801.6
10°	954.3	937.8	921.5	899.9	883.0	866.5	851.1	837.8	818.9	797.6	782.4
12.5°	968.3	950.1	927.6	906.6	884.7	863.6	843.0	825.9	803.7	781.7	763.7
15°	987.2	967.7	940.5	910.3	882.2	854.7	831.0	809.7	780.7	754.4	732.5
17.5°	1002.7	975.7	946.5	911.6	879.1	844.1	813.7	786.4	754.2	722.4	696.6
20°	1007.6	981.0	947.2	912.4	873.9	832.7	799.9	770.3	735.7	701.1	671.5
22.5°	1004.5	983.8	946.3	904.5	865.1	822.1	785.1	750.7	712.3	677.0	642.7
25°	983.7	976.5	941.0	895.5	850.5	800.5	757.6	720.0	676.3	638.4	601.1
27.5°	934.9	950.3	928.3	879.7	829.7	776.1	727.9	685.2	639.7	597.1	559.9
30°	888.1	923.3	913.8	868.9	812.9	760.3	706.2	661.5	613.0	569.2	532.5
32.5°	823.9	882.1	891.4	853.7	795.9	738.0	681.3	636.8	586.2	540.0	504.3
35°	721.8	808.8	848.7	824.7	766.8	704.4	645.8	594.1	543.1	497.6	462.1
37.5°	600.0	718.4	785.1	786.7	733.5	668.6	604.8	553.4	501.3	456.6	418.2
40°	520.9	649.4	736.0	755.3	710.3	640.2	575.7	523.3	472.5	428.6	384.6
42.5°	450.0	577.9	684.4	717.9	682.1	612.5	547.8	493.1	443.5	402.1	357.1
45°	363.8	475.7	593.1	652.9	633.1	568.5	500.3	448.2	401.7	365.9	322.7
47.5°	307.0	385.8	499.4	580.3	579.9	521.0	453.8	403.9	360.8	327.3	292.3
50°	274.5	343.2	439.3	531.0	538.7	489.3	425.4	376.0	335.8	300.6	272.4
52.5°	245.4	302.0	388.4	476.3	498.2	455.4	393.5	347.8	308.8	276.4	252.3
55°	207.4	251.1	316.9	399.1	432.2	402.0	347.0	304.4	272.7	245.6	224.8
57.5°	175.4	208.3	260.9	327.2	365.8	346.7	301.4	266.8	239.7	215.1	198.8
60°	155.3	182.2	226.9	282.3	324.8	311.5	272.7	240.5	217.5	196.1	180.8
62.5°	136.4	159.5	197.8	242.7	281.8	276.2	244.6	217.5	197.3	177.9	164.9
65°	109.7	126.6	156.5	191.7	223.1	225.7	203.0	184.6	166.5	151.1	139.7
67.5°	87.4	98.4	119.5	149.1	172.6	181.0	167.1	153.0	138.7	126.8	116.8
70°	73.7	82.5	97.9	121.9	143.5	152.3	144.3	133.4	121.0	111.2	102.7
72.5°	59.7	68.4	79.7	97.3	115.8	125.4	122.6	114.7	104.6	96.6	88.5
75°	45.0	47.6	55.3	67.2	81.7	89.9	92.0	87.9	79.9	73.7	68.9
77.5°	33.3	34.9	38.5	44.8	54.2	61.6	64.6	64.2	58.6	55.1	50.6
80°	26.6	27.5	29.3	31.9	39.1	46.4	48.5	48.5	44.7	43.2	38.7
82.5°	20.2	20.9	21.9	23.4	26.8	33.2	35.5	36.0	33.5	31.6	28.1
85°	11.6	11.2	11.8	12.8	13.3	15.1	18.6	19.3	18.6	16.2	15.4
87.5°	6.5	6.5	6.2	5.6	5.5	5.4	6.2	7.1	6.4	6.1	6.0
90°	12.4	11.1	9.7	8.2	6.3	4.4	2.6	0.8	2.6	4.4	6.3
92.5°	16.2	15.5	14.9	14.7	14.8	15.0	15.1	15.3	15.1	15.0	14.8
95°	27.2	26.0	24.8	27.0	32.6	38.1	43.6	49.2	43.6	38.1	32.6
97.5°	34.1	31.4	28.6	35.1	50.7	66.4	82.0	97.7	82.0	66.4	50.7
100°	37.4	34.5	31.7	41.8	64.9	87.9	110.9	134.0	110.9	87.9	64.9
102.5°	92.2	116.1	140.1	154.4	159.3	164.2	169.1	174.0	169.1	164.2	159.3
105°	138.0	183.9	229.9	250.3	245.3	240.2	235.2	230.1	235.2	240.2	245.3
107.5°	174.8	229.9	284.9	310.5	306.3	302.3	298.3	294.1	298.3	302.3	306.3
110°	229.7	278.3	326.9	349.4	345.9	342.4	338.9	335.3	338.9	342.4	345.9





TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	358.1	370.2	382.1	386.6	383.5	380.3	377.2	374.1	377.2	380.3	383.5
115°	458.6	454.4	450.2	446.7	443.9	441.0	438.1	435.2	438.1	441.0	443.9
117.5°	511.5	508.7	505.7	502.7	499.5	496.3	493.1	489.9	493.1	496.3	499.5
120°	548.8	545.7	542.7	540.0	537.4	534.9	532.4	529.9	532.4	534.9	537.4
122.5°	584.0	580.7	577.4	574.4	571.7	569.1	566.4	563.8	566.4	569.1	571.7
125°	633.3	630.0	626.9	624.2	621.9	619.8	617.6	615.4	617.6	619.8	621.9
127.5°	679.1	676.7	674.3	671.8	669.5	667.0	664.6	662.2	664.6	667.0	669.5
130°	708.6	706.7	704.9	702.6	699.9	697.3	694.6	691.9	694.6	697.3	699.9
132.5°	737.0	735.2	733.3	731.3	729.0	726.7	724.5	722.2	724.5	726.7	729.0
135°	777.4	775.9	774.4	772.3	769.6	766.9	764.2	761.5	764.2	766.9	769.6
137.5°	814.0	812.4	810.6	808.8	807.0	805.1	803.2	801.3	803.2	805.1	807.0
140°	838.0	836.1	834.3	832.7	831.4	830.0	828.7	827.4	828.7	830.0	831.4
142.5°	859.9	857.8	855.6	854.0	852.8	851.6	850.3	849.1	850.3	851.6	852.8
145°	889.8	886.9	884.1	882.7	882.9	883.0	883.2	883.4	883.2	883.0	882.9
147.5°	917.3	914.6	911.7	910.6	911.2	911.9	912.5	913.2	912.5	911.9	911.2
150°	934.0	931.3	928.6	927.9	929.1	930.2	931.4	932.6	931.4	930.2	929.1
152.5°	949.4	946.8	944.3	943.6	945.0	946.3	947.6	949.0	947.6	946.3	945.0
155°	970.9	968.9	966.9	966.6	968.1	969.6	971.1	972.7	971.1	969.6	968.1
157.5°	989.1	987.7	986.3	986.2	987.5	988.7	990.1	991.3	990.1	988.7	987.5
160°	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2	1001.2	1000.2	999.2
162.5°	1009.6	1008.7	1007.8	1007.9	1008.8	1009.9	1010.9	1011.9	1010.9	1009.9	1008.8
165°	1021.6	1021.1	1020.6	1020.9	1021.9	1022.9	1023.9	1024.9	1023.9	1022.9	1021.9
167.5°	1031.3	1030.8	1030.3	1030.5	1031.6	1032.6	1033.6	1034.6	1033.6	1032.6	1031.6
170°	1036.3	1036.0	1035.7	1036.0	1037.0	1038.1	1039.0	1040.1	1039.0	1038.1	1037.0
172.5°	1040.0	1039.7	1039.3	1039.7	1040.7	1041.6	1042.7	1043.7	1042.7	1041.6	1040.7
175°	1043.9	1043.6	1043.2	1043.7	1044.9	1046.0	1047.2	1048.4	1047.2	1046.0	1044.9
177.5°	1045.2	1045.1	1045.0	1045.4	1046.3	1047.3	1048.2	1049.2	1048.2	1047.3	1046.3
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	839.3	837.7	834.6	829.9	827.0	822.0	818.7	820.6	821.1	820.6	820.1
5°	816.8	810.6	802.0	793.7	786.0	777.8	773.0	771.0	766.8	764.5	763.3
7.5°	789.5	778.8	766.7	752.3	740.0	727.1	720.6	717.3	708.8	704.3	700.2
10°	769.1	752.3	740.1	721.2	709.7	692.8	681.3	681.6	670.0	663.5	658.8
12.5°	746.7	728.2	708.0	690.9	674.9	661.4	647.5	641.8	629.5	623.3	610.5
15°	709.4	687.8	666.5	643.4	627.2	606.2	586.1	561.5	541.7	524.5	519.8
17.5°	668.7	642.0	620.6	593.5	565.6	530.3	507.0	492.7	480.8	471.7	465.0
20°	640.8	613.5	590.8	549.9	512.4	488.4	471.3	460.3	447.9	438.2	432.8
22.5°	611.4	583.0	552.0	506.4	477.1	457.9	442.6	430.0	421.6	414.0	409.2
25°	569.7	538.7	487.5	456.1	432.5	412.4	401.7	394.0	385.2	374.8	370.1
27.5°	525.8	476.3	439.6	416.3	393.7	380.6	371.1	359.6	351.6	347.0	342.1
30°	492.8	443.5	414.8	389.3	373.4	358.9	347.6	341.1	333.4	325.4	322.2
32.5°	456.1	416.7	389.2	368.0	351.8	339.5	330.6	320.0	314.5	309.6	302.8
35°	410.6	380.7	355.6	338.4	323.1	313.0	302.6	296.4	286.4	282.3	279.6
37.5°	372.0	346.1	327.3	309.3	297.1	286.0	279.6	269.7	265.4	259.6	254.0
40°	350.2	324.8	306.8	292.0	278.4	270.1	262.1	254.1	247.6	244.9	238.1
42.5°	328.0	307.3	289.2	273.1	264.0	255.2	245.1	239.2	232.4	228.1	223.9
45°	297.3	279.0	263.6	250.3	240.2	231.1	224.5	214.8	211.0	202.3	198.8
47.5°	270.3	253.3	238.6	225.9	216.1	210.2	200.7	193.0	186.9	181.6	177.1
50°	251.1	236.9	222.8	211.5	202.6	194.1	184.3	180.5	171.0	168.3	165.6
52.5°	233.6	220.1	207.2	196.1	187.3	179.0	170.3	165.3	158.9	156.2	154.3
55°	209.1	196.1	183.7	174.0	165.1	156.5	151.1	145.0	142.0	139.9	137.5
57.5°	184.5	172.9	163.3	153.4	144.5	137.7	131.5	127.8	124.7	122.0	119.1
60°	168.9	157.6	149.1	139.9	130.8	125.2	120.4	116.0	112.4	108.3	107.1
62.5°	152.3	142.5	134.7	125.7	117.7	112.6	108.1	103.9	99.7	93.6	92.0
65°	129.6	121.9	113.6	106.2	99.1	94.1	87.5	82.9	81.0	80.5	80.2
67.5°	109.0	101.7	94.6	87.1	80.6	75.9	72.6	71.9	70.7	70.3	69.5
70°	95.2	88.5	81.4	74.2	68.0	67.2	66.0	64.8	63.3	62.7	62.1
72.5°	82.9	75.9	68.8	63.1	60.4	59.3	58.1	57.0	56.0	55.4	55.1
75°	63.6	57.1	52.4	50.3	48.8	47.9	46.2	45.2	44.7	43.8	43.5
77.5°	45.8	42.1	39.9	38.7	37.1	36.1	35.2	34.2	33.6	33.4	33.0
80°	34.9	33.1	31.7	29.9	29.3	28.1	27.8	26.9	27.3	26.3	26.3
82.5°	27.1	24.9	23.6	22.8	22.2	21.2	20.9	20.5	20.6	20.0	20.0
85°	13.9	13.3	12.8	12.1	12.1	11.2	11.6	11.2	11.2	10.6	10.4
87.5°	6.1	6.2	6.0	6.3	6.6	6.6	6.7	6.7	6.8	7.1	6.9
90°	8.2	9.7	11.1	12.4	13.8	15.1	16.0	16.8	17.7	18.5	19.1
92.5°	14.7	14.9	15.5	16.2	16.9	17.6	18.0	18.5	18.9	19.3	19.6
95°	27.0	24.8	26.0	27.2	28.4	29.5	30.3	31.2	32.1	32.9	33.2
97.5°	35.1	28.6	31.4	34.1	36.8	39.5	40.2	40.9	41.5	42.2	42.6
100°	41.8	31.7	34.5	37.4	40.3	43.2	44.5	45.9	47.2	48.6	49.4
102.5°	154.4	140.1	116.1	92.2	68.3	44.4	46.1	47.8	49.6	51.3	52.4
105°	250.3	229.9	183.9	138.0	92.1	46.2	48.0	49.9	51.7	53.6	54.8
107.5°	310.5	284.9	229.9	174.8	119.7	64.6	62.7	60.8	59.0	57.1	56.5
110°	349.4	326.9	278.3	229.7	181.1	132.5	115.7	98.8	82.0	65.2	57.1



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	386.6	382.1	370.2	358.1	346.1	334.1	272.7	211.4	150.0	88.6	58.2
115°	446.7	450.2	454.4	458.6	462.9	467.1	389.1	311.2	233.4	155.5	110.5
117.5°	502.7	505.7	508.7	511.5	514.4	517.3	498.4	479.6	460.8	442.0	412.6
120°	540.0	542.7	545.7	548.8	551.8	554.8	556.9	558.9	560.9	562.9	552.5
122.5°	574.4	577.4	580.7	584.0	587.2	590.6	591.8	593.0	594.2	595.4	593.8
125°	624.2	626.9	630.0	633.3	636.4	639.6	640.8	642.0	643.2	644.4	645.2
127.5°	671.8	674.3	676.7	679.1	681.4	683.8	685.6	687.3	689.0	690.7	691.6
130°	702.6	704.9	706.7	708.6	710.4	712.3	714.2	716.0	717.9	719.7	720.6
132.5°	731.3	733.3	735.2	737.0	738.9	740.8	742.4	743.9	745.5	747.1	747.8
135°	772.3	774.4	775.9	777.4	778.9	780.5	782.1	783.8	785.4	787.1	787.8
137.5°	808.8	810.6	812.4	814.0	815.8	817.5	819.2	820.8	822.4	824.1	824.7
140°	832.7	834.3	836.1	838.0	839.9	841.8	843.3	844.8	846.3	847.8	848.1
142.5°	854.0	855.6	857.8	859.9	862.1	864.1	865.5	866.9	868.3	869.7	869.9
145°	882.7	884.1	886.9	889.8	892.6	895.5	896.7	897.9	899.0	900.2	900.4
147.5°	910.6	911.7	914.6	917.3	920.2	923.1	923.9	924.8	925.7	926.5	926.6
150°	927.9	928.6	931.3	934.0	936.7	939.4	940.4	941.4	942.4	943.4	943.5
152.5°	943.6	944.3	946.8	949.4	952.0	954.5	955.5	956.6	957.5	958.5	958.5
155°	966.6	966.9	968.9	970.9	973.0	974.9	976.0	977.0	977.9	979.0	978.8
157.5°	986.2	986.3	987.7	989.1	990.5	991.9	993.1	994.2	995.4	996.5	996.4
160°	998.1	998.1	999.2	1000.2	1001.2	1002.2	1003.2	1004.2	1005.2	1006.2	1006.2
162.5°	1007.9	1007.8	1008.7	1009.6	1010.4	1011.3	1012.4	1013.6	1014.7	1015.9	1015.7
165°	1020.9	1020.6	1021.1	1021.6	1022.2	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4
167.5°	1030.5	1030.3	1030.8	1031.3	1031.7	1032.2	1033.3	1034.5	1035.7	1036.9	1036.7
170°	1036.0	1035.7	1036.0	1036.3	1036.7	1037.0	1038.2	1039.4	1040.5	1041.7	1041.6
172.5°	1039.7	1039.3	1039.7	1040.0	1040.3	1040.7	1041.9	1043.0	1044.2	1045.4	1045.2
175°	1043.7	1043.2	1043.6	1043.9	1044.3	1044.6	1045.8	1046.9	1048.1	1049.3	1049.1
177.5°	1045.4	1045.0	1045.1	1045.2	1045.4	1045.5	1046.5	1047.4	1048.3	1049.2	1049.2
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	817.5	818.0	817.3	817.8	817.3	818.0	817.5	820.1	820.6	821.1	820.6
5°	761.8	758.2	757.6	756.8	757.6	758.2	761.8	763.3	764.5	766.8	771.0
7.5°	695.1	694.6	693.2	691.0	693.2	694.6	695.1	700.2	704.3	708.8	717.3
10°	652.3	650.9	650.5	648.5	650.5	650.9	652.3	658.8	663.5	670.0	681.6
12.5°	602.1	592.6	591.6	586.5	591.6	592.6	602.1	610.5	623.3	629.5	641.8
15°	512.7	510.9	505.0	501.1	505.0	510.9	512.7	519.8	524.5	541.7	561.5
17.5°	461.5	455.7	453.9	453.1	453.9	455.7	461.5	465.0	471.7	480.8	492.7
20°	428.6	423.3	422.5	421.8	422.5	423.3	428.6	432.8	438.2	447.9	460.3
22.5°	405.9	400.4	398.1	396.3	398.1	400.4	405.9	409.2	414.0	421.6	430.0
25°	367.1	365.0	363.8	363.3	363.8	365.0	367.1	370.1	374.8	385.2	394.0
27.5°	336.8	332.2	331.3	329.8	331.3	332.2	336.8	342.1	347.0	351.6	359.6
30°	319.5	318.0	315.9	314.2	315.9	318.0	319.5	322.2	325.4	333.4	341.1
32.5°	299.1	297.9	296.0	295.2	296.0	297.9	299.1	302.8	309.6	314.5	320.0
35°	276.6	272.4	270.7	268.0	270.7	272.4	276.6	279.6	282.3	286.4	296.4
37.5°	252.8	250.6	248.1	249.0	248.1	250.6	252.8	254.0	259.6	265.4	269.7
40°	234.3	232.8	232.2	232.0	232.2	232.8	234.3	238.1	244.9	247.6	254.1
42.5°	219.6	215.6	214.0	214.0	214.0	215.6	219.6	223.9	228.1	232.4	239.2
45°	197.3	193.5	190.8	191.1	190.8	193.5	197.3	198.8	202.3	211.0	214.8
47.5°	174.5	174.4	172.7	173.3	172.7	174.4	174.5	177.1	181.6	186.9	193.0
50°	163.6	161.8	160.7	160.9	160.7	161.8	163.6	165.6	168.3	171.0	180.5
52.5°	153.2	151.6	150.7	151.9	150.7	151.6	153.2	154.3	156.2	158.9	165.3
55°	136.1	134.3	134.0	133.7	134.0	134.3	136.1	137.5	139.9	142.0	145.0
57.5°	117.0	115.8	114.0	113.3	114.0	115.8	117.0	119.1	122.0	124.7	127.8
60°	103.2	100.8	97.9	97.6	97.9	100.8	103.2	107.1	108.3	112.4	116.0
62.5°	90.7	90.2	89.7	89.6	89.7	90.2	90.7	92.0	93.6	99.7	103.9
65°	79.6	79.3	79.6	79.9	79.6	79.3	79.6	80.2	80.5	81.0	82.9
67.5°	69.3	68.8	68.3	68.5	68.3	68.8	69.3	69.5	70.3	70.7	71.9
70°	61.6	61.2	60.9	60.9	60.9	61.2	61.6	62.1	62.7	63.3	64.8
72.5°	53.9	53.9	53.6	53.4	53.6	53.9	53.9	55.1	55.4	56.0	57.0
75°	43.2	42.6	42.6	42.6	42.6	42.6	43.2	43.5	43.8	44.7	45.2
77.5°	32.9	32.6	32.3	32.1	32.3	32.6	32.9	33.0	33.4	33.6	34.2
80°	26.1	25.7	25.4	25.4	25.4	25.7	26.1	26.3	26.3	27.3	26.9
82.5°	19.9	19.6	19.5	19.3	19.5	19.6	19.9	20.0	20.0	20.6	20.5
85°	10.6	10.9	10.6	11.2	10.6	10.9	10.6	10.4	10.6	11.2	11.2
87.5°	7.0	6.8	7.1	6.9	7.1	6.8	7.0	6.9	7.1	6.8	6.7
90°	19.4	19.7	20.1	20.4	20.1	19.7	19.4	19.1	18.5	17.7	16.8
92.5°	19.8	20.0	20.2	20.4	20.2	20.0	19.8	19.6	19.3	18.9	18.5
95°	33.0	32.9	32.7	32.6	32.7	32.9	33.0	33.2	32.9	32.1	31.2
97.5°	42.9	43.0	43.3	43.4	43.3	43.0	42.9	42.6	42.2	41.5	40.9
100°	49.7	50.1	50.4	50.7	50.4	50.1	49.7	49.4	48.6	47.2	45.9
102.5°	52.9	53.4	53.9	54.3	53.9	53.4	52.9	52.4	51.3	49.6	47.8
105°	55.5	56.2	56.9	57.5	56.9	56.2	55.5	54.8	53.6	51.7	49.9
107.5°	57.2	57.8	58.5	59.2	58.5	57.8	57.2	56.5	57.1	59.0	60.8
110°	57.8	58.5	59.1	59.8	59.1	58.5	57.8	57.1	65.2	82.0	98.8



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	58.8	59.3	59.9	60.4	59.9	59.3	58.8	58.2	88.6	150.0	211.4
115°	98.4	86.3	74.1	62.1	74.1	86.3	98.4	110.5	155.5	233.4	311.2
117.5°	372.8	333.0	293.3	253.4	293.3	333.0	372.8	412.6	442.0	460.8	479.6
120°	529.9	507.2	484.4	461.8	484.4	507.2	529.9	552.5	562.9	560.9	558.9
122.5°	589.4	585.0	580.6	576.2	580.6	585.0	589.4	593.8	595.4	594.2	593.0
125°	645.7	646.2	646.7	647.2	646.7	646.2	645.7	645.2	644.4	643.2	642.0
127.5°	691.7	691.8	691.9	692.0	691.9	691.8	691.7	691.6	690.7	689.0	687.3
130°	720.3	720.2	720.0	719.9	720.0	720.2	720.3	720.6	719.7	717.9	716.0
132.5°	747.6	747.4	747.3	747.1	747.3	747.4	747.6	747.8	747.1	745.5	743.9
135°	787.5	787.1	786.8	786.5	786.8	787.1	787.5	787.8	787.1	785.4	783.8
137.5°	824.1	823.5	822.9	822.4	822.9	823.5	824.1	824.7	824.1	822.4	820.8
140°	847.3	846.4	845.6	844.8	845.6	846.4	847.3	848.1	847.8	846.3	844.8
142.5°	869.1	868.2	867.4	866.6	867.4	868.2	869.1	869.9	869.7	868.3	866.9
145°	899.5	898.7	897.9	897.0	897.9	898.7	899.5	900.4	900.2	899.0	897.9
147.5°	925.9	925.2	924.5	923.8	924.5	925.2	925.9	926.6	926.5	925.7	924.8
150°	942.7	941.8	941.0	940.2	941.0	941.8	942.7	943.5	943.4	942.4	941.4
152.5°	957.4	956.3	955.2	954.1	955.2	956.3	957.4	958.5	958.5	957.5	956.6
155°	977.5	976.1	974.8	973.4	974.8	976.1	977.5	978.8	979.0	977.9	977.0
157.5°	995.1	993.8	992.4	991.2	992.4	993.8	995.1	996.4	996.5	995.4	994.2
160°	1005.0	1003.8	1002.7	1001.5	1002.7	1003.8	1005.0	1006.2	1006.2	1005.2	1004.2
162.5°	1014.2	1012.8	1011.4	1010.0	1011.4	1012.8	1014.2	1015.7	1015.9	1014.7	1013.6
165°	1026.2	1025.0	1023.8	1022.6	1023.8	1025.0	1026.2	1027.4	1027.4	1026.2	1025.0
167.5°	1035.2	1033.7	1032.2	1030.7	1032.2	1033.7	1035.2	1036.7	1036.9	1035.7	1034.5
170°	1040.1	1038.6	1037.0	1035.5	1037.0	1038.6	1040.1	1041.6	1041.7	1040.5	1039.4
172.5°	1043.7	1042.2	1040.7	1039.2	1040.7	1042.2	1043.7	1045.2	1045.4	1044.2	1043.0
175°	1047.3	1045.7	1044.0	1042.4	1044.0	1045.7	1047.3	1049.1	1049.3	1048.1	1046.9
177.5°	1047.9	1046.7	1045.5	1044.3	1045.5	1046.7	1047.9	1049.2	1049.2	1048.3	1047.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	818.7	822.0	827.0	829.9	834.6	837.7	839.3	842.4	844.1	850.0	856.1
5°	773.0	777.8	786.0	793.7	802.0	810.6	816.8	823.9	830.4	841.6	853.5
7.5°	720.6	727.1	740.0	752.3	766.7	778.8	789.5	801.6	812.5	828.5	845.3
10°	681.3	692.8	709.7	721.2	740.1	752.3	769.1	782.4	797.6	818.9	837.8
12.5°	647.5	661.4	674.9	690.9	708.0	728.2	746.7	763.7	781.7	803.7	825.9
15°	586.1	606.2	627.2	643.4	666.5	687.8	709.4	732.5	754.4	780.7	809.7
17.5°	507.0	530.3	565.6	593.5	620.6	642.0	668.7	696.6	722.4	754.2	786.4
20°	471.3	488.4	512.4	549.9	590.8	613.5	640.8	671.5	701.1	735.7	770.3
22.5°	442.6	457.9	477.1	506.4	552.0	583.0	611.4	642.7	677.0	712.3	750.7
25°	401.7	412.4	432.5	456.1	487.5	538.7	569.7	601.1	638.4	676.3	720.0
27.5°	371.1	380.6	393.7	416.3	439.6	476.3	525.8	559.9	597.1	639.7	685.2
30°	347.6	358.9	373.4	389.3	414.8	443.5	492.8	532.5	569.2	613.0	661.5
32.5°	330.6	339.5	351.8	368.0	389.2	416.7	456.1	504.3	540.0	586.2	636.8
35°	302.6	313.0	323.1	338.4	355.6	380.7	410.6	462.1	497.6	543.1	594.1
37.5°	279.6	286.0	297.1	309.3	327.3	346.1	372.0	418.2	456.6	501.3	553.4
40°	262.1	270.1	278.4	292.0	306.8	324.8	350.2	384.6	428.6	472.5	523.3
42.5°	245.1	255.2	264.0	273.1	289.2	307.3	328.0	357.1	402.1	443.5	493.1
45°	224.5	231.1	240.2	250.3	263.6	279.0	297.3	322.7	365.9	401.7	448.2
47.5°	200.7	210.2	216.1	225.9	238.6	253.3	270.3	292.3	327.3	360.8	403.9
50°	184.3	194.1	202.6	211.5	222.8	236.9	251.1	272.4	300.6	335.8	376.0
52.5°	170.3	179.0	187.3	196.1	207.2	220.1	233.6	252.3	276.4	308.8	347.8
55°	151.1	156.5	165.1	174.0	183.7	196.1	209.1	224.8	245.6	272.7	304.4
57.5°	131.5	137.7	144.5	153.4	163.3	172.9	184.5	198.8	215.1	239.7	266.8
60°	120.4	125.2	130.8	139.9	149.1	157.6	168.9	180.8	196.1	217.5	240.5
62.5°	108.1	112.6	117.7	125.7	134.7	142.5	152.3	164.9	177.9	197.3	217.5
65°	87.5	94.1	99.1	106.2	113.6	121.9	129.6	139.7	151.1	166.5	184.6
67.5°	72.6	75.9	80.6	87.1	94.6	101.7	109.0	116.8	126.8	138.7	153.0
70°	66.0	67.2	68.0	74.2	81.4	88.5	95.2	102.7	111.2	121.0	133.4
72.5°	58.1	59.3	60.4	63.1	68.8	75.9	82.9	88.5	96.6	104.6	114.7
75°	46.2	47.9	48.8	50.3	52.4	57.1	63.6	68.9	73.7	79.9	87.9
77.5°	35.2	36.1	37.1	38.7	39.9	42.1	45.8	50.6	55.1	58.6	64.2
80°	27.8	28.1	29.3	29.9	31.7	33.1	34.9	38.7	43.2	44.7	48.5
82.5°	20.9	21.2	22.2	22.8	23.6	24.9	27.1	28.1	31.6	33.5	36.0
85°	11.6	11.2	12.1	12.1	12.8	13.3	13.9	15.4	16.2	18.6	19.3
87.5°	6.7	6.6	6.6	6.3	6.0	6.2	6.1	6.0	6.1	6.4	7.1
90°	16.0	15.1	13.8	12.4	11.1	9.7	8.2	6.3	4.4	2.6	0.8
92.5°	18.0	17.6	16.9	16.2	15.5	14.9	14.7	14.8	15.0	15.1	15.3
95°	30.3	29.5	28.4	27.2	26.0	24.8	27.0	32.6	38.1	43.6	49.2
97.5°	40.2	39.5	36.8	34.1	31.4	28.6	35.1	50.7	66.4	82.0	97.7
100°	44.5	43.2	40.3	37.4	34.5	31.7	41.8	64.9	87.9	110.9	134.0
102.5°	46.1	44.4	68.3	92.2	116.1	140.1	154.4	159.3	164.2	169.1	174.0
105°	48.0	46.2	92.1	138.0	183.9	229.9	250.3	245.3	240.2	235.2	230.1
107.5°	62.7	64.6	119.7	174.8	229.9	284.9	310.5	306.3	302.3	298.3	294.1
110°	115.7	132.5	181.1	229.7	278.3	326.9	349.4	345.9	342.4	338.9	335.3



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	272.7	334.1	346.1	358.1	370.2	382.1	386.6	383.5	380.3	377.2	374.1
115°	389.1	467.1	462.9	458.6	454.4	450.2	446.7	443.9	441.0	438.1	435.2
117.5°	498.4	517.3	514.4	511.5	508.7	505.7	502.7	499.5	496.3	493.1	489.9
120°	556.9	554.8	551.8	548.8	545.7	542.7	540.0	537.4	534.9	532.4	529.9
122.5°	591.8	590.6	587.2	584.0	580.7	577.4	574.4	571.7	569.1	566.4	563.8
125°	640.8	639.6	636.4	633.3	630.0	626.9	624.2	621.9	619.8	617.6	615.4
127.5°	685.6	683.8	681.4	679.1	676.7	674.3	671.8	669.5	667.0	664.6	662.2
130°	714.2	712.3	710.4	708.6	706.7	704.9	702.6	699.9	697.3	694.6	691.9
132.5°	742.4	740.8	738.9	737.0	735.2	733.3	731.3	729.0	726.7	724.5	722.2
135°	782.1	780.5	778.9	777.4	775.9	774.4	772.3	769.6	766.9	764.2	761.5
137.5°	819.2	817.5	815.8	814.0	812.4	810.6	808.8	807.0	805.1	803.2	801.3
140°	843.3	841.8	839.9	838.0	836.1	834.3	832.7	831.4	830.0	828.7	827.4
142.5°	865.5	864.1	862.1	859.9	857.8	855.6	854.0	852.8	851.6	850.3	849.1
145°	896.7	895.5	892.6	889.8	886.9	884.1	882.7	882.9	883.0	883.2	883.4
147.5°	923.9	923.1	920.2	917.3	914.6	911.7	910.6	911.2	911.9	912.5	913.2
150°	940.4	939.4	936.7	934.0	931.3	928.6	927.9	929.1	930.2	931.4	932.6
152.5°	955.5	954.5	952.0	949.4	946.8	944.3	943.6	945.0	946.3	947.6	949.0
155°	976.0	974.9	973.0	970.9	968.9	966.9	966.6	968.1	969.6	971.1	972.7
157.5°	993.1	991.9	990.5	989.1	987.7	986.3	986.2	987.5	988.7	990.1	991.3
160°	1003.2	1002.2	1001.2	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2
162.5°	1012.4	1011.3	1010.4	1009.6	1008.7	1007.8	1007.9	1008.8	1009.9	1010.9	1011.9
165°	1023.8	1022.6	1022.2	1021.6	1021.1	1020.6	1020.9	1021.9	1022.9	1023.9	1024.9
167.5°	1033.3	1032.2	1031.7	1031.3	1030.8	1030.3	1030.5	1031.6	1032.6	1033.6	1034.6
170°	1038.2	1037.0	1036.7	1036.3	1036.0	1035.7	1036.0	1037.0	1038.1	1039.0	1040.1
172.5°	1041.9	1040.7	1040.3	1040.0	1039.7	1039.3	1039.7	1040.7	1041.6	1042.7	1043.7
175°	1045.8	1044.6	1044.3	1043.9	1043.6	1043.2	1043.7	1044.9	1046.0	1047.2	1048.4
177.5°	1046.5	1045.5	1045.4	1045.2	1045.1	1045.0	1045.4	1046.3	1047.3	1048.2	1049.2
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	856.3	857.1	861.8	864.0	868.2	869.9	871.7	871.2	871.2	872.2	878.8
5°	858.2	864.1	873.0	881.5	889.9	897.0	901.7	906.4	908.2	916.8	924.5
7.5°	855.2	866.0	880.7	893.7	909.4	921.7	931.8	941.0	947.3	959.8	972.6
10°	851.1	866.5	883.0	899.9	921.5	937.8	954.3	967.1	971.2	989.8	1000.5
12.5°	843.0	863.6	884.7	906.6	927.6	950.1	968.3	981.0	995.6	1012.3	1032.0
15°	831.0	854.7	882.2	910.3	940.5	967.7	987.2	1009.4	1025.3	1043.7	1060.8
17.5°	813.7	844.1	879.1	911.6	946.5	975.7	1002.7	1023.9	1035.1	1045.6	1048.2
20°	799.9	832.7	873.9	912.4	947.2	981.0	1007.6	1025.3	1028.3	1028.6	1012.9
22.5°	785.1	822.1	865.1	904.5	946.3	983.8	1004.5	1012.1	1000.4	980.3	950.0
25°	757.6	800.5	850.5	895.5	941.0	976.5	983.7	970.3	929.2	886.0	831.3
27.5°	727.9	776.1	829.7	879.7	928.3	950.3	934.9	886.9	812.9	748.5	670.5
30°	706.2	760.3	812.9	868.9	913.8	923.3	888.1	817.4	731.0	634.0	556.2
32.5°	681.3	738.0	795.9	853.7	891.4	882.1	823.9	736.9	635.6	540.3	466.7
35°	645.8	704.4	766.8	824.7	848.7	808.8	721.8	608.6	505.0	416.0	365.4
37.5°	604.8	668.6	733.5	786.7	785.1	718.4	600.0	483.0	396.0	343.3	307.3
40°	575.7	640.2	710.3	755.3	736.0	649.4	520.9	410.6	347.0	305.0	278.7
42.5°	547.8	612.5	682.1	717.9	684.4	577.9	450.0	363.5	311.0	278.3	256.9
45°	500.3	568.5	633.1	652.9	593.1	475.7	363.8	301.2	266.3	242.0	227.2
47.5°	453.8	521.0	579.9	580.3	499.4	385.8	307.0	260.6	230.8	212.1	201.3
50°	425.4	489.3	538.7	531.0	439.3	343.2	274.5	234.6	209.8	195.3	184.0
52.5°	393.5	455.4	498.2	476.3	388.4	302.0	245.4	211.9	191.3	178.7	168.7
55°	347.0	402.0	432.2	399.1	316.9	251.1	207.4	181.0	165.6	155.0	146.5
57.5°	301.4	346.7	365.8	327.2	260.9	208.3	175.4	155.7	140.4	132.8	128.3
60°	272.7	311.5	324.8	282.3	226.9	182.2	155.3	137.0	125.7	120.7	116.3
62.5°	244.6	276.2	281.8	242.7	197.8	159.5	136.4	120.9	113.4	108.6	104.4
65°	203.0	225.7	223.1	191.7	156.5	126.6	109.7	100.3	94.7	87.9	80.5
67.5°	167.1	181.0	172.6	149.1	119.5	98.4	87.4	80.2	73.3	66.8	65.1
70°	144.3	152.3	143.5	121.9	97.9	82.5	73.7	65.1	60.9	59.5	56.8
72.5°	122.6	125.4	115.8	97.3	79.7	68.4	59.7	54.9	52.7	51.4	49.7
75°	92.0	89.9	81.7	67.2	55.3	47.6	45.0	43.2	41.7	40.6	39.6
77.5°	64.6	61.6	54.2	44.8	38.5	34.9	33.3	32.3	31.6	31.0	30.1
80°	48.5	46.4	39.1	31.9	29.3	27.5	26.6	25.4	25.4	24.9	23.9
82.5°	35.5	33.2	26.8	23.4	21.9	20.9	20.2	19.5	19.3	19.4	18.8
85°	18.6	15.1	13.3	12.8	11.8	11.2	11.6	10.9	10.9	10.9	10.6
87.5°	6.2	5.4	5.5	5.6	6.2	6.5	6.5	6.8	7.3	7.2	7.6
90°	2.6	4.4	6.3	8.2	9.7	11.1	12.4	13.8	15.1	16.0	16.8
92.5°	15.1	15.0	14.8	14.7	14.9	15.5	16.2	16.9	17.6	18.0	18.5
95°	43.6	38.1	32.6	27.0	24.8	26.0	27.2	28.4	29.5	30.3	31.2
97.5°	82.0	66.4	50.7	35.1	28.6	31.4	34.1	36.8	39.5	40.2	40.9
100°	110.9	87.9	64.9	41.8	31.7	34.5	37.4	40.3	43.2	44.5	45.9
102.5°	169.1	164.2	159.3	154.4	140.1	116.1	92.2	68.3	44.4	46.1	47.8
105°	235.2	240.2	245.3	250.3	229.9	183.9	138.0	92.1	46.2	48.0	49.9
107.5°	298.3	302.3	306.3	310.5	284.9	229.9	174.8	119.7	64.6	62.7	60.8
110°	338.9	342.4	345.9	349.4	326.9	278.3	229.7	181.1	132.5	115.7	98.8





TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	377.2	380.3	383.5	386.6	382.1	370.2	358.1	346.1	334.1	272.7	211.4
115°	438.1	441.0	443.9	446.7	450.2	454.4	458.6	462.9	467.1	389.1	311.2
117.5°	493.1	496.3	499.5	502.7	505.7	508.7	511.5	514.4	517.3	498.4	479.6
120°	532.4	534.9	537.4	540.0	542.7	545.7	548.8	551.8	554.8	556.9	558.9
122.5°	566.4	569.1	571.7	574.4	577.4	580.7	584.0	587.2	590.6	591.8	593.0
125°	617.6	619.8	621.9	624.2	626.9	630.0	633.3	636.4	639.6	640.8	642.0
127.5°	664.6	667.0	669.5	671.8	674.3	676.7	679.1	681.4	683.8	685.6	687.3
130°	694.6	697.3	699.9	702.6	704.9	706.7	708.6	710.4	712.3	714.2	716.0
132.5°	724.5	726.7	729.0	731.3	733.3	735.2	737.0	738.9	740.8	742.4	743.9
135°	764.2	766.9	769.6	772.3	774.4	775.9	777.4	778.9	780.5	782.1	783.8
137.5°	803.2	805.1	807.0	808.8	810.6	812.4	814.0	815.8	817.5	819.2	820.8
140°	828.7	830.0	831.4	832.7	834.3	836.1	838.0	839.9	841.8	843.3	844.8
142.5°	850.3	851.6	852.8	854.0	855.6	857.8	859.9	862.1	864.1	865.5	866.9
145°	883.2	883.0	882.9	882.7	884.1	886.9	889.8	892.6	895.5	896.7	897.9
147.5°	912.5	911.9	911.2	910.6	911.7	914.6	917.3	920.2	923.1	923.9	924.8
150°	931.4	930.2	929.1	927.9	928.6	931.3	934.0	936.7	939.4	940.4	941.4
152.5°	947.6	946.3	945.0	943.6	944.3	946.8	949.4	952.0	954.5	955.5	956.6
155°	971.1	969.6	968.1	966.6	966.9	968.9	970.9	973.0	974.9	976.0	977.0
157.5°	990.1	988.7	987.5	986.2	986.3	987.7	989.1	990.5	991.9	993.1	994.2
160°	1001.2	1000.2	999.2	998.1	998.1	999.2	1000.2	1001.2	1002.2	1003.2	1004.2
162.5°	1010.9	1009.9	1008.8	1007.9	1007.8	1008.7	1009.6	1010.4	1011.3	1012.4	1013.6
165°	1023.9	1022.9	1021.9	1020.9	1020.6	1021.1	1021.6	1022.2	1022.6	1023.8	1025.0
167.5°	1033.6	1032.6	1031.6	1030.5	1030.3	1030.8	1031.3	1031.7	1032.2	1033.3	1034.5
170°	1039.0	1038.1	1037.0	1036.0	1035.7	1036.0	1036.3	1036.7	1037.0	1038.2	1039.4
172.5°	1042.7	1041.6	1040.7	1039.7	1039.3	1039.7	1040.0	1040.3	1040.7	1041.9	1043.0
175°	1047.2	1046.0	1044.9	1043.7	1043.2	1043.6	1043.9	1044.3	1044.6	1045.8	1046.9
177.5°	1048.2	1047.3	1046.3	1045.4	1045.0	1045.1	1045.2	1045.4	1045.5	1046.5	1047.4
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	851.4	851.4	851.4	851.4	851.4	851.4	851.4
2.5°	881.2	884.3	885.7	885.7	887.4	886.7	886.0
5°	931.8	937.5	938.7	944.0	947.8	946.7	947.2
7.5°	982.2	991.3	1000.2	1004.2	1005.0	1007.3	1008.2
10°	1013.2	1020.6	1034.5	1032.5	1042.8	1048.7	1038.9
12.5°	1043.1	1053.0	1062.7	1065.3	1071.2	1073.1	1069.2
15°	1070.0	1075.3	1075.9	1074.4	1076.3	1074.8	1069.1
17.5°	1044.8	1036.2	1018.7	1010.3	1003.8	994.1	990.2
20°	1003.1	977.7	948.2	936.3	922.4	895.2	901.7
22.5°	913.2	884.2	854.7	820.1	803.6	777.8	776.3
25°	773.3	723.3	668.3	629.8	607.4	581.6	570.4
27.5°	601.3	538.3	493.2	470.4	449.6	429.2	428.3
30°	488.1	440.8	405.9	386.3	373.7	365.0	366.9
32.5°	411.5	379.0	355.5	339.3	329.9	323.4	323.3
35°	336.4	314.2	299.0	292.3	285.5	280.7	281.1
37.5°	287.9	274.5	266.1	258.6	254.4	252.1	250.7
40°	263.0	252.1	245.6	241.1	237.6	234.3	233.7
42.5°	243.4	234.3	227.8	224.3	221.0	218.6	218.1
45°	215.9	208.6	202.6	198.8	197.3	195.3	195.3
47.5°	192.1	184.8	180.2	177.8	175.2	173.9	173.8
50°	176.0	170.4	166.3	164.8	162.7	161.8	161.5
52.5°	161.6	157.4	154.4	153.4	152.5	151.4	151.5
55°	142.0	139.7	138.5	137.5	136.1	134.3	135.5
57.5°	125.5	123.5	120.3	117.5	116.1	114.9	115.3
60°	113.9	109.7	105.6	102.3	101.5	98.8	98.8
62.5°	99.3	93.4	88.3	86.5	85.6	84.4	84.1
65°	76.3	74.0	72.8	71.6	71.0	71.0	70.4
67.5°	63.2	62.3	61.0	60.7	60.1	60.0	59.7
70°	55.9	54.7	54.1	53.9	53.2	53.6	52.7
72.5°	48.8	47.8	47.8	47.0	46.7	46.7	46.0
75°	38.4	38.4	38.2	37.9	37.3	37.0	37.3
77.5°	29.5	29.6	29.1	29.1	29.0	29.1	28.8
80°	23.7	23.9	23.7	23.4	23.1	23.4	23.1
82.5°	18.7	18.3	18.2	18.1	18.1	17.9	17.9
85°	10.6	10.9	10.6	10.4	10.4	10.4	10.6
87.5°	7.5	7.8	7.8	7.9	8.0	8.1	7.8
90°	17.7	18.5	19.1	19.4	19.7	20.1	20.4
92.5°	18.9	19.3	19.6	19.8	20.0	20.2	20.4
95°	32.1	32.9	33.2	33.0	32.9	32.7	32.6
97.5°	41.5	42.2	42.6	42.9	43.0	43.3	43.4
100°	47.2	48.6	49.4	49.7	50.1	50.4	50.7
102.5°	49.6	51.3	52.4	52.9	53.4	53.9	54.3
105°	51.7	53.6	54.8	55.5	56.2	56.9	57.5
107.5°	59.0	57.1	56.5	57.2	57.8	58.5	59.2
110°	82.0	65.2	57.1	57.8	58.5	59.1	59.8



TEST NUMBER: P331793-927

CATALOG NUMBER: S122RDIW-S485D970U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	150.0	88.6	58.2	58.8	59.3	59.9	60.4
115°	233.4	155.5	110.5	98.4	86.3	74.1	62.1
117.5°	460.8	442.0	412.6	372.8	333.0	293.3	253.4
120°	560.9	562.9	552.5	529.9	507.2	484.4	461.8
122.5°	594.2	595.4	593.8	589.4	585.0	580.6	576.2
125°	643.2	644.4	645.2	645.7	646.2	646.7	647.2
127.5°	689.0	690.7	691.6	691.7	691.8	691.9	692.0
130°	717.9	719.7	720.6	720.3	720.2	720.0	719.9
132.5°	745.5	747.1	747.8	747.6	747.4	747.3	747.1
135°	785.4	787.1	787.8	787.5	787.1	786.8	786.5
137.5°	822.4	824.1	824.7	824.1	823.5	822.9	822.4
140°	846.3	847.8	848.1	847.3	846.4	845.6	844.8
142.5°	868.3	869.7	869.9	869.1	868.2	867.4	866.6
145°	899.0	900.2	900.4	899.5	898.7	897.9	897.0
147.5°	925.7	926.5	926.6	925.9	925.2	924.5	923.8
150°	942.4	943.4	943.5	942.7	941.8	941.0	940.2
152.5°	957.5	958.5	958.5	957.4	956.3	955.2	954.1
155°	977.9	979.0	978.8	977.5	976.1	974.8	973.4
157.5°	995.4	996.5	996.4	995.1	993.8	992.4	991.2
160°	1005.2	1006.2	1006.2	1005.0	1003.8	1002.7	1001.5
162.5°	1014.7	1015.9	1015.7	1014.2	1012.8	1011.4	1010.0
165°	1026.2	1027.4	1027.4	1026.2	1025.0	1023.8	1022.6
167.5°	1035.7	1036.9	1036.7	1035.2	1033.7	1032.2	1030.7
170°	1040.5	1041.7	1041.6	1040.1	1038.6	1037.0	1035.5
172.5°	1044.2	1045.4	1045.2	1043.7	1042.2	1040.7	1039.2
175°	1048.1	1049.3	1049.1	1047.3	1045.7	1044.0	1042.4
177.5°	1048.3	1049.2	1049.2	1047.9	1046.7	1045.5	1044.3
180°	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1	1046.1

(END OF REPORT)