

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331824-927

Luminaire Tested: **S122RDIW-S675D1440U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331824-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D1440U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5800.8 lumens  
Efficiency: N/A  
Efficacy: 85.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331824-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331824-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	79	73	68	77	71	66	62	57	53	51	44	41	39	31	30	29	23
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22	18
5	66	55	47	42	59	50	43	38	40	35	32	31	28	25	23	21	19	15
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14428	14428	14428
5°	14483	14248	14326
10°	14372	14014	13895
15°	14206	13600	13207
20°	13979	13005	12352
25°	13744	12332	11526
30°	13420	11639	10465
35°	13102	10886	9532
40°	12783	10108	8454
45°	12408	9232	7478
50°	12024	8349	6521
55°	11634	7398	5599
60°	11176	6397	4647
65°	10659	5375	4233
70°	10041	4428	3895
75°	9283	4036	3631
80°	8201	3608	3310
85°	6447	2853	2853



TEST NUMBER: P331824-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.6	1.4
10°-20°	229.7	4.0
20°-30°	322.5	5.6
30°-40°	351.7	6.1
40°-50°	323.4	5.6
50°-60°	254.0	4.4
60°-70°	165.6	2.9
70°-80°	85.4	1.5
80°-90°	27.8	0.5
90°-100°	89.7	1.5
100°-110°	278.5	4.8
110°-120°	476.1	8.2
120°-130°	626.1	10.8
130°-140°	702.7	12.1
140°-150°	689.0	11.9
150°-160°	577.9	10.0
160°-170°	383.3	6.6
170°-180°	134.0	2.3
0°-30°	635.8	11.0
0°-40°	987.5	17.0
0°-60°	1564.8	27.0
0°-90°	1843.6	31.8
90°-120°	844.3	14.6
90°-150°	2862.0	49.3
90°-180°	3957.0	68.2
0°-180°	5800.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	894	894	894	894	894	
5°	894	889	879	886	884	85
15°	850	840	814	799	790	239
25°	772	744	692	660	647	355
35°	665	622	552	503	484	416
45°	543	488	404	349	328	419
55°	413	349	263	216	199	369
65°	279	213	141	115	111	277
75°	149	94	65	59	58	158
85°	35	19	15	15	15	41
90°	1	16	42	40	41	5
95°	62	74	76	76	74	71
105°	257	260	263	265	265	271
115°	478	484	482	481	478	472
125°	695	705	702	699	697	621
135°	899	912	915	914	910	694
145°	1092	1100	1107	1108	1104	682
155°	1248	1252	1255	1261	1258	574
165°	1358	1357	1357	1364	1359	383
175°	1413	1409	1407	1414	1408	134
180°	1415	1415	1415	1415	1415	



TEST NUMBER: P331824-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	896.8	896.1	895.4	894.7	894.0	892.8	891.2	889.6	888.1	886.5	888.0
5°	893.6	892.7	891.8	890.9	890.0	888.4	886.1	883.8	881.4	879.1	880.7
7.5°	884.4	883.3	882.2	881.1	880.0	878.0	875.3	872.6	869.8	867.1	867.5
10°	876.6	875.4	874.1	872.8	871.6	869.2	865.5	862.0	858.4	854.8	854.3
12.5°	866.9	865.4	863.8	862.3	860.7	857.7	853.1	848.5	843.8	839.2	838.3
15°	849.9	848.0	846.0	844.0	842.0	838.0	831.9	825.8	819.7	813.6	810.2
17.5°	829.1	826.1	823.1	820.0	817.0	811.6	803.7	795.9	788.1	780.2	776.2
20°	813.6	809.9	806.4	802.8	799.2	792.9	783.9	774.9	766.0	756.9	752.4
22.5°	796.7	792.7	788.7	784.7	780.6	773.6	763.4	753.3	743.1	733.0	727.2
25°	771.5	765.7	760.0	754.2	748.5	739.7	727.9	716.0	704.1	692.2	684.8
27.5°	741.1	734.8	728.6	722.3	716.1	706.2	692.9	679.5	666.1	652.8	644.2
30°	719.8	712.9	706.1	699.3	692.4	681.8	667.4	653.1	638.7	624.3	615.1
32.5°	699.0	691.0	683.1	675.1	667.1	655.8	641.1	626.5	611.8	597.1	586.7
35°	664.7	655.6	646.4	637.2	628.1	615.6	599.8	584.0	568.2	552.3	541.0
37.5°	630.5	620.4	610.3	600.2	590.2	576.7	559.9	543.0	526.2	509.3	496.9
40°	606.5	595.7	584.9	574.2	563.4	549.3	531.9	514.4	497.0	479.6	466.8
42.5°	581.9	570.6	559.2	547.9	536.5	521.8	503.8	485.8	467.8	449.8	436.6
45°	543.4	531.4	519.4	507.3	495.3	479.8	461.0	442.1	423.2	404.3	391.6
47.5°	505.9	493.1	480.4	467.6	454.9	438.8	419.3	399.8	380.3	360.8	348.2
50°	478.7	466.0	453.2	440.5	427.7	411.5	391.7	371.9	352.1	332.4	320.0
52.5°	452.3	438.9	425.6	412.3	398.9	382.5	363.2	343.9	324.6	305.2	293.3
55°	413.3	399.3	385.2	371.2	357.2	340.5	321.1	301.7	282.3	262.8	252.1
57.5°	373.3	358.9	344.5	330.2	315.8	299.3	280.6	262.0	243.3	224.7	214.8
60°	346.1	331.8	317.3	303.0	288.6	272.2	253.7	235.1	216.7	198.1	188.9
62.5°	319.6	305.2	290.8	276.5	262.1	246.1	228.5	210.8	193.1	175.5	166.8
65°	279.0	264.4	249.9	235.4	220.8	205.4	189.3	173.1	156.9	140.7	134.6
67.5°	239.9	225.4	211.0	196.5	182.0	167.5	153.0	138.5	123.9	109.3	106.5
70°	212.7	198.7	184.7	170.6	156.6	143.4	131.0	118.6	106.2	93.8	92.0
72.5°	186.8	173.3	159.9	146.5	133.0	121.4	111.4	101.4	91.5	81.5	80.0
75°	148.8	136.3	123.7	111.1	98.5	89.1	83.0	76.9	70.8	64.7	63.5
77.5°	111.5	100.4	89.4	78.3	67.3	60.3	57.4	54.4	51.5	48.6	47.8
80°	88.2	79.0	69.8	60.7	51.5	46.0	44.2	42.4	40.6	38.8	38.1
82.5°	66.8	59.7	52.5	45.3	38.2	34.0	32.8	31.5	30.3	29.2	28.7
85°	34.8	31.0	27.3	23.4	19.6	17.5	17.0	16.5	15.9	15.4	15.4
87.5°	10.6	10.1	9.6	9.0	8.6	8.9	10.1	11.2	12.4	13.5	13.3
90°	1.2	4.4	7.5	10.8	13.9	18.5	24.3	30.1	36.0	41.8	41.3
92.5°	21.2	23.6	25.9	28.3	30.6	32.5	33.8	35.3	36.6	37.9	38.1
95°	62.1	64.7	67.4	70.0	72.7	74.3	74.9	75.3	75.9	76.4	76.4
97.5°	113.4	115.8	118.1	120.5	122.8	124.5	125.5	126.5	127.5	128.5	128.5
100°	151.7	153.8	155.9	158.0	160.2	161.6	162.4	163.2	164.0	164.8	164.8
102.5°	191.8	193.5	195.2	196.9	198.6	199.9	201.0	201.9	203.0	204.0	204.2
105°	256.7	257.5	258.3	259.1	259.9	260.6	261.2	261.7	262.2	262.8	263.2
107.5°	322.2	323.4	324.6	325.7	326.9	327.5	327.5	327.5	327.5	327.5	327.6
110°	364.2	365.8	367.4	369.0	370.6	371.5	371.5	371.5	371.5	371.5	371.5



TEST NUMBER: P331824-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	410.1	411.7	413.3	414.9	416.5	417.2	416.9	416.8	416.5	416.3	415.7
115°	477.7	479.3	480.9	482.5	484.1	484.6	484.1	483.5	483.0	482.5	482.2
117.5°	545.1	547.2	549.3	551.4	553.6	553.9	552.4	550.9	549.4	548.0	547.3
120°	589.9	592.1	594.2	596.4	598.5	598.5	596.4	594.2	592.1	589.9	589.9
122.5°	631.1	633.6	636.1	638.7	641.3	641.7	640.3	638.8	637.3	635.8	635.2
125°	695.1	697.4	699.8	702.2	704.6	705.4	704.6	703.9	703.1	702.2	701.4
127.5°	757.4	760.4	763.4	766.5	769.5	770.6	769.6	768.7	767.7	766.8	765.7
130°	796.5	800.0	803.5	806.9	810.4	811.8	811.3	810.8	810.2	809.7	809.2
132.5°	840.5	843.4	846.1	849.0	851.8	853.3	853.3	853.4	853.6	853.7	852.5
135°	899.3	902.2	905.1	908.0	910.9	912.7	913.2	913.8	914.3	914.8	914.6
137.5°	961.2	963.5	965.9	968.3	970.7	972.2	973.0	973.6	974.3	975.0	974.8
140°	998.4	1000.8	1003.2	1005.6	1008.0	1009.8	1011.1	1012.5	1013.8	1015.1	1015.1
142.5°	1036.6	1039.0	1041.4	1043.8	1046.2	1047.8	1048.7	1049.6	1050.5	1051.5	1051.6
145°	1091.5	1093.4	1095.3	1097.1	1099.0	1100.7	1102.3	1103.9	1105.5	1107.1	1107.3
147.5°	1140.5	1142.7	1144.9	1147.2	1149.5	1151.1	1152.1	1153.2	1154.3	1155.3	1156.0
150°	1173.9	1175.5	1177.2	1178.8	1180.4	1181.6	1182.7	1183.8	1184.9	1185.9	1186.7
152.5°	1203.6	1205.1	1206.7	1208.3	1210.0	1211.4	1212.7	1213.9	1215.2	1216.5	1217.5
155°	1248.0	1248.8	1249.6	1250.4	1251.2	1252.0	1252.8	1253.5	1254.3	1255.1	1256.5
157.5°	1285.9	1286.5	1287.1	1287.6	1288.1	1288.6	1289.1	1289.6	1290.1	1290.5	1292.3
160°	1308.9	1309.5	1310.0	1310.5	1311.1	1311.5	1311.7	1311.9	1312.2	1312.5	1314.1
162.5°	1329.9	1330.1	1330.2	1330.2	1330.4	1330.5	1330.8	1331.1	1331.3	1331.6	1333.4
165°	1357.9	1357.6	1357.3	1357.1	1356.8	1356.7	1356.7	1356.7	1356.7	1356.7	1358.5
167.5°	1381.2	1380.5	1379.7	1378.9	1378.1	1377.7	1377.6	1377.6	1377.5	1377.4	1379.3
170°	1393.7	1392.9	1392.1	1391.3	1390.5	1390.0	1389.7	1389.5	1389.2	1388.9	1390.8
172.5°	1402.3	1401.5	1400.7	1399.9	1399.2	1398.6	1398.4	1398.0	1397.8	1397.5	1399.4
175°	1412.8	1412.0	1411.2	1410.4	1409.6	1409.0	1408.4	1407.9	1407.4	1406.8	1408.7
177.5°	1417.1	1416.5	1415.9	1415.2	1414.6	1414.0	1413.6	1413.2	1412.8	1412.3	1413.6
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2



TEST NUMBER: P331824-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	889.4	890.8	892.2	892.8	892.6	892.2	892.0	891.7
5°	882.3	883.9	885.5	886.1	885.5	884.9	884.5	883.9
7.5°	868.0	868.5	868.9	868.7	867.8	866.9	865.9	865.0
10°	853.7	853.2	852.6	851.8	850.7	849.7	848.6	847.5
12.5°	837.3	836.4	835.4	834.0	832.2	830.4	828.6	826.8
15°	806.8	803.3	799.9	797.3	795.5	793.7	791.9	790.1
17.5°	772.1	768.0	764.0	760.4	757.3	754.2	751.1	748.1
20°	748.0	743.5	738.9	734.7	730.8	726.8	722.9	718.9
22.5°	721.4	715.7	709.9	705.5	702.5	699.6	696.6	693.7
25°	677.5	670.1	662.7	657.7	655.1	652.4	649.7	647.0
27.5°	635.6	627.0	618.5	612.0	607.7	603.4	599.1	594.8
30°	606.0	596.8	587.6	580.7	575.8	570.9	566.1	561.3
32.5°	576.2	565.8	555.3	547.8	543.2	538.7	534.1	529.6
35°	529.7	518.4	507.1	499.4	495.4	491.5	487.6	483.6
37.5°	484.3	471.9	459.5	450.9	446.4	441.9	437.4	432.8
40°	454.0	441.2	428.5	419.8	415.1	410.4	405.8	401.1
42.5°	423.4	410.2	397.0	388.2	383.7	379.1	374.6	370.0
45°	378.8	366.1	353.3	344.8	340.5	336.1	331.8	327.5
47.5°	335.5	322.8	310.1	301.8	297.9	294.0	290.0	286.1
50°	307.6	295.2	282.8	274.6	270.9	267.1	263.4	259.6
52.5°	281.3	269.3	257.3	249.6	246.1	242.6	239.2	235.7
55°	241.3	230.4	219.7	212.6	209.2	205.7	202.3	198.9
57.5°	204.9	195.0	185.1	178.7	175.9	173.0	170.1	167.2
60°	179.8	170.6	161.4	155.4	152.6	149.7	146.8	143.9
62.5°	158.0	149.2	140.5	135.3	133.6	131.9	130.2	128.4
65°	128.5	122.4	116.3	113.0	112.4	111.9	111.3	110.8
67.5°	103.7	100.9	98.2	96.4	95.9	95.3	94.7	94.1
70°	90.2	88.4	86.6	85.4	84.6	83.9	83.2	82.5
72.5°	78.5	77.0	75.5	74.5	74.1	73.7	73.2	72.8
75°	62.2	60.9	59.7	58.9	58.8	58.6	58.4	58.2
77.5°	47.1	46.3	45.6	45.2	44.8	44.6	44.3	44.0
80°	37.4	36.7	36.0	35.6	35.6	35.6	35.6	35.6
82.5°	28.3	27.8	27.4	27.2	27.2	27.2	27.2	27.2
85°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
87.5°	13.1	12.8	12.5	12.4	12.5	12.5	12.6	12.7
90°	40.7	40.2	39.7	39.5	39.8	40.1	40.3	40.6
92.5°	38.2	38.3	38.4	38.5	38.5	38.6	38.7	38.7
95°	76.4	76.4	76.4	76.1	75.7	75.1	74.5	74.1
97.5°	128.5	128.5	128.5	128.5	128.4	128.3	128.3	128.3
100°	164.8	164.8	164.8	164.7	164.4	164.1	163.9	163.6
102.5°	204.4	204.6	204.9	204.8	204.5	204.3	204.0	203.7
105°	263.8	264.4	264.8	265.1	265.1	265.1	265.1	265.1
107.5°	327.9	328.1	328.3	327.8	326.6	325.3	324.2	322.9
110°	371.5	371.5	371.5	371.0	370.2	369.4	368.6	367.8





TEST NUMBER: P331824-927

CATALOG NUMBER: S122RDIW-S675D1440U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	415.0	414.4	413.8	413.1	412.6	412.0	411.4	410.8
115°	482.0	481.6	481.4	480.9	480.1	479.3	478.5	477.7
117.5°	546.7	546.1	545.4	544.6	543.8	543.0	542.2	541.5
120°	589.9	589.9	589.9	589.5	588.7	588.0	587.2	586.4
122.5°	634.5	633.9	633.3	632.6	632.1	631.5	630.9	630.3
125°	700.6	699.8	699.0	698.5	698.2	698.0	697.8	697.4
127.5°	764.8	763.8	762.9	762.0	761.1	760.3	759.5	758.6
130°	808.7	808.1	807.6	806.8	805.7	804.7	803.6	802.6
132.5°	851.4	850.2	849.0	848.0	847.2	846.3	845.4	844.5
135°	914.3	914.0	913.8	913.2	912.4	911.6	910.9	910.1
137.5°	974.5	974.4	974.1	973.5	972.5	971.4	970.3	969.2
140°	1015.1	1015.1	1015.1	1014.6	1013.5	1012.5	1011.4	1010.3
142.5°	1051.9	1052.1	1052.3	1051.9	1050.8	1049.7	1048.7	1047.6
145°	1107.6	1107.9	1108.1	1107.7	1106.7	1105.6	1104.5	1103.5
147.5°	1156.5	1157.1	1157.7	1157.5	1156.4	1155.4	1154.4	1153.4
150°	1187.5	1188.3	1189.1	1189.1	1188.3	1187.5	1186.7	1185.9
152.5°	1218.5	1219.5	1220.5	1220.5	1219.5	1218.5	1217.5	1216.5
155°	1257.8	1259.2	1260.4	1260.8	1260.0	1259.2	1258.4	1257.6
157.5°	1294.1	1295.9	1297.8	1298.0	1296.7	1295.5	1294.2	1292.9
160°	1315.7	1317.2	1318.8	1319.1	1318.0	1317.0	1316.0	1314.9
162.5°	1335.2	1337.0	1338.8	1339.1	1337.8	1336.6	1335.3	1334.0
165°	1360.4	1362.2	1364.1	1364.4	1363.0	1361.8	1360.4	1359.1
167.5°	1381.2	1383.1	1384.9	1385.1	1383.8	1382.4	1381.0	1379.6
170°	1392.7	1394.5	1396.4	1396.5	1394.9	1393.3	1391.7	1390.1
172.5°	1401.2	1403.1	1404.9	1405.1	1403.5	1401.9	1400.3	1398.8
175°	1410.6	1412.4	1414.3	1414.4	1412.8	1411.2	1409.6	1408.0
177.5°	1414.9	1416.2	1417.5	1417.5	1416.2	1414.9	1413.6	1412.3
180°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2

(END OF REPORT)