

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331805-927

Luminaire Tested: **S122RDIW-S675D435U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331805-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D435U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3383.7 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59				59
1	101	97	93	90	94	91	87	85	79	77	75	68	67	65	59	58	57				52	
2	93	86	80	75	86	80	75	71	70	67	63	61	59	56	53	51	49				45	
3	85	76	69	64	79	72	66	61	63	58	55	55	52	49	48	45	43				39	
4	78	68	61	55	73	64	58	52	57	52	48	50	46	43	43	40	38				35	
5	73	61	54	48	68	58	51	46	51	46	42	45	41	38	40	36	34				31	
6	67	56	48	42	63	53	46	41	47	41	37	42	37	34	36	33	30				28	
7	63	51	43	38	58	48	41	36	43	37	33	38	34	30	34	30	28				25	
8	58	46	39	34	55	44	37	33	40	34	30	35	31	28	31	28	25				23	
9	55	43	35	31	51	41	34	29	37	31	27	33	28	25	29	26	23				21	
10	51	39	32	28	48	38	31	27	34	29	25	30	26	23	27	24	21				19	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18791	18791	18791	18791
5°	20985	18908	16765	18908
10°	23282	18775	14532	18775
15°	24428	18501	11450	18501
20°	21179	18093	9907	18093
25°	13890	17533	8845	17533
30°	9350	16858	8006	16858
35°	7571	16005	7222	16005
40°	6734	15076	6681	15076
45°	6094	13988	5966	13988
50°	5546	12911	5526	12911
55°	5213	11713	5146	11713
60°	4363	10618	4308	10618
65°	3679	9639	4172	9639
70°	3399	8611	3932	8611
75°	3175	7492	3631	7492
80°	2929	6165	3236	6165
85°	2705	4872	2853	4872



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.3	3.3
10°-20°	307.4	9.1
20°-30°	396.1	11.7
30°-40°	376.4	11.1
40°-50°	322.5	9.5
50°-60°	245.6	7.3
60°-70°	155.2	4.6
70°-80°	77.5	2.3
80°-90°	21.3	0.6
90°-100°	15.6	0.5
100°-110°	57.2	1.7
110°-120°	153.0	4.5
120°-130°	252.6	7.5
130°-140°	268.6	7.9
140°-150°	249.7	7.4
150°-160°	200.7	5.9
160°-170°	129.3	3.8
170°-180°	44.5	1.3
0°-30°	813.8	24.1
0°-40°	1190.3	35.2
0°-60°	1758.3	52.0
0°-90°	2012.4	59.5
90°-120°	225.9	6.7
90°-150°	996.7	29.5
90°-180°	1371.0	40.5
0°-180°	3383.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1164	1164	1164	1164	1164	
5°	1295	1167	1034	1167	1295	128
15°	1461	1107	685	1107	1461	394
25°	780	984	496	984	780	370
35°	384	812	366	812	384	246
45°	267	613	261	613	267	207
55°	185	416	183	416	185	163
65°	96	252	109	252	96	98
75°	51	120	58	120	51	54
85°	15	26	15	26	15	16
90°	9	0	9	0	9	5
95°	15	22	15	22	15	14
105°	26	103	26	103	26	27
115°	28	195	28	195	28	70
125°	290	275	290	275	290	250
135°	352	341	352	341	352	271
145°	401	395	401	395	401	251
155°	436	435	436	435	436	201
165°	457	458	457	458	457	129
175°	466	469	466	469	466	44
180°	468	468	468	468	468	



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1211.0	1212.0	1213.0	1210.7	1210.7	1208.7	1204.5	1201.3	1192.2	1191.0	1191.0
5°	1294.8	1294.0	1295.6	1290.4	1283.1	1281.4	1273.7	1263.7	1253.2	1241.4	1239.0
7.5°	1378.1	1376.9	1373.6	1372.8	1367.1	1354.9	1342.6	1329.4	1311.9	1294.9	1286.3
10°	1420.1	1433.5	1425.4	1411.3	1414.1	1395.1	1385.0	1367.6	1353.0	1327.5	1321.9
12.5°	1461.6	1466.8	1464.3	1456.2	1452.5	1439.4	1425.8	1410.6	1383.8	1360.9	1341.0
15°	1461.4	1469.1	1471.1	1468.7	1470.7	1469.9	1462.6	1450.1	1426.6	1401.5	1379.7
17.5°	1353.5	1358.8	1372.1	1381.1	1392.4	1416.3	1428.1	1432.7	1429.3	1415.0	1399.6
20°	1232.6	1223.6	1260.8	1279.8	1296.0	1336.4	1371.2	1384.6	1406.0	1405.6	1401.5
22.5°	1061.0	1063.2	1098.4	1121.0	1168.2	1208.6	1248.3	1298.5	1340.0	1367.4	1383.5
25°	779.7	795.0	830.2	860.9	913.5	988.7	1057.0	1136.3	1211.1	1270.1	1326.4
27.5°	585.5	586.7	614.6	642.9	674.1	735.8	821.8	916.5	1023.1	1111.1	1212.4
30°	501.5	499.0	510.7	528.1	554.8	602.5	667.2	760.3	866.6	999.2	1117.3
32.5°	441.9	442.0	450.9	463.7	485.9	518.1	562.4	637.9	738.5	868.9	1007.3
35°	384.1	383.7	390.2	399.5	408.8	429.4	459.8	499.4	568.5	690.2	831.8
37.5°	342.8	344.5	347.7	353.5	363.8	375.3	393.5	420.1	469.3	541.3	660.3
40°	319.5	320.3	324.7	329.5	335.6	344.5	359.5	380.9	416.9	474.4	561.3
42.5°	298.1	298.9	302.1	306.6	311.3	320.3	332.6	351.2	380.3	425.2	496.9
45°	266.9	266.9	269.7	271.7	277.0	285.1	295.2	310.5	330.8	363.9	411.6
47.5°	237.6	237.7	239.6	243.0	246.4	252.6	262.6	275.1	289.9	315.5	356.2
50°	220.8	221.2	222.4	225.2	227.3	232.9	240.6	251.5	266.9	286.7	320.7
52.5°	207.2	206.9	208.5	209.7	211.1	215.2	220.9	230.5	244.2	261.5	289.6
55°	185.2	183.5	186.0	188.1	189.3	190.8	194.1	200.2	211.9	226.5	247.5
57.5°	157.7	157.1	158.8	160.7	164.5	168.8	171.5	175.4	181.5	191.9	212.8
60°	135.1	135.1	138.7	139.9	144.3	150.0	155.7	158.9	165.0	171.8	187.2
62.5°	115.0	115.3	117.0	118.3	120.7	127.7	135.6	142.8	148.5	155.0	165.2
65°	96.3	97.0	97.0	97.8	99.5	101.1	104.3	110.0	120.1	129.4	137.0
67.5°	81.7	81.9	82.1	82.9	83.4	85.2	86.4	89.0	91.3	100.1	109.6
70°	72.0	73.2	72.8	73.6	74.0	74.8	76.4	77.6	81.3	83.3	89.0
72.5°	62.9	63.8	63.7	64.2	65.3	65.4	66.7	68.0	70.3	72.0	75.0
75°	50.9	50.5	50.9	51.7	52.1	52.6	52.6	54.2	55.4	57.0	59.0
77.5°	39.3	39.7	39.6	39.7	39.8	40.5	40.4	41.2	42.4	43.2	44.1
80°	31.5	31.9	31.5	31.9	32.3	32.7	32.3	32.7	34.0	34.8	34.8
82.5°	24.4	24.5	24.7	24.8	24.9	25.0	25.6	25.7	26.5	26.4	26.7
85°	14.6	14.2	14.2	14.2	14.6	15.0	14.6	14.6	15.0	15.0	15.0
87.5°	7.0	7.3	7.3	7.2	7.2	7.1	7.1	7.4	6.9	7.2	6.7
90°	9.1	9.0	8.9	8.7	8.6	8.2	7.9	7.5	7.1	6.7	6.2
92.5°	9.1	9.0	9.0	8.9	8.8	8.6	8.5	8.2	8.1	7.8	7.5
95°	14.6	14.7	14.7	14.8	14.9	14.7	14.3	13.9	13.5	13.2	12.7
97.5°	19.4	19.3	19.3	19.2	19.1	18.9	18.6	18.3	18.0	17.7	16.5
100°	22.7	22.5	22.4	22.3	22.1	21.7	21.1	20.5	19.9	19.3	18.0
102.5°	24.3	24.1	23.9	23.7	23.4	23.0	22.2	21.4	20.6	19.8	30.6
105°	25.7	25.4	25.1	24.8	24.6	24.0	23.1	22.3	21.5	20.7	41.2
107.5°	26.5	26.1	25.9	25.6	25.3	25.5	26.4	27.3	28.0	28.9	53.6
110°	26.8	26.5	26.1	25.8	25.5	29.2	36.7	44.2	51.7	59.3	81.0



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	27.0	26.8	26.5	26.3	26.1	39.7	67.1	94.6	122.0	149.5	154.8
115°	27.7	33.2	38.6	44.0	49.4	69.6	104.4	139.3	174.0	208.9	207.0
117.5°	113.4	131.2	148.9	166.8	184.6	197.6	206.1	214.5	223.0	231.4	230.1
120°	206.5	216.7	226.9	237.0	247.2	251.8	250.9	250.0	249.1	248.2	246.8
122.5°	257.7	259.7	261.7	263.6	265.6	266.3	265.8	265.2	264.7	264.2	262.7
125°	289.5	289.3	289.1	288.8	288.6	288.2	287.7	287.2	286.6	286.1	284.7
127.5°	309.5	309.5	309.4	309.4	309.3	309.0	308.2	307.4	306.7	305.9	304.8
130°	322.0	322.1	322.2	322.3	322.3	321.9	321.1	320.3	319.4	318.6	317.8
132.5°	334.2	334.3	334.3	334.4	334.5	334.1	333.4	332.8	332.1	331.4	330.5
135°	351.8	352.0	352.1	352.3	352.4	352.1	351.3	350.6	349.8	349.1	348.4
137.5°	367.8	368.1	368.4	368.6	368.8	368.6	367.9	367.2	366.4	365.7	364.9
140°	377.9	378.3	378.6	379.0	379.4	379.2	378.6	377.9	377.2	376.5	375.7
142.5°	387.6	388.0	388.4	388.7	389.1	389.0	388.4	387.8	387.1	386.5	385.6
145°	401.2	401.6	402.0	402.3	402.7	402.7	402.1	401.6	401.1	400.5	399.3
147.5°	413.2	413.5	413.8	414.2	414.5	414.5	414.1	413.7	413.3	412.9	411.6
150°	420.6	420.9	421.3	421.7	422.1	422.0	421.5	421.1	420.6	420.2	419.0
152.5°	426.7	427.2	427.8	428.3	428.7	428.8	428.3	427.9	427.4	427.0	425.8
155°	435.5	436.0	436.7	437.2	437.8	437.9	437.4	437.0	436.6	436.1	435.2
157.5°	443.4	443.9	444.5	445.1	445.7	445.8	445.2	444.7	444.2	443.7	443.1
160°	448.0	448.5	449.0	449.6	450.0	450.1	449.6	449.2	448.8	448.3	447.8
162.5°	451.8	452.4	453.0	453.7	454.3	454.4	453.9	453.4	452.9	452.3	451.9
165°	457.4	458.0	458.5	459.0	459.5	459.5	459.0	458.5	458.0	457.4	457.2
167.5°	461.1	461.7	462.4	463.0	463.7	463.8	463.3	462.8	462.2	461.7	461.5
170°	463.2	463.9	464.5	465.2	465.9	466.0	465.5	464.9	464.4	463.9	463.7
172.5°	464.9	465.5	466.2	466.8	467.5	467.6	467.1	466.5	466.0	465.5	465.3
175°	466.3	467.0	467.8	468.5	469.3	469.4	468.8	468.3	467.8	467.2	467.1
177.5°	467.1	467.6	468.2	468.7	469.3	469.4	468.9	468.5	468.1	467.6	467.6
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1191.6	1189.0	1186.8	1180.9	1178.1	1171.6	1170.6	1170.3	1161.8	1153.7	1151.5
5°	1232.6	1226.1	1216.3	1205.0	1193.3	1181.1	1173.1	1166.6	1150.4	1135.0	1126.2
7.5°	1273.7	1259.9	1243.1	1221.7	1203.8	1183.8	1168.9	1155.6	1132.6	1110.6	1095.7
10°	1304.5	1281.8	1259.6	1230.1	1207.0	1184.4	1163.4	1145.2	1119.3	1090.2	1069.5
12.5°	1323.6	1298.7	1268.0	1239.1	1209.3	1180.5	1152.4	1129.0	1098.6	1068.5	1044.0
15°	1349.4	1322.7	1285.5	1244.3	1205.9	1168.2	1135.9	1106.8	1067.1	1031.2	1001.2
17.5°	1370.5	1333.8	1293.8	1246.1	1201.7	1153.8	1112.1	1075.0	1030.9	987.5	952.2
20°	1377.3	1340.9	1294.8	1247.1	1194.5	1138.3	1093.4	1053.0	1005.7	958.4	917.9
22.5°	1373.1	1344.8	1293.5	1236.4	1182.6	1123.7	1073.0	1026.1	973.7	925.3	878.5
25°	1344.6	1334.8	1286.3	1224.0	1162.6	1094.2	1035.6	984.2	924.4	872.7	821.7
27.5°	1277.9	1298.9	1268.8	1202.5	1134.2	1060.9	995.0	936.5	874.4	816.2	765.4
30°	1213.9	1262.0	1249.1	1187.6	1111.2	1039.3	965.3	904.2	837.9	778.0	727.9
32.5°	1126.2	1205.8	1218.4	1167.0	1087.9	1008.8	931.3	870.5	801.3	738.2	689.4
35°	986.7	1105.6	1160.2	1127.4	1048.1	962.8	882.7	812.0	742.4	680.2	631.6
37.5°	820.1	982.1	1073.0	1075.4	1002.6	913.9	826.7	756.5	685.2	624.1	571.6
40°	712.1	887.6	1006.1	1032.4	970.9	875.0	786.9	715.3	645.8	585.9	525.7
42.5°	615.1	789.9	935.6	981.3	932.4	837.2	748.8	673.9	606.3	549.7	488.1
45°	497.4	650.2	810.8	892.5	865.4	777.2	683.8	612.6	549.1	500.2	441.2
47.5°	419.5	527.3	682.6	793.1	792.7	712.2	620.3	552.2	493.3	447.4	399.6
50°	375.3	469.1	600.5	725.9	736.3	668.8	581.5	514.0	459.0	410.8	372.4
52.5°	335.5	412.8	530.9	651.1	681.0	622.6	537.8	475.5	422.1	377.9	344.9
55°	283.4	343.3	433.1	545.5	590.8	549.5	474.4	416.1	372.8	335.6	307.3
57.5°	239.8	284.7	356.7	447.3	499.9	474.0	411.9	364.6	327.6	294.0	271.6
60°	212.3	249.1	310.1	385.8	444.0	425.8	372.8	328.8	297.2	268.1	247.1
62.5°	186.4	218.0	270.4	331.8	385.2	377.6	334.3	297.4	269.7	243.2	225.4
65°	150.0	173.1	213.9	262.1	304.9	308.6	277.4	252.3	227.7	206.6	190.8
67.5°	119.5	134.5	163.3	203.8	235.9	247.4	228.4	209.2	189.6	173.4	159.7
70°	100.7	112.8	133.9	166.6	196.1	208.3	197.3	182.4	165.4	152.0	140.3
72.5°	81.6	93.4	108.9	132.9	158.3	171.3	167.5	156.9	143.1	132.0	120.9
75°	61.5	65.1	75.7	91.8	111.6	122.9	125.8	120.1	109.2	100.7	94.2
77.5°	45.5	47.6	52.7	61.2	74.1	84.2	88.3	87.7	80.2	75.2	69.2
80°	36.4	37.6	40.0	43.6	53.4	63.5	66.3	66.3	61.1	59.0	53.0
82.5°	27.6	28.5	30.0	32.0	36.5	45.4	48.6	49.2	45.9	43.2	38.4
85°	15.8	15.4	16.2	17.3	18.2	20.6	25.5	26.3	25.5	22.3	21.0
87.5°	6.6	6.8	6.7	6.3	6.4	6.6	8.0	9.4	8.3	7.5	7.1
90°	5.5	5.0	4.4	3.6	2.9	2.0	1.2	0.3	1.2	2.0	2.9
92.5°	7.3	7.0	6.7	6.6	6.6	6.7	6.7	6.8	6.7	6.7	6.6
95°	12.1	11.6	11.1	12.0	14.6	17.0	19.5	22.0	19.5	17.0	14.6
97.5°	15.2	14.0	12.8	15.7	22.7	29.7	36.7	43.6	36.7	29.7	22.7
100°	16.7	15.4	14.2	18.7	29.0	39.3	49.6	60.0	49.6	39.3	29.0
102.5°	41.3	52.0	62.7	69.1	71.3	73.4	75.7	77.8	75.7	73.4	71.3
105°	61.7	82.3	102.8	111.9	109.7	107.4	105.2	102.9	105.2	107.4	109.7
107.5°	78.2	102.8	127.5	138.9	137.0	135.2	133.4	131.6	133.4	135.2	137.0
110°	102.7	124.5	146.2	156.3	154.7	153.1	151.5	150.0	151.5	153.1	154.7



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	160.2	165.6	171.0	172.9	171.5	170.2	168.7	167.3	168.7	170.2	171.5
115°	205.2	203.3	201.4	199.8	198.5	197.3	196.0	194.7	196.0	197.3	198.5
117.5°	228.8	227.5	226.2	224.8	223.4	222.0	220.5	219.1	220.5	222.0	223.4
120°	245.5	244.2	242.8	241.5	240.4	239.2	238.1	237.0	238.1	239.2	240.4
122.5°	261.2	259.8	258.3	256.9	255.7	254.5	253.3	252.2	253.3	254.5	255.7
125°	283.3	281.9	280.4	279.2	278.2	277.3	276.2	275.3	276.2	277.3	278.2
127.5°	303.7	302.7	301.6	300.6	299.4	298.3	297.3	296.2	297.3	298.3	299.4
130°	317.0	316.2	315.3	314.3	313.1	311.9	310.7	309.5	310.7	311.9	313.1
132.5°	329.7	328.8	328.0	327.1	326.1	325.0	324.0	323.1	324.0	325.0	326.1
135°	347.8	347.1	346.3	345.5	344.2	343.0	341.8	340.6	341.8	343.0	344.2
137.5°	364.2	363.4	362.6	361.8	361.0	360.1	359.3	358.5	359.3	360.1	361.0
140°	374.9	374.1	373.2	372.5	371.9	371.3	370.7	370.1	370.7	371.3	371.9
142.5°	384.6	383.7	382.8	382.0	381.4	380.9	380.4	379.9	380.4	380.9	381.4
145°	398.0	396.7	395.5	394.8	394.9	395.0	395.1	395.1	395.1	395.0	394.9
147.5°	410.4	409.1	407.8	407.3	407.7	407.9	408.2	408.4	408.2	407.9	407.7
150°	417.8	416.6	415.3	415.0	415.6	416.1	416.6	417.2	416.6	416.1	415.6
152.5°	424.7	423.5	422.4	422.1	422.7	423.3	423.9	424.5	423.9	423.3	422.7
155°	434.3	433.4	432.5	432.4	433.1	433.7	434.4	435.1	434.4	433.7	433.1
157.5°	442.4	441.8	441.2	441.2	441.7	442.3	442.8	443.4	442.8	442.3	441.7
160°	447.4	446.9	446.5	446.5	446.9	447.4	447.8	448.3	447.8	447.4	446.9
162.5°	451.5	451.1	450.8	450.8	451.3	451.7	452.2	452.7	452.2	451.7	451.3
165°	457.0	456.8	456.5	456.6	457.1	457.6	458.0	458.4	458.0	457.6	457.1
167.5°	461.3	461.1	460.9	461.0	461.4	461.9	462.3	462.8	462.3	461.9	461.4
170°	463.6	463.4	463.3	463.4	463.9	464.3	464.8	465.2	464.8	464.3	463.9
172.5°	465.2	465.0	464.9	465.0	465.5	466.0	466.4	466.8	466.4	466.0	465.5
175°	467.0	466.8	466.7	466.8	467.4	467.9	468.4	469.0	468.4	467.9	467.4
177.5°	467.5	467.5	467.4	467.6	468.0	468.4	468.9	469.3	468.9	468.4	468.0
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1147.3	1145.0	1140.8	1134.3	1130.4	1123.6	1119.1	1121.7	1122.4	1121.7	1121.1
5°	1116.5	1107.9	1096.2	1084.9	1074.4	1063.1	1056.6	1053.8	1048.1	1044.9	1043.3
7.5°	1079.2	1064.5	1048.0	1028.3	1011.5	994.0	985.0	980.5	968.9	962.7	957.1
10°	1051.4	1028.3	1011.8	985.9	970.1	947.1	931.3	931.7	915.9	907.0	900.6
12.5°	1020.6	995.3	967.7	944.4	922.5	904.0	885.0	877.3	860.5	852.0	834.6
15°	969.7	940.2	911.1	879.5	857.3	828.5	801.1	767.5	740.4	716.9	710.5
17.5°	914.0	877.5	848.3	811.3	773.2	724.8	693.0	673.5	657.2	644.8	635.6
20°	875.8	838.7	807.6	751.7	700.4	667.7	644.2	629.2	612.2	598.9	591.6
22.5°	835.8	796.9	754.5	692.2	652.2	625.9	605.0	587.8	576.3	565.9	559.3
25°	778.8	736.3	666.4	623.5	591.2	563.7	549.1	538.6	526.5	512.3	505.9
27.5°	718.7	651.1	600.9	569.0	538.1	520.2	507.2	491.5	480.6	474.3	467.5
30°	673.7	606.2	567.0	532.2	510.3	490.5	475.2	466.3	455.7	444.8	440.4
32.5°	623.5	569.6	532.0	503.0	480.9	464.0	451.9	437.4	429.8	423.1	413.8
35°	561.3	520.5	486.1	462.6	441.6	427.9	413.7	405.2	391.4	385.8	382.1
37.5°	508.5	473.1	447.5	422.7	406.1	390.9	382.2	368.7	362.7	354.9	347.2
40°	478.8	444.0	419.3	399.1	380.5	369.2	358.3	347.4	338.4	334.9	325.5
42.5°	448.4	420.1	395.4	373.2	360.8	348.8	335.0	327.0	317.7	311.9	306.1
45°	406.4	381.4	360.3	342.1	328.4	315.8	306.9	293.6	288.4	276.6	271.7
47.5°	369.6	346.2	326.1	308.9	295.4	287.2	274.3	263.8	255.4	248.2	242.0
50°	343.3	323.9	304.5	289.1	277.0	265.3	251.9	246.7	233.7	230.0	226.5
52.5°	319.4	301.0	283.1	268.1	256.0	244.5	232.8	225.9	217.2	213.6	211.0
55°	285.9	268.1	251.1	237.7	225.6	213.9	206.6	198.1	194.1	191.2	188.1
57.5°	252.2	236.2	223.2	209.7	197.5	188.2	179.7	174.7	170.5	166.8	162.9
60°	230.9	215.6	203.8	191.2	178.7	171.0	164.6	158.5	153.7	148.0	146.4
62.5°	208.3	194.8	184.1	171.8	161.0	153.9	147.7	142.0	136.2	127.9	125.6
65°	177.1	166.6	155.3	145.2	135.5	128.6	119.7	113.2	110.8	110.0	109.6
67.5°	149.0	139.0	129.3	119.0	110.1	103.8	99.3	98.2	96.6	96.1	95.0
70°	130.2	120.9	111.2	101.5	93.0	91.8	90.2	88.6	86.5	85.7	84.9
72.5°	113.4	103.8	94.0	86.3	82.6	81.1	79.5	77.9	76.5	75.7	75.2
75°	86.9	78.0	71.6	68.8	66.7	65.5	63.1	61.9	61.1	59.8	59.4
77.5°	62.6	57.6	54.6	52.8	50.7	49.4	48.0	46.8	45.9	45.7	45.1
80°	47.7	45.3	43.3	40.9	40.0	38.4	38.0	36.8	37.2	36.0	36.0
82.5°	37.1	34.0	32.2	31.1	30.3	29.1	28.6	28.0	28.1	27.3	27.3
85°	19.0	18.2	17.3	16.6	16.6	15.4	15.8	15.4	15.4	14.6	14.2
87.5°	6.9	6.7	6.2	6.3	6.4	6.2	6.3	6.0	6.1	6.2	5.9
90°	3.6	4.4	5.0	5.5	6.2	6.7	7.1	7.5	7.9	8.2	8.6
92.5°	6.6	6.7	7.0	7.3	7.5	7.8	8.1	8.2	8.5	8.6	8.8
95°	12.0	11.1	11.6	12.1	12.7	13.2	13.5	13.9	14.3	14.7	14.9
97.5°	15.7	12.8	14.0	15.2	16.5	17.7	18.0	18.3	18.6	18.9	19.1
100°	18.7	14.2	15.4	16.7	18.0	19.3	19.9	20.5	21.1	21.7	22.1
102.5°	69.1	62.7	52.0	41.3	30.6	19.8	20.6	21.4	22.2	23.0	23.4
105°	111.9	102.8	82.3	61.7	41.2	20.7	21.5	22.3	23.1	24.0	24.6
107.5°	138.9	127.5	102.8	78.2	53.6	28.9	28.0	27.3	26.4	25.5	25.3
110°	156.3	146.2	124.5	102.7	81.0	59.3	51.7	44.2	36.7	29.2	25.5



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	172.9	171.0	165.6	160.2	154.8	149.5	122.0	94.6	67.1	39.7	26.1
115°	199.8	201.4	203.3	205.2	207.0	208.9	174.0	139.3	104.4	69.6	49.4
117.5°	224.8	226.2	227.5	228.8	230.1	231.4	223.0	214.5	206.1	197.6	184.6
120°	241.5	242.8	244.2	245.5	246.8	248.2	249.1	250.0	250.9	251.8	247.2
122.5°	256.9	258.3	259.8	261.2	262.7	264.2	264.7	265.2	265.8	266.3	265.6
125°	279.2	280.4	281.9	283.3	284.7	286.1	286.6	287.2	287.7	288.2	288.6
127.5°	300.6	301.6	302.7	303.7	304.8	305.9	306.7	307.4	308.2	309.0	309.3
130°	314.3	315.3	316.2	317.0	317.8	318.6	319.4	320.3	321.1	321.9	322.3
132.5°	327.1	328.0	328.8	329.7	330.5	331.4	332.1	332.8	333.4	334.1	334.5
135°	345.5	346.3	347.1	347.8	348.4	349.1	349.8	350.6	351.3	352.1	352.4
137.5°	361.8	362.6	363.4	364.2	364.9	365.7	366.4	367.2	367.9	368.6	368.8
140°	372.5	373.2	374.1	374.9	375.7	376.5	377.2	377.9	378.6	379.2	379.4
142.5°	382.0	382.8	383.7	384.6	385.6	386.5	387.1	387.8	388.4	389.0	389.1
145°	394.8	395.5	396.7	398.0	399.3	400.5	401.1	401.6	402.1	402.7	402.7
147.5°	407.3	407.8	409.1	410.4	411.6	412.9	413.3	413.7	414.1	414.5	414.5
150°	415.0	415.3	416.6	417.8	419.0	420.2	420.6	421.1	421.5	422.0	422.1
152.5°	422.1	422.4	423.5	424.7	425.8	427.0	427.4	427.9	428.3	428.8	428.7
155°	432.4	432.5	433.4	434.3	435.2	436.1	436.6	437.0	437.4	437.9	437.8
157.5°	441.2	441.2	441.8	442.4	443.1	443.7	444.2	444.7	445.2	445.8	445.7
160°	446.5	446.5	446.9	447.4	447.8	448.3	448.8	449.2	449.6	450.1	450.0
162.5°	450.8	450.8	451.1	451.5	451.9	452.3	452.9	453.4	453.9	454.4	454.3
165°	456.6	456.5	456.8	457.0	457.2	457.4	458.0	458.5	459.0	459.5	459.5
167.5°	461.0	460.9	461.1	461.3	461.5	461.7	462.2	462.8	463.3	463.8	463.7
170°	463.4	463.3	463.4	463.6	463.7	463.9	464.4	464.9	465.5	466.0	465.9
172.5°	465.0	464.9	465.0	465.2	465.3	465.5	466.0	466.5	467.1	467.6	467.5
175°	466.8	466.7	466.8	467.0	467.1	467.2	467.8	468.3	468.8	469.4	469.3
177.5°	467.6	467.4	467.5	467.5	467.6	467.6	468.1	468.5	468.9	469.4	469.3
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1117.5	1118.2	1117.2	1117.8	1117.2	1118.2	1117.5	1121.1	1121.7	1122.4	1121.7
5°	1041.2	1036.4	1035.6	1034.4	1035.6	1036.4	1041.2	1043.3	1044.9	1048.1	1053.8
7.5°	950.2	949.4	947.5	944.6	947.5	949.4	950.2	957.1	962.7	968.9	980.5
10°	891.6	889.6	889.2	886.4	889.2	889.6	891.6	900.6	907.0	915.9	931.7
12.5°	823.1	810.0	808.7	801.6	808.7	810.0	823.1	834.6	852.0	860.5	877.3
15°	700.8	698.4	690.2	685.0	690.2	698.4	700.8	710.5	716.9	740.4	767.5
17.5°	630.9	623.0	620.4	619.3	620.4	623.0	630.9	635.6	644.8	657.2	673.5
20°	585.9	578.7	577.4	576.6	577.4	578.7	585.9	591.6	598.9	612.2	629.2
22.5°	554.8	547.2	544.2	541.7	544.2	547.2	554.8	559.3	565.9	576.3	587.8
25°	501.8	499.0	497.4	496.5	497.4	499.0	501.8	505.9	512.3	526.5	538.6
27.5°	460.3	454.1	452.9	450.8	452.9	454.1	460.3	467.5	474.3	480.6	491.5
30°	436.7	434.7	431.9	429.4	431.9	434.7	436.7	440.4	444.8	455.7	466.3
32.5°	408.9	407.2	404.7	403.5	404.7	407.2	408.9	413.8	423.1	429.8	437.4
35°	378.1	372.4	370.0	366.4	370.0	372.4	378.1	382.1	385.8	391.4	405.2
37.5°	345.5	342.5	339.1	340.3	339.1	342.5	345.5	347.2	354.9	362.7	368.7
40°	320.3	318.2	317.4	317.0	317.4	318.2	320.3	325.5	334.9	338.4	347.4
42.5°	300.2	294.6	292.6	292.5	292.6	294.6	300.2	306.1	311.9	317.7	327.0
45°	269.7	264.4	260.8	261.3	260.8	264.4	269.7	271.7	276.6	288.4	293.6
47.5°	238.5	238.4	236.1	236.8	236.1	238.4	238.5	242.0	248.2	255.4	263.8
50°	223.6	221.2	219.6	220.0	219.6	221.2	223.6	226.5	230.0	233.7	246.7
52.5°	209.4	207.3	206.0	207.7	206.0	207.3	209.4	211.0	213.6	217.2	225.9
55°	186.0	183.5	183.2	182.8	183.2	183.5	186.0	188.1	191.2	194.1	198.1
57.5°	159.9	158.3	155.8	154.8	155.8	158.3	159.9	162.9	166.8	170.5	174.7
60°	141.1	137.9	133.9	133.4	133.9	137.9	141.1	146.4	148.0	153.7	158.5
62.5°	124.0	123.3	122.6	122.5	122.6	123.3	124.0	125.6	127.9	136.2	142.0
65°	108.8	108.4	108.8	109.2	108.8	108.4	108.8	109.6	110.0	110.8	113.2
67.5°	94.8	94.0	93.3	93.6	93.3	94.0	94.8	95.0	96.1	96.6	98.2
70°	84.1	83.7	83.3	83.3	83.3	83.7	84.1	84.9	85.7	86.5	88.6
72.5°	73.8	73.7	73.3	73.0	73.3	73.7	73.8	75.2	75.7	76.5	77.9
75°	59.0	58.2	58.2	58.2	58.2	58.2	59.0	59.4	59.8	61.1	61.9
77.5°	45.0	44.6	44.1	43.8	44.1	44.6	45.0	45.1	45.7	45.9	46.8
80°	35.6	35.2	34.8	34.8	34.8	35.2	35.6	36.0	36.0	37.2	36.8
82.5°	27.2	26.8	26.7	26.4	26.7	26.8	27.2	27.3	27.3	28.1	28.0
85°	14.6	15.0	14.6	15.4	14.6	15.0	14.6	14.2	14.6	15.4	15.4
87.5°	5.9	5.6	6.0	5.7	6.0	5.6	5.9	5.9	6.2	6.1	6.0
90°	8.7	8.9	9.0	9.1	9.0	8.9	8.7	8.6	8.2	7.9	7.5
92.5°	8.9	9.0	9.0	9.1	9.0	9.0	8.9	8.8	8.6	8.5	8.2
95°	14.8	14.7	14.7	14.6	14.7	14.7	14.8	14.9	14.7	14.3	13.9
97.5°	19.2	19.3	19.3	19.4	19.3	19.3	19.2	19.1	18.9	18.6	18.3
100°	22.3	22.4	22.5	22.7	22.5	22.4	22.3	22.1	21.7	21.1	20.5
102.5°	23.7	23.9	24.1	24.3	24.1	23.9	23.7	23.4	23.0	22.2	21.4
105°	24.8	25.1	25.4	25.7	25.4	25.1	24.8	24.6	24.0	23.1	22.3
107.5°	25.6	25.9	26.1	26.5	26.1	25.9	25.6	25.3	25.5	26.4	27.3
110°	25.8	26.1	26.5	26.8	26.5	26.1	25.8	25.5	29.2	36.7	44.2



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	26.3	26.5	26.8	27.0	26.8	26.5	26.3	26.1	39.7	67.1	94.6
115°	44.0	38.6	33.2	27.7	33.2	38.6	44.0	49.4	69.6	104.4	139.3
117.5°	166.8	148.9	131.2	113.4	131.2	148.9	166.8	184.6	197.6	206.1	214.5
120°	237.0	226.9	216.7	206.5	216.7	226.9	237.0	247.2	251.8	250.9	250.0
122.5°	263.6	261.7	259.7	257.7	259.7	261.7	263.6	265.6	266.3	265.8	265.2
125°	288.8	289.1	289.3	289.5	289.3	289.1	288.8	288.6	288.2	287.7	287.2
127.5°	309.4	309.4	309.5	309.5	309.5	309.4	309.4	309.3	309.0	308.2	307.4
130°	322.3	322.2	322.1	322.0	322.1	322.2	322.3	322.3	321.9	321.1	320.3
132.5°	334.4	334.3	334.3	334.2	334.3	334.3	334.4	334.5	334.1	333.4	332.8
135°	352.3	352.1	352.0	351.8	352.0	352.1	352.3	352.4	352.1	351.3	350.6
137.5°	368.6	368.4	368.1	367.8	368.1	368.4	368.6	368.8	368.6	367.9	367.2
140°	379.0	378.6	378.3	377.9	378.3	378.6	379.0	379.4	379.2	378.6	377.9
142.5°	388.7	388.4	388.0	387.6	388.0	388.4	388.7	389.1	389.0	388.4	387.8
145°	402.3	402.0	401.6	401.2	401.6	402.0	402.3	402.7	402.7	402.1	401.6
147.5°	414.2	413.8	413.5	413.2	413.5	413.8	414.2	414.5	414.5	414.1	413.7
150°	421.7	421.3	420.9	420.6	420.9	421.3	421.7	422.1	422.0	421.5	421.1
152.5°	428.3	427.8	427.2	426.7	427.2	427.8	428.3	428.7	428.8	428.3	427.9
155°	437.2	436.7	436.0	435.5	436.0	436.7	437.2	437.8	437.9	437.4	437.0
157.5°	445.1	444.5	443.9	443.4	443.9	444.5	445.1	445.7	445.8	445.2	444.7
160°	449.6	449.0	448.5	448.0	448.5	449.0	449.6	450.0	450.1	449.6	449.2
162.5°	453.7	453.0	452.4	451.8	452.4	453.0	453.7	454.3	454.4	453.9	453.4
165°	459.0	458.5	458.0	457.4	458.0	458.5	459.0	459.5	459.5	459.0	458.5
167.5°	463.0	462.4	461.7	461.1	461.7	462.4	463.0	463.7	463.8	463.3	462.8
170°	465.2	464.5	463.9	463.2	463.9	464.5	465.2	465.9	466.0	465.5	464.9
172.5°	466.8	466.2	465.5	464.9	465.5	466.2	466.8	467.5	467.6	467.1	466.5
175°	468.5	467.8	467.0	466.3	467.0	467.8	468.5	469.3	469.4	468.8	468.3
177.5°	468.7	468.2	467.6	467.1	467.6	468.2	468.7	469.3	469.4	468.9	468.5
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1119.1	1123.6	1130.4	1134.3	1140.8	1145.0	1147.3	1151.5	1153.7	1161.8	1170.3
5°	1056.6	1063.1	1074.4	1084.9	1096.2	1107.9	1116.5	1126.2	1135.0	1150.4	1166.6
7.5°	985.0	994.0	1011.5	1028.3	1048.0	1064.5	1079.2	1095.7	1110.6	1132.6	1155.6
10°	931.3	947.1	970.1	985.9	1011.8	1028.3	1051.4	1069.5	1090.2	1119.3	1145.2
12.5°	885.0	904.0	922.5	944.4	967.7	995.3	1020.6	1044.0	1068.5	1098.6	1129.0
15°	801.1	828.5	857.3	879.5	911.1	940.2	969.7	1001.2	1031.2	1067.1	1106.8
17.5°	693.0	724.8	773.2	811.3	848.3	877.5	914.0	952.2	987.5	1030.9	1075.0
20°	644.2	667.7	700.4	751.7	807.6	838.7	875.8	917.9	958.4	1005.7	1053.0
22.5°	605.0	625.9	652.2	692.2	754.5	796.9	835.8	878.5	925.3	973.7	1026.1
25°	549.1	563.7	591.2	623.5	666.4	736.3	778.8	821.7	872.7	924.4	984.2
27.5°	507.2	520.2	538.1	569.0	600.9	651.1	718.7	765.4	816.2	874.4	936.5
30°	475.2	490.5	510.3	532.2	567.0	606.2	673.7	727.9	778.0	837.9	904.2
32.5°	451.9	464.0	480.9	503.0	532.0	569.6	623.5	689.4	738.2	801.3	870.5
35°	413.7	427.9	441.6	462.6	486.1	520.5	561.3	631.6	680.2	742.4	812.0
37.5°	382.2	390.9	406.1	422.7	447.5	473.1	508.5	571.6	624.1	685.2	756.5
40°	358.3	369.2	380.5	399.1	419.3	444.0	478.8	525.7	585.9	645.8	715.3
42.5°	335.0	348.8	360.8	373.2	395.4	420.1	448.4	488.1	549.7	606.3	673.9
45°	306.9	315.8	328.4	342.1	360.3	381.4	406.4	441.2	500.2	549.1	612.6
47.5°	274.3	287.2	295.4	308.9	326.1	346.2	369.6	399.6	447.4	493.3	552.2
50°	251.9	265.3	277.0	289.1	304.5	323.9	343.3	372.4	410.8	459.0	514.0
52.5°	232.8	244.5	256.0	268.1	283.1	301.0	319.4	344.9	377.9	422.1	475.5
55°	206.6	213.9	225.6	237.7	251.1	268.1	285.9	307.3	335.6	372.8	416.1
57.5°	179.7	188.2	197.5	209.7	223.2	236.2	252.2	271.6	294.0	327.6	364.6
60°	164.6	171.0	178.7	191.2	203.8	215.6	230.9	247.1	268.1	297.2	328.8
62.5°	147.7	153.9	161.0	171.8	184.1	194.8	208.3	225.4	243.2	269.7	297.4
65°	119.7	128.6	135.5	145.2	155.3	166.6	177.1	190.8	206.6	227.7	252.3
67.5°	99.3	103.8	110.1	119.0	129.3	139.0	149.0	159.7	173.4	189.6	209.2
70°	90.2	91.8	93.0	101.5	111.2	120.9	130.2	140.3	152.0	165.4	182.4
72.5°	79.5	81.1	82.6	86.3	94.0	103.8	113.4	120.9	132.0	143.1	156.9
75°	63.1	65.5	66.7	68.8	71.6	78.0	86.9	94.2	100.7	109.2	120.1
77.5°	48.0	49.4	50.7	52.8	54.6	57.6	62.6	69.2	75.2	80.2	87.7
80°	38.0	38.4	40.0	40.9	43.3	45.3	47.7	53.0	59.0	61.1	66.3
82.5°	28.6	29.1	30.3	31.1	32.2	34.0	37.1	38.4	43.2	45.9	49.2
85°	15.8	15.4	16.6	16.6	17.3	18.2	19.0	21.0	22.3	25.5	26.3
87.5°	6.3	6.2	6.4	6.3	6.2	6.7	6.9	7.1	7.5	8.3	9.4
90°	7.1	6.7	6.2	5.5	5.0	4.4	3.6	2.9	2.0	1.2	0.3
92.5°	8.1	7.8	7.5	7.3	7.0	6.7	6.6	6.6	6.7	6.7	6.8
95°	13.5	13.2	12.7	12.1	11.6	11.1	12.0	14.6	17.0	19.5	22.0
97.5°	18.0	17.7	16.5	15.2	14.0	12.8	15.7	22.7	29.7	36.7	43.6
100°	19.9	19.3	18.0	16.7	15.4	14.2	18.7	29.0	39.3	49.6	60.0
102.5°	20.6	19.8	30.6	41.3	52.0	62.7	69.1	71.3	73.4	75.7	77.8
105°	21.5	20.7	41.2	61.7	82.3	102.8	111.9	109.7	107.4	105.2	102.9
107.5°	28.0	28.9	53.6	78.2	102.8	127.5	138.9	137.0	135.2	133.4	131.6
110°	51.7	59.3	81.0	102.7	124.5	146.2	156.3	154.7	153.1	151.5	150.0



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	122.0	149.5	154.8	160.2	165.6	171.0	172.9	171.5	170.2	168.7	167.3
115°	174.0	208.9	207.0	205.2	203.3	201.4	199.8	198.5	197.3	196.0	194.7
117.5°	223.0	231.4	230.1	228.8	227.5	226.2	224.8	223.4	222.0	220.5	219.1
120°	249.1	248.2	246.8	245.5	244.2	242.8	241.5	240.4	239.2	238.1	237.0
122.5°	264.7	264.2	262.7	261.2	259.8	258.3	256.9	255.7	254.5	253.3	252.2
125°	286.6	286.1	284.7	283.3	281.9	280.4	279.2	278.2	277.3	276.2	275.3
127.5°	306.7	305.9	304.8	303.7	302.7	301.6	300.6	299.4	298.3	297.3	296.2
130°	319.4	318.6	317.8	317.0	316.2	315.3	314.3	313.1	311.9	310.7	309.5
132.5°	332.1	331.4	330.5	329.7	328.8	328.0	327.1	326.1	325.0	324.0	323.1
135°	349.8	349.1	348.4	347.8	347.1	346.3	345.5	344.2	343.0	341.8	340.6
137.5°	366.4	365.7	364.9	364.2	363.4	362.6	361.8	361.0	360.1	359.3	358.5
140°	377.2	376.5	375.7	374.9	374.1	373.2	372.5	371.9	371.3	370.7	370.1
142.5°	387.1	386.5	385.6	384.6	383.7	382.8	382.0	381.4	380.9	380.4	379.9
145°	401.1	400.5	399.3	398.0	396.7	395.5	394.8	394.9	395.0	395.1	395.1
147.5°	413.3	412.9	411.6	410.4	409.1	407.8	407.3	407.7	407.9	408.2	408.4
150°	420.6	420.2	419.0	417.8	416.6	415.3	415.0	415.6	416.1	416.6	417.2
152.5°	427.4	427.0	425.8	424.7	423.5	422.4	422.1	422.7	423.3	423.9	424.5
155°	436.6	436.1	435.2	434.3	433.4	432.5	432.4	433.1	433.7	434.4	435.1
157.5°	444.2	443.7	443.1	442.4	441.8	441.2	441.2	441.7	442.3	442.8	443.4
160°	448.8	448.3	447.8	447.4	446.9	446.5	446.5	446.9	447.4	447.8	448.3
162.5°	452.9	452.3	451.9	451.5	451.1	450.8	450.8	451.3	451.7	452.2	452.7
165°	458.0	457.4	457.2	457.0	456.8	456.5	456.6	457.1	457.6	458.0	458.4
167.5°	462.2	461.7	461.5	461.3	461.1	460.9	461.0	461.4	461.9	462.3	462.8
170°	464.4	463.9	463.7	463.6	463.4	463.3	463.4	463.9	464.3	464.8	465.2
172.5°	466.0	465.5	465.3	465.2	465.0	464.9	465.0	465.5	466.0	466.4	466.8
175°	467.8	467.2	467.1	467.0	466.8	466.7	466.8	467.4	467.9	468.4	469.0
177.5°	468.1	467.6	467.6	467.5	467.5	467.4	467.6	468.0	468.4	468.9	469.3
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1170.6	1171.6	1178.1	1180.9	1186.8	1189.0	1191.6	1191.0	1191.0	1192.2	1201.3
5°	1173.1	1181.1	1193.3	1205.0	1216.3	1226.1	1232.6	1239.0	1241.4	1253.2	1263.7
7.5°	1168.9	1183.8	1203.8	1221.7	1243.1	1259.9	1273.7	1286.3	1294.9	1311.9	1329.4
10°	1163.4	1184.4	1207.0	1230.1	1259.6	1281.8	1304.5	1321.9	1327.5	1353.0	1367.6
12.5°	1152.4	1180.5	1209.3	1239.1	1268.0	1298.7	1323.6	1341.0	1360.9	1383.8	1410.6
15°	1135.9	1168.2	1205.9	1244.3	1285.5	1322.7	1349.4	1379.7	1401.5	1426.6	1450.1
17.5°	1112.1	1153.8	1201.7	1246.1	1293.8	1333.8	1370.5	1399.6	1415.0	1429.3	1432.7
20°	1093.4	1138.3	1194.5	1247.1	1294.8	1340.9	1377.3	1401.5	1405.6	1406.0	1384.6
22.5°	1073.0	1123.7	1182.6	1236.4	1293.5	1344.8	1373.1	1383.5	1367.4	1340.0	1298.5
25°	1035.6	1094.2	1162.6	1224.0	1286.3	1334.8	1344.6	1326.4	1270.1	1211.1	1136.3
27.5°	995.0	1060.9	1134.2	1202.5	1268.8	1298.9	1277.9	1212.4	1111.1	1023.1	916.5
30°	965.3	1039.3	1111.2	1187.6	1249.1	1262.0	1213.9	1117.3	999.2	866.6	760.3
32.5°	931.3	1008.8	1087.9	1167.0	1218.4	1205.8	1126.2	1007.3	868.9	738.5	637.9
35°	882.7	962.8	1048.1	1127.4	1160.2	1105.6	986.7	831.8	690.2	568.5	499.4
37.5°	826.7	913.9	1002.6	1075.4	1073.0	982.1	820.1	660.3	541.3	469.3	420.1
40°	786.9	875.0	970.9	1032.4	1006.1	887.6	712.1	561.3	474.4	416.9	380.9
42.5°	748.8	837.2	932.4	981.3	935.6	789.9	615.1	496.9	425.2	380.3	351.2
45°	683.8	777.2	865.4	892.5	810.8	650.2	497.4	411.6	363.9	330.8	310.5
47.5°	620.3	712.2	792.7	793.1	682.6	527.3	419.5	356.2	315.5	289.9	275.1
50°	581.5	668.8	736.3	725.9	600.5	469.1	375.3	320.7	286.7	266.9	251.5
52.5°	537.8	622.6	681.0	651.1	530.9	412.8	335.5	289.6	261.5	244.2	230.5
55°	474.4	549.5	590.8	545.5	433.1	343.3	283.4	247.5	226.5	211.9	200.2
57.5°	411.9	474.0	499.9	447.3	356.7	284.7	239.8	212.8	191.9	181.5	175.4
60°	372.8	425.8	444.0	385.8	310.1	249.1	212.3	187.2	171.8	165.0	158.9
62.5°	334.3	377.6	385.2	331.8	270.4	218.0	186.4	165.2	155.0	148.5	142.8
65°	277.4	308.6	304.9	262.1	213.9	173.1	150.0	137.0	129.4	120.1	110.0
67.5°	228.4	247.4	235.9	203.8	163.3	134.5	119.5	109.6	100.1	91.3	89.0
70°	197.3	208.3	196.1	166.6	133.9	112.8	100.7	89.0	83.3	81.3	77.6
72.5°	167.5	171.3	158.3	132.9	108.9	93.4	81.6	75.0	72.0	70.3	68.0
75°	125.8	122.9	111.6	91.8	75.7	65.1	61.5	59.0	57.0	55.4	54.2
77.5°	88.3	84.2	74.1	61.2	52.7	47.6	45.5	44.1	43.2	42.4	41.2
80°	66.3	63.5	53.4	43.6	40.0	37.6	36.4	34.8	34.8	34.0	32.7
82.5°	48.6	45.4	36.5	32.0	30.0	28.5	27.6	26.7	26.4	26.5	25.7
85°	25.5	20.6	18.2	17.3	16.2	15.4	15.8	15.0	15.0	15.0	14.6
87.5°	8.0	6.6	6.4	6.3	6.7	6.8	6.6	6.7	7.2	6.9	7.4
90°	1.2	2.0	2.9	3.6	4.4	5.0	5.5	6.2	6.7	7.1	7.5
92.5°	6.7	6.7	6.6	6.6	6.7	7.0	7.3	7.5	7.8	8.1	8.2
95°	19.5	17.0	14.6	12.0	11.1	11.6	12.1	12.7	13.2	13.5	13.9
97.5°	36.7	29.7	22.7	15.7	12.8	14.0	15.2	16.5	17.7	18.0	18.3
100°	49.6	39.3	29.0	18.7	14.2	15.4	16.7	18.0	19.3	19.9	20.5
102.5°	75.7	73.4	71.3	69.1	62.7	52.0	41.3	30.6	19.8	20.6	21.4
105°	105.2	107.4	109.7	111.9	102.8	82.3	61.7	41.2	20.7	21.5	22.3
107.5°	133.4	135.2	137.0	138.9	127.5	102.8	78.2	53.6	28.9	28.0	27.3
110°	151.5	153.1	154.7	156.3	146.2	124.5	102.7	81.0	59.3	51.7	44.2



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	168.7	170.2	171.5	172.9	171.0	165.6	160.2	154.8	149.5	122.0	94.6
115°	196.0	197.3	198.5	199.8	201.4	203.3	205.2	207.0	208.9	174.0	139.3
117.5°	220.5	222.0	223.4	224.8	226.2	227.5	228.8	230.1	231.4	223.0	214.5
120°	238.1	239.2	240.4	241.5	242.8	244.2	245.5	246.8	248.2	249.1	250.0
122.5°	253.3	254.5	255.7	256.9	258.3	259.8	261.2	262.7	264.2	264.7	265.2
125°	276.2	277.3	278.2	279.2	280.4	281.9	283.3	284.7	286.1	286.6	287.2
127.5°	297.3	298.3	299.4	300.6	301.6	302.7	303.7	304.8	305.9	306.7	307.4
130°	310.7	311.9	313.1	314.3	315.3	316.2	317.0	317.8	318.6	319.4	320.3
132.5°	324.0	325.0	326.1	327.1	328.0	328.8	329.7	330.5	331.4	332.1	332.8
135°	341.8	343.0	344.2	345.5	346.3	347.1	347.8	348.4	349.1	349.8	350.6
137.5°	359.3	360.1	361.0	361.8	362.6	363.4	364.2	364.9	365.7	366.4	367.2
140°	370.7	371.3	371.9	372.5	373.2	374.1	374.9	375.7	376.5	377.2	377.9
142.5°	380.4	380.9	381.4	382.0	382.8	383.7	384.6	385.6	386.5	387.1	387.8
145°	395.1	395.0	394.9	394.8	395.5	396.7	398.0	399.3	400.5	401.1	401.6
147.5°	408.2	407.9	407.7	407.3	407.8	409.1	410.4	411.6	412.9	413.3	413.7
150°	416.6	416.1	415.6	415.0	415.3	416.6	417.8	419.0	420.2	420.6	421.1
152.5°	423.9	423.3	422.7	422.1	422.4	423.5	424.7	425.8	427.0	427.4	427.9
155°	434.4	433.7	433.1	432.4	432.5	433.4	434.3	435.2	436.1	436.6	437.0
157.5°	442.8	442.3	441.7	441.2	441.2	441.8	442.4	443.1	443.7	444.2	444.7
160°	447.8	447.4	446.9	446.5	446.5	446.9	447.4	447.8	448.3	448.8	449.2
162.5°	452.2	451.7	451.3	450.8	450.8	451.1	451.5	451.9	452.3	452.9	453.4
165°	458.0	457.6	457.1	456.6	456.5	456.8	457.0	457.2	457.4	458.0	458.5
167.5°	462.3	461.9	461.4	461.0	460.9	461.1	461.3	461.5	461.7	462.2	462.8
170°	464.8	464.3	463.9	463.4	463.3	463.4	463.6	463.7	463.9	464.4	464.9
172.5°	466.4	466.0	465.5	465.0	464.9	465.0	465.2	465.3	465.5	466.0	466.5
175°	468.4	467.9	467.4	466.8	466.7	466.8	467.0	467.1	467.2	467.8	468.3
177.5°	468.9	468.4	468.0	467.6	467.4	467.5	467.5	467.6	467.6	468.1	468.5
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9	467.9



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1204.5	1208.7	1210.7	1210.7	1213.0	1212.0	1211.0
5°	1273.7	1281.4	1283.1	1290.4	1295.6	1294.0	1294.8
7.5°	1342.6	1354.9	1367.1	1372.8	1373.6	1376.9	1378.1
10°	1385.0	1395.1	1414.1	1411.3	1425.4	1433.5	1420.1
12.5°	1425.8	1439.4	1452.5	1456.2	1464.3	1466.8	1461.6
15°	1462.6	1469.9	1470.7	1468.7	1471.1	1469.1	1461.4
17.5°	1428.1	1416.3	1392.4	1381.1	1372.1	1358.8	1353.5
20°	1371.2	1336.4	1296.0	1279.8	1260.8	1223.6	1232.6
22.5°	1248.3	1208.6	1168.2	1121.0	1098.4	1063.2	1061.0
25°	1057.0	988.7	913.5	860.9	830.2	795.0	779.7
27.5°	821.8	735.8	674.1	642.9	614.6	586.7	585.5
30°	667.2	602.5	554.8	528.1	510.7	499.0	501.5
32.5°	562.4	518.1	485.9	463.7	450.9	442.0	441.9
35°	459.8	429.4	408.8	399.5	390.2	383.7	384.1
37.5°	393.5	375.3	363.8	353.5	347.7	344.5	342.8
40°	359.5	344.5	335.6	329.5	324.7	320.3	319.5
42.5°	332.6	320.3	311.3	306.6	302.1	298.9	298.1
45°	295.2	285.1	277.0	271.7	269.7	266.9	266.9
47.5°	262.6	252.6	246.4	243.0	239.6	237.7	237.6
50°	240.6	232.9	227.3	225.2	222.4	221.2	220.8
52.5°	220.9	215.2	211.1	209.7	208.5	206.9	207.2
55°	194.1	190.8	189.3	188.1	186.0	183.5	185.2
57.5°	171.5	168.8	164.5	160.7	158.8	157.1	157.7
60°	155.7	150.0	144.3	139.9	138.7	135.1	135.1
62.5°	135.6	127.7	120.7	118.3	117.0	115.3	115.0
65°	104.3	101.1	99.5	97.8	97.0	97.0	96.3
67.5°	86.4	85.2	83.4	82.9	82.1	81.9	81.7
70°	76.4	74.8	74.0	73.6	72.8	73.2	72.0
72.5°	66.7	65.4	65.3	64.2	63.7	63.8	62.9
75°	52.6	52.6	52.1	51.7	50.9	50.5	50.9
77.5°	40.4	40.5	39.8	39.7	39.6	39.7	39.3
80°	32.3	32.7	32.3	31.9	31.5	31.9	31.5
82.5°	25.6	25.0	24.9	24.8	24.7	24.5	24.4
85°	14.6	15.0	14.6	14.2	14.2	14.2	14.6
87.5°	7.1	7.1	7.2	7.2	7.3	7.3	7.0
90°	7.9	8.2	8.6	8.7	8.9	9.0	9.1
92.5°	8.5	8.6	8.8	8.9	9.0	9.0	9.1
95°	14.3	14.7	14.9	14.8	14.7	14.7	14.6
97.5°	18.6	18.9	19.1	19.2	19.3	19.3	19.4
100°	21.1	21.7	22.1	22.3	22.4	22.5	22.7
102.5°	22.2	23.0	23.4	23.7	23.9	24.1	24.3
105°	23.1	24.0	24.6	24.8	25.1	25.4	25.7
107.5°	26.4	25.5	25.3	25.6	25.9	26.1	26.5
110°	36.7	29.2	25.5	25.8	26.1	26.5	26.8



TEST NUMBER: P331805-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	67.1	39.7	26.1	26.3	26.5	26.8	27.0
115°	104.4	69.6	49.4	44.0	38.6	33.2	27.7
117.5°	206.1	197.6	184.6	166.8	148.9	131.2	113.4
120°	250.9	251.8	247.2	237.0	226.9	216.7	206.5
122.5°	265.8	266.3	265.6	263.6	261.7	259.7	257.7
125°	287.7	288.2	288.6	288.8	289.1	289.3	289.5
127.5°	308.2	309.0	309.3	309.4	309.4	309.5	309.5
130°	321.1	321.9	322.3	322.3	322.2	322.1	322.0
132.5°	333.4	334.1	334.5	334.4	334.3	334.3	334.2
135°	351.3	352.1	352.4	352.3	352.1	352.0	351.8
137.5°	367.9	368.6	368.8	368.6	368.4	368.1	367.8
140°	378.6	379.2	379.4	379.0	378.6	378.3	377.9
142.5°	388.4	389.0	389.1	388.7	388.4	388.0	387.6
145°	402.1	402.7	402.7	402.3	402.0	401.6	401.2
147.5°	414.1	414.5	414.5	414.2	413.8	413.5	413.2
150°	421.5	422.0	422.1	421.7	421.3	420.9	420.6
152.5°	428.3	428.8	428.7	428.3	427.8	427.2	426.7
155°	437.4	437.9	437.8	437.2	436.7	436.0	435.5
157.5°	445.2	445.8	445.7	445.1	444.5	443.9	443.4
160°	449.6	450.1	450.0	449.6	449.0	448.5	448.0
162.5°	453.9	454.4	454.3	453.7	453.0	452.4	451.8
165°	459.0	459.5	459.5	459.0	458.5	458.0	457.4
167.5°	463.3	463.8	463.7	463.0	462.4	461.7	461.1
170°	465.5	466.0	465.9	465.2	464.5	463.9	463.2
172.5°	467.1	467.6	467.5	466.8	466.2	465.5	464.9
175°	468.8	469.4	469.3	468.5	467.8	467.0	466.3
177.5°	468.9	469.4	469.3	468.7	468.2	467.6	467.1
180°	467.9	467.9	467.9	467.9	467.9	467.9	467.9

(END OF REPORT)