

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331806-927

Luminaire Tested: **S122RDIW-S675D435U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331806-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D435U927-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3202.2 lumens  
Efficiency: N/A  
Efficacy: 84.9 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	102	98	94	91	95	92	89	86	81	78	76	71	69	68	62	60	59	55
2	93	86	81	76	87	81	76	72	72	68	65	63	61	58	55	53	52	48
3	86	77	70	65	80	73	67	62	65	60	56	57	53	50	50	47	45	42
4	79	69	61	56	74	65	59	53	58	53	49	52	48	44	46	42	40	37
5	73	62	54	49	69	59	52	47	53	47	43	47	43	39	42	38	36	33
6	68	56	49	43	64	53	46	41	48	42	38	43	38	35	38	35	32	29
7	63	51	44	38	59	49	42	37	44	38	34	40	35	32	35	32	29	27
8	59	47	40	34	55	45	38	33	41	35	31	37	32	29	33	29	26	24
9	55	43	36	31	52	41	35	30	38	32	28	34	29	26	31	27	24	22
10	52	40	33	28	49	38	32	27	35	29	26	32	27	24	29	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	18791	18791	18791	18791
5°	20985	18908	16765	18908
10°	23282	18775	14532	18775
15°	24428	18501	11450	18501
20°	21179	18093	9907	18093
25°	13890	17533	8845	17533
30°	9350	16858	8006	16858
35°	7571	16005	7222	16005
40°	6734	15076	6681	15076
45°	6094	13988	5966	13988
50°	5546	12911	5526	12911
55°	5213	11713	5146	11713
60°	4363	10618	4308	10618
65°	3679	9639	4172	9639
70°	3399	8611	3932	8611
75°	3175	7492	3631	7492
80°	2929	6165	3236	6165
85°	2705	4872	2853	4872



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.3	3.4
10°-20°	307.4	9.6
20°-30°	396.1	12.4
30°-40°	376.4	11.8
40°-50°	322.5	10.1
50°-60°	245.6	7.7
60°-70°	155.2	4.8
70°-80°	77.5	2.4
80°-90°	21.9	0.7
90°-100°	27.0	0.8
100°-110°	83.7	2.6
110°-120°	143.1	4.5
120°-130°	188.1	5.9
130°-140°	211.2	6.6
140°-150°	207.1	6.5
150°-160°	173.7	5.4
160°-170°	115.2	3.6
170°-180°	40.3	1.3
0°-30°	813.8	25.4
0°-40°	1190.3	37.2
0°-60°	1758.3	54.9
0°-90°	2013.0	62.9
90°-120°	253.7	7.9
90°-150°	860.1	26.9
90°-180°	1189.0	37.1
0°-180°	3202.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1164	1164	1164	1164	1164	
5°	1295	1167	1034	1167	1295	128
15°	1461	1107	685	1107	1461	394
25°	780	984	496	984	780	370
35°	384	812	366	812	384	246
45°	267	613	261	613	267	207
55°	185	416	183	416	185	163
65°	96	252	109	252	96	98
75°	51	120	58	120	51	54
85°	15	26	15	26	15	16
90°	12	0	12	0	12	6
95°	22	19	22	19	22	25
105°	80	77	80	77	80	84
115°	144	144	144	144	144	142
125°	210	209	210	209	210	187
135°	274	270	274	270	274	211
145°	332	328	332	328	332	207
155°	378	375	378	375	378	174
165°	408	408	408	408	408	115
175°	423	425	423	425	423	40
180°	425	425	425	425	425	



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1211.0	1212.0	1213.0	1210.7	1210.7	1208.7	1204.5	1201.3	1192.2	1191.0	1191.0
5°	1294.8	1294.0	1295.6	1290.4	1283.1	1281.4	1273.7	1263.7	1253.2	1241.4	1239.0
7.5°	1378.1	1376.9	1373.6	1372.8	1367.1	1354.9	1342.6	1329.4	1311.9	1294.9	1286.3
10°	1420.1	1433.5	1425.4	1411.3	1414.1	1395.1	1385.0	1367.6	1353.0	1327.5	1321.9
12.5°	1461.6	1466.8	1464.3	1456.2	1452.5	1439.4	1425.8	1410.6	1383.8	1360.9	1341.0
15°	1461.4	1469.1	1471.1	1468.7	1470.7	1469.9	1462.6	1450.1	1426.6	1401.5	1379.7
17.5°	1353.5	1358.8	1372.1	1381.1	1392.4	1416.3	1428.1	1432.7	1429.3	1415.0	1399.6
20°	1232.6	1223.6	1260.8	1279.8	1296.0	1336.4	1371.2	1384.6	1406.0	1405.6	1401.5
22.5°	1061.0	1063.2	1098.4	1121.0	1168.2	1208.6	1248.3	1298.5	1340.0	1367.4	1383.5
25°	779.7	795.0	830.2	860.9	913.5	988.7	1057.0	1136.3	1211.1	1270.1	1326.4
27.5°	585.5	586.7	614.6	642.9	674.1	735.8	821.8	916.5	1023.1	1111.1	1212.4
30°	501.5	499.0	510.7	528.1	554.8	602.5	667.2	760.3	866.6	999.2	1117.3
32.5°	441.9	442.0	450.9	463.7	485.9	518.1	562.4	637.9	738.5	868.9	1007.3
35°	384.1	383.7	390.2	399.5	408.8	429.4	459.8	499.4	568.5	690.2	831.8
37.5°	342.8	344.5	347.7	353.5	363.8	375.3	393.5	420.1	469.3	541.3	660.3
40°	319.5	320.3	324.7	329.5	335.6	344.5	359.5	380.9	416.9	474.4	561.3
42.5°	298.1	298.9	302.1	306.6	311.3	320.3	332.6	351.2	380.3	425.2	496.9
45°	266.9	266.9	269.7	271.7	277.0	285.1	295.2	310.5	330.8	363.9	411.6
47.5°	237.6	237.7	239.6	243.0	246.4	252.6	262.6	275.1	289.9	315.5	356.2
50°	220.8	221.2	222.4	225.2	227.3	232.9	240.6	251.5	266.9	286.7	320.7
52.5°	207.2	206.9	208.5	209.7	211.1	215.2	220.9	230.5	244.2	261.5	289.6
55°	185.2	183.5	186.0	188.1	189.3	190.8	194.1	200.2	211.9	226.5	247.5
57.5°	157.7	157.1	158.8	160.7	164.5	168.8	171.5	175.4	181.5	191.9	212.8
60°	135.1	135.1	138.7	139.9	144.3	150.0	155.7	158.9	165.0	171.8	187.2
62.5°	115.0	115.3	117.0	118.3	120.7	127.7	135.6	142.8	148.5	155.0	165.2
65°	96.3	97.0	97.0	97.8	99.5	101.1	104.3	110.0	120.1	129.4	137.0
67.5°	81.7	81.9	82.1	82.9	83.4	85.2	86.4	89.0	91.3	100.1	109.6
70°	72.0	73.2	72.8	73.6	74.0	74.8	76.4	77.6	81.3	83.3	89.0
72.5°	62.9	63.8	63.7	64.2	65.3	65.4	66.7	68.0	70.3	72.0	75.0
75°	50.9	50.5	50.9	51.7	52.1	52.6	52.6	54.2	55.4	57.0	59.0
77.5°	39.3	39.7	39.6	39.7	39.8	40.5	40.4	41.2	42.4	43.2	44.1
80°	31.5	31.9	31.5	31.9	32.3	32.7	32.3	32.7	34.0	34.8	34.8
82.5°	24.4	24.5	24.7	24.8	24.9	25.0	25.6	25.7	26.5	26.4	26.7
85°	14.6	14.2	14.2	14.2	14.6	15.0	14.6	14.6	15.0	15.0	15.0
87.5°	7.6	7.9	7.9	7.9	7.8	7.9	7.9	8.2	8.0	8.3	7.7
90°	12.2	12.1	12.0	12.0	11.9	12.0	12.1	12.3	12.4	12.6	10.8
92.5°	11.6	11.6	11.6	11.6	11.6	11.6	11.5	11.5	11.4	11.4	11.0
95°	22.3	22.4	22.6	22.7	22.9	23.0	23.0	23.0	23.0	23.0	22.8
97.5°	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.3
100°	49.2	49.3	49.4	49.4	49.5	49.5	49.5	49.5	49.5	49.5	49.3
102.5°	61.2	61.3	61.4	61.5	61.6	61.6	61.5	61.4	61.4	61.3	61.0
105°	79.7	79.7	79.7	79.7	79.7	79.6	79.5	79.3	79.1	79.0	78.8
107.5°	97.0	97.4	97.8	98.2	98.5	98.7	98.6	98.5	98.5	98.4	98.4
110°	110.5	110.7	111.0	111.2	111.5	111.6	111.6	111.6	111.6	111.6	111.6



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.5	123.7	123.8	124.0	124.1	124.4	124.5	124.8	124.9	125.1	125.2
115°	143.5	143.8	144.0	144.3	144.5	144.7	144.7	144.8	144.9	145.0	145.1
117.5°	162.7	163.0	163.2	163.4	163.7	163.9	164.1	164.3	164.5	164.7	165.1
120°	176.3	176.5	176.7	177.0	177.2	177.3	177.3	177.3	177.3	177.3	177.9
122.5°	189.4	189.6	189.8	190.0	190.1	190.3	190.5	190.7	190.9	191.1	191.5
125°	209.6	209.7	209.8	209.8	209.9	210.1	210.3	210.6	210.8	211.0	211.3
127.5°	228.0	228.2	228.5	228.7	229.0	229.3	229.6	229.8	230.1	230.4	230.7
130°	241.2	241.5	241.9	242.2	242.5	242.7	242.9	243.0	243.2	243.4	243.5
132.5°	253.8	254.1	254.3	254.6	254.8	255.2	255.5	255.9	256.2	256.5	256.5
135°	273.5	273.7	273.9	274.2	274.4	274.6	274.6	274.7	274.8	274.9	274.7
137.5°	291.3	291.6	291.9	292.2	292.6	292.8	292.8	292.9	292.9	293.0	292.8
140°	303.6	304.0	304.3	304.6	304.9	305.1	305.1	305.1	305.1	305.1	304.7
142.5°	314.8	315.1	315.4	315.8	316.1	316.2	316.2	316.1	316.1	316.0	315.7
145°	331.6	331.9	332.2	332.6	332.9	333.0	333.0	332.9	332.8	332.7	332.2
147.5°	346.7	346.9	347.2	347.5	347.8	347.9	347.8	347.5	347.4	347.2	346.9
150°	356.4	356.6	356.9	357.1	357.4	357.4	357.1	356.9	356.6	356.4	356.1
152.5°	365.6	365.9	366.1	366.5	366.8	366.8	366.5	366.1	365.9	365.6	365.2
155°	378.0	378.2	378.4	378.7	378.9	378.8	378.4	378.0	377.6	377.2	377.0
157.5°	388.6	389.0	389.3	389.7	390.1	390.0	389.4	388.9	388.4	387.9	387.7
160°	395.1	395.5	395.8	396.1	396.4	396.3	395.9	395.4	394.9	394.4	394.3
162.5°	400.9	401.2	401.6	402.0	402.4	402.3	401.8	401.2	400.7	400.2	400.1
165°	408.4	408.8	409.2	409.6	410.0	410.0	409.4	408.8	408.3	407.7	407.7
167.5°	414.6	415.0	415.4	415.8	416.3	416.2	415.7	415.1	414.5	414.0	414.0
170°	417.8	418.3	418.7	419.2	419.7	419.6	419.1	418.5	418.0	417.4	417.5
172.5°	420.3	420.8	421.3	421.8	422.2	422.2	421.7	421.1	420.6	420.0	420.1
175°	423.2	423.7	424.1	424.6	425.1	425.0	424.5	423.9	423.3	422.8	422.9
177.5°	424.5	424.8	425.2	425.6	426.0	426.0	425.6	425.2	424.8	424.5	424.5
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1191.6	1189.0	1186.8	1180.9	1178.1	1171.6	1170.6	1170.3	1161.8	1153.7	1151.5
5°	1232.6	1226.1	1216.3	1205.0	1193.3	1181.1	1173.1	1166.6	1150.4	1135.0	1126.2
7.5°	1273.7	1259.9	1243.1	1221.7	1203.8	1183.8	1168.9	1155.6	1132.6	1110.6	1095.7
10°	1304.5	1281.8	1259.6	1230.1	1207.0	1184.4	1163.4	1145.2	1119.3	1090.2	1069.5
12.5°	1323.6	1298.7	1268.0	1239.1	1209.3	1180.5	1152.4	1129.0	1098.6	1068.5	1044.0
15°	1349.4	1322.7	1285.5	1244.3	1205.9	1168.2	1135.9	1106.8	1067.1	1031.2	1001.2
17.5°	1370.5	1333.8	1293.8	1246.1	1201.7	1153.8	1112.1	1075.0	1030.9	987.5	952.2
20°	1377.3	1340.9	1294.8	1247.1	1194.5	1138.3	1093.4	1053.0	1005.7	958.4	917.9
22.5°	1373.1	1344.8	1293.5	1236.4	1182.6	1123.7	1073.0	1026.1	973.7	925.3	878.5
25°	1344.6	1334.8	1286.3	1224.0	1162.6	1094.2	1035.6	984.2	924.4	872.7	821.7
27.5°	1277.9	1298.9	1268.8	1202.5	1134.2	1060.9	995.0	936.5	874.4	816.2	765.4
30°	1213.9	1262.0	1249.1	1187.6	1111.2	1039.3	965.3	904.2	837.9	778.0	727.9
32.5°	1126.2	1205.8	1218.4	1167.0	1087.9	1008.8	931.3	870.5	801.3	738.2	689.4
35°	986.7	1105.6	1160.2	1127.4	1048.1	962.8	882.7	812.0	742.4	680.2	631.6
37.5°	820.1	982.1	1073.0	1075.4	1002.6	913.9	826.7	756.5	685.2	624.1	571.6
40°	712.1	887.6	1006.1	1032.4	970.9	875.0	786.9	715.3	645.8	585.9	525.7
42.5°	615.1	789.9	935.6	981.3	932.4	837.2	748.8	673.9	606.3	549.7	488.1
45°	497.4	650.2	810.8	892.5	865.4	777.2	683.8	612.6	549.1	500.2	441.2
47.5°	419.5	527.3	682.6	793.1	792.7	712.2	620.3	552.2	493.3	447.4	399.6
50°	375.3	469.1	600.5	725.9	736.3	668.8	581.5	514.0	459.0	410.8	372.4
52.5°	335.5	412.8	530.9	651.1	681.0	622.6	537.8	475.5	422.1	377.9	344.9
55°	283.4	343.3	433.1	545.5	590.8	549.5	474.4	416.1	372.8	335.6	307.3
57.5°	239.8	284.7	356.7	447.3	499.9	474.0	411.9	364.6	327.6	294.0	271.6
60°	212.3	249.1	310.1	385.8	444.0	425.8	372.8	328.8	297.2	268.1	247.1
62.5°	186.4	218.0	270.4	331.8	385.2	377.6	334.3	297.4	269.7	243.2	225.4
65°	150.0	173.1	213.9	262.1	304.9	308.6	277.4	252.3	227.7	206.6	190.8
67.5°	119.5	134.5	163.3	203.8	235.9	247.4	228.4	209.2	189.6	173.4	159.7
70°	100.7	112.8	133.9	166.6	196.1	208.3	197.3	182.4	165.4	152.0	140.3
72.5°	81.6	93.4	108.9	132.9	158.3	171.3	167.5	156.9	143.1	132.0	120.9
75°	61.5	65.1	75.7	91.8	111.6	122.9	125.8	120.1	109.2	100.7	94.2
77.5°	45.5	47.6	52.7	61.2	74.1	84.2	88.3	87.7	80.2	75.2	69.2
80°	36.4	37.6	40.0	43.6	53.4	63.5	66.3	66.3	61.1	59.0	53.0
82.5°	27.6	28.5	30.0	32.0	36.5	45.4	48.6	49.2	45.9	43.2	38.4
85°	15.8	15.4	16.2	17.3	18.2	20.6	25.5	26.3	25.5	22.3	21.0
87.5°	7.3	7.3	6.9	6.3	6.5	6.6	8.0	9.4	8.3	7.6	7.1
90°	9.0	7.3	5.5	4.2	3.2	2.3	1.3	0.4	1.3	2.3	3.2
92.5°	10.6	10.1	9.7	9.2	8.5	7.8	7.1	6.4	7.1	7.8	8.5
95°	22.7	22.5	22.3	21.9	21.1	20.3	19.5	18.7	19.5	20.3	21.1
97.5°	38.0	37.7	37.4	36.9	36.2	35.5	34.8	34.1	34.8	35.5	36.2
100°	49.0	48.8	48.6	48.2	47.5	46.8	46.2	45.6	46.2	46.8	47.5
102.5°	60.7	60.4	60.1	59.7	59.2	58.6	58.1	57.7	58.1	58.6	59.2
105°	78.7	78.5	78.3	78.1	77.9	77.6	77.4	77.2	77.4	77.6	77.9
107.5°	98.4	98.4	98.4	98.2	97.9	97.5	97.2	96.8	97.2	97.5	97.9
110°	111.6	111.6	111.6	111.4	110.9	110.4	110.0	109.5	110.0	110.4	110.9





TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	125.2	125.3	125.4	125.2	124.7	124.2	123.7	123.3	123.7	124.2	124.7
115°	145.3	145.4	145.6	145.4	145.0	144.5	144.0	143.5	144.0	144.5	145.0
117.5°	165.6	166.0	166.4	166.4	165.7	165.1	164.5	163.8	164.5	165.1	165.7
120°	178.6	179.2	179.8	179.8	179.2	178.6	177.9	177.3	177.9	178.6	179.2
122.5°	191.9	192.4	192.9	192.7	191.9	191.2	190.4	189.6	190.4	191.2	191.9
125°	211.5	211.8	212.0	211.8	211.0	210.3	209.6	208.9	209.6	210.3	211.0
127.5°	231.0	231.3	231.6	231.2	230.4	229.4	228.5	227.6	228.5	229.4	230.4
130°	243.7	243.8	244.0	243.5	242.5	241.5	240.4	239.4	240.4	241.5	242.5
132.5°	256.5	256.4	256.4	256.0	255.2	254.3	253.4	252.6	253.4	254.3	255.2
135°	274.6	274.4	274.3	273.8	272.9	272.0	271.2	270.3	271.2	272.0	272.9
137.5°	292.6	292.4	292.2	291.7	291.0	290.3	289.5	288.8	289.5	290.3	291.0
140°	304.3	303.9	303.5	302.9	302.2	301.5	300.8	300.1	300.8	301.5	302.2
142.5°	315.4	315.1	314.9	314.4	313.7	313.0	312.3	311.6	312.3	313.0	313.7
145°	331.8	331.3	330.8	330.3	329.7	329.2	328.6	328.0	328.6	329.2	329.7
147.5°	346.6	346.3	345.9	345.5	344.8	344.1	343.4	342.8	343.4	344.1	344.8
150°	355.8	355.5	355.1	354.7	354.3	353.8	353.3	352.8	353.3	353.8	354.3
152.5°	364.8	364.4	364.1	363.6	363.1	362.7	362.2	361.7	362.2	362.7	363.1
155°	376.8	376.5	376.3	376.0	375.8	375.5	375.3	375.0	375.3	375.5	375.8
157.5°	387.5	387.4	387.2	387.1	387.0	386.8	386.7	386.5	386.7	386.8	387.0
160°	394.3	394.2	394.1	394.0	393.9	393.7	393.6	393.4	393.6	393.7	393.9
162.5°	400.1	400.0	399.9	399.8	399.7	399.7	399.7	399.7	399.7	399.7	399.7
165°	407.7	407.7	407.7	407.7	407.8	407.9	408.0	408.1	408.0	407.9	407.8
167.5°	414.0	414.0	414.0	414.2	414.4	414.6	414.9	415.1	414.9	414.6	414.4
170°	417.6	417.6	417.7	417.9	418.1	418.4	418.6	418.8	418.6	418.4	418.1
172.5°	420.2	420.3	420.3	420.5	420.7	421.0	421.2	421.4	421.2	421.0	420.7
175°	423.1	423.3	423.4	423.7	423.9	424.1	424.4	424.6	424.4	424.1	423.9
177.5°	424.7	424.8	424.9	425.1	425.3	425.5	425.7	425.9	425.7	425.5	425.3
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1147.3	1145.0	1140.8	1134.3	1130.4	1123.6	1119.1	1121.7	1122.4	1121.7	1121.1
5°	1116.5	1107.9	1096.2	1084.9	1074.4	1063.1	1056.6	1053.8	1048.1	1044.9	1043.3
7.5°	1079.2	1064.5	1048.0	1028.3	1011.5	994.0	985.0	980.5	968.9	962.7	957.1
10°	1051.4	1028.3	1011.8	985.9	970.1	947.1	931.3	931.7	915.9	907.0	900.6
12.5°	1020.6	995.3	967.7	944.4	922.5	904.0	885.0	877.3	860.5	852.0	834.6
15°	969.7	940.2	911.1	879.5	857.3	828.5	801.1	767.5	740.4	716.9	710.5
17.5°	914.0	877.5	848.3	811.3	773.2	724.8	693.0	673.5	657.2	644.8	635.6
20°	875.8	838.7	807.6	751.7	700.4	667.7	644.2	629.2	612.2	598.9	591.6
22.5°	835.8	796.9	754.5	692.2	652.2	625.9	605.0	587.8	576.3	565.9	559.3
25°	778.8	736.3	666.4	623.5	591.2	563.7	549.1	538.6	526.5	512.3	505.9
27.5°	718.7	651.1	600.9	569.0	538.1	520.2	507.2	491.5	480.6	474.3	467.5
30°	673.7	606.2	567.0	532.2	510.3	490.5	475.2	466.3	455.7	444.8	440.4
32.5°	623.5	569.6	532.0	503.0	480.9	464.0	451.9	437.4	429.8	423.1	413.8
35°	561.3	520.5	486.1	462.6	441.6	427.9	413.7	405.2	391.4	385.8	382.1
37.5°	508.5	473.1	447.5	422.7	406.1	390.9	382.2	368.7	362.7	354.9	347.2
40°	478.8	444.0	419.3	399.1	380.5	369.2	358.3	347.4	338.4	334.9	325.5
42.5°	448.4	420.1	395.4	373.2	360.8	348.8	335.0	327.0	317.7	311.9	306.1
45°	406.4	381.4	360.3	342.1	328.4	315.8	306.9	293.6	288.4	276.6	271.7
47.5°	369.6	346.2	326.1	308.9	295.4	287.2	274.3	263.8	255.4	248.2	242.0
50°	343.3	323.9	304.5	289.1	277.0	265.3	251.9	246.7	233.7	230.0	226.5
52.5°	319.4	301.0	283.1	268.1	256.0	244.5	232.8	225.9	217.2	213.6	211.0
55°	285.9	268.1	251.1	237.7	225.6	213.9	206.6	198.1	194.1	191.2	188.1
57.5°	252.2	236.2	223.2	209.7	197.5	188.2	179.7	174.7	170.5	166.8	162.9
60°	230.9	215.6	203.8	191.2	178.7	171.0	164.6	158.5	153.7	148.0	146.4
62.5°	208.3	194.8	184.1	171.8	161.0	153.9	147.7	142.0	136.2	127.9	125.6
65°	177.1	166.6	155.3	145.2	135.5	128.6	119.7	113.2	110.8	110.0	109.6
67.5°	149.0	139.0	129.3	119.0	110.1	103.8	99.3	98.2	96.6	96.1	95.0
70°	130.2	120.9	111.2	101.5	93.0	91.8	90.2	88.6	86.5	85.7	84.9
72.5°	113.4	103.8	94.0	86.3	82.6	81.1	79.5	77.9	76.5	75.7	75.2
75°	86.9	78.0	71.6	68.8	66.7	65.5	63.1	61.9	61.1	59.8	59.4
77.5°	62.6	57.6	54.6	52.8	50.7	49.4	48.0	46.8	45.9	45.7	45.1
80°	47.7	45.3	43.3	40.9	40.0	38.4	38.0	36.8	37.2	36.0	36.0
82.5°	37.1	34.0	32.2	31.1	30.3	29.1	28.6	28.0	28.1	27.3	27.3
85°	19.0	18.2	17.3	16.6	16.6	15.4	15.8	15.4	15.4	14.6	14.2
87.5°	7.0	6.9	6.7	7.0	7.4	7.4	7.4	7.0	7.0	6.9	6.6
90°	4.2	5.5	7.3	9.0	10.8	12.6	12.4	12.3	12.1	12.0	11.9
92.5°	9.2	9.7	10.1	10.6	11.0	11.4	11.4	11.5	11.5	11.6	11.6
95°	21.9	22.3	22.5	22.7	22.8	23.0	23.0	23.0	23.0	23.0	22.9
97.5°	36.9	37.4	37.7	38.0	38.3	38.6	38.6	38.6	38.6	38.6	38.6
100°	48.2	48.6	48.8	49.0	49.3	49.5	49.5	49.5	49.5	49.5	49.5
102.5°	59.7	60.1	60.4	60.7	61.0	61.3	61.4	61.4	61.5	61.6	61.6
105°	78.1	78.3	78.5	78.7	78.8	79.0	79.1	79.3	79.5	79.6	79.7
107.5°	98.2	98.4	98.4	98.4	98.4	98.4	98.5	98.5	98.6	98.7	98.5
110°	111.4	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.6	111.5



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	125.2	125.4	125.3	125.2	125.2	125.1	124.9	124.8	124.5	124.4	124.1
115°	145.4	145.6	145.4	145.3	145.1	145.0	144.9	144.8	144.7	144.7	144.5
117.5°	166.4	166.4	166.0	165.6	165.1	164.7	164.5	164.3	164.1	163.9	163.7
120°	179.8	179.8	179.2	178.6	177.9	177.3	177.3	177.3	177.3	177.3	177.2
122.5°	192.7	192.9	192.4	191.9	191.5	191.1	190.9	190.7	190.5	190.3	190.1
125°	211.8	212.0	211.8	211.5	211.3	211.0	210.8	210.6	210.3	210.1	209.9
127.5°	231.2	231.6	231.3	231.0	230.7	230.4	230.1	229.8	229.6	229.3	229.0
130°	243.5	244.0	243.8	243.7	243.5	243.4	243.2	243.0	242.9	242.7	242.5
132.5°	256.0	256.4	256.4	256.5	256.5	256.5	256.2	255.9	255.5	255.2	254.8
135°	273.8	274.3	274.4	274.6	274.7	274.9	274.8	274.7	274.6	274.6	274.4
137.5°	291.7	292.2	292.4	292.6	292.8	293.0	292.9	292.9	292.8	292.8	292.6
140°	302.9	303.5	303.9	304.3	304.7	305.1	305.1	305.1	305.1	305.1	304.9
142.5°	314.4	314.9	315.1	315.4	315.7	316.0	316.1	316.1	316.2	316.2	316.1
145°	330.3	330.8	331.3	331.8	332.2	332.7	332.8	332.9	333.0	333.0	332.9
147.5°	345.5	345.9	346.3	346.6	346.9	347.2	347.4	347.5	347.8	347.9	347.8
150°	354.7	355.1	355.5	355.8	356.1	356.4	356.6	356.9	357.1	357.4	357.4
152.5°	363.6	364.1	364.4	364.8	365.2	365.6	365.9	366.1	366.5	366.8	366.8
155°	376.0	376.3	376.5	376.8	377.0	377.2	377.6	378.0	378.4	378.8	378.9
157.5°	387.1	387.2	387.4	387.5	387.7	387.9	388.4	388.9	389.4	390.0	390.1
160°	394.0	394.1	394.2	394.3	394.3	394.4	394.9	395.4	395.9	396.3	396.4
162.5°	399.8	399.9	400.0	400.1	400.1	400.2	400.7	401.2	401.8	402.3	402.4
165°	407.7	407.7	407.7	407.7	407.7	407.7	408.3	408.8	409.4	410.0	410.0
167.5°	414.2	414.0	414.0	414.0	414.0	414.0	414.5	415.1	415.7	416.2	416.3
170°	417.9	417.7	417.6	417.6	417.5	417.4	418.0	418.5	419.1	419.6	419.7
172.5°	420.5	420.3	420.3	420.2	420.1	420.0	420.6	421.1	421.7	422.2	422.2
175°	423.7	423.4	423.3	423.1	422.9	422.8	423.3	423.9	424.5	425.0	425.1
177.5°	425.1	424.9	424.8	424.7	424.5	424.5	424.8	425.2	425.6	426.0	426.0
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1117.5	1118.2	1117.2	1117.8	1117.2	1118.2	1117.5	1121.1	1121.7	1122.4	1121.7
5°	1041.2	1036.4	1035.6	1034.4	1035.6	1036.4	1041.2	1043.3	1044.9	1048.1	1053.8
7.5°	950.2	949.4	947.5	944.6	947.5	949.4	950.2	957.1	962.7	968.9	980.5
10°	891.6	889.6	889.2	886.4	889.2	889.6	891.6	900.6	907.0	915.9	931.7
12.5°	823.1	810.0	808.7	801.6	808.7	810.0	823.1	834.6	852.0	860.5	877.3
15°	700.8	698.4	690.2	685.0	690.2	698.4	700.8	710.5	716.9	740.4	767.5
17.5°	630.9	623.0	620.4	619.3	620.4	623.0	630.9	635.6	644.8	657.2	673.5
20°	585.9	578.7	577.4	576.6	577.4	578.7	585.9	591.6	598.9	612.2	629.2
22.5°	554.8	547.2	544.2	541.7	544.2	547.2	554.8	559.3	565.9	576.3	587.8
25°	501.8	499.0	497.4	496.5	497.4	499.0	501.8	505.9	512.3	526.5	538.6
27.5°	460.3	454.1	452.9	450.8	452.9	454.1	460.3	467.5	474.3	480.6	491.5
30°	436.7	434.7	431.9	429.4	431.9	434.7	436.7	440.4	444.8	455.7	466.3
32.5°	408.9	407.2	404.7	403.5	404.7	407.2	408.9	413.8	423.1	429.8	437.4
35°	378.1	372.4	370.0	366.4	370.0	372.4	378.1	382.1	385.8	391.4	405.2
37.5°	345.5	342.5	339.1	340.3	339.1	342.5	345.5	347.2	354.9	362.7	368.7
40°	320.3	318.2	317.4	317.0	317.4	318.2	320.3	325.5	334.9	338.4	347.4
42.5°	300.2	294.6	292.6	292.5	292.6	294.6	300.2	306.1	311.9	317.7	327.0
45°	269.7	264.4	260.8	261.3	260.8	264.4	269.7	271.7	276.6	288.4	293.6
47.5°	238.5	238.4	236.1	236.8	236.1	238.4	238.5	242.0	248.2	255.4	263.8
50°	223.6	221.2	219.6	220.0	219.6	221.2	223.6	226.5	230.0	233.7	246.7
52.5°	209.4	207.3	206.0	207.7	206.0	207.3	209.4	211.0	213.6	217.2	225.9
55°	186.0	183.5	183.2	182.8	183.2	183.5	186.0	188.1	191.2	194.1	198.1
57.5°	159.9	158.3	155.8	154.8	155.8	158.3	159.9	162.9	166.8	170.5	174.7
60°	141.1	137.9	133.9	133.4	133.9	137.9	141.1	146.4	148.0	153.7	158.5
62.5°	124.0	123.3	122.6	122.5	122.6	123.3	124.0	125.6	127.9	136.2	142.0
65°	108.8	108.4	108.8	109.2	108.8	108.4	108.8	109.6	110.0	110.8	113.2
67.5°	94.8	94.0	93.3	93.6	93.3	94.0	94.8	95.0	96.1	96.6	98.2
70°	84.1	83.7	83.3	83.3	83.3	83.7	84.1	84.9	85.7	86.5	88.6
72.5°	73.8	73.7	73.3	73.0	73.3	73.7	73.8	75.2	75.7	76.5	77.9
75°	59.0	58.2	58.2	58.2	58.2	58.2	59.0	59.4	59.8	61.1	61.9
77.5°	45.0	44.6	44.1	43.8	44.1	44.6	45.0	45.1	45.7	45.9	46.8
80°	35.6	35.2	34.8	34.8	34.8	35.2	35.6	36.0	36.0	37.2	36.8
82.5°	27.2	26.8	26.7	26.4	26.7	26.8	27.2	27.3	27.3	28.1	28.0
85°	14.6	15.0	14.6	15.4	14.6	15.0	14.6	14.2	14.6	15.4	15.4
87.5°	6.6	6.3	6.7	6.3	6.7	6.3	6.6	6.6	6.9	7.0	7.0
90°	12.0	12.0	12.1	12.2	12.1	12.0	12.0	11.9	12.0	12.1	12.3
92.5°	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.5	11.5
95°	22.7	22.6	22.4	22.3	22.4	22.6	22.7	22.9	23.0	23.0	23.0
97.5°	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6
100°	49.4	49.4	49.3	49.2	49.3	49.4	49.4	49.5	49.5	49.5	49.5
102.5°	61.5	61.4	61.3	61.2	61.3	61.4	61.5	61.6	61.6	61.5	61.4
105°	79.7	79.7	79.7	79.7	79.7	79.7	79.7	79.7	79.6	79.5	79.3
107.5°	98.2	97.8	97.4	97.0	97.4	97.8	98.2	98.5	98.7	98.6	98.5
110°	111.2	111.0	110.7	110.5	110.7	111.0	111.2	111.5	111.6	111.6	111.6



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	124.0	123.8	123.7	123.5	123.7	123.8	124.0	124.1	124.4	124.5	124.8
115°	144.3	144.0	143.8	143.5	143.8	144.0	144.3	144.5	144.7	144.7	144.8
117.5°	163.4	163.2	163.0	162.7	163.0	163.2	163.4	163.7	163.9	164.1	164.3
120°	177.0	176.7	176.5	176.3	176.5	176.7	177.0	177.2	177.3	177.3	177.3
122.5°	190.0	189.8	189.6	189.4	189.6	189.8	190.0	190.1	190.3	190.5	190.7
125°	209.8	209.8	209.7	209.6	209.7	209.8	209.8	209.9	210.1	210.3	210.6
127.5°	228.7	228.5	228.2	228.0	228.2	228.5	228.7	229.0	229.3	229.6	229.8
130°	242.2	241.9	241.5	241.2	241.5	241.9	242.2	242.5	242.7	242.9	243.0
132.5°	254.6	254.3	254.1	253.8	254.1	254.3	254.6	254.8	255.2	255.5	255.9
135°	274.2	273.9	273.7	273.5	273.7	273.9	274.2	274.4	274.6	274.6	274.7
137.5°	292.2	291.9	291.6	291.3	291.6	291.9	292.2	292.6	292.8	292.8	292.9
140°	304.6	304.3	304.0	303.6	304.0	304.3	304.6	304.9	305.1	305.1	305.1
142.5°	315.8	315.4	315.1	314.8	315.1	315.4	315.8	316.1	316.2	316.2	316.1
145°	332.6	332.2	331.9	331.6	331.9	332.2	332.6	332.9	333.0	333.0	332.9
147.5°	347.5	347.2	346.9	346.7	346.9	347.2	347.5	347.8	347.9	347.8	347.5
150°	357.1	356.9	356.6	356.4	356.6	356.9	357.1	357.4	357.4	357.1	356.9
152.5°	366.5	366.1	365.9	365.6	365.9	366.1	366.5	366.8	366.8	366.5	366.1
155°	378.7	378.4	378.2	378.0	378.2	378.4	378.7	378.9	378.8	378.4	378.0
157.5°	389.7	389.3	389.0	388.6	389.0	389.3	389.7	390.1	390.0	389.4	388.9
160°	396.1	395.8	395.5	395.1	395.5	395.8	396.1	396.4	396.3	395.9	395.4
162.5°	402.0	401.6	401.2	400.9	401.2	401.6	402.0	402.4	402.3	401.8	401.2
165°	409.6	409.2	408.8	408.4	408.8	409.2	409.6	410.0	410.0	409.4	408.8
167.5°	415.8	415.4	415.0	414.6	415.0	415.4	415.8	416.3	416.2	415.7	415.1
170°	419.2	418.7	418.3	417.8	418.3	418.7	419.2	419.7	419.6	419.1	418.5
172.5°	421.8	421.3	420.8	420.3	420.8	421.3	421.8	422.2	422.2	421.7	421.1
175°	424.6	424.1	423.7	423.2	423.7	424.1	424.6	425.1	425.0	424.5	423.9
177.5°	425.6	425.2	424.8	424.5	424.8	425.2	425.6	426.0	426.0	425.6	425.2
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1119.1	1123.6	1130.4	1134.3	1140.8	1145.0	1147.3	1151.5	1153.7	1161.8	1170.3
5°	1056.6	1063.1	1074.4	1084.9	1096.2	1107.9	1116.5	1126.2	1135.0	1150.4	1166.6
7.5°	985.0	994.0	1011.5	1028.3	1048.0	1064.5	1079.2	1095.7	1110.6	1132.6	1155.6
10°	931.3	947.1	970.1	985.9	1011.8	1028.3	1051.4	1069.5	1090.2	1119.3	1145.2
12.5°	885.0	904.0	922.5	944.4	967.7	995.3	1020.6	1044.0	1068.5	1098.6	1129.0
15°	801.1	828.5	857.3	879.5	911.1	940.2	969.7	1001.2	1031.2	1067.1	1106.8
17.5°	693.0	724.8	773.2	811.3	848.3	877.5	914.0	952.2	987.5	1030.9	1075.0
20°	644.2	667.7	700.4	751.7	807.6	838.7	875.8	917.9	958.4	1005.7	1053.0
22.5°	605.0	625.9	652.2	692.2	754.5	796.9	835.8	878.5	925.3	973.7	1026.1
25°	549.1	563.7	591.2	623.5	666.4	736.3	778.8	821.7	872.7	924.4	984.2
27.5°	507.2	520.2	538.1	569.0	600.9	651.1	718.7	765.4	816.2	874.4	936.5
30°	475.2	490.5	510.3	532.2	567.0	606.2	673.7	727.9	778.0	837.9	904.2
32.5°	451.9	464.0	480.9	503.0	532.0	569.6	623.5	689.4	738.2	801.3	870.5
35°	413.7	427.9	441.6	462.6	486.1	520.5	561.3	631.6	680.2	742.4	812.0
37.5°	382.2	390.9	406.1	422.7	447.5	473.1	508.5	571.6	624.1	685.2	756.5
40°	358.3	369.2	380.5	399.1	419.3	444.0	478.8	525.7	585.9	645.8	715.3
42.5°	335.0	348.8	360.8	373.2	395.4	420.1	448.4	488.1	549.7	606.3	673.9
45°	306.9	315.8	328.4	342.1	360.3	381.4	406.4	441.2	500.2	549.1	612.6
47.5°	274.3	287.2	295.4	308.9	326.1	346.2	369.6	399.6	447.4	493.3	552.2
50°	251.9	265.3	277.0	289.1	304.5	323.9	343.3	372.4	410.8	459.0	514.0
52.5°	232.8	244.5	256.0	268.1	283.1	301.0	319.4	344.9	377.9	422.1	475.5
55°	206.6	213.9	225.6	237.7	251.1	268.1	285.9	307.3	335.6	372.8	416.1
57.5°	179.7	188.2	197.5	209.7	223.2	236.2	252.2	271.6	294.0	327.6	364.6
60°	164.6	171.0	178.7	191.2	203.8	215.6	230.9	247.1	268.1	297.2	328.8
62.5°	147.7	153.9	161.0	171.8	184.1	194.8	208.3	225.4	243.2	269.7	297.4
65°	119.7	128.6	135.5	145.2	155.3	166.6	177.1	190.8	206.6	227.7	252.3
67.5°	99.3	103.8	110.1	119.0	129.3	139.0	149.0	159.7	173.4	189.6	209.2
70°	90.2	91.8	93.0	101.5	111.2	120.9	130.2	140.3	152.0	165.4	182.4
72.5°	79.5	81.1	82.6	86.3	94.0	103.8	113.4	120.9	132.0	143.1	156.9
75°	63.1	65.5	66.7	68.8	71.6	78.0	86.9	94.2	100.7	109.2	120.1
77.5°	48.0	49.4	50.7	52.8	54.6	57.6	62.6	69.2	75.2	80.2	87.7
80°	38.0	38.4	40.0	40.9	43.3	45.3	47.7	53.0	59.0	61.1	66.3
82.5°	28.6	29.1	30.3	31.1	32.2	34.0	37.1	38.4	43.2	45.9	49.2
85°	15.8	15.4	16.6	16.6	17.3	18.2	19.0	21.0	22.3	25.5	26.3
87.5°	7.4	7.4	7.4	7.0	6.7	6.9	7.0	7.1	7.6	8.3	9.4
90°	12.4	12.6	10.8	9.0	7.3	5.5	4.2	3.2	2.3	1.3	0.4
92.5°	11.4	11.4	11.0	10.6	10.1	9.7	9.2	8.5	7.8	7.1	6.4
95°	23.0	23.0	22.8	22.7	22.5	22.3	21.9	21.1	20.3	19.5	18.7
97.5°	38.6	38.6	38.3	38.0	37.7	37.4	36.9	36.2	35.5	34.8	34.1
100°	49.5	49.5	49.3	49.0	48.8	48.6	48.2	47.5	46.8	46.2	45.6
102.5°	61.4	61.3	61.0	60.7	60.4	60.1	59.7	59.2	58.6	58.1	57.7
105°	79.1	79.0	78.8	78.7	78.5	78.3	78.1	77.9	77.6	77.4	77.2
107.5°	98.5	98.4	98.4	98.4	98.4	98.4	98.2	97.9	97.5	97.2	96.8
110°	111.6	111.6	111.6	111.6	111.6	111.6	111.4	110.9	110.4	110.0	109.5



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	124.9	125.1	125.2	125.2	125.3	125.4	125.2	124.7	124.2	123.7	123.3
115°	144.9	145.0	145.1	145.3	145.4	145.6	145.4	145.0	144.5	144.0	143.5
117.5°	164.5	164.7	165.1	165.6	166.0	166.4	166.4	165.7	165.1	164.5	163.8
120°	177.3	177.3	177.9	178.6	179.2	179.8	179.8	179.2	178.6	177.9	177.3
122.5°	190.9	191.1	191.5	191.9	192.4	192.9	192.7	191.9	191.2	190.4	189.6
125°	210.8	211.0	211.3	211.5	211.8	212.0	211.8	211.0	210.3	209.6	208.9
127.5°	230.1	230.4	230.7	231.0	231.3	231.6	231.2	230.4	229.4	228.5	227.6
130°	243.2	243.4	243.5	243.7	243.8	244.0	243.5	242.5	241.5	240.4	239.4
132.5°	256.2	256.5	256.5	256.5	256.4	256.4	256.0	255.2	254.3	253.4	252.6
135°	274.8	274.9	274.7	274.6	274.4	274.3	273.8	272.9	272.0	271.2	270.3
137.5°	292.9	293.0	292.8	292.6	292.4	292.2	291.7	291.0	290.3	289.5	288.8
140°	305.1	305.1	304.7	304.3	303.9	303.5	302.9	302.2	301.5	300.8	300.1
142.5°	316.1	316.0	315.7	315.4	315.1	314.9	314.4	313.7	313.0	312.3	311.6
145°	332.8	332.7	332.2	331.8	331.3	330.8	330.3	329.7	329.2	328.6	328.0
147.5°	347.4	347.2	346.9	346.6	346.3	345.9	345.5	344.8	344.1	343.4	342.8
150°	356.6	356.4	356.1	355.8	355.5	355.1	354.7	354.3	353.8	353.3	352.8
152.5°	365.9	365.6	365.2	364.8	364.4	364.1	363.6	363.1	362.7	362.2	361.7
155°	377.6	377.2	377.0	376.8	376.5	376.3	376.0	375.8	375.5	375.3	375.0
157.5°	388.4	387.9	387.7	387.5	387.4	387.2	387.1	387.0	386.8	386.7	386.5
160°	394.9	394.4	394.3	394.3	394.2	394.1	394.0	393.9	393.7	393.6	393.4
162.5°	400.7	400.2	400.1	400.1	400.0	399.9	399.8	399.7	399.7	399.7	399.7
165°	408.3	407.7	407.7	407.7	407.7	407.7	407.7	407.8	407.9	408.0	408.1
167.5°	414.5	414.0	414.0	414.0	414.0	414.0	414.2	414.4	414.6	414.9	415.1
170°	418.0	417.4	417.5	417.6	417.6	417.7	417.9	418.1	418.4	418.6	418.8
172.5°	420.6	420.0	420.1	420.2	420.3	420.3	420.5	420.7	421.0	421.2	421.4
175°	423.3	422.8	422.9	423.1	423.3	423.4	423.7	423.9	424.1	424.4	424.6
177.5°	424.8	424.5	424.5	424.7	424.8	424.9	425.1	425.3	425.5	425.7	425.9
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1170.6	1171.6	1178.1	1180.9	1186.8	1189.0	1191.6	1191.0	1191.0	1192.2	1201.3
5°	1173.1	1181.1	1193.3	1205.0	1216.3	1226.1	1232.6	1239.0	1241.4	1253.2	1263.7
7.5°	1168.9	1183.8	1203.8	1221.7	1243.1	1259.9	1273.7	1286.3	1294.9	1311.9	1329.4
10°	1163.4	1184.4	1207.0	1230.1	1259.6	1281.8	1304.5	1321.9	1327.5	1353.0	1367.6
12.5°	1152.4	1180.5	1209.3	1239.1	1268.0	1298.7	1323.6	1341.0	1360.9	1383.8	1410.6
15°	1135.9	1168.2	1205.9	1244.3	1285.5	1322.7	1349.4	1379.7	1401.5	1426.6	1450.1
17.5°	1112.1	1153.8	1201.7	1246.1	1293.8	1333.8	1370.5	1399.6	1415.0	1429.3	1432.7
20°	1093.4	1138.3	1194.5	1247.1	1294.8	1340.9	1377.3	1401.5	1405.6	1406.0	1384.6
22.5°	1073.0	1123.7	1182.6	1236.4	1293.5	1344.8	1373.1	1383.5	1367.4	1340.0	1298.5
25°	1035.6	1094.2	1162.6	1224.0	1286.3	1334.8	1344.6	1326.4	1270.1	1211.1	1136.3
27.5°	995.0	1060.9	1134.2	1202.5	1268.8	1298.9	1277.9	1212.4	1111.1	1023.1	916.5
30°	965.3	1039.3	1111.2	1187.6	1249.1	1262.0	1213.9	1117.3	999.2	866.6	760.3
32.5°	931.3	1008.8	1087.9	1167.0	1218.4	1205.8	1126.2	1007.3	868.9	738.5	637.9
35°	882.7	962.8	1048.1	1127.4	1160.2	1105.6	986.7	831.8	690.2	568.5	499.4
37.5°	826.7	913.9	1002.6	1075.4	1073.0	982.1	820.1	660.3	541.3	469.3	420.1
40°	786.9	875.0	970.9	1032.4	1006.1	887.6	712.1	561.3	474.4	416.9	380.9
42.5°	748.8	837.2	932.4	981.3	935.6	789.9	615.1	496.9	425.2	380.3	351.2
45°	683.8	777.2	865.4	892.5	810.8	650.2	497.4	411.6	363.9	330.8	310.5
47.5°	620.3	712.2	792.7	793.1	682.6	527.3	419.5	356.2	315.5	289.9	275.1
50°	581.5	668.8	736.3	725.9	600.5	469.1	375.3	320.7	286.7	266.9	251.5
52.5°	537.8	622.6	681.0	651.1	530.9	412.8	335.5	289.6	261.5	244.2	230.5
55°	474.4	549.5	590.8	545.5	433.1	343.3	283.4	247.5	226.5	211.9	200.2
57.5°	411.9	474.0	499.9	447.3	356.7	284.7	239.8	212.8	191.9	181.5	175.4
60°	372.8	425.8	444.0	385.8	310.1	249.1	212.3	187.2	171.8	165.0	158.9
62.5°	334.3	377.6	385.2	331.8	270.4	218.0	186.4	165.2	155.0	148.5	142.8
65°	277.4	308.6	304.9	262.1	213.9	173.1	150.0	137.0	129.4	120.1	110.0
67.5°	228.4	247.4	235.9	203.8	163.3	134.5	119.5	109.6	100.1	91.3	89.0
70°	197.3	208.3	196.1	166.6	133.9	112.8	100.7	89.0	83.3	81.3	77.6
72.5°	167.5	171.3	158.3	132.9	108.9	93.4	81.6	75.0	72.0	70.3	68.0
75°	125.8	122.9	111.6	91.8	75.7	65.1	61.5	59.0	57.0	55.4	54.2
77.5°	88.3	84.2	74.1	61.2	52.7	47.6	45.5	44.1	43.2	42.4	41.2
80°	66.3	63.5	53.4	43.6	40.0	37.6	36.4	34.8	34.8	34.0	32.7
82.5°	48.6	45.4	36.5	32.0	30.0	28.5	27.6	26.7	26.4	26.5	25.7
85°	25.5	20.6	18.2	17.3	16.2	15.4	15.8	15.0	15.0	15.0	14.6
87.5°	8.0	6.6	6.5	6.3	6.9	7.3	7.3	7.7	8.3	8.0	8.2
90°	1.3	2.3	3.2	4.2	5.5	7.3	9.0	10.8	12.6	12.4	12.3
92.5°	7.1	7.8	8.5	9.2	9.7	10.1	10.6	11.0	11.4	11.4	11.5
95°	19.5	20.3	21.1	21.9	22.3	22.5	22.7	22.8	23.0	23.0	23.0
97.5°	34.8	35.5	36.2	36.9	37.4	37.7	38.0	38.3	38.6	38.6	38.6
100°	46.2	46.8	47.5	48.2	48.6	48.8	49.0	49.3	49.5	49.5	49.5
102.5°	58.1	58.6	59.2	59.7	60.1	60.4	60.7	61.0	61.3	61.4	61.4
105°	77.4	77.6	77.9	78.1	78.3	78.5	78.7	78.8	79.0	79.1	79.3
107.5°	97.2	97.5	97.9	98.2	98.4	98.4	98.4	98.4	98.4	98.5	98.5
110°	110.0	110.4	110.9	111.4	111.6	111.6	111.6	111.6	111.6	111.6	111.6





TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.7	124.2	124.7	125.2	125.4	125.3	125.2	125.2	125.1	124.9	124.8
115°	144.0	144.5	145.0	145.4	145.6	145.4	145.3	145.1	145.0	144.9	144.8
117.5°	164.5	165.1	165.7	166.4	166.4	166.0	165.6	165.1	164.7	164.5	164.3
120°	177.9	178.6	179.2	179.8	179.8	179.2	178.6	177.9	177.3	177.3	177.3
122.5°	190.4	191.2	191.9	192.7	192.9	192.4	191.9	191.5	191.1	190.9	190.7
125°	209.6	210.3	211.0	211.8	212.0	211.8	211.5	211.3	211.0	210.8	210.6
127.5°	228.5	229.4	230.4	231.2	231.6	231.3	231.0	230.7	230.4	230.1	229.8
130°	240.4	241.5	242.5	243.5	244.0	243.8	243.7	243.5	243.4	243.2	243.0
132.5°	253.4	254.3	255.2	256.0	256.4	256.4	256.5	256.5	256.5	256.2	255.9
135°	271.2	272.0	272.9	273.8	274.3	274.4	274.6	274.7	274.9	274.8	274.7
137.5°	289.5	290.3	291.0	291.7	292.2	292.4	292.6	292.8	293.0	292.9	292.9
140°	300.8	301.5	302.2	302.9	303.5	303.9	304.3	304.7	305.1	305.1	305.1
142.5°	312.3	313.0	313.7	314.4	314.9	315.1	315.4	315.7	316.0	316.1	316.1
145°	328.6	329.2	329.7	330.3	330.8	331.3	331.8	332.2	332.7	332.8	332.9
147.5°	343.4	344.1	344.8	345.5	345.9	346.3	346.6	346.9	347.2	347.4	347.5
150°	353.3	353.8	354.3	354.7	355.1	355.5	355.8	356.1	356.4	356.6	356.9
152.5°	362.2	362.7	363.1	363.6	364.1	364.4	364.8	365.2	365.6	365.9	366.1
155°	375.3	375.5	375.8	376.0	376.3	376.5	376.8	377.0	377.2	377.6	378.0
157.5°	386.7	386.8	387.0	387.1	387.2	387.4	387.5	387.7	387.9	388.4	388.9
160°	393.6	393.7	393.9	394.0	394.1	394.2	394.3	394.3	394.4	394.9	395.4
162.5°	399.7	399.7	399.7	399.8	399.9	400.0	400.1	400.1	400.2	400.7	401.2
165°	408.0	407.9	407.8	407.7	407.7	407.7	407.7	407.7	407.7	408.3	408.8
167.5°	414.9	414.6	414.4	414.2	414.0	414.0	414.0	414.0	414.0	414.5	415.1
170°	418.6	418.4	418.1	417.9	417.7	417.6	417.6	417.5	417.4	418.0	418.5
172.5°	421.2	421.0	420.7	420.5	420.3	420.3	420.2	420.1	420.0	420.6	421.1
175°	424.4	424.1	423.9	423.7	423.4	423.3	423.1	422.9	422.8	423.3	423.9
177.5°	425.7	425.5	425.3	425.1	424.9	424.8	424.7	424.5	424.5	424.8	425.2
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1204.5	1208.7	1210.7	1210.7	1213.0	1212.0	1211.0
5°	1273.7	1281.4	1283.1	1290.4	1295.6	1294.0	1294.8
7.5°	1342.6	1354.9	1367.1	1372.8	1373.6	1376.9	1378.1
10°	1385.0	1395.1	1414.1	1411.3	1425.4	1433.5	1420.1
12.5°	1425.8	1439.4	1452.5	1456.2	1464.3	1466.8	1461.6
15°	1462.6	1469.9	1470.7	1468.7	1471.1	1469.1	1461.4
17.5°	1428.1	1416.3	1392.4	1381.1	1372.1	1358.8	1353.5
20°	1371.2	1336.4	1296.0	1279.8	1260.8	1223.6	1232.6
22.5°	1248.3	1208.6	1168.2	1121.0	1098.4	1063.2	1061.0
25°	1057.0	988.7	913.5	860.9	830.2	795.0	779.7
27.5°	821.8	735.8	674.1	642.9	614.6	586.7	585.5
30°	667.2	602.5	554.8	528.1	510.7	499.0	501.5
32.5°	562.4	518.1	485.9	463.7	450.9	442.0	441.9
35°	459.8	429.4	408.8	399.5	390.2	383.7	384.1
37.5°	393.5	375.3	363.8	353.5	347.7	344.5	342.8
40°	359.5	344.5	335.6	329.5	324.7	320.3	319.5
42.5°	332.6	320.3	311.3	306.6	302.1	298.9	298.1
45°	295.2	285.1	277.0	271.7	269.7	266.9	266.9
47.5°	262.6	252.6	246.4	243.0	239.6	237.7	237.6
50°	240.6	232.9	227.3	225.2	222.4	221.2	220.8
52.5°	220.9	215.2	211.1	209.7	208.5	206.9	207.2
55°	194.1	190.8	189.3	188.1	186.0	183.5	185.2
57.5°	171.5	168.8	164.5	160.7	158.8	157.1	157.7
60°	155.7	150.0	144.3	139.9	138.7	135.1	135.1
62.5°	135.6	127.7	120.7	118.3	117.0	115.3	115.0
65°	104.3	101.1	99.5	97.8	97.0	97.0	96.3
67.5°	86.4	85.2	83.4	82.9	82.1	81.9	81.7
70°	76.4	74.8	74.0	73.6	72.8	73.2	72.0
72.5°	66.7	65.4	65.3	64.2	63.7	63.8	62.9
75°	52.6	52.6	52.1	51.7	50.9	50.5	50.9
77.5°	40.4	40.5	39.8	39.7	39.6	39.7	39.3
80°	32.3	32.7	32.3	31.9	31.5	31.9	31.5
82.5°	25.6	25.0	24.9	24.8	24.7	24.5	24.4
85°	14.6	15.0	14.6	14.2	14.2	14.2	14.6
87.5°	7.9	7.9	7.8	7.9	7.9	7.9	7.6
90°	12.1	12.0	11.9	12.0	12.0	12.1	12.2
92.5°	11.5	11.6	11.6	11.6	11.6	11.6	11.6
95°	23.0	23.0	22.9	22.7	22.6	22.4	22.3
97.5°	38.6	38.6	38.6	38.6	38.6	38.6	38.6
100°	49.5	49.5	49.5	49.4	49.4	49.3	49.2
102.5°	61.5	61.6	61.6	61.5	61.4	61.3	61.2
105°	79.5	79.6	79.7	79.7	79.7	79.7	79.7
107.5°	98.6	98.7	98.5	98.2	97.8	97.4	97.0
110°	111.6	111.6	111.5	111.2	111.0	110.7	110.5



TEST NUMBER: P331806-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	124.5	124.4	124.1	124.0	123.8	123.7	123.5
115°	144.7	144.7	144.5	144.3	144.0	143.8	143.5
117.5°	164.1	163.9	163.7	163.4	163.2	163.0	162.7
120°	177.3	177.3	177.2	177.0	176.7	176.5	176.3
122.5°	190.5	190.3	190.1	190.0	189.8	189.6	189.4
125°	210.3	210.1	209.9	209.8	209.8	209.7	209.6
127.5°	229.6	229.3	229.0	228.7	228.5	228.2	228.0
130°	242.9	242.7	242.5	242.2	241.9	241.5	241.2
132.5°	255.5	255.2	254.8	254.6	254.3	254.1	253.8
135°	274.6	274.6	274.4	274.2	273.9	273.7	273.5
137.5°	292.8	292.8	292.6	292.2	291.9	291.6	291.3
140°	305.1	305.1	304.9	304.6	304.3	304.0	303.6
142.5°	316.2	316.2	316.1	315.8	315.4	315.1	314.8
145°	333.0	333.0	332.9	332.6	332.2	331.9	331.6
147.5°	347.8	347.9	347.8	347.5	347.2	346.9	346.7
150°	357.1	357.4	357.4	357.1	356.9	356.6	356.4
152.5°	366.5	366.8	366.8	366.5	366.1	365.9	365.6
155°	378.4	378.8	378.9	378.7	378.4	378.2	378.0
157.5°	389.4	390.0	390.1	389.7	389.3	389.0	388.6
160°	395.9	396.3	396.4	396.1	395.8	395.5	395.1
162.5°	401.8	402.3	402.4	402.0	401.6	401.2	400.9
165°	409.4	410.0	410.0	409.6	409.2	408.8	408.4
167.5°	415.7	416.2	416.3	415.8	415.4	415.0	414.6
170°	419.1	419.6	419.7	419.2	418.7	418.3	417.8
172.5°	421.7	422.2	422.2	421.8	421.3	420.8	420.3
175°	424.5	425.0	425.1	424.6	424.1	423.7	423.2
177.5°	425.6	426.0	426.0	425.6	425.2	424.8	424.5
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3

(END OF REPORT)