

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331808-927

Luminaire Tested: **S122RDIW-S675D435U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331808-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D435U927-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3028.9 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331808-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331808-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	93	89	94	91	87	84	79	77	75	69	67	65	59	58	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	75	68	62	79	71	64	59	62	57	53	55	51	48	47	45	42	39
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	43	40	37	34
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33	30
6	66	54	46	41	62	51	44	39	46	40	35	40	36	32	35	32	29	26
7	61	49	41	36	57	47	39	34	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	53	43	36	31	38	32	28	34	29	26	30	26	23	21
9	53	41	34	29	50	39	32	28	35	29	26	31	27	23	28	24	21	19
10	50	38	31	26	47	36	29	25	32	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14428	14428	14428
5°	14483	14248	14326
10°	14372	14014	13895
15°	14206	13600	13207
20°	13979	13005	12352
25°	13744	12332	11526
30°	13420	11639	10465
35°	13102	10886	9532
40°	12783	10108	8454
45°	12408	9232	7478
50°	12024	8349	6521
55°	11634	7398	5599
60°	11176	6397	4647
65°	10659	5375	4233
70°	10041	4428	3895
75°	9283	4036	3631
80°	8201	3608	3310
85°	6447	2853	2853



TEST NUMBER: P331808-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	2.8
10°-20°	229.7	7.6
20°-30°	322.5	10.6
30°-40°	351.7	11.6
40°-50°	323.4	10.7
50°-60°	254.0	8.4
60°-70°	165.6	5.5
70°-80°	85.4	2.8
80°-90°	23.9	0.8
90°-100°	27.0	0.9
100°-110°	83.7	2.8
110°-120°	143.1	4.7
120°-130°	188.1	6.2
130°-140°	211.2	7.0
140°-150°	207.1	6.8
150°-160°	173.7	5.7
160°-170°	115.2	3.8
170°-180°	40.3	1.3
0°-30°	635.8	21.0
0°-40°	987.5	32.6
0°-60°	1564.8	51.7
0°-90°	1839.7	60.7
90°-120°	253.7	8.4
90°-150°	860.1	28.4
90°-180°	1189.0	39.3
0°-180°	3028.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	894	894	894	894	894	
5°	894	889	879	886	884	85
15°	850	840	814	799	790	239
25°	772	744	692	660	647	355
35°	665	622	552	503	484	416
45°	543	488	404	349	328	419
55°	413	349	263	216	199	369
65°	279	213	141	115	111	277
75°	149	94	65	59	58	158
85°	35	19	15	15	15	41
90°	0	5	13	12	12	2
95°	19	22	23	23	22	21
105°	77	78	79	80	80	82
115°	144	146	145	145	144	142
125°	209	212	211	210	210	187
135°	270	274	275	274	274	209
145°	328	331	333	333	332	205
155°	375	376	377	379	378	173
165°	408	408	408	410	408	115
175°	425	424	423	425	423	40
180°	425	425	425	425	425	



TEST NUMBER: P331808-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	896.8	896.1	895.4	894.7	894.0	892.8	891.2	889.6	888.1	886.5	888.0
5°	893.6	892.7	891.8	890.9	890.0	888.4	886.1	883.8	881.4	879.1	880.7
7.5°	884.4	883.3	882.2	881.1	880.0	878.0	875.3	872.6	869.8	867.1	867.5
10°	876.6	875.4	874.1	872.8	871.6	869.2	865.5	862.0	858.4	854.8	854.3
12.5°	866.9	865.4	863.8	862.3	860.7	857.7	853.1	848.5	843.8	839.2	838.3
15°	849.9	848.0	846.0	844.0	842.0	838.0	831.9	825.8	819.7	813.6	810.2
17.5°	829.1	826.1	823.1	820.0	817.0	811.6	803.7	795.9	788.1	780.2	776.2
20°	813.6	809.9	806.4	802.8	799.2	792.9	783.9	774.9	766.0	756.9	752.4
22.5°	796.7	792.7	788.7	784.7	780.6	773.6	763.4	753.3	743.1	733.0	727.2
25°	771.5	765.7	760.0	754.2	748.5	739.7	727.9	716.0	704.1	692.2	684.8
27.5°	741.1	734.8	728.6	722.3	716.1	706.2	692.9	679.5	666.1	652.8	644.2
30°	719.8	712.9	706.1	699.3	692.4	681.8	667.4	653.1	638.7	624.3	615.1
32.5°	699.0	691.0	683.1	675.1	667.1	655.8	641.1	626.5	611.8	597.1	586.7
35°	664.7	655.6	646.4	637.2	628.1	615.6	599.8	584.0	568.2	552.3	541.0
37.5°	630.5	620.4	610.3	600.2	590.2	576.7	559.9	543.0	526.2	509.3	496.9
40°	606.5	595.7	584.9	574.2	563.4	549.3	531.9	514.4	497.0	479.6	466.8
42.5°	581.9	570.6	559.2	547.9	536.5	521.8	503.8	485.8	467.8	449.8	436.6
45°	543.4	531.4	519.4	507.3	495.3	479.8	461.0	442.1	423.2	404.3	391.6
47.5°	505.9	493.1	480.4	467.6	454.9	438.8	419.3	399.8	380.3	360.8	348.2
50°	478.7	466.0	453.2	440.5	427.7	411.5	391.7	371.9	352.1	332.4	320.0
52.5°	452.3	438.9	425.6	412.3	398.9	382.5	363.2	343.9	324.6	305.2	293.3
55°	413.3	399.3	385.2	371.2	357.2	340.5	321.1	301.7	282.3	262.8	252.1
57.5°	373.3	358.9	344.5	330.2	315.8	299.3	280.6	262.0	243.3	224.7	214.8
60°	346.1	331.8	317.3	303.0	288.6	272.2	253.7	235.1	216.7	198.1	188.9
62.5°	319.6	305.2	290.8	276.5	262.1	246.1	228.5	210.8	193.1	175.5	166.8
65°	279.0	264.4	249.9	235.4	220.8	205.4	189.3	173.1	156.9	140.7	134.6
67.5°	239.9	225.4	211.0	196.5	182.0	167.5	153.0	138.5	123.9	109.3	106.5
70°	212.7	198.7	184.7	170.6	156.6	143.4	131.0	118.6	106.2	93.8	92.0
72.5°	186.8	173.3	159.9	146.5	133.0	121.4	111.4	101.4	91.5	81.5	80.0
75°	148.8	136.3	123.7	111.1	98.5	89.1	83.0	76.9	70.8	64.7	63.5
77.5°	111.5	100.4	89.4	78.3	67.3	60.3	57.4	54.4	51.5	48.6	47.8
80°	88.2	79.0	69.8	60.7	51.5	46.0	44.2	42.4	40.6	38.8	38.1
82.5°	66.8	59.7	52.5	45.3	38.2	34.0	32.8	31.5	30.3	29.2	28.7
85°	34.8	31.0	27.3	23.4	19.6	17.5	17.0	16.5	15.9	15.4	15.4
87.5°	10.5	9.4	8.5	7.5	6.6	6.3	6.7	7.0	7.4	7.7	7.5
90°	0.4	1.3	2.3	3.2	4.2	5.5	7.3	9.0	10.8	12.6	12.4
92.5°	6.4	7.1	7.8	8.5	9.2	9.7	10.1	10.6	11.0	11.4	11.4
95°	18.7	19.5	20.3	21.1	21.9	22.3	22.5	22.7	22.8	23.0	23.0
97.5°	34.1	34.8	35.5	36.2	36.9	37.4	37.7	38.0	38.3	38.6	38.6
100°	45.6	46.2	46.8	47.5	48.2	48.6	48.8	49.0	49.3	49.5	49.5
102.5°	57.7	58.1	58.6	59.2	59.7	60.1	60.4	60.7	61.0	61.3	61.4
105°	77.2	77.4	77.6	77.9	78.1	78.3	78.5	78.7	78.8	79.0	79.1
107.5°	96.8	97.2	97.5	97.9	98.2	98.4	98.4	98.4	98.4	98.4	98.5
110°	109.5	110.0	110.4	110.9	111.4	111.6	111.6	111.6	111.6	111.6	111.6



TEST NUMBER: P331808-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.3	123.7	124.2	124.7	125.2	125.4	125.3	125.2	125.2	125.1	124.9
115°	143.5	144.0	144.5	145.0	145.4	145.6	145.4	145.3	145.1	145.0	144.9
117.5°	163.8	164.5	165.1	165.7	166.4	166.4	166.0	165.6	165.1	164.7	164.5
120°	177.3	177.9	178.6	179.2	179.8	179.8	179.2	178.6	177.9	177.3	177.3
122.5°	189.6	190.4	191.2	191.9	192.7	192.9	192.4	191.9	191.5	191.1	190.9
125°	208.9	209.6	210.3	211.0	211.8	212.0	211.8	211.5	211.3	211.0	210.8
127.5°	227.6	228.5	229.4	230.4	231.2	231.6	231.3	231.0	230.7	230.4	230.1
130°	239.4	240.4	241.5	242.5	243.5	244.0	243.8	243.7	243.5	243.4	243.2
132.5°	252.6	253.4	254.3	255.2	256.0	256.4	256.4	256.5	256.5	256.5	256.2
135°	270.3	271.2	272.0	272.9	273.8	274.3	274.4	274.6	274.7	274.9	274.8
137.5°	288.8	289.5	290.3	291.0	291.7	292.2	292.4	292.6	292.8	293.0	292.9
140°	300.1	300.8	301.5	302.2	302.9	303.5	303.9	304.3	304.7	305.1	305.1
142.5°	311.6	312.3	313.0	313.7	314.4	314.9	315.1	315.4	315.7	316.0	316.1
145°	328.0	328.6	329.2	329.7	330.3	330.8	331.3	331.8	332.2	332.7	332.8
147.5°	342.8	343.4	344.1	344.8	345.5	345.9	346.3	346.6	346.9	347.2	347.4
150°	352.8	353.3	353.8	354.3	354.7	355.1	355.5	355.8	356.1	356.4	356.6
152.5°	361.7	362.2	362.7	363.1	363.6	364.1	364.4	364.8	365.2	365.6	365.9
155°	375.0	375.3	375.5	375.8	376.0	376.3	376.5	376.8	377.0	377.2	377.6
157.5°	386.5	386.7	386.8	387.0	387.1	387.2	387.4	387.5	387.7	387.9	388.4
160°	393.4	393.6	393.7	393.9	394.0	394.1	394.2	394.3	394.3	394.4	394.9
162.5°	399.7	399.7	399.7	399.7	399.8	399.9	400.0	400.1	400.1	400.2	400.7
165°	408.1	408.0	407.9	407.8	407.7	407.7	407.7	407.7	407.7	407.7	408.3
167.5°	415.1	414.9	414.6	414.4	414.2	414.0	414.0	414.0	414.0	414.0	414.5
170°	418.8	418.6	418.4	418.1	417.9	417.7	417.6	417.6	417.5	417.4	418.0
172.5°	421.4	421.2	421.0	420.7	420.5	420.3	420.3	420.2	420.1	420.0	420.6
175°	424.6	424.4	424.1	423.9	423.7	423.4	423.3	423.1	422.9	422.8	423.3
177.5°	425.9	425.7	425.5	425.3	425.1	424.9	424.8	424.7	424.5	424.5	424.8
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3



TEST NUMBER: P331808-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	889.4	890.8	892.2	892.8	892.6	892.2	892.0	891.7
5°	882.3	883.9	885.5	886.1	885.5	884.9	884.5	883.9
7.5°	868.0	868.5	868.9	868.7	867.8	866.9	865.9	865.0
10°	853.7	853.2	852.6	851.8	850.7	849.7	848.6	847.5
12.5°	837.3	836.4	835.4	834.0	832.2	830.4	828.6	826.8
15°	806.8	803.3	799.9	797.3	795.5	793.7	791.9	790.1
17.5°	772.1	768.0	764.0	760.4	757.3	754.2	751.1	748.1
20°	748.0	743.5	738.9	734.7	730.8	726.8	722.9	718.9
22.5°	721.4	715.7	709.9	705.5	702.5	699.6	696.6	693.7
25°	677.5	670.1	662.7	657.7	655.1	652.4	649.7	647.0
27.5°	635.6	627.0	618.5	612.0	607.7	603.4	599.1	594.8
30°	606.0	596.8	587.6	580.7	575.8	570.9	566.1	561.3
32.5°	576.2	565.8	555.3	547.8	543.2	538.7	534.1	529.6
35°	529.7	518.4	507.1	499.4	495.4	491.5	487.6	483.6
37.5°	484.3	471.9	459.5	450.9	446.4	441.9	437.4	432.8
40°	454.0	441.2	428.5	419.8	415.1	410.4	405.8	401.1
42.5°	423.4	410.2	397.0	388.2	383.7	379.1	374.6	370.0
45°	378.8	366.1	353.3	344.8	340.5	336.1	331.8	327.5
47.5°	335.5	322.8	310.1	301.8	297.9	294.0	290.0	286.1
50°	307.6	295.2	282.8	274.6	270.9	267.1	263.4	259.6
52.5°	281.3	269.3	257.3	249.6	246.1	242.6	239.2	235.7
55°	241.3	230.4	219.7	212.6	209.2	205.7	202.3	198.9
57.5°	204.9	195.0	185.1	178.7	175.9	173.0	170.1	167.2
60°	179.8	170.6	161.4	155.4	152.6	149.7	146.8	143.9
62.5°	158.0	149.2	140.5	135.3	133.6	131.9	130.2	128.4
65°	128.5	122.4	116.3	113.0	112.4	111.9	111.3	110.8
67.5°	103.7	100.9	98.2	96.4	95.9	95.3	94.7	94.1
70°	90.2	88.4	86.6	85.4	84.6	83.9	83.2	82.5
72.5°	78.5	77.0	75.5	74.5	74.1	73.7	73.2	72.8
75°	62.2	60.9	59.7	58.9	58.8	58.6	58.4	58.2
77.5°	47.1	46.3	45.6	45.2	44.8	44.6	44.3	44.0
80°	37.4	36.7	36.0	35.6	35.6	35.6	35.6	35.6
82.5°	28.3	27.8	27.4	27.2	27.2	27.2	27.2	27.2
85°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
87.5°	7.4	7.1	7.0	6.9	6.9	7.0	7.0	7.0
90°	12.3	12.1	12.0	11.9	12.0	12.0	12.1	12.2
92.5°	11.5	11.5	11.6	11.6	11.6	11.6	11.6	11.6
95°	23.0	23.0	23.0	22.9	22.7	22.6	22.4	22.3
97.5°	38.6	38.6	38.6	38.6	38.6	38.6	38.6	38.6
100°	49.5	49.5	49.5	49.5	49.4	49.4	49.3	49.2
102.5°	61.4	61.5	61.6	61.6	61.5	61.4	61.3	61.2
105°	79.3	79.5	79.6	79.7	79.7	79.7	79.7	79.7
107.5°	98.5	98.6	98.7	98.5	98.2	97.8	97.4	97.0
110°	111.6	111.6	111.6	111.5	111.2	111.0	110.7	110.5



TEST NUMBER: P331808-927

CATALOG NUMBER: S122RDIW-S675D435U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	124.8	124.5	124.4	124.1	124.0	123.8	123.7	123.5
115°	144.8	144.7	144.7	144.5	144.3	144.0	143.8	143.5
117.5°	164.3	164.1	163.9	163.7	163.4	163.2	163.0	162.7
120°	177.3	177.3	177.3	177.2	177.0	176.7	176.5	176.3
122.5°	190.7	190.5	190.3	190.1	190.0	189.8	189.6	189.4
125°	210.6	210.3	210.1	209.9	209.8	209.8	209.7	209.6
127.5°	229.8	229.6	229.3	229.0	228.7	228.5	228.2	228.0
130°	243.0	242.9	242.7	242.5	242.2	241.9	241.5	241.2
132.5°	255.9	255.5	255.2	254.8	254.6	254.3	254.1	253.8
135°	274.7	274.6	274.6	274.4	274.2	273.9	273.7	273.5
137.5°	292.9	292.8	292.8	292.6	292.2	291.9	291.6	291.3
140°	305.1	305.1	305.1	304.9	304.6	304.3	304.0	303.6
142.5°	316.1	316.2	316.2	316.1	315.8	315.4	315.1	314.8
145°	332.9	333.0	333.0	332.9	332.6	332.2	331.9	331.6
147.5°	347.5	347.8	347.9	347.8	347.5	347.2	346.9	346.7
150°	356.9	357.1	357.4	357.4	357.1	356.9	356.6	356.4
152.5°	366.1	366.5	366.8	366.8	366.5	366.1	365.9	365.6
155°	378.0	378.4	378.8	378.9	378.7	378.4	378.2	378.0
157.5°	388.9	389.4	390.0	390.1	389.7	389.3	389.0	388.6
160°	395.4	395.9	396.3	396.4	396.1	395.8	395.5	395.1
162.5°	401.2	401.8	402.3	402.4	402.0	401.6	401.2	400.9
165°	408.8	409.4	410.0	410.0	409.6	409.2	408.8	408.4
167.5°	415.1	415.7	416.2	416.3	415.8	415.4	415.0	414.6
170°	418.5	419.1	419.6	419.7	419.2	418.7	418.3	417.8
172.5°	421.1	421.7	422.2	422.2	421.8	421.3	420.8	420.3
175°	423.9	424.5	425.0	425.1	424.6	424.1	423.7	423.2
177.5°	425.2	425.6	426.0	426.0	425.6	425.2	424.8	424.5
180°	425.3	425.3	425.3	425.3	425.3	425.3	425.3	425.3

(END OF REPORT)