

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331839-927

Luminaire Tested: **S122RDIW-S865D1240U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331839-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S865D1240U927-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6317.0 lumens  
Efficiency: N/A  
Efficacy: 90.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331839-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331839-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38																				
1	95	91	88	84	86	83	80	77	68	65	63	53	52	51	40	39	39	33																				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28																				
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24																				
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21																				
5	67	56	48	43	61	51	45	39	42	37	33	34	30	28	26	24	22	18																				
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16																				
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15																				
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13																				
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12																				
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13	11																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18755	18755	18755
5°	18827	18519	18621
10°	18682	18216	18061
15°	18467	17677	17167
20°	18170	16905	16057
25°	17865	16030	14982
30°	17443	15129	13601
35°	17030	14152	12390
40°	16617	13139	10989
45°	16130	12001	9720
50°	15631	10854	8475
55°	15122	9619	7279
60°	14528	8315	6042
65°	13857	6988	5501
70°	13053	5755	5061
75°	12071	5246	4722
80°	10646	4695	4305
85°	8373	3705	3705



TEST NUMBER: P331839-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.7	1.7
10°-20°	298.5	4.7
20°-30°	419.2	6.6
30°-40°	457.1	7.2
40°-50°	420.3	6.7
50°-60°	330.1	5.2
60°-70°	215.2	3.4
70°-80°	111.0	1.8
80°-90°	32.1	0.5
90°-100°	44.7	0.7
100°-110°	163.8	2.6
110°-120°	437.9	6.9
120°-130°	722.9	11.4
130°-140°	768.8	12.2
140°-150°	714.5	11.3
150°-160°	574.5	9.1
160°-170°	370.2	5.9
170°-180°	127.4	2.0
0°-30°	826.5	13.1
0°-40°	1283.6	20.3
0°-60°	2034.0	32.2
0°-90°	2392.3	37.9
90°-120°	646.4	10.2
90°-150°	2852.5	45.2
90°-180°	3925.0	62.1
0°-180°	6317.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1162	1162	1162	1162	1162	
5°	1162	1156	1143	1151	1149	110
15°	1105	1092	1058	1038	1027	311
25°	1003	967	900	858	841	461
35°	864	808	718	654	629	541
45°	706	634	526	454	426	545
55°	537	453	342	281	259	480
65°	363	277	183	149	144	359
75°	194	122	84	77	76	205
85°	45	24	20	20	20	53
90°	1	12	19	24	26	5
95°	63	33	38	42	42	77
105°	295	307	59	69	74	315
115°	557	574	598	170	80	548
125°	788	801	819	825	828	702
135°	975	990	999	1008	1007	753
145°	1131	1131	1146	1152	1148	707
155°	1245	1238	1248	1253	1246	574
165°	1312	1307	1309	1315	1309	371
175°	1342	1336	1337	1343	1334	128
180°	1339	1339	1339	1339	1339	



TEST NUMBER: P331839-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1165.8	1164.8	1163.9	1162.9	1162.1	1160.5	1158.5	1156.4	1154.4	1152.3	1154.2
5°	1161.6	1160.4	1159.2	1158.0	1156.9	1154.8	1151.8	1148.7	1145.7	1142.6	1144.7
7.5°	1149.5	1148.1	1146.7	1145.3	1143.8	1141.3	1137.7	1134.2	1130.6	1127.0	1127.7
10°	1139.5	1137.8	1136.2	1134.6	1132.9	1129.8	1125.1	1120.5	1115.8	1111.1	1110.4
12.5°	1126.9	1124.8	1122.8	1120.9	1118.8	1114.8	1108.8	1102.9	1096.9	1090.9	1089.6
15°	1104.8	1102.2	1099.6	1097.1	1094.5	1089.3	1081.3	1073.4	1065.4	1057.5	1053.0
17.5°	1077.7	1073.7	1069.8	1065.9	1062.0	1054.9	1044.7	1034.5	1024.4	1014.2	1008.9
20°	1057.5	1052.8	1048.1	1043.5	1038.8	1030.6	1018.9	1007.3	995.6	983.9	978.0
22.5°	1035.6	1030.4	1025.2	1019.9	1014.7	1005.5	992.3	979.1	966.0	952.8	945.2
25°	1002.8	995.4	987.9	980.4	973.0	961.5	946.0	930.7	915.2	899.8	890.3
27.5°	963.3	955.1	947.1	938.9	930.8	918.1	900.6	883.3	865.9	848.5	837.3
30°	935.6	926.7	917.8	908.9	900.1	886.3	867.6	848.9	830.2	811.5	799.6
32.5°	908.6	898.3	887.9	877.5	867.1	852.5	833.4	814.3	795.3	776.2	762.6
35°	864.0	852.2	840.3	828.3	816.4	800.2	779.6	759.1	738.6	718.0	703.2
37.5°	819.5	806.4	793.4	780.2	767.1	749.6	727.8	705.8	684.0	662.0	645.8
40°	788.4	774.4	760.3	746.3	732.3	714.0	691.3	668.7	646.0	623.4	606.7
42.5°	756.5	741.6	726.9	712.2	697.4	678.3	654.9	631.4	608.1	584.6	567.5
45°	706.4	690.7	675.1	659.4	643.8	623.7	599.2	574.6	550.1	525.6	509.0
47.5°	657.6	641.0	624.5	607.8	591.3	570.3	545.0	519.7	494.3	469.1	452.6
50°	622.3	605.7	589.1	572.5	556.0	534.8	509.1	483.4	457.7	432.1	415.9
52.5°	587.8	570.5	553.2	535.8	518.5	497.3	472.1	446.9	421.8	396.7	381.1
55°	537.2	519.0	500.7	482.5	464.3	442.5	417.3	392.1	366.9	341.7	327.6
57.5°	485.2	466.5	447.8	429.1	410.5	389.0	364.7	340.5	316.2	292.0	279.2
60°	449.9	431.2	412.6	393.9	375.2	353.8	329.7	305.6	281.6	257.5	245.7
62.5°	415.4	396.7	378.0	359.3	340.6	319.9	296.9	274.0	251.0	228.1	216.7
65°	362.7	343.7	324.8	305.9	287.0	267.0	246.0	225.0	203.9	182.9	175.0
67.5°	311.8	293.0	274.3	255.4	236.6	217.8	198.9	180.0	161.1	142.1	138.5
70°	276.5	258.3	240.0	221.8	203.6	186.4	170.3	154.2	138.1	121.9	119.6
72.5°	242.8	225.4	207.9	190.4	172.9	157.7	144.8	131.8	118.9	106.0	104.0
75°	193.5	177.1	160.7	144.3	128.0	115.9	107.9	100.0	92.1	84.1	82.5
77.5°	144.9	130.5	116.1	101.8	87.5	78.4	74.5	70.7	66.9	63.1	62.1
80°	114.5	102.7	90.8	78.8	66.9	59.8	57.4	55.1	52.8	50.5	49.5
82.5°	86.8	77.6	68.2	58.9	49.7	44.2	42.6	41.0	39.5	37.9	37.3
85°	45.2	40.3	35.4	30.5	25.6	22.8	22.1	21.4	20.7	20.0	20.0
87.5°	13.6	12.6	11.6	10.6	9.6	9.2	9.6	9.9	10.3	10.6	10.6
90°	1.0	3.3	5.7	8.1	10.5	12.5	14.2	15.9	17.7	19.4	20.4
92.5°	19.6	19.3	19.2	18.9	18.7	19.0	19.9	20.8	21.6	22.5	23.1
95°	63.0	55.8	48.8	41.7	34.5	31.8	33.3	34.8	36.3	37.8	38.9
97.5°	125.0	105.0	84.9	65.0	44.9	36.6	40.1	43.6	47.1	50.6	51.4
100°	171.5	142.0	112.5	83.0	53.6	40.6	44.3	47.9	51.6	55.2	57.0
102.5°	222.7	216.4	210.2	204.0	197.7	179.3	148.6	118.0	87.4	56.8	59.0
105°	294.6	301.0	307.5	313.9	320.4	294.3	235.5	176.7	117.9	59.1	61.5
107.5°	376.6	381.8	387.0	392.2	397.4	364.8	294.3	223.8	153.3	82.8	80.3
110°	429.3	433.8	438.3	442.8	447.3	418.5	356.3	294.1	231.8	169.6	148.1



TEST NUMBER: P331839-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	478.9	482.9	486.9	490.9	495.0	489.3	473.9	458.5	443.1	427.7	349.2
115°	557.2	560.9	564.5	568.2	571.9	576.4	581.8	587.2	592.6	597.9	498.2
117.5°	627.2	631.3	635.3	639.4	643.6	647.5	651.1	654.8	658.5	662.3	638.1
120°	678.3	681.6	684.8	688.0	691.3	694.8	698.7	702.6	706.5	710.3	712.9
122.5°	721.8	725.2	728.6	732.0	735.4	739.2	743.4	747.6	751.9	756.1	757.6
125°	787.8	790.6	793.4	796.2	799.0	802.5	806.6	810.6	814.8	818.9	820.4
127.5°	847.7	850.8	853.9	857.1	860.2	863.2	866.3	869.3	872.4	875.4	877.7
130°	885.7	889.1	892.6	896.0	899.5	902.4	904.8	907.1	909.5	911.9	914.3
132.5°	924.5	927.4	930.3	933.3	936.2	938.8	941.2	943.6	945.9	948.3	950.3
135°	974.9	978.3	981.8	985.2	988.6	991.3	993.2	995.2	997.1	999.1	1001.2
137.5°	1025.8	1028.3	1030.6	1033.1	1035.5	1037.8	1040.0	1042.2	1044.3	1046.6	1048.7
140°	1059.1	1060.9	1062.6	1064.3	1066.0	1068.1	1070.5	1072.9	1075.2	1077.6	1079.5
142.5°	1087.1	1088.6	1090.2	1091.7	1093.3	1095.4	1098.1	1100.8	1103.5	1106.3	1108.0
145°	1130.8	1130.7	1130.4	1130.2	1130.0	1131.7	1135.4	1139.1	1142.7	1146.4	1147.9
147.5°	1169.0	1168.2	1167.4	1166.6	1165.8	1167.2	1170.8	1174.4	1178.1	1181.6	1182.8
150°	1193.9	1192.4	1190.9	1189.3	1187.8	1188.8	1192.2	1195.7	1199.1	1202.6	1203.9
152.5°	1214.8	1213.1	1211.4	1209.7	1208.1	1208.9	1212.1	1215.4	1218.7	1221.9	1223.3
155°	1245.2	1243.3	1241.3	1239.4	1237.5	1237.8	1240.4	1242.9	1245.5	1248.2	1249.4
157.5°	1269.1	1267.4	1265.7	1264.2	1262.5	1262.6	1264.4	1266.2	1268.0	1269.9	1271.3
160°	1283.0	1281.8	1280.4	1279.1	1277.9	1277.9	1279.1	1280.4	1281.8	1283.0	1284.3
162.5°	1295.5	1294.1	1292.8	1291.6	1290.2	1290.1	1291.3	1292.4	1293.6	1294.7	1296.1
165°	1312.1	1310.8	1309.5	1308.2	1306.9	1306.6	1307.3	1307.9	1308.5	1309.2	1310.7
167.5°	1324.5	1323.2	1321.9	1320.6	1319.3	1319.0	1319.6	1320.2	1320.8	1321.4	1322.9
170°	1331.5	1330.2	1328.9	1327.6	1326.3	1325.9	1326.3	1326.7	1327.1	1327.6	1329.1
172.5°	1336.1	1334.8	1333.6	1332.2	1330.9	1330.5	1330.9	1331.3	1331.8	1332.2	1333.7
175°	1342.1	1340.6	1339.1	1337.6	1336.1	1335.5	1336.0	1336.4	1336.9	1337.3	1338.8
177.5°	1343.1	1341.9	1340.7	1339.5	1338.2	1337.8	1337.9	1338.1	1338.2	1338.5	1339.7
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2



TEST NUMBER: P331839-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1156.0	1157.9	1159.8	1160.5	1160.2	1159.8	1159.4	1159.0
5°	1146.8	1148.9	1151.0	1151.8	1151.0	1150.3	1149.6	1148.9
7.5°	1128.3	1128.9	1129.5	1129.2	1128.0	1126.8	1125.5	1124.3
10°	1109.7	1109.0	1108.3	1107.2	1105.8	1104.5	1103.0	1101.6
12.5°	1088.4	1087.1	1085.8	1084.1	1081.7	1079.4	1077.1	1074.8
15°	1048.6	1044.2	1039.7	1036.3	1034.0	1031.7	1029.4	1027.0
17.5°	1003.6	998.3	993.1	988.4	984.4	980.4	976.4	972.3
20°	972.2	966.4	960.5	955.1	949.9	944.8	939.6	934.5
22.5°	937.8	930.3	922.7	917.0	913.2	909.3	905.5	901.7
25°	880.7	871.1	861.5	854.9	851.4	848.0	844.5	841.0
27.5°	826.2	815.0	803.8	795.5	790.0	784.3	778.8	773.2
30°	787.7	775.8	763.8	754.7	748.5	742.1	735.9	729.5
32.5°	749.0	735.4	721.8	712.0	706.2	700.2	694.3	688.3
35°	688.5	673.8	659.1	649.2	644.0	638.9	633.7	628.6
37.5°	629.6	613.4	597.2	586.1	580.3	574.3	568.5	562.6
40°	590.2	573.6	557.0	545.7	539.6	533.5	527.4	521.4
42.5°	550.4	533.2	516.1	504.5	498.7	492.8	486.9	481.0
45°	492.4	475.9	459.2	448.1	442.5	437.0	431.3	425.7
47.5°	436.0	419.5	403.1	392.3	387.2	382.1	377.0	371.9
50°	399.8	383.7	367.6	357.0	352.1	347.2	342.3	337.4
52.5°	365.6	350.1	334.5	324.5	319.9	315.4	310.9	306.3
55°	313.6	299.6	285.6	276.3	271.9	267.4	263.0	258.6
57.5°	266.3	253.5	240.7	232.3	228.6	224.8	221.1	217.4
60°	233.7	221.8	209.8	202.1	198.3	194.6	190.8	187.1
62.5°	205.4	194.1	182.7	175.9	173.6	171.4	169.1	166.9
65°	167.0	159.1	151.1	146.8	146.1	145.4	144.7	144.0
67.5°	134.8	131.2	127.5	125.3	124.6	123.8	123.1	122.4
70°	117.2	114.9	112.6	111.0	110.0	109.1	108.1	107.2
72.5°	102.0	100.1	98.1	96.9	96.3	95.7	95.1	94.6
75°	80.8	79.2	77.6	76.6	76.4	76.1	75.9	75.7
77.5°	61.2	60.3	59.3	58.7	58.3	57.9	57.6	57.2
80°	48.6	47.7	46.7	46.3	46.3	46.3	46.3	46.3
82.5°	36.8	36.1	35.6	35.3	35.3	35.3	35.3	35.3
85°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
87.5°	10.7	10.7	10.7	10.8	10.9	10.9	11.0	11.1
90°	21.5	22.6	23.7	24.5	24.9	25.3	25.7	26.1
92.5°	23.6	24.2	24.7	25.1	25.3	25.7	25.9	26.1
95°	39.9	41.0	42.1	42.5	42.3	42.1	41.9	41.7
97.5°	52.3	53.2	54.0	54.6	54.8	55.1	55.4	55.6
100°	58.7	60.4	62.1	63.2	63.6	64.1	64.5	65.0
102.5°	61.2	63.5	65.8	67.2	67.7	68.4	69.0	69.6
105°	63.8	66.2	68.6	70.2	71.1	71.9	72.8	73.7
107.5°	78.0	75.5	73.1	72.3	73.2	74.1	74.9	75.8
110°	126.5	105.0	83.4	73.1	74.0	74.9	75.7	76.5





TEST NUMBER: P331839-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	270.6	192.1	113.5	74.5	75.3	76.0	76.6	77.3
115°	398.5	298.8	199.1	141.5	126.0	110.5	95.0	79.5
117.5°	614.0	589.9	565.8	528.2	477.3	426.4	375.4	324.4
120°	715.5	718.0	720.6	707.4	678.3	649.3	620.2	591.1
122.5°	759.1	760.7	762.2	760.2	754.6	748.9	743.3	737.6
125°	821.9	823.4	824.9	825.9	826.6	827.3	827.9	828.5
127.5°	879.8	882.0	884.2	885.4	885.5	885.7	885.7	885.9
130°	916.6	919.0	921.3	922.4	922.2	922.0	921.8	921.5
132.5°	952.4	954.3	956.4	957.3	957.1	956.9	956.6	956.5
135°	1003.4	1005.5	1007.7	1008.5	1008.1	1007.7	1007.3	1006.9
137.5°	1050.8	1052.9	1055.0	1055.7	1054.9	1054.2	1053.5	1052.7
140°	1081.5	1083.4	1085.4	1085.8	1084.7	1083.6	1082.5	1081.5
142.5°	1109.8	1111.6	1113.3	1113.6	1112.6	1111.5	1110.4	1109.4
145°	1149.4	1150.9	1152.4	1152.6	1151.5	1150.5	1149.4	1148.3
147.5°	1183.9	1185.0	1186.1	1186.2	1185.3	1184.4	1183.5	1182.6
150°	1205.1	1206.5	1207.8	1207.8	1206.8	1205.7	1204.6	1203.6
152.5°	1224.6	1225.8	1227.2	1227.1	1225.7	1224.2	1222.8	1221.4
155°	1250.7	1252.0	1253.3	1253.1	1251.3	1249.7	1247.9	1246.2
157.5°	1272.8	1274.2	1275.7	1275.6	1273.9	1272.2	1270.6	1268.8
160°	1285.6	1286.9	1288.2	1288.1	1286.6	1285.1	1283.6	1282.1
162.5°	1297.6	1299.0	1300.5	1300.3	1298.5	1296.6	1294.7	1292.9
165°	1312.2	1313.7	1315.2	1315.2	1313.7	1312.2	1310.7	1309.2
167.5°	1324.4	1325.9	1327.4	1327.2	1325.2	1323.3	1321.4	1319.5
170°	1330.6	1332.1	1333.6	1333.4	1331.5	1329.5	1327.6	1325.6
172.5°	1335.2	1336.7	1338.2	1338.1	1336.1	1334.2	1332.2	1330.3
175°	1340.3	1341.8	1343.3	1343.0	1340.8	1338.7	1336.5	1334.4
177.5°	1340.8	1342.0	1343.3	1343.1	1341.6	1340.0	1338.5	1336.9
180°	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2	1339.2

(END OF REPORT)