

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331840-927

Luminaire Tested: **S122RDIW-S865D1240U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331840-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S865D1240U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5797.4 lumens  
Efficiency: N/A  
Efficacy: 83.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331840-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331840-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23
5	68	57	49	43	62	52	45	40	44	38	34	36	32	29	28	26	23	20
6	63	51	43	37	57	47	40	35	39	34	30	32	28	26	26	23	21	18
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18755	18755	18755
5°	18827	18519	18621
10°	18682	18216	18061
15°	18467	17677	17167
20°	18170	16905	16057
25°	17865	16030	14982
30°	17443	15129	13601
35°	17030	14152	12390
40°	16617	13139	10989
45°	16130	12001	9720
50°	15631	10854	8475
55°	15122	9619	7279
60°	14528	8315	6042
65°	13857	6988	5501
70°	13053	5755	5061
75°	12071	5246	4722
80°	10646	4695	4305
85°	8373	3705	3705



TEST NUMBER: P331840-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.7	1.9
10°-20°	298.5	5.1
20°-30°	419.2	7.2
30°-40°	457.1	7.9
40°-50°	420.3	7.3
50°-60°	330.1	5.7
60°-70°	215.2	3.7
70°-80°	111.0	1.9
80°-90°	33.7	0.6
90°-100°	77.1	1.3
100°-110°	239.6	4.1
110°-120°	409.5	7.1
120°-130°	538.5	9.3
130°-140°	604.4	10.4
140°-150°	592.6	10.2
150°-160°	497.0	8.6
160°-170°	329.7	5.7
170°-180°	115.2	2.0
0°-30°	826.5	14.3
0°-40°	1283.6	22.1
0°-60°	2034.0	35.1
0°-90°	2393.9	41.3
90°-120°	726.2	12.5
90°-150°	2461.6	42.5
90°-180°	3404.0	58.7
0°-180°	5797.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1162	1162	1162	1162	1162	
5°	1162	1156	1143	1151	1149	110
15°	1105	1092	1058	1038	1027	311
25°	1003	967	900	858	841	461
35°	864	808	718	654	629	541
45°	706	634	526	454	426	545
55°	537	453	342	281	259	480
65°	363	277	183	149	144	359
75°	194	122	84	77	76	205
85°	45	24	20	20	20	53
90°	1	14	36	34	35	5
95°	53	63	66	66	64	61
105°	221	224	226	228	228	233
115°	411	417	415	414	411	406
125°	598	606	604	601	600	534
135°	774	784	787	786	783	597
145°	939	946	952	953	949	586
155°	1073	1076	1080	1084	1082	494
165°	1168	1167	1167	1173	1169	329
175°	1215	1212	1210	1216	1211	115
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P331840-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1165.8	1164.8	1163.9	1162.9	1162.1	1160.5	1158.5	1156.4	1154.4	1152.3	1154.2
5°	1161.6	1160.4	1159.2	1158.0	1156.9	1154.8	1151.8	1148.7	1145.7	1142.6	1144.7
7.5°	1149.5	1148.1	1146.7	1145.3	1143.8	1141.3	1137.7	1134.2	1130.6	1127.0	1127.7
10°	1139.5	1137.8	1136.2	1134.6	1132.9	1129.8	1125.1	1120.5	1115.8	1111.1	1110.4
12.5°	1126.9	1124.8	1122.8	1120.9	1118.8	1114.8	1108.8	1102.9	1096.9	1090.9	1089.6
15°	1104.8	1102.2	1099.6	1097.1	1094.5	1089.3	1081.3	1073.4	1065.4	1057.5	1053.0
17.5°	1077.7	1073.7	1069.8	1065.9	1062.0	1054.9	1044.7	1034.5	1024.4	1014.2	1008.9
20°	1057.5	1052.8	1048.1	1043.5	1038.8	1030.6	1018.9	1007.3	995.6	983.9	978.0
22.5°	1035.6	1030.4	1025.2	1019.9	1014.7	1005.5	992.3	979.1	966.0	952.8	945.2
25°	1002.8	995.4	987.9	980.4	973.0	961.5	946.0	930.7	915.2	899.8	890.3
27.5°	963.3	955.1	947.1	938.9	930.8	918.1	900.6	883.3	865.9	848.5	837.3
30°	935.6	926.7	917.8	908.9	900.1	886.3	867.6	848.9	830.2	811.5	799.6
32.5°	908.6	898.3	887.9	877.5	867.1	852.5	833.4	814.3	795.3	776.2	762.6
35°	864.0	852.2	840.3	828.3	816.4	800.2	779.6	759.1	738.6	718.0	703.2
37.5°	819.5	806.4	793.4	780.2	767.1	749.6	727.8	705.8	684.0	662.0	645.8
40°	788.4	774.4	760.3	746.3	732.3	714.0	691.3	668.7	646.0	623.4	606.7
42.5°	756.5	741.6	726.9	712.2	697.4	678.3	654.9	631.4	608.1	584.6	567.5
45°	706.4	690.7	675.1	659.4	643.8	623.7	599.2	574.6	550.1	525.6	509.0
47.5°	657.6	641.0	624.5	607.8	591.3	570.3	545.0	519.7	494.3	469.1	452.6
50°	622.3	605.7	589.1	572.5	556.0	534.8	509.1	483.4	457.7	432.1	415.9
52.5°	587.8	570.5	553.2	535.8	518.5	497.3	472.1	446.9	421.8	396.7	381.1
55°	537.2	519.0	500.7	482.5	464.3	442.5	417.3	392.1	366.9	341.7	327.6
57.5°	485.2	466.5	447.8	429.1	410.5	389.0	364.7	340.5	316.2	292.0	279.2
60°	449.9	431.2	412.6	393.9	375.2	353.8	329.7	305.6	281.6	257.5	245.7
62.5°	415.4	396.7	378.0	359.3	340.6	319.9	296.9	274.0	251.0	228.1	216.7
65°	362.7	343.7	324.8	305.9	287.0	267.0	246.0	225.0	203.9	182.9	175.0
67.5°	311.8	293.0	274.3	255.4	236.6	217.8	198.9	180.0	161.1	142.1	138.5
70°	276.5	258.3	240.0	221.8	203.6	186.4	170.3	154.2	138.1	121.9	119.6
72.5°	242.8	225.4	207.9	190.4	172.9	157.7	144.8	131.8	118.9	106.0	104.0
75°	193.5	177.1	160.7	144.3	128.0	115.9	107.9	100.0	92.1	84.1	82.5
77.5°	144.9	130.5	116.1	101.8	87.5	78.4	74.5	70.7	66.9	63.1	62.1
80°	114.5	102.7	90.8	78.8	66.9	59.8	57.4	55.1	52.8	50.5	49.5
82.5°	86.8	77.6	68.2	58.9	49.7	44.2	42.6	41.0	39.5	37.9	37.3
85°	45.2	40.3	35.4	30.5	25.6	22.8	22.1	21.4	20.7	20.0	20.0
87.5°	13.6	12.7	11.8	10.9	9.9	9.9	10.9	11.9	12.9	13.9	13.6
90°	1.0	3.8	6.5	9.3	12.0	15.8	20.9	25.9	30.9	36.0	35.5
92.5°	18.3	20.3	22.3	24.3	26.3	27.9	29.1	30.3	31.4	32.6	32.7
95°	53.4	55.7	58.0	60.3	62.6	63.9	64.4	64.8	65.3	65.8	65.8
97.5°	97.6	99.6	101.6	103.6	105.6	107.0	107.9	108.8	109.6	110.5	110.5
100°	130.5	132.3	134.1	135.9	137.8	139.0	139.7	140.4	141.1	141.7	141.7
102.5°	164.9	166.4	167.9	169.4	170.8	172.0	172.9	173.7	174.6	175.5	175.6
105°	220.9	221.5	222.2	222.9	223.6	224.2	224.6	225.1	225.5	226.0	226.4
107.5°	277.1	278.1	279.2	280.1	281.1	281.6	281.6	281.6	281.6	281.6	281.9
110°	313.3	314.7	316.0	317.4	318.8	319.5	319.5	319.5	319.5	319.5	319.5



TEST NUMBER: P331840-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	352.8	354.1	355.5	356.9	358.2	358.8	358.6	358.5	358.2	358.1	357.5
115°	410.9	412.3	413.6	414.9	416.4	416.8	416.4	415.9	415.4	414.9	414.8
117.5°	468.8	470.6	472.5	474.3	476.1	476.4	475.1	473.8	472.5	471.3	470.7
120°	507.4	509.2	511.1	512.9	514.8	514.8	512.9	511.1	509.2	507.4	507.4
122.5°	542.7	544.9	547.2	549.3	551.5	552.0	550.7	549.5	548.1	546.8	546.3
125°	597.8	599.8	601.9	604.0	606.0	606.7	606.0	605.4	604.7	604.0	603.3
127.5°	651.4	654.0	656.6	659.3	661.9	662.7	661.9	661.1	660.3	659.4	658.6
130°	685.2	688.1	691.1	694.0	697.0	698.2	697.8	697.4	696.9	696.4	695.9
132.5°	722.9	725.3	727.8	730.2	732.6	733.9	734.0	734.0	734.1	734.2	733.2
135°	773.5	775.9	778.5	781.0	783.5	785.0	785.4	785.9	786.4	786.8	786.6
137.5°	826.6	828.7	830.8	832.8	834.9	836.2	836.8	837.4	838.0	838.6	838.4
140°	858.7	860.8	862.8	864.9	867.0	868.5	869.7	870.8	872.0	873.1	873.1
142.5°	891.6	893.7	895.7	897.8	899.8	901.2	902.0	902.8	903.6	904.4	904.5
145°	938.8	940.5	942.1	943.6	945.2	946.7	948.1	949.4	950.9	952.2	952.4
147.5°	981.0	982.9	984.8	986.7	988.6	990.1	990.9	991.9	992.8	993.7	994.2
150°	1009.7	1011.1	1012.5	1013.8	1015.2	1016.4	1017.2	1018.2	1019.1	1020.0	1020.6
152.5°	1035.2	1036.6	1037.9	1039.3	1040.7	1041.9	1043.0	1044.1	1045.2	1046.3	1047.2
155°	1073.4	1074.1	1074.8	1075.5	1076.2	1076.8	1077.5	1078.2	1078.9	1079.6	1080.7
157.5°	1106.0	1106.5	1107.0	1107.5	1107.9	1108.3	1108.7	1109.1	1109.5	1110.0	1111.5
160°	1125.8	1126.2	1126.7	1127.2	1127.6	1128.0	1128.1	1128.4	1128.6	1128.9	1130.2
162.5°	1143.8	1144.0	1144.1	1144.1	1144.2	1144.4	1144.6	1144.9	1145.1	1145.3	1146.8
165°	1167.9	1167.7	1167.4	1167.2	1167.0	1166.9	1166.9	1166.9	1166.9	1166.9	1168.5
167.5°	1188.0	1187.3	1186.7	1186.0	1185.3	1184.9	1184.9	1184.9	1184.8	1184.7	1186.4
170°	1198.7	1198.0	1197.4	1196.7	1196.0	1195.6	1195.3	1195.1	1194.8	1194.6	1196.2
172.5°	1206.1	1205.5	1204.8	1204.0	1203.4	1202.9	1202.7	1202.5	1202.2	1202.0	1203.6
175°	1215.1	1214.5	1213.8	1213.1	1212.4	1211.9	1211.4	1210.9	1210.5	1210.0	1211.6
177.5°	1218.9	1218.3	1217.7	1217.2	1216.6	1216.2	1215.8	1215.4	1215.1	1214.7	1215.8
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2



TEST NUMBER: P331840-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1156.0	1157.9	1159.8	1160.5	1160.2	1159.8	1159.4	1159.0
5°	1146.8	1148.9	1151.0	1151.8	1151.0	1150.3	1149.6	1148.9
7.5°	1128.3	1128.9	1129.5	1129.2	1128.0	1126.8	1125.5	1124.3
10°	1109.7	1109.0	1108.3	1107.2	1105.8	1104.5	1103.0	1101.6
12.5°	1088.4	1087.1	1085.8	1084.1	1081.7	1079.4	1077.1	1074.8
15°	1048.6	1044.2	1039.7	1036.3	1034.0	1031.7	1029.4	1027.0
17.5°	1003.6	998.3	993.1	988.4	984.4	980.4	976.4	972.3
20°	972.2	966.4	960.5	955.1	949.9	944.8	939.6	934.5
22.5°	937.8	930.3	922.7	917.0	913.2	909.3	905.5	901.7
25°	880.7	871.1	861.5	854.9	851.4	848.0	844.5	841.0
27.5°	826.2	815.0	803.8	795.5	790.0	784.3	778.8	773.2
30°	787.7	775.8	763.8	754.7	748.5	742.1	735.9	729.5
32.5°	749.0	735.4	721.8	712.0	706.2	700.2	694.3	688.3
35°	688.5	673.8	659.1	649.2	644.0	638.9	633.7	628.6
37.5°	629.6	613.4	597.2	586.1	580.3	574.3	568.5	562.6
40°	590.2	573.6	557.0	545.7	539.6	533.5	527.4	521.4
42.5°	550.4	533.2	516.1	504.5	498.7	492.8	486.9	481.0
45°	492.4	475.9	459.2	448.1	442.5	437.0	431.3	425.7
47.5°	436.0	419.5	403.1	392.3	387.2	382.1	377.0	371.9
50°	399.8	383.7	367.6	357.0	352.1	347.2	342.3	337.4
52.5°	365.6	350.1	334.5	324.5	319.9	315.4	310.9	306.3
55°	313.6	299.6	285.6	276.3	271.9	267.4	263.0	258.6
57.5°	266.3	253.5	240.7	232.3	228.6	224.8	221.1	217.4
60°	233.7	221.8	209.8	202.1	198.3	194.6	190.8	187.1
62.5°	205.4	194.1	182.7	175.9	173.6	171.4	169.1	166.9
65°	167.0	159.1	151.1	146.8	146.1	145.4	144.7	144.0
67.5°	134.8	131.2	127.5	125.3	124.6	123.8	123.1	122.4
70°	117.2	114.9	112.6	111.0	110.0	109.1	108.1	107.2
72.5°	102.0	100.1	98.1	96.9	96.3	95.7	95.1	94.6
75°	80.8	79.2	77.6	76.6	76.4	76.1	75.9	75.7
77.5°	61.2	60.3	59.3	58.7	58.3	57.9	57.6	57.2
80°	48.6	47.7	46.7	46.3	46.3	46.3	46.3	46.3
82.5°	36.8	36.1	35.6	35.3	35.3	35.3	35.3	35.3
85°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
87.5°	13.4	13.1	12.8	12.7	12.8	12.8	12.8	12.8
90°	35.0	34.6	34.1	34.0	34.2	34.5	34.7	34.9
92.5°	32.9	33.0	33.0	33.1	33.1	33.2	33.3	33.3
95°	65.8	65.8	65.8	65.5	65.0	64.6	64.2	63.7
97.5°	110.5	110.5	110.5	110.5	110.4	110.4	110.4	110.4
100°	141.7	141.7	141.7	141.6	141.4	141.2	140.9	140.7
102.5°	175.8	176.0	176.2	176.2	175.9	175.7	175.5	175.2
105°	226.9	227.4	227.8	228.1	228.1	228.1	228.1	228.1
107.5°	282.0	282.2	282.4	281.9	280.9	279.9	278.8	277.7
110°	319.5	319.5	319.5	319.1	318.5	317.7	317.0	316.4





TEST NUMBER: P331840-927

CATALOG NUMBER: S122RDIW-S865D1240U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	357.0	356.4	355.8	355.4	354.8	354.3	353.9	353.3
115°	414.5	414.3	414.1	413.6	413.0	412.3	411.5	410.9
117.5°	470.2	469.6	469.1	468.5	467.8	467.1	466.4	465.7
120°	507.4	507.4	507.4	507.1	506.4	505.7	505.0	504.4
122.5°	545.8	545.3	544.7	544.2	543.7	543.1	542.6	542.2
125°	602.6	601.9	601.3	600.8	600.6	600.3	600.1	599.8
127.5°	657.8	657.0	656.2	655.4	654.7	653.9	653.2	652.4
130°	695.5	695.1	694.6	694.0	693.0	692.1	691.2	690.2
132.5°	732.2	731.2	730.2	729.4	728.6	727.9	727.1	726.4
135°	786.4	786.2	785.9	785.4	784.7	784.1	783.4	782.7
137.5°	838.2	838.0	837.9	837.3	836.4	835.5	834.6	833.7
140°	873.1	873.1	873.1	872.7	871.7	870.8	869.9	869.0
142.5°	904.7	904.9	905.1	904.7	903.8	902.9	902.0	901.0
145°	952.7	952.9	953.1	952.8	951.9	950.9	950.1	949.1
147.5°	994.7	995.2	995.7	995.5	994.7	993.8	992.9	992.0
150°	1021.4	1022.1	1022.7	1022.7	1022.1	1021.4	1020.6	1020.0
152.5°	1048.1	1048.8	1049.7	1049.7	1048.8	1048.1	1047.2	1046.3
155°	1081.9	1083.0	1084.1	1084.3	1083.7	1083.0	1082.3	1081.6
157.5°	1113.1	1114.6	1116.2	1116.4	1115.3	1114.2	1113.1	1112.0
160°	1131.6	1133.0	1134.3	1134.6	1133.7	1132.7	1131.9	1130.9
162.5°	1148.4	1149.9	1151.5	1151.8	1150.6	1149.5	1148.4	1147.4
165°	1170.1	1171.6	1173.3	1173.5	1172.4	1171.2	1170.1	1168.9
167.5°	1188.0	1189.5	1191.1	1191.4	1190.2	1189.0	1187.8	1186.6
170°	1197.8	1199.4	1201.0	1201.1	1199.8	1198.4	1197.0	1195.6
172.5°	1205.2	1206.8	1208.4	1208.5	1207.1	1205.8	1204.4	1203.0
175°	1213.2	1214.8	1216.4	1216.6	1215.1	1213.8	1212.4	1211.0
177.5°	1217.0	1218.1	1219.1	1219.1	1218.1	1217.0	1215.8	1214.7
180°	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2	1217.2

(END OF REPORT)