

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331609-830

Luminaire Tested: **S122DIW-S1005D1440U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331609-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1440U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9580.2 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	27	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30344	30344	30344	30344
5°	34020	30543	27067	30543
10°	38984	30293	23423	30293
15°	43127	29737	20694	29737
20°	42471	29141	18866	29141
25°	38297	28349	17706	28349
30°	31646	27082	16861	27082
35°	23065	25754	16259	25754
40°	18421	24190	15924	24190
45°	16098	22379	15470	22379
50°	15131	20627	15169	20627
55°	13948	18849	14762	18849
60°	12784	16956	14134	16956
65°	11645	15259	13521	15259
70°	10570	13605	12619	13605
75°	9370	11759	11179	11759
80°	8061	9735	9000	9735
85°	7225	7225	5354	7225



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.0	1.9
10°-20°	520.4	5.4
20°-30°	755.2	7.9
30°-40°	796.9	8.3
40°-50°	705.6	7.4
50°-60°	563.1	5.9
60°-70°	382.7	4.0
70°-80°	196.2	2.0
80°-90°	51.9	0.5
90°-100°	61.8	0.6
100°-110°	226.6	2.4
110°-120°	605.8	6.3
120°-130°	1000.0	10.4
130°-140°	1063.4	11.1
140°-150°	988.4	10.3
150°-160°	794.7	8.3
160°-170°	512.1	5.3
170°-180°	176.3	1.8
0°-30°	1454.6	15.2
0°-40°	2251.5	23.5
0°-60°	3520.2	36.7
0°-90°	4151.1	43.3
90°-120°	894.2	9.3
90°-150°	3946.0	41.2
90°-180°	5429.0	56.7
0°-180°	9580.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1879	1879	1879	1879	1879	
5°	2099	1884	1670	1884	2099	210
15°	2580	1779	1238	1779	2580	712
25°	2150	1591	994	1591	2150	972
35°	1170	1307	825	1307	1170	761
45°	705	980	678	980	705	554
55°	496	670	524	670	496	444
65°	305	399	354	399	305	303
75°	150	188	179	188	150	161
85°	39	39	29	39	39	44
90°	36	1	36	1	36	18
95°	58	87	58	87	58	54
105°	102	408	102	408	102	106
115°	110	771	110	771	110	275
125°	1146	1090	1146	1090	1146	992
135°	1393	1349	1393	1349	1393	1073
145°	1589	1564	1589	1564	1589	993
155°	1724	1723	1724	1723	1724	795
165°	1811	1815	1811	1815	1811	511
175°	1846	1857	1846	1857	1846	176
180°	1853	1853	1853	1853	1853	



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1966.1	1966.7	1967.8	1958.6	1957.5	1957.5	1949.4	1942.5	1934.4	1923.4	1924.6
5°	2099.0	2107.0	2109.9	2101.2	2088.2	2086.8	2074.5	2054.3	2035.5	2020.3	2009.5
7.5°	2257.7	2260.9	2253.8	2242.4	2232.7	2215.4	2192.5	2170.1	2138.8	2110.1	2088.7
10°	2377.8	2382.2	2369.9	2353.3	2339.6	2319.4	2286.1	2252.2	2211.0	2171.3	2139.5
12.5°	2469.2	2479.8	2464.1	2461.9	2438.5	2410.6	2371.1	2353.9	2295.9	2240.6	2206.6
15°	2580.1	2579.4	2580.9	2567.1	2549.8	2545.4	2503.6	2458.1	2376.4	2343.9	2287.6
17.5°	2548.1	2559.0	2564.1	2563.9	2563.5	2560.8	2547.3	2518.6	2477.7	2425.0	2359.9
20°	2471.8	2486.2	2488.4	2505.0	2514.4	2526.7	2531.8	2523.8	2498.5	2454.5	2398.1
22.5°	2353.9	2358.0	2364.7	2390.6	2410.9	2441.8	2457.8	2484.4	2474.8	2453.2	2406.2
25°	2149.7	2142.4	2167.7	2180.7	2227.6	2276.7	2312.2	2351.2	2385.9	2406.8	2393.0
27.5°	1904.3	1893.5	1931.4	1965.9	2004.0	2057.2	2112.3	2177.5	2231.7	2299.4	2322.7
30°	1697.4	1703.9	1740.0	1776.9	1834.7	1909.8	1971.9	2043.4	2120.7	2196.6	2249.3
32.5°	1474.4	1499.4	1522.2	1578.7	1629.6	1713.4	1804.3	1893.8	1990.2	2076.4	2158.0
35°	1170.2	1199.0	1230.9	1272.0	1343.5	1426.5	1515.4	1636.1	1767.6	1885.3	1982.1
37.5°	985.0	980.3	998.5	1028.3	1086.2	1153.3	1255.6	1374.7	1529.5	1667.8	1804.3
40°	874.0	871.1	884.1	911.5	955.6	1004.8	1094.3	1199.0	1342.7	1511.8	1674.3
42.5°	797.8	799.5	806.7	826.0	856.2	896.6	963.7	1052.8	1184.5	1343.7	1518.3
45°	705.0	710.0	718.0	727.4	744.7	778.0	815.5	879.1	983.1	1116.0	1287.9
47.5°	638.2	638.4	646.5	654.7	665.0	683.7	714.4	754.2	827.6	935.9	1083.6
50°	602.4	597.4	603.1	609.6	620.5	633.5	653.7	691.3	740.4	827.7	951.3
52.5°	558.5	558.6	563.8	566.3	576.0	589.0	607.5	633.5	678.0	746.3	847.8
55°	495.5	499.1	502.0	506.3	515.0	524.4	538.9	556.2	590.9	642.2	717.3
57.5°	436.3	437.4	440.4	448.6	454.0	462.7	476.5	492.2	514.7	552.7	609.2
60°	395.9	395.9	401.6	405.2	412.5	421.1	432.0	447.1	467.3	498.4	543.9
62.5°	358.8	358.3	360.6	366.5	372.0	380.1	390.9	403.8	422.8	450.4	487.9
65°	304.8	303.4	307.7	309.2	314.9	322.9	331.6	345.3	360.4	380.7	413.9
67.5°	252.8	254.6	256.8	259.6	262.8	271.2	276.9	286.6	299.4	316.2	338.7
70°	223.9	223.9	223.9	226.1	230.5	234.8	240.5	248.5	260.8	275.2	295.4
72.5°	191.5	193.9	196.1	194.9	200.4	202.9	209.9	214.4	226.1	235.4	253.3
75°	150.2	150.2	150.2	153.8	156.0	158.2	162.5	166.8	172.7	184.2	193.6
77.5°	112.1	111.8	112.5	113.4	115.7	118.3	119.6	123.5	128.8	134.2	142.1
80°	86.7	88.1	88.9	90.3	90.3	91.7	92.5	97.6	101.1	104.7	109.8
82.5°	67.0	67.3	67.5	67.8	68.3	69.2	71.1	72.7	74.0	77.0	80.9
85°	39.0	38.3	38.3	39.7	39.0	39.0	40.4	41.8	41.8	42.6	44.8
87.5°	22.2	22.1	22.6	21.9	21.8	22.1	21.9	21.0	21.3	21.6	21.7
90°	36.2	35.6	35.0	34.4	33.8	32.8	31.3	29.8	28.3	26.8	24.4
92.5°	36.2	35.8	35.4	35.2	34.8	34.2	33.5	32.6	31.9	31.1	29.9
95°	57.7	58.0	58.2	58.5	58.8	58.2	56.7	55.2	53.7	52.3	50.2
97.5°	76.9	76.6	76.3	75.9	75.5	74.7	73.5	72.4	71.2	69.9	65.1
100°	89.8	89.3	88.6	88.0	87.5	86.0	83.6	81.2	78.8	76.4	71.4
102.5°	96.2	95.4	94.5	93.8	92.9	91.0	87.8	84.7	81.6	78.5	72.9
105°	101.9	100.7	99.5	98.3	97.1	94.9	91.6	88.3	85.0	81.8	76.1
107.5°	104.8	103.7	102.5	101.2	100.1	101.1	104.4	107.8	111.1	114.5	120.0
110°	105.9	104.7	103.5	102.4	101.1	115.5	145.2	175.0	204.8	234.6	320.7



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	107.0	106.0	105.1	104.2	103.1	157.0	265.7	374.4	483.1	591.7	612.9
115°	109.9	131.4	152.8	174.3	195.7	275.4	413.3	551.3	689.2	827.1	819.6
117.5°	448.8	519.2	589.7	660.3	730.8	782.7	816.1	849.4	882.8	916.2	911.0
120°	817.7	857.9	898.1	938.4	978.5	996.9	993.3	989.8	986.2	982.6	977.2
122.5°	1020.4	1028.2	1036.0	1043.8	1051.6	1054.4	1052.3	1050.2	1048.0	1045.8	1040.0
125°	1146.1	1145.3	1144.3	1143.5	1142.6	1141.0	1139.0	1136.9	1134.8	1132.7	1127.1
127.5°	1225.5	1225.3	1225.1	1224.9	1224.8	1223.1	1220.1	1217.1	1214.1	1211.1	1206.8
130°	1274.8	1275.2	1275.4	1275.7	1276.0	1274.5	1271.3	1268.0	1264.7	1261.4	1258.1
132.5°	1323.0	1323.4	1323.7	1324.0	1324.3	1323.0	1320.2	1317.4	1314.7	1311.8	1308.5
135°	1392.8	1393.4	1394.0	1394.6	1395.2	1394.0	1391.0	1388.0	1385.1	1382.1	1379.4
137.5°	1456.3	1457.4	1458.4	1459.3	1460.4	1459.4	1456.5	1453.6	1450.7	1447.7	1444.7
140°	1496.0	1497.5	1499.0	1500.5	1501.9	1501.4	1498.7	1496.0	1493.4	1490.6	1487.4
142.5°	1534.6	1536.2	1537.6	1539.1	1540.6	1540.1	1537.7	1535.2	1532.8	1530.3	1526.5
145°	1588.6	1590.0	1591.5	1593.0	1594.5	1594.2	1592.0	1590.0	1587.9	1585.8	1580.7
147.5°	1636.0	1637.2	1638.5	1639.7	1641.0	1640.9	1639.3	1637.8	1636.2	1634.7	1629.7
150°	1664.9	1666.4	1667.9	1669.4	1670.8	1670.8	1669.0	1667.2	1665.4	1663.6	1658.8
152.5°	1689.6	1691.6	1693.6	1695.4	1697.4	1697.5	1695.7	1693.9	1692.1	1690.4	1685.8
155°	1723.9	1726.3	1728.7	1731.1	1733.4	1733.7	1731.9	1730.1	1728.3	1726.5	1723.1
157.5°	1755.3	1757.6	1759.9	1762.3	1764.5	1764.7	1762.6	1760.7	1758.7	1756.6	1754.1
160°	1773.5	1775.6	1777.6	1779.8	1781.9	1782.0	1780.2	1778.4	1776.6	1774.8	1773.0
162.5°	1788.6	1791.1	1793.7	1796.2	1798.7	1799.0	1797.1	1795.0	1793.0	1790.9	1789.4
165°	1811.0	1813.2	1815.2	1817.3	1819.4	1819.4	1817.3	1815.2	1813.2	1811.0	1810.2
167.5°	1825.2	1828.0	1830.6	1833.3	1836.0	1836.3	1834.2	1832.1	1830.0	1828.0	1827.1
170°	1833.8	1836.5	1839.2	1841.9	1844.6	1844.8	1842.8	1840.7	1838.6	1836.5	1835.9
172.5°	1840.2	1843.0	1845.6	1848.3	1851.0	1851.2	1849.2	1847.1	1845.0	1843.0	1842.4
175°	1845.9	1848.9	1851.8	1854.8	1857.8	1858.2	1856.1	1854.1	1852.0	1849.9	1849.4
177.5°	1849.4	1851.5	1853.7	1855.8	1857.9	1858.2	1856.5	1854.8	1853.2	1851.5	1851.2
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1928.6	1924.0	1921.1	1910.7	1901.4	1892.2	1889.3	1890.5	1877.7	1865.6	1860.4
5°	2003.8	1989.2	1975.6	1956.1	1933.0	1907.6	1894.6	1884.5	1859.3	1831.8	1815.9
7.5°	2071.0	2050.4	2023.9	1987.3	1953.6	1913.8	1888.6	1866.1	1829.2	1790.5	1766.8
10°	2112.0	2083.9	2049.9	2005.2	1964.0	1915.6	1881.6	1847.7	1804.3	1758.1	1729.2
12.5°	2147.3	2109.3	2075.9	2018.5	1969.7	1909.2	1869.0	1821.1	1775.5	1720.5	1692.2
15°	2231.3	2161.2	2097.6	2032.6	1972.6	1888.1	1843.3	1779.0	1719.1	1651.2	1618.7
17.5°	2296.1	2217.3	2117.2	2034.7	1964.7	1871.1	1805.3	1728.3	1657.5	1579.9	1535.7
20°	2333.1	2242.8	2135.1	2036.9	1953.1	1846.3	1774.7	1696.0	1613.0	1525.5	1477.9
22.5°	2355.0	2260.1	2153.7	2028.3	1930.0	1826.0	1736.0	1649.7	1565.6	1471.2	1421.3
25°	2362.0	2275.3	2162.7	2021.1	1901.1	1783.4	1675.1	1591.3	1489.4	1401.3	1328.3
27.5°	2327.6	2265.5	2157.1	2007.4	1867.7	1730.1	1609.3	1514.4	1406.9	1311.3	1237.9
30°	2285.4	2249.3	2143.8	1993.6	1841.2	1693.1	1560.2	1452.6	1345.7	1248.9	1173.7
32.5°	2220.2	2212.3	2119.6	1974.0	1812.9	1646.3	1508.8	1400.0	1281.6	1186.5	1114.8
35°	2091.9	2126.5	2068.0	1930.0	1759.5	1579.7	1430.9	1306.6	1183.9	1092.9	1025.7
37.5°	1920.0	2006.0	1990.7	1865.8	1687.6	1507.2	1342.9	1213.1	1096.1	1004.2	938.3
40°	1801.5	1911.3	1927.1	1816.7	1636.8	1451.1	1277.1	1147.7	1033.6	949.9	883.4
42.5°	1674.3	1802.6	1846.3	1757.7	1581.3	1392.2	1218.1	1084.2	971.2	889.8	830.9
45°	1461.2	1631.0	1709.8	1659.2	1488.7	1295.1	1116.0	980.1	877.6	801.1	755.5
47.5°	1262.1	1447.6	1553.4	1535.5	1385.7	1194.0	1016.9	886.6	786.7	725.7	684.9
50°	1121.1	1311.7	1439.5	1445.4	1311.7	1121.7	944.1	821.2	729.5	672.5	639.2
52.5°	998.5	1180.5	1319.9	1350.6	1229.1	1046.6	878.7	756.6	675.8	623.4	593.6
55°	838.6	992.5	1147.1	1203.3	1105.9	932.6	777.2	669.6	593.7	557.6	531.6
57.5°	697.2	825.5	968.2	1030.5	970.3	822.0	676.4	582.9	521.4	489.7	469.8
60°	622.6	723.8	850.9	925.3	873.3	741.1	614.0	525.1	474.6	446.4	427.6
62.5°	553.3	642.9	750.4	818.4	790.0	665.4	551.6	473.2	429.5	403.0	389.5
65°	456.5	527.3	610.4	673.2	654.4	559.8	466.7	399.4	364.8	343.8	333.0
67.5°	375.9	427.1	484.7	539.7	524.5	457.5	382.7	330.4	304.5	286.4	279.9
70°	325.1	364.0	415.4	459.4	447.1	392.2	333.0	288.2	265.8	250.6	244.1
72.5°	276.5	308.6	347.7	383.7	375.4	329.8	280.4	246.6	229.4	215.4	210.1
75°	208.8	233.3	257.1	281.0	278.8	243.5	214.5	188.5	174.8	164.0	161.8
77.5°	154.1	167.9	184.1	198.2	194.3	174.1	151.4	136.5	126.4	119.1	118.0
80°	117.7	125.6	137.2	147.3	142.3	133.7	115.6	104.7	97.6	90.3	87.4
82.5°	85.4	93.3	100.3	105.8	101.9	93.8	82.7	75.3	71.0	66.0	64.8
85°	44.8	49.1	52.0	53.4	52.0	46.9	41.8	39.0	35.4	33.3	32.5
87.5°	21.8	21.3	20.8	21.4	18.9	18.4	15.4	13.0	13.1	13.1	12.6
90°	22.1	19.7	17.2	14.4	11.2	7.9	4.6	1.3	4.6	7.9	11.2
92.5°	28.7	27.5	26.3	25.9	26.2	26.5	26.8	27.1	26.8	26.5	26.2
95°	48.1	46.0	43.9	47.8	57.7	67.5	77.3	87.1	77.3	67.5	57.7
97.5°	60.3	55.5	50.7	62.1	89.8	117.5	145.2	173.0	145.2	117.5	89.8
100°	66.3	61.2	56.2	74.0	114.8	155.6	196.4	237.2	196.4	155.6	114.8
102.5°	163.2	205.7	248.0	273.5	282.1	290.8	299.4	308.0	299.4	290.8	282.1
105°	244.4	325.7	407.1	443.3	434.3	425.4	416.4	407.6	416.4	425.4	434.3
107.5°	309.5	407.1	504.6	549.8	542.5	535.4	528.1	520.9	528.1	535.4	542.5
110°	406.8	492.9	578.9	618.9	612.7	606.3	600.1	593.9	600.1	606.3	612.7



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	634.2	655.5	676.7	684.7	679.1	673.5	668.0	662.5	668.0	673.5	679.1
115°	812.2	804.7	797.3	791.1	786.0	780.9	775.9	770.8	775.9	780.9	786.0
117.5°	905.9	900.7	895.6	890.2	884.6	878.9	873.3	867.6	873.3	878.9	884.6
120°	971.9	966.5	961.1	956.2	951.8	947.3	942.8	938.4	942.8	947.3	951.8
122.5°	1034.2	1028.3	1022.6	1017.3	1012.6	1007.9	1003.1	998.4	1003.1	1007.9	1012.6
125°	1121.4	1115.8	1110.1	1105.3	1101.5	1097.6	1093.7	1089.9	1093.7	1097.6	1101.5
127.5°	1202.6	1198.3	1194.1	1189.9	1185.5	1181.3	1177.0	1172.7	1177.0	1181.3	1185.5
130°	1254.9	1251.6	1248.3	1244.3	1239.5	1234.7	1230.0	1225.2	1230.0	1234.7	1239.5
132.5°	1305.2	1302.0	1298.7	1295.1	1291.0	1286.9	1282.9	1278.8	1282.9	1286.9	1291.0
135°	1376.7	1374.0	1371.3	1367.6	1362.8	1358.1	1353.3	1348.6	1353.3	1358.1	1362.8
137.5°	1441.7	1438.6	1435.6	1432.4	1429.1	1425.8	1422.4	1419.1	1422.4	1425.8	1429.1
140°	1484.1	1480.8	1477.5	1474.7	1472.3	1470.0	1467.5	1465.2	1467.5	1470.0	1472.3
142.5°	1522.9	1519.1	1515.3	1512.4	1510.2	1508.1	1505.9	1503.8	1505.9	1508.1	1510.2
145°	1575.7	1570.7	1565.6	1563.2	1563.5	1563.8	1564.1	1564.4	1564.1	1563.8	1563.5
147.5°	1624.7	1619.6	1614.6	1612.7	1613.8	1615.0	1616.1	1617.2	1616.1	1615.0	1613.8
150°	1654.1	1649.3	1644.5	1643.1	1645.3	1647.4	1649.4	1651.5	1649.4	1647.4	1645.3
152.5°	1681.3	1676.8	1672.3	1671.2	1673.5	1675.8	1678.2	1680.5	1678.2	1675.8	1673.5
155°	1719.5	1715.9	1712.3	1711.8	1714.5	1717.2	1719.9	1722.6	1719.9	1717.2	1714.5
157.5°	1751.6	1749.1	1746.6	1746.5	1748.8	1751.1	1753.3	1755.6	1753.3	1751.1	1748.8
160°	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1773.0	1771.3	1769.5
162.5°	1787.8	1786.3	1784.7	1784.9	1786.7	1788.5	1790.3	1792.0	1790.3	1788.5	1786.7
165°	1809.2	1808.4	1807.5	1807.9	1809.7	1811.5	1813.3	1815.1	1813.3	1811.5	1809.7
167.5°	1826.3	1825.4	1824.6	1825.0	1826.8	1828.6	1830.4	1832.2	1830.4	1828.6	1826.8
170°	1835.3	1834.8	1834.1	1834.8	1836.5	1838.3	1840.1	1841.9	1840.1	1838.3	1836.5
172.5°	1841.7	1841.2	1840.6	1841.2	1843.0	1844.7	1846.5	1848.3	1846.5	1844.7	1843.0
175°	1848.7	1848.1	1847.6	1848.3	1850.4	1852.5	1854.5	1856.6	1854.5	1852.5	1850.4
177.5°	1851.1	1850.8	1850.6	1851.2	1852.9	1854.6	1856.3	1857.9	1856.3	1854.6	1852.9
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1854.6	1851.2	1839.0	1832.7	1822.3	1812.4	1806.1	1809.0	1811.3	1810.2	1808.4
5°	1801.5	1787.7	1766.8	1748.7	1735.7	1711.9	1701.8	1696.8	1692.4	1687.3	1682.2
7.5°	1738.1	1716.6	1686.5	1660.8	1636.4	1606.8	1590.0	1579.9	1569.4	1558.0	1547.9
10°	1693.1	1662.7	1631.0	1594.9	1566.0	1539.3	1515.4	1499.5	1485.1	1471.4	1461.2
12.5°	1645.8	1610.8	1571.5	1522.1	1490.3	1452.0	1448.4	1420.4	1397.8	1389.3	1377.4
15°	1570.3	1521.2	1471.4	1412.9	1387.6	1352.9	1331.2	1309.6	1290.1	1276.3	1272.7
17.5°	1484.7	1421.1	1371.5	1329.5	1288.1	1252.5	1232.6	1215.2	1199.2	1180.8	1178.4
20°	1419.4	1364.4	1310.3	1273.5	1230.9	1194.7	1170.2	1152.8	1139.1	1128.2	1118.9
22.5°	1357.5	1297.4	1247.8	1207.6	1165.5	1136.3	1117.0	1100.2	1088.8	1076.9	1068.0
25°	1258.3	1211.4	1157.2	1111.6	1076.9	1058.2	1042.3	1027.8	1020.7	1012.7	1002.6
27.5°	1171.5	1119.3	1068.6	1033.3	1002.9	986.3	975.0	965.2	958.4	953.8	948.0
30°	1110.2	1057.4	1017.8	983.1	957.8	941.2	934.0	928.2	920.2	917.4	914.5
32.5°	1051.2	1003.7	969.8	939.7	915.6	904.7	898.1	893.0	886.7	883.8	878.1
35°	967.9	928.2	894.9	878.4	858.8	849.4	844.4	837.2	831.4	828.5	827.7
37.5°	889.5	855.0	833.1	811.7	803.5	797.8	790.8	785.9	784.2	783.7	783.0
40°	838.6	810.4	791.0	773.6	770.0	761.3	755.5	751.2	751.2	752.0	751.2
42.5°	792.4	767.1	749.9	734.9	730.7	725.5	719.7	719.4	720.6	723.0	720.6
45°	722.4	704.3	692.0	684.8	676.8	671.8	671.0	673.2	673.9	674.7	676.8
47.5°	657.9	645.9	634.8	626.8	623.4	622.5	621.6	625.4	628.9	630.2	633.5
50°	619.7	606.1	596.6	591.5	588.7	587.2	588.7	593.0	595.9	599.6	601.7
52.5°	577.0	567.3	560.8	556.9	555.7	556.7	556.9	561.8	566.5	567.8	568.7
55°	517.9	510.7	509.3	502.8	505.6	504.9	508.5	511.4	515.8	520.1	520.8
57.5°	458.9	453.2	449.3	449.9	450.7	453.9	456.9	462.0	466.7	471.3	471.6
60°	419.7	416.8	414.6	414.6	416.0	420.4	424.0	429.0	432.0	434.8	437.0
62.5°	383.8	381.0	378.8	379.9	383.7	386.3	390.5	393.2	396.2	399.0	400.0
65°	327.3	325.7	327.9	329.4	330.1	333.8	338.7	340.9	343.8	345.3	350.3
67.5°	275.0	275.3	275.0	277.1	281.3	282.1	286.9	292.0	292.6	295.3	298.6
70°	239.8	241.3	242.7	244.1	247.8	249.2	252.8	255.0	257.9	260.0	262.2
72.5°	207.5	207.7	209.2	208.9	211.9	215.1	218.1	220.3	223.2	225.9	228.1
75°	159.7	159.7	161.1	161.8	165.4	169.0	168.3	169.8	172.7	175.5	177.0
77.5°	116.6	115.0	116.6	117.3	118.5	121.5	122.1	124.1	127.4	126.4	128.0
80°	88.9	86.7	88.9	89.5	89.5	93.2	93.2	94.6	96.8	94.6	96.8
82.5°	63.4	62.4	64.0	64.2	65.3	65.4	66.6	66.9	69.1	68.1	69.1
85°	31.8	31.1	31.8	31.1	31.8	32.5	32.5	31.8	31.8	33.3	31.1
87.5°	12.7	12.7	12.6	13.1	13.0	12.9	12.6	12.9	13.2	12.3	12.5
90°	14.4	17.2	19.7	22.1	24.4	26.8	28.3	29.8	31.3	32.8	33.8
92.5°	25.9	26.3	27.5	28.7	29.9	31.1	31.9	32.6	33.5	34.2	34.8
95°	47.8	43.9	46.0	48.1	50.2	52.3	53.7	55.2	56.7	58.2	58.8
97.5°	62.1	50.7	55.5	60.3	65.1	69.9	71.2	72.4	73.5	74.7	75.5
100°	74.0	56.2	61.2	66.3	71.4	76.4	78.8	81.2	83.6	86.0	87.5
102.5°	273.5	248.0	205.7	163.2	120.9	78.5	81.6	84.7	87.8	91.0	92.9
105°	443.3	407.1	325.7	244.4	163.1	81.8	85.0	88.3	91.6	94.9	97.1
107.5°	549.8	504.6	407.1	309.5	212.0	114.5	111.1	107.8	104.4	101.1	100.1
110°	618.9	578.9	492.9	406.8	320.7	234.6	204.8	175.0	145.2	115.5	101.1



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	684.7	676.7	655.5	634.2	612.9	591.7	483.1	374.4	265.7	157.0	103.1
115°	791.1	797.3	804.7	812.2	819.6	827.1	689.2	551.3	413.3	275.4	195.7
117.5°	890.2	895.6	900.7	905.9	911.0	916.2	882.8	849.4	816.1	782.7	730.8
120°	956.2	961.1	966.5	971.9	977.2	982.6	986.2	989.8	993.3	996.9	978.5
122.5°	1017.3	1022.6	1028.3	1034.2	1040.0	1045.8	1048.0	1050.2	1052.3	1054.4	1051.6
125°	1105.3	1110.1	1115.8	1121.4	1127.1	1132.7	1134.8	1136.9	1139.0	1141.0	1142.6
127.5°	1189.9	1194.1	1198.3	1202.6	1206.8	1211.1	1214.1	1217.1	1220.1	1223.1	1224.8
130°	1244.3	1248.3	1251.6	1254.9	1258.1	1261.4	1264.7	1268.0	1271.3	1274.5	1276.0
132.5°	1295.1	1298.7	1302.0	1305.2	1308.5	1311.8	1314.7	1317.4	1320.2	1323.0	1324.3
135°	1367.6	1371.3	1374.0	1376.7	1379.4	1382.1	1385.1	1388.0	1391.0	1394.0	1395.2
137.5°	1432.4	1435.6	1438.6	1441.7	1444.7	1447.7	1450.7	1453.6	1456.5	1459.4	1460.4
140°	1474.7	1477.5	1480.8	1484.1	1487.4	1490.6	1493.4	1496.0	1498.7	1501.4	1501.9
142.5°	1512.4	1515.3	1519.1	1522.9	1526.5	1530.3	1532.8	1535.2	1537.7	1540.1	1540.6
145°	1563.2	1565.6	1570.7	1575.7	1580.7	1585.8	1587.9	1590.0	1592.0	1594.2	1594.5
147.5°	1612.7	1614.6	1619.6	1624.7	1629.7	1634.7	1636.2	1637.8	1639.3	1640.9	1641.0
150°	1643.1	1644.5	1649.3	1654.1	1658.8	1663.6	1665.4	1667.2	1669.0	1670.8	1670.8
152.5°	1671.2	1672.3	1676.8	1681.3	1685.8	1690.4	1692.1	1693.9	1695.7	1697.5	1697.4
155°	1711.8	1712.3	1715.9	1719.5	1723.1	1726.5	1728.3	1730.1	1731.9	1733.7	1733.4
157.5°	1746.5	1746.6	1749.1	1751.6	1754.1	1756.6	1758.7	1760.7	1762.6	1764.7	1764.5
160°	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1776.6	1778.4	1780.2	1782.0	1781.9
162.5°	1784.9	1784.7	1786.3	1787.8	1789.4	1790.9	1793.0	1795.0	1797.1	1799.0	1798.7
165°	1807.9	1807.5	1808.4	1809.2	1810.2	1811.0	1813.2	1815.2	1817.3	1819.4	1819.4
167.5°	1825.0	1824.6	1825.4	1826.3	1827.1	1828.0	1830.0	1832.1	1834.2	1836.3	1836.0
170°	1834.8	1834.1	1834.8	1835.3	1835.9	1836.5	1838.6	1840.7	1842.8	1844.8	1844.6
172.5°	1841.2	1840.6	1841.2	1841.7	1842.4	1843.0	1845.0	1847.1	1849.2	1851.2	1851.0
175°	1848.3	1847.6	1848.1	1848.7	1849.4	1849.9	1852.0	1854.1	1856.1	1858.2	1857.8
177.5°	1851.2	1850.6	1850.8	1851.1	1851.2	1851.5	1853.2	1854.8	1856.5	1858.2	1857.9
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1802.6	1801.5	1801.5	1796.3	1801.5	1801.5	1802.6	1808.4	1810.2	1811.3	1809.0
5°	1672.2	1670.0	1666.4	1670.0	1666.4	1670.0	1672.2	1682.2	1687.3	1692.4	1696.8
7.5°	1543.1	1534.5	1533.2	1524.7	1533.2	1534.5	1543.1	1547.9	1558.0	1569.4	1579.9
10°	1449.0	1443.2	1442.5	1428.7	1442.5	1443.2	1449.0	1461.2	1471.4	1485.1	1499.5
12.5°	1377.3	1363.5	1366.2	1358.2	1366.2	1363.5	1377.3	1377.4	1389.3	1397.8	1420.4
15°	1253.2	1253.2	1250.4	1238.0	1250.4	1253.2	1253.2	1272.7	1276.3	1290.1	1309.6
17.5°	1164.1	1162.6	1155.7	1159.1	1155.7	1162.6	1164.1	1178.4	1180.8	1199.2	1215.2
20°	1110.9	1106.6	1098.0	1098.0	1098.0	1106.6	1110.9	1118.9	1128.2	1139.1	1152.8
22.5°	1060.6	1060.4	1051.1	1054.0	1051.1	1060.4	1060.6	1068.0	1076.9	1088.8	1100.2
25°	1001.8	996.1	991.7	993.9	991.7	996.1	1001.8	1002.6	1012.7	1020.7	1027.8
27.5°	946.1	942.9	942.6	936.7	942.6	942.9	946.1	948.0	953.8	958.4	965.2
30°	913.7	906.5	908.0	904.4	908.0	906.5	913.7	914.5	917.4	920.2	928.2
32.5°	876.8	874.1	872.7	869.7	872.7	874.1	876.8	878.1	883.8	886.7	893.0
35°	826.3	827.1	823.4	824.9	823.4	827.1	826.3	827.7	828.5	831.4	837.2
37.5°	782.3	784.6	782.9	783.3	782.9	784.6	782.3	783.0	783.7	784.2	785.9
40°	753.4	753.4	753.4	755.5	753.4	753.4	753.4	751.2	752.0	751.2	751.2
42.5°	725.7	724.5	723.3	723.2	723.3	724.5	725.7	720.6	723.0	720.6	719.4
45°	678.3	680.4	681.2	677.5	681.2	680.4	678.3	676.8	674.7	673.9	673.2
47.5°	635.4	635.7	635.4	638.6	635.4	635.7	635.4	633.5	630.2	628.9	625.4
50°	605.3	603.9	605.3	603.9	605.3	603.9	605.3	601.7	599.6	595.9	593.0
52.5°	573.5	573.8	573.0	572.7	573.0	573.8	573.5	568.7	567.8	566.5	561.8
55°	523.7	525.1	524.4	524.4	524.4	525.1	523.7	520.8	520.1	515.8	511.4
57.5°	472.1	473.4	474.4	471.3	474.4	473.4	472.1	471.6	471.3	466.7	462.0
60°	436.3	439.9	439.1	437.7	439.1	439.9	436.3	437.0	434.8	432.0	429.0
62.5°	403.3	404.6	404.5	404.3	404.5	404.6	403.3	400.0	399.0	396.2	393.2
65°	352.5	353.9	351.8	353.9	351.8	353.9	352.5	350.3	345.3	343.8	340.9
67.5°	297.7	298.2	299.7	300.8	299.7	298.2	297.7	298.6	295.3	292.6	292.0
70°	263.6	263.0	265.1	267.3	265.1	263.0	263.6	262.2	260.0	257.9	255.0
72.5°	227.8	229.4	228.7	230.3	228.7	229.4	227.8	228.1	225.9	223.2	220.3
75°	175.5	177.7	177.0	179.2	177.0	177.7	175.5	177.0	175.5	172.7	169.8
77.5°	126.9	127.1	126.9	128.0	126.9	127.1	126.9	128.0	126.4	127.4	124.1
80°	96.8	95.4	93.9	96.8	93.9	95.4	96.8	96.8	94.6	96.8	94.6
82.5°	67.3	68.1	66.7	66.7	66.7	68.1	67.3	69.1	68.1	69.1	66.9
85°	31.1	30.3	28.9	28.9	28.9	30.3	31.1	31.1	33.3	31.8	31.8
87.5°	12.6	12.2	12.3	11.9	12.3	12.2	12.6	12.5	12.3	13.2	12.9
90°	34.4	35.0	35.6	36.2	35.6	35.0	34.4	33.8	32.8	31.3	29.8
92.5°	35.2	35.4	35.8	36.2	35.8	35.4	35.2	34.8	34.2	33.5	32.6
95°	58.5	58.2	58.0	57.7	58.0	58.2	58.5	58.8	58.2	56.7	55.2
97.5°	75.9	76.3	76.6	76.9	76.6	76.3	75.9	75.5	74.7	73.5	72.4
100°	88.0	88.6	89.3	89.8	89.3	88.6	88.0	87.5	86.0	83.6	81.2
102.5°	93.8	94.5	95.4	96.2	95.4	94.5	93.8	92.9	91.0	87.8	84.7
105°	98.3	99.5	100.7	101.9	100.7	99.5	98.3	97.1	94.9	91.6	88.3
107.5°	101.2	102.5	103.7	104.8	103.7	102.5	101.2	100.1	101.1	104.4	107.8
110°	102.4	103.5	104.7	105.9	104.7	103.5	102.4	101.1	115.5	145.2	175.0



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	104.2	105.1	106.0	107.0	106.0	105.1	104.2	103.1	157.0	265.7	374.4
115°	174.3	152.8	131.4	109.9	131.4	152.8	174.3	195.7	275.4	413.3	551.3
117.5°	660.3	589.7	519.2	448.8	519.2	589.7	660.3	730.8	782.7	816.1	849.4
120°	938.4	898.1	857.9	817.7	857.9	898.1	938.4	978.5	996.9	993.3	989.8
122.5°	1043.8	1036.0	1028.2	1020.4	1028.2	1036.0	1043.8	1051.6	1054.4	1052.3	1050.2
125°	1143.5	1144.3	1145.3	1146.1	1145.3	1144.3	1143.5	1142.6	1141.0	1139.0	1136.9
127.5°	1224.9	1225.1	1225.3	1225.5	1225.3	1225.1	1224.9	1224.8	1223.1	1220.1	1217.1
130°	1275.7	1275.4	1275.2	1274.8	1275.2	1275.4	1275.7	1276.0	1274.5	1271.3	1268.0
132.5°	1324.0	1323.7	1323.4	1323.0	1323.4	1323.7	1324.0	1324.3	1323.0	1320.2	1317.4
135°	1394.6	1394.0	1393.4	1392.8	1393.4	1394.0	1394.6	1395.2	1394.0	1391.0	1388.0
137.5°	1459.3	1458.4	1457.4	1456.3	1457.4	1458.4	1459.3	1460.4	1459.4	1456.5	1453.6
140°	1500.5	1499.0	1497.5	1496.0	1497.5	1499.0	1500.5	1501.9	1501.4	1498.7	1496.0
142.5°	1539.1	1537.6	1536.2	1534.6	1536.2	1537.6	1539.1	1540.6	1540.1	1537.7	1535.2
145°	1593.0	1591.5	1590.0	1588.6	1590.0	1591.5	1593.0	1594.5	1594.2	1592.0	1590.0
147.5°	1639.7	1638.5	1637.2	1636.0	1637.2	1638.5	1639.7	1641.0	1640.9	1639.3	1637.8
150°	1669.4	1667.9	1666.4	1664.9	1666.4	1667.9	1669.4	1670.8	1670.8	1669.0	1667.2
152.5°	1695.4	1693.6	1691.6	1689.6	1691.6	1693.6	1695.4	1697.4	1697.5	1695.7	1693.9
155°	1731.1	1728.7	1726.3	1723.9	1726.3	1728.7	1731.1	1733.4	1733.7	1731.9	1730.1
157.5°	1762.3	1759.9	1757.6	1755.3	1757.6	1759.9	1762.3	1764.5	1764.7	1762.6	1760.7
160°	1779.8	1777.6	1775.6	1773.5	1775.6	1777.6	1779.8	1781.9	1782.0	1780.2	1778.4
162.5°	1796.2	1793.7	1791.1	1788.6	1791.1	1793.7	1796.2	1798.7	1799.0	1797.1	1795.0
165°	1817.3	1815.2	1813.2	1811.0	1813.2	1815.2	1817.3	1819.4	1819.4	1817.3	1815.2
167.5°	1833.3	1830.6	1828.0	1825.2	1828.0	1830.6	1833.3	1836.0	1836.3	1834.2	1832.1
170°	1841.9	1839.2	1836.5	1833.8	1836.5	1839.2	1841.9	1844.6	1844.8	1842.8	1840.7
172.5°	1848.3	1845.6	1843.0	1840.2	1843.0	1845.6	1848.3	1851.0	1851.2	1849.2	1847.1
175°	1854.8	1851.8	1848.9	1845.9	1848.9	1851.8	1854.8	1857.8	1858.2	1856.1	1854.1
177.5°	1855.8	1853.7	1851.5	1849.4	1851.5	1853.7	1855.8	1857.9	1858.2	1856.5	1854.8
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1806.1	1812.4	1822.3	1832.7	1839.0	1851.2	1854.6	1860.4	1865.6	1877.7	1890.5
5°	1701.8	1711.9	1735.7	1748.7	1766.8	1787.7	1801.5	1815.9	1831.8	1859.3	1884.5
7.5°	1590.0	1606.8	1636.4	1660.8	1686.5	1716.6	1738.1	1766.8	1790.5	1829.2	1866.1
10°	1515.4	1539.3	1566.0	1594.9	1631.0	1662.7	1693.1	1729.2	1758.1	1804.3	1847.7
12.5°	1448.4	1452.0	1490.3	1522.1	1571.5	1610.8	1645.8	1692.2	1720.5	1775.5	1821.1
15°	1331.2	1352.9	1387.6	1412.9	1471.4	1521.2	1570.3	1618.7	1651.2	1719.1	1779.0
17.5°	1232.6	1252.5	1288.1	1329.5	1371.5	1421.1	1484.7	1535.7	1579.9	1657.5	1728.3
20°	1170.2	1194.7	1230.9	1273.5	1310.3	1364.4	1419.4	1477.9	1525.5	1613.0	1696.0
22.5°	1117.0	1136.3	1165.5	1207.6	1247.8	1297.4	1357.5	1421.3	1471.2	1565.6	1649.7
25°	1042.3	1058.2	1076.9	1111.6	1157.2	1211.4	1258.3	1328.3	1401.3	1489.4	1591.3
27.5°	975.0	986.3	1002.9	1033.3	1068.6	1119.3	1171.5	1237.9	1311.3	1406.9	1514.4
30°	934.0	941.2	957.8	983.1	1017.8	1057.4	1110.2	1173.7	1248.9	1345.7	1452.6
32.5°	898.1	904.7	915.6	939.7	969.8	1003.7	1051.2	1114.8	1186.5	1281.6	1400.0
35°	844.4	849.4	858.8	878.4	894.9	928.2	967.9	1025.7	1092.9	1183.9	1306.6
37.5°	790.8	797.8	803.5	811.7	833.1	855.0	889.5	938.3	1004.2	1096.1	1213.1
40°	755.5	761.3	770.0	773.6	791.0	810.4	838.6	883.4	949.9	1033.6	1147.7
42.5°	719.7	725.5	730.7	734.9	749.9	767.1	792.4	830.9	889.8	971.2	1084.2
45°	671.0	671.8	676.8	684.8	692.0	704.3	722.4	755.5	801.1	877.6	980.1
47.5°	621.6	622.5	623.4	626.8	634.8	645.9	657.9	684.9	725.7	786.7	886.6
50°	588.7	587.2	588.7	591.5	596.6	606.1	619.7	639.2	672.5	729.5	821.2
52.5°	556.9	556.7	555.7	556.9	560.8	567.3	577.0	593.6	623.4	675.8	756.6
55°	508.5	504.9	505.6	502.8	509.3	510.7	517.9	531.6	557.6	593.7	669.6
57.5°	456.9	453.9	450.7	449.9	449.3	453.2	458.9	469.8	489.7	521.4	582.9
60°	424.0	420.4	416.0	414.6	414.6	416.8	419.7	427.6	446.4	474.6	525.1
62.5°	390.5	386.3	383.7	379.9	378.8	381.0	383.8	389.5	403.0	429.5	473.2
65°	338.7	333.8	330.1	329.4	327.9	325.7	327.3	333.0	343.8	364.8	399.4
67.5°	286.9	282.1	281.3	277.1	275.0	275.3	275.0	279.9	286.4	304.5	330.4
70°	252.8	249.2	247.8	244.1	242.7	241.3	239.8	244.1	250.6	265.8	288.2
72.5°	218.1	215.1	211.9	208.9	209.2	207.7	207.5	210.1	215.4	229.4	246.6
75°	168.3	169.0	165.4	161.8	161.1	159.7	159.7	161.8	164.0	174.8	188.5
77.5°	122.1	121.5	118.5	117.3	116.6	115.0	116.6	118.0	119.1	126.4	136.5
80°	93.2	93.2	89.5	89.5	88.9	86.7	88.9	87.4	90.3	97.6	104.7
82.5°	66.6	65.4	65.3	64.2	64.0	62.4	63.4	64.8	66.0	71.0	75.3
85°	32.5	32.5	31.8	31.1	31.8	31.1	31.8	32.5	33.3	35.4	39.0
87.5°	12.6	12.9	13.0	13.1	12.6	12.7	12.7	12.6	13.1	13.1	13.0
90°	28.3	26.8	24.4	22.1	19.7	17.2	14.4	11.2	7.9	4.6	1.3
92.5°	31.9	31.1	29.9	28.7	27.5	26.3	25.9	26.2	26.5	26.8	27.1
95°	53.7	52.3	50.2	48.1	46.0	43.9	47.8	57.7	67.5	77.3	87.1
97.5°	71.2	69.9	65.1	60.3	55.5	50.7	62.1	89.8	117.5	145.2	173.0
100°	78.8	76.4	71.4	66.3	61.2	56.2	74.0	114.8	155.6	196.4	237.2
102.5°	81.6	78.5	120.9	163.2	205.7	248.0	273.5	282.1	290.8	299.4	308.0
105°	85.0	81.8	163.1	244.4	325.7	407.1	443.3	434.3	425.4	416.4	407.6
107.5°	111.1	114.5	212.0	309.5	407.1	504.6	549.8	542.5	535.4	528.1	520.9
110°	204.8	234.6	320.7	406.8	492.9	578.9	618.9	612.7	606.3	600.1	593.9



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	483.1	591.7	612.9	634.2	655.5	676.7	684.7	679.1	673.5	668.0	662.5
115°	689.2	827.1	819.6	812.2	804.7	797.3	791.1	786.0	780.9	775.9	770.8
117.5°	882.8	916.2	911.0	905.9	900.7	895.6	890.2	884.6	878.9	873.3	867.6
120°	986.2	982.6	977.2	971.9	966.5	961.1	956.2	951.8	947.3	942.8	938.4
122.5°	1048.0	1045.8	1040.0	1034.2	1028.3	1022.6	1017.3	1012.6	1007.9	1003.1	998.4
125°	1134.8	1132.7	1127.1	1121.4	1115.8	1110.1	1105.3	1101.5	1097.6	1093.7	1089.9
127.5°	1214.1	1211.1	1206.8	1202.6	1198.3	1194.1	1189.9	1185.5	1181.3	1177.0	1172.7
130°	1264.7	1261.4	1258.1	1254.9	1251.6	1248.3	1244.3	1239.5	1234.7	1230.0	1225.2
132.5°	1314.7	1311.8	1308.5	1305.2	1302.0	1298.7	1295.1	1291.0	1286.9	1282.9	1278.8
135°	1385.1	1382.1	1379.4	1376.7	1374.0	1371.3	1367.6	1362.8	1358.1	1353.3	1348.6
137.5°	1450.7	1447.7	1444.7	1441.7	1438.6	1435.6	1432.4	1429.1	1425.8	1422.4	1419.1
140°	1493.4	1490.6	1487.4	1484.1	1480.8	1477.5	1474.7	1472.3	1470.0	1467.5	1465.2
142.5°	1532.8	1530.3	1526.5	1522.9	1519.1	1515.3	1512.4	1510.2	1508.1	1505.9	1503.8
145°	1587.9	1585.8	1580.7	1575.7	1570.7	1565.6	1563.2	1563.5	1563.8	1564.1	1564.4
147.5°	1636.2	1634.7	1629.7	1624.7	1619.6	1614.6	1612.7	1613.8	1615.0	1616.1	1617.2
150°	1665.4	1663.6	1658.8	1654.1	1649.3	1644.5	1643.1	1645.3	1647.4	1649.4	1651.5
152.5°	1692.1	1690.4	1685.8	1681.3	1676.8	1672.3	1671.2	1673.5	1675.8	1678.2	1680.5
155°	1728.3	1726.5	1723.1	1719.5	1715.9	1712.3	1711.8	1714.5	1717.2	1719.9	1722.6
157.5°	1758.7	1756.6	1754.1	1751.6	1749.1	1746.6	1746.5	1748.8	1751.1	1753.3	1755.6
160°	1776.6	1774.8	1773.0	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8
162.5°	1793.0	1790.9	1789.4	1787.8	1786.3	1784.7	1784.9	1786.7	1788.5	1790.3	1792.0
165°	1813.2	1811.0	1810.2	1809.2	1808.4	1807.5	1807.9	1809.7	1811.5	1813.3	1815.1
167.5°	1830.0	1828.0	1827.1	1826.3	1825.4	1824.6	1825.0	1826.8	1828.6	1830.4	1832.2
170°	1838.6	1836.5	1835.9	1835.3	1834.8	1834.1	1834.8	1836.5	1838.3	1840.1	1841.9
172.5°	1845.0	1843.0	1842.4	1841.7	1841.2	1840.6	1841.2	1843.0	1844.7	1846.5	1848.3
175°	1852.0	1849.9	1849.4	1848.7	1848.1	1847.6	1848.3	1850.4	1852.5	1854.5	1856.6
177.5°	1853.2	1851.5	1851.2	1851.1	1850.8	1850.6	1851.2	1852.9	1854.6	1856.3	1857.9
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1889.3	1892.2	1901.4	1910.7	1921.1	1924.0	1928.6	1924.6	1923.4	1934.4	1942.5
5°	1894.6	1907.6	1933.0	1956.1	1975.6	1989.2	2003.8	2009.5	2020.3	2035.5	2054.3
7.5°	1888.6	1913.8	1953.6	1987.3	2023.9	2050.4	2071.0	2088.7	2110.1	2138.8	2170.1
10°	1881.6	1915.6	1964.0	2005.2	2049.9	2083.9	2112.0	2139.5	2171.3	2211.0	2252.2
12.5°	1869.0	1909.2	1969.7	2018.5	2075.9	2109.3	2147.3	2206.6	2240.6	2295.9	2353.9
15°	1843.3	1888.1	1972.6	2032.6	2097.6	2161.2	2231.3	2287.6	2343.9	2376.4	2458.1
17.5°	1805.3	1871.1	1964.7	2034.7	2117.2	2217.3	2296.1	2359.9	2425.0	2477.7	2518.6
20°	1774.7	1846.3	1953.1	2036.9	2135.1	2242.8	2333.1	2398.1	2454.5	2498.5	2523.8
22.5°	1736.0	1826.0	1930.0	2028.3	2153.7	2260.1	2355.0	2406.2	2453.2	2474.8	2484.4
25°	1675.1	1783.4	1901.1	2021.1	2162.7	2275.3	2362.0	2393.0	2406.8	2385.9	2351.2
27.5°	1609.3	1730.1	1867.7	2007.4	2157.1	2265.5	2327.6	2322.7	2299.4	2231.7	2177.5
30°	1560.2	1693.1	1841.2	1993.6	2143.8	2249.3	2285.4	2249.3	2196.6	2120.7	2043.4
32.5°	1508.8	1646.3	1812.9	1974.0	2119.6	2212.3	2220.2	2158.0	2076.4	1990.2	1893.8
35°	1430.9	1579.7	1759.5	1930.0	2068.0	2126.5	2091.9	1982.1	1885.3	1767.6	1636.1
37.5°	1342.9	1507.2	1687.6	1865.8	1990.7	2006.0	1920.0	1804.3	1667.8	1529.5	1374.7
40°	1277.1	1451.1	1636.8	1816.7	1927.1	1911.3	1801.5	1674.3	1511.8	1342.7	1199.0
42.5°	1218.1	1392.2	1581.3	1757.7	1846.3	1802.6	1674.3	1518.3	1343.7	1184.5	1052.8
45°	1116.0	1295.1	1488.7	1659.2	1709.8	1631.0	1461.2	1287.9	1116.0	983.1	879.1
47.5°	1016.9	1194.0	1385.7	1535.5	1553.4	1447.6	1262.1	1083.6	935.9	827.6	754.2
50°	944.1	1121.7	1311.7	1445.4	1439.5	1311.7	1121.1	951.3	827.7	740.4	691.3
52.5°	878.7	1046.6	1229.1	1350.6	1319.9	1180.5	998.5	847.8	746.3	678.0	633.5
55°	777.2	932.6	1105.9	1203.3	1147.1	992.5	838.6	717.3	642.2	590.9	556.2
57.5°	676.4	822.0	970.3	1030.5	968.2	825.5	697.2	609.2	552.7	514.7	492.2
60°	614.0	741.1	873.3	925.3	850.9	723.8	622.6	543.9	498.4	467.3	447.1
62.5°	551.6	665.4	790.0	818.4	750.4	642.9	553.3	487.9	450.4	422.8	403.8
65°	466.7	559.8	654.4	673.2	610.4	527.3	456.5	413.9	380.7	360.4	345.3
67.5°	382.7	457.5	524.5	539.7	484.7	427.1	375.9	338.7	316.2	299.4	286.6
70°	333.0	392.2	447.1	459.4	415.4	364.0	325.1	295.4	275.2	260.8	248.5
72.5°	280.4	329.8	375.4	383.7	347.7	308.6	276.5	253.3	235.4	226.1	214.4
75°	214.5	243.5	278.8	281.0	257.1	233.3	208.8	193.6	184.2	172.7	166.8
77.5°	151.4	174.1	194.3	198.2	184.1	167.9	154.1	142.1	134.2	128.8	123.5
80°	115.6	133.7	142.3	147.3	137.2	125.6	117.7	109.8	104.7	101.1	97.6
82.5°	82.7	93.8	101.9	105.8	100.3	93.3	85.4	80.9	77.0	74.0	72.7
85°	41.8	46.9	52.0	53.4	52.0	49.1	44.8	44.8	42.6	41.8	41.8
87.5°	15.4	18.4	18.9	21.4	20.8	21.3	21.8	21.7	21.6	21.3	21.0
90°	4.6	7.9	11.2	14.4	17.2	19.7	22.1	24.4	26.8	28.3	29.8
92.5°	26.8	26.5	26.2	25.9	26.3	27.5	28.7	29.9	31.1	31.9	32.6
95°	77.3	67.5	57.7	47.8	43.9	46.0	48.1	50.2	52.3	53.7	55.2
97.5°	145.2	117.5	89.8	62.1	50.7	55.5	60.3	65.1	69.9	71.2	72.4
100°	196.4	155.6	114.8	74.0	56.2	61.2	66.3	71.4	76.4	78.8	81.2
102.5°	299.4	290.8	282.1	273.5	248.0	205.7	163.2	120.9	78.5	81.6	84.7
105°	416.4	425.4	434.3	443.3	407.1	325.7	244.4	163.1	81.8	85.0	88.3
107.5°	528.1	535.4	542.5	549.8	504.6	407.1	309.5	212.0	114.5	111.1	107.8
110°	600.1	606.3	612.7	618.9	578.9	492.9	406.8	320.7	234.6	204.8	175.0



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	668.0	673.5	679.1	684.7	676.7	655.5	634.2	612.9	591.7	483.1	374.4
115°	775.9	780.9	786.0	791.1	797.3	804.7	812.2	819.6	827.1	689.2	551.3
117.5°	873.3	878.9	884.6	890.2	895.6	900.7	905.9	911.0	916.2	882.8	849.4
120°	942.8	947.3	951.8	956.2	961.1	966.5	971.9	977.2	982.6	986.2	989.8
122.5°	1003.1	1007.9	1012.6	1017.3	1022.6	1028.3	1034.2	1040.0	1045.8	1048.0	1050.2
125°	1093.7	1097.6	1101.5	1105.3	1110.1	1115.8	1121.4	1127.1	1132.7	1134.8	1136.9
127.5°	1177.0	1181.3	1185.5	1189.9	1194.1	1198.3	1202.6	1206.8	1211.1	1214.1	1217.1
130°	1230.0	1234.7	1239.5	1244.3	1248.3	1251.6	1254.9	1258.1	1261.4	1264.7	1268.0
132.5°	1282.9	1286.9	1291.0	1295.1	1298.7	1302.0	1305.2	1308.5	1311.8	1314.7	1317.4
135°	1353.3	1358.1	1362.8	1367.6	1371.3	1374.0	1376.7	1379.4	1382.1	1385.1	1388.0
137.5°	1422.4	1425.8	1429.1	1432.4	1435.6	1438.6	1441.7	1444.7	1447.7	1450.7	1453.6
140°	1467.5	1470.0	1472.3	1474.7	1477.5	1480.8	1484.1	1487.4	1490.6	1493.4	1496.0
142.5°	1505.9	1508.1	1510.2	1512.4	1515.3	1519.1	1522.9	1526.5	1530.3	1532.8	1535.2
145°	1564.1	1563.8	1563.5	1563.2	1565.6	1570.7	1575.7	1580.7	1585.8	1587.9	1590.0
147.5°	1616.1	1615.0	1613.8	1612.7	1614.6	1619.6	1624.7	1629.7	1634.7	1636.2	1637.8
150°	1649.4	1647.4	1645.3	1643.1	1644.5	1649.3	1654.1	1658.8	1663.6	1665.4	1667.2
152.5°	1678.2	1675.8	1673.5	1671.2	1672.3	1676.8	1681.3	1685.8	1690.4	1692.1	1693.9
155°	1719.9	1717.2	1714.5	1711.8	1712.3	1715.9	1719.5	1723.1	1726.5	1728.3	1730.1
157.5°	1753.3	1751.1	1748.8	1746.5	1746.6	1749.1	1751.6	1754.1	1756.6	1758.7	1760.7
160°	1773.0	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1776.6	1778.4
162.5°	1790.3	1788.5	1786.7	1784.9	1784.7	1786.3	1787.8	1789.4	1790.9	1793.0	1795.0
165°	1813.3	1811.5	1809.7	1807.9	1807.5	1808.4	1809.2	1810.2	1811.0	1813.2	1815.2
167.5°	1830.4	1828.6	1826.8	1825.0	1824.6	1825.4	1826.3	1827.1	1828.0	1830.0	1832.1
170°	1840.1	1838.3	1836.5	1834.8	1834.1	1834.8	1835.3	1835.9	1836.5	1838.6	1840.7
172.5°	1846.5	1844.7	1843.0	1841.2	1840.6	1841.2	1841.7	1842.4	1843.0	1845.0	1847.1
175°	1854.5	1852.5	1850.4	1848.3	1847.6	1848.1	1848.7	1849.4	1849.9	1852.0	1854.1
177.5°	1856.3	1854.6	1852.9	1851.2	1850.6	1850.8	1851.1	1851.2	1851.5	1853.2	1854.8
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1949.4	1957.5	1957.5	1958.6	1967.8	1966.7	1966.1
5°	2074.5	2086.8	2088.2	2101.2	2109.9	2107.0	2099.0
7.5°	2192.5	2215.4	2232.7	2242.4	2253.8	2260.9	2257.7
10°	2286.1	2319.4	2339.6	2353.3	2369.9	2382.2	2377.8
12.5°	2371.1	2410.6	2438.5	2461.9	2464.1	2479.8	2469.2
15°	2503.6	2545.4	2549.8	2567.1	2580.9	2579.4	2580.1
17.5°	2547.3	2560.8	2563.5	2563.9	2564.1	2559.0	2548.1
20°	2531.8	2526.7	2514.4	2505.0	2488.4	2486.2	2471.8
22.5°	2457.8	2441.8	2410.9	2390.6	2364.7	2358.0	2353.9
25°	2312.2	2276.7	2227.6	2180.7	2167.7	2142.4	2149.7
27.5°	2112.3	2057.2	2004.0	1965.9	1931.4	1893.5	1904.3
30°	1971.9	1909.8	1834.7	1776.9	1740.0	1703.9	1697.4
32.5°	1804.3	1713.4	1629.6	1578.7	1522.2	1499.4	1474.4
35°	1515.4	1426.5	1343.5	1272.0	1230.9	1199.0	1170.2
37.5°	1255.6	1153.3	1086.2	1028.3	998.5	980.3	985.0
40°	1094.3	1004.8	955.6	911.5	884.1	871.1	874.0
42.5°	963.7	896.6	856.2	826.0	806.7	799.5	797.8
45°	815.5	778.0	744.7	727.4	718.0	710.0	705.0
47.5°	714.4	683.7	665.0	654.7	646.5	638.4	638.2
50°	653.7	633.5	620.5	609.6	603.1	597.4	602.4
52.5°	607.5	589.0	576.0	566.3	563.8	558.6	558.5
55°	538.9	524.4	515.0	506.3	502.0	499.1	495.5
57.5°	476.5	462.7	454.0	448.6	440.4	437.4	436.3
60°	432.0	421.1	412.5	405.2	401.6	395.9	395.9
62.5°	390.9	380.1	372.0	366.5	360.6	358.3	358.8
65°	331.6	322.9	314.9	309.2	307.7	303.4	304.8
67.5°	276.9	271.2	262.8	259.6	256.8	254.6	252.8
70°	240.5	234.8	230.5	226.1	223.9	223.9	223.9
72.5°	209.9	202.9	200.4	194.9	196.1	193.9	191.5
75°	162.5	158.2	156.0	153.8	150.2	150.2	150.2
77.5°	119.6	118.3	115.7	113.4	112.5	111.8	112.1
80°	92.5	91.7	90.3	90.3	88.9	88.1	86.7
82.5°	71.1	69.2	68.3	67.8	67.5	67.3	67.0
85°	40.4	39.0	39.0	39.7	38.3	38.3	39.0
87.5°	21.9	22.1	21.8	21.9	22.6	22.1	22.2
90°	31.3	32.8	33.8	34.4	35.0	35.6	36.2
92.5°	33.5	34.2	34.8	35.2	35.4	35.8	36.2
95°	56.7	58.2	58.8	58.5	58.2	58.0	57.7
97.5°	73.5	74.7	75.5	75.9	76.3	76.6	76.9
100°	83.6	86.0	87.5	88.0	88.6	89.3	89.8
102.5°	87.8	91.0	92.9	93.8	94.5	95.4	96.2
105°	91.6	94.9	97.1	98.3	99.5	100.7	101.9
107.5°	104.4	101.1	100.1	101.2	102.5	103.7	104.8
110°	145.2	115.5	101.1	102.4	103.5	104.7	105.9



TEST NUMBER: P331609-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	265.7	157.0	103.1	104.2	105.1	106.0	107.0
115°	413.3	275.4	195.7	174.3	152.8	131.4	109.9
117.5°	816.1	782.7	730.8	660.3	589.7	519.2	448.8
120°	993.3	996.9	978.5	938.4	898.1	857.9	817.7
122.5°	1052.3	1054.4	1051.6	1043.8	1036.0	1028.2	1020.4
125°	1139.0	1141.0	1142.6	1143.5	1144.3	1145.3	1146.1
127.5°	1220.1	1223.1	1224.8	1224.9	1225.1	1225.3	1225.5
130°	1271.3	1274.5	1276.0	1275.7	1275.4	1275.2	1274.8
132.5°	1320.2	1323.0	1324.3	1324.0	1323.7	1323.4	1323.0
135°	1391.0	1394.0	1395.2	1394.6	1394.0	1393.4	1392.8
137.5°	1456.5	1459.4	1460.4	1459.3	1458.4	1457.4	1456.3
140°	1498.7	1501.4	1501.9	1500.5	1499.0	1497.5	1496.0
142.5°	1537.7	1540.1	1540.6	1539.1	1537.6	1536.2	1534.6
145°	1592.0	1594.2	1594.5	1593.0	1591.5	1590.0	1588.6
147.5°	1639.3	1640.9	1641.0	1639.7	1638.5	1637.2	1636.0
150°	1669.0	1670.8	1670.8	1669.4	1667.9	1666.4	1664.9
152.5°	1695.7	1697.5	1697.4	1695.4	1693.6	1691.6	1689.6
155°	1731.9	1733.7	1733.4	1731.1	1728.7	1726.3	1723.9
157.5°	1762.6	1764.7	1764.5	1762.3	1759.9	1757.6	1755.3
160°	1780.2	1782.0	1781.9	1779.8	1777.6	1775.6	1773.5
162.5°	1797.1	1799.0	1798.7	1796.2	1793.7	1791.1	1788.6
165°	1817.3	1819.4	1819.4	1817.3	1815.2	1813.2	1811.0
167.5°	1834.2	1836.3	1836.0	1833.3	1830.6	1828.0	1825.2
170°	1842.8	1844.8	1844.6	1841.9	1839.2	1836.5	1833.8
172.5°	1849.2	1851.2	1851.0	1848.3	1845.6	1843.0	1840.2
175°	1856.1	1858.2	1857.8	1854.8	1851.8	1848.9	1845.9
177.5°	1856.5	1858.2	1857.9	1855.8	1853.7	1851.5	1849.4
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6

(END OF REPORT)