

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331610-830

Luminaire Tested: **S122DIW-S1005D1440U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331610-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1440U830-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8861.5 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	38	36	34	32	30	26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30344	30344	30344	30344
5°	34020	30543	27067	30543
10°	38984	30293	23423	30293
15°	43127	29737	20694	29737
20°	42471	29141	18866	29141
25°	38297	28349	17706	28349
30°	31646	27082	16861	27082
35°	23065	25754	16259	25754
40°	18421	24190	15924	24190
45°	16098	22379	15470	22379
50°	15131	20627	15169	20627
55°	13948	18849	14762	18849
60°	12784	16956	14134	16956
65°	11645	15259	13521	15259
70°	10570	13605	12619	13605
75°	9370	11759	11179	11759
80°	8061	9735	9000	9735
85°	7225	7225	5354	7225



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.0	2.0
10°-20°	520.4	5.9
20°-30°	755.2	8.5
30°-40°	796.9	9.0
40°-50°	705.6	8.0
50°-60°	563.1	6.4
60°-70°	382.7	4.3
70°-80°	196.2	2.2
80°-90°	54.0	0.6
90°-100°	106.7	1.2
100°-110°	331.4	3.7
110°-120°	566.4	6.4
120°-130°	744.9	8.4
130°-140°	836.1	9.4
140°-150°	819.8	9.3
150°-160°	687.6	7.8
160°-170°	456.0	5.1
170°-180°	159.4	1.8
0°-30°	1454.6	16.4
0°-40°	2251.5	25.4
0°-60°	3520.2	39.7
0°-90°	4153.2	46.9
90°-120°	1004.5	11.3
90°-150°	3405.2	38.4
90°-180°	4708.0	53.1
0°-180°	8861.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1879	1879	1879	1879	1879	
5°	2099	1884	1670	1884	2099	210
15°	2580	1779	1238	1779	2580	712
25°	2150	1591	994	1591	2150	972
35°	1170	1307	825	1307	1170	761
45°	705	980	678	980	705	554
55°	496	670	524	670	496	444
65°	305	399	354	399	305	303
75°	150	188	179	188	150	161
85°	39	39	29	39	39	44
90°	48	1	48	1	48	23
95°	88	74	88	74	88	98
105°	316	306	316	306	316	332
115°	568	568	568	568	568	561
125°	830	827	830	827	830	740
135°	1083	1070	1083	1070	1083	833
145°	1313	1299	1313	1299	1313	820
155°	1496	1485	1496	1485	1496	689
165°	1617	1616	1617	1616	1617	456
175°	1675	1681	1675	1681	1675	159
180°	1684	1684	1684	1684	1684	



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1966.1	1966.7	1967.8	1958.6	1957.5	1957.5	1949.4	1942.5	1934.4	1923.4	1924.6
5°	2099.0	2107.0	2109.9	2101.2	2088.2	2086.8	2074.5	2054.3	2035.5	2020.3	2009.5
7.5°	2257.7	2260.9	2253.8	2242.4	2232.7	2215.4	2192.5	2170.1	2138.8	2110.1	2088.7
10°	2377.8	2382.2	2369.9	2353.3	2339.6	2319.4	2286.1	2252.2	2211.0	2171.3	2139.5
12.5°	2469.2	2479.8	2464.1	2461.9	2438.5	2410.6	2371.1	2353.9	2295.9	2240.6	2206.6
15°	2580.1	2579.4	2580.9	2567.1	2549.8	2545.4	2503.6	2458.1	2376.4	2343.9	2287.6
17.5°	2548.1	2559.0	2564.1	2563.9	2563.5	2560.8	2547.3	2518.6	2477.7	2425.0	2359.9
20°	2471.8	2486.2	2488.4	2505.0	2514.4	2526.7	2531.8	2523.8	2498.5	2454.5	2398.1
22.5°	2353.9	2358.0	2364.7	2390.6	2410.9	2441.8	2457.8	2484.4	2474.8	2453.2	2406.2
25°	2149.7	2142.4	2167.7	2180.7	2227.6	2276.7	2312.2	2351.2	2385.9	2406.8	2393.0
27.5°	1904.3	1893.5	1931.4	1965.9	2004.0	2057.2	2112.3	2177.5	2231.7	2299.4	2322.7
30°	1697.4	1703.9	1740.0	1776.9	1834.7	1909.8	1971.9	2043.4	2120.7	2196.6	2249.3
32.5°	1474.4	1499.4	1522.2	1578.7	1629.6	1713.4	1804.3	1893.8	1990.2	2076.4	2158.0
35°	1170.2	1199.0	1230.9	1272.0	1343.5	1426.5	1515.4	1636.1	1767.6	1885.3	1982.1
37.5°	985.0	980.3	998.5	1028.3	1086.2	1153.3	1255.6	1374.7	1529.5	1667.8	1804.3
40°	874.0	871.1	884.1	911.5	955.6	1004.8	1094.3	1199.0	1342.7	1511.8	1674.3
42.5°	797.8	799.5	806.7	826.0	856.2	896.6	963.7	1052.8	1184.5	1343.7	1518.3
45°	705.0	710.0	718.0	727.4	744.7	778.0	815.5	879.1	983.1	1116.0	1287.9
47.5°	638.2	638.4	646.5	654.7	665.0	683.7	714.4	754.2	827.6	935.9	1083.6
50°	602.4	597.4	603.1	609.6	620.5	633.5	653.7	691.3	740.4	827.7	951.3
52.5°	558.5	558.6	563.8	566.3	576.0	589.0	607.5	633.5	678.0	746.3	847.8
55°	495.5	499.1	502.0	506.3	515.0	524.4	538.9	556.2	590.9	642.2	717.3
57.5°	436.3	437.4	440.4	448.6	454.0	462.7	476.5	492.2	514.7	552.7	609.2
60°	395.9	395.9	401.6	405.2	412.5	421.1	432.0	447.1	467.3	498.4	543.9
62.5°	358.8	358.3	360.6	366.5	372.0	380.1	390.9	403.8	422.8	450.4	487.9
65°	304.8	303.4	307.7	309.2	314.9	322.9	331.6	345.3	360.4	380.7	413.9
67.5°	252.8	254.6	256.8	259.6	262.8	271.2	276.9	286.6	299.4	316.2	338.7
70°	223.9	223.9	223.9	226.1	230.5	234.8	240.5	248.5	260.8	275.2	295.4
72.5°	191.5	193.9	196.1	194.9	200.4	202.9	209.9	214.4	226.1	235.4	253.3
75°	150.2	150.2	150.2	153.8	156.0	158.2	162.5	166.8	172.7	184.2	193.6
77.5°	112.1	111.8	112.5	113.4	115.7	118.3	119.6	123.5	128.8	134.2	142.1
80°	86.7	88.1	88.9	90.3	90.3	91.7	92.5	97.6	101.1	104.7	109.8
82.5°	67.0	67.3	67.5	67.8	68.3	69.2	71.1	72.7	74.0	77.0	80.9
85°	39.0	38.3	38.3	39.7	39.0	39.0	40.4	41.8	41.8	42.6	44.8
87.5°	24.7	24.6	25.2	24.5	24.4	25.1	25.2	24.7	25.4	26.1	25.4
90°	48.4	48.0	47.7	47.4	47.0	47.2	47.9	48.4	49.1	49.8	42.8
92.5°	46.0	46.0	45.9	45.8	45.8	45.7	45.5	45.4	45.3	45.1	43.5
95°	88.1	88.7	89.4	90.0	90.6	91.0	91.0	91.0	91.0	91.0	90.3
97.5°	152.6	152.7	152.7	152.8	152.9	152.9	152.9	152.9	152.9	152.9	151.7
100°	194.6	195.0	195.3	195.6	196.0	196.0	196.0	196.0	196.0	196.0	195.1
102.5°	242.4	242.7	243.1	243.4	243.6	243.7	243.5	243.2	243.0	242.7	241.5
105°	315.5	315.5	315.5	315.5	315.5	315.1	314.5	313.9	313.2	312.6	312.0
107.5°	384.2	385.7	387.1	388.6	390.0	390.6	390.4	390.1	389.8	389.6	389.6
110°	437.6	438.6	439.5	440.5	441.4	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.8	489.5	490.2	490.9	491.5	492.3	493.0	493.8	494.6	495.3	495.6
115°	568.4	569.3	570.2	571.2	572.1	572.8	573.1	573.4	573.7	574.1	574.7
117.5°	644.2	645.2	646.1	647.1	648.0	648.9	649.7	650.4	651.2	652.0	653.7
120°	697.7	698.6	699.6	700.5	701.4	701.9	701.9	701.9	701.9	701.9	704.5
122.5°	750.0	750.6	751.4	752.1	752.7	753.5	754.2	755.0	755.7	756.5	758.3
125°	829.8	830.2	830.5	830.8	831.1	831.7	832.6	833.6	834.5	835.5	836.5
127.5°	902.6	903.6	904.6	905.6	906.6	907.7	908.8	909.9	911.1	912.3	913.4
130°	954.9	956.1	957.4	958.7	959.9	960.8	961.5	962.1	962.8	963.4	964.0
132.5°	1004.8	1005.9	1006.9	1008.0	1008.9	1010.1	1011.5	1013.0	1014.3	1015.7	1015.6
135°	1082.8	1083.7	1084.7	1085.6	1086.6	1087.2	1087.5	1087.8	1088.2	1088.4	1087.8
137.5°	1153.2	1154.5	1155.7	1157.1	1158.3	1159.0	1159.3	1159.5	1159.8	1160.1	1159.2
140°	1202.1	1203.3	1204.7	1205.9	1207.2	1207.8	1207.8	1207.8	1207.8	1207.8	1206.3
142.5°	1246.4	1247.7	1249.0	1250.3	1251.5	1252.0	1251.8	1251.5	1251.2	1251.0	1249.9
145°	1313.0	1314.2	1315.5	1316.7	1318.0	1318.4	1318.1	1317.9	1317.5	1317.2	1315.3
147.5°	1372.3	1373.6	1374.7	1375.9	1377.1	1377.4	1376.7	1376.0	1375.4	1374.6	1373.4
150°	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0	1409.8
152.5°	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4	1445.9
155°	1496.3	1497.2	1498.2	1499.1	1500.1	1499.7	1498.2	1496.6	1495.0	1493.4	1492.4
157.5°	1538.3	1539.8	1541.3	1542.8	1544.4	1544.1	1541.9	1539.7	1537.6	1535.5	1534.9
160°	1564.4	1565.8	1567.0	1568.2	1569.5	1569.1	1567.3	1565.4	1563.5	1561.6	1561.3
162.5°	1587.1	1588.7	1590.3	1591.8	1593.3	1592.9	1590.8	1588.7	1586.5	1584.3	1584.0
165°	1617.0	1618.6	1620.2	1621.7	1623.3	1623.1	1620.8	1618.6	1616.4	1614.2	1614.2
167.5°	1641.4	1643.1	1644.7	1646.4	1648.0	1647.8	1645.6	1643.3	1641.2	1638.9	1639.0
170°	1654.0	1655.9	1657.7	1659.6	1661.5	1661.4	1659.2	1657.0	1654.7	1652.6	1652.8
172.5°	1664.2	1666.1	1668.0	1669.9	1671.8	1671.6	1669.4	1667.2	1665.0	1662.7	1663.1
175°	1675.3	1677.2	1679.0	1680.9	1682.9	1682.7	1680.5	1678.3	1676.1	1673.9	1674.5
177.5°	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4	1680.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1928.6	1924.0	1921.1	1910.7	1901.4	1892.2	1889.3	1890.5	1877.7	1865.6	1860.4
5°	2003.8	1989.2	1975.6	1956.1	1933.0	1907.6	1894.6	1884.5	1859.3	1831.8	1815.9
7.5°	2071.0	2050.4	2023.9	1987.3	1953.6	1913.8	1888.6	1866.1	1829.2	1790.5	1766.8
10°	2112.0	2083.9	2049.9	2005.2	1964.0	1915.6	1881.6	1847.7	1804.3	1758.1	1729.2
12.5°	2147.3	2109.3	2075.9	2018.5	1969.7	1909.2	1869.0	1821.1	1775.5	1720.5	1692.2
15°	2231.3	2161.2	2097.6	2032.6	1972.6	1888.1	1843.3	1779.0	1719.1	1651.2	1618.7
17.5°	2296.1	2217.3	2117.2	2034.7	1964.7	1871.1	1805.3	1728.3	1657.5	1579.9	1535.7
20°	2333.1	2242.8	2135.1	2036.9	1953.1	1846.3	1774.7	1696.0	1613.0	1525.5	1477.9
22.5°	2355.0	2260.1	2153.7	2028.3	1930.0	1826.0	1736.0	1649.7	1565.6	1471.2	1421.3
25°	2362.0	2275.3	2162.7	2021.1	1901.1	1783.4	1675.1	1591.3	1489.4	1401.3	1328.3
27.5°	2327.6	2265.5	2157.1	2007.4	1867.7	1730.1	1609.3	1514.4	1406.9	1311.3	1237.9
30°	2285.4	2249.3	2143.8	1993.6	1841.2	1693.1	1560.2	1452.6	1345.7	1248.9	1173.7
32.5°	2220.2	2212.3	2119.6	1974.0	1812.9	1646.3	1508.8	1400.0	1281.6	1186.5	1114.8
35°	2091.9	2126.5	2068.0	1930.0	1759.5	1579.7	1430.9	1306.6	1183.9	1092.9	1025.7
37.5°	1920.0	2006.0	1990.7	1865.8	1687.6	1507.2	1342.9	1213.1	1096.1	1004.2	938.3
40°	1801.5	1911.3	1927.1	1816.7	1636.8	1451.1	1277.1	1147.7	1033.6	949.9	883.4
42.5°	1674.3	1802.6	1846.3	1757.7	1581.3	1392.2	1218.1	1084.2	971.2	889.8	830.9
45°	1461.2	1631.0	1709.8	1659.2	1488.7	1295.1	1116.0	980.1	877.6	801.1	755.5
47.5°	1262.1	1447.6	1553.4	1535.5	1385.7	1194.0	1016.9	886.6	786.7	725.7	684.9
50°	1121.1	1311.7	1439.5	1445.4	1311.7	1121.7	944.1	821.2	729.5	672.5	639.2
52.5°	998.5	1180.5	1319.9	1350.6	1229.1	1046.6	878.7	756.6	675.8	623.4	593.6
55°	838.6	992.5	1147.1	1203.3	1105.9	932.6	777.2	669.6	593.7	557.6	531.6
57.5°	697.2	825.5	968.2	1030.5	970.3	822.0	676.4	582.9	521.4	489.7	469.8
60°	622.6	723.8	850.9	925.3	873.3	741.1	614.0	525.1	474.6	446.4	427.6
62.5°	553.3	642.9	750.4	818.4	790.0	665.4	551.6	473.2	429.5	403.0	389.5
65°	456.5	527.3	610.4	673.2	654.4	559.8	466.7	399.4	364.8	343.8	333.0
67.5°	375.9	427.1	484.7	539.7	524.5	457.5	382.7	330.4	304.5	286.4	279.9
70°	325.1	364.0	415.4	459.4	447.1	392.2	333.0	288.2	265.8	250.6	244.1
72.5°	276.5	308.6	347.7	383.7	375.4	329.8	280.4	246.6	229.4	215.4	210.1
75°	208.8	233.3	257.1	281.0	278.8	243.5	214.5	188.5	174.8	164.0	161.8
77.5°	154.1	167.9	184.1	198.2	194.3	174.1	151.4	136.5	126.4	119.1	118.0
80°	117.7	125.6	137.2	147.3	142.3	133.7	115.6	104.7	97.6	90.3	87.4
82.5°	85.4	93.3	100.3	105.8	101.9	93.8	82.7	75.3	71.0	66.0	64.8
85°	44.8	49.1	52.0	53.4	52.0	46.9	41.8	39.0	35.4	33.3	32.5
87.5°	24.5	23.1	21.7	21.8	19.3	18.6	15.5	13.0	13.2	13.4	12.9
90°	35.8	28.9	22.0	16.6	12.8	9.0	5.2	1.4	5.2	9.0	12.8
92.5°	41.9	40.2	38.6	36.4	33.6	30.8	28.1	25.3	28.1	30.8	33.6
95°	89.6	89.1	88.4	86.5	83.3	80.2	77.0	73.9	77.0	80.2	83.3
97.5°	150.5	149.3	148.1	146.1	143.4	140.5	137.8	135.0	137.8	140.5	143.4
100°	194.2	193.2	192.3	190.6	188.0	185.5	182.9	180.5	182.9	185.5	188.0
102.5°	240.3	239.1	237.9	236.3	234.2	232.2	230.3	228.2	230.3	232.2	234.2
105°	311.3	310.8	310.1	309.2	308.3	307.4	306.4	305.5	306.4	307.4	308.3
107.5°	389.6	389.6	389.6	388.9	387.6	386.2	384.7	383.3	384.7	386.2	387.6
110°	442.0	442.0	442.0	440.9	439.0	437.2	435.3	433.4	435.3	437.2	439.0



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	495.9	496.1	496.3	495.5	493.6	491.7	489.8	488.0	489.8	491.7	493.6
115°	575.3	576.0	576.6	576.0	574.1	572.1	570.2	568.4	570.2	572.1	574.1
117.5°	655.4	657.2	659.0	658.6	656.1	653.6	651.0	648.6	651.0	653.6	656.1
120°	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	704.5	707.0	709.5
122.5°	760.1	761.9	763.6	763.0	759.9	756.9	753.8	750.8	753.8	756.9	759.9
125°	837.4	838.4	839.3	838.4	835.5	832.6	829.8	827.0	829.8	832.6	835.5
127.5°	914.5	915.7	916.8	915.6	912.0	908.3	904.7	901.2	904.7	908.3	912.0
130°	964.7	965.3	965.9	964.2	960.1	956.0	951.9	947.7	951.9	956.0	960.1
132.5°	1015.4	1015.3	1015.2	1013.4	1010.1	1006.7	1003.4	1000.0	1003.4	1006.7	1010.1
135°	1087.2	1086.6	1085.9	1083.8	1080.3	1076.9	1073.5	1070.0	1073.5	1076.9	1080.3
137.5°	1158.4	1157.6	1156.8	1154.9	1152.1	1149.2	1146.4	1143.6	1146.4	1149.2	1152.1
140°	1204.7	1203.1	1201.5	1199.3	1196.5	1193.6	1190.7	1187.9	1190.7	1193.6	1196.5
142.5°	1248.9	1247.7	1246.7	1244.7	1241.9	1239.1	1236.2	1233.4	1236.2	1239.1	1241.9
145°	1313.4	1311.5	1309.7	1307.6	1305.3	1303.2	1301.0	1298.7	1301.0	1303.2	1305.3
147.5°	1372.1	1370.8	1369.6	1367.6	1365.0	1362.3	1359.6	1357.0	1359.6	1362.3	1365.0
150°	1408.4	1407.2	1405.9	1404.4	1402.5	1400.6	1398.6	1396.8	1398.6	1400.6	1402.5
152.5°	1444.4	1442.8	1441.3	1439.6	1437.7	1435.8	1433.9	1432.0	1433.9	1435.8	1437.7
155°	1491.5	1490.5	1489.6	1488.7	1487.7	1486.8	1485.8	1484.9	1485.8	1486.8	1487.7
157.5°	1534.4	1533.8	1533.2	1532.6	1532.0	1531.3	1530.7	1530.0	1530.7	1531.3	1532.0
160°	1560.9	1560.7	1560.4	1559.9	1559.2	1558.6	1558.0	1557.4	1558.0	1558.6	1559.2
162.5°	1583.8	1583.4	1583.1	1582.9	1582.7	1582.6	1582.5	1582.3	1582.5	1582.6	1582.7
165°	1614.2	1614.2	1614.2	1614.4	1614.7	1615.0	1615.3	1615.6	1615.3	1615.0	1614.7
167.5°	1639.1	1639.1	1639.2	1639.6	1640.6	1641.5	1642.5	1643.4	1642.5	1641.5	1640.6
170°	1653.2	1653.5	1653.8	1654.4	1655.4	1656.3	1657.3	1658.2	1657.3	1656.3	1655.4
172.5°	1663.4	1663.8	1664.1	1664.7	1665.7	1666.6	1667.5	1668.5	1667.5	1666.6	1665.7
175°	1675.1	1675.7	1676.4	1677.2	1678.1	1679.0	1680.0	1680.9	1680.0	1679.0	1678.1
177.5°	1681.4	1681.9	1682.4	1683.1	1683.9	1684.6	1685.4	1686.1	1685.4	1684.6	1683.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1854.6	1851.2	1839.0	1832.7	1822.3	1812.4	1806.1	1809.0	1811.3	1810.2	1808.4
5°	1801.5	1787.7	1766.8	1748.7	1735.7	1711.9	1701.8	1696.8	1692.4	1687.3	1682.2
7.5°	1738.1	1716.6	1686.5	1660.8	1636.4	1606.8	1590.0	1579.9	1569.4	1558.0	1547.9
10°	1693.1	1662.7	1631.0	1594.9	1566.0	1539.3	1515.4	1499.5	1485.1	1471.4	1461.2
12.5°	1645.8	1610.8	1571.5	1522.1	1490.3	1452.0	1448.4	1420.4	1397.8	1389.3	1377.4
15°	1570.3	1521.2	1471.4	1412.9	1387.6	1352.9	1331.2	1309.6	1290.1	1276.3	1272.7
17.5°	1484.7	1421.1	1371.5	1329.5	1288.1	1252.5	1232.6	1215.2	1199.2	1180.8	1178.4
20°	1419.4	1364.4	1310.3	1273.5	1230.9	1194.7	1170.2	1152.8	1139.1	1128.2	1118.9
22.5°	1357.5	1297.4	1247.8	1207.6	1165.5	1136.3	1117.0	1100.2	1088.8	1076.9	1068.0
25°	1258.3	1211.4	1157.2	1111.6	1076.9	1058.2	1042.3	1027.8	1020.7	1012.7	1002.6
27.5°	1171.5	1119.3	1068.6	1033.3	1002.9	986.3	975.0	965.2	958.4	953.8	948.0
30°	1110.2	1057.4	1017.8	983.1	957.8	941.2	934.0	928.2	920.2	917.4	914.5
32.5°	1051.2	1003.7	969.8	939.7	915.6	904.7	898.1	893.0	886.7	883.8	878.1
35°	967.9	928.2	894.9	878.4	858.8	849.4	844.4	837.2	831.4	828.5	827.7
37.5°	889.5	855.0	833.1	811.7	803.5	797.8	790.8	785.9	784.2	783.7	783.0
40°	838.6	810.4	791.0	773.6	770.0	761.3	755.5	751.2	751.2	752.0	751.2
42.5°	792.4	767.1	749.9	734.9	730.7	725.5	719.7	719.4	720.6	723.0	720.6
45°	722.4	704.3	692.0	684.8	676.8	671.8	671.0	673.2	673.9	674.7	676.8
47.5°	657.9	645.9	634.8	626.8	623.4	622.5	621.6	625.4	628.9	630.2	633.5
50°	619.7	606.1	596.6	591.5	588.7	587.2	588.7	593.0	595.9	599.6	601.7
52.5°	577.0	567.3	560.8	556.9	555.7	556.7	556.9	561.8	566.5	567.8	568.7
55°	517.9	510.7	509.3	502.8	505.6	504.9	508.5	511.4	515.8	520.1	520.8
57.5°	458.9	453.2	449.3	449.9	450.7	453.9	456.9	462.0	466.7	471.3	471.6
60°	419.7	416.8	414.6	414.6	416.0	420.4	424.0	429.0	432.0	434.8	437.0
62.5°	383.8	381.0	378.8	379.9	383.7	386.3	390.5	393.2	396.2	399.0	400.0
65°	327.3	325.7	327.9	329.4	330.1	333.8	338.7	340.9	343.8	345.3	350.3
67.5°	275.0	275.3	275.0	277.1	281.3	282.1	286.9	292.0	292.6	295.3	298.6
70°	239.8	241.3	242.7	244.1	247.8	249.2	252.8	255.0	257.9	260.0	262.2
72.5°	207.5	207.7	209.2	208.9	211.9	215.1	218.1	220.3	223.2	225.9	228.1
75°	159.7	159.7	161.1	161.8	165.4	169.0	168.3	169.8	172.7	175.5	177.0
77.5°	116.6	115.0	116.6	117.3	118.5	121.5	122.1	124.1	127.4	126.4	128.0
80°	88.9	86.7	88.9	89.5	89.5	93.2	93.2	94.6	96.8	94.6	96.8
82.5°	63.4	62.4	64.0	64.2	65.3	65.4	66.6	66.9	69.1	68.1	69.1
85°	31.8	31.1	31.8	31.1	31.8	32.5	32.5	31.8	31.8	33.3	31.1
87.5°	13.1	13.7	14.4	15.8	16.7	17.4	16.8	16.6	16.5	15.2	15.2
90°	16.6	22.0	28.9	35.8	42.8	49.8	49.1	48.4	47.9	47.2	47.0
92.5°	36.4	38.6	40.2	41.9	43.5	45.1	45.3	45.4	45.5	45.7	45.8
95°	86.5	88.4	89.1	89.6	90.3	91.0	91.0	91.0	91.0	91.0	90.6
97.5°	146.1	148.1	149.3	150.5	151.7	152.9	152.9	152.9	152.9	152.9	152.9
100°	190.6	192.3	193.2	194.2	195.1	196.0	196.0	196.0	196.0	196.0	196.0
102.5°	236.3	237.9	239.1	240.3	241.5	242.7	243.0	243.2	243.5	243.7	243.6
105°	309.2	310.1	310.8	311.3	312.0	312.6	313.2	313.9	314.5	315.1	315.5
107.5°	388.9	389.6	389.6	389.6	389.6	389.6	389.8	390.1	390.4	390.6	390.0
110°	440.9	442.0	442.0	442.0	442.0	442.0	442.0	442.0	442.0	442.0	441.4



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	495.5	496.3	496.1	495.9	495.6	495.3	494.6	493.8	493.0	492.3	491.5
115°	576.0	576.6	576.0	575.3	574.7	574.1	573.7	573.4	573.1	572.8	572.1
117.5°	658.6	659.0	657.2	655.4	653.7	652.0	651.2	650.4	649.7	648.9	648.0
120°	712.1	712.1	709.5	707.0	704.5	701.9	701.9	701.9	701.9	701.9	701.4
122.5°	763.0	763.6	761.9	760.1	758.3	756.5	755.7	755.0	754.2	753.5	752.7
125°	838.4	839.3	838.4	837.4	836.5	835.5	834.5	833.6	832.6	831.7	831.1
127.5°	915.6	916.8	915.7	914.5	913.4	912.3	911.1	909.9	908.8	907.7	906.6
130°	964.2	965.9	965.3	964.7	964.0	963.4	962.8	962.1	961.5	960.8	959.9
132.5°	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3	1013.0	1011.5	1010.1	1008.9
135°	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2	1087.8	1087.5	1087.2	1086.6
137.5°	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8	1159.5	1159.3	1159.0	1158.3
140°	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8	1207.8	1207.8	1207.8	1207.2
142.5°	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2	1251.5	1251.8	1252.0	1251.5
145°	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5	1317.9	1318.1	1318.4	1318.0
147.5°	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4	1376.0	1376.7	1377.4	1377.1
150°	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8
152.5°	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2
155°	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0	1496.6	1498.2	1499.7	1500.1
157.5°	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6	1539.7	1541.9	1544.1	1544.4
160°	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5	1565.4	1567.3	1569.1	1569.5
162.5°	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5	1588.7	1590.8	1592.9	1593.3
165°	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4	1618.6	1620.8	1623.1	1623.3
167.5°	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2	1643.3	1645.6	1647.8	1648.0
170°	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7	1657.0	1659.2	1661.4	1661.5
172.5°	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0	1667.2	1669.4	1671.6	1671.8
175°	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1	1678.3	1680.5	1682.7	1682.9
177.5°	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1802.6	1801.5	1801.5	1796.3	1801.5	1801.5	1802.6	1808.4	1810.2	1811.3	1809.0
5°	1672.2	1670.0	1666.4	1670.0	1666.4	1670.0	1672.2	1682.2	1687.3	1692.4	1696.8
7.5°	1543.1	1534.5	1533.2	1524.7	1533.2	1534.5	1543.1	1547.9	1558.0	1569.4	1579.9
10°	1449.0	1443.2	1442.5	1428.7	1442.5	1443.2	1449.0	1461.2	1471.4	1485.1	1499.5
12.5°	1377.3	1363.5	1366.2	1358.2	1366.2	1363.5	1377.3	1377.4	1389.3	1397.8	1420.4
15°	1253.2	1253.2	1250.4	1238.0	1250.4	1253.2	1253.2	1272.7	1276.3	1290.1	1309.6
17.5°	1164.1	1162.6	1155.7	1159.1	1155.7	1162.6	1164.1	1178.4	1180.8	1199.2	1215.2
20°	1110.9	1106.6	1098.0	1098.0	1098.0	1106.6	1110.9	1118.9	1128.2	1139.1	1152.8
22.5°	1060.6	1060.4	1051.1	1054.0	1051.1	1060.4	1060.6	1068.0	1076.9	1088.8	1100.2
25°	1001.8	996.1	991.7	993.9	991.7	996.1	1001.8	1002.6	1012.7	1020.7	1027.8
27.5°	946.1	942.9	942.6	936.7	942.6	942.9	946.1	948.0	953.8	958.4	965.2
30°	913.7	906.5	908.0	904.4	908.0	906.5	913.7	914.5	917.4	920.2	928.2
32.5°	876.8	874.1	872.7	869.7	872.7	874.1	876.8	878.1	883.8	886.7	893.0
35°	826.3	827.1	823.4	824.9	823.4	827.1	826.3	827.7	828.5	831.4	837.2
37.5°	782.3	784.6	782.9	783.3	782.9	784.6	782.3	783.0	783.7	784.2	785.9
40°	753.4	753.4	753.4	755.5	753.4	753.4	753.4	751.2	752.0	751.2	751.2
42.5°	725.7	724.5	723.3	723.2	723.3	724.5	725.7	720.6	723.0	720.6	719.4
45°	678.3	680.4	681.2	677.5	681.2	680.4	678.3	676.8	674.7	673.9	673.2
47.5°	635.4	635.7	635.4	638.6	635.4	635.7	635.4	633.5	630.2	628.9	625.4
50°	605.3	603.9	605.3	603.9	605.3	603.9	605.3	601.7	599.6	595.9	593.0
52.5°	573.5	573.8	573.0	572.7	573.0	573.8	573.5	568.7	567.8	566.5	561.8
55°	523.7	525.1	524.4	524.4	524.4	525.1	523.7	520.8	520.1	515.8	511.4
57.5°	472.1	473.4	474.4	471.3	474.4	473.4	472.1	471.6	471.3	466.7	462.0
60°	436.3	439.9	439.1	437.7	439.1	439.9	436.3	437.0	434.8	432.0	429.0
62.5°	403.3	404.6	404.5	404.3	404.5	404.6	403.3	400.0	399.0	396.2	393.2
65°	352.5	353.9	351.8	353.9	351.8	353.9	352.5	350.3	345.3	343.8	340.9
67.5°	297.7	298.2	299.7	300.8	299.7	298.2	297.7	298.6	295.3	292.6	292.0
70°	263.6	263.0	265.1	267.3	265.1	263.0	263.6	262.2	260.0	257.9	255.0
72.5°	227.8	229.4	228.7	230.3	228.7	229.4	227.8	228.1	225.9	223.2	220.3
75°	175.5	177.7	177.0	179.2	177.0	177.7	175.5	177.0	175.5	172.7	169.8
77.5°	126.9	127.1	126.9	128.0	126.9	127.1	126.9	128.0	126.4	127.4	124.1
80°	96.8	95.4	93.9	96.8	93.9	95.4	96.8	96.8	94.6	96.8	94.6
82.5°	67.3	68.1	66.7	66.7	66.7	68.1	67.3	69.1	68.1	69.1	66.9
85°	31.1	30.3	28.9	28.9	28.9	30.3	31.1	31.1	33.3	31.8	31.8
87.5°	15.3	14.7	14.8	14.3	14.8	14.7	15.3	15.2	15.2	16.5	16.6
90°	47.4	47.7	48.0	48.4	48.0	47.7	47.4	47.0	47.2	47.9	48.4
92.5°	45.8	45.9	46.0	46.0	46.0	45.9	45.8	45.8	45.7	45.5	45.4
95°	90.0	89.4	88.7	88.1	88.7	89.4	90.0	90.6	91.0	91.0	91.0
97.5°	152.8	152.7	152.7	152.6	152.7	152.7	152.8	152.9	152.9	152.9	152.9
100°	195.6	195.3	195.0	194.6	195.0	195.3	195.6	196.0	196.0	196.0	196.0
102.5°	243.4	243.1	242.7	242.4	242.7	243.1	243.4	243.6	243.7	243.5	243.2
105°	315.5	315.5	315.5	315.5	315.5	315.5	315.5	315.5	315.1	314.5	313.9
107.5°	388.6	387.1	385.7	384.2	385.7	387.1	388.6	390.0	390.6	390.4	390.1
110°	440.5	439.5	438.6	437.6	438.6	439.5	440.5	441.4	442.0	442.0	442.0



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	490.9	490.2	489.5	488.8	489.5	490.2	490.9	491.5	492.3	493.0	493.8
115°	571.2	570.2	569.3	568.4	569.3	570.2	571.2	572.1	572.8	573.1	573.4
117.5°	647.1	646.1	645.2	644.2	645.2	646.1	647.1	648.0	648.9	649.7	650.4
120°	700.5	699.6	698.6	697.7	698.6	699.6	700.5	701.4	701.9	701.9	701.9
122.5°	752.1	751.4	750.6	750.0	750.6	751.4	752.1	752.7	753.5	754.2	755.0
125°	830.8	830.5	830.2	829.8	830.2	830.5	830.8	831.1	831.7	832.6	833.6
127.5°	905.6	904.6	903.6	902.6	903.6	904.6	905.6	906.6	907.7	908.8	909.9
130°	958.7	957.4	956.1	954.9	956.1	957.4	958.7	959.9	960.8	961.5	962.1
132.5°	1008.0	1006.9	1005.9	1004.8	1005.9	1006.9	1008.0	1008.9	1010.1	1011.5	1013.0
135°	1085.6	1084.7	1083.7	1082.8	1083.7	1084.7	1085.6	1086.6	1087.2	1087.5	1087.8
137.5°	1157.1	1155.7	1154.5	1153.2	1154.5	1155.7	1157.1	1158.3	1159.0	1159.3	1159.5
140°	1205.9	1204.7	1203.3	1202.1	1203.3	1204.7	1205.9	1207.2	1207.8	1207.8	1207.8
142.5°	1250.3	1249.0	1247.7	1246.4	1247.7	1249.0	1250.3	1251.5	1252.0	1251.8	1251.5
145°	1316.7	1315.5	1314.2	1313.0	1314.2	1315.5	1316.7	1318.0	1318.4	1318.1	1317.9
147.5°	1375.9	1374.7	1373.6	1372.3	1373.6	1374.7	1375.9	1377.1	1377.4	1376.7	1376.0
150°	1413.8	1412.9	1411.9	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9
152.5°	1451.0	1449.7	1448.6	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7
155°	1499.1	1498.2	1497.2	1496.3	1497.2	1498.2	1499.1	1500.1	1499.7	1498.2	1496.6
157.5°	1542.8	1541.3	1539.8	1538.3	1539.8	1541.3	1542.8	1544.4	1544.1	1541.9	1539.7
160°	1568.2	1567.0	1565.8	1564.4	1565.8	1567.0	1568.2	1569.5	1569.1	1567.3	1565.4
162.5°	1591.8	1590.3	1588.7	1587.1	1588.7	1590.3	1591.8	1593.3	1592.9	1590.8	1588.7
165°	1621.7	1620.2	1618.6	1617.0	1618.6	1620.2	1621.7	1623.3	1623.1	1620.8	1618.6
167.5°	1646.4	1644.7	1643.1	1641.4	1643.1	1644.7	1646.4	1648.0	1647.8	1645.6	1643.3
170°	1659.6	1657.7	1655.9	1654.0	1655.9	1657.7	1659.6	1661.5	1661.4	1659.2	1657.0
172.5°	1669.9	1668.0	1666.1	1664.2	1666.1	1668.0	1669.9	1671.8	1671.6	1669.4	1667.2
175°	1680.9	1679.0	1677.2	1675.3	1677.2	1679.0	1680.9	1682.9	1682.7	1680.5	1678.3
177.5°	1685.0	1683.5	1681.9	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1806.1	1812.4	1822.3	1832.7	1839.0	1851.2	1854.6	1860.4	1865.6	1877.7	1890.5
5°	1701.8	1711.9	1735.7	1748.7	1766.8	1787.7	1801.5	1815.9	1831.8	1859.3	1884.5
7.5°	1590.0	1606.8	1636.4	1660.8	1686.5	1716.6	1738.1	1766.8	1790.5	1829.2	1866.1
10°	1515.4	1539.3	1566.0	1594.9	1631.0	1662.7	1693.1	1729.2	1758.1	1804.3	1847.7
12.5°	1448.4	1452.0	1490.3	1522.1	1571.5	1610.8	1645.8	1692.2	1720.5	1775.5	1821.1
15°	1331.2	1352.9	1387.6	1412.9	1471.4	1521.2	1570.3	1618.7	1651.2	1719.1	1779.0
17.5°	1232.6	1252.5	1288.1	1329.5	1371.5	1421.1	1484.7	1535.7	1579.9	1657.5	1728.3
20°	1170.2	1194.7	1230.9	1273.5	1310.3	1364.4	1419.4	1477.9	1525.5	1613.0	1696.0
22.5°	1117.0	1136.3	1165.5	1207.6	1247.8	1297.4	1357.5	1421.3	1471.2	1565.6	1649.7
25°	1042.3	1058.2	1076.9	1111.6	1157.2	1211.4	1258.3	1328.3	1401.3	1489.4	1591.3
27.5°	975.0	986.3	1002.9	1033.3	1068.6	1119.3	1171.5	1237.9	1311.3	1406.9	1514.4
30°	934.0	941.2	957.8	983.1	1017.8	1057.4	1110.2	1173.7	1248.9	1345.7	1452.6
32.5°	898.1	904.7	915.6	939.7	969.8	1003.7	1051.2	1114.8	1186.5	1281.6	1400.0
35°	844.4	849.4	858.8	878.4	894.9	928.2	967.9	1025.7	1092.9	1183.9	1306.6
37.5°	790.8	797.8	803.5	811.7	833.1	855.0	889.5	938.3	1004.2	1096.1	1213.1
40°	755.5	761.3	770.0	773.6	791.0	810.4	838.6	883.4	949.9	1033.6	1147.7
42.5°	719.7	725.5	730.7	734.9	749.9	767.1	792.4	830.9	889.8	971.2	1084.2
45°	671.0	671.8	676.8	684.8	692.0	704.3	722.4	755.5	801.1	877.6	980.1
47.5°	621.6	622.5	623.4	626.8	634.8	645.9	657.9	684.9	725.7	786.7	886.6
50°	588.7	587.2	588.7	591.5	596.6	606.1	619.7	639.2	672.5	729.5	821.2
52.5°	556.9	556.7	555.7	556.9	560.8	567.3	577.0	593.6	623.4	675.8	756.6
55°	508.5	504.9	505.6	502.8	509.3	510.7	517.9	531.6	557.6	593.7	669.6
57.5°	456.9	453.9	450.7	449.9	449.3	453.2	458.9	469.8	489.7	521.4	582.9
60°	424.0	420.4	416.0	414.6	414.6	416.8	419.7	427.6	446.4	474.6	525.1
62.5°	390.5	386.3	383.7	379.9	378.8	381.0	383.8	389.5	403.0	429.5	473.2
65°	338.7	333.8	330.1	329.4	327.9	325.7	327.3	333.0	343.8	364.8	399.4
67.5°	286.9	282.1	281.3	277.1	275.0	275.3	275.0	279.9	286.4	304.5	330.4
70°	252.8	249.2	247.8	244.1	242.7	241.3	239.8	244.1	250.6	265.8	288.2
72.5°	218.1	215.1	211.9	208.9	209.2	207.7	207.5	210.1	215.4	229.4	246.6
75°	168.3	169.0	165.4	161.8	161.1	159.7	159.7	161.8	164.0	174.8	188.5
77.5°	122.1	121.5	118.5	117.3	116.6	115.0	116.6	118.0	119.1	126.4	136.5
80°	93.2	93.2	89.5	89.5	88.9	86.7	88.9	87.4	90.3	97.6	104.7
82.5°	66.6	65.4	65.3	64.2	64.0	62.4	63.4	64.8	66.0	71.0	75.3
85°	32.5	32.5	31.8	31.1	31.8	31.1	31.8	32.5	33.3	35.4	39.0
87.5°	16.8	17.4	16.7	15.8	14.4	13.7	13.1	12.9	13.4	13.2	13.0
90°	49.1	49.8	42.8	35.8	28.9	22.0	16.6	12.8	9.0	5.2	1.4
92.5°	45.3	45.1	43.5	41.9	40.2	38.6	36.4	33.6	30.8	28.1	25.3
95°	91.0	91.0	90.3	89.6	89.1	88.4	86.5	83.3	80.2	77.0	73.9
97.5°	152.9	152.9	151.7	150.5	149.3	148.1	146.1	143.4	140.5	137.8	135.0
100°	196.0	196.0	195.1	194.2	193.2	192.3	190.6	188.0	185.5	182.9	180.5
102.5°	243.0	242.7	241.5	240.3	239.1	237.9	236.3	234.2	232.2	230.3	228.2
105°	313.2	312.6	312.0	311.3	310.8	310.1	309.2	308.3	307.4	306.4	305.5
107.5°	389.8	389.6	389.6	389.6	389.6	389.6	388.9	387.6	386.2	384.7	383.3
110°	442.0	442.0	442.0	442.0	442.0	442.0	440.9	439.0	437.2	435.3	433.4



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.6	495.3	495.6	495.9	496.1	496.3	495.5	493.6	491.7	489.8	488.0
115°	573.7	574.1	574.7	575.3	576.0	576.6	576.0	574.1	572.1	570.2	568.4
117.5°	651.2	652.0	653.7	655.4	657.2	659.0	658.6	656.1	653.6	651.0	648.6
120°	701.9	701.9	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9
122.5°	755.7	756.5	758.3	760.1	761.9	763.6	763.0	759.9	756.9	753.8	750.8
125°	834.5	835.5	836.5	837.4	838.4	839.3	838.4	835.5	832.6	829.8	827.0
127.5°	911.1	912.3	913.4	914.5	915.7	916.8	915.6	912.0	908.3	904.7	901.2
130°	962.8	963.4	964.0	964.7	965.3	965.9	964.2	960.1	956.0	951.9	947.7
132.5°	1014.3	1015.7	1015.6	1015.4	1015.3	1015.2	1013.4	1010.1	1006.7	1003.4	1000.0
135°	1088.2	1088.4	1087.8	1087.2	1086.6	1085.9	1083.8	1080.3	1076.9	1073.5	1070.0
137.5°	1159.8	1160.1	1159.2	1158.4	1157.6	1156.8	1154.9	1152.1	1149.2	1146.4	1143.6
140°	1207.8	1207.8	1206.3	1204.7	1203.1	1201.5	1199.3	1196.5	1193.6	1190.7	1187.9
142.5°	1251.2	1251.0	1249.9	1248.9	1247.7	1246.7	1244.7	1241.9	1239.1	1236.2	1233.4
145°	1317.5	1317.2	1315.3	1313.4	1311.5	1309.7	1307.6	1305.3	1303.2	1301.0	1298.7
147.5°	1375.4	1374.6	1373.4	1372.1	1370.8	1369.6	1367.6	1365.0	1362.3	1359.6	1357.0
150°	1411.9	1411.0	1409.8	1408.4	1407.2	1405.9	1404.4	1402.5	1400.6	1398.6	1396.8
152.5°	1448.6	1447.4	1445.9	1444.4	1442.8	1441.3	1439.6	1437.7	1435.8	1433.9	1432.0
155°	1495.0	1493.4	1492.4	1491.5	1490.5	1489.6	1488.7	1487.7	1486.8	1485.8	1484.9
157.5°	1537.6	1535.5	1534.9	1534.4	1533.8	1533.2	1532.6	1532.0	1531.3	1530.7	1530.0
160°	1563.5	1561.6	1561.3	1560.9	1560.7	1560.4	1559.9	1559.2	1558.6	1558.0	1557.4
162.5°	1586.5	1584.3	1584.0	1583.8	1583.4	1583.1	1582.9	1582.7	1582.6	1582.5	1582.3
165°	1616.4	1614.2	1614.2	1614.2	1614.2	1614.2	1614.4	1614.7	1615.0	1615.3	1615.6
167.5°	1641.2	1638.9	1639.0	1639.1	1639.1	1639.2	1639.6	1640.6	1641.5	1642.5	1643.4
170°	1654.7	1652.6	1652.8	1653.2	1653.5	1653.8	1654.4	1655.4	1656.3	1657.3	1658.2
172.5°	1665.0	1662.7	1663.1	1663.4	1663.8	1664.1	1664.7	1665.7	1666.6	1667.5	1668.5
175°	1676.1	1673.9	1674.5	1675.1	1675.7	1676.4	1677.2	1678.1	1679.0	1680.0	1680.9
177.5°	1681.9	1680.4	1680.9	1681.4	1681.9	1682.4	1683.1	1683.9	1684.6	1685.4	1686.1
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1889.3	1892.2	1901.4	1910.7	1921.1	1924.0	1928.6	1924.6	1923.4	1934.4	1942.5
5°	1894.6	1907.6	1933.0	1956.1	1975.6	1989.2	2003.8	2009.5	2020.3	2035.5	2054.3
7.5°	1888.6	1913.8	1953.6	1987.3	2023.9	2050.4	2071.0	2088.7	2110.1	2138.8	2170.1
10°	1881.6	1915.6	1964.0	2005.2	2049.9	2083.9	2112.0	2139.5	2171.3	2211.0	2252.2
12.5°	1869.0	1909.2	1969.7	2018.5	2075.9	2109.3	2147.3	2206.6	2240.6	2295.9	2353.9
15°	1843.3	1888.1	1972.6	2032.6	2097.6	2161.2	2231.3	2287.6	2343.9	2376.4	2458.1
17.5°	1805.3	1871.1	1964.7	2034.7	2117.2	2217.3	2296.1	2359.9	2425.0	2477.7	2518.6
20°	1774.7	1846.3	1953.1	2036.9	2135.1	2242.8	2333.1	2398.1	2454.5	2498.5	2523.8
22.5°	1736.0	1826.0	1930.0	2028.3	2153.7	2260.1	2355.0	2406.2	2453.2	2474.8	2484.4
25°	1675.1	1783.4	1901.1	2021.1	2162.7	2275.3	2362.0	2393.0	2406.8	2385.9	2351.2
27.5°	1609.3	1730.1	1867.7	2007.4	2157.1	2265.5	2327.6	2322.7	2299.4	2231.7	2177.5
30°	1560.2	1693.1	1841.2	1993.6	2143.8	2249.3	2285.4	2249.3	2196.6	2120.7	2043.4
32.5°	1508.8	1646.3	1812.9	1974.0	2119.6	2212.3	2220.2	2158.0	2076.4	1990.2	1893.8
35°	1430.9	1579.7	1759.5	1930.0	2068.0	2126.5	2091.9	1982.1	1885.3	1767.6	1636.1
37.5°	1342.9	1507.2	1687.6	1865.8	1990.7	2006.0	1920.0	1804.3	1667.8	1529.5	1374.7
40°	1277.1	1451.1	1636.8	1816.7	1927.1	1911.3	1801.5	1674.3	1511.8	1342.7	1199.0
42.5°	1218.1	1392.2	1581.3	1757.7	1846.3	1802.6	1674.3	1518.3	1343.7	1184.5	1052.8
45°	1116.0	1295.1	1488.7	1659.2	1709.8	1631.0	1461.2	1287.9	1116.0	983.1	879.1
47.5°	1016.9	1194.0	1385.7	1535.5	1553.4	1447.6	1262.1	1083.6	935.9	827.6	754.2
50°	944.1	1121.7	1311.7	1445.4	1439.5	1311.7	1121.1	951.3	827.7	740.4	691.3
52.5°	878.7	1046.6	1229.1	1350.6	1319.9	1180.5	998.5	847.8	746.3	678.0	633.5
55°	777.2	932.6	1105.9	1203.3	1147.1	992.5	838.6	717.3	642.2	590.9	556.2
57.5°	676.4	822.0	970.3	1030.5	968.2	825.5	697.2	609.2	552.7	514.7	492.2
60°	614.0	741.1	873.3	925.3	850.9	723.8	622.6	543.9	498.4	467.3	447.1
62.5°	551.6	665.4	790.0	818.4	750.4	642.9	553.3	487.9	450.4	422.8	403.8
65°	466.7	559.8	654.4	673.2	610.4	527.3	456.5	413.9	380.7	360.4	345.3
67.5°	382.7	457.5	524.5	539.7	484.7	427.1	375.9	338.7	316.2	299.4	286.6
70°	333.0	392.2	447.1	459.4	415.4	364.0	325.1	295.4	275.2	260.8	248.5
72.5°	280.4	329.8	375.4	383.7	347.7	308.6	276.5	253.3	235.4	226.1	214.4
75°	214.5	243.5	278.8	281.0	257.1	233.3	208.8	193.6	184.2	172.7	166.8
77.5°	151.4	174.1	194.3	198.2	184.1	167.9	154.1	142.1	134.2	128.8	123.5
80°	115.6	133.7	142.3	147.3	137.2	125.6	117.7	109.8	104.7	101.1	97.6
82.5°	82.7	93.8	101.9	105.8	100.3	93.3	85.4	80.9	77.0	74.0	72.7
85°	41.8	46.9	52.0	53.4	52.0	49.1	44.8	44.8	42.6	41.8	41.8
87.5°	15.5	18.6	19.3	21.8	21.7	23.1	24.5	25.4	26.1	25.4	24.7
90°	5.2	9.0	12.8	16.6	22.0	28.9	35.8	42.8	49.8	49.1	48.4
92.5°	28.1	30.8	33.6	36.4	38.6	40.2	41.9	43.5	45.1	45.3	45.4
95°	77.0	80.2	83.3	86.5	88.4	89.1	89.6	90.3	91.0	91.0	91.0
97.5°	137.8	140.5	143.4	146.1	148.1	149.3	150.5	151.7	152.9	152.9	152.9
100°	182.9	185.5	188.0	190.6	192.3	193.2	194.2	195.1	196.0	196.0	196.0
102.5°	230.3	232.2	234.2	236.3	237.9	239.1	240.3	241.5	242.7	243.0	243.2
105°	306.4	307.4	308.3	309.2	310.1	310.8	311.3	312.0	312.6	313.2	313.9
107.5°	384.7	386.2	387.6	388.9	389.6	389.6	389.6	389.6	389.6	389.8	390.1
110°	435.3	437.2	439.0	440.9	442.0	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	489.8	491.7	493.6	495.5	496.3	496.1	495.9	495.6	495.3	494.6	493.8
115°	570.2	572.1	574.1	576.0	576.6	576.0	575.3	574.7	574.1	573.7	573.4
117.5°	651.0	653.6	656.1	658.6	659.0	657.2	655.4	653.7	652.0	651.2	650.4
120°	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	701.9	701.9
122.5°	753.8	756.9	759.9	763.0	763.6	761.9	760.1	758.3	756.5	755.7	755.0
125°	829.8	832.6	835.5	838.4	839.3	838.4	837.4	836.5	835.5	834.5	833.6
127.5°	904.7	908.3	912.0	915.6	916.8	915.7	914.5	913.4	912.3	911.1	909.9
130°	951.9	956.0	960.1	964.2	965.9	965.3	964.7	964.0	963.4	962.8	962.1
132.5°	1003.4	1006.7	1010.1	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3	1013.0
135°	1073.5	1076.9	1080.3	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2	1087.8
137.5°	1146.4	1149.2	1152.1	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8	1159.5
140°	1190.7	1193.6	1196.5	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8	1207.8
142.5°	1236.2	1239.1	1241.9	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2	1251.5
145°	1301.0	1303.2	1305.3	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5	1317.9
147.5°	1359.6	1362.3	1365.0	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4	1376.0
150°	1398.6	1400.6	1402.5	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9	1412.9
152.5°	1433.9	1435.8	1437.7	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6	1449.7
155°	1485.8	1486.8	1487.7	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0	1496.6
157.5°	1530.7	1531.3	1532.0	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6	1539.7
160°	1558.0	1558.6	1559.2	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5	1565.4
162.5°	1582.5	1582.6	1582.7	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5	1588.7
165°	1615.3	1615.0	1614.7	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4	1618.6
167.5°	1642.5	1641.5	1640.6	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2	1643.3
170°	1657.3	1656.3	1655.4	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7	1657.0
172.5°	1667.5	1666.6	1665.7	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0	1667.2
175°	1680.0	1679.0	1678.1	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1	1678.3
177.5°	1685.4	1684.6	1683.9	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9	1683.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1949.4	1957.5	1957.5	1958.6	1967.8	1966.7	1966.1
5°	2074.5	2086.8	2088.2	2101.2	2109.9	2107.0	2099.0
7.5°	2192.5	2215.4	2232.7	2242.4	2253.8	2260.9	2257.7
10°	2286.1	2319.4	2339.6	2353.3	2369.9	2382.2	2377.8
12.5°	2371.1	2410.6	2438.5	2461.9	2464.1	2479.8	2469.2
15°	2503.6	2545.4	2549.8	2567.1	2580.9	2579.4	2580.1
17.5°	2547.3	2560.8	2563.5	2563.9	2564.1	2559.0	2548.1
20°	2531.8	2526.7	2514.4	2505.0	2488.4	2486.2	2471.8
22.5°	2457.8	2441.8	2410.9	2390.6	2364.7	2358.0	2353.9
25°	2312.2	2276.7	2227.6	2180.7	2167.7	2142.4	2149.7
27.5°	2112.3	2057.2	2004.0	1965.9	1931.4	1893.5	1904.3
30°	1971.9	1909.8	1834.7	1776.9	1740.0	1703.9	1697.4
32.5°	1804.3	1713.4	1629.6	1578.7	1522.2	1499.4	1474.4
35°	1515.4	1426.5	1343.5	1272.0	1230.9	1199.0	1170.2
37.5°	1255.6	1153.3	1086.2	1028.3	998.5	980.3	985.0
40°	1094.3	1004.8	955.6	911.5	884.1	871.1	874.0
42.5°	963.7	896.6	856.2	826.0	806.7	799.5	797.8
45°	815.5	778.0	744.7	727.4	718.0	710.0	705.0
47.5°	714.4	683.7	665.0	654.7	646.5	638.4	638.2
50°	653.7	633.5	620.5	609.6	603.1	597.4	602.4
52.5°	607.5	589.0	576.0	566.3	563.8	558.6	558.5
55°	538.9	524.4	515.0	506.3	502.0	499.1	495.5
57.5°	476.5	462.7	454.0	448.6	440.4	437.4	436.3
60°	432.0	421.1	412.5	405.2	401.6	395.9	395.9
62.5°	390.9	380.1	372.0	366.5	360.6	358.3	358.8
65°	331.6	322.9	314.9	309.2	307.7	303.4	304.8
67.5°	276.9	271.2	262.8	259.6	256.8	254.6	252.8
70°	240.5	234.8	230.5	226.1	223.9	223.9	223.9
72.5°	209.9	202.9	200.4	194.9	196.1	193.9	191.5
75°	162.5	158.2	156.0	153.8	150.2	150.2	150.2
77.5°	119.6	118.3	115.7	113.4	112.5	111.8	112.1
80°	92.5	91.7	90.3	90.3	88.9	88.1	86.7
82.5°	71.1	69.2	68.3	67.8	67.5	67.3	67.0
85°	40.4	39.0	39.0	39.7	38.3	38.3	39.0
87.5°	25.2	25.1	24.4	24.5	25.2	24.6	24.7
90°	47.9	47.2	47.0	47.4	47.7	48.0	48.4
92.5°	45.5	45.7	45.8	45.8	45.9	46.0	46.0
95°	91.0	91.0	90.6	90.0	89.4	88.7	88.1
97.5°	152.9	152.9	152.9	152.8	152.7	152.7	152.6
100°	196.0	196.0	196.0	195.6	195.3	195.0	194.6
102.5°	243.5	243.7	243.6	243.4	243.1	242.7	242.4
105°	314.5	315.1	315.5	315.5	315.5	315.5	315.5
107.5°	390.4	390.6	390.0	388.6	387.1	385.7	384.2
110°	442.0	442.0	441.4	440.5	439.5	438.6	437.6



TEST NUMBER: P331610-830

CATALOG NUMBER: S122DIW-S1005D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	493.0	492.3	491.5	490.9	490.2	489.5	488.8
115°	573.1	572.8	572.1	571.2	570.2	569.3	568.4
117.5°	649.7	648.9	648.0	647.1	646.1	645.2	644.2
120°	701.9	701.9	701.4	700.5	699.6	698.6	697.7
122.5°	754.2	753.5	752.7	752.1	751.4	750.6	750.0
125°	832.6	831.7	831.1	830.8	830.5	830.2	829.8
127.5°	908.8	907.7	906.6	905.6	904.6	903.6	902.6
130°	961.5	960.8	959.9	958.7	957.4	956.1	954.9
132.5°	1011.5	1010.1	1008.9	1008.0	1006.9	1005.9	1004.8
135°	1087.5	1087.2	1086.6	1085.6	1084.7	1083.7	1082.8
137.5°	1159.3	1159.0	1158.3	1157.1	1155.7	1154.5	1153.2
140°	1207.8	1207.8	1207.2	1205.9	1204.7	1203.3	1202.1
142.5°	1251.8	1252.0	1251.5	1250.3	1249.0	1247.7	1246.4
145°	1318.1	1318.4	1318.0	1316.7	1315.5	1314.2	1313.0
147.5°	1376.7	1377.4	1377.1	1375.9	1374.7	1373.6	1372.3
150°	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0
152.5°	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4
155°	1498.2	1499.7	1500.1	1499.1	1498.2	1497.2	1496.3
157.5°	1541.9	1544.1	1544.4	1542.8	1541.3	1539.8	1538.3
160°	1567.3	1569.1	1569.5	1568.2	1567.0	1565.8	1564.4
162.5°	1590.8	1592.9	1593.3	1591.8	1590.3	1588.7	1587.1
165°	1620.8	1623.1	1623.3	1621.7	1620.2	1618.6	1617.0
167.5°	1645.6	1647.8	1648.0	1646.4	1644.7	1643.1	1641.4
170°	1659.2	1661.4	1661.5	1659.6	1657.7	1655.9	1654.0
172.5°	1669.4	1671.6	1671.8	1669.9	1668.0	1666.1	1664.2
175°	1680.5	1682.7	1682.9	1680.9	1679.0	1677.2	1675.3
177.5°	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9

(END OF REPORT)