

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331590-830

Luminaire Tested: **S122DIW-S1005D435U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331590-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D435U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5238.9 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331590-830

CATALOG NUMBER: S122DIW-S1005D435U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331590-830

CATALOG NUMBER: S122DIW-S1005D435U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	61
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	57	55	52
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35	33
6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	45	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331590-830

CATALOG NUMBER: S122DIW-S1005D435U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	2.7
10°-20°	397.5	7.6
20°-30°	584.2	11.2
30°-40°	678.6	13.0
40°-50°	677.9	12.9
50°-60°	591.2	11.3
60°-70°	437.1	8.3
70°-80°	247.6	4.7
80°-90°	68.6	1.3
90°-100°	32.1	0.6
100°-110°	99.6	1.9
110°-120°	170.2	3.2
120°-130°	223.9	4.3
130°-140°	251.3	4.8
140°-150°	246.4	4.7
150°-160°	206.6	3.9
160°-170°	137.1	2.6
170°-180°	47.9	0.9
0°-30°	1123.0	21.4
0°-40°	1801.6	34.4
0°-60°	3070.7	58.6
0°-90°	3824.0	73.0
90°-120°	301.9	5.8
90°-150°	1023.3	19.5
90°-180°	1415.0	27.0
0°-180°	5238.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	0	6	15	14	14	4
95°	22	26	27	27	26	25
105°	92	93	94	95	95	97
115°	171	173	172	172	171	169
125°	248	252	251	250	249	222
135°	322	326	327	327	325	248
145°	390	393	396	396	394	244
155°	446	448	449	451	450	205
165°	486	485	485	488	486	137
175°	505	504	503	506	504	48
180°	506	506	506	506	506	



TEST NUMBER: P331590-830

CATALOG NUMBER: S122DIW-S1005D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	20.9	20.6	20.4	20.0	19.7	19.5	19.4	19.3	19.2	19.1	18.4
90°	0.5	1.6	2.7	3.9	5.0	6.6	8.7	10.7	12.8	15.0	14.8
92.5°	7.6	8.5	9.2	10.1	10.9	11.6	12.1	12.6	13.1	13.6	13.6
95°	22.2	23.2	24.1	25.1	26.0	26.6	26.8	27.0	27.1	27.3	27.3
97.5°	40.5	41.4	42.2	43.1	43.9	44.5	44.9	45.2	45.6	45.9	45.9
100°	54.2	55.0	55.7	56.6	57.3	57.8	58.1	58.3	58.6	58.9	58.9
102.5°	68.6	69.2	69.7	70.4	71.0	71.5	71.8	72.2	72.6	73.0	73.0
105°	91.8	92.1	92.4	92.7	92.9	93.2	93.4	93.6	93.8	94.0	94.2
107.5°	115.2	115.6	116.0	116.5	116.9	117.1	117.1	117.1	117.1	117.1	117.2
110°	130.3	130.8	131.4	132.0	132.5	132.8	132.8	132.8	132.8	132.8	132.8



TEST NUMBER: P331590-830

CATALOG NUMBER: S122DIW-S1005D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.7	147.2	147.8	148.4	148.9	149.2	149.1	149.0	148.9	148.8	148.6
115°	170.8	171.4	171.9	172.5	173.1	173.2	173.1	172.9	172.7	172.5	172.4
117.5°	194.9	195.7	196.4	197.2	197.9	198.0	197.6	197.0	196.4	196.0	195.7
120°	210.9	211.7	212.4	213.2	214.0	214.0	213.2	212.4	211.7	210.9	210.9
122.5°	225.6	226.6	227.4	228.4	229.3	229.5	228.9	228.4	227.9	227.3	227.2
125°	248.5	249.4	250.2	251.1	251.9	252.2	251.9	251.7	251.4	251.1	250.8
127.5°	270.8	271.9	273.0	274.1	275.1	275.5	275.2	274.8	274.5	274.2	273.8
130°	284.8	286.1	287.3	288.5	289.7	290.3	290.1	289.9	289.7	289.5	289.4
132.5°	300.6	301.5	302.6	303.6	304.5	305.1	305.1	305.2	305.2	305.2	304.8
135°	321.6	322.6	323.7	324.7	325.7	326.3	326.5	326.7	326.9	327.1	327.0
137.5°	343.7	344.5	345.3	346.2	347.0	347.6	347.9	348.2	348.4	348.6	348.6
140°	357.0	357.9	358.7	359.6	360.4	361.1	361.6	362.0	362.5	363.0	363.0
142.5°	370.7	371.6	372.4	373.2	374.1	374.7	374.9	375.3	375.6	376.0	376.1
145°	390.3	391.0	391.6	392.3	392.9	393.6	394.2	394.7	395.3	395.9	396.0
147.5°	407.8	408.6	409.4	410.2	411.0	411.6	412.0	412.4	412.7	413.1	413.3
150°	419.8	420.4	420.9	421.5	422.1	422.5	422.9	423.3	423.7	424.0	424.3
152.5°	430.4	430.9	431.5	432.1	432.6	433.2	433.6	434.0	434.5	435.0	435.4
155°	446.2	446.5	446.8	447.1	447.4	447.7	448.0	448.3	448.6	448.8	449.3
157.5°	459.9	460.1	460.2	460.4	460.6	460.7	460.9	461.1	461.3	461.5	462.1
160°	468.1	468.3	468.4	468.6	468.8	468.9	469.0	469.1	469.2	469.3	469.9
162.5°	475.5	475.6	475.6	475.6	475.7	475.8	475.9	476.0	476.1	476.2	476.7
165°	485.5	485.4	485.3	485.2	485.1	485.1	485.1	485.1	485.1	485.1	485.8
167.5°	493.9	493.6	493.3	493.0	492.8	492.6	492.6	492.6	492.6	492.6	493.2
170°	498.3	498.0	497.8	497.5	497.2	497.0	496.9	496.8	496.7	496.6	497.3
172.5°	501.4	501.1	500.9	500.6	500.3	500.1	500.0	499.9	499.8	499.7	500.4
175°	505.2	504.9	504.6	504.4	504.1	503.8	503.6	503.4	503.2	503.0	503.7
177.5°	506.7	506.5	506.2	506.1	505.8	505.6	505.5	505.3	505.1	505.0	505.5
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1



TEST NUMBER: P331590-830

CATALOG NUMBER: S122DIW-S1005D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	17.5	16.8	15.9	15.5	15.2	14.9	14.7	14.4
90°	14.6	14.4	14.2	14.1	14.2	14.3	14.4	14.5
92.5°	13.7	13.7	13.8	13.8	13.8	13.8	13.9	13.9
95°	27.3	27.3	27.3	27.2	27.1	26.9	26.7	26.5
97.5°	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9
100°	58.9	58.9	58.9	58.9	58.8	58.7	58.6	58.5
102.5°	73.0	73.1	73.2	73.2	73.1	73.0	73.0	72.9
105°	94.3	94.5	94.7	94.8	94.8	94.8	94.8	94.8
107.5°	117.3	117.3	117.4	117.3	116.8	116.3	115.9	115.5
110°	132.8	132.8	132.8	132.6	132.3	132.1	131.8	131.5



TEST NUMBER: P331590-830

CATALOG NUMBER: S122DIW-S1005D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	148.5	148.2	148.0	147.7	147.5	147.3	147.1	146.9
115°	172.3	172.2	172.1	171.9	171.6	171.4	171.1	170.8
117.5°	195.5	195.2	195.0	194.7	194.4	194.2	193.9	193.6
120°	210.9	210.9	210.9	210.8	210.6	210.3	210.0	209.7
122.5°	226.9	226.7	226.4	226.2	226.0	225.8	225.6	225.4
125°	250.5	250.2	250.0	249.8	249.7	249.6	249.5	249.4
127.5°	273.4	273.1	272.8	272.5	272.1	271.8	271.5	271.3
130°	289.2	289.0	288.8	288.5	288.1	287.8	287.4	287.0
132.5°	304.4	304.0	303.6	303.2	302.9	302.6	302.3	302.0
135°	326.9	326.8	326.7	326.5	326.2	325.9	325.6	325.4
137.5°	348.5	348.4	348.4	348.1	347.7	347.3	346.9	346.6
140°	363.0	363.0	363.0	362.8	362.4	362.0	361.7	361.3
142.5°	376.1	376.2	376.3	376.1	375.7	375.3	374.9	374.6
145°	396.1	396.2	396.2	396.1	395.7	395.3	394.9	394.5
147.5°	413.5	413.8	414.0	413.9	413.5	413.1	412.7	412.5
150°	424.6	424.9	425.2	425.2	424.9	424.6	424.3	424.0
152.5°	435.6	436.0	436.4	436.4	436.0	435.6	435.4	435.0
155°	449.8	450.3	450.7	450.8	450.5	450.3	450.0	449.7
157.5°	462.7	463.4	464.0	464.1	463.6	463.2	462.8	462.3
160°	470.4	471.0	471.6	471.6	471.3	470.9	470.5	470.1
162.5°	477.4	478.1	478.7	478.8	478.3	477.9	477.4	477.0
165°	486.4	487.1	487.8	487.9	487.4	486.9	486.4	486.0
167.5°	493.9	494.6	495.2	495.3	494.7	494.3	493.8	493.3
170°	497.9	498.6	499.3	499.4	498.8	498.2	497.7	497.1
172.5°	501.1	501.7	502.4	502.4	501.8	501.2	500.7	500.1
175°	504.4	505.0	505.7	505.8	505.2	504.6	504.1	503.5
177.5°	506.0	506.3	506.8	506.8	506.3	506.0	505.5	505.0
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1

(END OF REPORT)