

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331595-830

Luminaire Tested: **S122DIW-S1005D710U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331595-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D710U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6496.5 lumens  
Efficiency: N/A  
Efficacy: 108.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331595-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331595-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331595-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.3	2.2
10°-20°	397.5	6.1
20°-30°	584.2	9.0
30°-40°	678.6	10.4
40°-50°	677.9	10.4
50°-60°	591.2	9.1
60°-70°	437.1	6.7
70°-80°	247.6	3.8
80°-90°	68.8	1.1
90°-100°	30.4	0.5
100°-110°	111.6	1.7
110°-120°	298.2	4.6
120°-130°	492.2	7.6
130°-140°	523.5	8.1
140°-150°	486.5	7.5
150°-160°	391.2	6.0
160°-170°	252.1	3.9
170°-180°	86.8	1.3
0°-30°	1123.0	17.3
0°-40°	1801.6	27.7
0°-60°	3070.7	47.3
0°-90°	3824.2	58.9
90°-120°	440.1	6.8
90°-150°	1942.3	29.9
90°-180°	2672.0	41.1
0°-180°	6496.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	1	8	13	16	18	5
95°	43	23	26	29	28	52
105°	201	209	40	47	50	214
115°	379	391	407	116	54	373
125°	536	545	558	562	564	478
135°	664	674	680	686	686	512
145°	770	770	781	785	782	481
155°	848	843	850	853	849	391
165°	893	890	892	896	892	252
175°	914	910	911	915	909	87
180°	912	912	912	912	912	



TEST NUMBER: P331595-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	20.9	20.7	20.5	20.4	20.2	19.9	19.7	19.4	19.1	18.9	18.2
90°	0.7	2.3	3.9	5.5	7.1	8.5	9.7	10.8	12.1	13.2	13.9
92.5°	13.3	13.2	13.0	12.9	12.7	13.0	13.6	14.1	14.7	15.3	15.6
95°	42.9	38.1	33.2	28.4	23.6	21.6	22.6	23.7	24.7	25.7	26.5
97.5°	85.1	71.4	57.9	44.2	30.5	25.0	27.3	29.7	32.0	34.4	35.1
100°	116.8	96.7	76.6	56.6	36.5	27.6	30.2	32.6	35.2	37.6	38.7
102.5°	151.7	147.4	143.1	138.8	134.6	122.1	101.2	80.4	59.5	38.6	40.2
105°	200.6	205.0	209.4	213.8	218.2	200.4	160.3	120.3	80.3	40.2	41.8
107.5°	256.4	260.0	263.5	267.0	270.6	248.4	200.4	152.4	104.3	56.4	54.7
110°	292.3	295.4	298.5	301.5	304.6	284.9	242.6	200.2	157.9	115.5	100.9



TEST NUMBER: P331595-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	326.1	328.9	331.6	334.2	337.0	333.1	322.6	312.2	301.7	291.2	237.8
115°	379.4	381.9	384.4	386.9	389.4	392.5	396.2	399.8	403.4	407.1	339.2
117.5°	427.1	429.8	432.6	435.4	438.2	440.8	443.4	445.9	448.4	450.9	434.5
120°	461.8	464.1	466.3	468.4	470.7	473.1	475.7	478.3	481.0	483.6	485.4
122.5°	491.4	493.8	496.1	498.4	500.7	503.3	506.1	509.1	511.9	514.8	515.9
125°	536.4	538.4	540.3	542.2	544.0	546.4	549.2	552.0	554.8	557.5	558.6
127.5°	577.2	579.3	581.5	583.5	585.7	587.8	589.8	591.9	594.0	596.1	597.6
130°	603.0	605.4	607.8	610.1	612.5	614.4	616.0	617.6	619.3	620.9	622.5
132.5°	629.5	631.5	633.5	635.5	637.4	639.2	640.8	642.4	644.1	645.7	647.1
135°	663.8	666.1	668.5	670.8	673.2	675.0	676.4	677.7	679.0	680.3	681.7
137.5°	698.5	700.1	701.8	703.4	705.0	706.6	708.1	709.6	711.1	712.7	714.1
140°	721.2	722.4	723.5	724.7	725.9	727.3	728.9	730.5	732.1	733.8	735.1
142.5°	740.2	741.2	742.3	743.4	744.4	745.8	747.7	749.6	751.4	753.3	754.5
145°	770.1	769.9	769.8	769.6	769.4	770.6	773.1	775.6	778.1	780.6	781.7
147.5°	796.0	795.5	794.9	794.4	793.8	794.8	797.2	799.7	802.1	804.6	805.4
150°	812.9	811.9	810.9	809.8	808.8	809.5	811.8	814.2	816.5	818.9	819.7
152.5°	827.2	826.0	824.9	823.7	822.6	823.1	825.4	827.6	829.8	832.1	832.9
155°	847.9	846.6	845.3	844.0	842.6	842.8	844.6	846.3	848.1	849.9	850.7
157.5°	864.1	863.0	861.9	860.7	859.7	859.7	860.9	862.1	863.4	864.6	865.6
160°	873.6	872.7	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6	874.5
162.5°	882.0	881.2	880.3	879.4	878.5	878.4	879.2	880.1	880.8	881.6	882.5
165°	893.4	892.5	891.6	890.8	889.9	889.7	890.1	890.5	891.0	891.5	892.5
167.5°	901.8	901.0	900.1	899.2	898.3	898.1	898.5	898.9	899.4	899.8	900.8
170°	906.6	905.7	904.8	904.0	903.1	902.8	903.1	903.4	903.7	904.0	905.0
172.5°	909.7	908.9	908.0	907.1	906.3	906.0	906.3	906.5	906.8	907.1	908.1
175°	913.9	912.9	911.8	910.8	909.7	909.4	909.6	910.0	910.3	910.6	911.6
177.5°	914.5	913.7	912.9	912.1	911.3	910.9	911.0	911.2	911.3	911.3	912.2
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331595-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	17.5	17.0	16.3	15.9	15.7	15.6	15.4	15.1
90°	14.7	15.4	16.1	16.7	17.0	17.2	17.5	17.8
92.5°	16.1	16.5	16.9	17.2	17.2	17.4	17.6	17.8
95°	27.2	27.9	28.7	28.9	28.8	28.7	28.6	28.4
97.5°	35.6	36.2	36.8	37.1	37.3	37.5	37.7	37.9
100°	40.0	41.1	42.3	43.1	43.4	43.6	43.9	44.2
102.5°	41.8	43.3	44.8	45.7	46.2	46.6	46.9	47.4
105°	43.5	45.1	46.7	47.8	48.4	49.0	49.6	50.1
107.5°	53.1	51.5	49.8	49.3	49.9	50.4	51.0	51.6
110°	86.1	71.4	56.8	49.8	50.3	51.0	51.6	52.1





TEST NUMBER: P331595-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	184.3	130.8	77.3	50.8	51.3	51.7	52.2	52.7
115°	271.4	203.4	135.5	96.3	85.8	75.2	64.7	54.1
117.5°	418.1	401.6	385.2	359.7	325.0	290.3	255.6	220.9
120°	487.2	488.9	490.7	481.6	461.8	442.1	422.3	402.5
122.5°	516.9	517.9	519.1	517.6	513.8	509.9	506.1	502.3
125°	559.6	560.6	561.7	562.4	562.8	563.3	563.7	564.1
127.5°	599.1	600.6	602.1	602.9	602.9	603.0	603.1	603.2
130°	624.2	625.8	627.4	628.1	627.9	627.8	627.6	627.5
132.5°	648.5	649.9	651.2	651.9	651.7	651.6	651.4	651.3
135°	683.2	684.7	686.2	686.7	686.5	686.2	685.9	685.6
137.5°	715.5	716.9	718.4	718.9	718.3	717.8	717.4	716.8
140°	736.4	737.7	739.0	739.3	738.6	737.8	737.1	736.4
142.5°	755.6	756.9	758.1	758.3	757.6	756.9	756.1	755.4
145°	782.6	783.6	784.7	784.9	784.1	783.3	782.6	781.9
147.5°	806.2	806.9	807.7	807.8	807.1	806.5	805.9	805.2
150°	820.6	821.5	822.4	822.5	821.7	821.0	820.2	819.5
152.5°	833.8	834.7	835.6	835.6	834.5	833.6	832.6	831.6
155°	851.6	852.5	853.4	853.2	852.1	850.9	849.7	848.6
157.5°	866.7	867.6	868.6	868.6	867.4	866.3	865.2	863.9
160°	875.3	876.3	877.1	877.0	876.0	875.0	874.0	873.0
162.5°	883.5	884.5	885.5	885.4	884.1	882.9	881.6	880.3
165°	893.5	894.5	895.5	895.5	894.5	893.5	892.5	891.5
167.5°	901.8	902.9	903.8	903.7	902.4	901.1	899.8	898.4
170°	906.1	907.0	908.0	908.0	906.6	905.3	904.0	902.7
172.5°	909.2	910.2	911.3	911.1	909.7	908.4	907.1	905.8
175°	912.7	913.6	914.6	914.5	912.9	911.5	910.0	908.6
177.5°	913.0	913.8	914.6	914.5	913.5	912.4	911.3	910.3
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9

(END OF REPORT)