

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331596-830

Luminaire Tested: **S122DIW-S1005D710U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331596-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D710U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6142.7 lumens  
Efficiency: N/A  
Efficacy: 102.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331596-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331596-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	52
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	52	50	48	44
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20	17
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331596-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.3	2.3
10°-20°	397.5	6.5
20°-30°	584.2	9.5
30°-40°	678.6	11.0
40°-50°	677.9	11.0
50°-60°	591.2	9.6
60°-70°	437.1	7.1
70°-80°	247.6	4.0
80°-90°	69.9	1.1
90°-100°	52.5	0.9
100°-110°	163.1	2.7
110°-120°	278.8	4.5
120°-130°	366.6	6.0
130°-140°	411.5	6.7
140°-150°	403.5	6.6
150°-160°	338.4	5.5
160°-170°	224.5	3.7
170°-180°	78.5	1.3
0°-30°	1123.0	18.3
0°-40°	1801.6	29.3
0°-60°	3070.7	50.0
0°-90°	3825.3	62.3
90°-120°	494.4	8.0
90°-150°	1676.1	27.3
90°-180°	2317.0	37.7
0°-180°	6142.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	1	10	24	23	24	5
95°	36	43	45	45	43	42
105°	150	152	154	155	155	159
115°	280	284	283	282	280	277
125°	407	413	411	409	408	364
135°	527	534	536	535	533	407
145°	639	644	648	649	646	399
155°	731	733	735	738	736	336
165°	795	795	795	799	796	224
175°	827	825	824	828	825	79
180°	829	829	829	829	829	



TEST NUMBER: P331596-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	20.9	20.8	20.6	20.5	20.4	20.4	20.5	20.7	20.9	21.1	20.3
90°	0.7	2.5	4.4	6.3	8.2	10.8	14.2	17.6	21.0	24.5	24.1
92.5°	12.4	13.9	15.2	16.6	17.9	19.0	19.8	20.6	21.4	22.2	22.3
95°	36.4	37.9	39.5	41.0	42.6	43.5	43.8	44.1	44.5	44.8	44.8
97.5°	66.4	67.8	69.2	70.5	71.9	72.9	73.5	74.1	74.6	75.2	75.2
100°	88.8	90.1	91.3	92.6	93.8	94.6	95.1	95.6	96.0	96.5	96.5
102.5°	112.4	113.3	114.3	115.3	116.3	117.1	117.7	118.3	118.9	119.4	119.6
105°	150.3	150.8	151.3	151.7	152.2	152.6	153.0	153.3	153.5	153.9	154.2
107.5°	188.7	189.4	190.1	190.8	191.4	191.8	191.8	191.8	191.8	191.8	191.9
110°	213.3	214.2	215.2	216.1	217.1	217.5	217.5	217.5	217.5	217.5	217.5



TEST NUMBER: P331596-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	240.2	241.1	242.0	243.0	243.9	244.3	244.2	244.0	243.9	243.8	243.5
115°	279.7	280.7	281.6	282.6	283.5	283.8	283.5	283.1	282.9	282.6	282.4
117.5°	319.2	320.5	321.7	322.9	324.1	324.3	323.5	322.6	321.8	320.9	320.6
120°	345.5	346.8	348.0	349.2	350.4	350.4	349.2	348.0	346.8	345.5	345.5
122.5°	369.6	371.1	372.6	374.0	375.5	375.9	374.9	374.1	373.2	372.4	372.0
125°	407.1	408.5	409.8	411.2	412.6	413.1	412.6	412.2	411.7	411.2	410.8
127.5°	443.6	445.4	447.1	448.8	450.6	451.3	450.7	450.2	449.6	449.0	448.5
130°	466.5	468.5	470.5	472.6	474.6	475.4	475.1	474.9	474.5	474.2	473.9
132.5°	492.3	493.9	495.6	497.2	498.8	499.7	499.7	499.8	499.9	499.9	499.3
135°	526.7	528.4	530.1	531.8	533.5	534.5	534.8	535.2	535.5	535.7	535.6
137.5°	562.9	564.3	565.7	567.1	568.4	569.4	569.8	570.2	570.6	571.0	570.9
140°	584.8	586.1	587.5	588.9	590.3	591.4	592.2	593.0	593.7	594.5	594.5
142.5°	607.1	608.5	609.9	611.3	612.7	613.7	614.2	614.7	615.2	615.8	615.9
145°	639.2	640.4	641.4	642.5	643.7	644.6	645.5	646.5	647.4	648.4	648.5
147.5°	668.0	669.2	670.5	671.8	673.2	674.1	674.8	675.3	676.0	676.7	676.9
150°	687.5	688.4	689.4	690.3	691.3	692.0	692.7	693.2	693.9	694.6	695.0
152.5°	704.8	705.8	706.7	707.7	708.6	709.5	710.2	711.0	711.7	712.5	713.0
155°	730.8	731.3	731.8	732.3	732.7	733.2	733.7	734.1	734.6	735.1	735.8
157.5°	753.1	753.5	753.8	754.0	754.4	754.7	755.0	755.3	755.5	755.8	756.9
160°	766.6	766.9	767.1	767.5	767.8	768.1	768.2	768.4	768.5	768.6	769.6
162.5°	778.8	778.9	779.0	779.0	779.1	779.2	779.4	779.6	779.7	779.9	780.9
165°	795.2	795.0	794.9	794.8	794.7	794.6	794.6	794.6	794.6	794.6	795.6
167.5°	809.0	808.5	808.0	807.6	807.1	806.8	806.8	806.7	806.7	806.7	807.8
170°	816.2	815.8	815.3	814.8	814.4	814.1	813.9	813.7	813.6	813.4	814.5
172.5°	821.2	820.8	820.3	819.8	819.4	819.1	818.9	818.8	818.6	818.4	819.5
175°	827.4	827.0	826.5	826.0	825.6	825.2	824.8	824.5	824.3	823.9	825.0
177.5°	829.9	829.5	829.2	828.8	828.4	828.1	827.8	827.6	827.4	827.1	827.8
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331596-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	19.4	18.6	17.7	17.2	17.0	16.8	16.5	16.3
90°	23.8	23.6	23.3	23.2	23.3	23.5	23.7	23.8
92.5°	22.3	22.4	22.5	22.5	22.5	22.6	22.6	22.6
95°	44.8	44.8	44.8	44.6	44.3	44.0	43.6	43.4
97.5°	75.2	75.2	75.2	75.2	75.2	75.2	75.1	75.1
100°	96.5	96.5	96.5	96.4	96.3	96.1	96.0	95.9
102.5°	119.7	119.8	120.0	120.0	119.8	119.6	119.5	119.3
105°	154.5	154.8	155.1	155.2	155.2	155.2	155.2	155.2
107.5°	192.0	192.2	192.3	192.0	191.2	190.6	189.8	189.2
110°	217.5	217.5	217.5	217.3	216.8	216.3	215.8	215.5





TEST NUMBER: P331596-830

CATALOG NUMBER: S122DIW-S1005D710U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	243.1	242.7	242.3	242.0	241.7	241.3	240.9	240.6
115°	282.3	282.1	281.9	281.6	281.2	280.7	280.2	279.7
117.5°	320.2	319.8	319.4	319.0	318.5	318.0	317.5	317.1
120°	345.5	345.5	345.5	345.3	344.8	344.3	343.8	343.4
122.5°	371.6	371.3	370.9	370.5	370.1	369.9	369.5	369.2
125°	410.3	409.8	409.3	409.1	409.0	408.8	408.6	408.5
127.5°	447.9	447.3	446.8	446.3	445.7	445.3	444.8	444.3
130°	473.6	473.3	473.0	472.5	471.8	471.3	470.6	470.0
132.5°	498.6	497.9	497.2	496.6	496.2	495.6	495.1	494.6
135°	535.5	535.3	535.2	534.8	534.3	533.9	533.4	532.9
137.5°	570.7	570.6	570.5	570.1	569.5	568.9	568.3	567.6
140°	594.5	594.5	594.5	594.2	593.6	593.0	592.3	591.7
142.5°	616.0	616.1	616.2	616.0	615.4	614.7	614.2	613.5
145°	648.7	648.8	648.9	648.8	648.1	647.5	646.9	646.3
147.5°	677.3	677.6	678.0	677.9	677.3	676.7	676.1	675.5
150°	695.4	695.9	696.4	696.4	695.9	695.4	695.0	694.6
152.5°	713.6	714.2	714.8	714.8	714.2	713.6	713.0	712.5
155°	736.6	737.4	738.2	738.4	737.9	737.4	737.0	736.5
157.5°	757.9	758.9	760.0	760.2	759.4	758.7	757.9	757.1
160°	770.5	771.5	772.4	772.5	771.9	771.3	770.7	770.1
162.5°	781.9	783.1	784.1	784.2	783.4	782.8	782.0	781.3
165°	796.7	797.8	798.9	799.1	798.2	797.5	796.7	796.0
167.5°	808.9	809.9	811.1	811.2	810.4	809.5	808.8	807.9
170°	815.6	816.7	817.7	817.8	816.9	816.0	815.0	814.1
172.5°	820.7	821.7	822.8	822.8	822.0	821.0	820.1	819.2
175°	826.0	827.2	828.3	828.3	827.4	826.5	825.6	824.6
177.5°	828.6	829.3	830.1	830.1	829.3	828.6	827.8	827.1
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8

(END OF REPORT)