

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644590

Luminaire Tested: OMN4DIP-SR4F0-100D25U930-WBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P644590
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-27)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-100D25U930-WBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - WHITE BAFFLE WITH MEDIUM OPTIC - 1000 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5033.0 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.21 / 1.19
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 46.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644590

CATALOG NUMBER: OMN4DIP-SR4F0-100D25U930-WBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644590

CATALOG NUMBER: OMN4DIP-SR4F0-100D25U930-WBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	115	115	115	115	110	110	110	110	102	102	102		94	94	94		86	86	86	83
1	108	105	102	99	104	101	98	96	94	92	90		87	85	84		81	80	79	76
2	101	95	90	86	97	92	88	84	86	82	79		80	78	75		75	73	71	68
3	94	87	81	76	91	84	78	74	79	74	71		74	70	67		69	67	64	62
4	88	79	72	67	85	77	71	66	72	67	63		68	64	61		64	61	58	56
5	82	72	65	60	79	70	64	59	67	61	57		63	59	55		60	56	53	51
6	77	66	59	54	74	65	58	53	61	56	52		58	54	50		55	51	48	46
7	72	61	54	49	70	60	53	48	57	51	47		54	49	46		51	47	44	42
8	68	57	50	45	65	55	49	44	53	47	43		50	45	42		48	44	41	39
9	64	52	46	41	61	51	45	40	49	43	39		47	42	38		45	40	37	36
10	60	49	42	38	58	48	41	37	46	40	36		44	39	35		42	38	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	33454	33454	33454
5°	33202	33657	34315
10°	33740	34405	34967
15°	34582	35052	35286
20°	34770	35091	34690
25°	34105	34188	33772
30°	32609	32521	31736
35°	29769	29523	28908
40°	24729	24368	23908
45°	15532	17670	14820
50°	5956	10463	5526
55°	2810	4391	2855
60°	1361	2217	1209
65°	1253	1311	1134
70°	1254	1254	1107
75°	1268	1268	1073
80°	1309	1160	1019
85°	1452	1156	874

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 17670 cd/sqm



TEST NUMBER: P644590

CATALOG NUMBER: OMN4DIP-SR4F0-100D25U930-WBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.5	5.0
10°-20°	737.8	14.7
20°-30°	1096.1	21.8
30°-40°	1147.2	22.8
40°-50°	694.9	13.8
50°-60°	160.3	3.2
60°-70°	44.1	0.9
70°-80°	25.8	0.5
80°-90°	9.3	0.2
90°-100°	19.9	0.4
100°-110°	141.6	2.8
110°-120°	192.2	3.8
120°-130°	156.4	3.1
130°-140°	125.8	2.5
140°-150°	99.2	2.0
150°-160°	72.5	1.4
160°-170°	45.0	0.9
170°-180°	15.4	0.3
0°-30°	2083.4	41.4
0°-40°	3230.6	64.2
0°-60°	4085.9	81.2
0°-90°	4165.1	82.8
90°-120°	353.6	7.0
90°-150°	735.0	14.6
90°-180°	868.0	17.2
0°-180°	5033.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2590	2590	2590	2590	2590	
5°	2561	2620	2596	2606	2646	245
15°	2586	2664	2621	2601	2639	728
25°	2393	2464	2399	2337	2370	1096
35°	1888	1916	1872	1830	1833	1160
45°	850	967	967	933	811	653
55°	125	142	195	134	127	130
65°	41	43	43	39	37	41
75°	25	25	25	23	22	27
85°	10	10	8	8	6	10
90°	0	1	2	3	3	1
95°	8	15	8	9	11	9
105°	32	48	184	235	156	33
115°	56	68	158	330	385	55
125°	80	91	149	261	309	71
135°	100	110	150	215	247	77
145°	118	128	151	187	207	74
155°	138	143	154	170	178	63
165°	154	155	158	163	166	43
175°	162	163	162	160	160	15
180°	162	162	162	162	162	



TEST NUMBER: P644590

CATALOG NUMBER: OMN4DIP-SR4F0-100D25U930-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2590.0	2590.0	2590.0	2590.0	2590.0
2.5°	2565.0	2610.8	2585.3	2587.3	2608.7
5°	2560.7	2619.8	2595.8	2606.5	2646.5
7.5°	2567.7	2629.5	2615.3	2619.1	2662.9
10°	2572.4	2637.3	2623.1	2622.2	2666.0
12.5°	2583.3	2651.2	2624.7	2619.0	2661.4
15°	2586.1	2664.3	2621.2	2600.6	2638.7
17.5°	2560.7	2646.9	2588.8	2546.2	2576.7
20°	2529.5	2617.2	2552.9	2493.2	2523.7
22.5°	2481.1	2567.3	2498.3	2433.9	2465.9
25°	2393.0	2463.6	2398.8	2337.2	2369.6
27.5°	2281.4	2331.0	2275.6	2217.1	2235.4
30°	2186.3	2235.8	2180.4	2120.1	2127.8
32.5°	2080.2	2122.1	2068.1	2014.0	2020.1
35°	1887.9	1916.5	1872.3	1829.5	1833.3
37.5°	1653.8	1657.7	1627.7	1588.7	1589.5
40°	1466.6	1478.1	1445.2	1414.0	1417.9
42.5°	1243.5	1288.5	1256.4	1228.3	1229.1
45°	850.3	966.6	967.3	933.4	811.3
47.5°	469.6	604.3	690.8	535.7	404.5
50°	296.4	382.3	520.7	313.1	275.0
52.5°	212.2	250.7	380.3	221.5	201.7
55°	124.8	142.0	195.0	134.4	126.8
57.5°	76.1	90.9	113.9	89.8	76.5
60°	52.7	66.0	85.8	60.2	46.8
62.5°	46.4	50.6	67.1	47.9	43.7
65°	41.0	42.9	42.9	39.0	37.1
67.5°	36.3	38.2	36.3	34.3	32.4
70°	33.2	35.1	33.2	31.2	29.3
72.5°	30.0	31.9	30.0	28.0	26.1
75°	25.4	25.4	25.4	23.4	21.5
77.5°	20.7	20.7	20.3	18.7	16.8
80°	17.6	17.6	15.6	15.6	13.7
82.5°	14.4	14.4	12.5	12.4	10.5
85°	9.8	9.8	7.8	7.8	5.9
87.5°	4.7	4.9	3.5	3.7	2.2
90°	0.0	1.0	2.0	3.0	3.0
92.5°	2.4	3.4	4.5	6.3	7.1
95°	8.1	15.1	8.1	9.2	11.2
97.5°	14.4	28.9	59.8	17.6	15.2
100°	19.3	36.2	119.9	35.3	23.4
102.5°	24.2	41.9	162.2	93.1	51.0
105°	31.5	48.4	183.9	235.0	155.5
107.5°	38.8	51.5	175.6	342.0	320.3
110°	43.7	55.6	170.7	359.3	386.2



TEST NUMBER: P644590

CATALOG NUMBER: OMN4DIP-SR4F0-100D25U930-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	48.6	60.5	165.8	349.2	394.3
115°	55.9	67.8	158.5	329.5	385.2
117.5°	63.4	75.1	156.7	308.2	365.4
120°	69.1	80.0	153.5	292.0	351.6
122.5°	73.2	84.9	149.4	278.1	332.9
125°	80.3	91.2	149.4	261.2	308.9
127.5°	86.2	97.3	149.6	241.7	288.8
130°	89.4	101.4	150.4	228.7	273.4
132.5°	93.5	105.4	150.4	222.8	259.5
135°	99.6	110.5	150.4	215.1	246.9
137.5°	104.7	116.4	150.4	206.7	233.9
140°	108.7	119.7	150.4	201.8	226.6
142.5°	112.8	122.9	151.2	196.1	219.3
145°	117.9	127.8	151.4	187.4	207.3
147.5°	124.0	132.7	152.6	181.2	196.5
150°	128.0	136.0	153.5	177.1	190.0
152.5°	132.1	139.3	153.5	173.8	184.3
155°	138.2	143.2	154.5	169.9	177.8
157.5°	143.1	147.9	155.7	167.4	173.2
160°	146.3	150.3	156.5	165.8	170.7
162.5°	148.8	152.8	157.3	164.9	168.3
165°	153.5	155.4	158.5	162.7	165.6
167.5°	156.1	157.9	159.5	161.6	163.4
170°	158.5	159.5	159.5	161.6	162.6
172.5°	159.3	161.1	160.4	160.8	161.8
175°	161.6	162.6	161.6	160.5	159.5
177.5°	161.6	162.4	161.6	161.6	160.8
180°	161.6	161.6	161.6	161.6	161.6

(END OF REPORT)