

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331602-830

Luminaire Tested: **S122DIW-S1005D970U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331602-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D970U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6989.7 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331602-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331602-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	53	52	51	46
2	90	83	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24	21
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331602-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.3	2.0
10°-20°	397.5	5.7
20°-30°	584.2	8.4
30°-40°	678.6	9.7
40°-50°	677.9	9.7
50°-60°	591.2	8.5
60°-70°	437.1	6.3
70°-80°	247.6	3.5
80°-90°	71.1	1.0
90°-100°	71.7	1.0
100°-110°	222.6	3.2
110°-120°	380.6	5.4
120°-130°	500.5	7.2
130°-140°	561.7	8.0
140°-150°	550.8	7.9
150°-160°	462.0	6.6
160°-170°	306.4	4.4
170°-180°	107.1	1.5
0°-30°	1123.0	16.1
0°-40°	1801.6	25.8
0°-60°	3070.7	43.9
0°-90°	3826.5	54.7
90°-120°	674.9	9.7
90°-150°	2287.8	32.7
90°-180°	3163.0	45.3
0°-180°	6989.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	1	13	33	32	32	5
95°	50	59	61	61	59	57
105°	205	208	210	212	212	217
115°	382	387	386	385	382	378
125°	556	564	561	559	558	496
135°	719	729	731	730	728	555
145°	872	879	885	886	882	545
155°	998	1000	1003	1008	1005	459
165°	1085	1085	1084	1090	1086	306
175°	1129	1126	1124	1131	1126	107
180°	1131	1131	1131	1131	1131	



TEST NUMBER: P331602-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	21.0	21.0	21.0	21.0	21.0	21.2	21.6	22.1	22.4	22.9	22.0
90°	0.9	3.5	6.0	8.6	11.1	14.7	19.4	24.0	28.7	33.4	33.0
92.5°	17.0	18.9	20.7	22.6	24.5	25.9	27.1	28.2	29.2	30.3	30.4
95°	49.7	51.7	53.9	56.0	58.2	59.4	59.9	60.2	60.7	61.1	61.1
97.5°	90.7	92.6	94.4	96.3	98.1	99.5	100.3	101.1	101.9	102.7	102.7
100°	121.2	122.9	124.6	126.3	128.0	129.2	129.8	130.4	131.1	131.8	131.8
102.5°	153.4	154.7	156.0	157.4	158.7	159.9	160.6	161.5	162.2	163.1	163.2
105°	205.3	205.9	206.5	207.2	207.8	208.3	208.8	209.2	209.6	210.0	210.5
107.5°	257.6	258.5	259.4	260.3	261.3	261.7	261.7	261.7	261.7	261.7	261.9
110°	291.2	292.5	293.7	295.0	296.2	296.9	296.9	296.9	296.9	296.9	296.9



TEST NUMBER: P331602-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.8	329.1	330.4	331.7	332.9	333.5	333.3	333.1	333.0	332.8	332.2
115°	381.8	383.1	384.4	385.7	386.9	387.4	386.9	386.5	386.1	385.7	385.5
117.5°	435.7	437.4	439.1	440.8	442.5	442.7	441.6	440.4	439.2	438.0	437.5
120°	471.6	473.3	475.0	476.7	478.4	478.4	476.7	475.0	473.3	471.6	471.6
122.5°	504.4	506.5	508.5	510.6	512.6	513.0	511.8	510.7	509.4	508.2	507.7
125°	555.6	557.5	559.4	561.4	563.3	563.9	563.3	562.6	561.9	561.4	560.7
127.5°	605.5	607.8	610.3	612.7	615.1	616.0	615.2	614.4	613.7	612.9	612.1
130°	636.8	639.5	642.2	645.1	647.8	648.9	648.6	648.1	647.7	647.2	646.9
132.5°	671.8	674.1	676.4	678.6	680.9	682.0	682.1	682.2	682.3	682.4	681.5
135°	718.9	721.2	723.5	725.9	728.2	729.5	730.0	730.4	730.8	731.2	731.0
137.5°	768.3	770.2	772.1	774.0	775.9	777.2	777.7	778.3	778.8	779.4	779.2
140°	798.1	800.0	801.9	803.8	805.7	807.2	808.3	809.4	810.4	811.4	811.4
142.5°	828.7	830.6	832.5	834.3	836.3	837.6	838.3	839.1	839.8	840.5	840.7
145°	872.5	874.0	875.5	877.0	878.5	879.9	881.2	882.4	883.7	885.0	885.1
147.5°	911.7	913.5	915.3	917.0	918.8	920.1	921.0	921.8	922.7	923.5	924.0
150°	938.4	939.7	940.9	942.3	943.5	944.6	945.5	946.3	947.2	948.0	948.6
152.5°	962.1	963.4	964.7	965.9	967.2	968.4	969.4	970.3	971.4	972.4	973.2
155°	997.6	998.2	998.9	999.6	1000.1	1000.8	1001.5	1002.1	1002.7	1003.3	1004.4
157.5°	1027.9	1028.4	1028.8	1029.3	1029.6	1030.1	1030.5	1030.9	1031.2	1031.6	1033.0
160°	1046.3	1046.7	1047.2	1047.5	1048.0	1048.3	1048.6	1048.8	1049.0	1049.1	1050.5
162.5°	1063.1	1063.2	1063.3	1063.4	1063.5	1063.6	1063.8	1064.0	1064.2	1064.4	1065.9
165°	1085.4	1085.2	1085.1	1084.8	1084.6	1084.5	1084.5	1084.5	1084.5	1084.5	1086.0
167.5°	1104.2	1103.5	1102.9	1102.2	1101.6	1101.3	1101.3	1101.2	1101.2	1101.1	1102.6
170°	1114.1	1113.4	1112.9	1112.2	1111.5	1111.2	1110.9	1110.7	1110.5	1110.3	1111.7
172.5°	1121.0	1120.3	1119.6	1119.1	1118.4	1117.9	1117.8	1117.6	1117.4	1117.1	1118.6
175°	1129.4	1128.7	1128.1	1127.5	1126.8	1126.2	1125.9	1125.4	1125.0	1124.5	1126.1
177.5°	1132.8	1132.3	1131.8	1131.2	1130.8	1130.3	1130.0	1129.6	1129.4	1129.0	1130.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331602-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	21.1	20.3	19.4	18.9	18.7	18.5	18.3	18.0
90°	32.5	32.1	31.7	31.6	31.9	32.0	32.2	32.4
92.5°	30.5	30.6	30.7	30.7	30.8	30.8	30.9	30.9
95°	61.1	61.1	61.1	60.9	60.4	60.0	59.6	59.2
97.5°	102.7	102.7	102.7	102.7	102.6	102.6	102.5	102.5
100°	131.8	131.8	131.8	131.7	131.4	131.2	131.0	130.8
102.5°	163.4	163.5	163.7	163.7	163.5	163.2	163.1	162.9
105°	210.8	211.3	211.7	212.0	212.0	212.0	212.0	212.0
107.5°	262.1	262.3	262.4	262.0	261.1	260.0	259.1	258.2
110°	296.9	296.9	296.9	296.6	296.0	295.3	294.6	294.1





TEST NUMBER: P331602-830

CATALOG NUMBER: S122DIW-S1005D970U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	331.8	331.3	330.7	330.3	329.8	329.3	328.9	328.4
115°	385.2	385.0	384.8	384.4	383.8	383.1	382.5	381.8
117.5°	437.0	436.5	435.9	435.4	434.8	434.1	433.5	432.8
120°	471.6	471.6	471.6	471.3	470.6	470.0	469.4	468.7
122.5°	507.3	506.7	506.2	505.8	505.3	504.8	504.4	503.9
125°	560.1	559.4	558.8	558.4	558.2	558.0	557.7	557.5
127.5°	611.3	610.6	609.8	609.1	608.4	607.8	607.1	606.4
130°	646.4	646.0	645.5	644.9	644.0	643.2	642.3	641.5
132.5°	680.5	679.6	678.6	677.9	677.2	676.5	675.8	675.1
135°	730.8	730.7	730.4	730.0	729.3	728.7	728.1	727.5
137.5°	779.0	778.9	778.7	778.2	777.3	776.5	775.6	774.8
140°	811.4	811.4	811.4	811.1	810.2	809.4	808.5	807.7
142.5°	840.8	841.0	841.1	840.8	840.0	839.1	838.3	837.4
145°	885.4	885.6	885.8	885.5	884.7	883.8	883.0	882.1
147.5°	924.4	924.9	925.4	925.2	924.4	923.6	922.8	922.0
150°	949.2	949.9	950.6	950.6	949.9	949.2	948.6	948.0
152.5°	974.0	974.9	975.6	975.6	974.9	974.0	973.2	972.4
155°	1005.5	1006.5	1007.6	1007.8	1007.2	1006.5	1005.9	1005.2
157.5°	1034.5	1035.9	1037.4	1037.6	1036.6	1035.6	1034.5	1033.5
160°	1051.7	1053.0	1054.2	1054.5	1053.7	1052.8	1052.0	1051.1
162.5°	1067.3	1068.7	1070.3	1070.4	1069.4	1068.4	1067.3	1066.4
165°	1087.5	1088.9	1090.4	1090.6	1089.6	1088.5	1087.5	1086.4
167.5°	1104.1	1105.6	1107.0	1107.2	1106.2	1105.0	1103.9	1102.9
170°	1113.2	1114.7	1116.3	1116.3	1115.0	1113.8	1112.5	1111.3
172.5°	1120.1	1121.6	1123.0	1123.2	1121.9	1120.7	1119.4	1118.1
175°	1127.6	1129.1	1130.5	1130.7	1129.4	1128.1	1126.8	1125.6
177.5°	1131.1	1132.0	1133.0	1133.0	1132.0	1131.1	1130.0	1129.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2

(END OF REPORT)