

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644825

Luminaire Tested: OMN4DIP-SR4F0-125D75U930-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



**Test Information**

Test Method: LM-79-2019  
Report Number: P644825  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-125D75U930-BBMOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE  
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 1250 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7388.1 lumens  
Efficiency: N/A  
Efficacy: 105.1 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18  
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 70.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P644825

CATALOG NUMBER: OMN4DIP-SR4F0-125D75U930-BBMOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P644825

CATALOG NUMBER: OMN4DIP-SR4F0-125D75U930-BBMOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66				
1	104	100	97	95	98	95	92	90	85	83	81	75	74	73	66	65	65	61				
2	97	91	86	82	91	86	82	78	77	74	72	69	67	65	62	60	59	55				
3	90	83	77	72	85	78	73	69	71	67	64	64	61	58	57	55	53	50				
4	84	75	68	63	79	72	66	61	65	60	57	59	55	53	53	51	48	46				
5	78	69	62	56	74	65	59	55	60	55	51	54	51	48	49	46	44	42				
6	73	63	56	51	69	60	54	49	55	50	46	50	46	43	46	43	40	38				
7	68	58	51	46	65	55	49	44	51	46	42	47	42	39	43	39	37	35				
8	64	53	46	41	61	51	45	40	47	42	38	43	39	36	40	36	34	32				
9	60	49	42	38	57	47	41	37	44	39	35	40	36	33	37	34	31	29				
10	57	46	39	35	54	44	38	34	41	36	32	38	33	30	35	31	29	27				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	40825	40825	40825
5°	40278	41141	41781
10°	40969	42005	42458
15°	42100	42727	42793
20°	42293	42767	42055
25°	41318	41776	40861
30°	39119	39560	38419
35°	35559	35559	34821
40°	29246	28956	28331
45°	17487	20552	16676
50°	5653	11454	5305
55°	2000	3833	2000
60°	127	1082	65
65°	76	76	0
70°	94	0	0
75°	0	0	0
80°	0	0	0
85°	371	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 20552 cd/sqm



TEST NUMBER: P644825

CATALOG NUMBER: OMN4DIP-SR4F0-125D75U930-BBMOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	304.1	4.1
10°-20°	899.8	12.2
20°-30°	1331.5	18.0
30°-40°	1376.3	18.6
40°-50°	800.8	10.8
50°-60°	135.6	1.8
60°-70°	5.4	0.1
70°-80°	0.8	0.0
80°-90°	1.8	0.0
90°-100°	57.9	0.8
100°-110°	413.0	5.6
110°-120°	560.7	7.6
120°-130°	456.3	6.2
130°-140°	367.0	5.0
140°-150°	289.3	3.9
150°-160°	211.6	2.9
160°-170°	131.4	1.8
170°-180°	44.8	0.6
0°-30°	2535.3	34.3
0°-40°	3911.6	52.9
0°-60°	4848.1	65.6
0°-90°	4856.0	65.7
90°-120°	1031.6	14.0
90°-150°	2144.3	29.0
90°-180°	2532.0	34.3
0°-180°	7388.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3161	3161	3161	3161	3161	
5°	3106	3188	3173	3181	3222	298
15°	3148	3259	3195	3178	3200	886
25°	2899	2996	2931	2843	2867	1324
35°	2255	2291	2255	2199	2208	1382
45°	957	1114	1125	1087	913	740
55°	89	103	170	96	89	98
65°	2	2	2	0	0	3
75°	0	2	0	0	0	1
85°	2	2	0	0	0	1
90°	0	3	6	9	9	1
95°	24	44	24	27	33	27
105°	92	141	537	686	454	97
115°	163	198	462	961	1124	162
125°	234	266	436	762	901	208
135°	290	322	439	628	720	224
145°	344	373	442	547	605	216
155°	403	418	451	496	519	185
165°	448	454	462	474	483	126
175°	471	474	471	468	465	45
180°	471	471	471	471	471	



TEST NUMBER: P644825

CATALOG NUMBER: OMN4DIP-SR4F0-125D75U930-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3160.6	3160.6	3160.6	3160.6	3160.6
2.5°	3119.2	3181.0	3158.7	3161.0	3176.4
5°	3106.4	3188.4	3173.0	3181.3	3222.3
7.5°	3115.7	3198.7	3196.7	3199.1	3239.1
10°	3123.6	3210.5	3202.6	3200.9	3237.1
12.5°	3139.4	3234.0	3202.6	3198.8	3229.2
15°	3148.3	3259.3	3195.2	3178.4	3200.1
17.5°	3118.2	3241.7	3154.7	3110.0	3118.7
20°	3076.8	3202.2	3111.3	3045.0	3059.5
22.5°	3011.6	3131.3	3050.1	2968.1	2986.5
25°	2899.1	2995.6	2931.2	2842.9	2867.0
27.5°	2739.2	2815.5	2774.8	2689.2	2704.2
30°	2622.8	2685.5	2652.4	2568.7	2575.9
32.5°	2488.5	2541.6	2506.3	2434.3	2433.8
35°	2255.1	2291.3	2255.1	2198.6	2208.3
37.5°	1949.7	1977.2	1940.3	1906.4	1911.2
40°	1734.5	1756.2	1717.3	1685.1	1680.2
42.5°	1466.1	1526.4	1488.3	1444.5	1451.3
45°	957.3	1114.1	1125.1	1086.6	912.9
47.5°	482.6	653.9	783.1	594.3	425.9
50°	281.3	385.0	570.0	314.7	264.0
52.5°	184.6	228.5	398.2	198.8	175.2
55°	88.8	103.3	170.2	96.1	88.8
57.5°	30.6	47.0	75.5	48.0	34.0
60°	4.9	19.4	41.9	14.5	2.5
62.5°	3.0	5.9	26.2	2.9	0.5
65°	2.5	2.5	2.5	0.0	0.0
67.5°	2.5	2.5	0.0	0.0	0.0
70°	2.5	2.5	0.0	0.0	0.0
72.5°	2.5	2.5	0.0	0.0	0.0
75°	0.0	2.4	0.0	0.0	0.0
77.5°	0.0	2.4	0.0	0.0	0.0
80°	0.0	2.4	0.0	0.0	0.0
82.5°	0.0	2.4	0.0	0.0	0.0
85°	2.5	2.5	0.0	0.0	0.0
87.5°	2.0	2.6	1.2	1.8	1.8
90°	0.0	2.9	5.9	8.9	8.9
92.5°	7.1	10.0	13.0	18.4	20.8
95°	23.7	44.0	23.7	26.8	32.6
97.5°	42.1	84.4	174.3	51.4	44.5
100°	56.3	105.6	349.8	103.0	68.2
102.5°	70.6	122.2	473.2	271.7	148.8
105°	91.9	141.2	536.6	685.5	453.6
107.5°	113.2	150.4	512.3	997.6	934.5
110°	127.5	162.3	498.1	1048.3	1126.6

TEST NUMBER: P644825

CATALOG NUMBER: OMN4DIP-SR4F0-125D75U930-BBMOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	141.7	176.5	483.8	1018.7	1150.3
115°	163.1	197.8	462.5	961.3	1123.6
117.5°	185.0	219.2	457.1	899.1	1066.1
120°	201.6	233.5	447.7	851.8	1025.8
122.5°	213.5	247.7	435.8	811.2	971.2
125°	234.2	266.1	435.8	762.1	901.2
127.5°	251.4	283.9	436.4	705.1	842.5
130°	260.9	295.7	438.8	667.0	797.5
132.5°	272.7	307.5	438.8	649.9	757.2
135°	290.5	322.4	438.8	627.6	720.4
137.5°	305.4	339.6	438.8	603.0	682.5
140°	317.2	349.1	438.8	588.6	661.1
142.5°	329.1	358.6	441.1	571.9	639.8
145°	343.9	372.9	441.7	546.8	604.8
147.5°	361.7	387.2	445.3	528.7	573.4
150°	373.5	396.7	447.7	516.7	554.4
152.5°	385.4	406.3	447.7	507.1	537.8
155°	403.2	417.7	450.6	495.6	518.8
157.5°	417.4	431.3	454.2	488.4	505.2
160°	426.9	438.5	456.6	483.6	498.1
162.5°	434.0	445.6	458.9	481.1	490.9
165°	447.7	453.5	462.5	474.5	483.2
167.5°	455.4	460.6	465.4	471.5	476.7
170°	462.5	465.4	465.4	471.4	474.3
172.5°	464.9	470.1	467.8	469.1	472.0
175°	471.4	474.3	471.4	468.3	465.4
177.5°	471.4	473.7	471.4	471.3	469.0
180°	471.4	471.4	471.4	471.4	471.4

(END OF REPORT)