

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331487-830

Luminaire Tested: **S122DIW-S290D1240U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331487-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1240U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5806.4 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331487-830

CATALOG NUMBER: S122DIW-S290D1240U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331487-830

CATALOG NUMBER: S122DIW-S290D1240U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	20
1	91	87	83	80	80	77	74	71	58	56	54	41	40	38	25	24	24	16
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17	12
4	69	59	51	46	61	52	46	41	40	35	32	28	25	23	17	16	15	10
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9
6	58	47	39	33	51	41	35	30	32	27	24	23	20	17	14	12	11	8
7	53	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7
8	49	38	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9	6
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7190	7190	7190
5°	7217	7112	7156
10°	7174	7040	7076
15°	7086	6950	6944
20°	6959	6813	6806
25°	6834	6645	6645
30°	6674	6490	6434
35°	6524	6303	6211
40°	6336	6119	6001
45°	6149	5934	5786
50°	5948	5745	5541
55°	5737	5520	5315
60°	5503	5254	5060
65°	5249	4989	4760
70°	4928	4669	4447
75°	4485	4298	4192
80°	3980	3868	3663
85°	3242	3094	2779



TEST NUMBER: P331487-830

CATALOG NUMBER: S122DIW-S290D1240U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	0.7
10°-20°	117.8	2.0
20°-30°	173.2	3.0
30°-40°	201.2	3.5
40°-50°	200.9	3.5
50°-60°	175.2	3.0
60°-70°	129.6	2.2
70°-80°	73.4	1.3
80°-90°	23.7	0.4
90°-100°	53.1	0.9
100°-110°	194.9	3.4
110°-120°	521.0	9.0
120°-130°	860.1	14.8
130°-140°	914.7	15.8
140°-150°	850.1	14.6
150°-160°	683.5	11.8
160°-170°	440.5	7.6
170°-180°	151.6	2.6
0°-30°	332.9	5.7
0°-40°	534.0	9.2
0°-60°	910.2	15.7
0°-90°	1136.8	19.6
90°-120°	769.1	13.2
90°-150°	3394.0	58.5
90°-180°	4670.0	80.4
0°-180°	5806.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	445	445	445	445	445	
5°	445	443	439	442	442	42
15°	424	421	416	417	415	119
25°	384	380	373	374	373	176
35°	331	327	320	317	315	207
45°	269	266	260	255	253	208
55°	204	201	196	191	189	182
65°	137	135	131	127	125	136
75°	72	71	69	66	67	77
85°	18	17	17	16	15	20
90°	1	14	23	29	31	4
95°	75	39	45	50	50	92
105°	350	366	70	83	88	375
115°	663	683	711	203	94	653
125°	937	953	974	982	986	835
135°	1160	1178	1189	1200	1198	896
145°	1346	1346	1364	1371	1366	841
155°	1482	1472	1485	1491	1483	682
165°	1561	1555	1558	1565	1558	441
175°	1597	1589	1591	1598	1588	152
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331487-830

CATALOG NUMBER: S122DIW-S290D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	447.3	447.0	446.6	446.2	445.8	445.3	444.4	443.6	442.7	441.9	442.6
5°	445.3	444.9	444.5	444.1	443.7	443.1	442.1	441.0	439.9	438.8	439.6
7.5°	441.4	440.7	440.2	439.6	439.0	438.2	437.2	436.0	435.0	433.9	434.7
10°	437.6	437.0	436.3	435.6	434.9	434.0	432.9	431.8	430.6	429.4	430.2
12.5°	432.4	431.9	431.3	430.6	430.1	429.2	428.1	427.0	425.8	424.7	425.2
15°	423.9	423.3	422.7	422.2	421.6	420.8	419.4	418.2	417.0	415.8	416.1
17.5°	412.9	412.4	411.8	411.2	410.7	409.7	408.5	407.2	406.0	404.7	405.1
20°	405.0	404.4	403.9	403.3	402.7	401.8	400.5	399.2	397.8	396.5	396.8
22.5°	397.2	396.3	395.6	394.7	394.0	392.9	391.7	390.4	389.2	388.0	388.0
25°	383.6	382.9	382.1	381.4	380.6	379.4	377.8	376.2	374.6	373.0	373.2
27.5°	368.3	367.6	366.8	366.2	365.5	364.5	363.3	361.9	360.7	359.4	359.1
30°	358.0	357.2	356.5	355.7	354.9	353.8	352.4	351.0	349.5	348.1	347.8
32.5°	346.9	346.4	345.8	345.2	344.6	343.5	342.0	340.5	339.0	337.5	337.0
35°	331.0	330.0	329.0	328.1	327.2	325.9	324.4	322.9	321.4	319.8	319.2
37.5°	312.9	312.1	311.2	310.4	309.5	308.4	306.9	305.4	303.8	302.3	301.6
40°	300.6	299.8	299.1	298.3	297.6	296.4	294.8	293.3	291.8	290.3	289.5
42.5°	288.6	287.9	287.1	286.3	285.6	284.4	282.9	281.3	279.8	278.3	277.4
45°	269.3	268.6	268.0	267.3	266.6	265.6	264.2	262.8	261.4	259.9	258.8
47.5°	250.2	249.5	248.9	248.3	247.6	246.6	245.1	243.6	242.1	240.6	239.5
50°	236.8	236.3	235.8	235.4	234.9	233.9	232.6	231.3	230.0	228.7	227.3
52.5°	223.8	223.1	222.5	221.9	221.2	220.3	219.0	217.8	216.5	215.3	214.1
55°	203.8	203.2	202.6	202.1	201.5	200.7	199.5	198.4	197.3	196.1	194.9
57.5°	183.8	183.3	182.9	182.4	181.9	181.1	179.8	178.6	177.3	176.1	174.9
60°	170.4	170.0	169.7	169.3	168.9	168.1	166.7	165.4	164.0	162.7	161.6
62.5°	157.4	156.7	156.2	155.6	155.0	154.1	153.1	152.1	151.1	150.1	149.0
65°	137.4	136.9	136.3	135.7	135.2	134.4	133.5	132.5	131.6	130.6	129.7
67.5°	117.2	116.7	116.2	115.7	115.4	114.7	113.8	112.9	112.1	111.2	110.6
70°	104.4	104.1	103.7	103.3	102.9	102.4	101.5	100.7	99.7	98.9	98.2
72.5°	91.4	91.0	90.7	90.3	89.9	89.4	88.9	88.4	87.8	87.3	86.6
75°	71.9	71.7	71.5	71.4	71.2	70.9	70.4	69.8	69.4	68.9	68.3
77.5°	54.5	54.1	53.8	53.5	53.2	52.9	52.7	52.5	52.3	52.1	51.8
80°	42.8	42.7	42.6	42.5	42.4	42.3	42.1	41.9	41.8	41.6	41.3
82.5°	31.9	31.9	31.9	31.8	31.8	31.7	31.6	31.5	31.4	31.3	30.9
85°	17.5	17.4	17.3	17.2	17.2	17.1	17.0	16.9	16.8	16.7	16.4
87.5°	6.4	6.8	7.3	7.6	8.0	8.4	8.7	8.9	9.1	9.4	9.4
90°	1.1	4.0	6.8	9.6	12.4	14.9	16.9	18.9	21.0	23.1	24.3
92.5°	23.3	23.0	22.8	22.5	22.2	22.6	23.7	24.7	25.7	26.8	27.4
95°	74.9	66.4	58.1	49.6	41.1	37.8	39.6	41.4	43.2	45.0	46.3
97.5°	148.7	124.9	101.0	77.3	53.4	43.5	47.7	51.8	56.1	60.2	61.2
100°	204.1	169.0	133.8	98.8	63.7	48.3	52.7	57.0	61.4	65.7	67.8
102.5°	264.9	257.5	250.1	242.7	235.3	213.3	176.8	140.4	104.0	67.6	70.2
105°	350.5	358.2	365.9	373.5	381.3	350.2	280.2	210.2	140.3	70.3	73.1
107.5°	448.1	454.2	460.4	466.7	472.9	434.0	350.2	266.3	182.4	98.5	95.6
110°	510.8	516.1	521.5	526.9	532.3	497.9	424.0	349.9	275.8	201.8	176.2



TEST NUMBER: P331487-830

CATALOG NUMBER: S122DIW-S290D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	569.8	574.6	579.3	584.1	588.9	582.1	563.8	545.5	527.3	508.9	415.5
115°	663.0	667.3	671.7	676.0	680.4	685.8	692.2	698.6	705.0	711.4	592.8
117.5°	746.2	751.1	755.9	760.8	765.7	770.3	774.7	779.1	783.5	788.0	759.2
120°	807.1	811.0	814.7	818.6	822.5	826.7	831.3	835.9	840.6	845.1	848.2
122.5°	858.8	862.8	866.9	870.9	875.0	879.5	884.5	889.5	894.6	899.6	901.4
125°	937.4	940.7	944.1	947.3	950.6	954.8	959.7	964.5	969.4	974.3	976.1
127.5°	1008.6	1012.3	1016.0	1019.7	1023.4	1027.1	1030.7	1034.3	1037.9	1041.6	1044.2
130°	1053.9	1057.9	1062.1	1066.1	1070.3	1073.7	1076.5	1079.3	1082.1	1085.0	1087.8
132.5°	1099.9	1103.4	1106.9	1110.4	1113.9	1117.0	1119.8	1122.7	1125.5	1128.3	1130.7
135°	1159.9	1163.9	1168.1	1172.1	1176.3	1179.5	1181.8	1184.1	1186.4	1188.7	1191.3
137.5°	1220.5	1223.4	1226.2	1229.2	1232.0	1234.7	1237.4	1240.0	1242.6	1245.2	1247.7
140°	1260.2	1262.3	1264.3	1266.3	1268.4	1270.8	1273.7	1276.5	1279.3	1282.1	1284.4
142.5°	1293.5	1295.2	1297.1	1298.9	1300.8	1303.3	1306.6	1309.8	1313.0	1316.3	1318.3
145°	1345.5	1345.3	1345.0	1344.7	1344.5	1346.5	1350.9	1355.3	1359.6	1364.0	1365.7
147.5°	1390.9	1390.0	1389.0	1388.0	1387.0	1388.7	1393.0	1397.3	1401.7	1405.9	1407.3
150°	1420.5	1418.7	1416.9	1415.0	1413.2	1414.5	1418.5	1422.7	1426.7	1430.9	1432.4
152.5°	1445.4	1443.4	1441.3	1439.4	1437.4	1438.3	1442.2	1446.1	1450.0	1453.9	1455.5
155°	1481.6	1479.2	1477.0	1474.6	1472.3	1472.7	1475.8	1478.8	1482.0	1485.1	1486.6
157.5°	1510.0	1508.0	1506.0	1504.1	1502.1	1502.2	1504.4	1506.6	1508.7	1510.9	1512.6
160°	1526.5	1525.0	1523.4	1521.9	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5	1528.0
162.5°	1541.3	1539.7	1538.2	1536.7	1535.1	1535.0	1536.3	1537.7	1539.1	1540.4	1542.1
165°	1561.1	1559.6	1558.0	1556.5	1555.0	1554.6	1555.4	1556.1	1556.9	1557.6	1559.4
167.5°	1575.9	1574.3	1572.8	1571.3	1569.7	1569.3	1570.1	1570.7	1571.5	1572.2	1574.0
170°	1584.2	1582.6	1581.1	1579.6	1578.0	1577.5	1578.0	1578.6	1579.0	1579.6	1581.4
172.5°	1589.7	1588.2	1586.7	1585.1	1583.6	1583.1	1583.6	1584.0	1584.6	1585.1	1586.9
175°	1596.9	1595.1	1593.3	1591.5	1589.7	1589.0	1589.6	1590.1	1590.6	1591.1	1592.9
177.5°	1598.0	1596.6	1595.2	1593.7	1592.2	1591.7	1591.9	1592.0	1592.2	1592.5	1593.9
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331487-830

CATALOG NUMBER: S122DIW-S290D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	443.4	444.1	444.9	445.3	445.1	444.9	444.8	444.6
5°	440.5	441.2	442.0	442.2	442.1	441.9	441.7	441.5
7.5°	435.5	436.2	437.0	437.2	437.1	436.8	436.6	436.4
10°	431.0	431.8	432.5	432.7	432.4	432.2	431.9	431.6
12.5°	425.7	426.2	426.8	427.0	426.8	426.5	426.3	426.1
15°	416.5	416.9	417.3	417.3	416.8	416.3	415.8	415.4
17.5°	405.6	406.0	406.4	406.4	406.0	405.6	405.1	404.6
20°	397.1	397.4	397.7	397.6	397.2	396.8	396.4	396.1
22.5°	388.0	388.1	388.1	388.0	387.9	387.6	387.4	387.2
25°	373.3	373.5	373.7	373.7	373.5	373.3	373.2	373.0
27.5°	358.8	358.5	358.3	357.9	357.4	356.9	356.6	356.1
30°	347.5	347.2	346.9	346.7	346.3	345.9	345.5	345.1
32.5°	336.5	335.9	335.5	335.0	334.6	334.2	333.8	333.5
35°	318.7	318.1	317.5	317.1	316.6	316.1	315.7	315.1
37.5°	300.9	300.2	299.4	298.9	298.4	297.9	297.6	297.1
40°	288.6	287.8	286.9	286.3	285.9	285.5	285.1	284.7
42.5°	276.4	275.5	274.6	273.8	273.3	272.8	272.3	271.7
45°	257.8	256.7	255.7	255.0	254.6	254.2	253.8	253.4
47.5°	238.5	237.3	236.2	235.4	234.9	234.3	233.8	233.2
50°	226.0	224.6	223.3	222.4	222.0	221.5	221.0	220.6
52.5°	213.1	212.0	210.8	210.0	209.3	208.8	208.1	207.5
55°	193.8	192.7	191.5	190.8	190.3	189.7	189.3	188.8
57.5°	173.8	172.7	171.5	170.8	170.5	170.1	169.8	169.4
60°	160.6	159.6	158.5	157.9	157.6	157.3	157.0	156.7
62.5°	148.1	147.1	146.2	145.5	145.2	144.8	144.4	144.0
65°	128.8	128.0	127.1	126.5	126.0	125.5	125.1	124.6
67.5°	109.9	109.2	108.6	108.0	107.6	107.3	106.9	106.5
70°	97.6	96.9	96.2	95.8	95.4	94.9	94.5	94.2
72.5°	86.0	85.3	84.6	84.1	83.8	83.5	83.2	82.8
75°	67.8	67.2	66.6	66.4	66.6	66.8	67.0	67.2
77.5°	51.6	51.3	51.0	50.7	50.4	50.2	50.0	49.7
80°	41.0	40.7	40.4	40.2	40.0	39.8	39.6	39.4
82.5°	30.5	30.2	29.8	29.6	29.6	29.5	29.5	29.5
85°	16.1	15.8	15.6	15.4	15.3	15.2	15.1	15.0
87.5°	9.4	9.5	9.5	9.5	9.6	9.6	9.6	9.6
90°	25.6	26.9	28.2	29.1	29.6	30.1	30.6	31.1
92.5°	28.1	28.7	29.4	29.9	30.2	30.5	30.8	31.1
95°	47.5	48.8	50.0	50.6	50.3	50.0	49.9	49.6
97.5°	62.2	63.2	64.3	64.9	65.2	65.6	65.9	66.2
100°	69.8	71.8	73.9	75.2	75.7	76.3	76.7	77.3
102.5°	72.9	75.6	78.2	79.9	80.6	81.3	82.1	82.8
105°	76.0	78.8	81.6	83.5	84.5	85.6	86.6	87.7
107.5°	92.7	89.8	87.0	86.1	87.1	88.1	89.2	90.2
110°	150.5	124.9	99.2	87.0	88.0	89.1	90.1	91.0



TEST NUMBER: P331487-830

CATALOG NUMBER: S122DIW-S290D1240U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	322.0	228.6	135.1	88.7	89.5	90.4	91.1	92.0
115°	474.1	355.5	236.9	168.3	149.9	131.5	113.0	94.5
117.5°	730.6	701.8	673.2	628.5	567.9	507.3	446.7	386.0
120°	851.3	854.3	857.4	841.7	807.1	772.5	737.9	703.3
122.5°	903.2	905.1	906.9	904.5	897.8	891.1	884.4	877.6
125°	977.9	979.7	981.5	982.7	983.4	984.3	985.1	985.8
127.5°	1046.8	1049.4	1052.1	1053.5	1053.6	1053.8	1053.9	1054.0
130°	1090.6	1093.4	1096.2	1097.5	1097.2	1097.0	1096.7	1096.5
132.5°	1133.1	1135.5	1137.9	1139.0	1138.8	1138.5	1138.2	1138.0
135°	1193.8	1196.4	1199.0	1200.0	1199.5	1199.0	1198.4	1198.0
137.5°	1250.2	1252.7	1255.3	1256.0	1255.2	1254.3	1253.5	1252.5
140°	1286.8	1289.0	1291.4	1291.8	1290.5	1289.3	1288.0	1286.8
142.5°	1320.4	1322.6	1324.6	1325.0	1323.8	1322.5	1321.2	1319.9
145°	1367.5	1369.3	1371.1	1371.4	1370.1	1368.9	1367.5	1366.3
147.5°	1408.6	1409.9	1411.3	1411.4	1410.3	1409.2	1408.2	1407.1
150°	1433.9	1435.5	1437.0	1437.1	1435.9	1434.5	1433.2	1432.0
152.5°	1457.0	1458.5	1460.1	1460.0	1458.3	1456.6	1454.9	1453.2
155°	1488.1	1489.7	1491.2	1490.9	1488.8	1486.9	1484.8	1482.7
157.5°	1514.4	1516.1	1517.9	1517.7	1515.7	1513.7	1511.7	1509.7
160°	1529.7	1531.2	1532.7	1532.6	1530.8	1529.0	1527.2	1525.4
162.5°	1543.9	1545.6	1547.4	1547.1	1544.9	1542.7	1540.5	1538.3
165°	1561.2	1563.0	1564.8	1564.8	1563.0	1561.2	1559.4	1557.6
167.5°	1575.7	1577.5	1579.3	1579.1	1576.8	1574.5	1572.2	1569.9
170°	1583.2	1585.0	1586.8	1586.5	1584.2	1581.9	1579.6	1577.3
172.5°	1588.7	1590.4	1592.2	1592.0	1589.7	1587.4	1585.1	1582.8
175°	1594.7	1596.5	1598.3	1597.9	1595.3	1592.8	1590.2	1587.6
177.5°	1595.3	1596.8	1598.3	1598.0	1596.2	1594.3	1592.5	1590.6
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4

(END OF REPORT)