

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645005

Luminaire Tested: OMN4DIP-SR4F0-50D75U930-BBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P645005
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-23)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-50D75U930-BBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - BLACK BAFFLE WITH MEDIUM OPTIC - 500 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4475.8 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.21 / 1.18
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 39
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P645005

CATALOG NUMBER: OMN4DIP-SR4F0-50D75U930-BBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P645005

CATALOG NUMBER: OMN4DIP-SR4F0-50D75U930-BBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43				43
1	98	94	91	88	90	87	84	82	72	70	69	59	58	57	47	46	46	40				40
2	91	85	79	75	83	78	74	70	65	62	60	54	52	50	43	42	41	36				36
3	84	76	70	65	77	70	65	61	59	56	53	49	47	45	40	39	37	33				33
4	78	68	62	56	71	63	58	53	54	50	46	45	42	40	37	35	34	30				30
5	72	62	55	50	66	58	51	47	49	45	41	42	38	36	34	32	31	27				27
6	67	56	49	44	62	52	46	42	45	40	37	38	35	32	32	30	28	25				25
7	62	51	44	39	57	48	42	37	41	37	33	35	32	29	30	27	25	23				23
8	58	47	40	35	54	44	38	34	38	33	30	33	29	27	28	25	23	21				21
9	54	43	36	32	50	41	34	30	35	31	27	30	27	24	26	23	21	19				19
10	51	40	33	29	47	37	32	28	33	28	25	28	25	22	24	22	20	18				18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16336	16336	16336
5°	16117	16462	16718
10°	16394	16808	16989
15°	16847	17097	17123
20°	16922	17113	16827
25°	16534	16716	16350
30°	15653	15829	15373
35°	14229	14229	13933
40°	11704	11586	11336
45°	6998	8224	6673
50°	2261	4584	2122
55°	799	1534	799
60°	52	434	26
65°	31	31	0
70°	38	0	0
75°	0	0	0
80°	0	0	0
85°	148	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 8224 cd/sqm



TEST NUMBER: P645005

CATALOG NUMBER: OMN4DIP-SR4F0-50D75U930-BBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.7	2.7
10°-20°	360.0	8.0
20°-30°	532.8	11.9
30°-40°	550.7	12.3
40°-50°	320.4	7.2
50°-60°	54.3	1.2
60°-70°	2.1	0.0
70°-80°	0.3	0.0
80°-90°	1.4	0.0
90°-100°	57.9	1.3
100°-110°	413.0	9.2
110°-120°	560.7	12.5
120°-130°	456.3	10.2
130°-140°	367.0	8.2
140°-150°	289.3	6.5
150°-160°	211.6	4.7
160°-170°	131.4	2.9
170°-180°	44.8	1.0
0°-30°	1014.5	22.7
0°-40°	1565.2	35.0
0°-60°	1939.9	43.3
0°-90°	1943.7	43.4
90°-120°	1031.6	23.0
90°-150°	2144.3	47.9
90°-180°	2532.0	56.6
0°-180°	4475.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1265	1265	1265	1265	1265	
5°	1243	1276	1270	1273	1289	119
15°	1260	1304	1278	1272	1280	354
25°	1160	1199	1173	1138	1147	530
35°	902	917	902	880	884	553
45°	383	446	450	435	365	296
55°	36	41	68	38	36	39
65°	1	1	1	0	0	1
75°	0	1	0	0	0	0
85°	1	1	0	0	0	0
90°	0	3	6	9	9	1
95°	24	44	24	27	33	27
105°	92	141	537	686	454	97
115°	163	198	462	961	1124	162
125°	234	266	436	762	901	208
135°	290	322	439	628	720	224
145°	344	373	442	547	605	216
155°	403	418	451	496	519	185
165°	448	454	462	474	483	126
175°	471	474	471	468	465	45
180°	471	471	471	471	471	



TEST NUMBER: P645005

CATALOG NUMBER: OMN4DIP-SR4F0-50D75U930-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1264.7	1264.7	1264.7	1264.7	1264.7
2.5°	1248.1	1272.8	1263.9	1264.8	1271.0
5°	1243.0	1275.8	1269.6	1273.0	1289.4
7.5°	1246.7	1279.9	1279.1	1280.1	1296.1
10°	1249.9	1284.6	1281.5	1280.8	1295.3
12.5°	1256.2	1294.1	1281.5	1280.0	1292.1
15°	1259.8	1304.2	1278.5	1271.8	1280.5
17.5°	1247.7	1297.1	1262.3	1244.4	1247.9
20°	1231.1	1281.3	1245.0	1218.4	1224.2
22.5°	1205.1	1253.0	1220.5	1187.7	1195.0
25°	1160.1	1198.7	1172.9	1137.6	1147.2
27.5°	1096.1	1126.6	1110.3	1076.1	1082.1
30°	1049.5	1074.6	1061.3	1027.8	1030.7
32.5°	995.8	1017.0	1002.9	974.0	973.9
35°	902.4	916.9	902.4	879.8	883.6
37.5°	780.1	791.2	776.4	762.8	764.7
40°	694.1	702.7	687.1	674.3	672.3
42.5°	586.6	610.8	595.5	578.0	580.7
45°	383.1	445.8	450.2	434.8	365.3
47.5°	193.1	261.7	313.4	237.8	170.4
50°	112.5	154.1	228.1	125.9	105.6
52.5°	73.8	91.4	159.3	79.6	70.1
55°	35.5	41.3	68.1	38.4	35.5
57.5°	12.2	18.8	30.2	19.2	13.6
60°	2.0	7.8	16.8	5.8	1.0
62.5°	1.2	2.3	10.5	1.2	0.2
65°	1.0	1.0	1.0	0.0	0.0
67.5°	1.0	1.0	0.0	0.0	0.0
70°	1.0	1.0	0.0	0.0	0.0
72.5°	1.0	1.0	0.0	0.0	0.0
75°	0.0	1.0	0.0	0.0	0.0
77.5°	0.0	1.0	0.0	0.0	0.0
80°	0.0	1.0	0.0	0.0	0.0
82.5°	0.0	1.0	0.0	0.0	0.0
85°	1.0	1.0	0.0	0.0	0.0
87.5°	0.8	1.4	1.2	1.8	1.8
90°	0.0	2.9	5.9	8.9	8.9
92.5°	7.1	10.0	13.0	18.4	20.8
95°	23.7	44.0	23.7	26.8	32.6
97.5°	42.1	84.4	174.3	51.4	44.5
100°	56.3	105.6	349.8	103.0	68.2
102.5°	70.6	122.2	473.2	271.7	148.8
105°	91.9	141.2	536.6	685.5	453.6
107.5°	113.2	150.4	512.3	997.6	934.5
110°	127.5	162.3	498.1	1048.3	1126.6



TEST NUMBER: P645005

CATALOG NUMBER: OMN4DIP-SR4F0-50D75U930-BBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.7	176.5	483.8	1018.7	1150.3
115°	163.1	197.8	462.5	961.3	1123.6
117.5°	185.0	219.2	457.1	899.1	1066.1
120°	201.6	233.5	447.7	851.8	1025.8
122.5°	213.5	247.7	435.8	811.2	971.2
125°	234.2	266.1	435.8	762.1	901.2
127.5°	251.4	283.9	436.4	705.1	842.5
130°	260.9	295.7	438.8	667.0	797.5
132.5°	272.7	307.5	438.8	649.9	757.2
135°	290.5	322.4	438.8	627.6	720.4
137.5°	305.4	339.6	438.8	603.0	682.5
140°	317.2	349.1	438.8	588.6	661.1
142.5°	329.1	358.6	441.1	571.9	639.8
145°	343.9	372.9	441.7	546.8	604.8
147.5°	361.7	387.2	445.3	528.7	573.4
150°	373.5	396.7	447.7	516.7	554.4
152.5°	385.4	406.3	447.7	507.1	537.8
155°	403.2	417.7	450.6	495.6	518.8
157.5°	417.4	431.3	454.2	488.4	505.2
160°	426.9	438.5	456.6	483.6	498.1
162.5°	434.0	445.6	458.9	481.1	490.9
165°	447.7	453.5	462.5	474.5	483.2
167.5°	455.4	460.6	465.4	471.5	476.7
170°	462.5	465.4	465.4	471.4	474.3
172.5°	464.9	470.1	467.8	469.1	472.0
175°	471.4	474.3	471.4	468.3	465.4
177.5°	471.4	473.7	471.4	471.3	469.0
180°	471.4	471.4	471.4	471.4	471.4

(END OF REPORT)