

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331470-830

Luminaire Tested: **S122DIW-S290D435U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331470-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D435U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2549.9 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331470-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331470-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	37
2	88	81	74	69	80	74	69	64	62	58	54	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	31	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7190	7190	7190
5°	7217	7112	7156
10°	7174	7040	7076
15°	7086	6950	6944
20°	6959	6813	6806
25°	6834	6645	6645
30°	6674	6490	6434
35°	6524	6303	6211
40°	6336	6119	6001
45°	6149	5934	5786
50°	5948	5745	5541
55°	5737	5520	5315
60°	5503	5254	5060
65°	5249	4989	4760
70°	4928	4669	4447
75°	4485	4298	4192
80°	3980	3868	3663
85°	3242	3094	2779



TEST NUMBER: P331470-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	1.6
10°-20°	117.8	4.6
20°-30°	173.2	6.8
30°-40°	201.2	7.9
40°-50°	200.9	7.9
50°-60°	175.2	6.9
60°-70°	129.6	5.1
70°-80°	73.4	2.9
80°-90°	21.8	0.9
90°-100°	32.1	1.3
100°-110°	99.6	3.9
110°-120°	170.2	6.7
120°-130°	223.9	8.8
130°-140°	251.3	9.9
140°-150°	246.4	9.7
150°-160°	206.6	8.1
160°-170°	137.1	5.4
170°-180°	47.9	1.9
0°-30°	332.9	13.1
0°-40°	534.0	20.9
0°-60°	910.2	35.7
0°-90°	1134.9	44.5
90°-120°	301.9	11.8
90°-150°	1023.3	40.1
90°-180°	1415.0	55.5
0°-180°	2549.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	445	445	445	445	445	
5°	445	443	439	442	442	42
15°	424	421	416	417	415	119
25°	384	380	373	374	373	176
35°	331	327	320	317	315	207
45°	269	266	260	255	253	208
55°	204	201	196	191	189	182
65°	137	135	131	127	125	136
75°	72	71	69	66	67	77
85°	18	17	17	16	15	20
90°	0	6	15	14	14	2
95°	22	26	27	27	26	25
105°	92	93	94	95	95	97
115°	171	173	172	172	171	169
125°	248	252	251	250	249	222
135°	322	326	327	327	325	248
145°	390	393	396	396	394	244
155°	446	448	449	451	450	205
165°	486	485	485	488	486	137
175°	505	504	503	506	504	48
180°	506	506	506	506	506	



TEST NUMBER: P331470-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	447.3	447.0	446.6	446.2	445.8	445.3	444.4	443.6	442.7	441.9	442.6
5°	445.3	444.9	444.5	444.1	443.7	443.1	442.1	441.0	439.9	438.8	439.6
7.5°	441.4	440.7	440.2	439.6	439.0	438.2	437.2	436.0	435.0	433.9	434.7
10°	437.6	437.0	436.3	435.6	434.9	434.0	432.9	431.8	430.6	429.4	430.2
12.5°	432.4	431.9	431.3	430.6	430.1	429.2	428.1	427.0	425.8	424.7	425.2
15°	423.9	423.3	422.7	422.2	421.6	420.8	419.4	418.2	417.0	415.8	416.1
17.5°	412.9	412.4	411.8	411.2	410.7	409.7	408.5	407.2	406.0	404.7	405.1
20°	405.0	404.4	403.9	403.3	402.7	401.8	400.5	399.2	397.8	396.5	396.8
22.5°	397.2	396.3	395.6	394.7	394.0	392.9	391.7	390.4	389.2	388.0	388.0
25°	383.6	382.9	382.1	381.4	380.6	379.4	377.8	376.2	374.6	373.0	373.2
27.5°	368.3	367.6	366.8	366.2	365.5	364.5	363.3	361.9	360.7	359.4	359.1
30°	358.0	357.2	356.5	355.7	354.9	353.8	352.4	351.0	349.5	348.1	347.8
32.5°	346.9	346.4	345.8	345.2	344.6	343.5	342.0	340.5	339.0	337.5	337.0
35°	331.0	330.0	329.0	328.1	327.2	325.9	324.4	322.9	321.4	319.8	319.2
37.5°	312.9	312.1	311.2	310.4	309.5	308.4	306.9	305.4	303.8	302.3	301.6
40°	300.6	299.8	299.1	298.3	297.6	296.4	294.8	293.3	291.8	290.3	289.5
42.5°	288.6	287.9	287.1	286.3	285.6	284.4	282.9	281.3	279.8	278.3	277.4
45°	269.3	268.6	268.0	267.3	266.6	265.6	264.2	262.8	261.4	259.9	258.8
47.5°	250.2	249.5	248.9	248.3	247.6	246.6	245.1	243.6	242.1	240.6	239.5
50°	236.8	236.3	235.8	235.4	234.9	233.9	232.6	231.3	230.0	228.7	227.3
52.5°	223.8	223.1	222.5	221.9	221.2	220.3	219.0	217.8	216.5	215.3	214.1
55°	203.8	203.2	202.6	202.1	201.5	200.7	199.5	198.4	197.3	196.1	194.9
57.5°	183.8	183.3	182.9	182.4	181.9	181.1	179.8	178.6	177.3	176.1	174.9
60°	170.4	170.0	169.7	169.3	168.9	168.1	166.7	165.4	164.0	162.7	161.6
62.5°	157.4	156.7	156.2	155.6	155.0	154.1	153.1	152.1	151.1	150.1	149.0
65°	137.4	136.9	136.3	135.7	135.2	134.4	133.5	132.5	131.6	130.6	129.7
67.5°	117.2	116.7	116.2	115.7	115.4	114.7	113.8	112.9	112.1	111.2	110.6
70°	104.4	104.1	103.7	103.3	102.9	102.4	101.5	100.7	99.7	98.9	98.2
72.5°	91.4	91.0	90.7	90.3	89.9	89.4	88.9	88.4	87.8	87.3	86.6
75°	71.9	71.7	71.5	71.4	71.2	70.9	70.4	69.8	69.4	68.9	68.3
77.5°	54.5	54.1	53.8	53.5	53.2	52.9	52.7	52.5	52.3	52.1	51.8
80°	42.8	42.7	42.6	42.5	42.4	42.3	42.1	41.9	41.8	41.6	41.3
82.5°	31.9	31.9	31.9	31.8	31.8	31.7	31.6	31.5	31.4	31.3	30.9
85°	17.5	17.4	17.3	17.2	17.2	17.1	17.0	16.9	16.8	16.7	16.4
87.5°	6.2	6.3	6.4	6.5	6.6	6.7	7.0	7.3	7.5	7.8	7.5
90°	0.5	1.6	2.7	3.9	5.0	6.6	8.7	10.7	12.8	15.0	14.8
92.5°	7.6	8.5	9.2	10.1	10.9	11.6	12.1	12.6	13.1	13.6	13.6
95°	22.2	23.2	24.1	25.1	26.0	26.6	26.8	27.0	27.1	27.3	27.3
97.5°	40.5	41.4	42.2	43.1	43.9	44.5	44.9	45.2	45.6	45.9	45.9
100°	54.2	55.0	55.7	56.6	57.3	57.8	58.1	58.3	58.6	58.9	58.9
102.5°	68.6	69.2	69.7	70.4	71.0	71.5	71.8	72.2	72.6	73.0	73.0
105°	91.8	92.1	92.4	92.7	92.9	93.2	93.4	93.6	93.8	94.0	94.2
107.5°	115.2	115.6	116.0	116.5	116.9	117.1	117.1	117.1	117.1	117.1	117.2
110°	130.3	130.8	131.4	132.0	132.5	132.8	132.8	132.8	132.8	132.8	132.8



TEST NUMBER: P331470-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.7	147.2	147.8	148.4	148.9	149.2	149.1	149.0	148.9	148.8	148.6
115°	170.8	171.4	171.9	172.5	173.1	173.2	173.1	172.9	172.7	172.5	172.4
117.5°	194.9	195.7	196.4	197.2	197.9	198.0	197.6	197.0	196.4	196.0	195.7
120°	210.9	211.7	212.4	213.2	214.0	214.0	213.2	212.4	211.7	210.9	210.9
122.5°	225.6	226.6	227.4	228.4	229.3	229.5	228.9	228.4	227.9	227.3	227.2
125°	248.5	249.4	250.2	251.1	251.9	252.2	251.9	251.7	251.4	251.1	250.8
127.5°	270.8	271.9	273.0	274.1	275.1	275.5	275.2	274.8	274.5	274.2	273.8
130°	284.8	286.1	287.3	288.5	289.7	290.3	290.1	289.9	289.7	289.5	289.4
132.5°	300.6	301.5	302.6	303.6	304.5	305.1	305.1	305.2	305.2	305.2	304.8
135°	321.6	322.6	323.7	324.7	325.7	326.3	326.5	326.7	326.9	327.1	327.0
137.5°	343.7	344.5	345.3	346.2	347.0	347.6	347.9	348.2	348.4	348.6	348.6
140°	357.0	357.9	358.7	359.6	360.4	361.1	361.6	362.0	362.5	363.0	363.0
142.5°	370.7	371.6	372.4	373.2	374.1	374.7	374.9	375.3	375.6	376.0	376.1
145°	390.3	391.0	391.6	392.3	392.9	393.6	394.2	394.7	395.3	395.9	396.0
147.5°	407.8	408.6	409.4	410.2	411.0	411.6	412.0	412.4	412.7	413.1	413.3
150°	419.8	420.4	420.9	421.5	422.1	422.5	422.9	423.3	423.7	424.0	424.3
152.5°	430.4	430.9	431.5	432.1	432.6	433.2	433.6	434.0	434.5	435.0	435.4
155°	446.2	446.5	446.8	447.1	447.4	447.7	448.0	448.3	448.6	448.8	449.3
157.5°	459.9	460.1	460.2	460.4	460.6	460.7	460.9	461.1	461.3	461.5	462.1
160°	468.1	468.3	468.4	468.6	468.8	468.9	469.0	469.1	469.2	469.3	469.9
162.5°	475.5	475.6	475.6	475.6	475.7	475.8	475.9	476.0	476.1	476.2	476.7
165°	485.5	485.4	485.3	485.2	485.1	485.1	485.1	485.1	485.1	485.1	485.8
167.5°	493.9	493.6	493.3	493.0	492.8	492.6	492.6	492.6	492.6	492.6	493.2
170°	498.3	498.0	497.8	497.5	497.2	497.0	496.9	496.8	496.7	496.6	497.3
172.5°	501.4	501.1	500.9	500.6	500.3	500.1	500.0	499.9	499.8	499.7	500.4
175°	505.2	504.9	504.6	504.4	504.1	503.8	503.6	503.4	503.2	503.0	503.7
177.5°	506.7	506.5	506.2	506.1	505.8	505.6	505.5	505.3	505.1	505.0	505.5
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1



TEST NUMBER: P331470-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	445.3	445.3	445.3	445.3	445.3	445.3	445.3	445.3
2.5°	443.4	444.1	444.9	445.3	445.1	444.9	444.8	444.6
5°	440.5	441.2	442.0	442.2	442.1	441.9	441.7	441.5
7.5°	435.5	436.2	437.0	437.2	437.1	436.8	436.6	436.4
10°	431.0	431.8	432.5	432.7	432.4	432.2	431.9	431.6
12.5°	425.7	426.2	426.8	427.0	426.8	426.5	426.3	426.1
15°	416.5	416.9	417.3	417.3	416.8	416.3	415.8	415.4
17.5°	405.6	406.0	406.4	406.4	406.0	405.6	405.1	404.6
20°	397.1	397.4	397.7	397.6	397.2	396.8	396.4	396.1
22.5°	388.0	388.1	388.1	388.0	387.9	387.6	387.4	387.2
25°	373.3	373.5	373.7	373.7	373.5	373.3	373.2	373.0
27.5°	358.8	358.5	358.3	357.9	357.4	356.9	356.6	356.1
30°	347.5	347.2	346.9	346.7	346.3	345.9	345.5	345.1
32.5°	336.5	335.9	335.5	335.0	334.6	334.2	333.8	333.5
35°	318.7	318.1	317.5	317.1	316.6	316.1	315.7	315.1
37.5°	300.9	300.2	299.4	298.9	298.4	297.9	297.6	297.1
40°	288.6	287.8	286.9	286.3	285.9	285.5	285.1	284.7
42.5°	276.4	275.5	274.6	273.8	273.3	272.8	272.3	271.7
45°	257.8	256.7	255.7	255.0	254.6	254.2	253.8	253.4
47.5°	238.5	237.3	236.2	235.4	234.9	234.3	233.8	233.2
50°	226.0	224.6	223.3	222.4	222.0	221.5	221.0	220.6
52.5°	213.1	212.0	210.8	210.0	209.3	208.8	208.1	207.5
55°	193.8	192.7	191.5	190.8	190.3	189.7	189.3	188.8
57.5°	173.8	172.7	171.5	170.8	170.5	170.1	169.8	169.4
60°	160.6	159.6	158.5	157.9	157.6	157.3	157.0	156.7
62.5°	148.1	147.1	146.2	145.5	145.2	144.8	144.4	144.0
65°	128.8	128.0	127.1	126.5	126.0	125.5	125.1	124.6
67.5°	109.9	109.2	108.6	108.0	107.6	107.3	106.9	106.5
70°	97.6	96.9	96.2	95.8	95.4	94.9	94.5	94.2
72.5°	86.0	85.3	84.6	84.1	83.8	83.5	83.2	82.8
75°	67.8	67.2	66.6	66.4	66.6	66.8	67.0	67.2
77.5°	51.6	51.3	51.0	50.7	50.4	50.2	50.0	49.7
80°	41.0	40.7	40.4	40.2	40.0	39.8	39.6	39.4
82.5°	30.5	30.2	29.8	29.6	29.6	29.5	29.5	29.5
85°	16.1	15.8	15.6	15.4	15.3	15.2	15.1	15.0
87.5°	7.3	7.0	6.7	6.6	6.5	6.4	6.4	6.3
90°	14.6	14.4	14.2	14.1	14.2	14.3	14.4	14.5
92.5°	13.7	13.7	13.8	13.8	13.8	13.8	13.9	13.9
95°	27.3	27.3	27.3	27.2	27.1	26.9	26.7	26.5
97.5°	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9
100°	58.9	58.9	58.9	58.9	58.8	58.7	58.6	58.5
102.5°	73.0	73.1	73.2	73.2	73.1	73.0	73.0	72.9
105°	94.3	94.5	94.7	94.8	94.8	94.8	94.8	94.8
107.5°	117.3	117.3	117.4	117.3	116.8	116.3	115.9	115.5
110°	132.8	132.8	132.8	132.6	132.3	132.1	131.8	131.5



TEST NUMBER: P331470-830

CATALOG NUMBER: S122DIW-S290D435U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	148.5	148.2	148.0	147.7	147.5	147.3	147.1	146.9
115°	172.3	172.2	172.1	171.9	171.6	171.4	171.1	170.8
117.5°	195.5	195.2	195.0	194.7	194.4	194.2	193.9	193.6
120°	210.9	210.9	210.9	210.8	210.6	210.3	210.0	209.7
122.5°	226.9	226.7	226.4	226.2	226.0	225.8	225.6	225.4
125°	250.5	250.2	250.0	249.8	249.7	249.6	249.5	249.4
127.5°	273.4	273.1	272.8	272.5	272.1	271.8	271.5	271.3
130°	289.2	289.0	288.8	288.5	288.1	287.8	287.4	287.0
132.5°	304.4	304.0	303.6	303.2	302.9	302.6	302.3	302.0
135°	326.9	326.8	326.7	326.5	326.2	325.9	325.6	325.4
137.5°	348.5	348.4	348.4	348.1	347.7	347.3	346.9	346.6
140°	363.0	363.0	363.0	362.8	362.4	362.0	361.7	361.3
142.5°	376.1	376.2	376.3	376.1	375.7	375.3	374.9	374.6
145°	396.1	396.2	396.2	396.1	395.7	395.3	394.9	394.5
147.5°	413.5	413.8	414.0	413.9	413.5	413.1	412.7	412.5
150°	424.6	424.9	425.2	425.2	424.9	424.6	424.3	424.0
152.5°	435.6	436.0	436.4	436.4	436.0	435.6	435.4	435.0
155°	449.8	450.3	450.7	450.8	450.5	450.3	450.0	449.7
157.5°	462.7	463.4	464.0	464.1	463.6	463.2	462.8	462.3
160°	470.4	471.0	471.6	471.6	471.3	470.9	470.5	470.1
162.5°	477.4	478.1	478.7	478.8	478.3	477.9	477.4	477.0
165°	486.4	487.1	487.8	487.9	487.4	486.9	486.4	486.0
167.5°	493.9	494.6	495.2	495.3	494.7	494.3	493.8	493.3
170°	497.9	498.6	499.3	499.4	498.8	498.2	497.7	497.1
172.5°	501.1	501.7	502.4	502.4	501.8	501.2	500.7	500.1
175°	504.4	505.0	505.7	505.8	505.2	504.6	504.1	503.5
177.5°	506.0	506.3	506.8	506.8	506.3	506.0	505.5	505.0
180°	506.1	506.1	506.1	506.1	506.1	506.1	506.1	506.1

(END OF REPORT)