

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645160

Luminaire Tested: OMN4DIP-SR4F0-75D50U930-WBMOOB-1DUDD-WW

Issue Date: 9/2/2020



Test Information

Test Method: LM-79-2019
Report Number: P645160
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-27)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DIP-SR4F0-75D50U930-WBMOOB-1DUDD-WW
Description: NEO-RAY CIRQUE 4-INCH DIAMETER LINEAR LED LUMINAIRE
DOWNLIGHT - WHITE BAFFLE WITH MEDIUM OPTIC - 750 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4799.7 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.21 / 1.19
Luminous Opening: Rectangular (W 0.21' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 42.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P645160
CATALOG NUMBER: OMN4DIP-SR4F0-75D50U930-WBMOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P645160

CATALOG NUMBER: OMN4DIP-SR4F0-75D50U930-WBMOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20				20				20	
RC	80									50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																			
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65	
1	104	100	97	94	97	94	92	89	84	82	80	75	73	72	66	65	64	60	
2	96	90	85	81	91	86	81	77	77	73	71	68	66	64	61	59	58	54	
3	90	82	76	71	85	78	72	68	70	66	62	63	60	57	56	54	52	49	
4	83	74	67	62	79	71	65	60	64	59	56	58	54	51	52	49	47	44	
5	78	68	60	55	73	64	58	53	59	54	50	53	49	46	48	45	43	40	
6	72	62	55	49	68	59	53	48	54	49	45	49	45	42	45	42	39	37	
7	68	57	50	45	64	54	48	43	50	44	41	46	41	38	42	38	36	33	
8	63	52	45	40	60	50	44	39	46	41	37	42	38	35	39	35	33	31	
9	59	48	41	37	56	46	40	36	43	37	34	39	35	32	36	33	30	28	
10	56	45	38	34	53	43	37	33	40	35	31	37	32	29	34	30	28	26	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25220	25220	25220
5°	25030	25373	25869
10°	25435	25937	26360
15°	26069	26424	26600
20°	26212	26454	26151
25°	25711	25773	25458
30°	24581	24516	23924
35°	22442	22256	21792
40°	18642	18369	18023
45°	11709	13320	11172
50°	4491	7889	4166
55°	2119	3310	2153
60°	1026	1671	912
65°	944	987	853
70°	944	944	835
75°	953	953	808
80°	982	878	766
85°	1097	874	652

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 13320 cd/sqm



TEST NUMBER: P645160

CATALOG NUMBER: OMN4DIP-SR4F0-75D50U930-WBMOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.1	3.9
10°-20°	556.2	11.6
20°-30°	826.3	17.2
30°-40°	864.8	18.0
40°-50°	523.8	10.9
50°-60°	120.9	2.5
60°-70°	33.2	0.7
70°-80°	19.4	0.4
80°-90°	7.4	0.2
90°-100°	38.0	0.8
100°-110°	270.7	5.6
110°-120°	367.5	7.7
120°-130°	299.1	6.2
130°-140°	240.5	5.0
140°-150°	189.6	4.0
150°-160°	138.7	2.9
160°-170°	86.1	1.8
170°-180°	29.4	0.6
0°-30°	1570.6	32.7
0°-40°	2435.4	50.7
0°-60°	3080.2	64.2
0°-90°	3140.2	65.4
90°-120°	676.1	14.1
90°-150°	1405.3	29.3
90°-180°	1659.0	34.6
0°-180°	4799.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1952	1952	1952	1952	1952	
5°	1930	1975	1957	1965	1995	185
15°	1950	2008	1976	1960	1989	549
25°	1804	1857	1808	1762	1786	826
35°	1423	1445	1411	1379	1382	875
45°	641	729	729	704	612	492
55°	94	107	147	101	96	98
65°	31	32	32	29	28	31
75°	19	19	19	18	16	20
85°	7	7	6	6	4	7
90°	0	2	4	6	6	1
95°	16	29	16	18	21	17
105°	60	92	352	449	297	63
115°	107	130	303	630	736	106
125°	154	174	286	500	591	136
135°	190	211	288	411	472	146
145°	225	244	290	358	396	142
155°	264	274	295	325	340	121
165°	293	297	303	311	317	82
175°	309	311	309	307	305	29
180°	309	309	309	309	309	



TEST NUMBER: P645160

CATALOG NUMBER: OMN4DIP-SR4F0-75D50U930-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1952.5	1952.5	1952.5	1952.5	1952.5
2.5°	1933.6	1968.1	1948.9	1950.5	1966.6
5°	1930.4	1975.0	1956.9	1964.9	1995.1
7.5°	1935.7	1982.3	1971.6	1974.4	2007.4
10°	1939.2	1988.1	1977.5	1976.7	2009.8
12.5°	1947.5	1998.6	1978.6	1974.4	2006.3
15°	1949.5	2008.5	1976.0	1960.5	1989.2
17.5°	1930.4	1995.4	1951.6	1919.5	1942.5
20°	1906.9	1973.0	1924.5	1879.5	1902.5
22.5°	1870.4	1935.4	1883.4	1834.8	1859.0
25°	1804.0	1857.2	1808.4	1761.9	1786.3
27.5°	1719.9	1757.2	1715.5	1671.4	1685.2
30°	1648.1	1685.5	1643.7	1598.3	1604.0
32.5°	1568.1	1599.8	1559.0	1518.3	1522.9
35°	1423.2	1444.7	1411.4	1379.1	1382.0
37.5°	1246.8	1249.6	1227.0	1197.7	1198.2
40°	1105.6	1114.2	1089.4	1066.0	1068.9
42.5°	937.4	971.3	947.1	926.0	926.5
45°	641.0	728.7	729.2	703.6	611.6
47.5°	354.0	455.5	520.8	403.8	304.9
50°	223.5	288.2	392.6	236.1	207.3
52.5°	160.0	189.0	286.7	167.0	152.0
55°	94.1	107.0	147.0	101.3	95.6
57.5°	57.3	68.6	85.9	67.7	57.6
60°	39.7	49.8	64.7	45.3	35.3
62.5°	35.0	38.2	50.6	36.1	32.9
65°	30.9	32.3	32.3	29.4	27.9
67.5°	27.3	28.8	27.3	25.8	24.4
70°	25.0	26.4	25.0	23.5	22.1
72.5°	22.6	24.1	22.6	21.1	19.7
75°	19.1	19.1	19.1	17.6	16.2
77.5°	15.6	15.6	15.3	14.1	12.6
80°	13.2	13.2	11.8	11.7	10.3
82.5°	10.9	10.9	9.4	9.4	7.9
85°	7.4	7.4	5.9	5.8	4.4
87.5°	3.5	3.9	3.1	3.5	2.3
90°	0.0	1.9	3.9	5.8	5.8
92.5°	4.7	6.6	8.5	12.1	13.6
95°	15.5	28.8	15.5	17.6	21.4
97.5°	27.6	55.3	114.2	33.7	29.1
100°	36.9	69.2	229.3	67.5	44.7
102.5°	46.2	80.1	310.1	178.1	97.5
105°	60.2	92.5	351.7	449.3	297.3
107.5°	74.2	98.5	335.7	653.8	612.4
110°	83.5	106.3	326.4	687.0	738.3



TEST NUMBER: P645160

CATALOG NUMBER: OMN4DIP-SR4F0-75D50U930-WBMOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	92.9	115.7	317.1	667.6	753.9
115°	106.9	129.7	303.1	630.0	736.4
117.5°	121.2	143.7	299.6	589.3	698.7
120°	132.1	153.0	293.4	558.3	672.3
122.5°	139.9	162.3	285.6	531.6	636.5
125°	153.5	174.4	285.6	499.5	590.7
127.5°	164.8	186.0	286.0	462.1	552.2
130°	171.0	193.8	287.6	437.2	522.7
132.5°	178.8	201.5	287.6	425.9	496.2
135°	190.4	211.3	287.6	411.3	472.1
137.5°	200.1	222.5	287.6	395.2	447.3
140°	207.9	228.8	287.6	385.8	433.3
142.5°	215.7	235.0	289.1	374.8	419.3
145°	225.4	244.4	289.5	358.4	396.4
147.5°	237.0	253.8	291.8	346.5	375.8
150°	244.8	260.0	293.4	338.6	363.3
152.5°	252.6	266.3	293.4	332.3	352.5
155°	264.2	273.7	295.3	324.8	340.0
157.5°	273.6	282.7	297.7	320.1	331.1
160°	279.8	287.4	299.2	316.9	326.4
162.5°	284.4	292.0	300.8	315.3	321.8
165°	293.4	297.2	303.1	311.0	316.7
167.5°	298.4	301.9	305.0	309.0	312.4
170°	303.1	305.0	305.0	309.0	310.9
172.5°	304.7	308.1	306.6	307.4	309.3
175°	308.9	310.8	308.9	306.9	305.0
177.5°	308.9	310.4	308.9	308.9	307.4
180°	308.9	308.9	308.9	308.9	308.9

(END OF REPORT)