

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331523-830

Luminaire Tested: **S122DIW-S485D1440U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331523-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1440U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7296.2 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331523-830

CATALOG NUMBER: S122DIW-S485D1440U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331523-830

CATALOG NUMBER: S122DIW-S485D1440U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	76	73	61	59	57	45	43	42	30	29	28	22
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	60	54	50	47	43	40	35	32	30	23	22	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	21	19	17	13
5	64	53	45	39	57	48	41	36	37	32	29	28	24	22	19	17	15	11
6	59	47	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	23	19	17	15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19	21	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	9	7
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11820	11820	11820
5°	11866	11694	11763
10°	11795	11576	11632
15°	11649	11425	11413
20°	11442	11201	11187
25°	11236	10922	10922
30°	10972	10670	10577
35°	10724	10364	10212
40°	10416	10060	9866
45°	10111	9757	9515
50°	9779	9442	9105
55°	9433	9073	8740
60°	9045	8638	8318
65°	8630	8202	7824
70°	8105	7676	7312
75°	7380	7068	6900
80°	6546	6341	6025
85°	5335	5076	4557



TEST NUMBER: P331523-830

CATALOG NUMBER: S122DIW-S485D1440U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	0.9
10°-20°	193.7	2.7
20°-30°	284.7	3.9
30°-40°	330.7	4.5
40°-50°	330.4	4.5
50°-60°	288.1	3.9
60°-70°	213.0	2.9
70°-80°	120.7	1.7
80°-90°	37.0	0.5
90°-100°	61.8	0.8
100°-110°	226.6	3.1
110°-120°	605.8	8.3
120°-130°	1000.0	13.7
130°-140°	1063.4	14.6
140°-150°	988.4	13.5
150°-160°	794.7	10.9
160°-170°	512.1	7.0
170°-180°	176.3	2.4
0°-30°	547.2	7.5
0°-40°	878.0	12.0
0°-60°	1496.4	20.5
0°-90°	1867.1	25.6
90°-120°	894.2	12.3
90°-150°	3946.0	54.1
90°-180°	5429.0	74.4
0°-180°	7296.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	732	729	722	727	726	69
15°	697	692	684	686	683	196
25°	631	625	613	614	613	290
35°	544	537	526	522	518	340
45°	443	438	427	420	417	342
55°	335	331	322	314	310	299
65°	226	222	215	208	205	223
75°	118	117	113	109	111	126
85°	29	28	27	25	25	33
90°	1	16	27	33	36	5
95°	87	46	52	58	58	107
105°	408	425	82	96	102	435
115°	771	794	827	236	110	759
125°	1090	1108	1133	1142	1146	971
135°	1349	1369	1382	1395	1393	1041
145°	1564	1564	1586	1594	1589	978
155°	1723	1712	1726	1734	1724	793
165°	1815	1808	1811	1819	1811	513
175°	1857	1848	1850	1858	1846	177
180°	1853	1853	1853	1853	1853	



TEST NUMBER: P331523-830

CATALOG NUMBER: S122DIW-S485D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	735.5	734.8	734.2	733.6	732.9	732.0	730.6	729.2	727.8	726.4	727.7
5°	732.1	731.4	730.8	730.2	729.6	728.4	726.7	725.0	723.2	721.5	722.7
7.5°	725.6	724.6	723.7	722.6	721.7	720.4	718.6	716.9	715.1	713.3	714.6
10°	719.4	718.3	717.2	716.1	715.0	713.5	711.6	709.8	707.9	706.1	707.3
12.5°	711.0	710.0	709.0	708.0	707.1	705.7	703.8	701.9	700.0	698.1	699.0
15°	696.9	696.0	695.0	694.1	693.1	691.6	689.6	687.6	685.5	683.5	684.1
17.5°	678.8	678.0	677.0	676.1	675.1	673.6	671.6	669.5	667.4	665.3	666.1
20°	665.9	665.0	664.0	663.1	662.1	660.6	658.4	656.2	654.0	651.9	652.3
22.5°	653.0	651.7	650.4	649.0	647.7	646.0	643.9	641.9	639.8	637.7	637.8
25°	630.7	629.4	628.2	627.0	625.8	623.8	621.1	618.4	615.8	613.1	613.4
27.5°	605.4	604.3	603.1	602.0	600.9	599.3	597.2	595.0	593.0	590.9	590.4
30°	588.5	587.2	586.0	584.8	583.4	581.6	579.3	577.0	574.7	572.3	571.8
32.5°	570.4	569.5	568.4	567.4	566.5	564.7	562.2	559.8	557.3	554.9	554.0
35°	544.1	542.5	541.0	539.4	537.9	535.8	533.4	530.8	528.3	525.8	524.9
37.5°	514.4	513.0	511.7	510.3	508.9	507.0	504.4	502.0	499.5	497.0	495.8
40°	494.2	492.9	491.6	490.4	489.2	487.3	484.7	482.3	479.8	477.3	475.9
42.5°	474.5	473.2	471.9	470.7	469.5	467.6	465.1	462.6	460.1	457.5	456.0
45°	442.8	441.7	440.5	439.5	438.4	436.7	434.3	432.0	429.6	427.3	425.6
47.5°	411.2	410.2	409.2	408.1	407.1	405.4	402.9	400.5	398.0	395.6	393.8
50°	389.3	388.5	387.7	386.9	386.2	384.7	382.5	380.3	378.1	375.9	373.7
52.5°	367.9	366.8	365.8	364.8	363.7	362.2	360.1	358.1	356.0	353.9	352.1
55°	335.1	334.1	333.2	332.2	331.3	329.9	328.0	326.1	324.2	322.3	320.6
57.5°	302.1	301.3	300.6	299.9	299.2	297.7	295.7	293.6	291.5	289.5	287.6
60°	280.1	279.6	278.9	278.2	277.7	276.3	274.1	271.8	269.7	267.5	265.8
62.5°	258.7	257.8	256.7	255.7	254.8	253.4	251.8	250.1	248.4	246.7	245.1
65°	225.9	225.0	224.0	223.1	222.3	220.9	219.4	217.8	216.2	214.7	213.3
67.5°	192.6	191.8	191.1	190.3	189.5	188.5	187.1	185.7	184.3	182.9	181.8
70°	171.7	171.2	170.5	169.8	169.3	168.2	166.8	165.4	164.0	162.6	161.6
72.5°	150.3	149.8	149.1	148.5	147.9	147.1	146.2	145.2	144.4	143.5	142.3
75°	118.3	117.9	117.6	117.3	117.0	116.5	115.6	114.9	114.1	113.3	112.4
77.5°	89.5	89.0	88.5	87.9	87.4	87.0	86.7	86.3	86.1	85.8	85.3
80°	70.4	70.2	70.1	69.9	69.7	69.6	69.2	68.9	68.6	68.2	67.8
82.5°	52.4	52.3	52.3	52.3	52.2	52.1	51.9	51.7	51.6	51.4	50.8
85°	28.8	28.7	28.6	28.4	28.3	28.1	27.9	27.8	27.6	27.4	27.0
87.5°	10.4	10.8	11.2	11.6	12.1	12.3	12.5	12.8	13.0	13.3	13.2
90°	1.3	4.6	7.9	11.2	14.4	17.2	19.7	22.1	24.4	26.8	28.3
92.5°	27.1	26.8	26.5	26.2	25.9	26.3	27.5	28.7	29.9	31.1	31.9
95°	87.1	77.3	67.5	57.7	47.8	43.9	46.0	48.1	50.2	52.3	53.7
97.5°	173.0	145.2	117.5	89.8	62.1	50.7	55.5	60.3	65.1	69.9	71.2
100°	237.2	196.4	155.6	114.8	74.0	56.2	61.2	66.3	71.4	76.4	78.8
102.5°	308.0	299.4	290.8	282.1	273.5	248.0	205.7	163.2	120.9	78.5	81.6
105°	407.6	416.4	425.4	434.3	443.3	407.1	325.7	244.4	163.1	81.8	85.0
107.5°	520.9	528.1	535.4	542.5	549.8	504.6	407.1	309.5	212.0	114.5	111.1
110°	593.9	600.1	606.3	612.7	618.9	578.9	492.9	406.8	320.7	234.6	204.8



TEST NUMBER: P331523-830

CATALOG NUMBER: S122DIW-S485D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	662.5	668.0	673.5	679.1	684.7	676.7	655.5	634.2	612.9	591.7	483.1
115°	770.8	775.9	780.9	786.0	791.1	797.3	804.7	812.2	819.6	827.1	689.2
117.5°	867.6	873.3	878.9	884.6	890.2	895.6	900.7	905.9	911.0	916.2	882.8
120°	938.4	942.8	947.3	951.8	956.2	961.1	966.5	971.9	977.2	982.6	986.2
122.5°	998.4	1003.1	1007.9	1012.6	1017.3	1022.6	1028.3	1034.2	1040.0	1045.8	1048.0
125°	1089.9	1093.7	1097.6	1101.5	1105.3	1110.1	1115.8	1121.4	1127.1	1132.7	1134.8
127.5°	1172.7	1177.0	1181.3	1185.5	1189.9	1194.1	1198.3	1202.6	1206.8	1211.1	1214.1
130°	1225.2	1230.0	1234.7	1239.5	1244.3	1248.3	1251.6	1254.9	1258.1	1261.4	1264.7
132.5°	1278.8	1282.9	1286.9	1291.0	1295.1	1298.7	1302.0	1305.2	1308.5	1311.8	1314.7
135°	1348.6	1353.3	1358.1	1362.8	1367.6	1371.3	1374.0	1376.7	1379.4	1382.1	1385.1
137.5°	1419.1	1422.4	1425.8	1429.1	1432.4	1435.6	1438.6	1441.7	1444.7	1447.7	1450.7
140°	1465.2	1467.5	1470.0	1472.3	1474.7	1477.5	1480.8	1484.1	1487.4	1490.6	1493.4
142.5°	1503.8	1505.9	1508.1	1510.2	1512.4	1515.3	1519.1	1522.9	1526.5	1530.3	1532.8
145°	1564.4	1564.1	1563.8	1563.5	1563.2	1565.6	1570.7	1575.7	1580.7	1585.8	1587.9
147.5°	1617.2	1616.1	1615.0	1613.8	1612.7	1614.6	1619.6	1624.7	1629.7	1634.7	1636.2
150°	1651.5	1649.4	1647.4	1645.3	1643.1	1644.5	1649.3	1654.1	1658.8	1663.6	1665.4
152.5°	1680.5	1678.2	1675.8	1673.5	1671.2	1672.3	1676.8	1681.3	1685.8	1690.4	1692.1
155°	1722.6	1719.9	1717.2	1714.5	1711.8	1712.3	1715.9	1719.5	1723.1	1726.5	1728.3
157.5°	1755.6	1753.3	1751.1	1748.8	1746.5	1746.6	1749.1	1751.6	1754.1	1756.6	1758.7
160°	1774.8	1773.0	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1776.6
162.5°	1792.0	1790.3	1788.5	1786.7	1784.9	1784.7	1786.3	1787.8	1789.4	1790.9	1793.0
165°	1815.1	1813.3	1811.5	1809.7	1807.9	1807.5	1808.4	1809.2	1810.2	1811.0	1813.2
167.5°	1832.2	1830.4	1828.6	1826.8	1825.0	1824.6	1825.4	1826.3	1827.1	1828.0	1830.0
170°	1841.9	1840.1	1838.3	1836.5	1834.8	1834.1	1834.8	1835.3	1835.9	1836.5	1838.6
172.5°	1848.3	1846.5	1844.7	1843.0	1841.2	1840.6	1841.2	1841.7	1842.4	1843.0	1845.0
175°	1856.6	1854.5	1852.5	1850.4	1848.3	1847.6	1848.1	1848.7	1849.4	1849.9	1852.0
177.5°	1857.9	1856.3	1854.6	1852.9	1851.2	1850.6	1850.8	1851.1	1851.2	1851.5	1853.2
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331523-830

CATALOG NUMBER: S122DIW-S485D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	729.0	730.2	731.4	732.0	731.7	731.4	731.2	730.9
5°	724.1	725.3	726.5	727.0	726.7	726.3	726.0	725.8
7.5°	715.9	717.1	718.4	718.8	718.5	718.1	717.7	717.5
10°	708.5	709.8	711.1	711.4	711.0	710.5	710.0	709.5
12.5°	699.9	700.8	701.6	701.9	701.5	701.3	700.9	700.5
15°	684.8	685.4	686.0	685.9	685.1	684.4	683.6	682.8
17.5°	666.8	667.5	668.3	668.2	667.4	666.8	666.0	665.2
20°	652.8	653.3	653.7	653.7	653.0	652.3	651.8	651.1
22.5°	637.9	638.0	638.1	638.0	637.6	637.3	636.9	636.5
25°	613.8	614.1	614.3	614.3	614.1	613.8	613.4	613.1
27.5°	589.9	589.5	589.0	588.4	587.7	586.9	586.2	585.4
30°	571.4	570.9	570.4	569.9	569.2	568.6	568.0	567.3
32.5°	553.2	552.3	551.5	550.7	550.1	549.5	548.8	548.2
35°	524.0	523.0	522.1	521.2	520.5	519.6	518.9	518.1
37.5°	494.6	493.5	492.4	491.3	490.6	489.8	489.1	488.4
40°	474.5	473.1	471.6	470.6	470.0	469.4	468.7	468.1
42.5°	454.5	453.0	451.4	450.3	449.3	448.5	447.6	446.7
45°	423.9	422.2	420.4	419.2	418.6	418.0	417.4	416.7
47.5°	392.0	390.1	388.3	387.0	386.1	385.2	384.3	383.3
50°	371.6	369.3	367.1	365.6	364.9	364.1	363.3	362.5
52.5°	350.3	348.5	346.7	345.3	344.2	343.2	342.1	341.1
55°	318.7	316.8	314.9	313.6	312.7	312.0	311.2	310.5
57.5°	285.8	283.9	282.1	280.9	280.2	279.7	279.1	278.4
60°	264.0	262.3	260.6	259.5	259.0	258.5	258.1	257.6
62.5°	243.5	241.9	240.3	239.2	238.6	238.0	237.4	236.8
65°	211.9	210.5	209.1	207.9	207.2	206.4	205.7	204.8
67.5°	180.7	179.6	178.5	177.7	177.0	176.3	175.8	175.1
70°	160.4	159.3	158.3	157.4	156.7	156.1	155.5	154.9
72.5°	141.3	140.2	139.1	138.3	137.8	137.2	136.8	136.3
75°	111.4	110.6	109.6	109.2	109.6	109.9	110.2	110.6
77.5°	84.8	84.4	83.9	83.4	82.9	82.6	82.1	81.6
80°	67.3	66.8	66.4	66.0	65.7	65.4	65.0	64.8
82.5°	50.2	49.6	49.0	48.6	48.6	48.5	48.4	48.4
85°	26.5	26.0	25.5	25.3	25.1	25.0	24.8	24.6
87.5°	13.1	13.0	12.9	12.9	12.9	12.9	12.9	12.9
90°	29.8	31.3	32.8	33.8	34.4	35.0	35.6	36.2
92.5°	32.6	33.5	34.2	34.8	35.2	35.4	35.8	36.2
95°	55.2	56.7	58.2	58.8	58.5	58.2	58.0	57.7
97.5°	72.4	73.5	74.7	75.5	75.9	76.3	76.6	76.9
100°	81.2	83.6	86.0	87.5	88.0	88.6	89.3	89.8
102.5°	84.7	87.8	91.0	92.9	93.8	94.5	95.4	96.2
105°	88.3	91.6	94.9	97.1	98.3	99.5	100.7	101.9
107.5°	107.8	104.4	101.1	100.1	101.2	102.5	103.7	104.8
110°	175.0	145.2	115.5	101.1	102.4	103.5	104.7	105.9



TEST NUMBER: P331523-830

CATALOG NUMBER: S122DIW-S485D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	374.4	265.7	157.0	103.1	104.2	105.1	106.0	107.0
115°	551.3	413.3	275.4	195.7	174.3	152.8	131.4	109.9
117.5°	849.4	816.1	782.7	730.8	660.3	589.7	519.2	448.8
120°	989.8	993.3	996.9	978.5	938.4	898.1	857.9	817.7
122.5°	1050.2	1052.3	1054.4	1051.6	1043.8	1036.0	1028.2	1020.4
125°	1136.9	1139.0	1141.0	1142.6	1143.5	1144.3	1145.3	1146.1
127.5°	1217.1	1220.1	1223.1	1224.8	1224.9	1225.1	1225.3	1225.5
130°	1268.0	1271.3	1274.5	1276.0	1275.7	1275.4	1275.2	1274.8
132.5°	1317.4	1320.2	1323.0	1324.3	1324.0	1323.7	1323.4	1323.0
135°	1388.0	1391.0	1394.0	1395.2	1394.6	1394.0	1393.4	1392.8
137.5°	1453.6	1456.5	1459.4	1460.4	1459.3	1458.4	1457.4	1456.3
140°	1496.0	1498.7	1501.4	1501.9	1500.5	1499.0	1497.5	1496.0
142.5°	1535.2	1537.7	1540.1	1540.6	1539.1	1537.6	1536.2	1534.6
145°	1590.0	1592.0	1594.2	1594.5	1593.0	1591.5	1590.0	1588.6
147.5°	1637.8	1639.3	1640.9	1641.0	1639.7	1638.5	1637.2	1636.0
150°	1667.2	1669.0	1670.8	1670.8	1669.4	1667.9	1666.4	1664.9
152.5°	1693.9	1695.7	1697.5	1697.4	1695.4	1693.6	1691.6	1689.6
155°	1730.1	1731.9	1733.7	1733.4	1731.1	1728.7	1726.3	1723.9
157.5°	1760.7	1762.6	1764.7	1764.5	1762.3	1759.9	1757.6	1755.3
160°	1778.4	1780.2	1782.0	1781.9	1779.8	1777.6	1775.6	1773.5
162.5°	1795.0	1797.1	1799.0	1798.7	1796.2	1793.7	1791.1	1788.6
165°	1815.2	1817.3	1819.4	1819.4	1817.3	1815.2	1813.2	1811.0
167.5°	1832.1	1834.2	1836.3	1836.0	1833.3	1830.6	1828.0	1825.2
170°	1840.7	1842.8	1844.8	1844.6	1841.9	1839.2	1836.5	1833.8
172.5°	1847.1	1849.2	1851.2	1851.0	1848.3	1845.6	1843.0	1840.2
175°	1854.1	1856.1	1858.2	1857.8	1854.8	1851.8	1848.9	1845.9
177.5°	1854.8	1856.5	1858.2	1857.9	1855.8	1853.7	1851.5	1849.4
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6

(END OF REPORT)