

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331499-830

Luminaire Tested: **S122DIW-S485D435U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331499-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D435U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3495.5 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331499-830

CATALOG NUMBER: S122DIW-S485D435U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331499-830

CATALOG NUMBER: S122DIW-S485D435U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53								
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45								
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38								
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32								
4	75	64	56	50	69	60	53	47	51	46	42	44	39	36	36	33	31	27								
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24								
6	63	51	43	37	59	48	41	35	41	36	31	35	31	27	30	26	24	21								
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19								
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17								
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	15								
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16	14								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11820	11820	11820
5°	11866	11694	11763
10°	11795	11576	11632
15°	11649	11425	11413
20°	11442	11201	11187
25°	11236	10922	10922
30°	10972	10670	10577
35°	10724	10364	10212
40°	10416	10060	9866
45°	10111	9757	9515
50°	9779	9442	9105
55°	9433	9073	8740
60°	9045	8638	8318
65°	8630	8202	7824
70°	8105	7676	7312
75°	7380	7068	6900
80°	6546	6341	6025
85°	5335	5076	4557



TEST NUMBER: P331499-830

CATALOG NUMBER: S122DIW-S485D435U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	2.0
10°-20°	193.7	5.5
20°-30°	284.7	8.1
30°-40°	330.7	9.5
40°-50°	330.4	9.5
50°-60°	288.1	8.2
60°-70°	213.0	6.1
70°-80°	120.7	3.5
80°-90°	33.8	1.0
90°-100°	18.6	0.5
100°-110°	68.1	1.9
110°-120°	182.0	5.2
120°-130°	300.5	8.6
130°-140°	319.6	9.1
140°-150°	297.0	8.5
150°-160°	238.8	6.8
160°-170°	153.9	4.4
170°-180°	53.0	1.5
0°-30°	547.2	15.7
0°-40°	878.0	25.1
0°-60°	1496.4	42.8
0°-90°	1863.9	53.3
90°-120°	268.7	7.7
90°-150°	1185.9	33.9
90°-180°	1632.0	46.7
0°-180°	3495.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	732	729	722	727	726	69
15°	697	692	684	686	683	196
25°	631	625	613	614	613	290
35°	544	537	526	522	518	340
45°	443	438	427	420	417	342
55°	335	331	322	314	310	299
65°	226	222	215	208	205	223
75°	118	117	113	109	111	126
85°	29	28	27	25	25	33
90°	0	5	8	10	11	3
95°	26	14	16	18	17	32
105°	122	128	25	29	31	131
115°	232	239	248	71	33	228
125°	328	333	340	343	344	292
135°	405	412	415	419	419	313
145°	470	470	476	479	477	294
155°	518	514	519	521	518	238
165°	545	543	544	547	544	154
175°	558	555	556	558	555	53
180°	557	557	557	557	557	



TEST NUMBER: P331499-830

CATALOG NUMBER: S122DIW-S485D435U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	735.5	734.8	734.2	733.6	732.9	732.0	730.6	729.2	727.8	726.4	727.7
5°	732.1	731.4	730.8	730.2	729.6	728.4	726.7	725.0	723.2	721.5	722.7
7.5°	725.6	724.6	723.7	722.6	721.7	720.4	718.6	716.9	715.1	713.3	714.6
10°	719.4	718.3	717.2	716.1	715.0	713.5	711.6	709.8	707.9	706.1	707.3
12.5°	711.0	710.0	709.0	708.0	707.1	705.7	703.8	701.9	700.0	698.1	699.0
15°	696.9	696.0	695.0	694.1	693.1	691.6	689.6	687.6	685.5	683.5	684.1
17.5°	678.8	678.0	677.0	676.1	675.1	673.6	671.6	669.5	667.4	665.3	666.1
20°	665.9	665.0	664.0	663.1	662.1	660.6	658.4	656.2	654.0	651.9	652.3
22.5°	653.0	651.7	650.4	649.0	647.7	646.0	643.9	641.9	639.8	637.7	637.8
25°	630.7	629.4	628.2	627.0	625.8	623.8	621.1	618.4	615.8	613.1	613.4
27.5°	605.4	604.3	603.1	602.0	600.9	599.3	597.2	595.0	593.0	590.9	590.4
30°	588.5	587.2	586.0	584.8	583.4	581.6	579.3	577.0	574.7	572.3	571.8
32.5°	570.4	569.5	568.4	567.4	566.5	564.7	562.2	559.8	557.3	554.9	554.0
35°	544.1	542.5	541.0	539.4	537.9	535.8	533.4	530.8	528.3	525.8	524.9
37.5°	514.4	513.0	511.7	510.3	508.9	507.0	504.4	502.0	499.5	497.0	495.8
40°	494.2	492.9	491.6	490.4	489.2	487.3	484.7	482.3	479.8	477.3	475.9
42.5°	474.5	473.2	471.9	470.7	469.5	467.6	465.1	462.6	460.1	457.5	456.0
45°	442.8	441.7	440.5	439.5	438.4	436.7	434.3	432.0	429.6	427.3	425.6
47.5°	411.2	410.2	409.2	408.1	407.1	405.4	402.9	400.5	398.0	395.6	393.8
50°	389.3	388.5	387.7	386.9	386.2	384.7	382.5	380.3	378.1	375.9	373.7
52.5°	367.9	366.8	365.8	364.8	363.7	362.2	360.1	358.1	356.0	353.9	352.1
55°	335.1	334.1	333.2	332.2	331.3	329.9	328.0	326.1	324.2	322.3	320.6
57.5°	302.1	301.3	300.6	299.9	299.2	297.7	295.7	293.6	291.5	289.5	287.6
60°	280.1	279.6	278.9	278.2	277.7	276.3	274.1	271.8	269.7	267.5	265.8
62.5°	258.7	257.8	256.7	255.7	254.8	253.4	251.8	250.1	248.4	246.7	245.1
65°	225.9	225.0	224.0	223.1	222.3	220.9	219.4	217.8	216.2	214.7	213.3
67.5°	192.6	191.8	191.1	190.3	189.5	188.5	187.1	185.7	184.3	182.9	181.8
70°	171.7	171.2	170.5	169.8	169.3	168.2	166.8	165.4	164.0	162.6	161.6
72.5°	150.3	149.8	149.1	148.5	147.9	147.1	146.2	145.2	144.4	143.5	142.3
75°	118.3	117.9	117.6	117.3	117.0	116.5	115.6	114.9	114.1	113.3	112.4
77.5°	89.5	89.0	88.5	87.9	87.4	87.0	86.7	86.3	86.1	85.8	85.3
80°	70.4	70.2	70.1	69.9	69.7	69.6	69.2	68.9	68.6	68.2	67.8
82.5°	52.4	52.3	52.3	52.3	52.2	52.1	51.9	51.7	51.6	51.4	50.8
85°	28.8	28.7	28.6	28.4	28.3	28.1	27.9	27.8	27.6	27.4	27.0
87.5°	10.2	10.2	10.1	10.1	10.0	9.9	9.8	9.7	9.6	9.5	9.2
90°	0.4	1.4	2.4	3.4	4.3	5.2	5.9	6.6	7.4	8.0	8.5
92.5°	8.1	8.0	7.9	7.8	7.8	7.9	8.3	8.7	9.0	9.3	9.6
95°	26.2	23.2	20.3	17.3	14.3	13.2	13.9	14.4	15.1	15.7	16.1
97.5°	51.9	43.6	35.3	27.0	18.7	15.3	16.7	18.1	19.6	21.0	21.4
100°	71.4	59.0	46.8	34.5	22.2	16.9	18.4	19.9	21.4	23.0	23.7
102.5°	92.6	90.0	87.4	84.8	82.2	74.6	61.8	49.1	36.4	23.6	24.5
105°	122.4	125.2	127.8	130.5	133.2	122.3	97.9	73.4	49.0	24.6	25.5
107.5°	156.6	158.7	160.9	163.1	165.2	151.7	122.3	93.0	63.7	34.4	33.4
110°	178.4	180.3	182.2	184.1	186.0	174.0	148.1	122.2	96.3	70.5	61.5



TEST NUMBER: P331499-830

CATALOG NUMBER: S122DIW-S485D435U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	199.1	200.8	202.5	204.1	205.8	203.4	197.0	190.6	184.2	177.9	145.2
115°	231.7	233.2	234.7	236.2	237.7	239.6	241.9	244.1	246.3	248.5	207.1
117.5°	260.7	262.4	264.1	265.8	267.5	269.2	270.7	272.2	273.8	275.3	265.3
120°	282.0	283.3	284.6	286.1	287.4	288.9	290.5	292.1	293.7	295.3	296.3
122.5°	300.0	301.4	302.8	304.3	305.7	307.3	309.1	310.8	312.5	314.3	315.0
125°	327.5	328.7	329.9	331.0	332.2	333.6	335.4	337.1	338.7	340.4	341.0
127.5°	352.4	353.7	355.0	356.3	357.6	358.8	360.1	361.4	362.7	363.9	364.9
130°	368.3	369.7	371.1	372.5	373.9	375.1	376.2	377.1	378.1	379.1	380.0
132.5°	384.4	385.5	386.7	388.0	389.2	390.3	391.2	392.3	393.2	394.3	395.1
135°	405.3	406.7	408.1	409.5	411.0	412.1	412.9	413.8	414.5	415.4	416.2
137.5°	426.5	427.4	428.5	429.5	430.5	431.4	432.3	433.3	434.1	435.1	435.9
140°	440.4	441.0	441.8	442.4	443.2	444.0	445.1	446.0	447.0	448.0	448.7
142.5°	451.9	452.6	453.2	453.8	454.5	455.4	456.5	457.6	458.7	459.9	460.6
145°	470.1	470.0	470.0	469.9	469.8	470.5	472.0	473.5	475.0	476.5	477.2
147.5°	486.0	485.7	485.3	485.0	484.7	485.2	486.7	488.2	489.7	491.3	491.7
150°	496.3	495.7	495.0	494.5	493.8	494.2	495.7	497.1	498.5	499.9	500.5
152.5°	505.0	504.4	503.6	502.9	502.2	502.6	503.9	505.3	506.6	508.0	508.5
155°	517.6	516.9	516.0	515.3	514.4	514.6	515.7	516.7	517.8	518.9	519.4
157.5°	527.5	526.9	526.2	525.6	524.9	524.9	525.7	526.4	527.2	527.9	528.5
160°	533.4	532.8	532.3	531.8	531.2	531.2	531.8	532.3	532.8	533.4	534.0
162.5°	538.6	538.0	537.4	537.0	536.4	536.4	536.8	537.2	537.7	538.2	538.9
165°	545.4	545.0	544.4	543.8	543.3	543.2	543.5	543.8	544.0	544.2	544.9
167.5°	550.6	550.1	549.6	549.0	548.5	548.4	548.6	548.8	549.1	549.3	550.0
170°	553.6	553.0	552.4	552.0	551.4	551.2	551.4	551.6	551.8	552.0	552.5
172.5°	555.4	555.0	554.4	553.8	553.3	553.2	553.3	553.5	553.6	553.8	554.5
175°	558.0	557.3	556.7	556.1	555.4	555.3	555.4	555.6	555.7	555.9	556.6
177.5°	558.4	557.9	557.3	556.9	556.4	556.1	556.2	556.3	556.4	556.4	556.9
180°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8



TEST NUMBER: P331499-830

CATALOG NUMBER: S122DIW-S485D435U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	729.0	730.2	731.4	732.0	731.7	731.4	731.2	730.9
5°	724.1	725.3	726.5	727.0	726.7	726.3	726.0	725.8
7.5°	715.9	717.1	718.4	718.8	718.5	718.1	717.7	717.5
10°	708.5	709.8	711.1	711.4	711.0	710.5	710.0	709.5
12.5°	699.9	700.8	701.6	701.9	701.5	701.3	700.9	700.5
15°	684.8	685.4	686.0	685.9	685.1	684.4	683.6	682.8
17.5°	666.8	667.5	668.3	668.2	667.4	666.8	666.0	665.2
20°	652.8	653.3	653.7	653.7	653.0	652.3	651.8	651.1
22.5°	637.9	638.0	638.1	638.0	637.6	637.3	636.9	636.5
25°	613.8	614.1	614.3	614.3	614.1	613.8	613.4	613.1
27.5°	589.9	589.5	589.0	588.4	587.7	586.9	586.2	585.4
30°	571.4	570.9	570.4	569.9	569.2	568.6	568.0	567.3
32.5°	553.2	552.3	551.5	550.7	550.1	549.5	548.8	548.2
35°	524.0	523.0	522.1	521.2	520.5	519.6	518.9	518.1
37.5°	494.6	493.5	492.4	491.3	490.6	489.8	489.1	488.4
40°	474.5	473.1	471.6	470.6	470.0	469.4	468.7	468.1
42.5°	454.5	453.0	451.4	450.3	449.3	448.5	447.6	446.7
45°	423.9	422.2	420.4	419.2	418.6	418.0	417.4	416.7
47.5°	392.0	390.1	388.3	387.0	386.1	385.2	384.3	383.3
50°	371.6	369.3	367.1	365.6	364.9	364.1	363.3	362.5
52.5°	350.3	348.5	346.7	345.3	344.2	343.2	342.1	341.1
55°	318.7	316.8	314.9	313.6	312.7	312.0	311.2	310.5
57.5°	285.8	283.9	282.1	280.9	280.2	279.7	279.1	278.4
60°	264.0	262.3	260.6	259.5	259.0	258.5	258.1	257.6
62.5°	243.5	241.9	240.3	239.2	238.6	238.0	237.4	236.8
65°	211.9	210.5	209.1	207.9	207.2	206.4	205.7	204.8
67.5°	180.7	179.6	178.5	177.7	177.0	176.3	175.8	175.1
70°	160.4	159.3	158.3	157.4	156.7	156.1	155.5	154.9
72.5°	141.3	140.2	139.1	138.3	137.8	137.2	136.8	136.3
75°	111.4	110.6	109.6	109.2	109.6	109.9	110.2	110.6
77.5°	84.8	84.4	83.9	83.4	82.9	82.6	82.1	81.6
80°	67.3	66.8	66.4	66.0	65.7	65.4	65.0	64.8
82.5°	50.2	49.6	49.0	48.6	48.6	48.5	48.4	48.4
85°	26.5	26.0	25.5	25.3	25.1	25.0	24.8	24.6
87.5°	9.0	8.7	8.4	8.2	8.1	8.0	7.9	7.8
90°	9.0	9.4	9.8	10.2	10.4	10.6	10.7	10.8
92.5°	9.8	10.1	10.3	10.5	10.6	10.7	10.7	10.8
95°	16.6	17.1	17.5	17.7	17.6	17.5	17.4	17.3
97.5°	21.8	22.1	22.4	22.7	22.8	22.9	23.0	23.1
100°	24.4	25.1	25.8	26.3	26.5	26.7	26.8	27.0
102.5°	25.4	26.4	27.3	27.9	28.2	28.5	28.7	28.9
105°	26.6	27.5	28.6	29.2	29.5	29.9	30.3	30.6
107.5°	32.4	31.4	30.3	30.1	30.4	30.8	31.1	31.5
110°	52.6	43.6	34.7	30.3	30.7	31.1	31.5	31.9



TEST NUMBER: P331499-830

CATALOG NUMBER: S122DIW-S485D435U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	112.5	79.8	47.2	31.0	31.3	31.6	31.9	32.1
115°	165.7	124.2	82.8	58.8	52.4	45.9	39.5	33.0
117.5°	255.2	245.2	235.2	219.6	198.4	177.2	156.1	134.9
120°	297.5	298.5	299.6	294.1	282.0	269.9	257.8	245.7
122.5°	315.6	316.2	316.9	316.0	313.7	311.3	309.0	306.6
125°	341.7	342.3	342.9	343.4	343.7	343.9	344.2	344.4
127.5°	365.8	366.6	367.6	368.1	368.2	368.2	368.3	368.3
130°	381.1	382.0	383.0	383.5	383.4	383.3	383.2	383.1
132.5°	396.0	396.7	397.6	397.9	397.8	397.8	397.8	397.7
135°	417.2	418.0	419.0	419.2	419.1	419.0	418.8	418.6
137.5°	436.9	437.7	438.6	438.8	438.6	438.3	438.0	437.6
140°	449.6	450.4	451.2	451.4	450.9	450.4	450.1	449.6
142.5°	461.4	462.1	462.9	463.0	462.5	462.1	461.7	461.2
145°	477.9	478.4	479.1	479.2	478.7	478.2	477.9	477.4
147.5°	492.2	492.7	493.1	493.1	492.8	492.4	492.0	491.6
150°	501.1	501.5	502.1	502.2	501.7	501.2	500.8	500.4
152.5°	509.1	509.6	510.2	510.1	509.5	509.0	508.3	507.7
155°	520.0	520.5	521.0	520.9	520.2	519.5	518.8	518.1
157.5°	529.1	529.7	530.4	530.3	529.6	528.9	528.2	527.5
160°	534.4	535.0	535.6	535.5	534.9	534.2	533.6	533.0
162.5°	539.4	540.1	540.6	540.5	539.8	539.0	538.3	537.5
165°	545.5	546.1	546.8	546.8	546.1	545.5	544.9	544.2
167.5°	550.6	551.2	551.9	551.8	550.9	550.2	549.3	548.6
170°	553.2	553.8	554.4	554.3	553.6	552.7	552.0	551.1
172.5°	555.1	555.7	556.4	556.3	555.4	554.7	553.8	553.1
175°	557.2	557.8	558.5	558.4	557.4	556.6	555.6	554.8
177.5°	557.4	557.9	558.5	558.4	557.7	557.0	556.4	555.8
180°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8

(END OF REPORT)