

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331501-830

Luminaire Tested: **S122DIW-S485D710U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331501-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D710U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4695.2 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43																												
1	97	93	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43	37																												
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	32																												
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32	27																												
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24																												
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	21																												
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19																												
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17																												
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17	15																												
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14																												
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14788	14788	14788	14788
5°	16579	14885	13190	14885
10°	18998	14762	11416	14762
15°	21018	14492	10084	14492
20°	20697	14201	9194	14201
25°	18661	13814	8630	13814
30°	15422	13196	8216	13196
35°	11239	12552	7924	12552
40°	8977	11788	7761	11788
45°	7846	10908	7540	10908
50°	7375	10052	7392	10052
55°	6798	9185	7192	9185
60°	6229	8263	6888	8263
65°	5673	7435	6590	7435
70°	5150	6628	6151	6628
75°	4566	5733	5446	5733
80°	3924	4751	4379	4751
85°	3520	3520	2594	3520



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	1.9
10°-20°	253.6	5.4
20°-30°	368.0	7.8
30°-40°	388.4	8.3
40°-50°	343.9	7.3
50°-60°	274.4	5.8
60°-70°	186.5	4.0
70°-80°	95.6	2.0
80°-90°	25.3	0.5
90°-100°	30.4	0.6
100°-110°	111.6	2.4
110°-120°	298.2	6.4
120°-130°	492.2	10.5
130°-140°	523.5	11.1
140°-150°	486.5	10.4
150°-160°	391.2	8.3
160°-170°	252.1	5.4
170°-180°	86.8	1.8
0°-30°	708.8	15.1
0°-40°	1097.2	23.4
0°-60°	1715.5	36.5
0°-90°	2022.9	43.1
90°-120°	440.1	9.4
90°-150°	1942.3	41.4
90°-180°	2672.0	56.9
0°-180°	4695.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	916	916	916	916	916	
5°	1023	918	814	918	1023	102
15°	1257	867	603	867	1257	347
25°	1048	775	484	775	1048	473
35°	570	637	402	637	570	371
45°	344	478	330	478	344	270
55°	242	326	256	326	242	217
65°	148	195	172	195	148	148
75°	73	92	87	92	73	78
85°	19	19	14	19	19	21
90°	18	1	18	1	18	9
95°	28	43	28	43	28	26
105°	50	201	50	201	50	52
115°	54	379	54	379	54	136
125°	564	536	564	536	564	488
135°	686	664	686	664	686	528
145°	782	770	782	770	782	489
155°	849	848	849	848	849	392
165°	892	893	892	893	892	252
175°	909	914	909	914	909	87
180°	912	912	912	912	912	



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	958.2	958.5	958.9	954.5	953.9	953.9	950.0	946.6	942.6	937.3	937.8
5°	1022.9	1026.8	1028.2	1024.0	1017.7	1016.9	1011.0	1001.1	991.9	984.6	979.3
7.5°	1100.2	1101.7	1098.3	1092.8	1088.1	1079.6	1068.5	1057.5	1042.3	1028.2	1017.9
10°	1158.8	1160.9	1154.9	1146.8	1140.1	1130.3	1114.1	1097.5	1077.5	1058.1	1042.6
12.5°	1203.2	1208.5	1200.8	1199.8	1188.3	1174.8	1155.5	1147.1	1118.9	1091.9	1075.3
15°	1257.4	1257.0	1257.7	1251.0	1242.6	1240.5	1220.0	1197.9	1158.1	1142.3	1114.7
17.5°	1241.7	1247.1	1249.5	1249.4	1249.2	1247.9	1241.3	1227.4	1207.4	1181.8	1150.1
20°	1204.6	1211.5	1212.7	1220.8	1225.3	1231.3	1233.8	1229.9	1217.6	1196.1	1168.7
22.5°	1147.1	1149.1	1152.4	1165.0	1174.9	1189.9	1197.7	1210.7	1206.0	1195.5	1172.6
25°	1047.5	1044.1	1056.3	1062.7	1085.5	1109.5	1126.7	1145.8	1162.6	1172.9	1166.2
27.5°	928.0	922.7	941.2	958.0	976.6	1002.5	1029.4	1061.1	1087.5	1120.6	1131.9
30°	827.2	830.4	848.0	865.9	894.1	930.7	960.9	995.8	1033.5	1070.4	1096.1
32.5°	718.5	730.7	741.8	769.3	794.1	834.9	879.3	922.8	969.9	1011.8	1051.6
35°	570.2	584.3	599.8	619.9	654.7	695.2	738.5	797.3	861.4	918.7	965.9
37.5°	479.9	477.8	486.6	501.1	529.3	562.0	611.8	670.0	745.4	812.8	879.3
40°	425.9	424.5	430.8	444.2	465.7	489.7	533.3	584.3	654.4	736.7	816.0
42.5°	388.7	389.6	393.1	402.6	417.3	437.0	469.7	513.1	577.2	654.8	739.9
45°	343.6	346.0	349.9	354.5	362.9	379.1	397.4	428.4	479.1	543.8	627.6
47.5°	311.0	311.1	315.0	319.1	324.0	333.2	348.2	367.6	403.3	456.1	528.1
50°	293.6	291.1	293.9	297.1	302.4	308.7	318.6	336.9	360.8	403.4	463.5
52.5°	272.2	272.2	274.8	276.0	280.7	287.0	296.1	308.7	330.4	363.7	413.2
55°	241.5	243.3	244.7	246.8	251.0	255.5	262.6	271.1	287.9	312.9	349.5
57.5°	212.6	213.2	214.6	218.6	221.3	225.5	232.1	239.9	250.8	269.4	296.9
60°	192.9	192.9	195.7	197.5	201.0	205.2	210.5	217.9	227.7	242.9	265.0
62.5°	174.8	174.6	175.7	178.6	181.3	185.2	190.5	196.8	206.0	219.5	237.7
65°	148.5	147.9	150.0	150.6	153.4	157.3	161.6	168.2	175.7	185.5	201.7
67.5°	123.2	124.0	125.2	126.5	128.1	132.1	135.0	139.7	145.9	154.1	165.1
70°	109.1	109.1	109.1	110.2	112.3	114.4	117.3	121.1	127.1	134.1	143.9
72.5°	93.3	94.4	95.6	95.0	97.6	98.9	102.3	104.4	110.2	114.7	123.4
75°	73.2	73.2	73.2	74.9	76.1	77.1	79.2	81.3	84.2	89.7	94.3
77.5°	54.7	54.5	54.9	55.2	56.4	57.7	58.2	60.2	62.8	65.4	69.3
80°	42.2	43.0	43.3	44.0	44.0	44.7	45.1	47.5	49.3	51.1	53.5
82.5°	32.7	32.8	32.9	33.0	33.3	33.7	34.6	35.4	36.0	37.5	39.4
85°	19.0	18.7	18.7	19.3	19.0	19.0	19.7	20.5	20.5	20.7	21.9
87.5°	10.8	10.8	11.0	10.7	10.7	10.8	10.7	10.3	10.4	10.6	10.6
90°	17.8	17.5	17.2	17.0	16.7	16.1	15.4	14.7	13.9	13.2	12.1
92.5°	17.8	17.6	17.4	17.2	17.2	16.9	16.5	16.1	15.6	15.3	14.7
95°	28.4	28.6	28.7	28.8	28.9	28.7	27.9	27.2	26.5	25.7	24.7
97.5°	37.9	37.7	37.5	37.3	37.1	36.8	36.2	35.6	35.1	34.4	32.0
100°	44.2	43.9	43.6	43.4	43.1	42.3	41.1	40.0	38.7	37.6	35.2
102.5°	47.4	46.9	46.6	46.2	45.7	44.8	43.3	41.8	40.2	38.6	35.5
105°	50.1	49.6	49.0	48.4	47.8	46.7	45.1	43.5	41.8	40.2	38.3
107.5°	51.6	51.0	50.4	49.9	49.3	49.8	51.5	53.1	54.7	56.4	104.3
110°	52.1	51.6	51.0	50.3	49.8	56.8	71.4	86.1	100.9	115.5	157.9



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	52.7	52.2	51.7	51.3	50.8	77.3	130.8	184.3	237.8	291.2	301.7
115°	54.1	64.7	75.2	85.8	96.3	135.5	203.4	271.4	339.2	407.1	403.4
117.5°	220.9	255.6	290.3	325.0	359.7	385.2	401.6	418.1	434.5	450.9	448.4
120°	402.5	422.3	442.1	461.8	481.6	490.7	488.9	487.2	485.4	483.6	481.0
122.5°	502.3	506.1	509.9	513.8	517.6	519.1	517.9	516.9	515.9	514.8	511.9
125°	564.1	563.7	563.3	562.8	562.4	561.7	560.6	559.6	558.6	557.5	554.8
127.5°	603.2	603.1	603.0	602.9	602.9	602.1	600.6	599.1	597.6	596.1	594.0
130°	627.5	627.6	627.8	627.9	628.1	627.4	625.8	624.2	622.5	620.9	619.3
132.5°	651.3	651.4	651.6	651.7	651.9	651.2	649.9	648.5	647.1	645.7	644.1
135°	685.6	685.9	686.2	686.5	686.7	686.2	684.7	683.2	681.7	680.3	679.0
137.5°	716.8	717.4	717.8	718.3	718.9	718.4	716.9	715.5	714.1	712.7	711.1
140°	736.4	737.1	737.8	738.6	739.3	739.0	737.7	736.4	735.1	733.8	732.1
142.5°	755.4	756.1	756.9	757.6	758.3	758.1	756.9	755.6	754.5	753.3	751.4
145°	781.9	782.6	783.3	784.1	784.9	784.7	783.6	782.6	781.7	780.6	778.1
147.5°	805.2	805.9	806.5	807.1	807.8	807.7	806.9	806.2	805.4	804.6	802.1
150°	819.5	820.2	821.0	821.7	822.5	822.4	821.5	820.6	819.7	818.9	816.5
152.5°	831.6	832.6	833.6	834.5	835.6	835.6	834.7	833.8	832.9	832.1	829.8
155°	848.6	849.7	850.9	852.1	853.2	853.4	852.5	851.6	850.7	849.9	848.1
157.5°	863.9	865.2	866.3	867.4	868.6	868.6	867.6	866.7	865.6	864.6	863.4
160°	873.0	874.0	875.0	876.0	877.0	877.1	876.3	875.3	874.5	873.6	872.7
162.5°	880.3	881.6	882.9	884.1	885.4	885.5	884.5	883.5	882.5	881.6	880.8
165°	891.5	892.5	893.5	894.5	895.5	895.5	894.5	893.5	892.5	891.5	891.0
167.5°	898.4	899.8	901.1	902.4	903.7	903.8	902.9	901.8	900.8	899.8	899.4
170°	902.7	904.0	905.3	906.6	908.0	908.0	907.0	906.1	905.0	904.0	903.7
172.5°	905.8	907.1	908.4	909.7	911.1	911.3	910.2	909.2	908.1	907.1	906.8
175°	908.6	910.0	911.5	912.9	914.5	914.6	913.6	912.7	911.6	910.6	910.3
177.5°	910.3	911.3	912.4	913.5	914.5	914.6	913.8	913.0	912.2	911.3	911.3
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	939.8	937.5	936.1	931.1	926.6	922.1	920.7	921.2	915.0	909.2	906.6
5°	976.5	969.4	962.7	953.2	942.0	929.6	923.3	918.4	906.1	892.7	885.0
7.5°	1009.3	999.2	986.3	968.5	952.1	932.6	920.3	909.5	891.4	872.5	861.0
10°	1029.3	1015.5	999.0	977.1	957.1	933.5	917.0	900.4	879.3	856.8	842.7
12.5°	1046.4	1027.9	1011.6	983.6	959.9	930.4	910.8	887.5	865.3	838.5	824.6
15°	1087.3	1053.2	1022.2	990.5	961.3	920.1	898.3	867.0	837.7	804.6	788.8
17.5°	1118.9	1080.5	1031.8	991.6	957.4	911.8	879.8	842.3	807.7	769.9	748.4
20°	1137.0	1093.0	1040.5	992.7	951.8	899.8	864.9	826.5	786.0	743.4	720.2
22.5°	1147.6	1101.5	1049.5	988.4	940.6	889.9	846.0	804.0	762.9	717.0	692.6
25°	1151.0	1108.8	1053.9	984.9	926.4	869.1	816.2	775.4	725.9	682.9	647.3
27.5°	1134.3	1104.0	1051.2	978.3	910.2	843.1	784.3	738.0	685.6	639.0	603.2
30°	1113.7	1096.1	1044.7	971.5	897.2	825.1	760.3	707.8	655.8	608.6	572.0
32.5°	1081.9	1078.1	1032.9	962.0	883.4	802.3	735.3	682.2	624.5	578.2	543.3
35°	1019.4	1036.3	1007.8	940.6	857.4	769.9	697.3	636.8	576.9	532.5	499.8
37.5°	935.7	977.6	970.2	909.2	822.4	734.5	654.4	591.2	534.1	489.4	457.2
40°	877.9	931.4	939.1	885.2	797.7	707.2	622.4	559.3	503.7	462.9	430.5
42.5°	816.0	878.4	899.8	856.6	770.6	678.4	593.6	528.4	473.3	433.6	404.9
45°	712.1	794.8	833.2	808.5	725.5	631.1	543.8	477.7	427.7	390.4	368.2
47.5°	615.0	705.4	757.1	748.3	675.2	581.8	495.6	432.1	383.4	353.6	333.8
50°	546.3	639.2	701.5	704.4	639.2	546.7	460.1	400.2	355.5	327.7	311.5
52.5°	486.6	575.3	643.3	658.2	599.0	510.0	428.2	368.7	329.3	303.8	289.3
55°	408.7	483.6	559.0	586.4	538.9	454.4	378.7	326.3	289.4	271.7	259.1
57.5°	339.8	402.3	471.8	502.2	472.9	400.6	329.6	284.1	254.1	238.7	228.9
60°	303.4	352.7	414.6	450.9	425.6	361.2	299.2	255.9	231.3	217.5	208.4
62.5°	269.7	313.3	365.6	398.8	385.0	324.2	268.8	230.5	209.3	196.4	189.8
65°	222.4	256.9	297.5	328.1	319.0	272.8	227.4	194.6	177.8	167.6	162.3
67.5°	183.1	208.1	236.2	263.0	255.6	222.9	186.5	161.0	148.4	139.6	136.5
70°	158.4	177.4	202.4	223.9	217.9	191.1	162.3	140.4	129.5	122.2	118.9
72.5°	134.8	150.3	169.5	187.0	182.9	160.7	136.7	120.2	111.8	105.0	102.4
75°	101.7	113.7	125.4	137.0	135.9	118.7	104.5	91.9	85.2	79.9	78.9
77.5°	75.1	81.8	89.7	96.6	94.7	84.8	73.8	66.5	61.6	58.1	57.5
80°	57.4	61.3	66.9	71.8	69.4	65.1	56.4	51.1	47.5	44.0	42.6
82.5°	41.6	45.5	48.8	51.6	49.7	45.7	40.2	36.7	34.6	32.1	31.6
85°	21.9	23.9	25.4	26.0	25.4	22.9	20.5	19.0	17.2	16.2	15.8
87.5°	10.7	10.4	10.2	10.5	9.2	9.0	7.5	6.3	6.4	6.4	6.1
90°	10.8	9.7	8.5	7.1	5.5	3.9	2.3	0.7	2.3	3.9	5.5
92.5°	14.1	13.6	13.0	12.7	12.9	13.0	13.2	13.3	13.2	13.0	12.9
95°	23.7	22.6	21.6	23.6	28.4	33.2	38.1	42.9	38.1	33.2	28.4
97.5°	29.7	27.3	25.0	30.5	44.2	57.9	71.4	85.1	71.4	57.9	44.2
100°	32.6	30.2	27.6	36.5	56.6	76.6	96.7	116.8	96.7	76.6	56.6
102.5°	80.4	101.2	122.1	134.6	138.8	143.1	147.4	151.7	147.4	143.1	138.8
105°	120.3	160.3	200.4	218.2	213.8	209.4	205.0	200.6	205.0	209.4	213.8
107.5°	152.4	200.4	248.4	270.6	267.0	263.5	260.0	256.4	260.0	263.5	267.0
110°	200.2	242.6	284.9	304.6	301.5	298.5	295.4	292.3	295.4	298.5	301.5



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	312.2	322.6	333.1	337.0	334.2	331.6	328.9	326.1	328.9	331.6	334.2
115°	399.8	396.2	392.5	389.4	386.9	384.4	381.9	379.4	381.9	384.4	386.9
117.5°	445.9	443.4	440.8	438.2	435.4	432.6	429.8	427.1	429.8	432.6	435.4
120°	478.3	475.7	473.1	470.7	468.4	466.3	464.1	461.8	464.1	466.3	468.4
122.5°	509.1	506.1	503.3	500.7	498.4	496.1	493.8	491.4	493.8	496.1	498.4
125°	552.0	549.2	546.4	544.0	542.2	540.3	538.4	536.4	538.4	540.3	542.2
127.5°	591.9	589.8	587.8	585.7	583.5	581.5	579.3	577.2	579.3	581.5	583.5
130°	617.6	616.0	614.4	612.5	610.1	607.8	605.4	603.0	605.4	607.8	610.1
132.5°	642.4	640.8	639.2	637.4	635.5	633.5	631.5	629.5	631.5	633.5	635.5
135°	677.7	676.4	675.0	673.2	670.8	668.5	666.1	663.8	666.1	668.5	670.8
137.5°	709.6	708.1	706.6	705.0	703.4	701.8	700.1	698.5	700.1	701.8	703.4
140°	730.5	728.9	727.3	725.9	724.7	723.5	722.4	721.2	722.4	723.5	724.7
142.5°	749.6	747.7	745.8	744.4	743.4	742.3	741.2	740.2	741.2	742.3	743.4
145°	775.6	773.1	770.6	769.4	769.6	769.8	769.9	770.1	769.9	769.8	769.6
147.5°	799.7	797.2	794.8	793.8	794.4	794.9	795.5	796.0	795.5	794.9	794.4
150°	814.2	811.8	809.5	808.8	809.8	810.9	811.9	812.9	811.9	810.9	809.8
152.5°	827.6	825.4	823.1	822.6	823.7	824.9	826.0	827.2	826.0	824.9	823.7
155°	846.3	844.6	842.8	842.6	844.0	845.3	846.6	847.9	846.6	845.3	844.0
157.5°	862.1	860.9	859.7	859.7	860.7	861.9	863.0	864.1	863.0	861.9	860.7
160°	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6	872.7	871.9	871.0
162.5°	880.1	879.2	878.4	878.5	879.4	880.3	881.2	882.0	881.2	880.3	879.4
165°	890.5	890.1	889.7	889.9	890.8	891.6	892.5	893.4	892.5	891.6	890.8
167.5°	898.9	898.5	898.1	898.3	899.2	900.1	901.0	901.8	901.0	900.1	899.2
170°	903.4	903.1	902.8	903.1	904.0	904.8	905.7	906.6	905.7	904.8	904.0
172.5°	906.5	906.3	906.0	906.3	907.1	908.0	908.9	909.7	908.9	908.0	907.1
175°	910.0	909.6	909.4	909.7	910.8	911.8	912.9	913.9	912.9	911.8	910.8
177.5°	911.2	911.0	910.9	911.3	912.1	912.9	913.7	914.5	913.7	912.9	912.1
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	903.8	902.1	896.2	893.1	888.1	883.3	880.1	881.6	882.7	882.1	881.3
5°	877.9	871.2	861.0	852.2	845.8	834.2	829.3	826.9	824.7	822.3	819.8
7.5°	847.1	836.5	821.9	809.4	797.5	783.1	774.9	769.9	764.8	759.2	754.3
10°	825.1	810.3	794.8	777.2	763.2	750.1	738.5	730.8	723.7	717.0	712.1
12.5°	802.0	784.9	765.8	741.8	726.2	707.6	705.9	692.2	681.2	677.0	671.3
15°	765.3	741.3	717.0	688.5	676.2	659.3	648.8	638.2	628.7	622.0	620.2
17.5°	723.5	692.5	668.4	647.9	627.7	610.4	600.7	592.2	584.4	575.4	574.3
20°	691.6	665.0	638.6	620.6	599.8	582.2	570.2	561.8	555.1	549.8	545.3
22.5°	661.6	632.3	608.1	588.4	568.0	553.7	544.3	536.2	530.7	524.8	520.5
25°	613.2	590.3	563.9	541.8	524.8	515.7	507.9	500.9	497.4	493.5	488.6
27.5°	570.9	545.4	520.8	503.6	488.7	480.6	475.1	470.3	467.0	464.8	461.9
30°	541.0	515.3	496.0	479.1	466.7	458.6	455.2	452.3	448.5	447.0	445.6
32.5°	512.3	489.2	472.6	458.0	446.2	440.9	437.7	435.2	432.2	430.7	427.9
35°	471.6	452.3	436.1	428.0	418.5	414.0	411.5	407.9	405.2	403.8	403.4
37.5°	433.5	416.6	406.0	395.6	391.5	388.7	385.4	383.0	382.1	381.9	381.5
40°	408.7	394.9	385.4	377.0	375.2	371.0	368.2	366.1	366.1	366.5	366.1
42.5°	386.2	373.8	365.4	358.2	356.1	353.5	350.7	350.6	351.2	352.3	351.2
45°	352.0	343.2	337.2	333.7	329.8	327.3	327.0	328.1	328.4	328.8	329.8
47.5°	320.6	314.7	309.3	305.5	303.8	303.3	302.9	304.7	306.4	307.1	308.7
50°	302.0	295.3	290.8	288.3	286.9	286.2	286.9	289.0	290.4	292.2	293.2
52.5°	281.2	276.4	273.3	271.4	270.8	271.3	271.4	273.8	276.1	276.6	277.2
55°	252.4	248.8	248.2	245.0	246.4	246.0	247.8	249.2	251.3	253.4	253.8
57.5°	223.7	220.8	219.0	219.2	219.6	221.2	222.6	225.2	227.4	229.6	229.9
60°	204.5	203.1	202.1	202.1	202.7	204.9	206.6	209.1	210.5	211.9	212.9
62.5°	187.1	185.7	184.5	185.1	187.0	188.2	190.3	191.6	193.0	194.4	194.9
65°	159.5	158.7	159.9	160.5	160.9	162.6	165.1	166.2	167.6	168.2	170.7
67.5°	134.0	134.2	134.0	135.1	137.0	137.5	139.8	142.3	142.6	143.9	145.5
70°	116.9	117.5	118.3	118.9	120.7	121.4	123.2	124.2	125.6	126.7	127.8
72.5°	101.1	101.2	102.0	101.8	103.3	104.8	106.3	107.4	108.8	110.1	111.1
75°	77.8	77.8	78.5	78.9	80.6	82.4	82.0	82.8	84.2	85.6	86.2
77.5°	56.8	56.1	56.8	57.1	57.7	59.2	59.5	60.5	62.1	61.6	62.4
80°	43.3	42.2	43.3	43.6	43.6	45.4	45.4	46.1	47.1	46.1	47.1
82.5°	30.9	30.4	31.2	31.3	31.9	31.9	32.4	32.6	33.6	33.2	33.6
85°	15.5	15.2	15.5	15.2	15.5	15.8	15.8	15.5	15.5	16.2	15.2
87.5°	6.2	6.2	6.1	6.4	6.3	6.3	6.1	6.3	6.5	6.0	6.1
90°	7.1	8.5	9.7	10.8	12.1	13.2	13.9	14.7	15.4	16.1	16.7
92.5°	12.7	13.0	13.6	14.1	14.7	15.3	15.6	16.1	16.5	16.9	17.2
95°	23.6	21.6	22.6	23.7	24.7	25.7	26.5	27.2	27.9	28.7	28.9
97.5°	30.5	25.0	27.3	29.7	32.0	34.4	35.1	35.6	36.2	36.8	37.1
100°	36.5	27.6	30.2	32.6	35.2	37.6	38.7	40.0	41.1	42.3	43.1
102.5°	134.6	122.1	101.2	80.4	59.5	38.6	40.2	41.8	43.3	44.8	45.7
105°	218.2	200.4	160.3	120.3	80.3	40.2	41.8	43.5	45.1	46.7	47.8
107.5°	270.6	248.4	200.4	152.4	104.3	56.4	54.7	53.1	51.5	49.8	49.3
110°	304.6	284.9	242.6	200.2	157.9	115.5	100.9	86.1	71.4	56.8	49.8



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	337.0	333.1	322.6	312.2	301.7	291.2	237.8	184.3	130.8	77.3	50.8
115°	389.4	392.5	396.2	399.8	403.4	407.1	339.2	271.4	203.4	135.5	96.3
117.5°	438.2	440.8	443.4	445.9	448.4	450.9	434.5	418.1	401.6	385.2	359.7
120°	470.7	473.1	475.7	478.3	481.0	483.6	485.4	487.2	488.9	490.7	481.6
122.5°	500.7	503.3	506.1	509.1	511.9	514.8	515.9	516.9	517.9	519.1	517.6
125°	544.0	546.4	549.2	552.0	554.8	557.5	558.6	559.6	560.6	561.7	562.4
127.5°	585.7	587.8	589.8	591.9	594.0	596.1	597.6	599.1	600.6	602.1	602.9
130°	612.5	614.4	616.0	617.6	619.3	620.9	622.5	624.2	625.8	627.4	628.1
132.5°	637.4	639.2	640.8	642.4	644.1	645.7	647.1	648.5	649.9	651.2	651.9
135°	673.2	675.0	676.4	677.7	679.0	680.3	681.7	683.2	684.7	686.2	686.7
137.5°	705.0	706.6	708.1	709.6	711.1	712.7	714.1	715.5	716.9	718.4	718.9
140°	725.9	727.3	728.9	730.5	732.1	733.8	735.1	736.4	737.7	739.0	739.3
142.5°	744.4	745.8	747.7	749.6	751.4	753.3	754.5	755.6	756.9	758.1	758.3
145°	769.4	770.6	773.1	775.6	778.1	780.6	781.7	782.6	783.6	784.7	784.9
147.5°	793.8	794.8	797.2	799.7	802.1	804.6	805.4	806.2	806.9	807.7	807.8
150°	808.8	809.5	811.8	814.2	816.5	818.9	819.7	820.6	821.5	822.4	822.5
152.5°	822.6	823.1	825.4	827.6	829.8	832.1	832.9	833.8	834.7	835.6	835.6
155°	842.6	842.8	844.6	846.3	848.1	849.9	850.7	851.6	852.5	853.4	853.2
157.5°	859.7	859.7	860.9	862.1	863.4	864.6	865.6	866.7	867.6	868.6	868.6
160°	870.1	870.1	871.0	871.9	872.7	873.6	874.5	875.3	876.3	877.1	877.0
162.5°	878.5	878.4	879.2	880.1	880.8	881.6	882.5	883.5	884.5	885.5	885.4
165°	889.9	889.7	890.1	890.5	891.0	891.5	892.5	893.5	894.5	895.5	895.5
167.5°	898.3	898.1	898.5	898.9	899.4	899.8	900.8	901.8	902.9	903.8	903.7
170°	903.1	902.8	903.1	903.4	903.7	904.0	905.0	906.1	907.0	908.0	908.0
172.5°	906.3	906.0	906.3	906.5	906.8	907.1	908.1	909.2	910.2	911.3	911.1
175°	909.7	909.4	909.6	910.0	910.3	910.6	911.6	912.7	913.6	914.6	914.5
177.5°	911.3	910.9	911.0	911.2	911.3	911.3	912.2	913.0	913.8	914.6	914.5
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	878.4	877.9	877.9	875.3	877.9	877.9	878.4	881.3	882.1	882.7	881.6
5°	814.9	813.8	812.1	813.8	812.1	813.8	814.9	819.8	822.3	824.7	826.9
7.5°	752.1	747.8	747.2	743.0	747.2	747.8	752.1	754.3	759.2	764.8	769.9
10°	706.2	703.3	702.9	696.3	702.9	703.3	706.2	712.1	717.0	723.7	730.8
12.5°	671.2	664.4	665.8	661.9	665.8	664.4	671.2	671.3	677.0	681.2	692.2
15°	610.7	610.7	609.4	603.3	609.4	610.7	610.7	620.2	622.0	628.7	638.2
17.5°	567.3	566.6	563.2	564.9	563.2	566.6	567.3	574.3	575.4	584.4	592.2
20°	541.4	539.2	535.1	535.1	535.1	539.2	541.4	545.3	549.8	555.1	561.8
22.5°	516.9	516.7	512.3	513.7	512.3	516.7	516.9	520.5	524.8	530.7	536.2
25°	488.2	485.4	483.3	484.4	483.3	485.4	488.2	488.6	493.5	497.4	500.9
27.5°	461.1	459.5	459.4	456.5	459.4	459.5	461.1	461.9	464.8	467.0	470.3
30°	445.3	441.8	442.4	440.7	442.4	441.8	445.3	445.6	447.0	448.5	452.3
32.5°	427.3	426.0	425.3	423.8	425.3	426.0	427.3	427.9	430.7	432.2	435.2
35°	402.7	403.0	401.2	402.0	401.2	403.0	402.7	403.4	403.8	405.2	407.9
37.5°	381.3	382.4	381.5	381.7	381.5	382.4	381.3	381.5	381.9	382.1	383.0
40°	367.1	367.1	367.1	368.2	367.1	367.1	367.1	366.1	366.5	366.1	366.1
42.5°	353.6	353.1	352.5	352.4	352.5	353.1	353.6	351.2	352.3	351.2	350.6
45°	330.5	331.6	332.0	330.2	332.0	331.6	330.5	329.8	328.8	328.4	328.1
47.5°	309.6	309.7	309.6	311.1	309.6	309.7	309.6	308.7	307.1	306.4	304.7
50°	295.0	294.3	295.0	294.3	295.0	294.3	295.0	293.2	292.2	290.4	289.0
52.5°	279.5	279.7	279.2	279.1	279.2	279.7	279.5	277.2	276.6	276.1	273.8
55°	255.2	255.9	255.5	255.5	255.5	255.9	255.2	253.8	253.4	251.3	249.2
57.5°	230.1	230.7	231.2	229.6	231.2	230.7	230.1	229.9	229.6	227.4	225.2
60°	212.6	214.3	214.1	213.3	214.1	214.3	212.6	212.9	211.9	210.5	209.1
62.5°	196.5	197.2	197.1	197.0	197.1	197.2	196.5	194.9	194.4	193.0	191.6
65°	171.7	172.5	171.4	172.5	171.4	172.5	171.7	170.7	168.2	167.6	166.2
67.5°	145.1	145.3	146.1	146.6	146.1	145.3	145.1	145.5	143.9	142.6	142.3
70°	128.5	128.1	129.2	130.3	129.2	128.1	128.5	127.8	126.7	125.6	124.2
72.5°	111.0	111.8	111.4	112.3	111.4	111.8	111.0	111.1	110.1	108.8	107.4
75°	85.6	86.6	86.2	87.3	86.2	86.6	85.6	86.2	85.6	84.2	82.8
77.5°	61.8	61.9	61.8	62.4	61.8	61.9	61.8	62.4	61.6	62.1	60.5
80°	47.1	46.5	45.7	47.1	45.7	46.5	47.1	47.1	46.1	47.1	46.1
82.5°	32.8	33.3	32.5	32.5	32.5	33.3	32.8	33.6	33.2	33.6	32.6
85°	15.2	14.8	14.0	14.0	14.0	14.8	15.2	15.2	16.2	15.5	15.5
87.5°	6.2	5.9	6.0	5.8	6.0	5.9	6.2	6.1	6.0	6.5	6.3
90°	17.0	17.2	17.5	17.8	17.5	17.2	17.0	16.7	16.1	15.4	14.7
92.5°	17.2	17.4	17.6	17.8	17.6	17.4	17.2	17.2	16.9	16.5	16.1
95°	28.8	28.7	28.6	28.4	28.6	28.7	28.8	28.9	28.7	27.9	27.2
97.5°	37.3	37.5	37.7	37.9	37.7	37.5	37.3	37.1	36.8	36.2	35.6
100°	43.4	43.6	43.9	44.2	43.9	43.6	43.4	43.1	42.3	41.1	40.0
102.5°	46.2	46.6	46.9	47.4	46.9	46.6	46.2	45.7	44.8	43.3	41.8
105°	48.4	49.0	49.6	50.1	49.6	49.0	48.4	47.8	46.7	45.1	43.5
107.5°	49.9	50.4	51.0	51.6	51.0	50.4	49.9	49.3	49.8	51.5	53.1
110°	50.3	51.0	51.6	52.1	51.6	51.0	50.3	49.8	56.8	71.4	86.1



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	51.3	51.7	52.2	52.7	52.2	51.7	51.3	50.8	77.3	130.8	184.3
115°	85.8	75.2	64.7	54.1	64.7	75.2	85.8	96.3	135.5	203.4	271.4
117.5°	325.0	290.3	255.6	220.9	255.6	290.3	325.0	359.7	385.2	401.6	418.1
120°	461.8	442.1	422.3	402.5	422.3	442.1	461.8	481.6	490.7	488.9	487.2
122.5°	513.8	509.9	506.1	502.3	506.1	509.9	513.8	517.6	519.1	517.9	516.9
125°	562.8	563.3	563.7	564.1	563.7	563.3	562.8	562.4	561.7	560.6	559.6
127.5°	602.9	603.0	603.1	603.2	603.1	603.0	602.9	602.9	602.1	600.6	599.1
130°	627.9	627.8	627.6	627.5	627.6	627.8	627.9	628.1	627.4	625.8	624.2
132.5°	651.7	651.6	651.4	651.3	651.4	651.6	651.7	651.9	651.2	649.9	648.5
135°	686.5	686.2	685.9	685.6	685.9	686.2	686.5	686.7	686.2	684.7	683.2
137.5°	718.3	717.8	717.4	716.8	717.4	717.8	718.3	718.9	718.4	716.9	715.5
140°	738.6	737.8	737.1	736.4	737.1	737.8	738.6	739.3	739.0	737.7	736.4
142.5°	757.6	756.9	756.1	755.4	756.1	756.9	757.6	758.3	758.1	756.9	755.6
145°	784.1	783.3	782.6	781.9	782.6	783.3	784.1	784.9	784.7	783.6	782.6
147.5°	807.1	806.5	805.9	805.2	805.9	806.5	807.1	807.8	807.7	806.9	806.2
150°	821.7	821.0	820.2	819.5	820.2	821.0	821.7	822.5	822.4	821.5	820.6
152.5°	834.5	833.6	832.6	831.6	832.6	833.6	834.5	835.6	835.6	834.7	833.8
155°	852.1	850.9	849.7	848.6	849.7	850.9	852.1	853.2	853.4	852.5	851.6
157.5°	867.4	866.3	865.2	863.9	865.2	866.3	867.4	868.6	868.6	867.6	866.7
160°	876.0	875.0	874.0	873.0	874.0	875.0	876.0	877.0	877.1	876.3	875.3
162.5°	884.1	882.9	881.6	880.3	881.6	882.9	884.1	885.4	885.5	884.5	883.5
165°	894.5	893.5	892.5	891.5	892.5	893.5	894.5	895.5	895.5	894.5	893.5
167.5°	902.4	901.1	899.8	898.4	899.8	901.1	902.4	903.7	903.8	902.9	901.8
170°	906.6	905.3	904.0	902.7	904.0	905.3	906.6	908.0	908.0	907.0	906.1
172.5°	909.7	908.4	907.1	905.8	907.1	908.4	909.7	911.1	911.3	910.2	909.2
175°	912.9	911.5	910.0	908.6	910.0	911.5	912.9	914.5	914.6	913.6	912.7
177.5°	913.5	912.4	911.3	910.3	911.3	912.4	913.5	914.5	914.6	913.8	913.0
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	880.1	883.3	888.1	893.1	896.2	902.1	903.8	906.6	909.2	915.0	921.2
5°	829.3	834.2	845.8	852.2	861.0	871.2	877.9	885.0	892.7	906.1	918.4
7.5°	774.9	783.1	797.5	809.4	821.9	836.5	847.1	861.0	872.5	891.4	909.5
10°	738.5	750.1	763.2	777.2	794.8	810.3	825.1	842.7	856.8	879.3	900.4
12.5°	705.9	707.6	726.2	741.8	765.8	784.9	802.0	824.6	838.5	865.3	887.5
15°	648.8	659.3	676.2	688.5	717.0	741.3	765.3	788.8	804.6	837.7	867.0
17.5°	600.7	610.4	627.7	647.9	668.4	692.5	723.5	748.4	769.9	807.7	842.3
20°	570.2	582.2	599.8	620.6	638.6	665.0	691.6	720.2	743.4	786.0	826.5
22.5°	544.3	553.7	568.0	588.4	608.1	632.3	661.6	692.6	717.0	762.9	804.0
25°	507.9	515.7	524.8	541.8	563.9	590.3	613.2	647.3	682.9	725.9	775.4
27.5°	475.1	480.6	488.7	503.6	520.8	545.4	570.9	603.2	639.0	685.6	738.0
30°	455.2	458.6	466.7	479.1	496.0	515.3	541.0	572.0	608.6	655.8	707.8
32.5°	437.7	440.9	446.2	458.0	472.6	489.2	512.3	543.3	578.2	624.5	682.2
35°	411.5	414.0	418.5	428.0	436.1	452.3	471.6	499.8	532.5	576.9	636.8
37.5°	385.4	388.7	391.5	395.6	406.0	416.6	433.5	457.2	489.4	534.1	591.2
40°	368.2	371.0	375.2	377.0	385.4	394.9	408.7	430.5	462.9	503.7	559.3
42.5°	350.7	353.5	356.1	358.2	365.4	373.8	386.2	404.9	433.6	473.3	528.4
45°	327.0	327.3	329.8	333.7	337.2	343.2	352.0	368.2	390.4	427.7	477.7
47.5°	302.9	303.3	303.8	305.5	309.3	314.7	320.6	333.8	353.6	383.4	432.1
50°	286.9	286.2	286.9	288.3	290.8	295.3	302.0	311.5	327.7	355.5	400.2
52.5°	271.4	271.3	270.8	271.4	273.3	276.4	281.2	289.3	303.8	329.3	368.7
55°	247.8	246.0	246.4	245.0	248.2	248.8	252.4	259.1	271.7	289.4	326.3
57.5°	222.6	221.2	219.6	219.2	219.0	220.8	223.7	228.9	238.7	254.1	284.1
60°	206.6	204.9	202.7	202.1	202.1	203.1	204.5	208.4	217.5	231.3	255.9
62.5°	190.3	188.2	187.0	185.1	184.5	185.7	187.1	189.8	196.4	209.3	230.5
65°	165.1	162.6	160.9	160.5	159.9	158.7	159.5	162.3	167.6	177.8	194.6
67.5°	139.8	137.5	137.0	135.1	134.0	134.2	134.0	136.5	139.6	148.4	161.0
70°	123.2	121.4	120.7	118.9	118.3	117.5	116.9	118.9	122.2	129.5	140.4
72.5°	106.3	104.8	103.3	101.8	102.0	101.2	101.1	102.4	105.0	111.8	120.2
75°	82.0	82.4	80.6	78.9	78.5	77.8	77.8	78.9	79.9	85.2	91.9
77.5°	59.5	59.2	57.7	57.1	56.8	56.1	56.8	57.5	58.1	61.6	66.5
80°	45.4	45.4	43.6	43.6	43.3	42.2	43.3	42.6	44.0	47.5	51.1
82.5°	32.4	31.9	31.9	31.3	31.2	30.4	30.9	31.6	32.1	34.6	36.7
85°	15.8	15.8	15.5	15.2	15.5	15.2	15.5	15.8	16.2	17.2	19.0
87.5°	6.1	6.3	6.3	6.4	6.1	6.2	6.2	6.1	6.4	6.4	6.3
90°	13.9	13.2	12.1	10.8	9.7	8.5	7.1	5.5	3.9	2.3	0.7
92.5°	15.6	15.3	14.7	14.1	13.6	13.0	12.7	12.9	13.0	13.2	13.3
95°	26.5	25.7	24.7	23.7	22.6	21.6	23.6	28.4	33.2	38.1	42.9
97.5°	35.1	34.4	32.0	29.7	27.3	25.0	30.5	44.2	57.9	71.4	85.1
100°	38.7	37.6	35.2	32.6	30.2	27.6	36.5	56.6	76.6	96.7	116.8
102.5°	40.2	38.6	59.5	80.4	101.2	122.1	134.6	138.8	143.1	147.4	151.7
105°	41.8	40.2	80.3	120.3	160.3	200.4	218.2	213.8	209.4	205.0	200.6
107.5°	54.7	56.4	104.3	152.4	200.4	248.4	270.6	267.0	263.5	260.0	256.4
110°	100.9	115.5	157.9	200.2	242.6	284.9	304.6	301.5	298.5	295.4	292.3



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	237.8	291.2	301.7	312.2	322.6	333.1	337.0	334.2	331.6	328.9	326.1
115°	339.2	407.1	403.4	399.8	396.2	392.5	389.4	386.9	384.4	381.9	379.4
117.5°	434.5	450.9	448.4	445.9	443.4	440.8	438.2	435.4	432.6	429.8	427.1
120°	485.4	483.6	481.0	478.3	475.7	473.1	470.7	468.4	466.3	464.1	461.8
122.5°	515.9	514.8	511.9	509.1	506.1	503.3	500.7	498.4	496.1	493.8	491.4
125°	558.6	557.5	554.8	552.0	549.2	546.4	544.0	542.2	540.3	538.4	536.4
127.5°	597.6	596.1	594.0	591.9	589.8	587.8	585.7	583.5	581.5	579.3	577.2
130°	622.5	620.9	619.3	617.6	616.0	614.4	612.5	610.1	607.8	605.4	603.0
132.5°	647.1	645.7	644.1	642.4	640.8	639.2	637.4	635.5	633.5	631.5	629.5
135°	681.7	680.3	679.0	677.7	676.4	675.0	673.2	670.8	668.5	666.1	663.8
137.5°	714.1	712.7	711.1	709.6	708.1	706.6	705.0	703.4	701.8	700.1	698.5
140°	735.1	733.8	732.1	730.5	728.9	727.3	725.9	724.7	723.5	722.4	721.2
142.5°	754.5	753.3	751.4	749.6	747.7	745.8	744.4	743.4	742.3	741.2	740.2
145°	781.7	780.6	778.1	775.6	773.1	770.6	769.4	769.6	769.8	769.9	770.1
147.5°	805.4	804.6	802.1	799.7	797.2	794.8	793.8	794.4	794.9	795.5	796.0
150°	819.7	818.9	816.5	814.2	811.8	809.5	808.8	809.8	810.9	811.9	812.9
152.5°	832.9	832.1	829.8	827.6	825.4	823.1	822.6	823.7	824.9	826.0	827.2
155°	850.7	849.9	848.1	846.3	844.6	842.8	842.6	844.0	845.3	846.6	847.9
157.5°	865.6	864.6	863.4	862.1	860.9	859.7	859.7	860.7	861.9	863.0	864.1
160°	874.5	873.6	872.7	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6
162.5°	882.5	881.6	880.8	880.1	879.2	878.4	878.5	879.4	880.3	881.2	882.0
165°	892.5	891.5	891.0	890.5	890.1	889.7	889.9	890.8	891.6	892.5	893.4
167.5°	900.8	899.8	899.4	898.9	898.5	898.1	898.3	899.2	900.1	901.0	901.8
170°	905.0	904.0	903.7	903.4	903.1	902.8	903.1	904.0	904.8	905.7	906.6
172.5°	908.1	907.1	906.8	906.5	906.3	906.0	906.3	907.1	908.0	908.9	909.7
175°	911.6	910.6	910.3	910.0	909.6	909.4	909.7	910.8	911.8	912.9	913.9
177.5°	912.2	911.3	911.3	911.2	911.0	910.9	911.3	912.1	912.9	913.7	914.5
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	920.7	922.1	926.6	931.1	936.1	937.5	939.8	937.8	937.3	942.6	946.6
5°	923.3	929.6	942.0	953.2	962.7	969.4	976.5	979.3	984.6	991.9	1001.1
7.5°	920.3	932.6	952.1	968.5	986.3	999.2	1009.3	1017.9	1028.2	1042.3	1057.5
10°	917.0	933.5	957.1	977.1	999.0	1015.5	1029.3	1042.6	1058.1	1077.5	1097.5
12.5°	910.8	930.4	959.9	983.6	1011.6	1027.9	1046.4	1075.3	1091.9	1118.9	1147.1
15°	898.3	920.1	961.3	990.5	1022.2	1053.2	1087.3	1114.7	1142.3	1158.1	1197.9
17.5°	879.8	911.8	957.4	991.6	1031.8	1080.5	1118.9	1150.1	1181.8	1207.4	1227.4
20°	864.9	899.8	951.8	992.7	1040.5	1093.0	1137.0	1168.7	1196.1	1217.6	1229.9
22.5°	846.0	889.9	940.6	988.4	1049.5	1101.5	1147.6	1172.6	1195.5	1206.0	1210.7
25°	816.2	869.1	926.4	984.9	1053.9	1108.8	1151.0	1166.2	1172.9	1162.6	1145.8
27.5°	784.3	843.1	910.2	978.3	1051.2	1104.0	1134.3	1131.9	1120.6	1087.5	1061.1
30°	760.3	825.1	897.2	971.5	1044.7	1096.1	1113.7	1096.1	1070.4	1033.5	995.8
32.5°	735.3	802.3	883.4	962.0	1032.9	1078.1	1081.9	1051.6	1011.8	969.9	922.8
35°	697.3	769.9	857.4	940.6	1007.8	1036.3	1019.4	965.9	918.7	861.4	797.3
37.5°	654.4	734.5	822.4	909.2	970.2	977.6	935.7	879.3	812.8	745.4	670.0
40°	622.4	707.2	797.7	885.2	939.1	931.4	877.9	816.0	736.7	654.4	584.3
42.5°	593.6	678.4	770.6	856.6	899.8	878.4	816.0	739.9	654.8	577.2	513.1
45°	543.8	631.1	725.5	808.5	833.2	794.8	712.1	627.6	543.8	479.1	428.4
47.5°	495.6	581.8	675.2	748.3	757.1	705.4	615.0	528.1	456.1	403.3	367.6
50°	460.1	546.7	639.2	704.4	701.5	639.2	546.3	463.5	403.4	360.8	336.9
52.5°	428.2	510.0	599.0	658.2	643.3	575.3	486.6	413.2	363.7	330.4	308.7
55°	378.7	454.4	538.9	586.4	559.0	483.6	408.7	349.5	312.9	287.9	271.1
57.5°	329.6	400.6	472.9	502.2	471.8	402.3	339.8	296.9	269.4	250.8	239.9
60°	299.2	361.2	425.6	450.9	414.6	352.7	303.4	265.0	242.9	227.7	217.9
62.5°	268.8	324.2	385.0	398.8	365.6	313.3	269.7	237.7	219.5	206.0	196.8
65°	227.4	272.8	319.0	328.1	297.5	256.9	222.4	201.7	185.5	175.7	168.2
67.5°	186.5	222.9	255.6	263.0	236.2	208.1	183.1	165.1	154.1	145.9	139.7
70°	162.3	191.1	217.9	223.9	202.4	177.4	158.4	143.9	134.1	127.1	121.1
72.5°	136.7	160.7	182.9	187.0	169.5	150.3	134.8	123.4	114.7	110.2	104.4
75°	104.5	118.7	135.9	137.0	125.4	113.7	101.7	94.3	89.7	84.2	81.3
77.5°	73.8	84.8	94.7	96.6	89.7	81.8	75.1	69.3	65.4	62.8	60.2
80°	56.4	65.1	69.4	71.8	66.9	61.3	57.4	53.5	51.1	49.3	47.5
82.5°	40.2	45.7	49.7	51.6	48.8	45.5	41.6	39.4	37.5	36.0	35.4
85°	20.5	22.9	25.4	26.0	25.4	23.9	21.9	21.9	20.7	20.5	20.5
87.5°	7.5	9.0	9.2	10.5	10.2	10.4	10.7	10.6	10.6	10.4	10.3
90°	2.3	3.9	5.5	7.1	8.5	9.7	10.8	12.1	13.2	13.9	14.7
92.5°	13.2	13.0	12.9	12.7	13.0	13.6	14.1	14.7	15.3	15.6	16.1
95°	38.1	33.2	28.4	23.6	21.6	22.6	23.7	24.7	25.7	26.5	27.2
97.5°	71.4	57.9	44.2	30.5	25.0	27.3	29.7	32.0	34.4	35.1	35.6
100°	96.7	76.6	56.6	36.5	27.6	30.2	32.6	35.2	37.6	38.7	40.0
102.5°	147.4	143.1	138.8	134.6	122.1	101.2	80.4	59.5	38.6	40.2	41.8
105°	205.0	209.4	213.8	218.2	200.4	160.3	120.3	80.3	40.2	41.8	43.5
107.5°	260.0	263.5	267.0	270.6	248.4	200.4	152.4	104.3	56.4	54.7	53.1
110°	295.4	298.5	301.5	304.6	284.9	242.6	200.2	157.9	115.5	100.9	86.1



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	328.9	331.6	334.2	337.0	333.1	322.6	312.2	301.7	291.2	237.8	184.3
115°	381.9	384.4	386.9	389.4	392.5	396.2	399.8	403.4	407.1	339.2	271.4
117.5°	429.8	432.6	435.4	438.2	440.8	443.4	445.9	448.4	450.9	434.5	418.1
120°	464.1	466.3	468.4	470.7	473.1	475.7	478.3	481.0	483.6	485.4	487.2
122.5°	493.8	496.1	498.4	500.7	503.3	506.1	509.1	511.9	514.8	515.9	516.9
125°	538.4	540.3	542.2	544.0	546.4	549.2	552.0	554.8	557.5	558.6	559.6
127.5°	579.3	581.5	583.5	585.7	587.8	589.8	591.9	594.0	596.1	597.6	599.1
130°	605.4	607.8	610.1	612.5	614.4	616.0	617.6	619.3	620.9	622.5	624.2
132.5°	631.5	633.5	635.5	637.4	639.2	640.8	642.4	644.1	645.7	647.1	648.5
135°	666.1	668.5	670.8	673.2	675.0	676.4	677.7	679.0	680.3	681.7	683.2
137.5°	700.1	701.8	703.4	705.0	706.6	708.1	709.6	711.1	712.7	714.1	715.5
140°	722.4	723.5	724.7	725.9	727.3	728.9	730.5	732.1	733.8	735.1	736.4
142.5°	741.2	742.3	743.4	744.4	745.8	747.7	749.6	751.4	753.3	754.5	755.6
145°	769.9	769.8	769.6	769.4	770.6	773.1	775.6	778.1	780.6	781.7	782.6
147.5°	795.5	794.9	794.4	793.8	794.8	797.2	799.7	802.1	804.6	805.4	806.2
150°	811.9	810.9	809.8	808.8	809.5	811.8	814.2	816.5	818.9	819.7	820.6
152.5°	826.0	824.9	823.7	822.6	823.1	825.4	827.6	829.8	832.1	832.9	833.8
155°	846.6	845.3	844.0	842.6	842.8	844.6	846.3	848.1	849.9	850.7	851.6
157.5°	863.0	861.9	860.7	859.7	859.7	860.9	862.1	863.4	864.6	865.6	866.7
160°	872.7	871.9	871.0	870.1	870.1	871.0	871.9	872.7	873.6	874.5	875.3
162.5°	881.2	880.3	879.4	878.5	878.4	879.2	880.1	880.8	881.6	882.5	883.5
165°	892.5	891.6	890.8	889.9	889.7	890.1	890.5	891.0	891.5	892.5	893.5
167.5°	901.0	900.1	899.2	898.3	898.1	898.5	898.9	899.4	899.8	900.8	901.8
170°	905.7	904.8	904.0	903.1	902.8	903.1	903.4	903.7	904.0	905.0	906.1
172.5°	908.9	908.0	907.1	906.3	906.0	906.3	906.5	906.8	907.1	908.1	909.2
175°	912.9	911.8	910.8	909.7	909.4	909.6	910.0	910.3	910.6	911.6	912.7
177.5°	913.7	912.9	912.1	911.3	910.9	911.0	911.2	911.3	911.3	912.2	913.0
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9	911.9



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	950.0	953.9	953.9	954.5	958.9	958.5	958.2
5°	1011.0	1016.9	1017.7	1024.0	1028.2	1026.8	1022.9
7.5°	1068.5	1079.6	1088.1	1092.8	1098.3	1101.7	1100.2
10°	1114.1	1130.3	1140.1	1146.8	1154.9	1160.9	1158.8
12.5°	1155.5	1174.8	1188.3	1199.8	1200.8	1208.5	1203.2
15°	1220.0	1240.5	1242.6	1251.0	1257.7	1257.0	1257.4
17.5°	1241.3	1247.9	1249.2	1249.4	1249.5	1247.1	1241.7
20°	1233.8	1231.3	1225.3	1220.8	1212.7	1211.5	1204.6
22.5°	1197.7	1189.9	1174.9	1165.0	1152.4	1149.1	1147.1
25°	1126.7	1109.5	1085.5	1062.7	1056.3	1044.1	1047.5
27.5°	1029.4	1002.5	976.6	958.0	941.2	922.7	928.0
30°	960.9	930.7	894.1	865.9	848.0	830.4	827.2
32.5°	879.3	834.9	794.1	769.3	741.8	730.7	718.5
35°	738.5	695.2	654.7	619.9	599.8	584.3	570.2
37.5°	611.8	562.0	529.3	501.1	486.6	477.8	479.9
40°	533.3	489.7	465.7	444.2	430.8	424.5	425.9
42.5°	469.7	437.0	417.3	402.6	393.1	389.6	388.7
45°	397.4	379.1	362.9	354.5	349.9	346.0	343.6
47.5°	348.2	333.2	324.0	319.1	315.0	311.1	311.0
50°	318.6	308.7	302.4	297.1	293.9	291.1	293.6
52.5°	296.1	287.0	280.7	276.0	274.8	272.2	272.2
55°	262.6	255.5	251.0	246.8	244.7	243.3	241.5
57.5°	232.1	225.5	221.3	218.6	214.6	213.2	212.6
60°	210.5	205.2	201.0	197.5	195.7	192.9	192.9
62.5°	190.5	185.2	181.3	178.6	175.7	174.6	174.8
65°	161.6	157.3	153.4	150.6	150.0	147.9	148.5
67.5°	135.0	132.1	128.1	126.5	125.2	124.0	123.2
70°	117.3	114.4	112.3	110.2	109.1	109.1	109.1
72.5°	102.3	98.9	97.6	95.0	95.6	94.4	93.3
75°	79.2	77.1	76.1	74.9	73.2	73.2	73.2
77.5°	58.2	57.7	56.4	55.2	54.9	54.5	54.7
80°	45.1	44.7	44.0	44.0	43.3	43.0	42.2
82.5°	34.6	33.7	33.3	33.0	32.9	32.8	32.7
85°	19.7	19.0	19.0	19.3	18.7	18.7	19.0
87.5°	10.7	10.8	10.7	10.7	11.0	10.8	10.8
90°	15.4	16.1	16.7	17.0	17.2	17.5	17.8
92.5°	16.5	16.9	17.2	17.2	17.4	17.6	17.8
95°	27.9	28.7	28.9	28.8	28.7	28.6	28.4
97.5°	36.2	36.8	37.1	37.3	37.5	37.7	37.9
100°	41.1	42.3	43.1	43.4	43.6	43.9	44.2
102.5°	43.3	44.8	45.7	46.2	46.6	46.9	47.4
105°	45.1	46.7	47.8	48.4	49.0	49.6	50.1
107.5°	51.5	49.8	49.3	49.9	50.4	51.0	51.6
110°	71.4	56.8	49.8	50.3	51.0	51.6	52.1



TEST NUMBER: P331501-830

CATALOG NUMBER: S122DIW-S485D710U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	130.8	77.3	50.8	51.3	51.7	52.2	52.7
115°	203.4	135.5	96.3	85.8	75.2	64.7	54.1
117.5°	401.6	385.2	359.7	325.0	290.3	255.6	220.9
120°	488.9	490.7	481.6	461.8	442.1	422.3	402.5
122.5°	517.9	519.1	517.6	513.8	509.9	506.1	502.3
125°	560.6	561.7	562.4	562.8	563.3	563.7	564.1
127.5°	600.6	602.1	602.9	602.9	603.0	603.1	603.2
130°	625.8	627.4	628.1	627.9	627.8	627.6	627.5
132.5°	649.9	651.2	651.9	651.7	651.6	651.4	651.3
135°	684.7	686.2	686.7	686.5	686.2	685.9	685.6
137.5°	716.9	718.4	718.9	718.3	717.8	717.4	716.8
140°	737.7	739.0	739.3	738.6	737.8	737.1	736.4
142.5°	756.9	758.1	758.3	757.6	756.9	756.1	755.4
145°	783.6	784.7	784.9	784.1	783.3	782.6	781.9
147.5°	806.9	807.7	807.8	807.1	806.5	805.9	805.2
150°	821.5	822.4	822.5	821.7	821.0	820.2	819.5
152.5°	834.7	835.6	835.6	834.5	833.6	832.6	831.6
155°	852.5	853.4	853.2	852.1	850.9	849.7	848.6
157.5°	867.6	868.6	868.6	867.4	866.3	865.2	863.9
160°	876.3	877.1	877.0	876.0	875.0	874.0	873.0
162.5°	884.5	885.5	885.4	884.1	882.9	881.6	880.3
165°	894.5	895.5	895.5	894.5	893.5	892.5	891.5
167.5°	902.9	903.8	903.7	902.4	901.1	899.8	898.4
170°	907.0	908.0	908.0	906.6	905.3	904.0	902.7
172.5°	910.2	911.3	911.1	909.7	908.4	907.1	905.8
175°	913.6	914.6	914.5	912.9	911.5	910.0	908.6
177.5°	913.8	914.6	914.5	913.5	912.4	911.3	910.3
180°	911.9	911.9	911.9	911.9	911.9	911.9	911.9

(END OF REPORT)