

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331507-830

Luminaire Tested: **S122DIW-S485D970U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331507-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D970U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5671.3 lumens
Efficiency: N/A
Efficacy: 125.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	38	38	37	31
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	61	50	42	37	56	46	39	34	38	32	29	30	26	24	23	20	19	15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14	11
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14788	14788	14788	14788
5°	16579	14885	13190	14885
10°	18998	14762	11416	14762
15°	21018	14492	10084	14492
20°	20697	14201	9194	14201
25°	18661	13814	8630	13814
30°	15422	13196	8216	13196
35°	11239	12552	7924	12552
40°	8977	11788	7761	11788
45°	7846	10908	7540	10908
50°	7375	10052	7392	10052
55°	6798	9185	7192	9185
60°	6229	8263	6888	8263
65°	5673	7435	6590	7435
70°	5150	6628	6151	6628
75°	4566	5733	5446	5733
80°	3924	4751	4379	4751
85°	3520	3520	2594	3520



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	1.5
10°-20°	253.6	4.5
20°-30°	368.0	6.5
30°-40°	388.4	6.8
40°-50°	343.9	6.1
50°-60°	274.4	4.8
60°-70°	186.5	3.3
70°-80°	95.6	1.7
80°-90°	26.1	0.5
90°-100°	41.5	0.7
100°-110°	152.3	2.7
110°-120°	407.0	7.2
120°-130°	671.8	11.8
130°-140°	714.5	12.6
140°-150°	664.1	11.7
150°-160°	533.9	9.4
160°-170°	344.1	6.1
170°-180°	118.4	2.1
0°-30°	708.8	12.5
0°-40°	1097.2	19.3
0°-60°	1715.5	30.2
0°-90°	2023.7	35.7
90°-120°	600.8	10.6
90°-150°	2651.1	46.7
90°-180°	3648.0	64.3
0°-180°	5671.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	916	916	916	916	916	
5°	1023	918	814	918	1023	102
15°	1257	867	603	867	1257	347
25°	1048	775	484	775	1048	473
35°	570	637	402	637	570	371
45°	344	478	330	478	344	270
55°	242	326	256	326	242	217
65°	148	195	172	195	148	148
75°	73	92	87	92	73	78
85°	19	19	14	19	19	21
90°	24	1	24	1	24	12
95°	39	58	39	58	39	36
105°	68	274	68	274	68	71
115°	74	518	74	518	74	185
125°	770	732	770	732	770	666
135°	936	906	936	906	936	721
145°	1067	1051	1067	1051	1067	667
155°	1158	1157	1158	1157	1158	534
165°	1217	1220	1217	1220	1217	344
175°	1240	1247	1240	1247	1240	118
180°	1245	1245	1245	1245	1245	



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	958.2	958.5	958.9	954.5	953.9	953.9	950.0	946.6	942.6	937.3	937.8
5°	1022.9	1026.8	1028.2	1024.0	1017.7	1016.9	1011.0	1001.1	991.9	984.6	979.3
7.5°	1100.2	1101.7	1098.3	1092.8	1088.1	1079.6	1068.5	1057.5	1042.3	1028.2	1017.9
10°	1158.8	1160.9	1154.9	1146.8	1140.1	1130.3	1114.1	1097.5	1077.5	1058.1	1042.6
12.5°	1203.2	1208.5	1200.8	1199.8	1188.3	1174.8	1155.5	1147.1	1118.9	1091.9	1075.3
15°	1257.4	1257.0	1257.7	1251.0	1242.6	1240.5	1220.0	1197.9	1158.1	1142.3	1114.7
17.5°	1241.7	1247.1	1249.5	1249.4	1249.2	1247.9	1241.3	1227.4	1207.4	1181.8	1150.1
20°	1204.6	1211.5	1212.7	1220.8	1225.3	1231.3	1233.8	1229.9	1217.6	1196.1	1168.7
22.5°	1147.1	1149.1	1152.4	1165.0	1174.9	1189.9	1197.7	1210.7	1206.0	1195.5	1172.6
25°	1047.5	1044.1	1056.3	1062.7	1085.5	1109.5	1126.7	1145.8	1162.6	1172.9	1166.2
27.5°	928.0	922.7	941.2	958.0	976.6	1002.5	1029.4	1061.1	1087.5	1120.6	1131.9
30°	827.2	830.4	848.0	865.9	894.1	930.7	960.9	995.8	1033.5	1070.4	1096.1
32.5°	718.5	730.7	741.8	769.3	794.1	834.9	879.3	922.8	969.9	1011.8	1051.6
35°	570.2	584.3	599.8	619.9	654.7	695.2	738.5	797.3	861.4	918.7	965.9
37.5°	479.9	477.8	486.6	501.1	529.3	562.0	611.8	670.0	745.4	812.8	879.3
40°	425.9	424.5	430.8	444.2	465.7	489.7	533.3	584.3	654.4	736.7	816.0
42.5°	388.7	389.6	393.1	402.6	417.3	437.0	469.7	513.1	577.2	654.8	739.9
45°	343.6	346.0	349.9	354.5	362.9	379.1	397.4	428.4	479.1	543.8	627.6
47.5°	311.0	311.1	315.0	319.1	324.0	333.2	348.2	367.6	403.3	456.1	528.1
50°	293.6	291.1	293.9	297.1	302.4	308.7	318.6	336.9	360.8	403.4	463.5
52.5°	272.2	272.2	274.8	276.0	280.7	287.0	296.1	308.7	330.4	363.7	413.2
55°	241.5	243.3	244.7	246.8	251.0	255.5	262.6	271.1	287.9	312.9	349.5
57.5°	212.6	213.2	214.6	218.6	221.3	225.5	232.1	239.9	250.8	269.4	296.9
60°	192.9	192.9	195.7	197.5	201.0	205.2	210.5	217.9	227.7	242.9	265.0
62.5°	174.8	174.6	175.7	178.6	181.3	185.2	190.5	196.8	206.0	219.5	237.7
65°	148.5	147.9	150.0	150.6	153.4	157.3	161.6	168.2	175.7	185.5	201.7
67.5°	123.2	124.0	125.2	126.5	128.1	132.1	135.0	139.7	145.9	154.1	165.1
70°	109.1	109.1	109.1	110.2	112.3	114.4	117.3	121.1	127.1	134.1	143.9
72.5°	93.3	94.4	95.6	95.0	97.6	98.9	102.3	104.4	110.2	114.7	123.4
75°	73.2	73.2	73.2	74.9	76.1	77.1	79.2	81.3	84.2	89.7	94.3
77.5°	54.7	54.5	54.9	55.2	56.4	57.7	58.2	60.2	62.8	65.4	69.3
80°	42.2	43.0	43.3	44.0	44.0	44.7	45.1	47.5	49.3	51.1	53.5
82.5°	32.7	32.8	32.9	33.0	33.3	33.7	34.6	35.4	36.0	37.5	39.4
85°	19.0	18.7	18.7	19.3	19.0	19.0	19.7	20.5	20.5	20.7	21.9
87.5°	12.2	12.1	12.3	12.0	11.9	12.0	11.8	11.3	11.4	11.5	11.4
90°	24.3	23.9	23.5	23.1	22.7	22.1	21.0	20.0	19.0	18.0	16.4
92.5°	24.3	24.0	23.8	23.6	23.4	23.0	22.4	22.0	21.4	20.9	20.1
95°	38.7	38.9	39.1	39.3	39.5	39.1	38.2	37.1	36.1	35.2	33.7
97.5°	51.7	51.5	51.2	51.0	50.7	50.2	49.4	48.6	47.8	47.0	43.7
100°	60.3	59.9	59.6	59.1	58.7	57.8	56.2	54.6	53.0	51.4	48.0
102.5°	64.7	64.1	63.5	63.0	62.4	61.1	59.0	56.9	54.9	52.8	48.1
105°	68.4	67.7	66.8	66.1	65.2	63.7	61.5	59.4	57.1	55.0	48.6
107.5°	70.4	69.7	68.8	68.1	67.2	68.0	70.2	72.4	74.6	76.9	71.4
110°	71.2	70.3	69.6	68.7	68.0	77.6	97.6	117.5	137.6	157.6	215.5



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	71.9	71.3	70.6	69.9	69.3	105.5	178.5	251.5	324.5	397.6	411.8
115°	73.9	88.2	102.6	117.1	131.5	185.0	277.7	370.3	463.0	555.7	550.7
117.5°	301.5	348.9	396.2	443.6	491.0	525.8	548.3	570.6	593.0	615.5	612.1
120°	549.4	576.4	603.4	630.5	657.4	669.8	667.3	665.0	662.6	660.2	656.6
122.5°	685.6	690.8	696.1	701.3	706.5	708.4	707.0	705.6	704.1	702.7	698.7
125°	770.1	769.4	768.8	768.3	767.6	766.7	765.3	763.8	762.4	761.0	757.2
127.5°	823.3	823.2	823.1	823.0	822.8	821.8	819.7	817.7	815.7	813.6	810.8
130°	856.5	856.7	856.9	857.1	857.3	856.3	854.1	851.9	849.7	847.5	845.3
132.5°	888.9	889.1	889.3	889.5	889.8	888.9	887.0	885.1	883.3	881.4	879.1
135°	935.8	936.1	936.5	937.0	937.4	936.5	934.5	932.6	930.6	928.6	926.7
137.5°	978.5	979.1	979.8	980.5	981.2	980.5	978.5	976.6	974.7	972.7	970.6
140°	1005.1	1006.1	1007.1	1008.1	1009.1	1008.7	1006.9	1005.1	1003.3	1001.5	999.3
142.5°	1031.0	1032.1	1033.0	1034.1	1035.0	1034.7	1033.1	1031.4	1029.8	1028.1	1025.7
145°	1067.2	1068.3	1069.2	1070.3	1071.3	1071.0	1069.7	1068.3	1066.9	1065.5	1062.1
147.5°	1099.1	1099.9	1100.8	1101.6	1102.5	1102.4	1101.4	1100.3	1099.3	1098.3	1094.9
150°	1118.6	1119.6	1120.6	1121.6	1122.6	1122.5	1121.2	1120.1	1118.9	1117.7	1114.5
152.5°	1135.2	1136.5	1137.8	1139.2	1140.5	1140.5	1139.3	1138.1	1136.9	1135.7	1132.7
155°	1158.2	1159.8	1161.4	1163.0	1164.6	1164.8	1163.6	1162.4	1161.2	1160.0	1157.6
157.5°	1179.3	1180.8	1182.4	1183.9	1185.5	1185.6	1184.3	1182.9	1181.6	1180.2	1178.5
160°	1191.6	1193.0	1194.3	1195.7	1197.1	1197.2	1196.0	1194.9	1193.6	1192.4	1191.3
162.5°	1201.6	1203.3	1205.0	1206.7	1208.5	1208.7	1207.3	1206.0	1204.6	1203.2	1202.2
165°	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4	1221.0	1219.6	1218.1	1216.7	1216.2
167.5°	1226.3	1228.1	1229.9	1231.7	1233.5	1233.7	1232.3	1230.9	1229.5	1228.1	1227.6
170°	1232.1	1233.9	1235.7	1237.5	1239.3	1239.4	1238.0	1236.7	1235.3	1233.9	1233.5
172.5°	1236.4	1238.2	1240.0	1241.8	1243.6	1243.8	1242.4	1241.0	1239.6	1238.2	1237.7
175°	1240.2	1242.2	1244.2	1246.1	1248.2	1248.5	1247.1	1245.7	1244.3	1242.8	1242.5
177.5°	1242.6	1244.0	1245.4	1246.8	1248.3	1248.4	1247.3	1246.2	1245.1	1244.0	1243.8
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	939.8	937.5	936.1	931.1	926.6	922.1	920.7	921.2	915.0	909.2	906.6
5°	976.5	969.4	962.7	953.2	942.0	929.6	923.3	918.4	906.1	892.7	885.0
7.5°	1009.3	999.2	986.3	968.5	952.1	932.6	920.3	909.5	891.4	872.5	861.0
10°	1029.3	1015.5	999.0	977.1	957.1	933.5	917.0	900.4	879.3	856.8	842.7
12.5°	1046.4	1027.9	1011.6	983.6	959.9	930.4	910.8	887.5	865.3	838.5	824.6
15°	1087.3	1053.2	1022.2	990.5	961.3	920.1	898.3	867.0	837.7	804.6	788.8
17.5°	1118.9	1080.5	1031.8	991.6	957.4	911.8	879.8	842.3	807.7	769.9	748.4
20°	1137.0	1093.0	1040.5	992.7	951.8	899.8	864.9	826.5	786.0	743.4	720.2
22.5°	1147.6	1101.5	1049.5	988.4	940.6	889.9	846.0	804.0	762.9	717.0	692.6
25°	1151.0	1108.8	1053.9	984.9	926.4	869.1	816.2	775.4	725.9	682.9	647.3
27.5°	1134.3	1104.0	1051.2	978.3	910.2	843.1	784.3	738.0	685.6	639.0	603.2
30°	1113.7	1096.1	1044.7	971.5	897.2	825.1	760.3	707.8	655.8	608.6	572.0
32.5°	1081.9	1078.1	1032.9	962.0	883.4	802.3	735.3	682.2	624.5	578.2	543.3
35°	1019.4	1036.3	1007.8	940.6	857.4	769.9	697.3	636.8	576.9	532.5	499.8
37.5°	935.7	977.6	970.2	909.2	822.4	734.5	654.4	591.2	534.1	489.4	457.2
40°	877.9	931.4	939.1	885.2	797.7	707.2	622.4	559.3	503.7	462.9	430.5
42.5°	816.0	878.4	899.8	856.6	770.6	678.4	593.6	528.4	473.3	433.6	404.9
45°	712.1	794.8	833.2	808.5	725.5	631.1	543.8	477.7	427.7	390.4	368.2
47.5°	615.0	705.4	757.1	748.3	675.2	581.8	495.6	432.1	383.4	353.6	333.8
50°	546.3	639.2	701.5	704.4	639.2	546.7	460.1	400.2	355.5	327.7	311.5
52.5°	486.6	575.3	643.3	658.2	599.0	510.0	428.2	368.7	329.3	303.8	289.3
55°	408.7	483.6	559.0	586.4	538.9	454.4	378.7	326.3	289.4	271.7	259.1
57.5°	339.8	402.3	471.8	502.2	472.9	400.6	329.6	284.1	254.1	238.7	228.9
60°	303.4	352.7	414.6	450.9	425.6	361.2	299.2	255.9	231.3	217.5	208.4
62.5°	269.7	313.3	365.6	398.8	385.0	324.2	268.8	230.5	209.3	196.4	189.8
65°	222.4	256.9	297.5	328.1	319.0	272.8	227.4	194.6	177.8	167.6	162.3
67.5°	183.1	208.1	236.2	263.0	255.6	222.9	186.5	161.0	148.4	139.6	136.5
70°	158.4	177.4	202.4	223.9	217.9	191.1	162.3	140.4	129.5	122.2	118.9
72.5°	134.8	150.3	169.5	187.0	182.9	160.7	136.7	120.2	111.8	105.0	102.4
75°	101.7	113.7	125.4	137.0	135.9	118.7	104.5	91.9	85.2	79.9	78.9
77.5°	75.1	81.8	89.7	96.6	94.7	84.8	73.8	66.5	61.6	58.1	57.5
80°	57.4	61.3	66.9	71.8	69.4	65.1	56.4	51.1	47.5	44.0	42.6
82.5°	41.6	45.5	48.8	51.6	49.7	45.7	40.2	36.7	34.6	32.1	31.6
85°	21.9	23.9	25.4	26.0	25.4	22.9	20.5	19.0	17.2	16.2	15.8
87.5°	11.4	11.1	10.7	10.9	9.7	9.2	7.6	6.4	6.5	6.7	6.6
90°	14.8	13.2	11.6	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.3	18.5	17.7	17.4	17.6	17.8	18.0	18.2	18.0	17.8	17.6
95°	32.3	30.9	29.5	32.1	38.7	45.3	51.9	58.5	51.9	45.3	38.7
97.5°	40.5	37.3	34.0	41.8	60.3	79.0	97.6	116.2	97.6	79.0	60.3
100°	44.5	41.1	37.7	49.8	77.2	104.5	132.0	159.4	132.0	104.5	77.2
102.5°	109.7	138.2	166.6	183.7	189.5	195.4	201.1	207.0	201.1	195.4	189.5
105°	164.2	218.9	273.5	297.8	291.8	285.8	279.8	273.8	279.8	285.8	291.8
107.5°	207.9	273.5	339.0	369.4	364.5	359.7	354.9	350.0	354.9	359.7	364.5
110°	273.3	331.1	389.0	415.8	411.6	407.4	403.2	399.0	403.2	407.4	411.6



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	426.1	440.5	454.7	460.0	456.3	452.5	448.8	445.1	448.8	452.5	456.3
115°	545.6	540.6	535.6	531.5	528.1	524.7	521.2	517.8	521.2	524.7	528.1
117.5°	608.6	605.2	601.7	598.1	594.3	590.5	586.7	582.9	586.7	590.5	594.3
120°	653.0	649.3	645.7	642.4	639.4	636.4	633.5	630.5	633.5	636.4	639.4
122.5°	694.8	690.9	687.0	683.4	680.2	677.1	673.9	670.8	673.9	677.1	680.2
125°	753.5	749.6	745.8	742.6	740.0	737.4	734.8	732.2	734.8	737.4	740.0
127.5°	807.9	805.1	802.3	799.4	796.5	793.6	790.8	787.9	790.8	793.6	796.5
130°	843.1	840.8	838.7	835.9	832.7	829.6	826.4	823.2	826.4	829.6	832.7
132.5°	876.9	874.8	872.5	870.1	867.3	864.7	862.0	859.2	862.0	864.7	867.3
135°	924.9	923.1	921.3	918.9	915.7	912.5	909.3	906.1	909.3	912.5	915.7
137.5°	968.6	966.6	964.5	962.3	960.2	957.9	955.6	953.4	955.6	957.9	960.2
140°	997.1	994.9	992.7	990.8	989.2	987.6	986.0	984.4	986.0	987.6	989.2
142.5°	1023.1	1020.6	1018.0	1016.1	1014.6	1013.2	1011.7	1010.3	1011.7	1013.2	1014.6
145°	1058.7	1055.3	1051.9	1050.3	1050.5	1050.7	1050.8	1051.0	1050.8	1050.7	1050.5
147.5°	1091.5	1088.2	1084.8	1083.5	1084.2	1085.0	1085.7	1086.6	1085.7	1085.0	1084.2
150°	1111.3	1108.1	1104.8	1104.0	1105.4	1106.7	1108.1	1109.6	1108.1	1106.7	1105.4
152.5°	1129.6	1126.5	1123.5	1122.8	1124.4	1125.9	1127.5	1129.1	1127.5	1125.9	1124.4
155°	1155.2	1152.8	1150.4	1150.1	1151.9	1153.7	1155.5	1157.3	1155.5	1153.7	1151.9
157.5°	1176.9	1175.2	1173.5	1173.4	1174.9	1176.4	1178.0	1179.5	1178.0	1176.4	1174.9
160°	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1191.3	1190.1	1188.8
162.5°	1201.2	1200.1	1199.1	1199.2	1200.3	1201.6	1202.8	1204.0	1202.8	1201.6	1200.3
165°	1215.5	1214.9	1214.4	1214.7	1215.9	1217.0	1218.2	1219.5	1218.2	1217.0	1215.9
167.5°	1227.0	1226.4	1225.9	1226.2	1227.4	1228.6	1229.7	1231.0	1229.7	1228.6	1227.4
170°	1233.0	1232.7	1232.3	1232.7	1233.9	1235.1	1236.2	1237.5	1236.2	1235.1	1233.9
172.5°	1237.4	1237.0	1236.6	1237.0	1238.2	1239.3	1240.6	1241.8	1240.6	1239.3	1238.2
175°	1242.1	1241.7	1241.2	1241.8	1243.2	1244.5	1245.9	1247.4	1245.9	1244.5	1243.2
177.5°	1243.6	1243.5	1243.3	1243.8	1244.9	1246.0	1247.2	1248.3	1247.2	1246.0	1244.9
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	903.8	902.1	896.2	893.1	888.1	883.3	880.1	881.6	882.7	882.1	881.3
5°	877.9	871.2	861.0	852.2	845.8	834.2	829.3	826.9	824.7	822.3	819.8
7.5°	847.1	836.5	821.9	809.4	797.5	783.1	774.9	769.9	764.8	759.2	754.3
10°	825.1	810.3	794.8	777.2	763.2	750.1	738.5	730.8	723.7	717.0	712.1
12.5°	802.0	784.9	765.8	741.8	726.2	707.6	705.9	692.2	681.2	677.0	671.3
15°	765.3	741.3	717.0	688.5	676.2	659.3	648.8	638.2	628.7	622.0	620.2
17.5°	723.5	692.5	668.4	647.9	627.7	610.4	600.7	592.2	584.4	575.4	574.3
20°	691.6	665.0	638.6	620.6	599.8	582.2	570.2	561.8	555.1	549.8	545.3
22.5°	661.6	632.3	608.1	588.4	568.0	553.7	544.3	536.2	530.7	524.8	520.5
25°	613.2	590.3	563.9	541.8	524.8	515.7	507.9	500.9	497.4	493.5	488.6
27.5°	570.9	545.4	520.8	503.6	488.7	480.6	475.1	470.3	467.0	464.8	461.9
30°	541.0	515.3	496.0	479.1	466.7	458.6	455.2	452.3	448.5	447.0	445.6
32.5°	512.3	489.2	472.6	458.0	446.2	440.9	437.7	435.2	432.2	430.7	427.9
35°	471.6	452.3	436.1	428.0	418.5	414.0	411.5	407.9	405.2	403.8	403.4
37.5°	433.5	416.6	406.0	395.6	391.5	388.7	385.4	383.0	382.1	381.9	381.5
40°	408.7	394.9	385.4	377.0	375.2	371.0	368.2	366.1	366.1	366.5	366.1
42.5°	386.2	373.8	365.4	358.2	356.1	353.5	350.7	350.6	351.2	352.3	351.2
45°	352.0	343.2	337.2	333.7	329.8	327.3	327.0	328.1	328.4	328.8	329.8
47.5°	320.6	314.7	309.3	305.5	303.8	303.3	302.9	304.7	306.4	307.1	308.7
50°	302.0	295.3	290.8	288.3	286.9	286.2	286.9	289.0	290.4	292.2	293.2
52.5°	281.2	276.4	273.3	271.4	270.8	271.3	271.4	273.8	276.1	276.6	277.2
55°	252.4	248.8	248.2	245.0	246.4	246.0	247.8	249.2	251.3	253.4	253.8
57.5°	223.7	220.8	219.0	219.2	219.6	221.2	222.6	225.2	227.4	229.6	229.9
60°	204.5	203.1	202.1	202.1	202.7	204.9	206.6	209.1	210.5	211.9	212.9
62.5°	187.1	185.7	184.5	185.1	187.0	188.2	190.3	191.6	193.0	194.4	194.9
65°	159.5	158.7	159.9	160.5	160.9	162.6	165.1	166.2	167.6	168.2	170.7
67.5°	134.0	134.2	134.0	135.1	137.0	137.5	139.8	142.3	142.6	143.9	145.5
70°	116.9	117.5	118.3	118.9	120.7	121.4	123.2	124.2	125.6	126.7	127.8
72.5°	101.1	101.2	102.0	101.8	103.3	104.8	106.3	107.4	108.8	110.1	111.1
75°	77.8	77.8	78.5	78.9	80.6	82.4	82.0	82.8	84.2	85.6	86.2
77.5°	56.8	56.1	56.8	57.1	57.7	59.2	59.5	60.5	62.1	61.6	62.4
80°	43.3	42.2	43.3	43.6	43.6	45.4	45.4	46.1	47.1	46.1	47.1
82.5°	30.9	30.4	31.2	31.3	31.9	31.9	32.4	32.6	33.6	33.2	33.6
85°	15.5	15.2	15.5	15.2	15.5	15.8	15.8	15.5	15.5	16.2	15.2
87.5°	6.7	6.8	6.9	7.2	7.3	7.3	7.2	7.4	7.5	7.3	7.4
90°	9.7	11.6	13.2	14.8	16.4	18.0	19.0	20.0	21.0	22.1	22.7
92.5°	17.4	17.7	18.5	19.3	20.1	20.9	21.4	22.0	22.4	23.0	23.4
95°	32.1	29.5	30.9	32.3	33.7	35.2	36.1	37.1	38.2	39.1	39.5
97.5°	41.8	34.0	37.3	40.5	43.7	47.0	47.8	48.6	49.4	50.2	50.7
100°	49.8	37.7	41.1	44.5	48.0	51.4	53.0	54.6	56.2	57.8	58.7
102.5°	183.7	166.6	138.2	109.7	81.2	52.8	54.9	56.9	59.0	61.1	62.4
105°	297.8	273.5	218.9	164.2	109.6	55.0	57.1	59.4	61.5	63.7	65.2
107.5°	369.4	339.0	273.5	207.9	142.4	76.9	74.6	72.4	70.2	68.0	67.2
110°	415.8	389.0	331.1	273.3	215.5	157.6	137.6	117.5	97.6	77.6	68.0



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	460.0	454.7	440.5	426.1	411.8	397.6	324.5	251.5	178.5	105.5	69.3
115°	531.5	535.6	540.6	545.6	550.7	555.7	463.0	370.3	277.7	185.0	131.5
117.5°	598.1	601.7	605.2	608.6	612.1	615.5	593.0	570.6	548.3	525.8	491.0
120°	642.4	645.7	649.3	653.0	656.6	660.2	662.6	665.0	667.3	669.8	657.4
122.5°	683.4	687.0	690.9	694.8	698.7	702.7	704.1	705.6	707.0	708.4	706.5
125°	742.6	745.8	749.6	753.5	757.2	761.0	762.4	763.8	765.3	766.7	767.6
127.5°	799.4	802.3	805.1	807.9	810.8	813.6	815.7	817.7	819.7	821.8	822.8
130°	835.9	838.7	840.8	843.1	845.3	847.5	849.7	851.9	854.1	856.3	857.3
132.5°	870.1	872.5	874.8	876.9	879.1	881.4	883.3	885.1	887.0	888.9	889.8
135°	918.9	921.3	923.1	924.9	926.7	928.6	930.6	932.6	934.5	936.5	937.4
137.5°	962.3	964.5	966.6	968.6	970.6	972.7	974.7	976.6	978.5	980.5	981.2
140°	990.8	992.7	994.9	997.1	999.3	1001.5	1003.3	1005.1	1006.9	1008.7	1009.1
142.5°	1016.1	1018.0	1020.6	1023.1	1025.7	1028.1	1029.8	1031.4	1033.1	1034.7	1035.0
145°	1050.3	1051.9	1055.3	1058.7	1062.1	1065.5	1066.9	1068.3	1069.7	1071.0	1071.3
147.5°	1083.5	1084.8	1088.2	1091.5	1094.9	1098.3	1099.3	1100.3	1101.4	1102.4	1102.5
150°	1104.0	1104.8	1108.1	1111.3	1114.5	1117.7	1118.9	1120.1	1121.2	1122.5	1122.6
152.5°	1122.8	1123.5	1126.5	1129.6	1132.7	1135.7	1136.9	1138.1	1139.3	1140.5	1140.5
155°	1150.1	1150.4	1152.8	1155.2	1157.6	1160.0	1161.2	1162.4	1163.6	1164.8	1164.6
157.5°	1173.4	1173.5	1175.2	1176.9	1178.5	1180.2	1181.6	1182.9	1184.3	1185.6	1185.5
160°	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1193.6	1194.9	1196.0	1197.2	1197.1
162.5°	1199.2	1199.1	1200.1	1201.2	1202.2	1203.2	1204.6	1206.0	1207.3	1208.7	1208.5
165°	1214.7	1214.4	1214.9	1215.5	1216.2	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4
167.5°	1226.2	1225.9	1226.4	1227.0	1227.6	1228.1	1229.5	1230.9	1232.3	1233.7	1233.5
170°	1232.7	1232.3	1232.7	1233.0	1233.5	1233.9	1235.3	1236.7	1238.0	1239.4	1239.3
172.5°	1237.0	1236.6	1237.0	1237.4	1237.7	1238.2	1239.6	1241.0	1242.4	1243.8	1243.6
175°	1241.8	1241.2	1241.7	1242.1	1242.5	1242.8	1244.3	1245.7	1247.1	1248.5	1248.2
177.5°	1243.8	1243.3	1243.5	1243.6	1243.8	1244.0	1245.1	1246.2	1247.3	1248.4	1248.3
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	878.4	877.9	877.9	875.3	877.9	877.9	878.4	881.3	882.1	882.7	881.6
5°	814.9	813.8	812.1	813.8	812.1	813.8	814.9	819.8	822.3	824.7	826.9
7.5°	752.1	747.8	747.2	743.0	747.2	747.8	752.1	754.3	759.2	764.8	769.9
10°	706.2	703.3	702.9	696.3	702.9	703.3	706.2	712.1	717.0	723.7	730.8
12.5°	671.2	664.4	665.8	661.9	665.8	664.4	671.2	671.3	677.0	681.2	692.2
15°	610.7	610.7	609.4	603.3	609.4	610.7	610.7	620.2	622.0	628.7	638.2
17.5°	567.3	566.6	563.2	564.9	563.2	566.6	567.3	574.3	575.4	584.4	592.2
20°	541.4	539.2	535.1	535.1	535.1	539.2	541.4	545.3	549.8	555.1	561.8
22.5°	516.9	516.7	512.3	513.7	512.3	516.7	516.9	520.5	524.8	530.7	536.2
25°	488.2	485.4	483.3	484.4	483.3	485.4	488.2	488.6	493.5	497.4	500.9
27.5°	461.1	459.5	459.4	456.5	459.4	459.5	461.1	461.9	464.8	467.0	470.3
30°	445.3	441.8	442.4	440.7	442.4	441.8	445.3	445.6	447.0	448.5	452.3
32.5°	427.3	426.0	425.3	423.8	425.3	426.0	427.3	427.9	430.7	432.2	435.2
35°	402.7	403.0	401.2	402.0	401.2	403.0	402.7	403.4	403.8	405.2	407.9
37.5°	381.3	382.4	381.5	381.7	381.5	382.4	381.3	381.5	381.9	382.1	383.0
40°	367.1	367.1	367.1	368.2	367.1	367.1	367.1	366.1	366.5	366.1	366.1
42.5°	353.6	353.1	352.5	352.4	352.5	353.1	353.6	351.2	352.3	351.2	350.6
45°	330.5	331.6	332.0	330.2	332.0	331.6	330.5	329.8	328.8	328.4	328.1
47.5°	309.6	309.7	309.6	311.1	309.6	309.7	309.6	308.7	307.1	306.4	304.7
50°	295.0	294.3	295.0	294.3	295.0	294.3	295.0	293.2	292.2	290.4	289.0
52.5°	279.5	279.7	279.2	279.1	279.2	279.7	279.5	277.2	276.6	276.1	273.8
55°	255.2	255.9	255.5	255.5	255.5	255.9	255.2	253.8	253.4	251.3	249.2
57.5°	230.1	230.7	231.2	229.6	231.2	230.7	230.1	229.9	229.6	227.4	225.2
60°	212.6	214.3	214.1	213.3	214.1	214.3	212.6	212.9	211.9	210.5	209.1
62.5°	196.5	197.2	197.1	197.0	197.1	197.2	196.5	194.9	194.4	193.0	191.6
65°	171.7	172.5	171.4	172.5	171.4	172.5	171.7	170.7	168.2	167.6	166.2
67.5°	145.1	145.3	146.1	146.6	146.1	145.3	145.1	145.5	143.9	142.6	142.3
70°	128.5	128.1	129.2	130.3	129.2	128.1	128.5	127.8	126.7	125.6	124.2
72.5°	111.0	111.8	111.4	112.3	111.4	111.8	111.0	111.1	110.1	108.8	107.4
75°	85.6	86.6	86.2	87.3	86.2	86.6	85.6	86.2	85.6	84.2	82.8
77.5°	61.8	61.9	61.8	62.4	61.8	61.9	61.8	62.4	61.6	62.1	60.5
80°	47.1	46.5	45.7	47.1	45.7	46.5	47.1	47.1	46.1	47.1	46.1
82.5°	32.8	33.3	32.5	32.5	32.5	33.3	32.8	33.6	33.2	33.6	32.6
85°	15.2	14.8	14.0	14.0	14.0	14.8	15.2	15.2	16.2	15.5	15.5
87.5°	7.4	7.3	7.4	7.2	7.4	7.3	7.4	7.4	7.3	7.5	7.4
90°	23.1	23.5	23.9	24.3	23.9	23.5	23.1	22.7	22.1	21.0	20.0
92.5°	23.6	23.8	24.0	24.3	24.0	23.8	23.6	23.4	23.0	22.4	22.0
95°	39.3	39.1	38.9	38.7	38.9	39.1	39.3	39.5	39.1	38.2	37.1
97.5°	51.0	51.2	51.5	51.7	51.5	51.2	51.0	50.7	50.2	49.4	48.6
100°	59.1	59.6	59.9	60.3	59.9	59.6	59.1	58.7	57.8	56.2	54.6
102.5°	63.0	63.5	64.1	64.7	64.1	63.5	63.0	62.4	61.1	59.0	56.9
105°	66.1	66.8	67.7	68.4	67.7	66.8	66.1	65.2	63.7	61.5	59.4
107.5°	68.1	68.8	69.7	70.4	69.7	68.8	68.1	67.2	68.0	70.2	72.4
110°	68.7	69.6	70.3	71.2	70.3	69.6	68.7	68.0	77.6	97.6	117.5



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	69.9	70.6	71.3	71.9	71.3	70.6	69.9	69.3	105.5	178.5	251.5
115°	117.1	102.6	88.2	73.9	88.2	102.6	117.1	131.5	185.0	277.7	370.3
117.5°	443.6	396.2	348.9	301.5	348.9	396.2	443.6	491.0	525.8	548.3	570.6
120°	630.5	603.4	576.4	549.4	576.4	603.4	630.5	657.4	669.8	667.3	665.0
122.5°	701.3	696.1	690.8	685.6	690.8	696.1	701.3	706.5	708.4	707.0	705.6
125°	768.3	768.8	769.4	770.1	769.4	768.8	768.3	767.6	766.7	765.3	763.8
127.5°	823.0	823.1	823.2	823.3	823.2	823.1	823.0	822.8	821.8	819.7	817.7
130°	857.1	856.9	856.7	856.5	856.7	856.9	857.1	857.3	856.3	854.1	851.9
132.5°	889.5	889.3	889.1	888.9	889.1	889.3	889.5	889.8	888.9	887.0	885.1
135°	937.0	936.5	936.1	935.8	936.1	936.5	937.0	937.4	936.5	934.5	932.6
137.5°	980.5	979.8	979.1	978.5	979.1	979.8	980.5	981.2	980.5	978.5	976.6
140°	1008.1	1007.1	1006.1	1005.1	1006.1	1007.1	1008.1	1009.1	1008.7	1006.9	1005.1
142.5°	1034.1	1033.0	1032.1	1031.0	1032.1	1033.0	1034.1	1035.0	1034.7	1033.1	1031.4
145°	1070.3	1069.2	1068.3	1067.2	1068.3	1069.2	1070.3	1071.3	1071.0	1069.7	1068.3
147.5°	1101.6	1100.8	1099.9	1099.1	1099.9	1100.8	1101.6	1102.5	1102.4	1101.4	1100.3
150°	1121.6	1120.6	1119.6	1118.6	1119.6	1120.6	1121.6	1122.6	1122.5	1121.2	1120.1
152.5°	1139.2	1137.8	1136.5	1135.2	1136.5	1137.8	1139.2	1140.5	1140.5	1139.3	1138.1
155°	1163.0	1161.4	1159.8	1158.2	1159.8	1161.4	1163.0	1164.6	1164.8	1163.6	1162.4
157.5°	1183.9	1182.4	1180.8	1179.3	1180.8	1182.4	1183.9	1185.5	1185.6	1184.3	1182.9
160°	1195.7	1194.3	1193.0	1191.6	1193.0	1194.3	1195.7	1197.1	1197.2	1196.0	1194.9
162.5°	1206.7	1205.0	1203.3	1201.6	1203.3	1205.0	1206.7	1208.5	1208.7	1207.3	1206.0
165°	1221.0	1219.6	1218.1	1216.7	1218.1	1219.6	1221.0	1222.4	1222.4	1221.0	1219.6
167.5°	1231.7	1229.9	1228.1	1226.3	1228.1	1229.9	1231.7	1233.5	1233.7	1232.3	1230.9
170°	1237.5	1235.7	1233.9	1232.1	1233.9	1235.7	1237.5	1239.3	1239.4	1238.0	1236.7
172.5°	1241.8	1240.0	1238.2	1236.4	1238.2	1240.0	1241.8	1243.6	1243.8	1242.4	1241.0
175°	1246.1	1244.2	1242.2	1240.2	1242.2	1244.2	1246.1	1248.2	1248.5	1247.1	1245.7
177.5°	1246.8	1245.4	1244.0	1242.6	1244.0	1245.4	1246.8	1248.3	1248.4	1247.3	1246.2
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	880.1	883.3	888.1	893.1	896.2	902.1	903.8	906.6	909.2	915.0	921.2
5°	829.3	834.2	845.8	852.2	861.0	871.2	877.9	885.0	892.7	906.1	918.4
7.5°	774.9	783.1	797.5	809.4	821.9	836.5	847.1	861.0	872.5	891.4	909.5
10°	738.5	750.1	763.2	777.2	794.8	810.3	825.1	842.7	856.8	879.3	900.4
12.5°	705.9	707.6	726.2	741.8	765.8	784.9	802.0	824.6	838.5	865.3	887.5
15°	648.8	659.3	676.2	688.5	717.0	741.3	765.3	788.8	804.6	837.7	867.0
17.5°	600.7	610.4	627.7	647.9	668.4	692.5	723.5	748.4	769.9	807.7	842.3
20°	570.2	582.2	599.8	620.6	638.6	665.0	691.6	720.2	743.4	786.0	826.5
22.5°	544.3	553.7	568.0	588.4	608.1	632.3	661.6	692.6	717.0	762.9	804.0
25°	507.9	515.7	524.8	541.8	563.9	590.3	613.2	647.3	682.9	725.9	775.4
27.5°	475.1	480.6	488.7	503.6	520.8	545.4	570.9	603.2	639.0	685.6	738.0
30°	455.2	458.6	466.7	479.1	496.0	515.3	541.0	572.0	608.6	655.8	707.8
32.5°	437.7	440.9	446.2	458.0	472.6	489.2	512.3	543.3	578.2	624.5	682.2
35°	411.5	414.0	418.5	428.0	436.1	452.3	471.6	499.8	532.5	576.9	636.8
37.5°	385.4	388.7	391.5	395.6	406.0	416.6	433.5	457.2	489.4	534.1	591.2
40°	368.2	371.0	375.2	377.0	385.4	394.9	408.7	430.5	462.9	503.7	559.3
42.5°	350.7	353.5	356.1	358.2	365.4	373.8	386.2	404.9	433.6	473.3	528.4
45°	327.0	327.3	329.8	333.7	337.2	343.2	352.0	368.2	390.4	427.7	477.7
47.5°	302.9	303.3	303.8	305.5	309.3	314.7	320.6	333.8	353.6	383.4	432.1
50°	286.9	286.2	286.9	288.3	290.8	295.3	302.0	311.5	327.7	355.5	400.2
52.5°	271.4	271.3	270.8	271.4	273.3	276.4	281.2	289.3	303.8	329.3	368.7
55°	247.8	246.0	246.4	245.0	248.2	248.8	252.4	259.1	271.7	289.4	326.3
57.5°	222.6	221.2	219.6	219.2	219.0	220.8	223.7	228.9	238.7	254.1	284.1
60°	206.6	204.9	202.7	202.1	202.1	203.1	204.5	208.4	217.5	231.3	255.9
62.5°	190.3	188.2	187.0	185.1	184.5	185.7	187.1	189.8	196.4	209.3	230.5
65°	165.1	162.6	160.9	160.5	159.9	158.7	159.5	162.3	167.6	177.8	194.6
67.5°	139.8	137.5	137.0	135.1	134.0	134.2	134.0	136.5	139.6	148.4	161.0
70°	123.2	121.4	120.7	118.9	118.3	117.5	116.9	118.9	122.2	129.5	140.4
72.5°	106.3	104.8	103.3	101.8	102.0	101.2	101.1	102.4	105.0	111.8	120.2
75°	82.0	82.4	80.6	78.9	78.5	77.8	77.8	78.9	79.9	85.2	91.9
77.5°	59.5	59.2	57.7	57.1	56.8	56.1	56.8	57.5	58.1	61.6	66.5
80°	45.4	45.4	43.6	43.6	43.3	42.2	43.3	42.6	44.0	47.5	51.1
82.5°	32.4	31.9	31.9	31.3	31.2	30.4	30.9	31.6	32.1	34.6	36.7
85°	15.8	15.8	15.5	15.2	15.5	15.2	15.5	15.8	16.2	17.2	19.0
87.5°	7.2	7.3	7.3	7.2	6.9	6.8	6.7	6.6	6.7	6.5	6.4
90°	19.0	18.0	16.4	14.8	13.2	11.6	9.7	7.5	5.3	3.1	0.9
92.5°	21.4	20.9	20.1	19.3	18.5	17.7	17.4	17.6	17.8	18.0	18.2
95°	36.1	35.2	33.7	32.3	30.9	29.5	32.1	38.7	45.3	51.9	58.5
97.5°	47.8	47.0	43.7	40.5	37.3	34.0	41.8	60.3	79.0	97.6	116.2
100°	53.0	51.4	48.0	44.5	41.1	37.7	49.8	77.2	104.5	132.0	159.4
102.5°	54.9	52.8	81.2	109.7	138.2	166.6	183.7	189.5	195.4	201.1	207.0
105°	57.1	55.0	109.6	164.2	218.9	273.5	297.8	291.8	285.8	279.8	273.8
107.5°	74.6	76.9	142.4	207.9	273.5	339.0	369.4	364.5	359.7	354.9	350.0
110°	137.6	157.6	215.5	273.3	331.1	389.0	415.8	411.6	407.4	403.2	399.0



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	324.5	397.6	411.8	426.1	440.5	454.7	460.0	456.3	452.5	448.8	445.1
115°	463.0	555.7	550.7	545.6	540.6	535.6	531.5	528.1	524.7	521.2	517.8
117.5°	593.0	615.5	612.1	608.6	605.2	601.7	598.1	594.3	590.5	586.7	582.9
120°	662.6	660.2	656.6	653.0	649.3	645.7	642.4	639.4	636.4	633.5	630.5
122.5°	704.1	702.7	698.7	694.8	690.9	687.0	683.4	680.2	677.1	673.9	670.8
125°	762.4	761.0	757.2	753.5	749.6	745.8	742.6	740.0	737.4	734.8	732.2
127.5°	815.7	813.6	810.8	807.9	805.1	802.3	799.4	796.5	793.6	790.8	787.9
130°	849.7	847.5	845.3	843.1	840.8	838.7	835.9	832.7	829.6	826.4	823.2
132.5°	883.3	881.4	879.1	876.9	874.8	872.5	870.1	867.3	864.7	862.0	859.2
135°	930.6	928.6	926.7	924.9	923.1	921.3	918.9	915.7	912.5	909.3	906.1
137.5°	974.7	972.7	970.6	968.6	966.6	964.5	962.3	960.2	957.9	955.6	953.4
140°	1003.3	1001.5	999.3	997.1	994.9	992.7	990.8	989.2	987.6	986.0	984.4
142.5°	1029.8	1028.1	1025.7	1023.1	1020.6	1018.0	1016.1	1014.6	1013.2	1011.7	1010.3
145°	1066.9	1065.5	1062.1	1058.7	1055.3	1051.9	1050.3	1050.5	1050.7	1050.8	1051.0
147.5°	1099.3	1098.3	1094.9	1091.5	1088.2	1084.8	1083.5	1084.2	1085.0	1085.7	1086.6
150°	1118.9	1117.7	1114.5	1111.3	1108.1	1104.8	1104.0	1105.4	1106.7	1108.1	1109.6
152.5°	1136.9	1135.7	1132.7	1129.6	1126.5	1123.5	1122.8	1124.4	1125.9	1127.5	1129.1
155°	1161.2	1160.0	1157.6	1155.2	1152.8	1150.4	1150.1	1151.9	1153.7	1155.5	1157.3
157.5°	1181.6	1180.2	1178.5	1176.9	1175.2	1173.5	1173.4	1174.9	1176.4	1178.0	1179.5
160°	1193.6	1192.4	1191.3	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4
162.5°	1204.6	1203.2	1202.2	1201.2	1200.1	1199.1	1199.2	1200.3	1201.6	1202.8	1204.0
165°	1218.1	1216.7	1216.2	1215.5	1214.9	1214.4	1214.7	1215.9	1217.0	1218.2	1219.5
167.5°	1229.5	1228.1	1227.6	1227.0	1226.4	1225.9	1226.2	1227.4	1228.6	1229.7	1231.0
170°	1235.3	1233.9	1233.5	1233.0	1232.7	1232.3	1232.7	1233.9	1235.1	1236.2	1237.5
172.5°	1239.6	1238.2	1237.7	1237.4	1237.0	1236.6	1237.0	1238.2	1239.3	1240.6	1241.8
175°	1244.3	1242.8	1242.5	1242.1	1241.7	1241.2	1241.8	1243.2	1244.5	1245.9	1247.4
177.5°	1245.1	1244.0	1243.8	1243.6	1243.5	1243.3	1243.8	1244.9	1246.0	1247.2	1248.3
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	920.7	922.1	926.6	931.1	936.1	937.5	939.8	937.8	937.3	942.6	946.6
5°	923.3	929.6	942.0	953.2	962.7	969.4	976.5	979.3	984.6	991.9	1001.1
7.5°	920.3	932.6	952.1	968.5	986.3	999.2	1009.3	1017.9	1028.2	1042.3	1057.5
10°	917.0	933.5	957.1	977.1	999.0	1015.5	1029.3	1042.6	1058.1	1077.5	1097.5
12.5°	910.8	930.4	959.9	983.6	1011.6	1027.9	1046.4	1075.3	1091.9	1118.9	1147.1
15°	898.3	920.1	961.3	990.5	1022.2	1053.2	1087.3	1114.7	1142.3	1158.1	1197.9
17.5°	879.8	911.8	957.4	991.6	1031.8	1080.5	1118.9	1150.1	1181.8	1207.4	1227.4
20°	864.9	899.8	951.8	992.7	1040.5	1093.0	1137.0	1168.7	1196.1	1217.6	1229.9
22.5°	846.0	889.9	940.6	988.4	1049.5	1101.5	1147.6	1172.6	1195.5	1206.0	1210.7
25°	816.2	869.1	926.4	984.9	1053.9	1108.8	1151.0	1166.2	1172.9	1162.6	1145.8
27.5°	784.3	843.1	910.2	978.3	1051.2	1104.0	1134.3	1131.9	1120.6	1087.5	1061.1
30°	760.3	825.1	897.2	971.5	1044.7	1096.1	1113.7	1096.1	1070.4	1033.5	995.8
32.5°	735.3	802.3	883.4	962.0	1032.9	1078.1	1081.9	1051.6	1011.8	969.9	922.8
35°	697.3	769.9	857.4	940.6	1007.8	1036.3	1019.4	965.9	918.7	861.4	797.3
37.5°	654.4	734.5	822.4	909.2	970.2	977.6	935.7	879.3	812.8	745.4	670.0
40°	622.4	707.2	797.7	885.2	939.1	931.4	877.9	816.0	736.7	654.4	584.3
42.5°	593.6	678.4	770.6	856.6	899.8	878.4	816.0	739.9	654.8	577.2	513.1
45°	543.8	631.1	725.5	808.5	833.2	794.8	712.1	627.6	543.8	479.1	428.4
47.5°	495.6	581.8	675.2	748.3	757.1	705.4	615.0	528.1	456.1	403.3	367.6
50°	460.1	546.7	639.2	704.4	701.5	639.2	546.3	463.5	403.4	360.8	336.9
52.5°	428.2	510.0	599.0	658.2	643.3	575.3	486.6	413.2	363.7	330.4	308.7
55°	378.7	454.4	538.9	586.4	559.0	483.6	408.7	349.5	312.9	287.9	271.1
57.5°	329.6	400.6	472.9	502.2	471.8	402.3	339.8	296.9	269.4	250.8	239.9
60°	299.2	361.2	425.6	450.9	414.6	352.7	303.4	265.0	242.9	227.7	217.9
62.5°	268.8	324.2	385.0	398.8	365.6	313.3	269.7	237.7	219.5	206.0	196.8
65°	227.4	272.8	319.0	328.1	297.5	256.9	222.4	201.7	185.5	175.7	168.2
67.5°	186.5	222.9	255.6	263.0	236.2	208.1	183.1	165.1	154.1	145.9	139.7
70°	162.3	191.1	217.9	223.9	202.4	177.4	158.4	143.9	134.1	127.1	121.1
72.5°	136.7	160.7	182.9	187.0	169.5	150.3	134.8	123.4	114.7	110.2	104.4
75°	104.5	118.7	135.9	137.0	125.4	113.7	101.7	94.3	89.7	84.2	81.3
77.5°	73.8	84.8	94.7	96.6	89.7	81.8	75.1	69.3	65.4	62.8	60.2
80°	56.4	65.1	69.4	71.8	66.9	61.3	57.4	53.5	51.1	49.3	47.5
82.5°	40.2	45.7	49.7	51.6	48.8	45.5	41.6	39.4	37.5	36.0	35.4
85°	20.5	22.9	25.4	26.0	25.4	23.9	21.9	21.9	20.7	20.5	20.5
87.5°	7.6	9.2	9.7	10.9	10.7	11.1	11.4	11.4	11.5	11.4	11.3
90°	3.1	5.3	7.5	9.7	11.6	13.2	14.8	16.4	18.0	19.0	20.0
92.5°	18.0	17.8	17.6	17.4	17.7	18.5	19.3	20.1	20.9	21.4	22.0
95°	51.9	45.3	38.7	32.1	29.5	30.9	32.3	33.7	35.2	36.1	37.1
97.5°	97.6	79.0	60.3	41.8	34.0	37.3	40.5	43.7	47.0	47.8	48.6
100°	132.0	104.5	77.2	49.8	37.7	41.1	44.5	48.0	51.4	53.0	54.6
102.5°	201.1	195.4	189.5	183.7	166.6	138.2	109.7	81.2	52.8	54.9	56.9
105°	279.8	285.8	291.8	297.8	273.5	218.9	164.2	109.6	55.0	57.1	59.4
107.5°	354.9	359.7	364.5	369.4	339.0	273.5	207.9	142.4	76.9	74.6	72.4
110°	403.2	407.4	411.6	415.8	389.0	331.1	273.3	215.5	157.6	137.6	117.5



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	448.8	452.5	456.3	460.0	454.7	440.5	426.1	411.8	397.6	324.5	251.5
115°	521.2	524.7	528.1	531.5	535.6	540.6	545.6	550.7	555.7	463.0	370.3
117.5°	586.7	590.5	594.3	598.1	601.7	605.2	608.6	612.1	615.5	593.0	570.6
120°	633.5	636.4	639.4	642.4	645.7	649.3	653.0	656.6	660.2	662.6	665.0
122.5°	673.9	677.1	680.2	683.4	687.0	690.9	694.8	698.7	702.7	704.1	705.6
125°	734.8	737.4	740.0	742.6	745.8	749.6	753.5	757.2	761.0	762.4	763.8
127.5°	790.8	793.6	796.5	799.4	802.3	805.1	807.9	810.8	813.6	815.7	817.7
130°	826.4	829.6	832.7	835.9	838.7	840.8	843.1	845.3	847.5	849.7	851.9
132.5°	862.0	864.7	867.3	870.1	872.5	874.8	876.9	879.1	881.4	883.3	885.1
135°	909.3	912.5	915.7	918.9	921.3	923.1	924.9	926.7	928.6	930.6	932.6
137.5°	955.6	957.9	960.2	962.3	964.5	966.6	968.6	970.6	972.7	974.7	976.6
140°	986.0	987.6	989.2	990.8	992.7	994.9	997.1	999.3	1001.5	1003.3	1005.1
142.5°	1011.7	1013.2	1014.6	1016.1	1018.0	1020.6	1023.1	1025.7	1028.1	1029.8	1031.4
145°	1050.8	1050.7	1050.5	1050.3	1051.9	1055.3	1058.7	1062.1	1065.5	1066.9	1068.3
147.5°	1085.7	1085.0	1084.2	1083.5	1084.8	1088.2	1091.5	1094.9	1098.3	1099.3	1100.3
150°	1108.1	1106.7	1105.4	1104.0	1104.8	1108.1	1111.3	1114.5	1117.7	1118.9	1120.1
152.5°	1127.5	1125.9	1124.4	1122.8	1123.5	1126.5	1129.6	1132.7	1135.7	1136.9	1138.1
155°	1155.5	1153.7	1151.9	1150.1	1150.4	1152.8	1155.2	1157.6	1160.0	1161.2	1162.4
157.5°	1178.0	1176.4	1174.9	1173.4	1173.5	1175.2	1176.9	1178.5	1180.2	1181.6	1182.9
160°	1191.3	1190.1	1188.8	1187.6	1187.6	1188.8	1190.1	1191.3	1192.4	1193.6	1194.9
162.5°	1202.8	1201.6	1200.3	1199.2	1199.1	1200.1	1201.2	1202.2	1203.2	1204.6	1206.0
165°	1218.2	1217.0	1215.9	1214.7	1214.4	1214.9	1215.5	1216.2	1216.7	1218.1	1219.6
167.5°	1229.7	1228.6	1227.4	1226.2	1225.9	1226.4	1227.0	1227.6	1228.1	1229.5	1230.9
170°	1236.2	1235.1	1233.9	1232.7	1232.3	1232.7	1233.0	1233.5	1233.9	1235.3	1236.7
172.5°	1240.6	1239.3	1238.2	1237.0	1236.6	1237.0	1237.4	1237.7	1238.2	1239.6	1241.0
175°	1245.9	1244.5	1243.2	1241.8	1241.2	1241.7	1242.1	1242.5	1242.8	1244.3	1245.7
177.5°	1247.2	1246.0	1244.9	1243.8	1243.3	1243.5	1243.6	1243.8	1244.0	1245.1	1246.2
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	950.0	953.9	953.9	954.5	958.9	958.5	958.2
5°	1011.0	1016.9	1017.7	1024.0	1028.2	1026.8	1022.9
7.5°	1068.5	1079.6	1088.1	1092.8	1098.3	1101.7	1100.2
10°	1114.1	1130.3	1140.1	1146.8	1154.9	1160.9	1158.8
12.5°	1155.5	1174.8	1188.3	1199.8	1200.8	1208.5	1203.2
15°	1220.0	1240.5	1242.6	1251.0	1257.7	1257.0	1257.4
17.5°	1241.3	1247.9	1249.2	1249.4	1249.5	1247.1	1241.7
20°	1233.8	1231.3	1225.3	1220.8	1212.7	1211.5	1204.6
22.5°	1197.7	1189.9	1174.9	1165.0	1152.4	1149.1	1147.1
25°	1126.7	1109.5	1085.5	1062.7	1056.3	1044.1	1047.5
27.5°	1029.4	1002.5	976.6	958.0	941.2	922.7	928.0
30°	960.9	930.7	894.1	865.9	848.0	830.4	827.2
32.5°	879.3	834.9	794.1	769.3	741.8	730.7	718.5
35°	738.5	695.2	654.7	619.9	599.8	584.3	570.2
37.5°	611.8	562.0	529.3	501.1	486.6	477.8	479.9
40°	533.3	489.7	465.7	444.2	430.8	424.5	425.9
42.5°	469.7	437.0	417.3	402.6	393.1	389.6	388.7
45°	397.4	379.1	362.9	354.5	349.9	346.0	343.6
47.5°	348.2	333.2	324.0	319.1	315.0	311.1	311.0
50°	318.6	308.7	302.4	297.1	293.9	291.1	293.6
52.5°	296.1	287.0	280.7	276.0	274.8	272.2	272.2
55°	262.6	255.5	251.0	246.8	244.7	243.3	241.5
57.5°	232.1	225.5	221.3	218.6	214.6	213.2	212.6
60°	210.5	205.2	201.0	197.5	195.7	192.9	192.9
62.5°	190.5	185.2	181.3	178.6	175.7	174.6	174.8
65°	161.6	157.3	153.4	150.6	150.0	147.9	148.5
67.5°	135.0	132.1	128.1	126.5	125.2	124.0	123.2
70°	117.3	114.4	112.3	110.2	109.1	109.1	109.1
72.5°	102.3	98.9	97.6	95.0	95.6	94.4	93.3
75°	79.2	77.1	76.1	74.9	73.2	73.2	73.2
77.5°	58.2	57.7	56.4	55.2	54.9	54.5	54.7
80°	45.1	44.7	44.0	44.0	43.3	43.0	42.2
82.5°	34.6	33.7	33.3	33.0	32.9	32.8	32.7
85°	19.7	19.0	19.0	19.3	18.7	18.7	19.0
87.5°	11.8	12.0	11.9	12.0	12.3	12.1	12.2
90°	21.0	22.1	22.7	23.1	23.5	23.9	24.3
92.5°	22.4	23.0	23.4	23.6	23.8	24.0	24.3
95°	38.2	39.1	39.5	39.3	39.1	38.9	38.7
97.5°	49.4	50.2	50.7	51.0	51.2	51.5	51.7
100°	56.2	57.8	58.7	59.1	59.6	59.9	60.3
102.5°	59.0	61.1	62.4	63.0	63.5	64.1	64.7
105°	61.5	63.7	65.2	66.1	66.8	67.7	68.4
107.5°	70.2	68.0	67.2	68.1	68.8	69.7	70.4
110°	97.6	77.6	68.0	68.7	69.6	70.3	71.2



TEST NUMBER: P331507-830

CATALOG NUMBER: S122DIW-S485D970U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	178.5	105.5	69.3	69.9	70.6	71.3	71.9
115°	277.7	185.0	131.5	117.1	102.6	88.2	73.9
117.5°	548.3	525.8	491.0	443.6	396.2	348.9	301.5
120°	667.3	669.8	657.4	630.5	603.4	576.4	549.4
122.5°	707.0	708.4	706.5	701.3	696.1	690.8	685.6
125°	765.3	766.7	767.6	768.3	768.8	769.4	770.1
127.5°	819.7	821.8	822.8	823.0	823.1	823.2	823.3
130°	854.1	856.3	857.3	857.1	856.9	856.7	856.5
132.5°	887.0	888.9	889.8	889.5	889.3	889.1	888.9
135°	934.5	936.5	937.4	937.0	936.5	936.1	935.8
137.5°	978.5	980.5	981.2	980.5	979.8	979.1	978.5
140°	1006.9	1008.7	1009.1	1008.1	1007.1	1006.1	1005.1
142.5°	1033.1	1034.7	1035.0	1034.1	1033.0	1032.1	1031.0
145°	1069.7	1071.0	1071.3	1070.3	1069.2	1068.3	1067.2
147.5°	1101.4	1102.4	1102.5	1101.6	1100.8	1099.9	1099.1
150°	1121.2	1122.5	1122.6	1121.6	1120.6	1119.6	1118.6
152.5°	1139.3	1140.5	1140.5	1139.2	1137.8	1136.5	1135.2
155°	1163.6	1164.8	1164.6	1163.0	1161.4	1159.8	1158.2
157.5°	1184.3	1185.6	1185.5	1183.9	1182.4	1180.8	1179.3
160°	1196.0	1197.2	1197.1	1195.7	1194.3	1193.0	1191.6
162.5°	1207.3	1208.7	1208.5	1206.7	1205.0	1203.3	1201.6
165°	1221.0	1222.4	1222.4	1221.0	1219.6	1218.1	1216.7
167.5°	1232.3	1233.7	1233.5	1231.7	1229.9	1228.1	1226.3
170°	1238.0	1239.4	1239.3	1237.5	1235.7	1233.9	1232.1
172.5°	1242.4	1243.8	1243.6	1241.8	1240.0	1238.2	1236.4
175°	1247.1	1248.5	1248.2	1246.1	1244.2	1242.2	1240.2
177.5°	1247.3	1248.4	1248.3	1246.8	1245.4	1244.0	1242.6
180°	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6	1244.6

(END OF REPORT)