

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645206

Luminaire Tested: OMN4DP-SR4F0-100D835-FLL-1DUDD-WW

Issue Date: 2/16/2023



Test Information

Test Method: LM-79-2019
Report Number: P645206
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-689-19)
Test Lab: INNOVATION CENTER
Issue Date: 2/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: OMN4DP-SR4F0-100D835-FLL-1DUDD-WW
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE
DOWNLIGHT - FLAT FROSTED LENS - 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3977.5 lumens
Efficiency: N/A
Efficacy: 133.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 29.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P645206

CATALOG NUMBER: OMN4DP-SR4F0-100D835-FLL-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P645206

CATALOG NUMBER: OMN4DP-SR4F0-100D835-FLL-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	99																				
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84																				
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71																				
3	91	81	73	67	89	79	72	66	76	70	65	73	68	63	71	66	62	60																				
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	63	58	54	52																				
5	77	65	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45																				
6	71	58	50	43	69	57	49	43	55	48	43	54	47	42	52	46	42	40																				
7	66	53	44	38	65	52	44	38	51	43	38	49	43	38	48	42	37	35																				
8	62	49	40	34	60	48	40	34	46	39	34	45	39	34	44	38	34	32																				
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29																				
10	54	41	34	28	53	41	33	28	40	33	28	39	32	28	38	32	28	26																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26329	26329	26329
5°	26034	26214	26394
10°	25825	25935	26117
15°	25478	25478	25626
20°	25122	24931	24854
25°	24465	24268	23952
30°	23743	23411	22956
35°	23002	22432	21908
40°	22118	21463	20714
45°	21379	20569	19555
50°	20451	19560	18558
55°	19674	18674	17548
60°	18771	17767	16262
65°	17799	16527	15255
70°	16862	15290	14242
75°	15777	13980	13288
80°	14440	12794	12171
85°	13561	11912	11097

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21379 cd/sqm



TEST NUMBER: P645206

CATALOG NUMBER: OMN4DP-SR4F0-100D835-FLL-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	3.9
10°-20°	430.5	10.8
20°-30°	625.9	15.7
30°-40°	712.0	17.9
40°-50°	694.2	17.5
50°-60°	592.5	14.9
60°-70°	430.6	10.8
70°-80°	243.5	6.1
80°-90°	75.0	1.9
90°-100°	9.5	0.2
100°-110°	5.3	0.1
110°-120°	3.2	0.1
120°-130°	1.9	0.0
130°-140°	0.2	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1209.7	30.4
0°-40°	1921.7	48.3
0°-60°	3208.4	80.7
0°-90°	3957.5	99.5
90°-120°	17.9	0.5
90°-150°	20.0	0.5
90°-180°	20.0	0.5
0°-180°	3977.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1631	1631	1631	1631	1631	
5°	1606	1630	1617	1615	1628	152
15°	1524	1544	1524	1522	1533	430
25°	1373	1386	1362	1338	1344	632
35°	1167	1171	1138	1112	1112	729
45°	936	932	901	869	856	721
55°	699	697	663	632	623	624
65°	466	462	433	406	399	463
75°	253	244	224	215	213	268
85°	73	64	64	62	60	78
90°	9	11	13	11	11	9
95°	18	9	7	7	4	13
105°	11	7	4	2	0	13
115°	7	4	2	0	0	7
125°	4	4	2	0	0	4
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P645206

CATALOG NUMBER: OMN4DP-SR4F0-100D835-FLL-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1630.7	1630.7	1630.7	1630.7	1630.7
2.5°	1616.5	1637.3	1625.4	1625.5	1632.5
5°	1606.3	1630.1	1617.4	1615.4	1628.5
7.5°	1589.4	1612.8	1597.8	1595.6	1612.5
10°	1575.2	1596.9	1581.9	1577.8	1593.0
12.5°	1555.7	1577.4	1562.3	1556.5	1571.7
15°	1524.2	1543.7	1524.2	1522.2	1533.1
17.5°	1488.7	1505.6	1482.9	1475.6	1483.8
20°	1462.1	1477.2	1451.0	1440.0	1446.5
22.5°	1428.3	1443.5	1415.5	1399.2	1407.5
25°	1373.3	1386.3	1362.2	1338.0	1344.5
27.5°	1314.3	1324.3	1300.1	1275.3	1277.5
30°	1273.5	1280.0	1255.7	1229.2	1231.3
32.5°	1230.9	1235.7	1209.6	1181.2	1181.6
35°	1167.0	1171.3	1138.1	1111.5	1111.5
37.5°	1099.1	1101.7	1066.3	1037.4	1034.3
40°	1049.4	1053.7	1018.3	989.4	982.8
42.5°	1003.3	1004.1	972.2	943.2	934.9
45°	936.3	931.9	900.8	869.4	856.4
47.5°	863.9	863.9	828.4	797.1	784.9
50°	814.2	814.2	778.7	747.5	738.8
52.5°	768.1	766.3	732.6	701.2	689.1
55°	698.9	696.7	663.4	632.1	623.4
57.5°	625.6	625.6	594.6	561.1	551.5
60°	581.3	581.3	550.2	516.6	503.6
62.5°	533.4	531.6	500.5	470.6	462.8
65°	465.9	461.6	432.6	405.9	399.3
67.5°	401.6	397.2	366.5	345.1	340.8
70°	357.2	352.9	323.9	306.1	301.7
72.5°	314.6	308.5	283.1	268.8	264.5
75°	252.9	244.2	224.1	215.2	213.0
77.5°	194.4	179.6	171.3	165.0	162.8
80°	155.3	142.3	137.6	133.1	130.9
82.5°	121.6	108.6	107.4	104.7	102.5
85°	73.2	64.5	64.3	62.1	59.9
87.5°	31.9	27.2	27.5	27.1	27.1
90°	8.9	11.0	13.3	11.1	11.1
92.5°	16.0	11.2	9.8	9.3	7.5
95°	17.7	9.1	6.7	6.6	4.4
97.5°	15.5	9.0	6.2	4.0	2.2
100°	15.5	9.0	4.4	2.2	2.2
102.5°	13.8	7.2	4.4	2.2	0.4
105°	11.1	6.8	4.4	2.2	0.0
107.5°	10.6	6.7	4.4	2.2	0.0
110°	8.9	6.7	4.4	2.2	0.0



TEST NUMBER: P645206

CATALOG NUMBER: OMN4DP-SR4F0-100D835-FLL-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	8.9	6.7	4.4	2.2	0.0
115°	6.7	4.5	2.2	0.0	0.0
117.5°	6.7	4.5	2.2	0.0	0.0
120°	6.7	4.5	2.2	0.0	0.0
122.5°	4.9	4.4	2.2	0.0	0.0
125°	4.4	4.4	2.2	0.0	0.0
127.5°	2.2	4.0	2.2	0.0	0.0
130°	2.2	2.2	2.2	0.0	0.0
132.5°	0.4	0.4	0.4	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)