

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331543-830

Luminaire Tested: **S122DIW-S675D1240U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331543-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1240U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7435.5 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37				
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32				
2	87	80	74	69	79	73	68	64	59	56	53	47	45	42	35	34	33	27				
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24				
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	29	26	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	14				
8	53	41	34	29	48	38	31	27	31	26	23	26	22	19	20	17	15	13				
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	18	16	14	12				
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20215	20215	20215	20215
5°	22663	20345	18029	20345
10°	25968	20179	15603	20179
15°	28727	19809	13785	19809
20°	28290	19411	12565	19411
25°	25509	18884	11794	18884
30°	21080	18040	11231	18040
35°	15364	17156	10831	17156
40°	12271	16115	10608	16115
45°	10723	14908	10305	14908
50°	10078	13742	10105	13742
55°	9292	12555	9833	12555
60°	8512	11296	9416	11296
65°	7755	10166	9005	10166
70°	7039	9064	8403	9064
75°	6245	7829	7442	7829
80°	5374	6481	5997	6481
85°	4817	4817	3557	4817



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.2	1.6
10°-20°	346.6	4.7
20°-30°	503.1	6.8
30°-40°	530.9	7.1
40°-50°	470.0	6.3
50°-60°	375.1	5.0
60°-70°	254.9	3.4
70°-80°	130.7	1.8
80°-90°	35.4	0.5
90°-100°	53.1	0.7
100°-110°	194.9	2.6
110°-120°	521.0	7.0
120°-130°	860.1	11.6
130°-140°	914.7	12.3
140°-150°	850.1	11.4
150°-160°	683.5	9.2
160°-170°	440.5	5.9
170°-180°	151.6	2.0
0°-30°	968.9	13.0
0°-40°	1499.8	20.2
0°-60°	2344.9	31.5
0°-90°	2766.0	37.2
90°-120°	769.1	10.3
90°-150°	3394.0	45.6
90°-180°	4670.0	62.8
0°-180°	7435.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1252	1252	1252	1252	1252	
5°	1398	1255	1112	1255	1398	140
15°	1719	1185	825	1185	1719	474
25°	1432	1060	662	1060	1432	647
35°	780	870	550	870	780	507
45°	470	653	451	653	470	369
55°	330	446	349	446	330	296
65°	203	266	236	266	203	202
75°	100	126	119	126	100	107
85°	26	26	19	26	26	29
90°	31	1	31	1	31	15
95°	50	75	50	75	50	46
105°	88	350	88	350	88	91
115°	94	663	94	663	94	237
125°	986	937	986	937	986	853
135°	1198	1160	1198	1160	1198	923
145°	1366	1346	1366	1346	1366	854
155°	1483	1482	1483	1482	1483	684
165°	1558	1561	1558	1561	1558	440
175°	1588	1597	1588	1597	1588	151
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1309.7	1310.0	1310.9	1304.7	1303.9	1303.9	1298.5	1293.9	1288.5	1281.2	1282.0
5°	1398.3	1403.5	1405.4	1399.7	1391.0	1390.1	1381.9	1368.4	1355.8	1345.8	1338.6
7.5°	1503.9	1506.0	1501.3	1493.6	1487.2	1475.7	1460.5	1445.6	1424.7	1405.5	1391.3
10°	1583.9	1586.9	1578.7	1567.6	1558.5	1545.0	1522.9	1500.2	1472.8	1446.3	1425.1
12.5°	1644.7	1651.9	1641.4	1639.9	1624.3	1605.8	1579.4	1568.0	1529.4	1492.5	1469.8
15°	1718.6	1718.2	1719.2	1710.1	1698.5	1695.5	1667.6	1637.4	1583.0	1561.3	1523.8
17.5°	1697.3	1704.6	1708.0	1707.9	1707.6	1705.8	1696.9	1677.7	1650.5	1615.3	1572.0
20°	1646.5	1656.1	1657.6	1668.7	1674.9	1683.1	1686.4	1681.1	1664.3	1634.9	1597.4
22.5°	1568.0	1570.7	1575.2	1592.4	1606.0	1626.5	1637.2	1655.0	1648.5	1634.2	1602.8
25°	1431.9	1427.1	1444.0	1452.6	1483.8	1516.6	1540.2	1566.1	1589.2	1603.2	1594.0
27.5°	1268.5	1261.3	1286.5	1309.5	1334.9	1370.4	1407.1	1450.5	1486.6	1531.7	1547.2
30°	1130.7	1135.0	1159.1	1183.6	1222.1	1272.1	1313.5	1361.2	1412.7	1463.2	1498.3
32.5°	982.1	998.8	1014.0	1051.6	1085.4	1141.3	1201.9	1261.5	1325.7	1383.1	1437.5
35°	779.5	798.7	819.9	847.3	894.9	950.3	1009.5	1089.8	1177.4	1255.8	1320.3
37.5°	656.1	653.0	665.2	684.9	723.6	768.2	836.3	915.8	1018.8	1111.0	1201.9
40°	582.2	580.2	588.9	607.2	636.6	669.3	729.0	798.7	894.5	1007.0	1115.3
42.5°	531.4	532.5	537.3	550.3	570.3	597.3	642.0	701.3	789.0	895.0	1011.3
45°	469.6	473.0	478.2	484.6	496.1	518.2	543.2	585.6	654.9	743.4	857.9
47.5°	425.2	425.3	430.6	436.1	443.0	455.4	475.9	502.4	551.3	623.4	721.8
50°	401.2	397.9	401.8	406.0	413.3	422.0	435.5	460.4	493.1	551.4	633.7
52.5°	372.0	372.1	375.6	377.2	383.7	392.3	404.6	422.0	451.6	497.1	564.8
55°	330.1	332.4	334.4	337.2	343.1	349.3	358.9	370.5	393.6	427.7	477.8
57.5°	290.6	291.3	293.3	298.8	302.5	308.2	317.4	327.8	342.9	368.2	405.8
60°	263.6	263.6	267.5	269.9	274.8	280.5	287.8	297.8	311.3	332.0	362.3
62.5°	239.0	238.7	240.2	244.1	247.8	253.2	260.4	269.0	281.6	300.0	325.0
65°	203.0	202.1	205.0	205.9	209.8	215.1	220.8	230.0	240.1	253.5	275.7
67.5°	168.4	169.6	171.1	173.0	175.0	180.6	184.5	191.0	199.4	210.7	225.6
70°	149.1	149.1	149.1	150.6	153.4	156.4	160.2	165.5	173.7	183.3	196.8
72.5°	127.6	129.1	130.6	129.8	133.5	135.2	139.8	142.8	150.6	156.7	168.7
75°	100.1	100.1	100.1	102.5	104.0	105.4	108.3	111.1	115.0	122.7	128.9
77.5°	74.6	74.5	74.9	75.5	77.1	78.8	79.6	82.3	85.9	89.4	94.7
80°	57.8	58.7	59.2	60.1	60.1	61.1	61.5	64.9	67.4	69.7	73.1
82.5°	44.7	44.9	45.0	45.1	45.5	46.1	47.3	48.4	49.3	51.3	53.9
85°	26.0	25.5	25.5	26.5	26.0	26.0	27.0	27.9	27.9	28.4	29.8
87.5°	16.2	16.1	16.4	15.9	15.8	16.0	15.7	15.2	15.3	15.4	15.4
90°	31.1	30.6	30.1	29.6	29.1	28.2	26.9	25.6	24.3	23.1	21.0
92.5°	31.1	30.8	30.5	30.2	29.9	29.4	28.7	28.1	27.4	26.8	25.7
95°	49.6	49.9	50.0	50.3	50.6	50.0	48.8	47.5	46.3	45.0	43.2
97.5°	66.2	65.9	65.6	65.2	64.9	64.3	63.2	62.2	61.2	60.2	56.1
100°	77.3	76.7	76.3	75.7	75.2	73.9	71.8	69.8	67.8	65.7	61.4
102.5°	82.8	82.1	81.3	80.6	79.9	78.2	75.6	72.9	70.2	67.6	104.0
105°	87.7	86.6	85.6	84.5	83.5	81.6	78.8	76.0	73.1	70.3	140.3
107.5°	90.2	89.2	88.1	87.1	86.1	87.0	89.8	92.7	95.6	98.5	182.4
110°	91.0	90.1	89.1	88.0	87.0	99.2	124.9	150.5	176.2	201.8	275.8



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	92.0	91.1	90.4	89.5	88.7	135.1	228.6	322.0	415.5	508.9	527.3
115°	94.5	113.0	131.5	149.9	168.3	236.9	355.5	474.1	592.8	711.4	705.0
117.5°	386.0	446.7	507.3	567.9	628.5	673.2	701.8	730.6	759.2	788.0	783.5
120°	703.3	737.9	772.5	807.1	841.7	857.4	854.3	851.3	848.2	845.1	840.6
122.5°	877.6	884.4	891.1	897.8	904.5	906.9	905.1	903.2	901.4	899.6	894.6
125°	985.8	985.1	984.3	983.4	982.7	981.5	979.7	977.9	976.1	974.3	969.4
127.5°	1054.0	1053.9	1053.8	1053.6	1053.5	1052.1	1049.4	1046.8	1044.2	1041.6	1037.9
130°	1096.5	1096.7	1097.0	1097.2	1097.5	1096.2	1093.4	1090.6	1087.8	1085.0	1082.1
132.5°	1138.0	1138.2	1138.5	1138.8	1139.0	1137.9	1135.5	1133.1	1130.7	1128.3	1125.5
135°	1198.0	1198.4	1199.0	1199.5	1200.0	1199.0	1196.4	1193.8	1191.3	1188.7	1186.4
137.5°	1252.5	1253.5	1254.3	1255.2	1256.0	1255.3	1252.7	1250.2	1247.7	1245.2	1242.6
140°	1286.8	1288.0	1289.3	1290.5	1291.8	1291.4	1289.0	1286.8	1284.4	1282.1	1279.3
142.5°	1319.9	1321.2	1322.5	1323.8	1325.0	1324.6	1322.6	1320.4	1318.3	1316.3	1313.0
145°	1366.3	1367.5	1368.9	1370.1	1371.4	1371.1	1369.3	1367.5	1365.7	1364.0	1359.6
147.5°	1407.1	1408.2	1409.2	1410.3	1411.4	1411.3	1409.9	1408.6	1407.3	1405.9	1401.7
150°	1432.0	1433.2	1434.5	1435.9	1437.1	1437.0	1435.5	1433.9	1432.4	1430.9	1426.7
152.5°	1453.2	1454.9	1456.6	1458.3	1460.0	1460.1	1458.5	1457.0	1455.5	1453.9	1450.0
155°	1482.7	1484.8	1486.9	1488.8	1490.9	1491.2	1489.7	1488.1	1486.6	1485.1	1482.0
157.5°	1509.7	1511.7	1513.7	1515.7	1517.7	1517.9	1516.1	1514.4	1512.6	1510.9	1508.7
160°	1525.4	1527.2	1529.0	1530.8	1532.6	1532.7	1531.2	1529.7	1528.0	1526.5	1525.0
162.5°	1538.3	1540.5	1542.7	1544.9	1547.1	1547.4	1545.6	1543.9	1542.1	1540.4	1539.1
165°	1557.6	1559.4	1561.2	1563.0	1564.8	1564.8	1563.0	1561.2	1559.4	1557.6	1556.9
167.5°	1569.9	1572.2	1574.5	1576.8	1579.1	1579.3	1577.5	1575.7	1574.0	1572.2	1571.5
170°	1577.3	1579.6	1581.9	1584.2	1586.5	1586.8	1585.0	1583.2	1581.4	1579.6	1579.0
172.5°	1582.8	1585.1	1587.4	1589.7	1592.0	1592.2	1590.4	1588.7	1586.9	1585.1	1584.6
175°	1587.6	1590.2	1592.8	1595.3	1597.9	1598.3	1596.5	1594.7	1592.9	1591.1	1590.6
177.5°	1590.6	1592.5	1594.3	1596.2	1598.0	1598.3	1596.8	1595.3	1593.9	1592.5	1592.2
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1284.7	1281.6	1279.7	1272.7	1266.6	1260.5	1258.5	1259.2	1250.8	1242.7	1239.3
5°	1334.7	1325.1	1316.0	1303.0	1287.6	1270.7	1262.1	1255.3	1238.5	1220.2	1209.7
7.5°	1379.6	1365.8	1348.2	1323.7	1301.4	1274.9	1258.0	1243.1	1218.4	1192.7	1176.9
10°	1406.9	1388.1	1365.5	1335.7	1308.2	1276.0	1253.4	1230.8	1201.9	1171.1	1151.9
12.5°	1430.4	1405.0	1382.8	1344.5	1312.1	1271.8	1244.9	1213.1	1182.7	1146.1	1127.3
15°	1486.3	1439.6	1397.2	1354.0	1314.0	1257.7	1227.9	1185.1	1145.1	1099.9	1078.3
17.5°	1529.5	1477.1	1410.3	1355.3	1308.7	1246.4	1202.6	1151.3	1104.1	1052.3	1022.9
20°	1554.2	1493.9	1422.3	1356.9	1301.0	1229.8	1182.2	1129.7	1074.4	1016.2	984.4
22.5°	1568.8	1505.5	1434.6	1351.0	1285.6	1216.4	1156.4	1098.9	1042.8	980.1	946.7
25°	1573.4	1515.6	1440.6	1346.2	1266.4	1188.0	1115.8	1060.0	992.1	933.4	884.9
27.5°	1550.5	1509.1	1436.9	1337.2	1244.2	1152.4	1072.0	1008.8	937.2	873.5	824.6
30°	1522.4	1498.3	1428.0	1327.9	1226.4	1127.8	1039.2	967.6	896.4	831.9	781.8
32.5°	1478.8	1473.7	1411.9	1314.8	1207.6	1096.6	1005.0	932.6	853.7	790.3	742.6
35°	1393.5	1416.5	1377.5	1285.6	1172.1	1052.3	953.2	870.4	788.6	728.0	683.2
37.5°	1278.9	1336.2	1326.1	1242.8	1124.2	1004.0	894.6	808.0	730.1	668.9	625.0
40°	1200.0	1273.1	1283.7	1210.1	1090.3	966.7	850.6	764.6	688.5	632.7	588.4
42.5°	1115.3	1200.8	1229.8	1170.8	1053.3	927.4	811.4	722.2	647.0	592.7	553.5
45°	973.4	1086.5	1138.9	1105.2	991.6	862.7	743.4	652.9	584.6	533.6	503.3
47.5°	840.7	964.2	1034.7	1022.8	923.0	795.3	677.4	590.6	524.1	483.3	456.2
50°	746.8	873.7	958.9	962.8	873.7	747.2	628.9	547.1	486.0	448.0	425.8
52.5°	665.2	786.4	879.3	899.7	818.7	697.2	585.4	504.0	450.2	415.2	395.4
55°	558.6	661.1	764.0	801.6	736.6	621.1	517.7	446.0	395.5	371.5	354.1
57.5°	464.4	549.9	645.0	686.5	646.4	547.5	450.5	388.3	347.3	326.2	312.9
60°	414.7	482.1	566.8	616.3	581.7	493.7	409.0	349.8	316.1	297.4	284.8
62.5°	368.5	428.2	499.8	545.2	526.3	443.3	367.4	315.2	286.1	268.4	259.5
65°	304.1	351.3	406.6	448.5	435.9	372.9	310.9	266.1	243.0	229.0	221.8
67.5°	250.4	284.5	322.8	359.5	349.4	304.7	255.0	220.1	202.8	190.9	186.5
70°	216.5	242.5	276.6	306.0	297.8	261.3	221.8	192.0	177.1	166.9	162.6
72.5°	184.2	205.6	231.6	255.6	250.1	219.7	186.8	164.3	152.8	143.5	139.9
75°	139.0	155.4	171.3	187.2	185.7	162.1	142.9	125.5	116.4	109.2	107.7
77.5°	102.6	111.8	122.6	132.1	129.4	115.9	100.9	91.0	84.2	79.4	78.6
80°	78.4	83.7	91.4	98.1	94.8	89.0	77.0	69.7	64.9	60.1	58.2
82.5°	56.8	62.2	66.8	70.4	67.9	62.5	55.0	50.1	47.2	44.0	43.2
85°	29.8	32.7	34.7	35.6	34.7	31.3	27.9	26.0	23.6	22.1	21.7
87.5°	15.4	14.9	14.5	14.8	13.1	12.5	10.5	8.7	8.9	9.0	8.9
90°	18.9	16.9	14.9	12.4	9.6	6.8	4.0	1.1	4.0	6.8	9.6
92.5°	24.7	23.7	22.6	22.2	22.5	22.8	23.0	23.3	23.0	22.8	22.5
95°	41.4	39.6	37.8	41.1	49.6	58.1	66.4	74.9	66.4	58.1	49.6
97.5°	51.8	47.7	43.5	53.4	77.3	101.0	124.9	148.7	124.9	101.0	77.3
100°	57.0	52.7	48.3	63.7	98.8	133.8	169.0	204.1	169.0	133.8	98.8
102.5°	140.4	176.8	213.3	235.3	242.7	250.1	257.5	264.9	257.5	250.1	242.7
105°	210.2	280.2	350.2	381.3	373.5	365.9	358.2	350.5	358.2	365.9	373.5
107.5°	266.3	350.2	434.0	472.9	466.7	460.4	454.2	448.1	454.2	460.4	466.7
110°	349.9	424.0	497.9	532.3	526.9	521.5	516.1	510.8	516.1	521.5	526.9



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	545.5	563.8	582.1	588.9	584.1	579.3	574.6	569.8	574.6	579.3	584.1
115°	698.6	692.2	685.8	680.4	676.0	671.7	667.3	663.0	667.3	671.7	676.0
117.5°	779.1	774.7	770.3	765.7	760.8	755.9	751.1	746.2	751.1	755.9	760.8
120°	835.9	831.3	826.7	822.5	818.6	814.7	811.0	807.1	811.0	814.7	818.6
122.5°	889.5	884.5	879.5	875.0	870.9	866.9	862.8	858.8	862.8	866.9	870.9
125°	964.5	959.7	954.8	950.6	947.3	944.1	940.7	937.4	940.7	944.1	947.3
127.5°	1034.3	1030.7	1027.1	1023.4	1019.7	1016.0	1012.3	1008.6	1012.3	1016.0	1019.7
130°	1079.3	1076.5	1073.7	1070.3	1066.1	1062.1	1057.9	1053.9	1057.9	1062.1	1066.1
132.5°	1122.7	1119.8	1117.0	1113.9	1110.4	1106.9	1103.4	1099.9	1103.4	1106.9	1110.4
135°	1184.1	1181.8	1179.5	1176.3	1172.1	1168.1	1163.9	1159.9	1163.9	1168.1	1172.1
137.5°	1240.0	1237.4	1234.7	1232.0	1229.2	1226.2	1223.4	1220.5	1223.4	1226.2	1229.2
140°	1276.5	1273.7	1270.8	1268.4	1266.3	1264.3	1262.3	1260.2	1262.3	1264.3	1266.3
142.5°	1309.8	1306.6	1303.3	1300.8	1298.9	1297.1	1295.2	1293.5	1295.2	1297.1	1298.9
145°	1355.3	1350.9	1346.5	1344.5	1344.7	1345.0	1345.3	1345.5	1345.3	1345.0	1344.7
147.5°	1397.3	1393.0	1388.7	1387.0	1388.0	1389.0	1390.0	1390.9	1390.0	1389.0	1388.0
150°	1422.7	1418.5	1414.5	1413.2	1415.0	1416.9	1418.7	1420.5	1418.7	1416.9	1415.0
152.5°	1446.1	1442.2	1438.3	1437.4	1439.4	1441.3	1443.4	1445.4	1443.4	1441.3	1439.4
155°	1478.8	1475.8	1472.7	1472.3	1474.6	1477.0	1479.2	1481.6	1479.2	1477.0	1474.6
157.5°	1506.6	1504.4	1502.2	1502.1	1504.1	1506.0	1508.0	1510.0	1508.0	1506.0	1504.1
160°	1523.4	1521.9	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5	1525.0	1523.4	1521.9
162.5°	1537.7	1536.3	1535.0	1535.1	1536.7	1538.2	1539.7	1541.3	1539.7	1538.2	1536.7
165°	1556.1	1555.4	1554.6	1555.0	1556.5	1558.0	1559.6	1561.1	1559.6	1558.0	1556.5
167.5°	1570.7	1570.1	1569.3	1569.7	1571.3	1572.8	1574.3	1575.9	1574.3	1572.8	1571.3
170°	1578.6	1578.0	1577.5	1578.0	1579.6	1581.1	1582.6	1584.2	1582.6	1581.1	1579.6
172.5°	1584.0	1583.6	1583.1	1583.6	1585.1	1586.7	1588.2	1589.7	1588.2	1586.7	1585.1
175°	1590.1	1589.6	1589.0	1589.7	1591.5	1593.3	1595.1	1596.9	1595.1	1593.3	1591.5
177.5°	1592.0	1591.9	1591.7	1592.2	1593.7	1595.2	1596.6	1598.0	1596.6	1595.2	1593.7
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1235.4	1233.1	1225.0	1220.8	1213.8	1207.3	1203.1	1205.0	1206.5	1205.8	1204.6
5°	1200.0	1190.8	1176.9	1164.9	1156.2	1140.3	1133.6	1130.2	1127.4	1124.0	1120.6
7.5°	1157.8	1143.4	1123.4	1106.3	1090.1	1070.4	1059.1	1052.3	1045.5	1037.8	1031.1
10°	1127.8	1107.6	1086.5	1062.3	1043.1	1025.3	1009.5	998.9	989.3	980.1	973.4
12.5°	1096.3	1073.0	1046.8	1013.9	992.7	967.2	964.8	946.1	931.1	925.5	917.6
15°	1046.0	1013.3	980.1	941.1	924.3	901.2	886.7	872.3	859.3	850.2	847.8
17.5°	988.9	946.6	913.6	885.6	858.0	834.3	821.0	809.5	798.8	786.6	784.9
20°	945.5	908.9	872.8	848.3	819.9	795.8	779.5	767.9	758.7	751.6	745.3
22.5°	904.3	864.2	831.2	804.4	776.4	757.0	744.0	732.9	725.3	717.3	711.4
25°	838.2	806.9	770.8	740.5	717.4	704.9	694.3	684.7	679.9	674.6	667.9
27.5°	780.3	745.6	711.8	688.3	668.1	657.0	649.4	642.9	638.4	635.3	631.5
30°	739.5	704.4	678.0	654.9	638.0	627.0	622.2	618.3	613.0	611.1	609.2
32.5°	700.3	668.6	646.0	625.9	609.9	602.7	598.2	594.8	590.7	588.7	584.8
35°	644.7	618.3	596.2	585.0	572.1	565.8	562.5	557.6	553.8	551.9	551.4
37.5°	592.5	569.5	555.0	540.7	535.3	531.4	526.8	523.5	522.4	522.1	521.6
40°	558.6	539.9	526.9	515.3	512.9	507.1	503.3	500.4	500.4	500.9	500.4
42.5°	527.8	511.0	499.5	489.6	486.7	483.2	479.4	479.2	480.0	481.6	480.0
45°	481.2	469.1	460.9	456.1	450.8	447.4	447.0	448.5	448.9	449.4	450.8
47.5°	438.2	430.3	422.8	417.5	415.2	414.6	414.1	416.6	418.9	419.7	422.0
50°	412.8	403.7	397.5	394.1	392.1	391.2	392.1	395.0	396.9	399.4	400.8
52.5°	384.4	377.9	373.5	371.0	370.2	370.8	371.0	374.3	377.3	378.1	378.9
55°	345.0	340.2	339.2	334.9	336.8	336.3	338.7	340.6	343.6	346.4	346.9
57.5°	305.8	301.9	299.3	299.6	300.2	302.4	304.3	307.7	310.9	313.9	314.1
60°	279.6	277.6	276.2	276.2	277.1	280.0	282.5	285.8	287.8	289.6	291.1
62.5°	255.7	253.7	252.3	253.1	255.6	257.3	260.1	261.9	263.8	265.8	266.5
65°	217.9	217.0	218.5	219.4	219.9	222.3	225.6	227.1	229.0	230.0	233.4
67.5°	183.2	183.4	183.2	184.5	187.4	187.9	191.1	194.4	194.8	196.7	198.9
70°	159.8	160.7	161.6	162.6	165.0	166.0	168.4	169.8	171.7	173.2	174.7
72.5°	138.2	138.4	139.3	139.1	141.2	143.3	145.3	146.8	148.6	150.5	151.9
75°	106.3	106.3	107.3	107.7	110.2	112.6	112.1	113.1	115.0	116.9	117.9
77.5°	77.7	76.6	77.7	78.1	78.9	81.0	81.3	82.7	84.8	84.2	85.3
80°	59.2	57.8	59.2	59.7	59.7	62.1	62.1	63.1	64.5	63.1	64.5
82.5°	42.2	41.6	42.6	42.7	43.5	43.5	44.4	44.6	46.0	45.3	46.0
85°	21.2	20.7	21.2	20.7	21.2	21.7	21.7	21.2	21.2	22.1	20.7
87.5°	9.0	9.1	9.1	9.5	9.6	9.6	9.5	9.7	10.0	9.5	9.7
90°	12.4	14.9	16.9	18.9	21.0	23.1	24.3	25.6	26.9	28.2	29.1
92.5°	22.2	22.6	23.7	24.7	25.7	26.8	27.4	28.1	28.7	29.4	29.9
95°	41.1	37.8	39.6	41.4	43.2	45.0	46.3	47.5	48.8	50.0	50.6
97.5°	53.4	43.5	47.7	51.8	56.1	60.2	61.2	62.2	63.2	64.3	64.9
100°	63.7	48.3	52.7	57.0	61.4	65.7	67.8	69.8	71.8	73.9	75.2
102.5°	235.3	213.3	176.8	140.4	104.0	67.6	70.2	72.9	75.6	78.2	79.9
105°	381.3	350.2	280.2	210.2	140.3	70.3	73.1	76.0	78.8	81.6	83.5
107.5°	472.9	434.0	350.2	266.3	182.4	98.5	95.6	92.7	89.8	87.0	86.1
110°	532.3	497.9	424.0	349.9	275.8	201.8	176.2	150.5	124.9	99.2	87.0



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	588.9	582.1	563.8	545.5	527.3	508.9	415.5	322.0	228.6	135.1	88.7
115°	680.4	685.8	692.2	698.6	705.0	711.4	592.8	474.1	355.5	236.9	168.3
117.5°	765.7	770.3	774.7	779.1	783.5	788.0	759.2	730.6	701.8	673.2	628.5
120°	822.5	826.7	831.3	835.9	840.6	845.1	848.2	851.3	854.3	857.4	841.7
122.5°	875.0	879.5	884.5	889.5	894.6	899.6	901.4	903.2	905.1	906.9	904.5
125°	950.6	954.8	959.7	964.5	969.4	974.3	976.1	977.9	979.7	981.5	982.7
127.5°	1023.4	1027.1	1030.7	1034.3	1037.9	1041.6	1044.2	1046.8	1049.4	1052.1	1053.5
130°	1070.3	1073.7	1076.5	1079.3	1082.1	1085.0	1087.8	1090.6	1093.4	1096.2	1097.5
132.5°	1113.9	1117.0	1119.8	1122.7	1125.5	1128.3	1130.7	1133.1	1135.5	1137.9	1139.0
135°	1176.3	1179.5	1181.8	1184.1	1186.4	1188.7	1191.3	1193.8	1196.4	1199.0	1200.0
137.5°	1232.0	1234.7	1237.4	1240.0	1242.6	1245.2	1247.7	1250.2	1252.7	1255.3	1256.0
140°	1268.4	1270.8	1273.7	1276.5	1279.3	1282.1	1284.4	1286.8	1289.0	1291.4	1291.8
142.5°	1300.8	1303.3	1306.6	1309.8	1313.0	1316.3	1318.3	1320.4	1322.6	1324.6	1325.0
145°	1344.5	1346.5	1350.9	1355.3	1359.6	1364.0	1365.7	1367.5	1369.3	1371.1	1371.4
147.5°	1387.0	1388.7	1393.0	1397.3	1401.7	1405.9	1407.3	1408.6	1409.9	1411.3	1411.4
150°	1413.2	1414.5	1418.5	1422.7	1426.7	1430.9	1432.4	1433.9	1435.5	1437.0	1437.1
152.5°	1437.4	1438.3	1442.2	1446.1	1450.0	1453.9	1455.5	1457.0	1458.5	1460.1	1460.0
155°	1472.3	1472.7	1475.8	1478.8	1482.0	1485.1	1486.6	1488.1	1489.7	1491.2	1490.9
157.5°	1502.1	1502.2	1504.4	1506.6	1508.7	1510.9	1512.6	1514.4	1516.1	1517.9	1517.7
160°	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5	1528.0	1529.7	1531.2	1532.7	1532.6
162.5°	1535.1	1535.0	1536.3	1537.7	1539.1	1540.4	1542.1	1543.9	1545.6	1547.4	1547.1
165°	1555.0	1554.6	1555.4	1556.1	1556.9	1557.6	1559.4	1561.2	1563.0	1564.8	1564.8
167.5°	1569.7	1569.3	1570.1	1570.7	1571.5	1572.2	1574.0	1575.7	1577.5	1579.3	1579.1
170°	1578.0	1577.5	1578.0	1578.6	1579.0	1579.6	1581.4	1583.2	1585.0	1586.8	1586.5
172.5°	1583.6	1583.1	1583.6	1584.0	1584.6	1585.1	1586.9	1588.7	1590.4	1592.2	1592.0
175°	1589.7	1589.0	1589.6	1590.1	1590.6	1591.1	1592.9	1594.7	1596.5	1598.3	1597.9
177.5°	1592.2	1591.7	1591.9	1592.0	1592.2	1592.5	1593.9	1595.3	1596.8	1598.3	1598.0
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1200.8	1200.0	1200.0	1196.6	1200.0	1200.0	1200.8	1204.6	1205.8	1206.5	1205.0
5°	1113.9	1112.4	1110.0	1112.4	1110.0	1112.4	1113.9	1120.6	1124.0	1127.4	1130.2
7.5°	1027.9	1022.2	1021.3	1015.6	1021.3	1022.2	1027.9	1031.1	1037.8	1045.5	1052.3
10°	965.2	961.3	960.8	951.7	960.8	961.3	965.2	973.4	980.1	989.3	998.9
12.5°	917.5	908.2	910.0	904.7	910.0	908.2	917.5	917.6	925.5	931.1	946.1
15°	834.8	834.8	832.8	824.7	832.8	834.8	834.8	847.8	850.2	859.3	872.3
17.5°	775.4	774.5	769.9	772.1	769.9	774.5	775.4	784.9	786.6	798.8	809.5
20°	740.0	737.2	731.3	731.3	731.3	737.2	740.0	745.3	751.6	758.7	767.9
22.5°	706.5	706.3	700.2	702.1	700.2	706.3	706.5	711.4	717.3	725.3	732.9
25°	667.3	663.5	660.6	662.0	660.6	663.5	667.3	667.9	674.6	679.9	684.7
27.5°	630.2	628.1	627.9	624.0	627.9	628.1	630.2	631.5	635.3	638.4	642.9
30°	608.7	603.9	604.8	602.4	604.8	603.9	608.7	609.2	611.1	613.0	618.3
32.5°	584.0	582.3	581.4	579.3	581.4	582.3	584.0	584.8	588.7	590.7	594.8
35°	550.4	550.9	548.6	549.5	548.6	550.9	550.4	551.4	551.9	553.8	557.6
37.5°	521.1	522.6	521.5	521.8	521.5	522.6	521.1	521.6	522.1	522.4	523.5
40°	501.8	501.8	501.8	503.3	501.8	501.8	501.8	500.4	500.9	500.4	500.4
42.5°	483.3	482.6	481.8	481.7	481.8	482.6	483.3	480.0	481.6	480.0	479.2
45°	451.8	453.3	453.7	451.3	453.7	453.3	451.8	450.8	449.4	448.9	448.5
47.5°	423.2	423.4	423.2	425.4	423.2	423.4	423.2	422.0	419.7	418.9	416.6
50°	403.2	402.3	403.2	402.3	403.2	402.3	403.2	400.8	399.4	396.9	395.0
52.5°	382.0	382.2	381.6	381.4	381.6	382.2	382.0	378.9	378.1	377.3	374.3
55°	348.8	349.8	349.3	349.3	349.3	349.8	348.8	346.9	346.4	343.6	340.6
57.5°	314.5	315.4	316.0	313.9	316.0	315.4	314.5	314.1	313.9	310.9	307.7
60°	290.6	293.0	292.6	291.6	292.6	293.0	290.6	291.1	289.6	287.8	285.8
62.5°	268.7	269.6	269.5	269.3	269.5	269.6	268.7	266.5	265.8	263.8	261.9
65°	234.8	235.7	234.3	235.7	234.3	235.7	234.8	233.4	230.0	229.0	227.1
67.5°	198.3	198.6	199.7	200.4	199.7	198.6	198.3	198.9	196.7	194.8	194.4
70°	175.6	175.1	176.5	178.0	176.5	175.1	175.6	174.7	173.2	171.7	169.8
72.5°	151.7	152.8	152.3	153.4	152.3	152.8	151.7	151.9	150.5	148.6	146.8
75°	116.9	118.4	117.9	119.3	117.9	118.4	116.9	117.9	116.9	115.0	113.1
77.5°	84.5	84.6	84.5	85.3	84.5	84.6	84.5	85.3	84.2	84.8	82.7
80°	64.5	63.5	62.6	64.5	62.6	63.5	64.5	64.5	63.1	64.5	63.1
82.5°	44.9	45.4	44.5	44.5	44.5	45.4	44.9	46.0	45.3	46.0	44.6
85°	20.7	20.2	19.2	19.2	19.2	20.2	20.7	20.7	22.1	21.2	21.2
87.5°	9.8	9.5	9.6	9.3	9.6	9.5	9.8	9.7	9.5	10.0	9.7
90°	29.6	30.1	30.6	31.1	30.6	30.1	29.6	29.1	28.2	26.9	25.6
92.5°	30.2	30.5	30.8	31.1	30.8	30.5	30.2	29.9	29.4	28.7	28.1
95°	50.3	50.0	49.9	49.6	49.9	50.0	50.3	50.6	50.0	48.8	47.5
97.5°	65.2	65.6	65.9	66.2	65.9	65.6	65.2	64.9	64.3	63.2	62.2
100°	75.7	76.3	76.7	77.3	76.7	76.3	75.7	75.2	73.9	71.8	69.8
102.5°	80.6	81.3	82.1	82.8	82.1	81.3	80.6	79.9	78.2	75.6	72.9
105°	84.5	85.6	86.6	87.7	86.6	85.6	84.5	83.5	81.6	78.8	76.0
107.5°	87.1	88.1	89.2	90.2	89.2	88.1	87.1	86.1	87.0	89.8	92.7
110°	88.0	89.1	90.1	91.0	90.1	89.1	88.0	87.0	99.2	124.9	150.5



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	89.5	90.4	91.1	92.0	91.1	90.4	89.5	88.7	135.1	228.6	322.0
115°	149.9	131.5	113.0	94.5	113.0	131.5	149.9	168.3	236.9	355.5	474.1
117.5°	567.9	507.3	446.7	386.0	446.7	507.3	567.9	628.5	673.2	701.8	730.6
120°	807.1	772.5	737.9	703.3	737.9	772.5	807.1	841.7	857.4	854.3	851.3
122.5°	897.8	891.1	884.4	877.6	884.4	891.1	897.8	904.5	906.9	905.1	903.2
125°	983.4	984.3	985.1	985.8	985.1	984.3	983.4	982.7	981.5	979.7	977.9
127.5°	1053.6	1053.8	1053.9	1054.0	1053.9	1053.8	1053.6	1053.5	1052.1	1049.4	1046.8
130°	1097.2	1097.0	1096.7	1096.5	1096.7	1097.0	1097.2	1097.5	1096.2	1093.4	1090.6
132.5°	1138.8	1138.5	1138.2	1138.0	1138.2	1138.5	1138.8	1139.0	1137.9	1135.5	1133.1
135°	1199.5	1199.0	1198.4	1198.0	1198.4	1199.0	1199.5	1200.0	1199.0	1196.4	1193.8
137.5°	1255.2	1254.3	1253.5	1252.5	1253.5	1254.3	1255.2	1256.0	1255.3	1252.7	1250.2
140°	1290.5	1289.3	1288.0	1286.8	1288.0	1289.3	1290.5	1291.8	1291.4	1289.0	1286.8
142.5°	1323.8	1322.5	1321.2	1319.9	1321.2	1322.5	1323.8	1325.0	1324.6	1322.6	1320.4
145°	1370.1	1368.9	1367.5	1366.3	1367.5	1368.9	1370.1	1371.4	1371.1	1369.3	1367.5
147.5°	1410.3	1409.2	1408.2	1407.1	1408.2	1409.2	1410.3	1411.4	1411.3	1409.9	1408.6
150°	1435.9	1434.5	1433.2	1432.0	1433.2	1434.5	1435.9	1437.1	1437.0	1435.5	1433.9
152.5°	1458.3	1456.6	1454.9	1453.2	1454.9	1456.6	1458.3	1460.0	1460.1	1458.5	1457.0
155°	1488.8	1486.9	1484.8	1482.7	1484.8	1486.9	1488.8	1490.9	1491.2	1489.7	1488.1
157.5°	1515.7	1513.7	1511.7	1509.7	1511.7	1513.7	1515.7	1517.7	1517.9	1516.1	1514.4
160°	1530.8	1529.0	1527.2	1525.4	1527.2	1529.0	1530.8	1532.6	1532.7	1531.2	1529.7
162.5°	1544.9	1542.7	1540.5	1538.3	1540.5	1542.7	1544.9	1547.1	1547.4	1545.6	1543.9
165°	1563.0	1561.2	1559.4	1557.6	1559.4	1561.2	1563.0	1564.8	1564.8	1563.0	1561.2
167.5°	1576.8	1574.5	1572.2	1569.9	1572.2	1574.5	1576.8	1579.1	1579.3	1577.5	1575.7
170°	1584.2	1581.9	1579.6	1577.3	1579.6	1581.9	1584.2	1586.5	1586.8	1585.0	1583.2
172.5°	1589.7	1587.4	1585.1	1582.8	1585.1	1587.4	1589.7	1592.0	1592.2	1590.4	1588.7
175°	1595.3	1592.8	1590.2	1587.6	1590.2	1592.8	1595.3	1597.9	1598.3	1596.5	1594.7
177.5°	1596.2	1594.3	1592.5	1590.6	1592.5	1594.3	1596.2	1598.0	1598.3	1596.8	1595.3
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1203.1	1207.3	1213.8	1220.8	1225.0	1233.1	1235.4	1239.3	1242.7	1250.8	1259.2
5°	1133.6	1140.3	1156.2	1164.9	1176.9	1190.8	1200.0	1209.7	1220.2	1238.5	1255.3
7.5°	1059.1	1070.4	1090.1	1106.3	1123.4	1143.4	1157.8	1176.9	1192.7	1218.4	1243.1
10°	1009.5	1025.3	1043.1	1062.3	1086.5	1107.6	1127.8	1151.9	1171.1	1201.9	1230.8
12.5°	964.8	967.2	992.7	1013.9	1046.8	1073.0	1096.3	1127.3	1146.1	1182.7	1213.1
15°	886.7	901.2	924.3	941.1	980.1	1013.3	1046.0	1078.3	1099.9	1145.1	1185.1
17.5°	821.0	834.3	858.0	885.6	913.6	946.6	988.9	1022.9	1052.3	1104.1	1151.3
20°	779.5	795.8	819.9	848.3	872.8	908.9	945.5	984.4	1016.2	1074.4	1129.7
22.5°	744.0	757.0	776.4	804.4	831.2	864.2	904.3	946.7	980.1	1042.8	1098.9
25°	694.3	704.9	717.4	740.5	770.8	806.9	838.2	884.9	933.4	992.1	1060.0
27.5°	649.4	657.0	668.1	688.3	711.8	745.6	780.3	824.6	873.5	937.2	1008.8
30°	622.2	627.0	638.0	654.9	678.0	704.4	739.5	781.8	831.9	896.4	967.6
32.5°	598.2	602.7	609.9	625.9	646.0	668.6	700.3	742.6	790.3	853.7	932.6
35°	562.5	565.8	572.1	585.0	596.2	618.3	644.7	683.2	728.0	788.6	870.4
37.5°	526.8	531.4	535.3	540.7	555.0	569.5	592.5	625.0	668.9	730.1	808.0
40°	503.3	507.1	512.9	515.3	526.9	539.9	558.6	588.4	632.7	688.5	764.6
42.5°	479.4	483.2	486.7	489.6	499.5	511.0	527.8	553.5	592.7	647.0	722.2
45°	447.0	447.4	450.8	456.1	460.9	469.1	481.2	503.3	533.6	584.6	652.9
47.5°	414.1	414.6	415.2	417.5	422.8	430.3	438.2	456.2	483.3	524.1	590.6
50°	392.1	391.2	392.1	394.1	397.5	403.7	412.8	425.8	448.0	486.0	547.1
52.5°	371.0	370.8	370.2	371.0	373.5	377.9	384.4	395.4	415.2	450.2	504.0
55°	338.7	336.3	336.8	334.9	339.2	340.2	345.0	354.1	371.5	395.5	446.0
57.5°	304.3	302.4	300.2	299.6	299.3	301.9	305.8	312.9	326.2	347.3	388.3
60°	282.5	280.0	277.1	276.2	276.2	277.6	279.6	284.8	297.4	316.1	349.8
62.5°	260.1	257.3	255.6	253.1	252.3	253.7	255.7	259.5	268.4	286.1	315.2
65°	225.6	222.3	219.9	219.4	218.5	217.0	217.9	221.8	229.0	243.0	266.1
67.5°	191.1	187.9	187.4	184.5	183.2	183.4	183.2	186.5	190.9	202.8	220.1
70°	168.4	166.0	165.0	162.6	161.6	160.7	159.8	162.6	166.9	177.1	192.0
72.5°	145.3	143.3	141.2	139.1	139.3	138.4	138.2	139.9	143.5	152.8	164.3
75°	112.1	112.6	110.2	107.7	107.3	106.3	106.3	107.7	109.2	116.4	125.5
77.5°	81.3	81.0	78.9	78.1	77.7	76.6	77.7	78.6	79.4	84.2	91.0
80°	62.1	62.1	59.7	59.7	59.2	57.8	59.2	58.2	60.1	64.9	69.7
82.5°	44.4	43.5	43.5	42.7	42.6	41.6	42.2	43.2	44.0	47.2	50.1
85°	21.7	21.7	21.2	20.7	21.2	20.7	21.2	21.7	22.1	23.6	26.0
87.5°	9.5	9.6	9.6	9.5	9.1	9.1	9.0	8.9	9.0	8.9	8.7
90°	24.3	23.1	21.0	18.9	16.9	14.9	12.4	9.6	6.8	4.0	1.1
92.5°	27.4	26.8	25.7	24.7	23.7	22.6	22.2	22.5	22.8	23.0	23.3
95°	46.3	45.0	43.2	41.4	39.6	37.8	41.1	49.6	58.1	66.4	74.9
97.5°	61.2	60.2	56.1	51.8	47.7	43.5	53.4	77.3	101.0	124.9	148.7
100°	67.8	65.7	61.4	57.0	52.7	48.3	63.7	98.8	133.8	169.0	204.1
102.5°	70.2	67.6	104.0	140.4	176.8	213.3	235.3	242.7	250.1	257.5	264.9
105°	73.1	70.3	140.3	210.2	280.2	350.2	381.3	373.5	365.9	358.2	350.5
107.5°	95.6	98.5	182.4	266.3	350.2	434.0	472.9	466.7	460.4	454.2	448.1
110°	176.2	201.8	275.8	349.9	424.0	497.9	532.3	526.9	521.5	516.1	510.8



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	415.5	508.9	527.3	545.5	563.8	582.1	588.9	584.1	579.3	574.6	569.8
115°	592.8	711.4	705.0	698.6	692.2	685.8	680.4	676.0	671.7	667.3	663.0
117.5°	759.2	788.0	783.5	779.1	774.7	770.3	765.7	760.8	755.9	751.1	746.2
120°	848.2	845.1	840.6	835.9	831.3	826.7	822.5	818.6	814.7	811.0	807.1
122.5°	901.4	899.6	894.6	889.5	884.5	879.5	875.0	870.9	866.9	862.8	858.8
125°	976.1	974.3	969.4	964.5	959.7	954.8	950.6	947.3	944.1	940.7	937.4
127.5°	1044.2	1041.6	1037.9	1034.3	1030.7	1027.1	1023.4	1019.7	1016.0	1012.3	1008.6
130°	1087.8	1085.0	1082.1	1079.3	1076.5	1073.7	1070.3	1066.1	1062.1	1057.9	1053.9
132.5°	1130.7	1128.3	1125.5	1122.7	1119.8	1117.0	1113.9	1110.4	1106.9	1103.4	1099.9
135°	1191.3	1188.7	1186.4	1184.1	1181.8	1179.5	1176.3	1172.1	1168.1	1163.9	1159.9
137.5°	1247.7	1245.2	1242.6	1240.0	1237.4	1234.7	1232.0	1229.2	1226.2	1223.4	1220.5
140°	1284.4	1282.1	1279.3	1276.5	1273.7	1270.8	1268.4	1266.3	1264.3	1262.3	1260.2
142.5°	1318.3	1316.3	1313.0	1309.8	1306.6	1303.3	1300.8	1298.9	1297.1	1295.2	1293.5
145°	1365.7	1364.0	1359.6	1355.3	1350.9	1346.5	1344.5	1344.7	1345.0	1345.3	1345.5
147.5°	1407.3	1405.9	1401.7	1397.3	1393.0	1388.7	1387.0	1388.0	1389.0	1390.0	1390.9
150°	1432.4	1430.9	1426.7	1422.7	1418.5	1414.5	1413.2	1415.0	1416.9	1418.7	1420.5
152.5°	1455.5	1453.9	1450.0	1446.1	1442.2	1438.3	1437.4	1439.4	1441.3	1443.4	1445.4
155°	1486.6	1485.1	1482.0	1478.8	1475.8	1472.7	1472.3	1474.6	1477.0	1479.2	1481.6
157.5°	1512.6	1510.9	1508.7	1506.6	1504.4	1502.2	1502.1	1504.1	1506.0	1508.0	1510.0
160°	1528.0	1526.5	1525.0	1523.4	1521.9	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5
162.5°	1542.1	1540.4	1539.1	1537.7	1536.3	1535.0	1535.1	1536.7	1538.2	1539.7	1541.3
165°	1559.4	1557.6	1556.9	1556.1	1555.4	1554.6	1555.0	1556.5	1558.0	1559.6	1561.1
167.5°	1574.0	1572.2	1571.5	1570.7	1570.1	1569.3	1569.7	1571.3	1572.8	1574.3	1575.9
170°	1581.4	1579.6	1579.0	1578.6	1578.0	1577.5	1578.0	1579.6	1581.1	1582.6	1584.2
172.5°	1586.9	1585.1	1584.6	1584.0	1583.6	1583.1	1583.6	1585.1	1586.7	1588.2	1589.7
175°	1592.9	1591.1	1590.6	1590.1	1589.6	1589.0	1589.7	1591.5	1593.3	1595.1	1596.9
177.5°	1593.9	1592.5	1592.2	1592.0	1591.9	1591.7	1592.2	1593.7	1595.2	1596.6	1598.0
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1258.5	1260.5	1266.6	1272.7	1279.7	1281.6	1284.7	1282.0	1281.2	1288.5	1293.9
5°	1262.1	1270.7	1287.6	1303.0	1316.0	1325.1	1334.7	1338.6	1345.8	1355.8	1368.4
7.5°	1258.0	1274.9	1301.4	1323.7	1348.2	1365.8	1379.6	1391.3	1405.5	1424.7	1445.6
10°	1253.4	1276.0	1308.2	1335.7	1365.5	1388.1	1406.9	1425.1	1446.3	1472.8	1500.2
12.5°	1244.9	1271.8	1312.1	1344.5	1382.8	1405.0	1430.4	1469.8	1492.5	1529.4	1568.0
15°	1227.9	1257.7	1314.0	1354.0	1397.2	1439.6	1486.3	1523.8	1561.3	1583.0	1637.4
17.5°	1202.6	1246.4	1308.7	1355.3	1410.3	1477.1	1529.5	1572.0	1615.3	1650.5	1677.7
20°	1182.2	1229.8	1301.0	1356.9	1422.3	1493.9	1554.2	1597.4	1634.9	1664.3	1681.1
22.5°	1156.4	1216.4	1285.6	1351.0	1434.6	1505.5	1568.8	1602.8	1634.2	1648.5	1655.0
25°	1115.8	1188.0	1266.4	1346.2	1440.6	1515.6	1573.4	1594.0	1603.2	1589.2	1566.1
27.5°	1072.0	1152.4	1244.2	1337.2	1436.9	1509.1	1550.5	1547.2	1531.7	1486.6	1450.5
30°	1039.2	1127.8	1226.4	1327.9	1428.0	1498.3	1522.4	1498.3	1463.2	1412.7	1361.2
32.5°	1005.0	1096.6	1207.6	1314.8	1411.9	1473.7	1478.8	1437.5	1383.1	1325.7	1261.5
35°	953.2	1052.3	1172.1	1285.6	1377.5	1416.5	1393.5	1320.3	1255.8	1177.4	1089.8
37.5°	894.6	1004.0	1124.2	1242.8	1326.1	1336.2	1278.9	1201.9	1111.0	1018.8	915.8
40°	850.6	966.7	1090.3	1210.1	1283.7	1273.1	1200.0	1115.3	1007.0	894.5	798.7
42.5°	811.4	927.4	1053.3	1170.8	1229.8	1200.8	1115.3	1011.3	895.0	789.0	701.3
45°	743.4	862.7	991.6	1105.2	1138.9	1086.5	973.4	857.9	743.4	654.9	585.6
47.5°	677.4	795.3	923.0	1022.8	1034.7	964.2	840.7	721.8	623.4	551.3	502.4
50°	628.9	747.2	873.7	962.8	958.9	873.7	746.8	633.7	551.4	493.1	460.4
52.5°	585.4	697.2	818.7	899.7	879.3	786.4	665.2	564.8	497.1	451.6	422.0
55°	517.7	621.1	736.6	801.6	764.0	661.1	558.6	477.8	427.7	393.6	370.5
57.5°	450.5	547.5	646.4	686.5	645.0	549.9	464.4	405.8	368.2	342.9	327.8
60°	409.0	493.7	581.7	616.3	566.8	482.1	414.7	362.3	332.0	311.3	297.8
62.5°	367.4	443.3	526.3	545.2	499.8	428.2	368.5	325.0	300.0	281.6	269.0
65°	310.9	372.9	435.9	448.5	406.6	351.3	304.1	275.7	253.5	240.1	230.0
67.5°	255.0	304.7	349.4	359.5	322.8	284.5	250.4	225.6	210.7	199.4	191.0
70°	221.8	261.3	297.8	306.0	276.6	242.5	216.5	196.8	183.3	173.7	165.5
72.5°	186.8	219.7	250.1	255.6	231.6	205.6	184.2	168.7	156.7	150.6	142.8
75°	142.9	162.1	185.7	187.2	171.3	155.4	139.0	128.9	122.7	115.0	111.1
77.5°	100.9	115.9	129.4	132.1	122.6	111.8	102.6	94.7	89.4	85.9	82.3
80°	77.0	89.0	94.8	98.1	91.4	83.7	78.4	73.1	69.7	67.4	64.9
82.5°	55.0	62.5	67.9	70.4	66.8	62.2	56.8	53.9	51.3	49.3	48.4
85°	27.9	31.3	34.7	35.6	34.7	32.7	29.8	29.8	28.4	27.9	27.9
87.5°	10.5	12.5	13.1	14.8	14.5	14.9	15.4	15.4	15.4	15.3	15.2
90°	4.0	6.8	9.6	12.4	14.9	16.9	18.9	21.0	23.1	24.3	25.6
92.5°	23.0	22.8	22.5	22.2	22.6	23.7	24.7	25.7	26.8	27.4	28.1
95°	66.4	58.1	49.6	41.1	37.8	39.6	41.4	43.2	45.0	46.3	47.5
97.5°	124.9	101.0	77.3	53.4	43.5	47.7	51.8	56.1	60.2	61.2	62.2
100°	169.0	133.8	98.8	63.7	48.3	52.7	57.0	61.4	65.7	67.8	69.8
102.5°	257.5	250.1	242.7	235.3	213.3	176.8	140.4	104.0	67.6	70.2	72.9
105°	358.2	365.9	373.5	381.3	350.2	280.2	210.2	140.3	70.3	73.1	76.0
107.5°	454.2	460.4	466.7	472.9	434.0	350.2	266.3	182.4	98.5	95.6	92.7
110°	516.1	521.5	526.9	532.3	497.9	424.0	349.9	275.8	201.8	176.2	150.5



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	574.6	579.3	584.1	588.9	582.1	563.8	545.5	527.3	508.9	415.5	322.0
115°	667.3	671.7	676.0	680.4	685.8	692.2	698.6	705.0	711.4	592.8	474.1
117.5°	751.1	755.9	760.8	765.7	770.3	774.7	779.1	783.5	788.0	759.2	730.6
120°	811.0	814.7	818.6	822.5	826.7	831.3	835.9	840.6	845.1	848.2	851.3
122.5°	862.8	866.9	870.9	875.0	879.5	884.5	889.5	894.6	899.6	901.4	903.2
125°	940.7	944.1	947.3	950.6	954.8	959.7	964.5	969.4	974.3	976.1	977.9
127.5°	1012.3	1016.0	1019.7	1023.4	1027.1	1030.7	1034.3	1037.9	1041.6	1044.2	1046.8
130°	1057.9	1062.1	1066.1	1070.3	1073.7	1076.5	1079.3	1082.1	1085.0	1087.8	1090.6
132.5°	1103.4	1106.9	1110.4	1113.9	1117.0	1119.8	1122.7	1125.5	1128.3	1130.7	1133.1
135°	1163.9	1168.1	1172.1	1176.3	1179.5	1181.8	1184.1	1186.4	1188.7	1191.3	1193.8
137.5°	1223.4	1226.2	1229.2	1232.0	1234.7	1237.4	1240.0	1242.6	1245.2	1247.7	1250.2
140°	1262.3	1264.3	1266.3	1268.4	1270.8	1273.7	1276.5	1279.3	1282.1	1284.4	1286.8
142.5°	1295.2	1297.1	1298.9	1300.8	1303.3	1306.6	1309.8	1313.0	1316.3	1318.3	1320.4
145°	1345.3	1345.0	1344.7	1344.5	1346.5	1350.9	1355.3	1359.6	1364.0	1365.7	1367.5
147.5°	1390.0	1389.0	1388.0	1387.0	1388.7	1393.0	1397.3	1401.7	1405.9	1407.3	1408.6
150°	1418.7	1416.9	1415.0	1413.2	1414.5	1418.5	1422.7	1426.7	1430.9	1432.4	1433.9
152.5°	1443.4	1441.3	1439.4	1437.4	1438.3	1442.2	1446.1	1450.0	1453.9	1455.5	1457.0
155°	1479.2	1477.0	1474.6	1472.3	1472.7	1475.8	1478.8	1482.0	1485.1	1486.6	1488.1
157.5°	1508.0	1506.0	1504.1	1502.1	1502.2	1504.4	1506.6	1508.7	1510.9	1512.6	1514.4
160°	1525.0	1523.4	1521.9	1520.4	1520.4	1521.9	1523.4	1525.0	1526.5	1528.0	1529.7
162.5°	1539.7	1538.2	1536.7	1535.1	1535.0	1536.3	1537.7	1539.1	1540.4	1542.1	1543.9
165°	1559.6	1558.0	1556.5	1555.0	1554.6	1555.4	1556.1	1556.9	1557.6	1559.4	1561.2
167.5°	1574.3	1572.8	1571.3	1569.7	1569.3	1570.1	1570.7	1571.5	1572.2	1574.0	1575.7
170°	1582.6	1581.1	1579.6	1578.0	1577.5	1578.0	1578.6	1579.0	1579.6	1581.4	1583.2
172.5°	1588.2	1586.7	1585.1	1583.6	1583.1	1583.6	1584.0	1584.6	1585.1	1586.9	1588.7
175°	1595.1	1593.3	1591.5	1589.7	1589.0	1589.6	1590.1	1590.6	1591.1	1592.9	1594.7
177.5°	1596.6	1595.2	1593.7	1592.2	1591.7	1591.9	1592.0	1592.2	1592.5	1593.9	1595.3
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1298.5	1303.9	1303.9	1304.7	1310.9	1310.0	1309.7
5°	1381.9	1390.1	1391.0	1399.7	1405.4	1403.5	1398.3
7.5°	1460.5	1475.7	1487.2	1493.6	1501.3	1506.0	1503.9
10°	1522.9	1545.0	1558.5	1567.6	1578.7	1586.9	1583.9
12.5°	1579.4	1605.8	1624.3	1639.9	1641.4	1651.9	1644.7
15°	1667.6	1695.5	1698.5	1710.1	1719.2	1718.2	1718.6
17.5°	1696.9	1705.8	1707.6	1707.9	1708.0	1704.6	1697.3
20°	1686.4	1683.1	1674.9	1668.7	1657.6	1656.1	1646.5
22.5°	1637.2	1626.5	1606.0	1592.4	1575.2	1570.7	1568.0
25°	1540.2	1516.6	1483.8	1452.6	1444.0	1427.1	1431.9
27.5°	1407.1	1370.4	1334.9	1309.5	1286.5	1261.3	1268.5
30°	1313.5	1272.1	1222.1	1183.6	1159.1	1135.0	1130.7
32.5°	1201.9	1141.3	1085.4	1051.6	1014.0	998.8	982.1
35°	1009.5	950.3	894.9	847.3	819.9	798.7	779.5
37.5°	836.3	768.2	723.6	684.9	665.2	653.0	656.1
40°	729.0	669.3	636.6	607.2	588.9	580.2	582.2
42.5°	642.0	597.3	570.3	550.3	537.3	532.5	531.4
45°	543.2	518.2	496.1	484.6	478.2	473.0	469.6
47.5°	475.9	455.4	443.0	436.1	430.6	425.3	425.2
50°	435.5	422.0	413.3	406.0	401.8	397.9	401.2
52.5°	404.6	392.3	383.7	377.2	375.6	372.1	372.0
55°	358.9	349.3	343.1	337.2	334.4	332.4	330.1
57.5°	317.4	308.2	302.5	298.8	293.3	291.3	290.6
60°	287.8	280.5	274.8	269.9	267.5	263.6	263.6
62.5°	260.4	253.2	247.8	244.1	240.2	238.7	239.0
65°	220.8	215.1	209.8	205.9	205.0	202.1	203.0
67.5°	184.5	180.6	175.0	173.0	171.1	169.6	168.4
70°	160.2	156.4	153.4	150.6	149.1	149.1	149.1
72.5°	139.8	135.2	133.5	129.8	130.6	129.1	127.6
75°	108.3	105.4	104.0	102.5	100.1	100.1	100.1
77.5°	79.6	78.8	77.1	75.5	74.9	74.5	74.6
80°	61.5	61.1	60.1	60.1	59.2	58.7	57.8
82.5°	47.3	46.1	45.5	45.1	45.0	44.9	44.7
85°	27.0	26.0	26.0	26.5	25.5	25.5	26.0
87.5°	15.7	16.0	15.8	15.9	16.4	16.1	16.2
90°	26.9	28.2	29.1	29.6	30.1	30.6	31.1
92.5°	28.7	29.4	29.9	30.2	30.5	30.8	31.1
95°	48.8	50.0	50.6	50.3	50.0	49.9	49.6
97.5°	63.2	64.3	64.9	65.2	65.6	65.9	66.2
100°	71.8	73.9	75.2	75.7	76.3	76.7	77.3
102.5°	75.6	78.2	79.9	80.6	81.3	82.1	82.8
105°	78.8	81.6	83.5	84.5	85.6	86.6	87.7
107.5°	89.8	87.0	86.1	87.1	88.1	89.2	90.2
110°	124.9	99.2	87.0	88.0	89.1	90.1	91.0



TEST NUMBER: P331543-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	228.6	135.1	88.7	89.5	90.4	91.1	92.0
115°	355.5	236.9	168.3	149.9	131.5	113.0	94.5
117.5°	701.8	673.2	628.5	567.9	507.3	446.7	386.0
120°	854.3	857.4	841.7	807.1	772.5	737.9	703.3
122.5°	905.1	906.9	904.5	897.8	891.1	884.4	877.6
125°	979.7	981.5	982.7	983.4	984.3	985.1	985.8
127.5°	1049.4	1052.1	1053.5	1053.6	1053.8	1053.9	1054.0
130°	1093.4	1096.2	1097.5	1097.2	1097.0	1096.7	1096.5
132.5°	1135.5	1137.9	1139.0	1138.8	1138.5	1138.2	1138.0
135°	1196.4	1199.0	1200.0	1199.5	1199.0	1198.4	1198.0
137.5°	1252.7	1255.3	1256.0	1255.2	1254.3	1253.5	1252.5
140°	1289.0	1291.4	1291.8	1290.5	1289.3	1288.0	1286.8
142.5°	1322.6	1324.6	1325.0	1323.8	1322.5	1321.2	1319.9
145°	1369.3	1371.1	1371.4	1370.1	1368.9	1367.5	1366.3
147.5°	1409.9	1411.3	1411.4	1410.3	1409.2	1408.2	1407.1
150°	1435.5	1437.0	1437.1	1435.9	1434.5	1433.2	1432.0
152.5°	1458.5	1460.1	1460.0	1458.3	1456.6	1454.9	1453.2
155°	1489.7	1491.2	1490.9	1488.8	1486.9	1484.8	1482.7
157.5°	1516.1	1517.9	1517.7	1515.7	1513.7	1511.7	1509.7
160°	1531.2	1532.7	1532.6	1530.8	1529.0	1527.2	1525.4
162.5°	1545.6	1547.4	1547.1	1544.9	1542.7	1540.5	1538.3
165°	1563.0	1564.8	1564.8	1563.0	1561.2	1559.4	1557.6
167.5°	1577.5	1579.3	1579.1	1576.8	1574.5	1572.2	1569.9
170°	1585.0	1586.8	1586.5	1584.2	1581.9	1579.6	1577.3
172.5°	1590.4	1592.2	1592.0	1589.7	1587.4	1585.1	1582.8
175°	1596.5	1598.3	1597.9	1595.3	1592.8	1590.2	1587.6
177.5°	1596.8	1598.3	1598.0	1596.2	1594.3	1592.5	1590.6
180°	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4	1593.4

(END OF REPORT)