

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P645259

Luminaire Tested: OMN4DP-SR4F0-75D835-CLB-1DUDD-WW

Issue Date: 2/16/2023



**Test Information**


Test Method: LM-79-2019  
Report Number: P645259  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-689-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DP-SR4F0-75D835-CLB-1DUDD-WW  
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE  
DOWNLIGHT - BATWING LENS - 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2788.7 lumens  
Efficiency: N/A  
Efficacy: 127.9 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 1.87 / 1.75  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P645259  
CATALOG NUMBER: OMN4DP-SR4F0-75D835-CLB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P645259

CATALOG NUMBER: OMN4DP-SR4F0-75D835-CLB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	101	101	101	99				
1	109	104	100	97	106	102	98	95	98	95	92	94	91	89	90	88	86	84				
2	99	91	85	79	97	89	83	78	86	81	76	82	78	74	79	76	73	70				
3	91	80	72	66	88	79	71	65	75	69	64	73	67	63	70	65	62	59				
4	83	71	62	56	80	70	61	55	67	60	54	65	58	53	62	57	53	51				
5	76	63	54	48	74	62	54	47	60	52	47	58	51	46	56	50	46	43				
6	70	57	48	41	68	56	47	41	54	46	41	52	45	40	50	45	40	38				
7	65	51	42	36	63	50	42	36	49	41	36	47	41	36	46	40	35	33				
8	60	47	38	32	59	46	38	32	44	37	32	43	36	32	42	36	31	29				
9	56	43	34	29	55	42	34	29	41	34	29	40	33	28	39	33	28	26				
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	25	24				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11641	11641	11641
5°	11468	12122	12828
10°	11106	13472	15369
15°	10567	15052	17518
20°	9940	16423	18785
25°	9260	17355	19417
30°	8660	18069	19727
35°	8263	18443	20061
40°	7988	18661	20322
45°	8003	18724	20331
50°	8128	18532	19753
55°	8495	18173	17937
60°	8664	16895	14567
65°	8776	14800	10697
70°	8389	11637	8313
75°	7530	8684	7006
80°	6397	6862	5616
85°	6206	5595	4668

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 20331 cd/sqm



TEST NUMBER: P645259

CATALOG NUMBER: OMN4DP-SR4F0-75D835-CLB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.9	2.7
10°-20°	245.8	8.8
20°-30°	408.3	14.6
30°-40°	515.0	18.5
40°-50°	550.6	19.7
50°-60°	485.9	17.4
60°-70°	311.9	11.2
70°-80°	138.3	5.0
80°-90°	35.9	1.3
90°-100°	9.4	0.3
100°-110°	6.0	0.2
110°-120°	4.5	0.2
120°-130°	2.9	0.1
130°-140°	0.3	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	728.0	26.1
0°-40°	1243.0	44.6
0°-60°	2279.5	81.7
0°-90°	2765.5	99.2
90°-120°	20.0	0.7
90°-150°	23.2	0.8
90°-180°	23.0	0.8
0°-180°	2788.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	721	721	721	721	721	
5°	708	729	748	773	792	66
15°	632	729	900	1009	1048	177
25°	520	705	974	1065	1090	239
35°	419	644	936	996	1018	263
45°	350	550	820	871	890	271
55°	302	433	646	649	637	268
65°	230	290	387	314	280	225
75°	121	134	139	119	112	129
85°	34	29	30	27	25	35
90°	12	12	10	10	7	8
95°	18	12	8	5	3	14
105°	12	10	5	2	0	13
115°	8	7	5	2	0	9
125°	5	5	5	2	0	5
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P645259

CATALOG NUMBER: OMN4DP-SR4F0-75D835-CLB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	721.0	721.0	721.0	721.0	721.0
2.5°	715.7	726.2	726.4	730.6	735.8
5°	707.6	728.9	747.9	773.4	791.5
7.5°	690.9	728.9	789.5	848.8	878.3
10°	677.4	729.9	821.7	901.3	937.4
12.5°	660.0	729.5	853.8	949.7	991.0
15°	632.2	728.9	900.5	1008.7	1048.0
17.5°	600.0	725.9	937.0	1045.5	1079.9
20°	578.5	722.8	955.8	1058.9	1093.3
22.5°	554.4	715.7	966.5	1065.5	1097.3
25°	519.8	705.1	974.2	1065.4	1089.9
27.5°	485.9	689.9	974.6	1051.9	1072.8
30°	464.5	677.6	969.2	1038.4	1058.1
32.5°	445.7	664.1	958.5	1022.3	1043.3
35°	419.2	643.8	935.7	996.5	1017.8
37.5°	396.4	620.7	906.8	966.1	991.0
40°	379.0	601.9	885.4	944.5	964.2
42.5°	365.6	582.0	859.9	917.6	934.7
45°	350.5	550.5	820.0	870.7	890.4
47.5°	334.4	518.0	774.0	821.9	834.7
50°	323.6	494.1	737.8	781.5	786.4
52.5°	316.9	469.1	702.9	730.5	731.4
55°	301.8	433.0	645.6	648.7	637.2
57.5°	281.7	390.9	572.8	556.4	528.9
60°	268.3	361.8	523.2	490.4	451.1
62.5°	254.9	333.9	470.9	417.8	371.9
65°	229.7	290.4	387.4	314.5	280.0
67.5°	200.6	242.5	304.2	235.2	212.3
70°	177.7	210.5	246.5	192.5	176.1
72.5°	156.3	178.6	199.5	159.1	150.6
75°	120.7	133.8	139.2	118.9	112.3
77.5°	88.9	89.5	96.6	83.8	80.5
80°	68.8	65.5	73.8	63.6	60.4
82.5°	52.7	48.1	53.7	46.2	44.3
85°	33.5	28.6	30.2	26.8	25.2
87.5°	19.8	15.9	15.4	14.0	12.1
90°	11.7	11.7	10.1	10.0	6.7
92.5°	15.8	11.8	8.7	7.3	4.0
95°	18.4	11.9	8.4	5.0	3.4
97.5°	16.4	11.5	6.4	3.3	1.7
100°	15.1	10.2	5.0	3.3	1.7
102.5°	13.8	10.1	5.0	2.0	0.3
105°	11.7	10.1	5.0	1.6	0.0
107.5°	11.4	8.5	5.0	1.6	0.0
110°	10.1	8.4	5.0	1.6	0.0



TEST NUMBER: P645259

CATALOG NUMBER: OMN4DP-SR4F0-75D835-CLB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	10.1	8.4	5.0	1.6	0.0
115°	8.4	6.7	5.0	1.6	0.0
117.5°	8.0	6.7	5.0	1.6	0.0
120°	6.7	6.7	5.0	1.6	0.0
122.5°	6.7	5.4	3.7	1.6	0.0
125°	5.0	5.0	5.0	1.6	0.0
127.5°	3.4	4.7	3.4	1.3	0.0
130°	3.4	3.4	3.4	0.0	0.0
132.5°	0.7	0.7	0.7	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)