

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331548-830

Luminaire Tested: **S122DIW-S675D1240U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331548-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1240U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6601.2 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331548-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331548-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	39	33
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	31	29	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16157	16157	16157
5°	16219	15985	16078
10°	16123	15823	15901
15°	15921	15616	15600
20°	15639	15309	15292
25°	15358	14931	14931
30°	14997	14585	14458
35°	14661	14168	13957
40°	14235	13748	13487
45°	13819	13337	13006
50°	13366	12906	12446
55°	12892	12405	11944
60°	12368	11806	11370
65°	11801	11213	10697
70°	11084	10494	9994
75°	10081	9669	9426
80°	8945	8675	8229
85°	7317	6947	6224



TEST NUMBER: P331548-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	1.4
10°-20°	264.8	4.0
20°-30°	389.2	5.9
30°-40°	452.1	6.8
40°-50°	451.6	6.8
50°-60°	393.8	6.0
60°-70°	291.2	4.4
70°-80°	164.9	2.5
80°-90°	50.1	0.8
90°-100°	91.8	1.4
100°-110°	285.0	4.3
110°-120°	487.2	7.4
120°-130°	640.7	9.7
130°-140°	719.1	10.9
140°-150°	705.1	10.7
150°-160°	591.4	9.0
160°-170°	392.2	5.9
170°-180°	137.1	2.1
0°-30°	748.0	11.3
0°-40°	1200.1	18.2
0°-60°	2045.4	31.0
0°-90°	2551.7	38.7
90°-120°	864.0	13.1
90°-150°	2928.8	44.4
90°-180°	4050.0	61.4
0°-180°	6601.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	1001	996	986	993	992	95
15°	952	946	934	938	933	268
25°	862	854	838	840	838	396
35°	744	734	719	713	708	464
45°	605	598	584	574	570	467
55°	458	452	441	430	424	409
65°	309	303	294	285	280	305
75°	162	160	155	150	151	173
85°	40	38	38	35	34	45
90°	1	17	43	40	42	5
95°	64	75	78	78	76	73
105°	263	266	269	271	271	277
115°	489	496	494	492	489	483
125°	711	721	719	715	714	635
135°	920	933	936	935	931	711
145°	1117	1126	1133	1134	1129	698
155°	1277	1281	1284	1290	1287	588
165°	1390	1388	1388	1396	1391	392
175°	1446	1442	1440	1447	1441	137
180°	1448	1448	1448	1448	1448	



TEST NUMBER: P331548-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	1005.3	1004.5	1003.6	1002.8	1001.9	1000.5	998.6	996.7	994.9	993.0	994.7
5°	1000.7	999.8	999.0	998.2	997.3	995.7	993.3	991.0	988.6	986.3	988.0
7.5°	991.8	990.5	989.2	987.9	986.6	984.7	982.3	979.9	977.5	975.1	976.8
10°	983.4	981.8	980.3	978.8	977.4	975.3	972.8	970.3	967.6	965.1	966.8
12.5°	971.9	970.5	969.1	967.8	966.5	964.6	962.0	959.4	956.9	954.3	955.5
15°	952.5	951.3	950.0	948.8	947.4	945.4	942.6	939.8	937.1	934.2	935.2
17.5°	927.9	926.6	925.4	924.1	922.8	920.8	917.9	915.1	912.3	909.5	910.5
20°	910.2	909.0	907.7	906.3	905.1	903.0	899.9	897.0	894.0	891.0	891.6
22.5°	892.5	890.7	888.9	887.1	885.3	883.1	880.2	877.4	874.6	871.8	871.9
25°	862.1	860.4	858.8	857.0	855.3	852.6	848.9	845.4	841.7	838.1	838.5
27.5°	827.5	826.0	824.4	822.8	821.3	819.2	816.2	813.4	810.5	807.7	807.0
30°	804.4	802.7	801.0	799.3	797.6	795.1	791.9	788.7	785.5	782.3	781.7
32.5°	779.8	778.4	777.0	775.6	774.3	771.9	768.5	765.2	761.8	758.4	757.2
35°	743.8	741.7	739.5	737.4	735.2	732.4	729.1	725.6	722.2	718.8	717.5
37.5°	703.1	701.3	699.4	697.5	695.7	693.0	689.6	686.2	682.8	679.3	677.7
40°	675.4	673.7	672.0	670.3	668.6	666.1	662.6	659.2	655.8	652.3	650.4
42.5°	648.6	646.8	645.1	643.4	641.7	639.1	635.7	632.3	628.9	625.5	623.3
45°	605.2	603.7	602.2	600.8	599.3	596.9	593.7	590.5	587.3	584.1	581.7
47.5°	562.1	560.7	559.3	557.9	556.5	554.1	550.7	547.4	544.1	540.7	538.3
50°	532.1	531.0	530.0	528.9	527.8	525.8	522.8	519.8	516.8	513.8	510.9
52.5°	502.8	501.4	500.0	498.6	497.2	495.1	492.3	489.5	486.6	483.8	481.4
55°	458.0	456.8	455.4	454.1	452.9	450.9	448.4	445.8	443.3	440.7	438.1
57.5°	412.9	412.0	410.9	409.9	408.9	407.0	404.2	401.3	398.5	395.7	393.1
60°	383.0	382.1	381.3	380.4	379.6	377.6	374.7	371.6	368.6	365.6	363.3
62.5°	353.7	352.3	351.0	349.6	348.3	346.4	344.1	341.8	339.5	337.1	335.0
65°	308.9	307.6	306.3	305.0	303.7	302.0	299.9	297.7	295.6	293.5	291.5
67.5°	263.3	262.2	261.2	260.1	259.1	257.7	255.7	253.8	251.9	250.0	248.5
70°	234.8	233.9	233.1	232.2	231.4	230.0	228.0	226.1	224.2	222.3	220.7
72.5°	205.6	204.6	203.8	202.9	202.1	201.0	199.8	198.6	197.4	196.0	194.6
75°	161.6	161.2	160.8	160.3	159.9	159.2	158.2	157.0	156.0	155.0	153.6
77.5°	122.4	121.7	120.9	120.2	119.5	118.9	118.5	118.0	117.6	117.2	116.6
80°	96.2	96.0	95.8	95.6	95.4	95.0	94.6	94.2	93.8	93.3	92.7
82.5°	71.6	71.5	71.5	71.4	71.4	71.3	71.0	70.8	70.5	70.2	69.5
85°	39.5	39.2	39.0	38.8	38.5	38.4	38.2	38.0	37.7	37.5	36.9
87.5°	14.1	14.4	14.7	15.0	15.4	15.9	16.8	17.6	18.5	19.3	18.8
90°	1.2	4.5	7.7	11.0	14.2	18.9	24.9	30.8	36.8	42.8	42.2
92.5°	21.8	24.1	26.6	28.9	31.3	33.2	34.6	36.0	37.4	38.8	38.9
95°	63.5	66.3	69.0	71.7	74.5	76.1	76.6	77.1	77.7	78.2	78.2
97.5°	116.1	118.5	120.9	123.3	125.6	127.3	128.4	129.4	130.4	131.5	131.5
100°	155.2	157.4	159.6	161.7	163.9	165.4	166.2	167.0	167.9	168.6	168.6
102.5°	196.2	198.0	199.7	201.5	203.2	204.6	205.7	206.7	207.7	208.8	209.0
105°	262.8	263.5	264.4	265.2	266.0	266.7	267.2	267.8	268.3	268.9	269.4
107.5°	329.7	330.9	332.2	333.3	334.5	335.1	335.1	335.1	335.1	335.1	335.4
110°	372.8	374.4	376.0	377.7	379.3	380.1	380.1	380.1	380.1	380.1	380.1



TEST NUMBER: P331548-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	419.7	421.3	422.9	424.6	426.2	426.9	426.7	426.5	426.2	426.0	425.4
115°	488.9	490.5	492.1	493.7	495.4	495.9	495.4	494.8	494.3	493.7	493.5
117.5°	557.8	560.0	562.1	564.3	566.5	566.8	565.2	563.7	562.2	560.7	560.1
120°	603.7	605.9	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7	603.7
122.5°	645.7	648.4	651.0	653.6	656.2	656.8	655.3	653.7	652.1	650.6	650.0
125°	711.2	713.7	716.1	718.6	721.0	721.9	721.0	720.3	719.4	718.6	717.8
127.5°	775.1	778.2	781.3	784.4	787.5	788.5	787.6	786.6	785.6	784.6	783.6
130°	815.2	818.7	822.3	825.8	829.2	830.8	830.3	829.7	829.2	828.6	828.0
132.5°	860.2	863.0	865.9	868.7	871.7	873.2	873.3	873.4	873.5	873.5	872.4
135°	920.3	923.2	926.2	929.3	932.3	934.0	934.5	935.1	935.7	936.1	935.9
137.5°	983.5	986.0	988.4	990.9	993.3	994.9	995.6	996.4	997.0	997.8	997.6
140°	1021.7	1024.2	1026.6	1029.1	1031.5	1033.4	1034.7	1036.1	1037.5	1038.8	1038.8
142.5°	1060.8	1063.3	1065.7	1068.2	1070.6	1072.2	1073.2	1074.1	1075.1	1076.0	1076.2
145°	1117.0	1119.0	1120.9	1122.8	1124.6	1126.4	1128.0	1129.6	1131.3	1132.9	1133.2
147.5°	1167.2	1169.4	1171.7	1174.0	1176.3	1178.0	1179.0	1180.2	1181.2	1182.3	1182.9
150°	1201.4	1203.0	1204.7	1206.3	1207.9	1209.3	1210.3	1211.4	1212.5	1213.6	1214.4
152.5°	1231.7	1233.3	1234.9	1236.5	1238.2	1239.6	1241.0	1242.3	1243.6	1244.9	1245.9
155°	1277.1	1278.0	1278.7	1279.6	1280.4	1281.2	1282.0	1282.8	1283.6	1284.5	1285.8
157.5°	1316.0	1316.5	1317.1	1317.7	1318.1	1318.7	1319.2	1319.7	1320.1	1320.7	1322.5
160°	1339.4	1340.0	1340.6	1341.1	1341.6	1342.1	1342.3	1342.6	1342.8	1343.1	1344.7
162.5°	1360.9	1361.1	1361.2	1361.3	1361.4	1361.6	1361.9	1362.2	1362.4	1362.7	1364.5
165°	1389.6	1389.3	1389.0	1388.7	1388.5	1388.4	1388.4	1388.4	1388.4	1388.4	1390.3
167.5°	1413.5	1412.7	1411.9	1411.1	1410.2	1409.9	1409.8	1409.8	1409.7	1409.6	1411.6
170°	1426.3	1425.4	1424.7	1423.8	1423.0	1422.5	1422.2	1421.9	1421.6	1421.4	1423.2
172.5°	1435.0	1434.3	1433.4	1432.6	1431.8	1431.3	1431.0	1430.7	1430.4	1430.1	1432.1
175°	1445.8	1445.0	1444.2	1443.3	1442.6	1441.9	1441.3	1440.8	1440.2	1439.6	1441.6
177.5°	1450.2	1449.5	1448.9	1448.2	1447.6	1447.1	1446.6	1446.1	1445.8	1445.3	1446.6
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331548-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	996.4	998.2	999.8	1000.5	1000.1	999.8	999.5	999.2
5°	989.7	991.4	993.1	993.7	993.3	992.9	992.5	992.0
7.5°	978.5	980.2	981.9	982.5	982.0	981.7	981.2	980.7
10°	968.5	970.3	971.9	972.4	971.9	971.2	970.5	969.9
12.5°	956.7	957.9	959.1	959.4	958.9	958.6	958.1	957.6
15°	936.0	936.9	937.7	937.6	936.5	935.5	934.4	933.3
17.5°	911.4	912.4	913.4	913.4	912.4	911.3	910.3	909.3
20°	892.3	893.0	893.5	893.4	892.6	891.7	890.9	890.0
22.5°	872.0	872.1	872.2	872.0	871.6	871.0	870.5	870.1
25°	839.0	839.3	839.8	839.8	839.3	839.0	838.5	838.1
27.5°	806.3	805.8	805.1	804.3	803.2	802.2	801.2	800.1
30°	781.0	780.3	779.7	778.9	778.1	777.2	776.4	775.5
32.5°	756.1	755.0	753.8	752.8	752.0	751.1	750.2	749.3
35°	716.2	714.9	713.6	712.5	711.4	710.3	709.3	708.1
37.5°	676.2	674.6	673.0	671.7	670.6	669.6	668.6	667.6
40°	648.6	646.6	644.7	643.3	642.4	641.6	640.7	639.9
42.5°	621.2	619.2	617.1	615.4	614.2	613.0	611.8	610.6
45°	579.4	577.0	574.7	573.1	572.2	571.4	570.5	569.6
47.5°	535.8	533.3	530.8	529.0	527.7	526.5	525.3	524.1
50°	507.8	504.8	501.8	499.8	498.7	497.7	496.6	495.5
52.5°	478.8	476.4	473.9	471.9	470.5	469.1	467.7	466.3
55°	435.5	433.0	430.5	428.6	427.5	426.5	425.4	424.3
57.5°	390.6	388.0	385.6	383.9	383.0	382.3	381.4	380.6
60°	360.9	358.5	356.2	354.8	354.1	353.5	352.8	352.1
62.5°	332.8	330.6	328.5	327.0	326.1	325.3	324.5	323.7
65°	289.6	287.7	285.8	284.3	283.2	282.1	281.1	280.0
67.5°	246.9	245.5	244.0	242.8	242.0	241.1	240.3	239.4
70°	219.2	217.8	216.3	215.1	214.2	213.4	212.5	211.7
72.5°	193.1	191.6	190.1	189.0	188.3	187.7	187.0	186.2
75°	152.3	151.1	149.8	149.4	149.8	150.2	150.6	151.1
77.5°	115.9	115.3	114.6	114.0	113.4	112.8	112.3	111.6
80°	92.1	91.4	90.8	90.2	89.8	89.4	89.0	88.5
82.5°	68.6	67.8	67.0	66.5	66.4	66.4	66.3	66.2
85°	36.3	35.6	35.0	34.5	34.3	34.1	33.9	33.6
87.5°	18.1	17.4	16.9	16.5	16.4	16.2	16.1	16.0
90°	41.7	41.2	40.6	40.4	40.7	41.0	41.3	41.6
92.5°	39.1	39.2	39.3	39.4	39.4	39.5	39.6	39.6
95°	78.2	78.2	78.2	77.9	77.4	76.8	76.3	75.8
97.5°	131.5	131.5	131.5	131.5	131.4	131.4	131.3	131.3
100°	168.6	168.6	168.6	168.5	168.2	168.0	167.7	167.4
102.5°	209.2	209.4	209.6	209.6	209.3	209.1	208.8	208.5
105°	269.9	270.5	271.1	271.4	271.4	271.4	271.4	271.4
107.5°	335.5	335.7	336.0	335.5	334.2	333.0	331.7	330.5
110°	380.1	380.1	380.1	379.7	378.9	378.1	377.2	376.5



TEST NUMBER: P331548-830

CATALOG NUMBER: S122DIW-S675D1240U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	424.7	424.0	423.4	422.8	422.2	421.6	421.0	420.4
115°	493.2	492.9	492.7	492.1	491.3	490.5	489.7	488.9
117.5°	559.4	558.7	558.1	557.4	556.6	555.7	555.0	554.1
120°	603.7	603.7	603.7	603.3	602.5	601.7	600.9	600.1
122.5°	649.4	648.8	648.1	647.4	646.9	646.2	645.6	645.1
125°	717.0	716.1	715.4	714.8	714.5	714.3	714.0	713.7
127.5°	782.7	781.7	780.7	779.8	778.9	778.1	777.2	776.3
130°	827.6	827.0	826.4	825.7	824.5	823.5	822.4	821.2
132.5°	871.2	870.0	868.8	867.8	867.0	866.0	865.2	864.3
135°	935.7	935.4	935.1	934.5	933.7	932.9	932.1	931.2
137.5°	997.3	997.1	996.9	996.3	995.1	994.1	993.0	991.9
140°	1038.8	1038.8	1038.8	1038.3	1037.2	1036.1	1035.0	1034.0
142.5°	1076.4	1076.7	1076.9	1076.4	1075.3	1074.2	1073.2	1072.0
145°	1133.5	1133.8	1134.0	1133.6	1132.6	1131.4	1130.4	1129.3
147.5°	1183.5	1184.1	1184.7	1184.5	1183.5	1182.4	1181.4	1180.3
150°	1215.2	1216.1	1216.8	1216.8	1216.1	1215.2	1214.4	1213.6
152.5°	1247.0	1247.9	1249.0	1249.0	1247.9	1247.0	1245.9	1244.9
155°	1287.2	1288.5	1289.9	1290.2	1289.4	1288.5	1287.7	1286.9
157.5°	1324.4	1326.2	1328.0	1328.3	1327.0	1325.7	1324.4	1323.0
160°	1346.4	1348.0	1349.6	1349.9	1348.9	1347.7	1346.7	1345.6
162.5°	1366.4	1368.2	1370.1	1370.4	1369.0	1367.7	1366.4	1365.2
165°	1392.1	1394.0	1396.0	1396.2	1394.9	1393.5	1392.1	1390.8
167.5°	1413.4	1415.3	1417.2	1417.5	1416.1	1414.7	1413.2	1411.8
170°	1425.1	1427.0	1429.0	1429.1	1427.5	1425.9	1424.2	1422.6
172.5°	1434.0	1435.9	1437.8	1437.8	1436.2	1434.6	1433.0	1431.3
175°	1443.5	1445.4	1447.3	1447.5	1445.8	1444.2	1442.6	1440.9
177.5°	1447.9	1449.3	1450.5	1450.5	1449.3	1447.9	1446.6	1445.3
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2

(END OF REPORT)