

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644503

Luminaire Tested: OMN4DIP-SR4F0-100D100U935-CLBOOB-1DUDD-WW

Issue Date: 2/16/2023



**Test Information**

Test Method: LM-79-2019  
Report Number: P644503  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: OMN4DIP-SR4F0-100D100U935-CLBOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE  
DOWNLIGHT - BATWING LENS - 1000 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 1000 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6774.5 lumens  
Efficiency: N/A  
Efficacy: 115.0 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 1.87 / 1.75  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 58.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P644503  
CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-CLBOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P644503

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-CLBOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	97	93	89	86	89	86	83	80	72	70	68	60	58	56	48	47	46				40	
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39				34	
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33				29	
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28				24	
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24				21	
6	62	50	42	36	57	46	39	34	39	34	30	33	29	25	27	24	21				18	
7	57	45	37	31	53	42	35	30	36	30	26	30	25	22	24	21	19				16	
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17				14	
9	49	37	30	24	45	34	28	23	30	24	20	25	21	18	20	17	15				13	
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13				11	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13611	13611	13611
5°	13408	14172	14997
10°	12985	15749	17967
15°	12354	17598	20481
20°	11622	19201	21962
25°	10826	20291	22702
30°	10125	21127	23064
35°	9660	21561	23455
40°	9339	21817	23760
45°	9355	21891	23770
50°	9505	21667	23096
55°	9934	21247	20971
60°	10130	19753	17031
65°	10262	17303	12508
70°	9810	13605	9720
75°	8808	10150	8197
80°	7476	8024	6564
85°	7262	6539	5446

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 23770 cd/sqm



TEST NUMBER: P644503

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-CLBOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.5	1.3
10°-20°	287.3	4.2
20°-30°	477.3	7.0
30°-40°	602.1	8.9
40°-50°	643.7	9.5
50°-60°	568.1	8.4
60°-70°	364.6	5.4
70°-80°	161.7	2.4
80°-90°	43.4	0.6
90°-100°	91.4	1.3
100°-110°	580.0	8.6
110°-120°	783.1	11.6
120°-130°	636.4	9.4
130°-140°	509.5	7.5
140°-150°	401.4	5.9
150°-160°	293.5	4.3
160°-170°	182.3	2.7
170°-180°	62.2	0.9
0°-30°	851.1	12.6
0°-40°	1453.2	21.5
0°-60°	2665.1	39.3
0°-90°	3234.8	47.7
90°-120°	1454.5	21.5
90°-150°	3001.8	44.3
90°-180°	3540.0	52.3
0°-180°	6774.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	843	843	843	843	843	
5°	827	852	874	904	925	78
15°	739	852	1053	1179	1225	207
25°	608	824	1139	1246	1274	280
35°	490	753	1094	1165	1190	308
45°	410	644	959	1018	1041	317
55°	353	506	755	758	745	313
65°	269	340	453	368	327	263
75°	141	156	163	139	131	151
85°	39	34	35	31	29	41
90°	14	18	20	24	20	11
95°	54	75	43	43	49	53
105°	141	208	750	953	629	150
115°	236	282	647	1335	1559	235
125°	331	375	610	1059	1250	294
135°	403	447	609	871	999	311
145°	477	517	613	758	839	300
155°	559	579	625	688	720	257
165°	621	629	642	658	670	174
175°	654	658	654	650	646	62
180°	654	654	654	654	654	



TEST NUMBER: P644503

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-CLBOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	843.0	843.0	843.0	843.0	843.0
2.5°	836.7	849.0	849.3	854.1	860.3
5°	827.3	852.2	874.4	904.3	925.3
7.5°	807.7	852.2	923.0	992.4	1026.9
10°	792.0	853.4	960.6	1053.7	1095.9
12.5°	771.6	852.9	998.3	1110.3	1158.6
15°	739.1	852.2	1052.8	1179.3	1225.3
17.5°	701.5	848.7	1095.5	1222.3	1262.5
20°	676.4	845.1	1117.5	1238.0	1278.2
22.5°	648.1	836.8	1130.0	1245.7	1282.9
25°	607.7	824.4	1139.0	1245.6	1274.3
27.5°	568.1	806.6	1139.4	1229.8	1254.3
30°	543.1	792.3	1133.2	1214.1	1237.1
32.5°	521.1	776.4	1120.6	1195.3	1219.8
35°	490.1	752.7	1093.9	1165.1	1190.0
37.5°	463.5	725.7	1060.2	1129.5	1158.6
40°	443.1	703.8	1035.1	1104.3	1127.3
42.5°	427.4	680.4	1005.3	1072.8	1092.8
45°	409.7	643.6	958.7	1018.0	1041.0
47.5°	390.9	605.6	905.0	961.0	975.9
50°	378.4	577.7	862.6	913.7	919.5
52.5°	370.5	548.4	821.8	854.0	855.2
55°	352.9	506.2	754.8	758.4	745.0
57.5°	329.4	457.0	669.7	650.5	618.3
60°	313.7	422.9	611.7	573.4	527.4
62.5°	298.0	390.4	550.5	488.5	434.8
65°	268.6	339.5	452.9	367.7	327.4
67.5°	234.5	283.5	355.6	275.0	248.2
70°	207.8	246.1	288.2	225.0	205.9
72.5°	182.7	208.8	233.3	186.0	176.1
75°	141.2	156.5	162.7	139.0	131.4
77.5°	103.9	104.7	112.9	97.9	94.1
80°	80.4	76.5	86.3	74.4	70.6
82.5°	61.6	56.2	62.7	54.1	51.8
85°	39.2	33.5	35.3	31.3	29.4
87.5°	23.1	19.3	19.7	18.9	16.6
90°	13.7	17.7	20.0	24.0	20.2
92.5°	28.3	27.7	28.3	34.1	33.5
95°	54.5	74.9	42.7	43.0	49.2
97.5°	77.6	130.6	249.3	75.2	63.6
100°	95.8	158.4	491.2	146.7	96.5
102.5°	114.0	181.3	662.2	379.3	206.8
105°	141.2	207.7	750.3	952.8	629.2
107.5°	170.4	218.5	716.5	1385.9	1296.3
110°	188.6	234.9	696.8	1456.1	1562.8



TEST NUMBER: P644503

CATALOG NUMBER: OMN4DIP-SR4F0-100D100U935-CLBOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	208.3	254.7	677.0	1415.0	1595.7
115°	236.0	282.3	647.4	1335.4	1558.7
117.5°	266.0	311.9	640.0	1249.2	1478.9
120°	287.5	331.7	626.9	1183.6	1422.9
122.5°	303.9	349.9	608.9	1127.2	1347.3
125°	330.8	375.0	610.4	1059.1	1250.2
127.5°	352.7	399.2	609.3	979.7	1168.8
130°	365.8	414.1	612.6	925.3	1106.3
132.5°	379.1	427.4	609.4	901.6	1050.3
135°	403.0	447.3	608.7	870.7	999.3
137.5°	423.6	471.0	608.7	836.5	946.7
140°	440.0	484.3	608.7	816.6	917.1
142.5°	456.5	497.5	611.9	793.4	887.5
145°	477.1	517.3	612.8	758.5	839.0
147.5°	501.7	537.1	617.7	733.4	795.4
150°	518.2	550.4	621.0	716.8	769.0
152.5°	534.6	563.6	621.0	703.4	746.0
155°	559.3	579.4	625.1	687.5	719.7
157.5°	579.0	598.3	630.0	677.5	700.8
160°	592.2	608.3	633.3	670.8	690.9
162.5°	602.1	618.2	636.6	667.4	681.0
165°	621.0	629.0	641.6	658.3	670.3
167.5°	631.7	638.9	645.7	654.1	661.3
170°	641.6	645.6	645.7	654.0	658.0
172.5°	644.8	652.1	649.0	650.7	654.7
175°	653.9	657.9	653.9	649.7	645.7
177.5°	653.9	657.1	653.9	653.8	650.6
180°	653.9	653.9	653.9	653.9	653.9

(END OF REPORT)